



INDUCTIVE PROXIMITY SENSORS



INDUCTIVE PROXIMITY SENSORS





Ordering information

Туре	Part no.
IH06-04NNS-VTK	6025883

Other models and accessories → www.sick.com/IMM

Detailed technical data

Features

Housing	Cylindrical
Housing	Short-body
Diameter	Ø 6.5 mm
Sensing range S _n	4 mm
Safe sensing range S _a	3.24 mm
Installation type	Non-flush
Switching frequency	2,500 Hz
Connection type	Connector M8, 3-pin
Switching output	NPN
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP67 ¹⁾

 $^{\mbox{1})}$ According to EN 60529.

Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	< 10 % ¹⁾
Voltage drop	$\leq 2 V^{2}$
Time delay before availability	≤ 50 ms
Hysteresis	1 % 20 %
Reproducibility	$\leq 5 \%^{(3)(4)}$
Temperature drift (of S _r)	± 10 %
EMC	EN 60947-5-2 IEC 61000-4-2: (Testlevel 2)

 $^{1)}$ Of $V_{\mbox{S}}.$

 $^{2)}$ With Ia = 200 mA.

 $^{\rm 3)}$ Supply voltage U_B and constant ambient temperature Ta.

⁴⁾ Of Sr.

INDUCTIVE PROXIMITY SENSORS

	IEC 61000-4-4: (Testlevel 3)
Continuous current I _a	≤ 200 mA
Short-circuit protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Ambient operating temperature	-25 °C +70 °C
Housing material	Stainless steel V2A, DIN 1.4305 / AISI 303
Sensing face material	Plastic, POM
Housing length	40 mm
UL File No.	NMFT2.E175606

 $^{1)}$ Of V_S.

 $^{2)}$ With Ia = 200 mA.

 $^{3)}\,\mbox{Supply voltage U}_B$ and constant ambient temperature Ta.

 $^{4)}$ Of Sr.

Reduction factors

Note	The values are reference values which may vary
Stainless steel (V2A, 304)	Approx. 0.77
Aluminum (AI)	Approx. 0.47
Copper (Cu)	Approx. 0.42
Brass (Br)	Approx. 0.52

Installation note

Remark	Associated graphic see "Installation"
A	6.5 mm
В	13 mm
С	6.5 mm
D	12 mm
E	8 mm
F	32 mm

Classifications


ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714

INDUCTIVE PROXIMITY SENSORS

ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230


Installation note

Non-flush installation




Connection diagram

Cd-002



Dimensional drawing (Dimensions in mm (inch))

Short-body, non-flush, connector







INDUCTIVE PROXIMITY SENSORS

Recommended accessories

Other models and accessories -> www.sick.com/IMM

	Brief description	Туре	Part no.	
Terminal and	Ferminal and alignment brackets			
	Plastic (PA6), without mounting hardware	BEF-KH-M06	2101067	
Others				
×.	 Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U13- 020VA1XLEAX	2095860	
N e	 Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U13- 050VA1XLEAX	2095884	
×.	 Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U13- 100VA1XLEAX	2095885	
5	 Connection type head A: Female connector, M8, 3-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YG8U13- 020VA1XLEAX	2096165	
5	 Connection type head A: Female connector, M8, 3-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YG8U13- 050VA1XLEAX	2096166	
3	 Connection type head A: Female connector, M8, 3-pin, angled, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YG8U13- 100VA1XLEAX	2096209	
	 Connection type head A: Male connector, M8, 3-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0803-G	6037322	
	 Connection type head A: Female connector, M8, 3-pin, straight, A-coded Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	DOS-0803-G	7902077	
×,	 Connection type head A: Female connector, M8, 3-pin, angled, A-coded Description: Unshielded Connection systems: Solder connection Permitted cross-section: ≤ 0.25 mm² 	DOS-0803-W	7902078	

INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
10 PG	 Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Male connector, M12, 3-pin, straight, A-coded Signal type: Sensor/actuator cable Cable: 2 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U13- 020VA1M2A13	2096605
10 Kg	 Connection type head A: Female connector, M8, 3-pin, straight, A-coded Connection type head B: Male connector, M12, 3-pin, straight, A-coded Signal type: Sensor/actuator cable Cable: 5 m, 3-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U13- 050VA1M2A13	2096606

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

