

# TMM22E-PLH090

TMS/TMM22

**INCLINATION SENSORS** 





#### Illustration may differ

## Ordering information

Туре	Part no.
TMM22E-PLH090	1116337

Other models and accessories → www.sick.com/TMS\_TMM22



#### Detailed technical data

#### Performance

Number of axis	2
Measuring range	± 90°
Resolution	≤ 0.015°
Static measurement accuracy	Typ. 0.25°, max. 0.6° <sup>1)</sup>
Repeatability	30 mV <sup>2)</sup>
Compensated cross-sensitivity (2-dimensional)	Typ. ± 0.5°, max. ± 0.9°
Temperature coefficient (zero point)	±0.03°/K <sup>3)</sup>
Limit frequency	2 Hz
Sampling rate	400 Hz

<sup>1)</sup> In accordance with DIN ISO 1319-1, position of the upper and lower error limit depends on the installation situation, specified value refers to a symmetrical position, i.e. deviation in upper and lower direction is the same.

#### Interfaces

Communication interface	Analog / Voltage
Voltage output	0 V 10 V
0-set function via hardware pin	<b>√</b>
Load resistance	≥ 2 kΩ
Status information	
LED	2x (green/red)
Output signal (error state)	0 V
Initialization time	250 ms

## Electrical data

Connection type	Cable, 5-wire, with male connector, M12, 5-pin, 0.3 m		
Supply voltage	12 V DC 30 V DC		
Current consumption	< 30 mA @ 24 V		
Reverse polarity protection	<b>√</b>		

<sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

 $<sup>^{2)}</sup>$  In accordance with DIN ISO 55350-13; 68.3% of the measured values are inside the specified area.

 $<sup>^{\</sup>rm 3)}$  68.3% of the measured values are inside the specified area.

Short-circuit protection of the outputs	✓
MTTFd: mean time to dangerous failure	961 years (EN ISO 13849-1) 1)

<sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

#### Mechanical data

Dimensions	38.8 mm x 30 mm x 10.4 mm		
Weight	Approx. 60 g		
Housing material	Plastic (PA12), glass-fiber reinforced		
Material, cable	PUR		


### Ambient data

EMC	EN 61326-1
Enclosure rating	IP66, IP67, IP68, IP69K
Operating temperature range	-40 °C +80 °C
Storage temperature range	-40 °C +85 °C
Resistance to shocks	100 g, 6 ms (EN 60068-2-27)
Resistance to vibration	10 g, 10 Hz 2,000 Hz (EN 60068-2-6)

#### Classifications

ECLASS 5.0	27270790
ECLASS 5.1.4	27270790
ECLASS 6.0	27270790
ECLASS 6.2	27270790
ECLASS 7.0	27270790
ECLASS 8.0	27270790
ECLASS 8.1	27270790
ECLASS 9.0	27270790
ECLASS 10.0	27271101
ECLASS 11.0	27271101
ECLASS 12.0	27271101
ETIM 5.0	EC001852
ETIM 6.0	EC001852
ETIM 7.0	EC001852
ETIM 8.0	EC001852
UNSPSC 16.0901	41111613

## Dimensional drawing (Dimensions in mm (inch))



## PIN assignment



PIN Male connector M12, 5-pin	Wire colors (cable connection)	Signal TMS22E	Signal TMM22E
1	Brown	Us	Us
2	White	Z-axis	Y-axis
3	Blue	GND	GND
4	Black	n.c.	X-axis
5	Gray	TEACH 1)	TEACH 1)
		1)	
To activate the zero point setting, connect TEACH (pin 5) to GND (pin 3) for at least 1 second.			

### Recommended accessories

Other models and accessories → www.sick.com/TMS\_TMM22

	Brief description	Туре	Part no.
Others			
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 1.5 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, shielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF2A25- 015UB6XLEAX	2095833
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 3 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, shielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF2A25- 030UB6XLEAX	2095834
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, shielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF2A25- 050UB6XLEAX	2095733
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 3 m, 5-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, shielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YG2A25- 030UB6XLEAX	2095791
	Connection type head A: Male connector, M12, 5-pin, straight, A-coded     Description: Unshielded, Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -     Connection systems: Screw-type terminals     Permitted cross-section: ≤ 0.75 mm²     Note: For field bus technology	STE-1205-G	6022083
	Connection type head A: Female connector, M12, 5-pin, straight, A-coded     Description: Unshielded, Head A: female connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -     Connection systems: Screw-type terminals     Permitted cross-section: ≤ 0.75 mm²	DOS-1205-G	6009719

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

