

## IM18-12NPS-ZC1

**IM Standard** 

**INDUCTIVE PROXIMITY SENSORS** 





#### Ordering information

Туре	Part no.
IM18-12NPS-ZC1	7900097

Other models and accessories → www.sick.com/IM\_Standard

Illustration may differ



#### Detailed technical data

#### **Features**

Housing	Metric
Housing	Standard design
Thread size	M18 x 1
Diameter	Ø 18 mm
Sensing range S <sub>n</sub>	12 mm
Installation type	Non-flush
Switching frequency	300 Hz
Connection type	Male connector M12, 4-pin
Switching output	PNP
Output function	NO
Electrical wiring	DC 3-wire
Enclosure rating	IP67 <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> According to EN 60529.

#### Mechanics/electronics

Supply voltage	10 V DC 30 V DC
Ripple	≤ 10 %
Voltage drop	$\leq$ 1 V $^{1)}$
Time delay before availability	≤ 100 ms
Hysteresis	2 % 15 %
Reproducibility	≤ 5 % <sup>2) 3)</sup>
Temperature drift (of S <sub>r</sub> )	± 10 %
EMC	According to EN 60947-5-2

<sup>1)</sup> At I may

 $<sup>^{\</sup>rm 2)}$  Supply voltage  $\rm U_B$  and constant ambient temperature Ta.

<sup>3)</sup> Of Sr.

Continuous current I <sub>a</sub>	≤ 400 mA
Short-circuit protection	<b>√</b>
Power-up pulse protection	✓
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Ambient operating temperature	-25 °C +70 °C
Housing material	Brass, Nickel-plated brass
Sensing face material	Plastic
Housing length	64 mm
Thread length	40 mm
Tightening torque, max.	≤ 30 Nm

<sup>1)</sup> At Ia max

#### Safety-related parameters

MTTF <sub>D</sub>	93 years
DC <sub>avg</sub>	0 %

#### Installation note

Remark	Associated graphic see "Installation"
A	18 mm
В	36 mm
c	18 mm
D	36 mm
E	16 mm
F	96 mm

#### Classifications


ECLASS 5.0	27270101
ECLASS 5.1.4	27270101
ECLASS 6.0	27270101
ECLASS 6.2	27270101
ECLASS 7.0	27270101
ECLASS 8.0	27270101
ECLASS 8.1	27270101
ECLASS 9.0	27270101
ECLASS 10.0	27270101
ECLASS 11.0	27270101
ECLASS 12.0	27274001
ETIM 5.0	EC002714
ETIM 6.0	EC002714
ETIM 7.0	EC002714
ETIM 8.0	EC002714
UNSPSC 16.0901	39122230


 $<sup>^{\</sup>rm 2)}$  Supply voltage  $\rm U_B$  and constant ambient temperature Ta.

<sup>&</sup>lt;sup>3)</sup> Of Sr.

#### Installation note

Non-flush installation







#### Connection type




#### Connection diagram



#### Cd-007




#### Response diagram



Distance of target edge to center of active face in mm (inch)

All dimensions in mm (inch)

#### Dimensional drawing (Dimensions in mm (inch))



- ① Connection
- ② Display LED
- ③ Fastening nuts (2x); width across 24, metal

#### Recommended accessories

Other models and accessories → www.sick.com/IM\_Standard

Mounting bra	ackets and plates			
ززن	Mounting plate for M18 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M18	5321870	
40	Mounting bracket for M18 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M18	5308446	
Terminal and	Ferminal and alignment brackets			
	Clamping block for round sensors M18, without fixed stop, plastic (PA12), glass-fiber reinforced, mounting hardware included	BEF-KH-M18	2051481	
Others				
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm 6.5 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	DOS-1204-W	6007303	
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	DOS-1204-G	6007302	
	<ul> <li>Connection type head A: Male connector, M12, 4-pin, straight, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	STE-1204-G	6009932	
	<ul> <li>Connection type head A: Male connector, M12, 4-pin, angled, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	STE-1204-W	6022084	
· ·	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 020VB3XLEAX	2096234	
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 050VB3XLEAX	2096235	
3	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14- 020VB3XLEAX	2095895	
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YG2A14- 050VB3XLEAX	2095897	

# IM18-12NPS-ZC1 | IM Standard INDUCTIVE PROXIMITY SENSORS

	Brief description	Туре	Part no.
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Note: Only suitable for PNP sensors</li> <li>Application: Zones with chemicals</li> </ul>	YI2A14- 020VB3XLEAX	2096222
13	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Note: Only suitable for PNP sensors</li> <li>Application: Zones with chemicals</li> </ul>	YI2A14- 050VB3XLEAX	2096223

#### SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

### **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

