



SICK Sensor Intelligence.

**3D MACHINE VISION** 

**3D MACHINE VISION** 



## Ordering information

Туре	Part no.
V3T13P-MR62A8	1091320

Other models and accessories -> www.sick.com/TriSpectorP1000



#### Detailed technical data

Features

Task	Detecting - Standard objects Detecting - Level Measuring - Dimension, contour and volume Measuring - Number Monitoring and controlling - Quality Determining position - 3D position determination
Technology	3D triangulation
Product category	Programmable
Toolkit	SICK algorithm API HALCON
Working distance	291 mm 1,091 mm
Example field of view	540 mm x 200 mm
Illumination	Integrated
Illumination color	Red, laser, Visible, 660 nm, ± 7 nm
Laser class	2 (EN 60825-1:2014+A11:2021; IEC 60825-1:2014, Complies with the FDA performance re- quirements for laser products except for conformance with IEC 60825-1 Ed.3., as described in Laser Notice 56 dated May 8, 2019.)
Factory calibrated	✓
Width at minimum operating distance	180 mm
Width at maximum operating distance	660 mm
Maximum height range	800 mm
Imaging angle	67°
Offline support	Emulator
Mechanics/electronics	
Connection type	M12, 12-pin male connector, A-coded (voltage supply, I/O) M12, 8-pin socket, X-coded (Gigabit Ethernet) M12, 8-pin female connector, A-coded (encoder)
Connector material	Nickel plated brass


**3D MACHINE VISION** 

Supply voltage	24 V, ± 20 %
Ripple	< 5 V <sub>pp</sub>
Power consumption	≤ 11 W
Current consumption	< 400 mA, without output load
Enclosure rating	IP67
Protection class	III
Housing material	Anodized aluminum
Window material	PMMA
Weight	1.7 kg
Dimensions (L x W x H)	307 mm x 62 mm x 84 mm
Performance	
Scan/frame rate	5,000 3D profiles/s
Maximum number of profiles	2,500 Per image
Data points/profile	1,536
Height resolution	80 μm 670 μm
3D profile resolution	0.43 mm/px
Interfaces	
Ethernet	✓, TCP/IP
Function	FTP, HTTP
Data transmission rate	≤ 1,000 Mbit/s
Serial	✓, RS-232, RS-422
Operator interfaces	Web server
Configuration software	SICK AppStudio
Digital input	3 inputs
Configurable outputs	4 inputs/outputs
Encoder interface	RS-422 / TTL
Maximum encoder frequency	300 kHz
Ambient data	
Electromagnetic compatibility (EMC)	EN 61000-6-2:2005 / EN 61000-6-3:2007
Shock load	15 g / 6 ms (EN 60068-2-27)
Vibration load	5 g, 10 Hz 150 Hz (EN 60068-2-6)
Ambient operating temperature	0 °C +50 °C
Storage temperature	-20 °C +70 °C
Classifications	
ECLASS 5.0	27310205
ECLASS 5.1.4	27310205
ECLASS 6.0	27310205
ECLASS 6.2	27310205
ECLASS 7.0	27310205
ECLASS 8.0	27310205
ECLASS 8.1	27310205

**3D MACHINE VISION** 

ECLASS 9.0	27310205
ECLASS 10.0	27310205
ECLASS 11.0	27310205
ECLASS 12.0	27310205
ETIM 5.0	EC001820
ETIM 6.0	EC001820
ETIM 7.0	EC001820
ETIM 8.0	EC001820
UNSPSC 16.0901	43211731


#### Dimensional drawing (Dimensions in mm (inch))



- ① Connector Encoder (thread inside)
- ② Connector Gigabit Ethernet (Gig E)
- ③ Connector Power I/O (thread inside)
- ④ LED; On
- ⑤ LED; State
- 6 LED; Link/Data
- ⑦ LED; Result
- 8 LED; Laser
- ③ Fastening threads (M5 x 8.5 mm length)
- 1 Optical receiver (center)
- ① Optical sender (center)
- 12 Micro SD memory card


## Field of view

# TriSpectorP1060



660 (25.98)


4



**3D MACHINE VISION** 

#### **Overview**

SICK AppSpace



## **Recommended accessories**

Other models and accessories → www.sick.com/TriSpectorP1000

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Mounting bracket set consisting of mounting bracket, cooling plate, includes angle display for setting the tilt angle	Mounting bracket	2076735
Others			
	<ul> <li>Connection type head A: Male connector, M12, 5-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 2 m</li> <li>Description: Shielded</li> <li>Connection systems: Flying leads</li> </ul>	Connecting cable	6024860

# V3T13P-MR62A8 | TriSpectorP1000 3D MACHINE VISION

	Brief description	Туре	Part no.
	<ul> <li>Connection type head A: Female connector, M12, 12-pin, straight</li> <li>Connection type head B: Male connector, M12, 5-pin, straight</li> <li>Signal type: Power</li> <li>Cable: 0.25 m</li> <li>Description: Power, Cable for connecting a TriSpector to power supply unit 2079609</li> </ul>	YF2A6B- C25XXXM2A15	2079766
100	<ul> <li>Connection type head A: Female connector, M12, 8-pin, straight, A-coded</li> <li>Connection type head B: Male connector, M12, 8-pin, straight, A-coded</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 8-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, shielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation</li> </ul>	YF2A28- 020UA6M2A28	2096105
	<ul> <li>Connection type head A: Male connector, M12, 8-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 8-wire, PVC</li> <li>Description: Sensor/actuator cable, shielded</li> <li>Application: Zones with chemicals</li> </ul>	YM2A28- 050VA6XLEAX	2096233
11	<ul> <li>Connection type head A: Male connector, M12, 8-pin, straight, X-coded</li> <li>Connection type head B: Male connector, RJ45, 8-pin, straight</li> <li>Signal type: Ethernet, Gigabit Ethernet</li> <li>Cable: 2 m, 8-wire, PUR, halogen-free</li> <li>Description: Ethernet, Gigabit Ethernet, shielded</li> <li>Application: Zones with oils and lubricants</li> </ul>	YM2X18- 020EG1MRJA8	2106258
Incremental e	ncoders		
fe	<ul> <li>Mechanical design: Solid shaft face mount flange 10 mm x 19 mm</li> <li>Communication interface: 4.5 V 32 V, TTL, HTL, programmable</li> <li>Connection type: Male connector, M12, 8-pin, radial</li> <li>Pulses per revolution: 10,000</li> </ul>	DFS60B-S4PC10000	1036721

#### **Recommended services**

Additional services -> www.sick.com/TriSpectorP1000

	Туре	Part no.
Extended warranty		
<ul> <li>Product area: Machine vision, LiDAR sensors, safety camera sensors, Safety laser scanners, Safety radar sensors, Radar sensors, Fixed mount barcode scanners, Image-based code readers, RFID, Mobile handheld scanners</li> <li>Range of services: The services correspond to the scope of the statutory manufacturer warranty (SICK general terms of delivery).</li> <li>Duration: Five-year warranty from delivery date.</li> </ul>	Extended warranty for a total of five years from delivery date	1680671

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

