

# **ENCODERS**

Incremental encoders, absolute encoders, safety encoders, linear encoders, wire draw encoders



#### REGISTER AT WWW.SICK.COM NOW TO ENJOY ALL OF THESE BENEFITS



- Select products, accessories, documentation and software simply and quickly.
- Create, save and share personalized wish lists.
- See the net price and delivery date for each product.
- Simple quote request, ordering and delivery tracking.
- ✓ Overview of all quotes and orders.
- Direct ordering: even large orders can be placed quickly.
- View the status of quotes and orders at any time. Notification by e-mail in the event of status changes.
- Easily reuse previous orders.
- Convenient export of quotes and orders in the right format for your systems.

#### Product family overview

Incremental encoders	
DBS36 Core	→ F-82
DBS50 Core	→ F-98
DKS40	→ F-110
DBS60 Core	→ F-120
DFS60	→ F-162
DGS34/DGS35	→ F-192
DKV60 measuring wheel encoder	→ F-202
DFV60 measuring wheel encoder	→ F-210

Absolute encoders	
AHS36/AHM36 SSI	→ G-232
AHS36/AHM36 CANopen	→ G-252
AFS60/AFM60 SSI	→ G-268
AFS60/AFM60 EtherNet/IP	→ G-312
AFS60/AFM60 PROFINET	→ G-332
AFS60/AFM60 EtherCAT®	→ G-352
A3M60 PROFIBUS	→ G-372
ATM60 PROFIBUS	→ G-386
ATM60 SSI	→ G-398
ATM60 CANopen	→ G-412
ATM60 DeviceNet	→ G-424
ATM90 SSI	→ G-436
ATM90 PROFIBUS	→ G-444
ARS60 SSI/Parallel	→ G-454
ACS36/ACM36 Analog	→ G-474
ACM60 Analog	→ G-482

Safety encoders	
DFS60S Pro	→ H-496

Wire draw encoders	
EcoLine (BCG, PFG)	→ I-528
Compact (BKS, XKS, PKS)	→ I-576
HighLine (BTF, PRF)	→ I-590

Linear encoders	
KH53	→ J-644
TTK70	→ J-660

Accessories	
Connection and mounting systems	→ K-668

Appendix	
Glossary	→ L-775



### HIGH-SPEED ETHERNET ENCODERS

#### Intelligent, powerful, precise

The trend in the market is moving more and more towards industrial Ethernet-based fieldbus systems – rapid technical developments such as fast Ethernet, dual-port switches and full-duplex transmission have turned the original Ethernet into a powerful communication system. The advantages resulting from the use of industrial Ethernet-based fieldbuses will make these networks a future standard in factory, logistics and process automation.

As a trendsetter, SICK has therefore expanded its tried and tested AFS/AFM60 absolute singleturn and multiturn encoders with the three most popular Ethernet variants: **PROFINET**, **EtherCAT®** and **EtherNet/IP**.

# SICK CONNECTS – ORIGINAL CONNECTION AND MOUNTING SYSTEM FOR ENCODERS



A perfectly configured connection and mounting system is essential for the optimal integration of encoders.

Only reliable mechanical installation and signal transmission guarantee the best possible measurement results. Furthermore, high-quality components with a long service life help reduce costs in the long term.

		GENERAL INFORMATION About SICK	A
		INDUSTRIAL COMMUNICATION	В
		PROGRAMMING SOLUTIONS	C
		TYPICAL APPLICATIONS	D
		ENCODER SELECTION GUIDE	E
		INCREMENTAL ENCODERS  DBS36, DBS50, DKS40, DBS60, DFS60, DGS34/DGS35, DKV60, DFV60	F
(a) (b) (b) (c) (c) (c) (c) (c) (c) (c) (c) (c) (c	(a) \$ (a)	ABSOLUTE ENCODERS  AHS36/AHM36, AFS60/AFM60, A3M60, ATM60, ATM90, ARS60, ACS36/ACM36, ACM60	G
	<b>&amp;</b>	SAFETY ENCODERS DFS60S Pro	н
	° Company	WIRE DRAW ENCODERS EcoLine, Compact, HighLine	1
		LINEAR ENCODERS KH53, TTK70	J
		ACCESSORIES	K
		APPENDIX Glossary	L

### SENSOR INTELLIGENCE IS A PROMISE

At SICK, sensor solutions are developed for industrial automation with commitment and experience. From development to service provision: every employee is completely committed to ensuring that sensors and application solutions from SICK optimally fulfill their versatile functions.

#### Company with a culture of success

With a variety of products and services, approximately 7,000 employees help SICK sensor technology users to increase their productivity and reduce their costs. Founded in 1946, the company has its headquarters in Waldkirch, Germany, and with more than 50 subsidiaries and equity investments, in addition to numerous agencies, it is globally active.

People like working at SICK. This is demonstrated by the accolades that the company is regularly awarded in the "Great Place to Work" competition. This lively corporate culture holds strong appeal for qualified and skilled persons. In SICK, they are part of a company that ensures an excellent balance between career progression and quality of life.



#### Innovation creates competitive advantage

SICK sensors simplify procedures and optimize processes to achieve sustainable production. To do this, SICK has research and development facilities in many locations across the globe. In discussion with its customers and in cooperation with higher education institutions, innovative sensor products and solutions are developed. These form the basis for reliable process control, personal protection and environmentally friendly production.

#### Model with a far-reaching effect

SICK builds upon an established corporate culture, pursuing financial independence and technological transparency. Innovation has made SICK into one of the technological and market leaders. Because it is only with targeted modernization and improvement that universally applicable sensors can be successful in the long term.







# SENSOR INTELLIGENCE FOR ALL REQUIREMENTS

SICK has representation in numerous fields and is therefore familiar with the processes used in a wide range of industry branches. Fundamental requirements such as precision, speed and availability apply globally, but must be implemented differently according to the branch in question.

#### For applications all over the world

Hundreds of thousands of installations and implemented applications prove it: SICK understands the industries and their processes. And that is not going to change – in the application centers in Europe, Asia and North America, sensors and system

solutions are designed, tested and optimized in accordance with customer specifications. This contributes to the company's position as a reliable supplier and development partner.









#### For industries with specific dynamics

Where the demands for quality and productivity rise in parallel, industries profit from SICK's profound knowledge and expertise in the relevant sectors. In addition to the automotive and pharmaceutical industries, this also applies to the electronics and solar sectors. SICK provides productive solutions for accident prevention in automated guided vehicles and increases the throughput speed and traceability in warehouses and distribution centers. For protection of the environment and process optimization in cement production, waste incineration or in power stations,

SICK can offer system solutions for gas analysis and flow volume measurement. Gas distribution networks use the high-precision gas meters manufactured by SICK.

#### For better results in all fields

Every field has special procedures. And yet, in principle, the tasks of the sensors are identical: measurement, detection, checking and monitoring, securing, linking, and integrating, identifying and positioning. This puts the SICK specialists in the position to provide successful solutions industry-wide for other industrial automation applications.

→ www.sick.com/industries










# SERVICES FOR MACHINES AND SYSTEMS: SICK LifeTime Services

From system planning to upgrade services, SICK LifeTime Services provide a high quality of service all over the world. These services enhance personal safety and increase machine and system productivity to provide a solid foundation for a sustainable business operation. Available services range from product-independent consultations to traditional product service offerings. They are characterized by SICK's extensive industry knowledge and more than 60 years of experience.









#### Consulting and design

- Plant walk-through
- Risk assessment
- · Safety concept
- Safety software and hardware design
- Validation of functional safety
- CE-conformance check







#### Product and system support

- Installation
- Commissioning
- Start-up support
- Calibration
- Telephone support
- 24-hour helpline
- SICK Remote Service
- Troubleshooting on site
- Repairs
- Exchange units
- Extended warranty





#### Verification and optimization

- Inspection
- Stop time measurement
- Machine safety inspection
- Electrical equipment check
- Accident investigation
- Initial verification
- Performance check
- Maintenance





#### Upgrade and retrofits

• Upgrade services



#### Training and education

- Training
- Seminars
- · Web training



# WIDE PRODUCT SPECTRUM FOR INDUSTRIAL AUTOMATION

From simple detection tasks to sophisticated sensors in a complex production process: every product in SICK's wide portfolio offers a sensor solution that optimally combines economy and safety.

→ www.sick.com/products

#### Photoelectric sensors

- MultiTask photoelectric sensors
- · Miniature photoelectric sensors
- · Small photoelectric sensors
- Compact photoelectric sensors
- Cylindrical photoelectric sensors
- · Fiber-optic sensors and fibers



#### **Proximity sensors**

- · Inductive proximity sensors
- · Capacitive proximity sensors
- · Magnetic proximity sensors



#### Magnetic cylinder sensors

- Analog positioning sensors
- · Sensors for T-slot cylinders
- · Sensors for C-slot cylinders
- Sensor adapters for other cylinder types



#### Registration sensors

- Contrast sensors
- Markless sensors
- Color sensors
- Luminescence sensors
- Fork sensors
- Array sensors
- · Registration sensors



#### Automation light grids

- Measuring automation light grids
- Switching automation light grids



#### Opto-electronic protective devices

- · Safety laser scanners
- · Safety light curtains
- Safety camera systems
- Multiple light beam safety devices
- Single-beam photoelectric safety switches
- Mirror columns and device columns



#### Safety switches

- · Electro-mechanical safety switches
- · Non-contact safety switches
- · Safety command devices



#### sens:Control - safe control solutions

- · Safety controllers
- · Safe sensor cascades
- · Safety relays



#### Gas analyzers

- Gas transmitters
- In-situ gas analyzers

• Extractive gas analyzers



#### Dust measuring devices

- Scattered light dust measuring devices
- Transmittance dust measuring devices
- Gravimetric dust measurement devices



#### **Analyzer solutions**

CEMS solutions

· Process solutions





#### Traffic sensors

- · Tunnel sensors
- · Overheight detectors
- Visual range measuring devices



#### Ultrasonic gas flow measuring devices

- Volume flow measuring devices
- · Mass flow measuring devices
- Flow velocity measuring devices
- · Gas flow meters
- · Flow computers



#### Motor feedback systems

- Motor feedback system rotary HIPERFACE®
- Motor feedback system rotary HIPERFACE DSL®
- Motor feedback system rotary incremental
- Motor feedback system rotary incremental with commutation
- Motor feedback system linear HIPERFACE®



#### **Encoders**

- · Absolute encoders
- Incremental encoders
- Linear encoders

- · Wire draw encoders
- · Safety encoders



#### Identification solutions

- Bar code scanners
- Image-based code readers
- Hand-held scanners
- RFID



#### Vision

- Vision sensors
- · Smart cameras

· 3D vision sensors



#### Distance sensors

- Short range distance sensors (displacement)
- Mid range distance sensors
- Long range distance sensors
- Linear measurement sensors
- Ultrasonic sensors
- Optical data transmission
- Position finders



#### Detection and ranging solutions

• 2D laser scanners

• 3D laser scanners



#### Fluid sensors

- Level sensors
- Pressure sensors

- Flow sensors
- · Temperature sensors



#### System solutions

- Customized analyzer systems
- Collision awareness systems
- Flexible automation systems
- · Object detection systems
- Profiling systems
- · Quality control systems
- · Security systems
- · Track and trace systems






# Industrial communication

Innovation is our driving force

With customer-oriented products and innovations, SICK has for five decades been a trendsetter and indispensable partner for industry. The complex, high-tech encoders and motor feedback systems measure angles, positions and speeds all over the world.

With the SSI interface and universal HIPERFACE® and HIPERFACE DSL® interfaces for motor feedback systems, SICK sets global standards.



Expertise with interfaces is part of our tradition – SICK has regularly been setting trends in this field for many years:

1985 – With the patented synchronous serial interface (SSI), SICK-STEGMANN GmbH created an interface which established itself as an undisputed standard in industrial environments.

With the innovative universal HIPERFACE® interface, SICK-STEGMANN set another global standard in 1996: There was now only one interface on the speed controller for all applications and only one type of signal line between the speed controller and feedback system.

2011 – HIPERFACE® goes digital: With HIPERFACE DSL®, technology leader SICK presents a purely digital protocol that uses a minimum of connection cables between the frequency converter and motor feedback system.

The result: HIPERFACE DSL®. This "digital servo link" interface enables an entirely new architecture for the servo drive with completely new options, as it is now purely digital instead of hybrid (analog/digital).

With SSI and HIPERFACE® we have succeeded in setting new industry standards. And HIPERFACE DSL® is currently in the process of establishing itself as a premium system.

In the open world of bus technology as well, our encoders offer a complete range.

The trend in the market is moving more and more towards industrial Ethernet-based fieldbus systems – rapid technical developments such as fast Ethernet, dual-port switches and full-duplex transmission have turned the original Ethernet into a powerful communication system. The advantages resulting from the use of industrial Ethernet-based fieldbuses will make these networks a future standard in factory, logistics and process automation.

As a trendsetter, SICK has therefore expanded its tried and tested AFS60/AFM60 absolute singleturn and multiturn encoders with the three most popular Ethernet variants - PROFINET, EtherCAT® and EtherNet/IP.

In addition to a wide range of diagnostic functions, the Ethernet-based encoders are also equipped with a web server and an FTP server. This enables users to make simple parameter settings and update all Ethernet encoders with the latest device firmware.

In addition to its own industry standards SSI, HIPERFACE® and HIPERFACE DSL®, SICK also supports standardized Ethernet and fieldbus systems.





#### **SICK standards**







**SSI** – With the patented synchronous serial interface (SSI), SICK-STEGMANN GmbH has created an interface which offers users a range of advantages.

This synchronous serial interface is used in both singleturn and multiturn encoders. HIPERFACE® motor feedback systems are used as a standard interface by almost all well-known manufacturers of drive technology.

The HIPERFACE® interface offers motor manufacturers, amongst other things, unprecedented savings on cabling and connectors.

#### HIPERFACE DSL® -

With HIPERFACE DSL®, technology leader SICK presents a strictly digital protocol.

The absence of motor feedback connections achieves significant cost savings and increased performance.

#### SICK fieldbus systems







**DeviceNet** – is a fieldbus specified by ODVA, based on the CIP protocol, which is used in international markets. As a global player, SICK offers DeviceNet in various different devices.

More detailed information about DeviceNet can be found at www.odva.org

PROFIBUS – is a fieldbus specified by the PNO and is used in global automation markets. SICK offers PROFIBUS devices in PROFIBUS DP.

More detailed information about PROFIBUS is available at www.profibus.com

**CANopen** – is a communication protocol based on CAN. It is mainly used in automation technology and for networking within complex devices.

More detailed information about CANopen is available at www.can-cia.org









EtherCAT® is a registered trademark and patented technology licensed by Beckhoff Automation GmbH, Germany. **SICK Ethernet systems** 

EtherNet/IP – based on standard TCP and UDP, EtherNet/IP supports the continuity between the office network and the system to be controlled. EtherNet/IP terminals support DHCP in the allocation of IP addresses and device-level ring functionality.

More detailed information about EtherNet can be found at www.odva.org

PROFINET – is the open industrial Ethernet standard for automation. TCP/IP and IP standards are used. PRO-FINET is realtime Ethernet-capable. Fieldbus systems can be integrated.

More detailed information about PROFINET can be found at www.profinet.com

EtherCAT® – is an Ethernetbased fieldbus that supports network topologies such as line, ring, tree, star and combinations thereof. The open protocol is suitable for realtime requirements in automation technology.

More detailed information about EtherCAT® can be found at www.ethercat.org



SICK incremental systems

TTL RS 422 – in a transistortransistor logic, both the logical status and the amplification are carried out by transistors. That's where the name comes from.

For more information, see the glossary.

HTL Push Pull – High voltage transistor logic functions with an energy supply in the range from 10-30 V DC, with 24 V DC being most common.

"Low" is defined as an output of between 0 VDC ... 3 VDC and "high" as between (Us - 3.5 VDC) ... Us. Sin/cos interface – unlike conventional pulse signals, sinecosine signals are emitted in sine-wave form.

These signals can be output at a higher resolution, as there is also an option to sample the signals using an analog-digital converter.

For more information, see the glossary.

#### FOR SPECIFIC ADAPTATION AND EVALUATION OF ENCODERS


SICK offers a variety of solutions for custom adaptation of encoders to user-specific and application-specific circumstances. The programming options range from a compact, light display unit, through PC-based tools, to integration into control units and web-based interfaces. This means that suitable solutions are available for every user and every application – for developers or service staff, for small batch series, spare parts sales, or highly automated systems. The available product range of incremental and absolute encoders and wire draw combinations offers the right product for every application, and can be programmed specifically to your needs.

C

# **ENCODER PROGRAMMING FROM A-Z** → PGT-10-P Pocket-sized programming unit for self-contained programming in the workplace or on a building site. → PGT-08-S PC-based programming unit for convenient programming in the workplace or in production.

#### Benefits for you

- The encoder properties can be quickly adapted to specific requirements
- Solutions tailored to the target group in question, from service and maintenance to large scale production
- Option to save and clone encoder settings enables fast programming and good traceability
- Cost savings for storage and data management due to reduced variant diversity
- · Fast spare parts supply if service is required







### ENCODER PROGRAMMING UNIT FOR UNIVERSAL MOBILE USE

The PGT-10-P is a light and compact programming unit for SICK incremental and absolute encoders. Because it has an integrated power supply, it is able to work in a fully self-contained manner and is therefore particularly suitable for mobile use in customer service. Various encoder parameters can be stored on the internal memory or on an SD card. Firmware updates enable the user to add new encoder functions and variants to the PGT-10-P. This means that the programming unit can enjoy a very long service life, offering an optimum price-performance ratio.

#### At a glance

- Programmed incremental and absolute encoders from SICK
- · A wide range of menu languages
- · Intuitive operation using four buttons
- Large four-line display with background lighting
- Simple cloning of encoder parameters
- Configuration exchange with the PGT-08-S via an SD card
- Optional updates for new encoder variants and functions

#### Your benefits

- Fewer costs as programming means that the customer does not need to store as many encoder variants
- · Quick encoder replacement
- Light-weight and compact programming unit for mobile use
- Large display with intuitive controls so that operating staff do not require extra training
- International application and simple operation possible thanks to a range of menu languages
- Cloning function saves time and reduces the risk of errors during programming

#### Fields of application

- Programming the incremental encoders DFS60, DFS20, DFS21, DFS22, DFS25, DFS26 and DFV60 measuring wheel encoder
- Programming the absolute encoders AHS36 SSI, AHM36 SSI, AFS60 SSI, AFM60 SSI
- Ideal for appliance manufacturers, customer service, developers, and distributors
- Ideal for mobile use, particularly in applications with poor access

Programmable encoder	Description
→ DFV60	Measuring wheel encoder, incremental encoder
→ DFS60	Incremental encoder
DFS2x	Incremental encoder
→ AFS/AFM60 SSI	Absolute encoder
→ AHS/AHM36 SSI	Absolute encoder





#### THE CONVENIENT AND CLEAR ALL-ROUNDER

The PGT-08-S is a computer-based programming unit for all programmable incremental and SSI absolute encoders and, as a convenient all-rounder, it is also suitable for machine outfits.

#### At a glance

- Programming unit with SOPAS software for commercially available PCs
- Clear graphical user interface for simple operation
- Programming settings can be saved and loaded
- Can be updated for future products and programming functions by performing a software update
- Modular product concept consisting of programming unit, adapter cables, and software
- Connection to the encoders using encoder-specific adapter cables

#### Your benefits

- Free driver and software updates via SOPAS
- Graphical user interface clearly displayed on the PC monitor and ergonomic operation using mouse and keyboard
- Programming settings can be saved and loaded to/from the computer memory, which enables fast duplication and traceability
- Encoder position information via the display enables diagnosis without disassembly
- Programming lowers storage costs due to reduced variant diversity

#### Fields of application

 Ideal for appliance manufacturers, development divisions, small batch series, prototype construction, and distribution

Programmable encoder	Description
→ DFV60	Measuring wheel encoder, incremental encoder
→ DFS60	Incremental encoder
DFS2x	Incremental encoder
→ AFS/AFM60 SSI	Absolute encoder
→ AHS/AHM36 SSI	Absolute encoder





#### **DIRECT ACCESS VIA RS-485**

SICK incremental and SSI absolute encoders can be programmed using a PC, industrial PC, or a control unit supplied by the customer via the RS-485 interface. An RS-485 interface is required for communication with the encoder. It is possible to change the encoder values during the process and without disconnecting the electrical connection. This means that a new encoder setting can be programmed within seconds and rapid changeover of machine properties is guaranteed.

#### At a glance

- · Programming in assembled state
- No programming software required, programming via control commands
- Encoder settings stored in the control unit or the industrial PC
- Functions are independent of the control unit manufacturer
- Switch between write mode and read mode using digital I/O card
- Connection to encoder via signal lines provided by the customer and RS-485 or RS-232 card

#### Your benefits


- Programming without electrical and mechanical disassembly
- Real-time changes to the encoder properties during operation
- Optimum integration into customer-specific control environment
- Customer-specific programming and evaluation functions

#### Fields of application

 Ideal for fast programming directly in the production line while processes are running, or during format adjustment

Programmable encoder	Description
→ DFV60	Measuring wheel encoder, incremental encoder
→ DFS60	Incremental encoder
DFS2x	Incremental encoder
→ AFS/AFM60 SSI	Absolute encoder
→ AHS/AHM36 SSI	Absolute encoder





### DIRECT ACCESS VIA FIELDBUS/ETHERNET

SICK absolute encoders can be programmed using the relevant engineering software and the control unit supplied by the customer via the fieldbus interface without a programming unit or any additional software. It is possible to change the encoder values during the process without disconnecting the electrical connection. This means that a new encoder setting can be programmed in seconds and rapid changeover of machine properties is guaranteed. On Ethernet-based encoders, there are function blocks available which make even complex programming tasks much simpler. As a result, the work required for programming and the error rate are significantly reduced. The encoders also have various diagnostics options. An office PC, industrial PC, or control unit can be used as the user interface.

#### At a glance

- Flexible programming options: in the workplace or directly in assembled state
- Supports function blocks and makes complex programming tasks easier
- Comprehensive diagnostic functions
- No programming software required, programming via control commands
- Encoder settings stored in the control unit or the industrial PC

#### Your benefits


- Programming without electrical and mechanical disassembly
- Less work required for programming and reduced frequency of errors due to pre-assembled function blocks
- Reduction in service and maintenance due to preventative diagnostic evaluation
- Customer-specific programming and evaluation functions
- Cost savings for storage and data management due to reduced variant diversity because it can be programmed freely

#### Fields of application

 Programming absolute encoders with standard fieldbus interfaces and Ethernet-based interfaces

Programmable encoder	Description
→ AFS/AFM60 EtherNet/IP	Absolute encoder
→ A3M60 PROFIBUS	Absolute encoder
→ ATM60 PROFIBUS	Absolute encoder
→ AHS/AHM36 CANopen	Absolute encoder
→ AFS/AFM60 PROFINET	Absolute encoder
→ AFS/AFM60 EtherCAT	Absolute encoder
→ ATM60 CANopen	Absolute encoder
→ ATM60 DeviceNet	Absolute encoder
→ ATM90 PROFIBUS	Absolute encoder





#### INTEGRATED AND SIMPLE REMOTE ACCESS

The encoders can be programmed easily via the integrated web server. To do this, a device capable of running a browser, such as a PC, laptop computer, iPad, or HMI (human machine interface) is required for visualization. No interface-specific technical knowledge is required. The encoders can be programmed directly on the control unit via the interface or via the web browser. Combined access is also possible. The device can be replaced easily using plug and play as the encoder data is mirrored on the control unit side and can be downloaded onto the new device. The encoders also have an integrated FTP server which makes it possible to update firmware directly in the application. The new option for programming via a web browser allows people with varying levels of interface knowledge to access the encoder data, which allows for flexible implementation, service, and maintenance.

#### At a glance

- Active web server installed as a programming tool
- Integrated FTP server
- Easy device replacement, plug and play
- · No programming software required
- Comprehensive diagnostic functions

#### Your benefits

- No interface-specific technical knowledge is required
- Less work required for programming and reduced frequency of errors due to simple operation
- Reduction in service and maintenance due to preventative diagnostic evaluation
- Cost savings for storage and data management due to reduced variant diversity because it can be programmed freely

#### Fields of application

 Programming absolute encoders with Ethernet-based interfaces and integrated web server functionality

Programmable encoder	Description
→ AFS/AFM60 EtherNet/IP	Absolute encoder

SICK encoders provide a wide range of programmable properties to meet your individual requirements and streamline your processes – these include resolution, electrical interfaces, offset/zero-set, and round axis functionality. The table below gives an overview of the type-specific programmable parameters.

Encoder	Programming functions	DFS2x	→ DFS60	→ DFV60	-+ AFS/AFM60 SSI	AHS/AHM36 SSI	-> AHS/AHM36 CANopen	- AFS/AFM60 EtherNet/IP	→ AFS/AFM60 PROFINET	- AFS/AFM60 EtherCAT	- A3M60 PROFIBUS	- ATM60 PROFIBUS	-> ATM60 CANopen	-> ATM60 DeviceNet	-> ATM90 PROFIBUS
	Number of lines	Х	Х	Х											
	TTL/HTL electrical interface	Х	Х	Х											
	Zero pulse width, electrical	Х	Х	Х											
Incremental encoder	Zero pulse width, mechanical	Х	Х	Х											
	Signal sequence/direction of rotation	х	Х	Х											
	Reset to factory settings	Х	Х	Х											
	Set zero point	Х	Х	Х											
	Singleturn scaling				Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
	Multiturn scaling					Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
	Counting direction CW/CCW				Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
Absolute encoder	Reset/preset value				Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
	Speed format						Х	Х	Х	Х	Х	Х	Х	Х	Х
	Round axis functionality					Х	Х	Х	Х	Х	Х	Х			
	Diagnostics						х	х	х	х	х				

#### **Description of programming functions**

Number of lines

Number of pulses emitted by the encoder per mechanical rotation.

TTL/HTL electrical interface

Choice between TTL-compatible or HTL-compatible signal output.

Zero pulse width, electrical Width of the zero pulse (= length of the high signal) in relation to an impulse period.

Zero pulse width, mechanical Width of the zero pulse in relation to a mechanical revolution of the shaft.

Signal sequence/direction of rotation 
This function can be used to change the signal sequence:

A leads B – A comes before B when rotating in a clockwise direction and looking at the shaft. B leads A – B comes before A when rotating in a clockwise direction and looking at the shaft.

Reset to factory settings All programmable values are reset to the values in place when the encoder left the production plant.

Set zero point

This function can be used to change the position of the zero pulse on a mechanical rotation of the encoder. The zero point

is assigned to the current position of the encoder.

The rotary encoder should not be rotated while the function is being executed.

Singleturn scaling Adjustability of the resolution output by the encoder per rotation.

**Multiturn scaling** Adjustability of the resolution output by the encoder via the number of rotations.

Counting direction CW/CCW Counting direction rising/falling.

Reset/preset value Resets the position value to zero (preset)/resets the position value to a preset value.

Speed format Selects the appropriate speed format (e.g., rpm, rps, etc.).

Round axis functionality The round axis functionality permits resolutions for non-integer numbers of rotations

(e.g., 3,600 steps at 2.75 rotations).

**Diagnostics** Additional data provided by the encoder

(such as temperature monitoring, elapsed hour counter, speed monitoring, etc.).



Technologies	Handheld	Software + PC tool	RS	-485	В	us	Web server
Programming or configuring	Configuring	Configuring	Progra	amming	Progra	mming	Configuring
In application				х	Х	Х	Х
Outside of application	Х	х	Х	х	Х	Х	Х
Products	PGT-10-P	PGT-08-S	RS-485 via PC	RS-485 via drive/control	Fieldbus	Ethernet	Web server
DFS2x 1)	x	х	X	Х			
→ DFS60 1)	Х	х	Х	х			
→ DFV60 1)	Х	х	Х	х			
→ AFS/AFM60 SSI 1)	Х	х	Х	х			
→ AHS/AHM36 SSI 1)	x	х	Х	х			
→ AHS/AHM36 CANopen					x		
→ AFS/AFM60 EtherNet/IP						Х	Х
→ AFS/AFM60 PROFINET						Х	•
→ AFS/AFM60 EtherCAT						x	•
→ A3M60 PROFIBUS					Х		
→ ATM60 PROFIBUS					Х		
→ ATM60 CANopen					Х		
→ ATM60 DeviceNet					Х		
→ ATM90 PROFIBUS					X		

In production.

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Only applies to programmable designs.

In preparation.

8015560/2015-09-01 Subject to change without notice



## D

### TYPICAL APPLICATIONS

This chapter describes typical applications for encoders. Arranged according to industry, you will find application examples with a brief description of the typical application as well as a product recommendation from our varied product

portfolio. The encoder types suggested have already been used in the application, however they are to be understood first and foremost as examples. Depending on the control concept and the mechanical requirements of the application,

other encoders can also present a better option. Should you need additional assistance with selecting one of our products, our encoder specialists around the world will be glad to advise you.



ш	•

Selection guide	D-30
Automotive and part supplier D-36	Warehouses and distribution centers D-50
Electrical drive technology D-38	Material transport vehicles, factory and logistics automation D-51
Printing industry D-39	Food and beverage industry D-53
Electronics and solar industry D-40	Tire industry D-54
Port and crane industry D-42	Traffic systems D-55
Wood industry D-43	Packaging industry D-56
Plastics and rubber industry D-45	Machine tool industry
CEP (courier, express, parcel and postal services)	Windenergy D-61
Storage and conveyors D-47	Cement industry D-62

# **APPLICATIONS OVERVIEW**

	Incremental encoders												
	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DFS60S Pro	DGS34/ DGS35	DKV60	DFV60				
Automotive and parts supplier industries	_	_		_	_	_		_					
Speed measurement of belt for detecting circuit boards													
Height positioning of electrical overhead conveyor													
Speed measurement of electrical overhead conveyor						•							
Height positioning of scissor lift table													
Measurement of vehicle speed AGS													
Measurement of lift height AGS-fork													
Electrical drive technology													
Speed measurement of asynchronous motors	•					•							
Printing industry													
Controlling the print head on ink jet printers					•								
Speed measurement for synchronization of machine processes													
Height positioning AGS fork for storage bay assignment													
Detection of steering angle													
Electronics and solar industry													
Height positioning of gripper for load-port feeding													
Monitoring the positions of wafer carriers													
Positioning of semiconductor chips in a bonding machine													
Collision prevention for automatically guided vehicle systems (AGS)													
Positioning a wire bonder													
Positioning of circuit boards under screen printing stencils													
Detection and identification of objects				•									
Monitoring and control of the saw-wire													
Port and crane industry													
Positioning of the trolley on a crane													
Monitoring of the crane winch													
Speed measurement on the crane drive													



	Absolute	e encodei	rs									Wire dra	w encod	ers		encoders v I measure ic tape	Page	
+0-30 +0-30	ACS36	AFS60	AHS36	ARS60	АЗМ60	ACM36	ACM60	AFM60	AHM36	АТМ60	АТМ90	EcoLine	Compact	HighLine	КН53	KH53A	ТТК70	
+0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.40																		→ D-36
+0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.40												•						<b>→</b> D-36
+0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.30 +0.40																		→ D-36
→ D-30  → D-30  → D-30  → D-30  → D-30  → D-30  → D-40  → D-4													•					→ D-36
→ D-36  → D-36  → D-36  → D-36  → D-36  → D-46																		→ D-37
→ D-3¢ → D-3¢ → D-3¢ → D-3¢ → D-3¢ → D-4¢																		→ D-37
→ D-35 → D-35 → D-36 → D-46 →																		→ D-38
→ D-35 → D-35 → D-36 → D-46 →																		
→ D-36  → D-36  → D-36  → D-46  → D-4																		<b>→</b> D-39
→ D-30  → D-40  → D-40  → D-40  → D-41  → D-42																		<b>→</b> D-39
→ D-40  → D-40  → D-40  → D-40  → D-40  → D-41  → D-42  → D-42  → D-42  → D-42  → D-42												•						<b>→</b> D-39
→ D-40 →		•	•															<b>→</b> D-39
→ D-40 →																		→ D-40
D-40  → D-40  → D-40  → D-41  → D-41  → D-42  → D-42  → D-42  → D-42  → D-42												•						
→ D-40  → D-41  → D-42  → D-42  → D-42  → D-42		•	-					•	_									
→ D-4:																	_	
→ D-4:																		→ D-41
→ D-42  → D-42  → D-42																		
D-4:  D-4:  D-4:  D-4:  D-4:																		→ D-41
D-42  → D-42																		→ D-41
→ D-42																		
															•			→ D-42
→ D-42																		→ D-42
																		→ D-42



# **APPLICATIONS OVERVIEW**

	Increme	ental enco	oders							
	Core	Core		Core		5 Pro				
	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DFS60S Pro	DGS34/ DGS35	DKV60	DFV60	
Wood industry		Δ	Δ	Δ	Δ		۵۵	Δ	Δ	
Height positioning of crane gripper										
Crane positioning										
Height positioning of hold-down arm for round wood sorting										
Saw-blade positioning										
Length measurement of the veneer material										
Plastics and rubber industry										
Speed measurement of film										
Speed measurement of roller conveyor										
CEP (courier, express, parcel and postal services)										
Speed measurement on the belt for ensuring equal object distances in a postal sorting system										
Speed measurement on the belt for speed control of the system										
Storage and conveyors										
Speed measurement and positioning at the transfer car					•	•				
Speed measurement and positioning of a storage and retrieval system					•	•				
Height positioning of a storage and retrieval system										
Speed measurement and positioning of the x axis on a tote shuttle	-					•				
Positioning a pallet shuttle	•									
Height positioning of the scissor lift table										
Positioning of roller conveyor in the contour measurement of the pallet loading										
Positioning of the lifting unit of a storage and retrieval system										
Speed measurement of the positioning unit on a storage and retrieval system					•	•				
Measuring the conveying speed of a roller conveyor					•					
Warehouses and distribution centers										
Positioning of storage and retrieval system and transfer cars										
Material transport vehicles, factory and logistics automation										
Height positioning of a storage and retrieval system										
Speed measurement of an automated guided system for switching the characteristic diagram of a safety laser scanner				•		•				
Height positioning of the forks of an automated guided system										
Safe speed measurement of an automated guided system					•	•				
Detection of the steering angle of an automated guided system										
Height positioning of the forks of a narrow aisle truck										



Absolute encoders											Wire dra	w encode	ers	materia	ncoders v I measure		Page
														magnet	ic tape		
ACS36	AFS60	AHS36	ARS60	АЗМ60	АСМЗ6	АСМ60	AFM60	АНМ36	АТМ60	АТМ90	EcoLine	Compact	HighLine	KH53	КН53А	ТТК70	
													•				→ D-43
														-			→ D-43
									•								→ D-43
									•								→ D-43
									•								→ D-44
																	→ D-45
																	→ D-45
																	→ D-46
																	→ D-46
																	→ D-47
																	→ D-47
							•										→ D-47
								•									→ D-47
								•									→ D-48
											•						→ D-48
							•										→ D-48
							•										→ D-48
																	→ D-49
																	→ D-49
							•	•									<b>→</b> D-50
																	-> D 54-
													•				→ D-51
																	→ D-51
											•						→ D-51
																	→ D-52
	•	•															→ D-52
												•					→ D-52



# APPLICATIONS OVERVIEW

	Incremental encoders												
	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DFS60S Pro	DGS34/ DGS35	DKV60	DFV60				
Food and beverage industry			_	_		_		_					
Position and speed measurement of the carousel of a bottle filling system													
Tire industry													
Speed measurement of rollers for loop control					•	•							
Speed measurement of roller conveyor for synchronization of the camera system													
Traffic systems													
Position determination at lock gates													
Freight train positioning													
Packaging industry													
$Speed\ regulation\ of\ the\ conveyor\ unit\ for\ beverage\ cartons\ from\ filling\ systems\ for\ dairy\ products$				•									
Control of the belt speed for primary packaging of meat products				•		•							
Fine positioning of the packaging film for bulk materials									•				
Speed measurement of belt on packaging systems for individual products													
Positioning of the individual wire axes of the pallet handling robot													
Machine tool industry													
Adjustment of press stroke after tool change													
Height positioning of press stroke													
Height positioning of press stroke with absolute encoders													
Speed measurement of sheet coil during decoiling process				•		•							
Speed measurement of CNC portal for secure drive monitoring					•	•							
Height positioning of scissor lift table													
Height positioning of sheet metal storage													
Speed measurement for safety gate securing of the drilling machine						•							
Saw-blade positioning	•												
Speed measurement for access protection of the saw line						•							
Windenergy													
Azimuth system: positioning of the gondola on a wind power plant													
Pitch system: adjustment of the rotor blades on a wind power plant													
Speed measurement of the rotor of a wind power plant					•								
Cement industry													
Speed measurement of the roller conveyor for palletizing cement sacks					•								



Detection of the number of windings on the stretch banding machine

Absolute encoders											Wire dra	aw encode	ers	Linear e materia magneti	vith or	Page	
ACS36	AFS60	AHS36	ARS60	АЗМ60	ACM36	ACM60	AFM60	АНМЗ6	АТМ60	АТМ90	EcoLine	Compact	HighLine	КН53	КН53А	ТТК70	
4	4	4	٩		Q.	q	•	q	q	q							
																	→ D-53
																	→ D-54
																	→ D-54
																	) D 55
																	→ D-55 → D-55
														•			<b>→</b> D-55
																	<b>→</b> D-56
																	→ D-56
																	→ D-56
																	→ D-56
							•		•								→ D-57
																	→ D-58
																	→ D-58
									•								→ D-58
																	→ D-58
																	→ D-59
											•						→ D-59
													•				→ D-59
																	→ D-59
																	→ D-60
																	→ D-60
																	→ D-61
																	→ D-61
																	→ D-61
																	→ D-62
							•		•								→ D-62



# Speed measurement of belt for detecting circuit boards




The DBS60 Core incremental encoder transfers the position of the belt for synchronization of both sensor signals. Alternatively, the belt speed can be taken

directly on the belt using a measuring wheel encoder. This can reduce slippage.

#### Recommended products

# Height positioning of electrical overhead conveyor



The electrical overhead conveyor brings the car bodies to designated workplaces. The compact BCG wire draw encoder ensures that the defined height position

is approached accurately. Eliminating the coupling between the wire draw encoder and suspension mechanism enables highly accurate positioning.

#### Recommended products

#### Speed measurement of electrical overhead conveyor



The electrical overhead conveyor brings the car bodies to designated workplaces. The speed is specified by the higher-level control; an incremental encoder determines the speed. In case of requirements for secure speed, the DFS60S Pro assists with the realization of collision protection in combination with a safety laser scanner.

## Recommended products

# Height positioning of scissor lift table



The compact BKS wire draw encoder measures the height of the scissor lift table accurately and forwards this to the

controller of the scissor lift table via the SSI interface.

## Recommended products

# Measurement of vehicle speed AGS



The route of the automated guided system (AGS) is stipulated by the higher-level control system. The DFS60 incremental encoder determines the speed of the

wheels of the AGS. This information is used to control the warning fields of the safety laser scanners.

#### **Recommended products**

# Measurement of lift height AGS-fork



The BCG08 EcoLine wire draw encoder determines the fork lifting height of the automated guided system and forwards this to the vehicle controller. The BCG08

EcoLine is available with different interfaces and can be integrated easily into all major industrial networks.

# Speed measurement of asynchronous motors



With asynchronous motors, the speed is measured with an incremental encoder. The DBS36 Core and DBS60 Core incremental encoders offer all the necessary features for this application at a competitive price. With speed information from the encoder, the speed of the motor is

regulated by the controller, which means in many cases that the efficiency can be increased.

If safe speed monitoring is required, the DFS60S Pro safety encoder can be used for functional safety.

DBS36 Core	DFS60S Pro H-496
DBS60 Core F-120	



# Controlling the print head on ink jet printers



Certain digital printing machines fire individual ink droplets onto the paper per drop-on-demand and with the highest accuracy. The DFS60 incremental encoder uses a measuring wheel to detect the

speed of the paper web. Its resolution of up to 65,536 pulses per revolution provides fast and high-precision control for this process. These encoders also control continuous ink jet printers.

#### Recommended products

DFS60F-1	162
----------	-----

# Speed measurement for synchronization of machine processes



The folding process, the adhesive joints and the paper travel must match exactly. The actual values in the process must also be compared to the positions of the drives. The extremely high resolution

means that the DFS60 incremental encoder satisfies the requirements for accurate synchronization. The easy programming capability enables adaptation to special customer requirements.

#### Recommended products

DFS60	 	F-162

# Height positioning AGS fork for storage bay assignment



The measurement of the fork lifting height on the AGS for the precise removal of print products from the bay is carried out using the EcoLine wire draw encoder.

#### Recommended products

EcoLine	28	
---------	----	--

# Detection of steering angle



The CLV650 bar code scanner reads the bar code at the shelf and delivers the data to a central computer. This assigns the corresponding path to the automated guided system (AGS) to incorporate the paper roll into the production process as

scheduled. This enhances the scan rate. The EcoLine wire draw encoder measures the lifting height at the AGS, while the AFS/AFS60 SSI absolute encoder takes care of steering control.

## Recommended products

VECEU

A1 000	A11000	

VH638

C 268

D

# Height positioning of gripper for load-port feeding



The risk of material breaks in expensive semiconductor wafers must be kept as small as possible. Therefore, the wafer box is monitored with sensors.

The Ecoline product family of wire draw encoders – lightweight at just 180 grams – provide the exact position of the FOUPs (wafer box) during lowering.

## Recommended products

# Monitoring the positions of wafer carriers



The position of the wafer carrier is determined reliably with absolute encoders: with the AFS60 Singleturn on the vertical and the AFM60 Multiturn on the hori-

zontal axis. Thanks to SSI and industrial Ethernet interfaces, it is possible to integrate these into the machine controller easily and cost-effectively.

## Recommended products

AFS60	88 A	AFM60	G-268
AHS36	32 <i>P</i>	AHM36	G-232

# Positioning of semiconductor chips in a bonding machine




Semiconductor chips are placed in bonding machines at high speed, which requires the greatest precision. The non-contact TTK70 linear encoder works

with a precision in the µm range, thus enabling the precise positioning on the lead frames.

#### Recommended products

TTK70......J-660

# Collision prevention for automatically guided vehicle systems (AGS)



Cleanrooms present a significant cost factor. With flexibly-equipped collision zones on automated guided systems – even at changing speeds – the workspace can be exploited optimally. SICK safety laser scanners adjust their protection and warning fields dynamically. The control data (direction and speed) is provided by two DFS60 incremental encoders, which are mounted on the AGS.

## Recommended products

DFS60...... F-162 DFS60S Pro ...... H-496

# Positioning a wire bonder



Temperatures are very high in the area around the bonding head, making fiber-optic cable systems the most effective for this application. With its 16  $\mu s$  response time, the WLL180T works together with the LL3-TH fibers to supply the control unit with a precise signal for edge detection. The grippers of the wire

bonder move the thin substrate carrier at a high speed. This is a process that requires maximum precision. The two read heads of the TTK70 linear encoder work with a precision in the  $\mu$ m range at a speed of up to 10 m/s, thus contributing to the increasing of machine throughput.

#### Recommended products

TTK70......J-660

# Positioning of circuit boards under screen printing stencils



Screen printing machines can process circuit boards of all sizes; however for this, they need precise position data ( $\pm$  10  $\mu$ m).

The TTK70 linear absolute encoder performs this task.

## Recommended products

TTK70......J-660

#### Detection and identification of objects




An innovative solution for detecting the leading edge of objects on belts is a fiber-optic sensor combined with fibers. This system supplies the position data of the detected objects quickly and reliably.

The DBS60 Core incremental encoder relays the position of the belt, thereby ensuring the synchronization of both sensor signals.

#### Recommended products

# Monitoring and control of the saw-blade




The precise use of saw-blades assumes the use of appropriate encoders. With the AFM60 absolute encoders from SICK, damage to wafers is minimized.

The absolute encoders check the precise position of the saw-blade and transmit the data with the resolution required for this process.

## Recommended products

D

# Positioning of the trolley on a crane



The KH53 is ideally-suited for positioning the trolley on the crane thanks to its good repeatability, large reading distances, and outstanding robustness in case of shocks, vibrations, and weather

influences of all kinds. With the position data of the trolley, it is possible to stack containers very precisely and with as little offset as possible.

#### Recommended products

KH53.....J-644

# Monitoring of the crane winch





The information for the safe speed and direction of rotation monitoring of the crane winch is generated by the DFS60S Pro safety encoder. This way, hazards

due to excessive speed or acceleration can be prevented depending on the cargo.

## Recommended products

PS60S Pro .......H-496

#### Speed measurement on the crane drive




The speed of the drive motor of a crane is measured with the DBS60 incremental encoder. This way, the speed can be con-

trolled depending on the cargo and the travel path of the crane determined.

## Recommended products

# Height positioning of crane gripper



BTF13 wire draw encoders for high-resolution linear measurement lengths up to

50 m are used for height positioning of the crane gripper.

#### Recommended products

HighLine	I-590
----------	-------

# Crane positioning




A non-contact KH53 linear encoder with a resolution of 0.1 mm and optionally for measurement lengths up to 38, 107, 354, and 1700 m is used for detecting the position of the crane portal. The KH53 is wear-free and is also ideal for harsh ambient conditions.

## Recommended products

KH53	 	J-644

# Height positioning of hold-down arm for round wood sorting



The height of the hold-down arm is detected with the ATM60 position encoder for determining the log diameter. The rotation time is calculated from this.

The ATM60 is extremely rugged and reliable and has high shock and vibration resistance.

## Recommended products

ATM60	0.000

# Saw-blade positioning



The positioning of saw-blades for setting to the thickness to be sawed is carried out with the ATM60 absolute encoder.

The ATM60 encoder signals the precise position of the saw-blades to the system control.



# Length measurement of the veneer material



The length of the veneer material is measured precisely with the ATM60 absolute

encoder. When the set length is reached, the veneer material is cut.

# **Recommended products**

ATM60......G-386



# Speed measurement of film



The DBS60 Core incremental encoder monitors the speed of the film sheet on a roller. This enables the film sheet to

be wound up onto the coil at a constant rate

#### **Recommended products**

# Speed measurement of roller conveyor



The DFV60 incremental measuring wheel encoder uses a friction wheel to measure the exact feed speed of the

extruded plastic panel. The measured value obtained is used to control the panel sizing saw downstream.

## **Recommended products**

DFV60......F-210



# Speed measurement on the belt for ensuring equal object distances in a postal sorting system



The leading edge detection serves to convey objects at a specified distance from the belts to the main sorter. The combination of high-resolution light grids and high-resolution encoders allows leading edge detection and the detection of additional object profile information such as the length.

The duration of the light grid interruption and the speed of the belt that is measured by the encoder provide information about the length of the objects. This information is required in order to accelerate or slow down individual belt segments so that the objects can be placed properly on the sorter.

#### Recommended products

# Speed measurement on the belt for speed control of the system



The current speed is a significant parameter for the precise control of a driven system such as a conveyor belt. Incremental measuring wheel encoders with

a high resolution of up to 65,536 pulses per rotation supply the controller with precise signals for the speed.

#### Recommended products

FV60......F-210

# Speed measurement and positioning at the transfer car



The measured values of the DFS60 programmable incremental encoder control the positioning and speed. With its high resolution, the DFS60 encoder ensures maximum repeatability. There

are numerous variants available to accommodate nearly all mechanical and electrical interfaces. The DFS60S Pro can help to realize safe speed and direction of rotation detection.

#### Recommended products

DFS60..... F-162 

# Speed measurement and positioning of a storage and retrieval system



The DFS60 incremental encoder supplies the value for controlling the positioning speed, acceleration, and delay. On entry into the protected area of the storage and retrieval system, it must

be ensured that the storage and retrieval system is at a standstill or is being operated in manual mode at a reduced speed. The DFS60S Pro can help to realize these safety functions.

## Recommended products

DFS60..... F-162 

# Height positioning of a storage and retrieval system




When it comes to the insertion depth, accurate measurements are crucial. A rugged absolute encoder on the belt drive with a high resolution and excel-

lent repeatability ensures precision. The availability of most common communication protocols make integration into the control architecture a breeze.

#### Recommended products

# Speed measurement and positioning of the x axis on a tote shuttle



The DBS36 Core incremental encoder or the AHM36 absolute encoder supplies the value for controlling the positioning, speed, and acceleration. The encoder

ensures that the positioning of the shuttle can be executed with precision. The DFS60S Pro can help to realize these safety functions.

## Recommended products

# Positioning a pallet shuttle



The shuttle is positioned by means of an incremental encoder mounted on the drive axis. Designs featuring a blind hollow shaft or a face mount flange with a solid shaft ensure flexible adaptation to the drive. They can even be used in cases where there is very little space available. Alternatively, an absolute encoder can also be used.

# Recommended products

DBS36 Core	G-232
------------	-------


# Height positioning of the scissor lift table



The scissor lift table is positioned using a high-resolution wire draw encoder with a teach-in function. The extremely reliable wire draw encoder does not require complex linear guidance, and can be integrated with ease both electrically and mechanically.

## Recommended products

# Positioning of roller conveyor in the contour measurement of the pallet loading



With both laser measurement and absolute encoders, an image and a position of the load can be determined, enabling

the robot system to correct the specified positioning data if necessary.

#### Recommended products

# Positioning of the lifting unit of a storage and retrieval system



To avoid an unnecessary increase in enormous cold store energy requirements, it is important to ensure optimal storage and retrieval. Among other things, this depends on accurate and above all, reproducible positioning of the

lifting unit. In addition to great precision, the AFM60 absolute encoder also offers a wide temperature range down to -40 °C, which makes it well-suited for use in cold storage.

## Recommended products

# Speed measurement of the positioning unit on a storage and retrieval system



To avoid an unnecessary increase in enormous cold store energy requirements, it is important to ensure optimal storage and retrieval. Among other things, this depends on accurate positioning of the drive unit for efficient flow.

This is realized thanks to the speed information provided by the DFS60 incremental encoder. With its high resolution and wide temperature range down to -40 °C, the DFS60 works precisely and reliably under even the harshest conditions.

#### Recommended products

# Measuring the conveying speed of a roller conveyor




The conveying speed is controlled using the measured values of a programmable incremental encoder. With its high resolution, the encoder ensures maximum repeatability. There are numerous variants available to accommodate nearly all mechanical and electrical interfaces.

#### Recommended products

DFS60......F-162

# Positioning of storage and retrieval system and transfer cars



SICK absolute encoders fulfill the requirements for high-precision distance measurement devices for the precise positioning of transport units such as storage and retrieval systems, transfer carriages, and automated guided systems.

AFM60 G-268	$AHM36\ldots\ldotsG-232$
-------------	--------------------------



# Height positioning of a storage and retrieval system




Wire draw encoders fulfill the requirements for the high-precision positioning of storage and retrieval systems. These

products are available in a wide variety of wire lengths and with different interfaces.

#### Recommended products

# Speed measurement of an automated guided system for switching the characteristic diagram of a safety laser scanner



For personal protection and collision prevention with other vehicles or materials on the floor, automated guided systems AGS are equipped on the fork side and on the back side with safety laser scanners. The AGS is equipped with two drive units with one DBS60 Core incremental

encoder apiece and determines the speed of the AGS. The encoder signals are compared to one another with a cross-comparison. The laser scanners use this information for switching depending on the speed of the protection and warning fields.

#### Recommended products

# Height positioning of the forks of an automated guided system



Positioning of the forks of the AGS is handled by constantly-measuring wire

draw encoders. This way, the bays are approached at the correct height.

## Recommended products

D

# Safe speed measurement of an automated guided system



With automated guided systems (AGS), the SSM (safety speed monitor) or SLS (safety-limited speed) function monitors the speed on the wheels using the DFS60S Pro encoder and reduces it via the controller if necessary. Thanks to a

central drive unit, with the DFS60S Pro and the Flexi Soft safety controller, it is possible to realize safe motion monitoring or warning field monitoring of the safety laser scanner.

#### Recommended products

DFS60S Pro H-496 DF	FS60 F-162
---------------------	------------

# Detection of the steering angle of an automated guided system



The motion direction of the AGS is measured with a singleturn absolute encoder. The driving direction information serves to control the engine safety characteristics.

## Recommended products

AFS60	AHS36 G-232
-------	-------------

# Height positioning of the forks of a narrow aisle truck




Using a BKS09 wire draw encoder enables the narrow aisle truck to accurately determine the position of the fork. The highly flexible steel wire is fixed to the

fork's 'shoulder'. The driver sees the position of the fork on a display. This provides support when the height of the fork cannot be seen (man-below system).

•	
Compact	I-5/6



# Position and speed measurement of the carousel of a bottle filling system



The precise position and speed monitoring is handled by an A3M60 absolute encoder. The encoder is connected directly to the carousel wheel via gear stages. The resolution per rotation depends on the number of filling stations. The number of encoder rotations depends on

the gear translation. Thanks to the round axis functionality of the encoder, individual resolutions can be configured quickly and safely. (Full scalability for binary, non-binary, as well as for non-integer rotations such as, e.g. 12.4 rotations)

A3M60	72
-------	----



# Speed measurement of rollers for loop control



DFS60 incremental encoders monitor the roller speed for loop control. The DFS60 encoders are highly durable and are available in a variety of mechanical and electrical variants. DFS60 incremental encoders can be configured as required. Thus, the storage of different resolution variants is not necessary.

#### Recommended products

# Speed measurement of roller conveyor for synchronization of the camera system




Image evaluation requires an undistorted image. The imaging technology obtains the information relating to the speed of

the roller conveyor and the tire (which is required for synchronization) from the DBS60 Core incremental encoder.

#### Recommended products

# Position determination at lock gates




The KH53 linear encoder determines the position of the lock gate during the closing process so that it can be controlled

optimally. Due to the non-contact technology, this system works wear-free and precisely even in a harsh environment.

#### **Recommended products**

KH53J-6	344
---------	-----

# Freight train positioning



So that loading and unloading is completed correctly, especially with automatic systems, freight trains must be positioned exactly. With a measurement length of max. 1,700 m, the KH53 linear encoder is especially well-suited for use

on tracks. Due to the non-contact technology, this system works wear-free and precisely – even in case of vibrations of the train, contamination, and precipitation.

KUES		 1644
NH33	 	 J-044



# Speed regulation of the conveyor unit for beverage cartons from filling systems for dairy products




The DBS60 Core incremental encoder measures the speed of the belt. This information is required in order to control

the camera for detection of the sealing lids depending on the speed.

## Recommended products

# Control of the belt speed for primary packaging of meat products



The DBS60 Core incremental encoder is used to regulate the speed of the belt. Both belts must be speed-synchronized

in order to guarantee precise storage of the meat portions in the plastic trays.

#### Recommended products

# Fine positioning of the packaging film for bulk materials




The DBS50 Core incremental encoder monitors the speed of the packaging film on a bag packaging machine. This measurement is required in order to control

the fill quantity and cutting process. For slip-free speed measurement, an alternative is to use the DFV60 incremental measuring wheel encoder.

#### Recommended products

# Speed measurement of belt on packaging systems for individual products




The DBS60 Core incremental encoder measures the speed of the belt. Pralines of different types are transported on the belt and sorted into the trays with a

Pick & Place robot. The processes must be synchronized and the encoder provides the required process speed.

## Recommended products

# Positioning of the individual wire axes of the pallet handling robot



ATM60 multiturn absolute encoders transmit the absolute positions of the

robot's individual axes of rotation to the controller.

# **Recommended products**

AFM60 G-268	ATM60
-------------	-------

D

# Adjustment of press stroke after tool change



Once the tools have been replaced, the press stroke must be adapted using a primarily mechanical adjustment mechanism. The procedure for adjusting the height of the press stroke can be

completed automatically with the help of an electric drive and the AFM60 absolute encoder, which determines the precise measurement of the revolution at the gear.

#### Recommended products

AFM60	G-268	AHM36	G-232

# Height positioning of press stroke



To determine the position of the press stroke, a BKS wire draw encoder is used. It reliably supplies signals for establishing the top dead center (TDC) and bottom dead center (BDC).

#### Recommended products

Compact	I-576
---------	-------

#### Height positioning of press stroke with absolute encoders



An ATM60 absolute encoder is mounted to the eccentric shaft on mechanical presses for the purpose of determining the position of the press stroke. It reli-

ably supplies signals for establishing the top dead center (TDC) and bottom dead center (BDC).

#### Recommended products

ATM60	60 G-268
-------	----------

# Speed measurement of sheet coil during decoiling process



To ensure a constant feed of material, the uncoiling speed of the sheet coil must be regulated. The distance sensor continuously measures the radius of the sheet coil throughout the entire unwinding process. The DBS60 Core incremental encoder uses a friction roller to mea-

sure the retraction speed of the sheet. If there is a safe stop of the upstream machine, this can cause a hazard due to the overrun of the sheet. Here, the DFS60S Pro safety encoders assist with the realization of the safety function.

DBS60 Core	F-120	DFS60S Pro	H-496

# Speed measurement of CNC portal for secure drive monitoring



The movements of the CNC portal, which the worker cannot predict and which can be very rapid, represent hazardous points during the machining process. The modules of the Drive Monitor FX3-MOC safely monitor the electric drive system of the CNC plasma cutting machine in conjunction with the signals of the Flexi

Soft safety controller. Depending on the performance level required or the drive used on the machine, it may be necessary to attach an additional incremental encoder (e.g., DFS60) and forward its signal to the safety controller separately for evaluation purposes.

## Recommended products

# Height positioning of scissor lift table




Following machining, residual grids are placed on a scissor lift table. To ensure a smooth transfer, the height of the stack must be aligned with that of the machining table. The analog signal values of the

EcoLine wire draw encoder are used to determine the lifting height. When the maximum load has been reached, the worker removes the stack of residual grids.

## Recommended products

#### Height positioning of sheet metal storage




The material lift is used to move stacks of sheets from a transfer carriage or residual sheets from a vacuum nozzle to an interim shelf for storage. The BTF13 wire draw encoder signals the absolute

height position of the material lift to the control. The bottom and top final positions of the material lift are monitored by inductive proximity sensors.

#### Recommended products

# Speed measurement for safety gate securing of the drilling machine




For stand-alone machines such as a drilling machine, the user is protected from the hazardous point by a safety door or hood. For set-up operation, the speed of the drilling arm and tool table must be

monitored safely at reduced speed. Here, the DFS60S Pro safety encoders assist reliably with the realization of the safety function.

## Recommended products



# Saw-blade positioning



The height of the saw blade is automatically positioned for optimum control of the sawing process. The DBS36 Core incremental encoder supplies precise measurement values for this purpose.

It can be easily and directly mounted using the face mount flange or the hollow shaft and its universal cable outlet. Its compact size saves space.

#### Recommended products

# Speed measurement for access protection of the saw line




On the saw line, the operator is kept away from the hazardous point by a safety fence. In order to eliminate faults on the line, a safe standstill detection is necessary or for the maintenance and

service mode, a safely-limited speed. The DFS60S Pro safety encoders assist reliably with the realization of safety functions.

#### Recommended products

# Azimuth system: positioning of the gondola on a wind power plant




Depending on the change in the wind, the gondola on the wind power plant must be aligned in the optimal wind direction. Thanks to the ATM60 absolute encoder, the correct rotation and function of the system is monitored, since there are very high forces, particularly during strong winds, and a malfunction of the gondola controller can result in high costs and downtimes.

#### Recommended products

AFM60 G-268	ATM60
-------------	-------

# Pitch system: adjustment of the rotor blades on a wind power plant



The adjustment of the rotor blades plays an important role in order to achieve as great a yield as possible of rotation energy. Depending on the wind strength and direction, the position of the rotor blades is adjusted accordingly. AFS60/AFM60 absolute encoders are used to set the

rotor blades. The advantage of these devices is their high resolution. In case of a power outage and after return of the power, the precise position value is output. A reference run as for incremental encoders is not required, which contributes to the safety of the application.

#### Recommended products

AFS60	68 AF	M60	G-268

# Speed measurement of the rotor of a wind power plant



Generally, incremental encoders are used to monitor the rotor speed. These are normally fastened to the hub of the rotor. The DFS60 incremental encoder is used around the world under the harshest conditions. Its stable construction with enclosure rating up to IP67 makes

it a rugged and nevertheless high-resolution incremental encoder. With through hollow shafts up to Ø 15,875 mm, the DFS60 family can be used universally. The safe detection of the rotor generator speed can alternatively be handled with the DFS60S Pro safety encoder.

DECCO	E 400	DE0000 D	11.400
DFS60	. F-162	DESGUS Pro	H-496

# Speed measurement of the roller conveyor for palletizing cement sacks




Automatic pallet handling machines stack the filled cement bags onto pallets. The DFS60 incremental encoder moni-

tors the transport speed of the pallets on the roller conveyor.

#### Recommended products

DFS60......F-162

# Detection of the number of windings on the stretch banding machine



After the pallet has reached its position, the stretch film is secured to the pallet and wrapped using upward and downward movements of the film. The number

of windings is determined via a gear wheel on the sprocket with an AFM60 absolute encoder.

# Recommended products

AFM60 ...... G-268 ATM60..... G-386

D



# WHAT IS THE DIFFERENCE BETWEEN INCREMENTAL AND ABSOLUTE MEASUREMENT?

#### Incremental measurement




- · Counts pulses from 1 to n
- A reference point (zero impulse) must be approached in order to determine the position
- Number of impulses = degree of resolution
- → Incremental encoders Chapter F/Safety encoders Chapter H
- → Wire draw encoders Chapter I/Linear encoders Chapter J

#### Absolute measurement



- Measures the absolute position of 1 to n
- Each step is allocated a unique code pattern, and thus a unique (absolute) position
- Number of steps = degree of resolution
- → Absolute encoders Chapter G
- → Wire draw encoders Chapter I/Linear encoders Chapter J

#### Incremental encoders



The figures only illustrate one possible variant from each product family.

Which interface connection is required?  TTL  HTL  TTL/HTL Universal  Open Collector  Sin/Cos  What is the maximum amount of space available or installation (diameter)?  Up to 37 mm  Up to 40 mm  Up to 50 mm  Up to 60 mm  Up to 90 mm  Which type of flange or shaft is required?		Core	:	Core	:	Pro	DGS35	:	:
TTL  HTL  TTL/HTL Universal  Open Collector  Sin/Cos  What is the maximum amount of space available or installation (diameter)?  Up to 37 mm  Up to 40 mm  Up to 50 mm  Up to 60 mm  Up to 90 mm	:	:	:	:	:	_	•	:	:
HTL  TTL/HTL Universal  Open Collector  Sin/Cos  What is the maximum amount of space available or installation (diameter)?  Up to 37 mm  Up to 40 mm  Up to 50 mm  Up to 60 mm  Up to 90 mm	:	:	:	:	:	_	•	•	•
TTL/HTL Universal Open Collector Sin/Cos What is the maximum amount of space available or installation (diameter)?  Up to 37 mm Up to 40 mm Up to 50 mm Up to 60 mm Up to 90 mm	:	:	:		٠	_	•		•
Open Collector Sin/Cos What is the maximum amount of space available or installation (diameter)?  Up to 37 mm Up to 40 mm Up to 50 mm Up to 60 mm Up to 90 mm	:	:	:		٠	_	•		•
Sin/Cos What is the maximum amount of space available or installation (diameter)?  Up to 37 mm  Up to 40 mm  Up to 50 mm  Up to 60 mm  Up to 90 mm	:	:	:			_	•		
What is the maximum amount of space available or installation (diameter)?  Up to 37 mm  Up to 40 mm  Up to 50 mm  Up to 60 mm  Up to 90 mm	:	•	•			_			
or installation (diameter)?  Up to 37 mm  Up to 40 mm  Up to 50 mm  Up to 60 mm  Up to 90 mm	:	•	•		-				
Up to 40 mm Up to 50 mm Up to 60 mm Up to 90 mm	:	•	•		•				
Up to 50 mm Up to 60 mm Up to 90 mm	:	•	•						
Up to 60 mm Up to 90 mm	:	•	•		•	_			
Up to 90 mm	:	•			-	_			
			•			_			
Which type of flange or shaft is required?						•			
The state of the s									
Face mount flange		_							
Servo flange						•			
Blind hollow shaft	•					•	•		
Through hollow shaft						•	•		
Measuring wheel system									
Vhat hollow shaft diameter is required?									
Up to 8 mm				•		•			
Up to 10 mm									
Up to 12 mm				•		•			
Up to 15 mm				•		•			
Up to 5/8"				•					
> 5/8"									
Vhat resolution is required? (pulses per revolu- ion/steps per revolution)									
Up to 2,500	•	•	•	•			•		•
Up to 5,000				•	•		•		•
Up to 8,192					•		•		•
Up to 16,384					•		•		•
> 16,384					•				•
1,024 sin/cos periods					•	•			
Should programming/configuration be performed by the customer?									
Yes, using a hand-held device					•				•
Yes, using software and PC tool					•				•
Yes, via RS-485					•				
No		•	•	•	•	•			
s a safety certificate required for the encoder?									
Yes						•			
No		•	-	-			•	•	•



# WHAT IS THE DIFFERENCE BETWEEN SINGLETURN AND MULTITURN?

# Singleturn



- · Variant of absolute encoders
- Measures the absolute position of 1 to n within one revolution


# Multiturn



- · Variant of absolute encoders
- Measures the absolute position of 1 to n within one revolution
- Also measures the number of revolutions

# → Absolute encoders Chapter G

## Absolute encoders



The figures only illustrate one possible variant from each product family.









→ To the selection guide

Absolute encoders Singleturn										
	ACS36		AF	S60	AH	S36	ARS60			
			√IP		ь		c			
	Analog		EtherNet/IP	EtherCAT®	PROFINET		CANopen		Parallel	
	Ana	SSI	Eţ	Eţ	PRC	SSI	CAN	SSI	Pari	
How many revolutions are to be absolutely measured?										
≤1	•							•	•	
>1										
Which interface connection is required?										
Analog 4 to 20 mA / Analog 0 to 10 V	-									
Parallel									-	
SSI		•				•		•		
SSI + incremental										
SSI + Sin/Cos										
Fieldbus/Ethernet			•	•	•		•			
What is the maximum amount of space available for installation (diameter)?										
Up to 36 mm	•						•			
Up to 40 mm	-									
Up to 50 mm	•					-				
Up to 60 mm									•	
Up to 90 mm							•	•	•	
Which type of flange or shaft is required?										
Face mount flange		•	•	•	•		•	•	•	
Servo flange	•	•	•	•	•	•	•			
Blind hollow shaft		•	•	•	•	•	•	•		
Through hollow shaft									•	
What hollow shaft diameter is required?										
Up to 8 mm			-		-	•	•	•	•	
Up to 10 mm		•	•	•	•			•	•	
Up to 12 mm		•	•	•	•			•	•	
Up to 15 mm		•	•	•	•					
Up to 5/8"		•	•	•	•					
> 5/8"										
What resolution is required? (pulses per revolution/steps per revolution)										
1,024	1)									
Up to 2,500	1)									
Up to 5,000	1)							•	•	
Up to 8,192	1)							•	•	
Up to 16,384	1)							•	•	
> 16,384	1)							•	•	
Should programming/configuration be performed by the										
customer?  Yes, using a hand-held device										
Yes, using software and PC tool										
Yes, using software and PC tool										
Yes, via BUS (fieldbus or Ethernet)		•				•				
Yes, via a web server				_	_		_			
Yes, using the teach-in function on the encoder	•		•							
No	2)		<b>2</b> )	2)	<b>2</b> )		<b>2</b> )			
Page	→ G-474	→ G-268	→ G-312	→ G-352	→ G-332	→ G-232	→ G-252	→ G-454	→ G-454	
rage	7 G-4/4	→ G-208	<b>→</b> G-312	→ G-352	→ G-332	→ u-232	→ G-252	→ G-454	→ G-454	

<sup>&</sup>lt;sup>1)</sup> Analog resolution dependent on programmed measuring range.


<sup>&</sup>lt;sup>2)</sup> Encoders can in principle be programmed/configured, but can also be used with the default factory settings without configuration.


Multitu	rn													
A3M6	D ACM36	ACM60		AFN	160		AHN	<b>//36</b>		ATN	160		ATM	190
PROFIBUS	Analog	Analog	SSI	EtherNet/IP	EtherCAT®	PROFINET	SSI	CANopen	SSI	PROFIBUS	CANopen	DeviceNet	SSI	PROFIBUS
_	_	_	_	_	_	_	_	_	_	_	_	_	-	_
			•				•						•	
			•											
			-											
_				•	_	_		_		_	_	_		_
								•						
	•		•			•	•		•					
			•	•	•		•	•		•	•	•	•	•
-		_	-	-	•	-	-	-	-	-	•	•		
	•	•			•	•	-	•						
			•								_	_	•	
			•	•	•		•	•	•	•	•	•	•	•
•			•	•	•	•	•	•	•	•	•	•	-	•
-			-	-	•	-			•	•	•	•	-	-
			-	•	•	•			•	•	•	•	-	
_													_	
	1)	1)												
	1)	1)		•		•	•	•		•			•	•
	1)	1)	•	•	•	•	•	•	•	•	•	•	•	•
•	1)	1)	•	•	•	•	•	•	•	•	•	•	•	•
	1)	1)	-	-	-	-	•							
	1)	±)	•											
			-				-							
			•				-		•				-	
										•				
				•										
		•												
<b>2</b> )	<b>2</b> )	<b>■</b> <sup>2)</sup> → G-482	→ G-268	→G-312	⇒ G-352	→ G-332	→ G-232	→ G-252	<b>■</b> <sup>2)</sup> → G-398	<b>■</b> <sup>2)</sup> → G-386	■ <sup>2)</sup> → G-412	→ G-412	<b>■</b> <sup>2)</sup> → G-436	→ G-444



# WHAT IS THE DIFFERENCE BETWEEN WIRE DRAW ENCODERS AND LINEAR ENCODERS?

#### Wire draw encoders






- Encoder counts from 1 to n and converts the figure into a measurement signal
- · Consists of an encoder and a wire draw
- · The wire draw travels the distance from A to B
- · The encoder is stationary
- → Wire draw encoders Chapter I

Linear encoders with material measure or magnetic tape



- . Measures distance from A to B
- · Consists of read head and material measure
- · The read head travels the distance from A to B
- The material measure with permanent magnets is stationary
- → Linear encoders Chapter J

#### Wire draw encoders and linear encoders



# Linear encoders with material measure or magnetic tape





The figures only illustrate one possible variant from each product family.

	Wire draw encode	ers		Linear encoders with material measure or magnetic tape				
	EcoLine	Compact	HighLine	KH53	КН53А	ТТК70		
How many measuring cycles are needed?								
Up to 1,000,000								
Unlimited								
What kind of position measurement is required?								
Absolute								
Incremental		•	•			•		
Which interface connection is required?								
πι		•	•					
HTL			•					
Analog	•		•					
HIPERFACE®	1)	•	<b>1</b> )			•		
SSI		•	•	•	•	•		
SSI + Sin/Cos	1)		<b>1</b> )			•		
PROFIBUS	•		•	•	•			
CANopen	•		•					
DeviceNet	•		•					
EtherNet/IP								
PROFINET	•		•					
EtherCAT®								
Is a consistent mounting surface available over the measuring distance?								
Yes	•	•	•	•	•			
No	•	•	•					
What are the mounting tolerances like?								
Low	•	-	-	•		•		
Medium	•	-	•	•	•			
High					•			
What measuring length is required?								
≤ 4 m	•	•	•	•	•			
≤ 5 m	•	•	•	•	•			
≤ 10 m	•		•	•	•			
≤ 50 m			•	•	•			
≤ 548 m				•	•			
≤ 1,700 m				•				
What resolution is required?								
≤ 0.1 mm	•	•	•	•	•			
≤ 0.05 mm	•	•	•					
≤ 1 µm		•				•		
How reliable does the measuring system need to be?								
Low								
Medium			•					
High			•		•			
Which installation size can be used?								
Small								
Medium								
Large			•					
Page	→ I-528	→ I-576	→ I-590	→ J-644	→ J-644	→ J-660		

<sup>1)</sup> Available upon request.

## SICK SENSOR INTELLIGENCE. - FOR ALL REQUIREMENTS

SICK has representation in numerous fields and is therefore familiar with the processes used in a wide range of industry branches. This enables us to recognize and understand our customers' requirements and respond to them by providing straightforward and pragmatic solutions.

When it comes to finding solutions for your requirements and optimizing your processes, SICK can also provide you with customized encoders in addition to its huge range of standard encoders. The basis for this flexibility is a process that employs the requisite level of standardization to ensure that your projects are handled efficiently – without losing any of their dynamism. SICK grows and develops with every new requirement.



SICK is also a reliable partner offering a whole host of advantages when it comes to developing customer-specific solutions:

#### Easy handling

SICK's global presence means that it is easy to get in touch with experts wherever you are.

#### Rapid processing

Our team of experts guarantees that the process will run smoothly.

#### **High product quality**

We deliver renowned SICK quality.

#### **Optimized logistics**

Joint sales planning means that your customer-specific encoders will always be available when you want them.

#### High level of transparency

Thanks to clear process structures, you will know the exact status of your project at all times.


#### **Excellent support**

Our team of experts epitomizes reliability. The success of your project is our shared objective.

# MORE FLEXIBILITY TO FIND SOLUTIONS FOR YOUR REQUIREMENTS

Perfectly matched to your application: with the right connection, the requested mechanical systems, and the required interface. And it goes without saying that we also provide the accessories you need.

Face mount flange encoder with connector outlet



Servo flange encoder with cable outlet

Hollow shaft encoder with connector outlet











#### Shaft dimensions:

- Shaft length
- · Shaft design
- · Shaft diameter







#### Mounting system:

- Adapter flange
- Mounting hole patterns in flange
- · Stator coupling





#### Connection type:

- Customer-specific length of cable
- Cable with attached male connector
- Customer-specific wire assignment
- Customer-specific pin assignment

#### **Electrical interfaces:**

- Customer-specific configuration
- · Communication interface

#### Accessories:

- Incorporate existing or customer-specific accessories in the scope of delivery
- Pre-install existing or customer-specific accessories

If your application requires a highly specialized encoder design, then please get in touch with us. We will work together with you to find a solution. For more detailed information, please contact your local SICK contact.



## **INCREMENTAL ENCODERS**

### Versatile, compact, and flexible - Incremental encoders

Incremental encoders generate information about position, angle and rotation counts. The number of graduations per revolution determines the number of impulses that the encoder transmits to the control unit for each revolution. The current position can be determined by the control unit by counting these impulses from a reference point. When the machine is switched on, a reference

run to the reference point is required to determine the absolute position of the encoder.

#### Your benefits

- Increased machine availability due to rugged, reliable design
- Precise determination of position and speed due to high resolution of up to 65,536 lines
- Perfect adaptation to application-specific requirements due to wide range of variants
- Small type encoders allow compact system design
- Reduced time and costs due to standardization by means of programming function, i.e., fewer part numbers, less warehouse stock, and minimization of downtime








	Applications		
	DBS36 Core	•	DGS34
_(@	DBS50 Core		DGS35
//e	DKS40		DKV60 measuring wheel encoder F-202 Rugged, high-performance measuring wheel incremental encoder
<u></u>	DBS60 Core	-01)	DFV60 measuring wheel encoder F-210 High-resolution, programmable measuring wheel incremental encoder
ie	DFS60		

## TYPICAL INCREMENTAL ENCODERS APPLICATIONS

Incremental encoders are used to detect speed, position, or angle. Thanks to their versatility, they are used in various applications in factory, logistics, and process automation.

Industrial trucks and forklifts - positioning in storage and transport halls



The incremental encoder provides information on the direction of travel and the speed of the automated guided system (AGS). The encoder can either be directly mounted on the motor, on an axle (see figure), or on a revolving wheel.

Solid shaft encoders are normally used in this context. The speed that is measured is used to calculate the position and to ensure the security field is observed using safety laser scanners.

#### Conveyor belts - positioning of transport material




The incremental encoder detects the speed of the conveyor belt and the objects transported on it. Using this information, the speed of other conveyor belts can be synchronized – for example, to control bar code scanners and label printers.

The speed is monitored on the drive roller, on the follower roller, or directly on the conveyor belt.

Measuring wheel encoders, such as the DFV60, may be useful in this context. They are made up of an encoder, a measuring wheel and a universal mounting arm. The measuring wheel is pressed by spring force onto the conveyor and measures the exact velocity of the moving object, without any potential slippage between the drive roller and the conveyor belt.

#### Printing machines - positioning of printed images



Incremental encoders detect the speed of the print media and provide key information on the correct position for the print and the quality of the printed image. Whether you require clearly legible bar codes or high resolution printed check cards, gift cards, or brochures – accurate speed monitoring ensures print quality.

For these types of application, the measuring wheel is used along with the DFS60 incremental encoder. You can easily program the DFS60 using the hand-held PGT-10-S display programmer and the RS485 control system interface, making it easy to adapt the encoder based on the print media.

S. S





DBS36 Core	DBS50 Core	
The multi-fit incremental encoder	The multi-fit incremental encoder	

Technical data overview			
Numbers of lines / pulses fromto	10 2,500	10 2,500	
Mechanical design	Solid shaft, face mount flange Blind hollow shaft	Solid shaft, face mount flange	
Electrical interface	4.5 V 5.5 V, TTL/RS422 7 V 30 V, TTL/RS422 7 V 30 V, HTL/Push Pull 7 V 27 V, HTL/Push Pull, 3 channel 4.5 V 5.5 V, Open Collector NPN 4.5 V 30 V, Open Collector NPN	4.5 V 5.5 V, TTL/RS422 7 V 30 V, TTL/RS422 7 V 30 V, HTL/Push Pull 7 V 27 V, HTL/Push Pull, 3 channel 4.5 V 5.5 V, Open Collector NPN 4.5 V 30 V, Open Collector NPN	
Permissible shaft load (solid shaft)	20 N axial / 40 N radial	30 N axial / 50 N radial	
Enclosure rating up to	IP 65	IP 65	
Programmable	-	-	
Maximum output frequency	≤ 300 kHz	≤ 300 kHz	
Ambient temperature	-20 °C +85 °C	-20 °C +85 °C	

#### At a glance

- Connection with universal cable outlet
- Designs with blind hollow shaft or face mount flange with solid shaft
- Face mount flange with 6 mounting hole patterns and servo groove
- · Hollow shaft with universal stator coupling
- Compact housing diameter of 37 mm with compact construction depth,
- Electrical interfaces: TTL/RS-422, HTL/Push
   Pull and Open Collector NPN
- Number of lines: 10 to 2,500
- Temperature range: -20 °C... +85 °C
- Enclosure rating: IP 65

- Connection with universal cable outlet
- Face mount flange with 8 mm solid shaft
- Face mount flange with 2 mounting hole patterns and servo groove
- Compact housing diameter of 37 mm with compact construction depth, flange diameter 50 mm
- Various electrical interfaces: TTL/RS-422, HTL/Push Pull and Open Collector NPN
- Number of lines from 10 to 2,500 possible
- Temperature range: -20 °C... +85 °C
- Enclosure rating: IP 65

→ F-98

**Detailed information** 



#### DKS40

Rugged, high-performance incremental encoder



#### **DBS60** Core

Rugged, versatile incremental encoder for industrial applications

1 2,048	4 5,000
Solid shaft, face mount flange	Solid shaft, face mount flange Solid shaft, servo flange Blind hollow shaft Through hollow shaft Through hollow shaft clamping at the back
4.5 5.5 V, TTL/RS422, 6 channel 10 30 V, HTL/Push Pull, 6 channel 4.5 5.5 V, Open Collector NPN, 3 channel 10 30 V, Open Collector NPN, 3 channel	4.5 V 5.5 V, TTL/RS422 10 V 30 V, TTL/RS422 10 V 27 V, HTL/Push Pull 4.5 V 30 V, TTL/HTL universal
20 N axial / 40 N radial	50 N axial / 100 N radial
IP 64	IP 67
-	-
≤ 50 kHz / ≤ 200 kHz	≤ 300 kHz
0 °C +60 °C	−20 °C +85 °C

- · Compact diameter
- Rugged, low-cost design
- Interfaces: Open collector NPN, TTL/RS-422 or HTL/Push
  Pull
- Connection via cable outlet, for radial or axial use with open ends or fitted with an M12 connector
- Face mount flange with solid shaft
- Housing for simple clamping ring mounting
- Any number of lines possible from 1 to 2,048

- Face mount flange, servo flange, blind and through hollow chaft
- Housing unit: Ø 58 mm; compact mounting depth, large bearing distance
- Flange and stator couplings enable diverse mounting options
- Number of lines: up to 5,000 pulses
- Cable outlet, radial M23 or M12 male connector
- TTL/RS-422 and HTL/Push-Pull, universal interface TTL/ HTL with 4.5 V DC to 30 V DC
- Hollow shafts: metal up to Ø 5/8", insulated up to Ø 15 mm; clamping at the front and back

→ F-110

→ F-120







High resolution, programmable encoder for demanding applications



DGS34/DGS35


Encoder with a large hollow shaft for harsh ambient conditions

Technical data overview			
Numbers of lines / pulses fromto	Type E 100 2,048 Type B 1 10,000 Type A 1 65,536	120 16,384	
Mechanical design	Solid shaft, face mount flange Solid shaft, servo flange Blind hollow shaft Through hollow shaft	Blind hollow shaft, through hollow shaft	
Electrical interface	4.5 V 5.5 V, TTL/RS422 10 V 32 V, HTL/Push Pull 10 V 32 V, TTL/RS422 4.5 V 32 V, TTL/HTL programmable 4.5 V 5.5 V, sin/cos 1.0 V <sub>SS</sub>	5 V, TTL 5 15 V, HTL/TTL 8 24 V, HTL	
Permissible shaft load (solid shaft)	40 N axial / 80 N radial	-	
Enclosure rating up to	IP 67	IP 66	
Programmable	<b>✓</b>	-	
Maximum output frequency	≤ 820 kHz	≤ 600 kHz	
Ambient temperature	Up to -40 °C to +100 °C	−20 °C +70 °C	

#### At a glance

- · Short installation depth
- High resolution of up to 16 bits
- Optional programming: output voltage, zero pulse position, zero impulse width, counting direction, and pulse count.
- Connection: radial or axial cable outlet, M23 or M12 male connector, radial or axial
- Incremental encoder with 3.5" diameter
- Pulses per revolution: 120 ... 16,384
- Selection of various electrical interfaces: TTL/RS-422, HTL/Push Pull and Open Collector
- High enclosure rating:IP 66
- Blind hollow shaft for shaft diameters up to 30 mm or 1-1/8"
- Connection via cable outlet or 10-pin MIL male connector

**Detailed information** 



#### **DKV60** measuring wheel encoder

Rugged, high-performance measuring wheel incremental encoder



#### DFV60 measuring wheel encoder

High-resolution, programmable measuring wheel incremental encoder

1 2,000	1 65,536
Measuring drum, knurled surface Measuring drum, O ring surface	2 measuring wheels, 0 ring surface
4.5 V 5.5 V, TTL/RS422 10 V 30 V, HTL/Push Pull	4.5 V 32 V TTL/HTL programmable
-	-
IP 65	IP 65
-	✓
≤ 50 kHz / ≤ 200 kHz	≤ 820 kHz
-10 °C +60 °C	−20 °C +100 °C

- Complete, pre-assembled measuring system
- Measuring wheel with knurl or 0-ring for adaptation to the measuring surface
- Mounting bracket made from anti-corrosive spring steel
- High resolution up to 0.1 mm (1 ... 2,000 pulses/revolution)
- Electrical interfaces: Open collector NPN, TTL/RS-422 or HTL/Push Pull
- Connection via cable outlet, for radial or axial use with open ends or fitted with an M12 connector

- Rotating spring arm for universal use
- 300 mm wheel circumference with 0 ring made from NBR70
- Mounting arm and measuring wheels made from aluminum
- Programming output voltage, zero pulse position, zero impulse width, counting direction, and pulse count
- Connection: radial M12 connector outlet or radial/axial cable outlet
- Electrical interfaces: 5 V & 24 V TTL/RS-422, 24 V HTL/ Push Pull
- · Remote zero set possible

→ F-210

## THE MULTI-FIT INCREMENTAL ENCODER





#### **Product description**

The DBS36 Core incremental encoder features impressively high mechanical flexibility, excellent technical properties, and a number of variations. A blind hollow shaft with a shaft diameter of up to 8 mm and a face mount flange with 6 mm and 1/4" solid shaft are available. The design with face mount flange offers 2 different flanges with 6 different mounting hole patterns and a servo

groove for mounting with servo clamps. The hollow shaft design has a universal stator coupling that can be used for multiple typical mounting hole circles. All models have compact dimensions and a universal cable outlet that allows for cables to run in an axial or radial direction.

#### At a glance

- · Connection with universal cable outlet
- Designs with blind hollow shaft or face mount flange with solid shaft
- Face mount flange with 6 mounting hole patterns and servo groove
- Hollow shaft with universal stator coupling
- Compact housing diameter of 37 mm with compact construction depth,
- Electrical interfaces: TTL/RS-422, HTL/Push Pull and Open Collector NPN
- Number of lines: 10 to 2,500
- Temperature range: -20 °C... +85 °C
- Enclosure rating: IP 65

#### Your benefits

- The universal cable outlet allows for use in tight spaces and for flexible cabling
- Face mount flange with various mounting hole patterns provides high flexibility when mounting in existing and new applications
- Face mount flange with servo groove makes mounting with servo clamps possible
- The universal stator coupling of the DBS36 Core allows for easy device replacement without adapting the application

- Shafts in metric and US design enable worldwide use.
- The high flexibility of the mechanical interface of the encoder and the available accessories allow for the use of a single design in many applications
- Long-term and reliable operation thanks to a high enclosure rating, temperature resistance and bearing lifetime



#### Additional information

Fields of application F-83		
Detailed technical dataF-83		
Type code		
Ordering informationF-87		
Interfaces F-90		
Dimensional drawings F-91		
Proposed fittingF-93		
PIN assignmentF-93		
Recommended accessories F-94		



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



### Fields of application

There are numerous application possibilities for positioning and speed measurement, such as in the textile industry, propulsion

technology, storage and conveyors, packaging machines, printing presses, glass industry, and elevators

#### Detailed technical data

#### Performance

Pulses per revolution	10 2,500
Measurement step	90° electric/pulse
Measurement step deviation	± 18°/pulses per revolution
Error limits	± 54°/pulses per revolution
Duty cycle	≤ 0.5 ± 5%
Initialization time	< 3 ms

#### Mechanical data

Mechanical design	Solid shaft, face mount flange Blind hollow shaft
Shaft diameter	
Solid shaft, face mount flange	6 mm x 12 mm 1/4" x 15.5 mm
Blind hollow shaft	8 mm (shaft diameter 1/4", 6 mm, 5 mm via collet possible – (see Accessories))
Mass	150 g (with connecting cable)
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum
Cable material	PVC
Start up torque	0.5 Ncm (+20 °C)
Operating torque	0.4 Ncm (+20 °C)
Permissible shaft movement, axial static/dynamic	
Blind hollow shaft	± 0.5 mm, ± 0.2 mm
Permissible shaft movement, radial static/dynamic	
Blind hollow shaft	± 0.3 mm, ± 0.1 mm
Permissible shaft load, radial/axial <sup>1)</sup>	
Solid shaft, face mount flange	40 N (radial) 20 N (axial)
Operating speed	6,000/min <sup>2)</sup> 6,000/min <sup>3)</sup>
Maximum operating speed	8,000 rpm <sup>4)</sup>
Rotor moment of inertia	
Solid shaft, face mount flange	0.6 gcm <sup>2</sup>
Blind hollow shaft	0.8 gcm <sup>2</sup>
Bearing lifetime	2 x 10^9 revolutions
Max. angular acceleration	≤ 500,000 rad/s²

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Higher values possible by limiting the overall service life.

 $<sup>^{\</sup>rm 2)}\, \text{Solid}$  shaft: Self-warming 3.3 K per 1,000 rpm.

 $<sup>^{\</sup>rm 3)}$  Hollow shaft: Self-warming 4.7 K per 1,000 rpm.

<sup>&</sup>lt;sup>4)</sup> No continuous operation. Signal quality is degraded.

#### Electrical data

Electrical interface	4,5 V 5,5 V, TTL/RS422 7 V 30 V, TTL/RS422 7 V 30 V, HTL Push Pull 7 V 27 V, HTL Push Pull, 3 channel 4.5 V 5.5 V, Open Collector NPN 4.5 V 30 V, Open Collector NPN
Connection type	Cable, 5 or 8-wire, universal, 0.5 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 1.5 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 3 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 5 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 10 m <sup>2)</sup> Cable, 8-wire with male connector M12, universal, 0.5 m Cable, 8-wire with male connector M23, universal, 0.5 m <sup>1)</sup>
Operating current without load	
4.5 V5.5 V, TTL/RS422	≤ 50 mA
4.5 V 5.5 V, Open Collector NPN	≤ 50 mA
Max. power consumption without load	
7 V 30 V, TTL/RS422	< 0.5 W
7 V 30 V, HTL Push Pull	< 0.5 W
7 V 27 V, HTL Push Pull	< 0.5 W
4.5 V 30 V, Open Collector NPN	< 0.5 W
Max. load current	
Open Collector	≤ 30 mA
TTL/HTL	≤ 30 mA
Maximum output frequency	300 kHz
Reference signal, number	1
Reference signal, position	90° electric, logically gated with A and B
Reverse polarity protection	
4,5 V 5,5 V, TTL/RS422	-
7 V 30 V, TTL/RS422	<b>✓</b>
7 V 30 V, HTL Push Pull	<b>√</b>
7 V 27 V, HTL Push Pull	<b>√</b>
4.5 V 5.5 V, Open Collector NPN	V
4.5 V 30 V, Open Collector NPN	V
Short-circuit protection of outputs 3)	
4,5 V 5,5 V, TTL/RS422	V
7 V 30 V, TTL/RS422	V
7 V 30 V, HTL Push Pull	V
7 V 27 V, HTL Push Pull	V
4.5 V 5.5 V, Open Collector NPN	V
4.5 V 30 V, Open Collector NPN	V
MTTFd: mean time to dangerous failure	600 years (EN ISO 13849-1) <sup>4)</sup>
10.1.00	

<sup>1)</sup> M23 male connector for central mounting

<sup>&</sup>lt;sup>2)</sup> Number of wires depending on electrical interface: Interface A, C, E: 8-wire; Interface G, P, R: 5-wire.

<sup>&</sup>lt;sup>3)</sup> Short-circuit protection is only guaranteed when Us and GND are connected correctly.


<sup>&</sup>lt;sup>4)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

#### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3 (class A)
Enclosure rating	IP 65
Permissible relative humidity	90% (condensation of optical surfaces not permitted)
Operating temperature range	
4,5 V 5,5 V, TTL/RS422	-20 °C +85 °C (-35 °C +95 °C upon request)
7 V 30 V, TTL/RS422	-20 °C +85 °C (-35 °C +95 °C upon request)
7 V 30 V, HTL Push Pull	-20 °C +85 °C (-35 °C +95 °C upon request)
7 V 27 V, HTL Push Pull	-20 °C+70 °C
4.5 V 5.5 V, Open Collector NPN	-20 °C +85 °C (-35 °C +95 °C upon request)
4.5 V 30 V, Open Collector NPN	-20 °C +85 °C (-35 °C +95 °C upon request)
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	100 g/6 ms (EN 60068-2-27)
Resistance to vibrations	20 g, 10 Hz 2,000 Hz (EN 60068-2-6)

#### Type code


Solid shaft



<sup>&</sup>lt;sup>1)</sup> Number of wires depending on electrical interface: Interface A, C, E: 8-wire; Interface G, P, R: 5-wire.

<sup>2)</sup> Other pulse on request.

#### Hollow shaft



<sup>1)</sup> Shaft diameter 1/4", 6 mm, 5 mm via collet possible (see Accessories).

## Pulses per revolution 1)

	E
	0010
	0020
	0050
	0100
	0120
	0125
	0200
	0250
	0256
	0300
Pulses per revolution	0360
	0400
	0500
	0512
	0600
	1000
	1024
	1200
	2000
	2048
	2500

<sup>1)</sup> Additional available upon request.

<sup>&</sup>lt;sup>2)</sup> Number of wires depending on electrical interface: Interface A, C, E: 8-wire; Interface G, P, R: 5-wire.

<sup>3)</sup> Other pulse on request.

## Ordering information

## Solid shaft, face mount flange

• Shaft diameter: 6 mm

Electrical interface	Voltage range	Connection type	Range of pulses per revolution	Туре	Part no.
			100	DBS36E-S3AJ00100	1061237
			360	DBS36E-S3AJ00360	1061238
		Cable, 8-wire universal, 0.5 m	400	DBS36E-S3AJ00400	1061239
		0.0 111	500	DBS36E-S3AJ00500	1061240
			1,024	DBS36E-S3AJ01024	1060867
			100	DBS36E-S3AK00100	1060535
	4.5 V 5.5 V		360	DBS36E-S3AK00360	1060536
			400	DBS36E-S3AK00400	1060537
		Cable, 8-wire, universal,	500	DBS36E-S3AK00500	1060538
		1.5 m	1,000	DBS36E-S3AK01000	1060539
TTL/RS422			1,024	DBS36E-S3AK01024	1060144
			2,048	DBS36E-S3AK02048	1058602
			2,500	DBS36E-S3AK02500	1060268
		Cable, 8-wire universal, 0.5 m	500	DBS36E-S3CJ00500	1066387
			100	DBS36E-S3CK00100	1063772
	7 V 30 V		500	DBS36E-S3CK00500	1062944
		Cable, 8-wire, universal,	1,000	DBS36E-S3CK01000	1064515
		1.5 m	1,024	DBS36E-S3CK01024	1067267
			2,048	DBS36E-S3CK02048	1059906
			2,500	DBS36E-S3CK02500	1068997
		Cable, 8-wire, universal,	100	DBS36E-S3EJ00100	1061242
			360	DBS36E-S3EJ00360	1061243
			400	DBS36E-S3EJ00400	1061244
		0.5 m	500	DBS36E-S3EJ00500	1061245
			1,000	DBS36E-S3EJ01000	1061246
			1,024	DBS36E-S3EJ01024	1061247
			100	DBS36E-S3EK00100	1060540
			200	DBS36E-S3EK00200	1062679
	<b>7</b> 1/ <b>2</b> 01/		256	DBS36E-S3EK00256	1065241
HTL/Push Pull	7 V 30 V		360	DBS36E-S3EK00360	1060541
		Cable, 8-wire, universal,	400	DBS36E-S3EK00400	1060542
		1.5 m	500	DBS36E-S3EK00500	1060543
			1,000	DBS36E-S3EK01000	1060544
			1,024	DBS36E-S3EK01024	1060545
			2,048	DBS36E-S3EK02048	1059907
			2,500	DBS36E-S3EK02500	1061133
		Cable, 8-wire with male connector M12, universal, 0.5 m	2,048	DBS36E-S3EP02048	1068156


ì		
ı		

Cable, 8-wire, universal, 1.00 DBS36E-BBA00360 1061249 106250	Electrical interface	Voltage range	Connection type	Range of pulses per revolution	Туре	Part no.
Cable, 8-wire universal, 0.5 m				360	DBS36E-BBAJ00360	1061249
0.5 m 500				400	DBS36E-BBAJ00400	1061250
1,000 DBS36E-BBA/01000 1061252 1,024 DBS36E-BBA/01024 1060868 100 DBS36E-BBAK00100 1060524 360 DBS36E-BBAK000360 1060525 400 DBS36E-BBAK00360 1060526 1000 DBS36E-BBAK00360 1060526 1000 DBS36E-BBAK00000 1060527 1.5 m 1,000 DBS36E-BBAK01000 1060527 2,048 DBS36E-BBAK01004 1060147 2,048 DBS36E-BBAK01004 1060147 2,048 DBS36E-BBAK02048 1058603 2,500 DBS36E-BBAK02004 1061235 1.5 m 1,000 DBS36E-BBCK0100 1061235 2,500 DBS36E-BBCK0100 1061235 3.5 m 1,000 DBS36E-BBCK0100 1065289 2,500 DBS36E-BBCK0100 1065289 2,500 DBS36E-BBCK0100 1065289 2,500 DBS36E-BBCK0100 1065289 2,048 DBS36E-BBCK0100 1061253 360 DBS36E-BBC0048 1061254 400 DBS36E-BBC00400 1061255 2,000 DBS36E-BBC00400 1061255 2,000 DBS36E-BBC0000 1061256 2,000 DBS36E-BBC00000 1061256 2,000 DBS36E-BBC00000 1061256 2,000 DBS36E-BBC00000 1061258 2,000 DBS36E-BBC00000 1061258 2,000 DBS36E-BBC00000 1061258 2,000 DBS36E-BBC00000 1061258 2,000 DBS36E-BBC00000 1066259 1,004 DBS36E-BBC00000 1066531 1,004 DBS36E-BBC00000 1060531 1,5 m 500 DBS36E-BBC00000 1060531 1,004 DBS36E-BBC00000 1060533 1,024 DBS36E-BBC00000 1060533 1,024 DBS36E-BBC00000 1060534 2,048 DBS36E-BBC00100 1060534 2,048 DBS36E-BBC00100 10605370 DBS36E-BBC00000 1060534 2,048 DBS36E-BBC00100 10605370 DBS36E-BBC00000 1060534 2,048 DBS36E-BBC00100 1060534				500	DBS36E-BBAJ00500	1061251
### TTL/RS422    TTL/RS422   A.5 V 5.5 V   360   DBS36E-BBAK00100   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060526   1060527   1.5 m   1,000   DBS36E-BBAK00500   1060528   1,024   DBS36E-BBAK01004   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060147   1060148   1.5 m   1,000   DBS36E-BBAK02500   1061235   1061235   1060148   1.5 m   1,000   DBS36E-BBCK00100   1066589   1060148   1.5 m   1,000   DBS36E-BBCK00100   1066589   1060148			0.5 111	1,000	DBS36E-BBAJ01000	1061252
4.5 V 5.5 V  360 DBS36E.BBAK00360 1060525 400 DBS36E.BBAK00400 1060526 400 DBS36E.BBAK00400 1060526 400 DBS36E.BBAK00500 1060527 1.5 m 1,000 DBS36E.BBAK01004 1060527 2,048 DBS36E.BBAK01004 1060147 2,048 DBS36E.BBAK0248 1058603 2,500 DBS36E.BBAK0248 1058603 2,500 DBS36E.BBAK02500 1061235 4.5 m 1,000 DBS36E.BBAK02500 1061235 4.5 m 1,000 DBS36E.BBCK01000 1060148 4.5 m 1,000 DBS36E.BBCK01000 1060148 4.5 m 1,000 DBS36E.BBCK01000 1060148 4.5 m 1,000 DBS36E.BBCW01000 1061253 4.5 m 1,000 DBS36E.BBCW01000 1061254 4.5 m 1,000 DBS36E.BBCW01000 1061254 4.5 m 1,000 DBS36E.BBCW01000 1061255 4.5 m 1,000 DBS36E.BBCW01000 1061256 4.5 m 1,000 DBS36E.BBCW01000 1061258 4.5 m 1,000 DBS36E.BBCW01000 1061258 4.5 m 1,000 DBS36E.BBCW01000 1060125 4.5 m 1,000 DBS				1,024	DBS36E-BBAJ01024	1060868
TTL/RS422  Cable, 8-wire, universal, 1.5 m 1,000 DBS36E-BBAK00400 1060527  1.5 m 1,000 DBS36E-BBAK01000 1060528  1,024 DBS36E-BBAK01024 1060147  2,048 DBS36E-BBAK01024 1060147  2,048 DBS36E-BBAK02048 1058603  2,500 DBS36E-BBAK02500 1061235  Cable, 8-wire universal, 100 DBS36E-BBCK01000 1060148  1.5 m 1,000 DBS36E-BBCK01000 106589  Cable, 8-wire with male connector M12, universal, 100 DBS36E-BBE00400 1061253  360 DBS36E-BBE00400 1061254  400 DBS36E-BBE100400 1061255  Cable, 8-wire universal, 0.5 m 1,000 DBS36E-BBE100400 1061255  Cable, 8-wire universal, 0.5 m 1,000 DBS36E-BBE100400 1061257  1,024 DBS36E-BBE10040 1061257  1,024 DBS36E-BBE10000 1061257  1,024 DBS36E-BBE10000 1061257  2,500 DBS36E-BBE10000 1061257  2,500 DBS36E-BBE10000 10661257  2,500 DBS36E-BBE10000 10661257  1,024 DBS36E-BBEK0000 1066300  DBS36E-BBEK0000 1066300  DBS36E-BBEK0000 1066300  DBS36E-BBEK0000 1066301  1,5 m 500 DBS36E-BBEK0000 1066301  1,5 m 500 DBS36E-BBEK0000 1066531  1,000 DBS36E-BBEK0000 1066531  1,000 DBS36E-BBEK0000 1066531  2,048 DBS36E-BBEK00044 1066534  2,048 DBS36E-BBEK0000 1066531  1,000 DBS36E-BBEK0000 1066531  2,048 DBS36E-BBEK0000 1066531				100	DBS36E-BBAK00100	1060524
TTL/RS422  Cable, 8-wire, universal, 1.5 m 1,000 DBS36E-BBAK00500 1060527 1,004 DBS36E-BBAK01004 1060528 1,024 DBS36E-BBAK01024 1060147 2,048 DBS36E-BBAK02048 1058603 2,500 DBS36E-BBAK02048 1058603 1,004 DBS36E-BBAK02048 1061235 1,5 m 1,000 DBS36E-BBCK00100 1060148 1,5 m 1,000 DBS36E-BBCK00100 1065589 1061255 1,000 DBS36E-BBCK00100 1065589 1061255 1,000 DBS36E-BBE00100 1061253 1,000 DBS36E-BBE00100 1061254 1,000 DBS36E-BBE00100 1061254 1,000 DBS36E-BBE00100 1061255 1,000 DBS36E-BBE00100 1060530 1,000 DBS36E-BBEK00100 1060530 1,000 DBS36E-BBER00100 1060530 1,000 DBS36E-BBEV00100 1060530 1,000 DBS36E-BBEV00100 1060530 1,000		4.5 V 5.5 V		360	DBS36E-BBAK00360	1060525
1.5 m 1,000 DBS36E-BBAK01000 1060528 1,024 DBS36E-BBAK01001 1060147 2,048 DBS36E-BBAK01024 1060147 2,048 DBS36E-BBAK02048 1058603 2,500 DBS36E-BBAK02500 1061235 1.5 m 1,000 DBS36E-BBCK00100 1060548 1.5 m 1,000 DBS36E-BBCK01000 1065589 10.5 m 100 DBS36E-BBCK01000 1065589 10.5 m 100 DBS36E-BBCV01000 1061253 360 DBS36E-BBCJ00100 1061254 400 DBS36E-BBCJ00360 1061254 400 DBS36E-BBCJ00360 1061254 400 DBS36E-BBCJ00360 1061255 10.5 m 1,000 DBS36E-BBCJ0000 1061255 10.5 m 1,000 DBS36E-BBCJ00100 1061257 1,024 DBS36E-BBCJ00200 1068715 2,500 DBS36E-BBCJ00200 1068715 2,500 DBS36E-BBCJ00200 1068715 2,500 DBS36E-BBCJ00200 1062490 DBS36E-BBCJ00200 106320 360 DBS36E-BBCJ00200 106320 360 DBS36E-BBCJ00200 106320 106320 360 DBS36E-BBCJ00200 106320 360 DBS36E-BBCJ00200 1066330 1.5 m 500 DBS36E-BBCJ00200 1066531 1.5 m 500 DBS36E-BBCJ00200 1066531 1.5 m 500 DBS36E-BBCJ00204 1060533 1,024 DBS36E-BBCJ00204 1060534 2,048 DBS36E-BBCJ00204 1050534 2,048 DBS36E-BBCJ00204 1050534 2,048 DBS36E-BBCJ00204 1050534 2,048 DBS36E-BBCJ00204 10505770 2000 DBS36E-BBCJ00200 10605770 2000 DBS36E-BBCJ00200 10005770 2000 DBS36E-BBCJ00200 10005				400	DBS36E-BBAK00400	1060526
1,024 DBS36E-BBAK01024 1060147 2,048 DBS36E-BBAK0248 1058603 2,500 DBS36E-BBAK0248 1058603 2,500 DBS36E-BBAK02500 1061235 2,500 DBS36E-BBAK02500 1061235 1.5 m 1,000 DBS36E-BBCK00100 1065589  Cable, 8-wire with male connector M12, universal, 100 DBS36E-BBC00100 1061253 360 DBS36E-BBL00360 1061254 400 DBS36E-BBL00360 1061254 400 DBS36E-BBL00400 1061255 Cable, 8-wire universal, 500 DBS36E-BBL00500 1061256 0.5 m 1,000 DBS36E-BBL00100 1061257 1,024 DBS36E-BBL00200 1068715 2,500 DBS36E-BBL00200 1068715 2,500 DBS36E-BBEK00100 1060529 HTL/Push Pull 7 V 30 V  Physic Pull 100 DBS36E-BBEK00100 1060529 Cable, 8-wire, universal, 400 DBS36E-BBEK00360 1066330 1,000 DBS36E-BBEK00360 1066531 1.5 m 500 DBS36E-BBEK00500 1066531 1.5 m 500 DBS36E-BBEK00500 1060532 1,000 DBS36E-BBEK00500 1060533 1,004 DBS36E-BBEK001024 1060534 2,048 DBS36E-BBEK01024 1059910 Cable, 8-wire with male connector M12, universal, 100 DBS36E-BBEK00100 1060534 2,048 DBS36E-BBEK01024 1059910 10605770	TTL/RS422		Cable, 8-wire, universal,	500	DBS36E-BBAK00500	1060527
Cable, 8-wire, universal, 1.5 m			1.5 m	1,000	DBS36E-BBAK01000	1060528
Cable, 8-wire, universal, 1.5 m 1,000 DBS36E-BBEK00100 1061235  7 V 30 V Cable, 8-wire with male connector M12, universal, 0.5 m 100 DBS36E-BBEK01000 1065589  Cable, 8-wire with male connector M12, universal, 0.5 m 100 DBS36E-BBEJ00100 1061253 360 DBS36E-BBEJ00400 1061254 400 DBS36E-BBEJ00400 1061255 10.5 m 1000 DBS36E-BBEJ00500 1061256 10.5 m 1000 DBS36E-BBEJ00500 1061256 10.5 m 1000 DBS36E-BBEJ00500 1061256 10.5 m 1000 DBS36E-BBEJ00500 1061257 10.024 DBS36E-BBEJ00500 1061257 10.024 DBS36E-BBEJ00500 106256 10.024 10.0257 10.024 DBS36E-BBEJ00500 1060529 10.02490 10.024				1,024	DBS36E-BBAK01024	1060147
Total				2,048	DBS36E-BBAK02048	1058603
1.5 m				2,500	DBS36E-BBAK02500	1061235
TV30 V  Cable, 8-wire with male connector M12, universal, 0.5 m  100 DBS36E-BBCP02048 1062240  1061253 360 DBS36E-BBEJ00100 1061254 400 DBS36E-BBEJ00400 1061255 10.5 m  Cable, 8-wire universal, 0.5 m  100 DBS36E-BBEJ00400 1061254 400 DBS36E-BBEJ00500 1061255 10.5 m  1,000 DBS36E-BBEJ00500 1061256 1.000 DBS36E-BBEJ00500 1061257 1.000 DBS36E-BBEJ00000 1068715 1.000 DBS36E-BBEJ00500 1068715 1.000 DBS36E-BBEN02000 1068715 1.000 DBS36E-BBEN02000 1068715 1.000 DBS36E-BBEN02000 1060529 1.000 DBS36E-BBEN00200 1060529 1.5 m  Cable, 8-wire, universal, 400 DBS36E-BBEN00300 1060530 DBS36E-BBEN00300 1060531 1.5 m  Cable, 8-wire, universal, 400 DBS36E-BBEN00500 1060531 1.000 DBS36E-BBEN00500 1060532 1.000 DBS36E-BBEN00500 1060533 1.000 DBS36E-BBEN00500 1060534 2.048 DBS36E-BBEN002048 1059910 DBS36E-BBEN000100 1065770 DBS36E-BBEN00100 106			Cable, 8-wire, universal,	100	DBS36E-BBCK00100	1060148
HTL/Push Pull  7 V 30 V  Cable, 8-wire, universal, 1.5 m  Cable, 8-wire, universal, 1.5 m  Cable, 8-wire, universal, 1.5 m  Cable, 8-wire, universal, 1.0 DBS36E-BBEK00200 1066534 1.000 DBS36E-BBEK00360 1060534 1.000 DBS36E-BBEK00360 1.0005570 1				1,000	DBS36E-BBCK01000	1065589
HTL/Push Pull  7 V 30 V  Cable, 8-wire universal, 0.5 m  Cable, 8-wire universal, 0.5 m  1,000 DBS36E-BBEJ00500 1061256  1,000 DBS36E-BBEJ01000 1061257  1,024 DBS36E-BBEJ01024 1061258  2,000 DBS36E-BBEJ02000 1068715  2,500 DBS36E-BBEJ02500 1062490  100 DBS36E-BBEK00100 1060529  200 DBS36E-BBEK00100 1060529  200 DBS36E-BBEK00200 1064320  360 DBS36E-BBEK00200 1064320  360 DBS36E-BBEK00360 1060530  Cable, 8-wire, universal, 400 DBS36E-BBEK00400 1060531  1.5 m  500 DBS36E-BBEK00500 1060531  1,004 DBS36E-BBEK01004 1060534  2,048 DBS36E-BBEK01024 1060534  2,048 DBS36E-BBEK02048 1059910  Cable, 8-wire with male connector M12, univer-		7 V 30 V	connector M12, univer-	2,048	DBS36E-BBCP02048	1062240
HTL/Push Pull  7 V 30 V  Cable, 8-wire universal, 0.5 m  1,000 DBS36E-BBEJ00500 1061256  1,000 DBS36E-BBEJ01000 1061257  1,024 DBS36E-BBEJ01024 1061258  2,000 DBS36E-BBEJ02000 1068715  2,500 DBS36E-BBEJ02500 1062490  100 DBS36E-BBEK00100 1060529  200 DBS36E-BBEK00200 1064320  360 DBS36E-BBEK00360 1060530  Cable, 8-wire, universal, 400 DBS36E-BBEK00400 1060531  1.5 m  500 DBS36E-BBEK00500 1060532  1,000 DBS36E-BBEK01000 1060533  1,024 DBS36E-BBEK01004 1060534  2,048 DBS36E-BBEK02048 1059910  Cable, 8-wire with male connector M12, univer-				100	DBS36E-BBEJ00100	1061253
Cable, 8-wire universal, 0.5 m				360	DBS36E-BBEJ00360	1061254
HTL/Push Pull  7 V 30 V  Cable, 8-wire, universal, 1,000  Cable, 8-wire, universal, 1,000  DBS36E-BBEJ01000  1061257  1,024  DBS36E-BBEJ01024  1061258  2,000  DBS36E-BBEJ02000  1068715  2,500  DBS36E-BBEK00200  1060529  200  DBS36E-BBEK00100  1060529  360  DBS36E-BBEK00200  1064320  360  DBS36E-BBEK00360  1060530  1.5 m  500  DBS36E-BBEK00400  1060531  1,000  DBS36E-BBEK01000  1060532  1,000  DBS36E-BBEK01000  1060533  1,024  DBS36E-BBEK01024  1060534  2,048  DBS36E-BBEK02048  1059910  Cable, 8-wire with male connector M12, univer-				400	DBS36E-BBEJ00400	1061255
1,024 DBS36E-BBEJ01024 1061258 2,000 DBS36E-BBEJ02000 1068715 2,500 DBS36E-BBEJ02500 1062490 100 DBS36E-BBEK00100 1060529 200 DBS36E-BBEK00200 1064320 360 DBS36E-BBEK00360 1060530 Cable, 8-wire, universal, 1.5 m 500 DBS36E-BBEK00400 1060531 1,000 DBS36E-BBEK00500 1060532 1,000 DBS36E-BBEK01000 1060533 1,024 DBS36E-BBEK01004 1060534 2,048 DBS36E-BBEK01024 1060534 2,048 DBS36E-BBEK02048 1059910 Cable, 8-wire with male connector M12, univer-			Cable, 8-wire universal,	500	DBS36E-BBEJ00500	1061256
2,000 DBS36E-BBEJ02000 1068715 2,500 DBS36E-BBEJ02500 1062490 100 DBS36E-BBEK00100 1060529 200 DBS36E-BBEK00200 1064320 360 DBS36E-BBEK00360 1060530 1.5 m DBS36E-BBEK00400 1060531 500 DBS36E-BBEK00500 1060532 1,000 DBS36E-BBEK01000 1060533 1,024 DBS36E-BBEK01024 1060534 2,048 DBS36E-BBEK01024 1059910 Cable, 8-wire with male connector M12, univer-			0.5 m	1,000	DBS36E-BBEJ01000	1061257
HTL/Push Pull  7 V 30 V  2,500  DBS36E-BBEJ02500  1062490  100  DBS36E-BBEK00100  1060529  200  DBS36E-BBEK00200  1064320  360  DBS36E-BBEK00360  1060530  400  DBS36E-BBEK00400  1060531  1.5 m  500  DBS36E-BBEK00500  1060532  1,000  DBS36E-BBEK01000  1060533  1,024  DBS36E-BBEK01024  1060534  2,048  DBS36E-BBEK02048  1059910  Cable, 8-wire with male connector M12, univer-				1,024	DBS36E-BBEJ01024	1061258
HTL/Push Pull  7 V 30 V  200  DBS36E-BBEK00200  1064320  360  DBS36E-BBEK00360  1060530  Cable, 8-wire, universal, 1.5 m  500  DBS36E-BBEK00400  1060531  1,000  DBS36E-BBEK00500  1060532  1,000  DBS36E-BBEK01000  1060533  1,024  DBS36E-BBEK01024  1060534  2,048  DBS36E-BBEK01024  1060534  2,048  DBS36E-BBEK02048  1059910  Cable, 8-wire with male connector M12, univer-				2,000	DBS36E-BBEJ02000	1068715
HTL/Push Pull  7 V 30 V  200  DBS36E-BBEK00200  1064320  360  DBS36E-BBEK00360  1060530  Cable, 8-wire, universal, 1.5 m  500  DBS36E-BBEK00400  1060531  1,000  DBS36E-BBEK00500  1060532  1,000  DBS36E-BBEK01000  1060533  1,024  DBS36E-BBEK01024  1060534  2,048  DBS36E-BBEK02048  1059910  Cable, 8-wire with male connector M12, univer-				2,500	DBS36E-BBEJ02500	1062490
200 DBS36E-BBEK00200 1064320 360 DBS36E-BBEK00360 1060530 Cable, 8-wire, universal, 1.5 m 500 DBS36E-BBEK00400 1060532 1,000 DBS36E-BBEK01000 1060533 1,024 DBS36E-BBEK01024 1060534 2,048 DBS36E-BBEK02048 1059910 Cable, 8-wire with male connector M12, univer-				100	DBS36E-BBEK00100	1060529
Cable, 8-wire, universal, 1.5 m 500 DBS36E-BBEK00500 1060532 1,000 DBS36E-BBEK01000 1060533 1,024 DBS36E-BBEK01024 1060534 2,048 DBS36E-BBEK02048 1059910 Cable, 8-wire with male connector M12, univer-	HTL/Push Pull	7 V 30 V		200	DBS36E-BBEK00200	1064320
1.5 m 500 DBS36E-BBEK00500 1060532 1,000 DBS36E-BBEK01000 1060533 1,024 DBS36E-BBEK01024 1060534 2,048 DBS36E-BBEK02048 1059910 Cable, 8-wire with male connector M12, univer-				360	DBS36E-BBEK00360	1060530
1.5 m 500 DBS36E-BBEK00500 1060532 1,000 DBS36E-BBEK01000 1060533 1,024 DBS36E-BBEK01024 1060534 2,048 DBS36E-BBEK02048 1059910 Cable, 8-wire with male connector M12, univer-			Cable, 8-wire, universal,	400	DBS36E-BBEK00400	1060531
1,024 DBS36E-BBEK01024 1060534 2,048 DBS36E-BBEK02048 1059910 Cable, 8-wire with male connector M12, univer-				500	DBS36E-BBEK00500	1060532
2,048 DBS36E-BBEK02048 1059910  Cable, 8-wire with male connector M12, univer-				1,000	DBS36E-BBEK01000	1060533
Cable, 8-wire with male 100 DBS36E-BBEP00100 1065770 connector M12, univer-				1,024	DBS36E-BBEK01024	1060534
connector M12, univer-				2,048	DBS36E-BBEK02048	1059910
000 DDCCC DDDCCCC				100	DBS36E-BBEP00100	1065770
			connector M12, univer- sal, 0.5 m	200	DBS36E-BBEP00200	1068935

Electrical interface	Voltage range	Connection type	Range of pulses per revolution	Туре	Part no.
			200	DBS36E-BBPK00200	1065144
			500	DBS36E-BBPK00500	1064120
		Cable, 8-wire, universal, 1.5 m	1,000	DBS36E-BBPK01000	1067836
		2.0	2,048	DBS36E-BBPK02048	1059911
Onen cellecter	4.5 V 5.5 V		2,500	DBS36E-BBPK02500	1065791
Open collector	Ca		360	DBS36E-BBAP00360	1067379
		Cable, 8-wire with male	500	DBS36E-BBAP00500	1068192
		connector M12, univer-	1,000	DBS36E-BBAP01000	1066259
		sal, 0.5 m	1,024	DBS36E-BBAP01024	1062784
			2,500	DBS36E-BBAP02500	1062785

#### Interfaces

Signal outputs for electrical interfaces TTL and HTL



CW with view on the encoder shaft in direction "A", compare dimensional drawing.


Interfaces G, P, R only for channels A, B, Z.

Supply voltage	Output
4.5 V 5.5 V	TTL/RS422
7 V 30 V	TTL/RS422
7 V 30 V	HTL Push Pull
7 V 27 V	HTL Push Pull, 3 channel
4.5 V 5.5 V	Open Collector NPN
4.5 V 30 V	Open Collector NPN


F

#### Dimensional drawings (dimensions in mm)


Solid shaft, face mount flange, shaft 6 mm x 12 mm, standard hole pattern




Solid shaft, face mount flange, shaft 6 mm x 12 mm, Type A flange design hole pattern




Solid shaft, face mount flange, shaft 1/4" x 15.5 mm, standard hole pattern





## Proposed fitting




Diameter X	Encoder	Collet
5 mm		2066991
6 mm		2056390
1/4"	1/4" DBS36E-BB 8 mm	upon request
8 mm		not required


## PIN assignment

#### 8-core cable

View of M12 device connector on cable

View of M23 device connector on cable





Wire color	Pin 8-pole for M12	Pin 12-pole for M23	Signal HTL/OC 3-channel	Signal TTL/HTL 6-channel	Explanation
brown	1	6	Not connected	A-	Signal wire
white	2	5	A	A	Signal wire
black	3	1	Not connected	B-	Signal wire
pink	4	8	В	В	Signal wire
Yellow	5	4	Not connected	Z-	Signal wire
purple	6	3	Z	Z	Signal wire
blue	7	10	GND	GND	Ground connection of the encoder
Red	8	12	+Us	+Us	Supply voltage
-	-	9	Not connected	Not connected	Not connected
-	-	2	Not connected	Not connected	Not connected
-	-	11	Not connected	Not connected	Not connected
-	-	7	Not connected	Not connected	Not connected
Shield	Shield	Shield	Shield	Shield	Shield (connected with housing on the encoder side)

#### Recommended accessories

### Mounting systems

Mounting brackets and plates

#### Mounting bracket

Figure	Brief description	Туре	Part no.
4	Mounting bracket for encoder with centering hub 20 mm, including mounting kit for face mount flange	BEF-WF-20	2066393

#### Flanges

#### Flange plate

Figure	Brief description	Туре	Part no.
60	Flange adapter, adaption of face mount flange with centering hub 20 mm to 33 mm servo flange, aluminum	BEF-FA-020-033	2066312

#### Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
1	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	O-ring for measuring wheels (circumference 200 mm)	BEF-OR-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-OR-083-050	2064076

#### Servo clamps

Figure	Brief description	Туре	Part no.
<b>3 3 3</b>	Servo clamps, small, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-RESOL	2039082

#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Two-sided stator coupling, screw hole diameter 42 - 46 mm, slot width 3.2 mm	BEF-DS-DBS36	2066301

#### Shaft adaptation

#### Collets and clamping rings

Figure	Brief description	Туре	Part no.
	Collet for blind hollow shaft, shaft diameter 5 mm, external diameter 8 mm	SPZ-005-AD-A	2066991
	Collet for blind hollow shaft, shaft diameter 6 mm, external diameter 8 mm	SPZ-006-DD36-A	2056390

#### Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
	Bellows coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $+/-$ 4°; max. speed 10,000 rpm, $-$ 30 °C to $+$ 120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10^{\circ}$ to $+80^{\circ}$ C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°, max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
10	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-30$ °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
(i	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985

## Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight Head B: cable	5 m	DOL-1208-G05MAC1	6032867
-	Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869
	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm $^{1)}$	2 m	DOL-2312-G02MLA3	2030682
		7 m	DOL-2312-G07MLA3	2030685
		10 m	DOL-2312-G10MLA3	2030688
		15 m	DOL-2312-G15MLA3	2030692
•		20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
		1.5 m	DOL-2312-G1M5MA3	2029212
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA3	2029213
700	Head B: cable  Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	5 m	DOL-2312-G05MMA3	2029214
		10 m	DOL-2312-G10MMA3	2029215
		20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Warning! Only in combination with electrical interfaces A, C, E and P.

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature: -40 °C +85 °C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-G	6027538
(H)-()	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , Ø 5.6 mm		LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm		LTG-2411-MW	6027530
_	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516

#### Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B:  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	STE-2312-G01	2077273

<sup>→</sup> For additional accessories, please see page K-668 onwards



## THE MULTI-FIT INCREMENTAL ENCODER





#### **Product description**

The DBS50 Core incremental encoder features impressively high mechanical flexibility, excellent technical properties, and a number of variations. The DBS50E has a face mount flange with 50 mm diameter and a solid shaft with 8 mm diameter. The housing diameter is extremely compact at 37 mm and thus saves valuable space. The face mount flange offers 2 different mounting hole

patterns and a servo groove for mounting with servo clamps. The encoder has compact dimensions and a universal cable outlet that allows for cables to run in an axial or radial direction. The DBS50 Core incremental encoder is fully compatible with the DDS50E incremental encoder.

#### At a glance

- · Connection with universal cable outlet
- Face mount flange with 8 mm solid shaft
- Face mount flange with 2 mounting hole patterns and servo groove
- Compact housing diameter of 37 mm with compact construction depth, flange diameter 50 mm
- Various electrical interfaces: TTL/ RS-422, HTL/Push Pull and Open Collector NPN
- Number of lines from 10 to 2,500 possible
- Temperature range: -20 °C... +85 °C
- Enclosure rating: IP 65

#### Your benefits

- The universal cable outlet allows for use in tight spaces and for flexible cabling
- Face mount flange with various mounting hole patterns for easy device replacement without adapting the application
- Face mount flange with servo groove makes mounting with servo clamps possible
- The high flexibility of the mechanical interface of the encoder and the available accessories allow for the use of a single design in many applications
- The compact housing diameter saves valuable space
- Long-term and reliable operation thanks to a high enclosure rating, temperature resistance and bearing lifetime



#### Additional information

Fields of application F-99
Detailed technical dataF-99
Type code
Ordering informationF-103
Interfaces
Dimensional drawings F-105
PIN assignmentF-106
Recommended accessories F-106



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



### Fields of application

There are numerous application possibilities for positioning and speed measurement, such as in the textile industry, propulsion

technology, storage and conveyors, packaging machines, printing presses, glass industry, and elevators

#### Detailed technical data

#### Performance

Pulses per revolution	10 2,500
Measurement step	90° / electric/pulse
Measurement step deviation	± 18°/pulses per revolution
Error limits	± 54°/pulses per revolution
Duty cycle	≤ 0.5 ± 5%
Initialization time	< 3 ms

#### Mechanical data

Solid shaft, face mount flange
8 mm x 15.5 m
170 g (with connecting cable 1.5 m)
Stainless steel
Aluminum
Aluminum
PVC
0.9 Ncm (+20 °C)
0.6 Ncm (+20 °C)
30 N (axial) 50 N (radial)
6,000 / min <sup>1)</sup>
8,000 rpm <sup>2)</sup>
0.65 gcm <sup>2</sup>
2 x 10^9 revolutions
Z X 10 3 Tevolutions

 $<sup>^{1)}</sup>$  Take into account self-heating of 3.3 K per 1,000 revolutions/min when designing the operating temperature range.

 $<sup>^{\</sup>rm 2)}\,\mbox{No}$  continuous operation. Signal quality is degraded.

#### Electrical data

Electrical interface	4,5 V 5,5 V, TTL/RS422 7 V 30 V, TTL/RS422 7 V 30 V, HTL Push Pull 7 V 27 V, HTL Push Pull, 3 channel 4.5 V 5.5 V, Open Collector NPN 4.5 V 30 V, Open Collector NPN
Connection type	Cable, 5 or 8-wire, universal, 0.5 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 1.5 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 3 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 5 m <sup>2)</sup> Cable, 5 or 8-wire, universal, 10 m <sup>2)</sup> Cable, 8-wire with male connector M12, universal, 0.5 m Cable, 8-wire with male connector M23, universal, 0.5 m <sup>1)</sup>
Operating current without load	
4.5 V5.5 V, TTL/RS422	≤ 50 mA
4.5 V 5.5 V, Open Collector NPN	≤ 50 mA
Max. power consumption without load	
7 V 30 V, TTL/RS422	< 0.5 W
7 V 30 V, HTL Push Pull	< 0.5 W
7 V 27 V, HTL Push Pull	< 0.5 W
4.5 V 30 V, Open Collector NPN	< 0.5 W
Operating voltage range	4.5 V 5.5 V 7 V 30 V
Max. load current	
Open Collector	≤ 30 mA
тть/нть	≤ 30 mA
Maximum output frequency	300 kHz
Reference signal, number	1
Reference signal, position	90° electric, logically gated with A and B
Reverse polarity protection	
4,5 V 5,5 V, TTL/RS422	-
7 V 30 V, TTL/RS422	V
7 V 30 V, HTL Push Pull	V
7 V 27 V, HTL Push Pull	V
4.5 V 5.5 V, Open Collector NPN	<b>v</b>
4.5 V 30 V, Open Collector NPN	<i>v</i>
Short-circuit protection of outputs 3)	
4,5 V 5,5 V, TTL/RS422	-
7 V 30 V, TTL/RS422	V
7 V 30 V, HTL Push Pull	V
7 V 27 V, HTL Push Pull	V
4.5 V 5.5 V, Open Collector NPN	V
4.5 V 30 V, Open Collector NPN	V
MTTFd: mean time to dangerous failure	600 years (EN ISO 13849-1) 4)

 $<sup>^{\</sup>mbox{\tiny 1)}}\,\mbox{M23}$  male connector for central mounting.

<sup>&</sup>lt;sup>2)</sup> Number of wires depending on electrical interface: Interface A, C, E: 8-wire; Interface G, P, R: 5-wire.


<sup>&</sup>lt;sup>3)</sup> Short-circuit protection is only guaranteed when Us and GND are connected correctly.

<sup>4)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3 (class A)
Enclosure rating	IP 65
Permissible relative humidity	90% (condensation of optical surfaces not permitted)
Operating temperature range	
4,5 V 5,5 V, TTL/RS422	-20 °C +85 °C (-35 °C +95 °C upon request)
7 V 30 V, TTL/RS422	-20 °C +85 °C (-35 °C +95 °C upon request)
7 V 30 V, HTL Push Pull	-20 °C +85 °C (-35 °C +95 °C upon request)
7 V 27 V, HTL Push Pull	-20°C+70°C
4.5 V 5.5 V, Open Collector NPN	-20 °C +85 °C (-35 °C +95 °C upon request)
4.5 V 30 V, Open Collector NPN	-20 °C +85 °C (-35 °C +95 °C upon request)
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	100 g/6 ms (EN 60068-2-27)
Resistance to vibrations	20 g, 10 Hz 2,000 Hz (EN 60068-2-6)

#### Type code



<sup>&</sup>lt;sup>1)</sup> Number of wires depending on electrical interface: Interface A, C, E: 8-wire; Interface G, P, R: 5-wire.

#### Pulses per revolution 1)



<sup>1)</sup> Additional available upon request.

<sup>&</sup>lt;sup>2)</sup> Other pulse on request.

## Ordering information


## Solid shaft, face mount flange

• Shaft diameter: 8 mm

Electrical interface	Voltage range	Connection type	Range of pulses per revolution	Туре	Part no.
			100	DBS50E-S5AJ00100	1061259
			360	DBS50E-S5AJ00360	1061260
			400	DBS50E-S5AJ00400	1061261
		Cable, 8-wire universal,	500	DBS50E-S5AJ00500	1061262
		0.5 m	1,000	DBS50E-S5AJ01000	1061263
			1,024	DBS50E-S5AJ01024	1060870
			2,048	DBS50E-S5AJ02048	1061085
			2,500	DBS50E-S5AJ02500	1061086
	45.7 55.7		100	DBS50E-S5AK00100	1060685
	4.5 V 5.5 V		360	DBS50E-S5AK00360	1060686
TTL/RS422			400	DBS50E-S5AK00400	1060687
		Cable, 8-wire, universal,	500	DBS50E-S5AK00500	1060688
		1.5 m	1,000	DBS50E-S5AK01000	1060145
			1,024	DBS50E-S5AK01024	1060689
			2,048	DBS50E-S5AK02048	1057446
			2,500	DBS50E-S5AK02500	1062722
		Cable, 8-wire with male connector M12, univer-	500	DBS50E-S5AP00500	1066755
		sal, 0.5 m	2,000	DBS50E-S5AP02000	1064388
	7 V 30 V	,	1,000	DBS50E-S5CK01000	1066828
		Cable, 8-wire, universal, 1.5 m	2,048	DBS50E-S5CK02048	1059902
		1.1 C.1	2,500	DBS50E-S5CK02500	1061172
			100	DBS50E-S5EJ00100	1061264
			360	DBS50E-S5EJ00360	1061265
		Cable, 8-wire universal,	400	DBS50E-S5EJ00400	1061266
		0.5 m	500	DBS50E-S5EJ00500	1061267
			1,000	DBS50E-S5EJ01000	1061268
			1,024	DBS50E-S5EJ01024	1061269
			2,000	DBS50E-S5EK02000	1062698
	7 V 30 V		100	DBS50E-S5EK00100	1060690
			360	DBS50E-S5EK00360	1060691
HTL/Push Pull		O-bl- Oii	400	DBS50E-S5EK00400	1060692
2/ 1 do 1 d	60 .	Cable, 8-wire, universal, 1.5 m	500	DBS50E-S5EK00500	1060693
			1,000	DBS50E-S5EK01000	1060694
			1,024	DBS50E-S5EK01024	1060695
			2,048	DBS50E-S5EK02048	1059903
			2,500	DBS50E-S5EK02500	1061230
			100	DBS50E-S5EP00100	1067000
		Cable, 8-wire with male connector M12, univer- sal 0.5 m	360	DBS50E-S5EP00360	1066061
			1,000	DBS50E-S5EP01000	1062886
			1,024	DBS50E-S5EP01024	1068207
			2,000	DBS50E-S5EP02000	1066174

#### Interfaces

Signal outputs for electrical interfaces TTL and HTL



7 V 30 V	TTL/RS422
7 V 30 V	HTL Push Pull
7 V 27 V	HTL Push Pull, 3 channel
4.5 V 5.5 V	Open Collector NPN
4.5 V 30 V	Open Collector NPN

Output

TTL/RS422

Supply voltage


4.5 V ... 5.5 V

CW with view on the encoder shaft in direction "A", compare dimensional drawing.

Interfaces G, P, R only for channels A, B, Z.

F


## Dimensional drawings (dimensions in mm)




#### 8-core cable

View of M12 device connector on cable

View of M23 device connector on cable





Wire color	Pin 8-pole for M12	Pin 12-pole for M23	Signal HTL/OC 3-channel	Signal TTL/HTL 6-channel	Explanation
brown	1	6	Not connected	A-	Signal wire
white	2	5	A	A	Signal wire
black	3	1	Not connected	B-	Signal wire
pink	4	8	В	В	Signal wire
Yellow	5	4	Not connected	Z-	Signal wire
purple	6	3	Z	Z	Signal wire
blue	7	10	GND	GND	Ground connection of the encoder
Red	8	12	+Us	+Us	Supply voltage
-	=	9	Not connected	Not connected	Not connected
-	=	2	Not connected	Not connected	Not connected
-	=	11	Not connected	Not connected	Not connected
-	-	7	Not connected	Not connected	Not connected
Shield	Shield	Shield	Shield	Shield	Shield (connected with housing on the encoder side)

#### Recommended accessories

### Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
•	Mounting bracket for encoder with centering hub 30 mm including mounting kit for face mount flange	BEF-WF-30	2066391

#### Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
	Measuring wheel with 0-ring (NBR70) for 8 mm solid shaft, circumference 200 mm	BEF-MR008020R	2055223
	Measuring wheel with 0-ring (NBR70) for 8 mm solid shaft, circumference 300 mm	BEF-MR008030R	2055635
	O-ring for measuring wheels (circumference 200 mm)	BEF-OR-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-0R-083-050	2064076

F

#### Modular measuring wheel system

Brief description	Туре	Part no.
Measuring wheel system, desired mounting position: left, for DBS50E-S5	BEF-MRS-08-1	2071956
Measuring wheel system, desired mounting position: right, for DBS50E-S5	BEF-MRS-08-2	2071953

#### Servo clamps

Figure	Brief description	Туре	Part no.
	Servo clamps, small, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-RESOL	2039082

### Shaft adaptation

### Shaft couplings

Figure	Brief description	Туре	Part no.
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
	Bar coupling, shaft diameter 8 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0808-S	5314177
	Bar coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
10	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, –30 °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704

## Connectivity

#### Plug connectors and cables

#### Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight	2 m	DOL-1208-G02MAC1	6032866
		5 m	DOL-1208-G05MAC1	6032867
-	Head B: cable  Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm², Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869
	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm <sup>1)</sup>	2 m	DOL-2312-G02MLA3	2030682
		7 m	DOL-2312-G07MLA3	2030685
		10 m	DOL-2312-G10MLA3	2030688
		15 m	DOL-2312-G15MLA3	2030692
•		20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, suitable for drag chain, PUR, shielded, $4 \times 2 \times 0.25$ mm <sup>2</sup> + $2 \times 0.5$ mm <sup>2</sup> + $1 \times 0.14$ mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	1.5 m	DOL-2312-G1M5MA3	2029212
		3 m	DOL-2312-G03MMA3	2029213
-		5 m	DOL-2312-G05MMA3	2029214
		10 m	DOL-2312-G10MMA3	2029215
		20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Warning! Only in combination with electrical interfaces A, C, E and P.

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^{\circ}$ C $+85~^{\circ}$ C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-G	6027538
(F)=O	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057

# Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , $\emptyset$ 5.6 mm		LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	Doubles	LTG-2411-MW	6027530
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2612-MW	6028516

# Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B:  Operating temperature: –20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40  ^{\circ}\text{C} \dots +125  ^{\circ}\text{C}$	STE-2312-G01	2077273

<sup>→</sup> For additional accessories, please see page K-668 onwards

# RUGGED, HIGH-PERFORMANCE INCREMENTAL ENCODER





# **Product description**

The DKS40 incremental encoder offers an outstanding price-performance ratio. Its housing is made of solid zinc die cast and, with an external diameter of 50 mm, it is extremely compact, saving

valuable installation space. Use of mini-disc technology makes the DKS40 extremely resistant to shock and vibration. In addition, the DKS40 has a high IP 64 enclosure rating.

# At a glance

- · Compact diameter
- · Rugged, low-cost design
- Interfaces: Open collector NPN, TTL/ RS-422 or HTL/Push Pull.
- Connection via cable outlet, for radial or axial use with open ends or fitted with an M12 connector
- · Face mount flange with solid shaft
- Housing for simple clamping ring mounting
- Any number of lines possible from 1 to 2,048

#### Your benefits

- Low-cost encoder with outstanding quality
- Withstands harsh ambient conditions due to high IP protection class and rugged design
- Universal cable outlet enables axial and radial cable guidance
- Compact dimensions enable simple installation even where space is cramped



#### Additional information

Fields of application F-111
Detailed technical dataF-111
Type code
Ordering informationF-113
Dimensional drawingsF-114
PIN assignmentF-115
Recommended accessories F-115

→ www.mysick.com/en/DKS40

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

• Due to the variety of products, there is a wide range of application possibilities such as in tool machines, textile

machines, wood processing machines, packaging machinery

# Detailed technical data

# Performance

Pulses per revolution	1 2,048
Error limits binary pulses	0.09° 1)
Error limits non-binary pulses	0.13° <sup>2)</sup>
Measuring step deviation at binary number of lines	0.035°
Measuring step deviation at non-binary number of lines	0.07°
Initialization time	40 ms
Measurement step	90° electrical/pulses per revolution

 $<sup>^{\</sup>mbox{\tiny 1)}}$  "Binary" number of lines: 2n, where n is a whole number

# Mechanical data

Mechanical design	Solid shaft
Shaft diameter	8 mm x 13 mm
Mass	0.18 kg
Start up torque	0.6 Ncm (+20 °C)
Operating torque	0.4 Ncm (+20 °C)
Permissible shaft load, radial/axial	40 N, 20 N
Maximum operating speed	6,000 rpm
Rotor moment of inertia	6 gcm <sup>2</sup>
Bearing lifetime	2 x 10^9 revolutions
Max. angular acceleration	5 x 10^5 rad/s²

#### Electrical data

Electrical interface	4.5 5.5 V, TTL/RS422, 6 channel 10 30 V, HTL/Push Pull, 6 channel 4.5 5.5 V, Open Collector NPN, 3 channel 10 30 V, Open Collector NPN, 3 channel		
Connection type	Cable, 8-wire, universal outlet, 0.5 m $^{1)}$ Cable, 8-wire, universal outlet, 1.5 m $^{1)}$ Cable, 8-wire, universal outlet, 3.0 m $^{1)}$ Cable, 8-wire, universal outlet, 5.0 m $^{1)}$ Cable, 8-pin, universal outlet, 1.5 m, male connector M12 $^{1)}$		
Operating current without load	≤ 40 mA		
Supply voltage	4.5 V 5.5 V 10 V 30 V		
Load current	≤ 30 mA		
Maximum output frequency			
Open Collector NPN	≤ 50 kHz		
TTL/RS422	≤ 200 kHz		
HTL/Push Pull	≤ 200 kHz		

<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.

<sup>&</sup>lt;sup>2)</sup> "Non-binary" number of lines: 2n, where n is not a whole number

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

Reference signal, number	1
Reference signal, position	90° electric, logically gated with A and B
MTTFd: mean time to dangerous failure	600 years (EN ISO 13849-1) <sup>2)</sup>


<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.

#### Ambient data

EMC	EN 61000-6-2, EN 61000-6-3
Enclosure rating as per IEC 60529	IP 64
Air humidity	90% 1)
Operating temperature range	0 °C +60 °C
Storage temperature range	-40 °C +70 °C, without packaging
Resistance to shocks	50 g/ 7 ms (EN 60068-2-27)
Resistance to vibrations	20 g / 10 Hz 2,000 Hz (EN 60068-2-6)

<sup>1)</sup> Condensation of optical surfaces not permitted.

# Type code



<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

# Ordering information


• Mechanical design: solid shaft, face mount flange


Electrical interface	Connection type	Pulses per revolution	Туре	Part no.
		10	DKS40-R5J00010	1034621
		20	DKS40-R5J00020	1034622
		50	DKS40-R5J00050	1034623
		100 DKS40-RS	DKS40-R5J00100	1034624
		200	DKS40-R5J00200	1034625
		250	DKS40-R5J00250	1034626
		256	DKS40-R5J00256	1034627
10 30 V	Cable universal 0.5 m	360	DKS40-R5J00360	1034628
Open Collector NPN	Cable, universal, 0.5 m	500	DKS40-R5J00500	1034629
		512	DKS40-R5J00512	1034630
		720	DKS40-R5J00720	1034631
		800	DKS40-R5J00800	1036154
		1,000	DKS40-R5J01000	1034632
		1,024	DKS40-R5J01024	1034633
		2,000	DKS40-R5J02000	1034813
		2,048	DKS40-R5J02048	1034627 1034628 1034629 1034630 1034631 1036154 1034632 1034633
		4	DKS40-A5J00004	1036293
		10	DKS40-A5J00010	1034634
		20	DKS40-A5J00020	1034635
		50	DKS40-A5J00050	1034636
		100	DKS40-A5J00100	1034637
		200	DKS40-A5J00200	1034638
45 557		250	DKS40-A5J00250	1034639
4.5 5.5 V TTL/RS422	Cable, universal, 0.5 m	360	DKS40-A5J00360	1034641
114 110422		500	DKS40-A5J00500	1034642
		512	DKS40-A5J00512	1034643
		720	DKS40-A5J00720	1034644
		1,000	DKS40-A5J01000	1034645
		1,024	DKS40-A5J01024	1034646
		2,000	DKS40-A5J02000	1034815
		2,048	DKS40-A5J02048	1034816

Electrical interface	Connection type	Pulses per revolution	Туре	Part no.
		10	DKS40-E5J00010	1034647
		20	DKS40-E5J00020	1034648
		50	DKS40-E5J00050	1034649
		100	DKS40-E5J00100	1034650
		200	DKS40-E5J00200	1034651
		250	DKS40-E5J00250	1034652
40. 00.4		256	DKS40-E5J00256	1034653
10 30 V HTL/Push Pull		360	DKS40-E5J00360	1034654
TTLy r don't dil	THE TUST TO THE	500	DKS40-E5J00500	1034655
		512	DKS40-E5J00512	1034656
		720	DKS40-E5J00720	1034657
		1,000	DKS40-E5J01000	1034658
		1,024	DKS40-E5J01024	1034659
		2,000	DKS40-E5J02000	1034817
		2,048	DKS40-E5J02048	1034818

# Dimensional drawings (dimensions in mm)

Face mount flange, cable output






General tolerances according to ISO 2768-mk

# F

# PIN assignment

# Cable, 8-wire

View of male connector, device side



PIN, 8-pin, M12 male connector	Wire colors	OC signal	TTL/HTL signal	Explanation
1	Brown	Not assigned	Ā	Signal wire
2	White	Α	A	Signal wire
3	Black	Not assigned	B	Signal wire
4	Pink	В	В	Signal wire
5	Yellow	Not assigned	Z	Signal wire
6	Violet	Z	Z	Signal wire
7	Blue	GND	GND	Ground connection of the encoder
8	Red	+U <sub>S</sub>	+U <sub>s</sub>	Supply voltage (volt-free to housing)
Screen	Screen	Screen	Screen	Screen, connected to housing on the encoder side. Connected to ground on control side.

# Mounting systems

Mounting brackets and plates

# Mounting bracket

Figure	Brief description	Туре	Part no.
P	Mounting bracket for encoder with centering hub 25 mm, including mounting kit for face mount flange	BEF-WF-25	2032621

# Flanges

# Flange plate

Figure	Brief description	Туре	Part no.
6	Flange adapter, adaption of face mount flange with centering hub 20 mm to 33 mm servo flange, aluminum	BEF-FA-020-033	2066312
0	Flange adapter, adaption of face mount flange with 25 mm centering hub to size 60 face mount flange with 36 mm centering hub, aluminum	BEF-FA-025-036	2034226
	Flange adapter, adaption of face mount flange with centering hub 25 mm to 50 mm servo flange, aluminum	BEF-FA-025-050	2032622
6	Flange adapter, adaption of face mount flange with 25 mm centering hub to 60 mm square mounting plate, aluminum	BEF-FA-025-060RCA	2032623
	Flange adapter, adaptation of face mount flange with 25 mm centering hub to 60 mm square mounting plate with shock absorbers, aluminum	BEF-FA-025-060RSA	2032624
E.	Flange adapter, adaption of face mount flange with 25 mm centering hub to 63 mm square mounting plate, aluminum	BEF-FA-025-063-REC	2033631

# Other mounting accessories

# Mounting bell

Figure	Brief description	Туре	Part no.
6	Mounting bell for encoders with a servo flange, centering collar 50 mm, including mounting kit	BEF-MG-50	5312987

# Servo clamps

Figure	Brief description	Туре	Part no.
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

# Shaft adaptation

# Shaft couplings

Figure	Brief description	Туре	Part no.
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
	Bar coupling, shaft diameter 8 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0808-S	5314177
	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
10	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, –30 °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704

# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight Head B: cable	5 m	DOL-1208-G05MAC1	6032867
-	Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869
		2 m	DOL-2312-G02MLA3	2030682
		7 m	DOL-2312-G07MLA3	2030685
_	Head A: female connector, M23, 12-pin, straight	10 m	m DOL-2312-G10MLA3 20	2030688
	Head B: cable Cable: incremental, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm $^{1)}$	15 m	DOL-2312-G15MLA3	2030692
•		20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
		1.5 m	DOL-2312-G1M5MA3	2029212
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA3	2029213
-	Head B: cable	5 m	m DOL-2312-G05MMA3 202	2029214
	Cable: incremental, suitable for drag chain, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm $^{1)}$	10 m	DOL-2312-G10MMA3	2029215
		20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217

<sup>1)</sup> Warning! Only in combination with electrical interfaces A, C, E and P.

Figure	Brief description	Туре	Part no.
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057

# Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , $\emptyset$ 5.6 mm	By the meter	LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , $\emptyset$ 7.5 mm		LTG-2411-MW	6027530
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516

# Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
The same of the sa	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B:  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40~^{\circ}$ C +125 $^{\circ}$ C	STE-2312-G01	2077273

<sup>→</sup> For additional accessories, please see page K-668 onwards

# RUGGED, VERSATILE INCREMENTAL ENCODERS FOR INDUSTRIAL APPLICATIONS





# **Product description**

The DBS60 Core is a rugged incremental encoder with a 58 mm diameter and compact installation depth. It offers a large range of mechanical and electrical interfaces. The solid shaft models are available with face mount flange and servo flange. The hollow shaft design is available as a blind hollow shaft and as a through hollow shaft and can receive shafts up to 5/8" (15.875 mm). The optional shaft insulation and the shaft clamping on the back of the encoder are unique to the hollow shafts. In addition

to the standard interfaces 5 V and 24 V TTL/RS422 and 24 V HTL/Push-Pull, the DBS60 Core offers a flexible universal interface which combines the 5 V TTL and 24 V HTL in one product. The high enclosure rating IP 65 and the large ball bearing distance ensure high robustness and reliability, even in the case of high shaft loads. With a resolution of up to 5,000 pulses, the DBS60 Core is the ideal product for standard use in various different industries.

# At a glance

- Face mount flange, servo flange, blind and through hollow shaft
- Housing: Ø 58 mm; compact installation depth, large bearing distance
- Flange and stator couplings enable diverse mounting options
- Number of lines: up to 5,000 pulses
- Cable outlet, radial M23 or M12 male connector
- TTL/RS-422 and HTL/Push-Pull, universal interface TTL/HTL with 4.5 V DC to 30 V DC
- Hollow shafts: metal up to Ø 5/8", isolated up to Ø 15 mm; clamping at the front and back

# 

#### Additional information

Fields of application F-121
Detailed technical dataF-121
Type code
Ordering informationF-128
Mounting suggestion for servo
flange
Dimensional drawingsF-130
Connection typeF-153
Viewing number of resolutions F-153
Zero declaration F-154
Signal outputs F-154
Recommended accessories F-156

### Your benefits

- Diverse installation options due to different flange and shaft designs
- Universal cable outlet and radial connector allow use in tight spaces and make flexible cable routing possible
- Compact housing dimensions save valuable space Optional hollow shaft clamp on the back facilitates mounting
- Protects the encoder against high shaft temperatures and currents through optional isolated shafts
- Flanges and stator couplings with different mounting holes allow diverse mounting options with one encoder variant
- Rugged design with large bearing distance allows high shaft loads and a longer service life
- The TTL/HTL combination interface enables less product variety and reduces storage costs

→ www.mysick.com/en/DBS60\_Core

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# F

# Fields of application

Measuring of position, speed and distance in applications with low to medium requirements on the encoder.

Developed for applications in factory and logistics automation, e.g., in

- · Asynchronous motors
- Elevators
- · Packaging machines
- Warehousing and transport logistics

#### Detailed technical data

# Performance

Pulses per revolution	4 5,000 1)
Measurement step	90° electrical/pulses per revolution
Measurement step deviation	
< 3,600 pulses per revolution	± 18°/pulses per revolution
≥ 3,600 pulses per revolution	± 36°/pulses per revolution
Error limits	Measurement step deviation x 3
Duty cycle	
< 3,600 pulses per revolution	$\leq 0.5 \pm 5\%$
≥ 3,600 pulses per revolution	≤ 0.5 ± 10 %
Initialization time	< 5 ms <sup>2)</sup>

<sup>1)</sup> For available pulses per revolution see type code.

#### Mechanical data

	Solid shaft	Blind hollow shaft	Through hollow shaft
Mechanical design	Solid shaft, servo flange Solid shaft, face mount flange	Blind hollow shaft	Through hollow shaft clamping at the back Through hollow shaft
Shaft diameter	6 mm x 10 mm <sup>1)</sup> 10 mm x 19 mm <sup>1)</sup>	6 mm 8 mm 3/8" 10 mm 12 mm 1/2" 14 mm 15 mm 5/8" 6 mm (shaft isolated) 8 mm (shaft isolated) 10 mm (shaft isolated) 12 mm (shaft isolated) 12 mm (shaft isolated) 14 mm (shaft isolated) 15 mm (shaft isolated)	
Mass	0.3 kg <sup>2)</sup>	0.25 kg <sup>2)</sup>	
Shaft material	Stainless steel	Stainless steel Stainless steel with plastic colla	ar
Flange material	Aluminum		
Housing material	Aluminum		

 $<sup>^{\</sup>scriptscriptstyle 1)}$  Other on request.

<sup>&</sup>lt;sup>2)</sup> After this period valid signals can be read.

<sup>&</sup>lt;sup>2)</sup> Based on an encoder with a connector outlet or a cable with a connector outlet.

<sup>&</sup>lt;sup>3)</sup> Higher values possible by limiting the overall service life.

<sup>&</sup>lt;sup>4)</sup> Take into account self-heating of 3.2 K per 1000 revolutions/min when designing the working temperature range.

<sup>&</sup>lt;sup>5)</sup> Take into account self-heating of 2.6 K per 1,000 revolutions/min when designing the operating temperature range.

<sup>6)</sup> Maximum speed which does not lead to any harm to the encoder. Impact on the service life and signal quality is possible. Please note the maximum output frequency.

	Solid shaft	Blind hollow shaft	Through hollow shaft
Cable material	PVC		
Start up torque	1.2 Ncm (+20 °C)	0.5 Ncm (+20 °C)	
Operating torque	1.1 Ncm (+20 °C)	0.4 Ncm (+20 °C)	
Permissible shaft movement, axial static/dynamic	-	± 0.5 mm, ± 0.2 mm	
Permissible shaft movement, radial static/dynamic	-	± 0.3 mm, ± 0.1 mm	
Permissible shaft load, radial/axial	100 N (radial) <sup>3)</sup> 50 N (axial) <sup>3)</sup>	-	
Operating speed	6,000 / min <sup>4)</sup>	6,000 / min <sup>5)</sup>	
Maximum operating speed	9,000 /min <sup>6)</sup>		
Rotor moment of inertia	33 gcm <sup>2</sup>	50 gcm <sup>2</sup>	
Bearing lifetime	3.6 x 10^9 revolutions		
Max. angular acceleration	500,000 rad/s <sup>2</sup>	500,000 rad/s² 200,000 rad/s² (shaft isolated)	

<sup>1)</sup> Other on request.

#### Electrical data

	Solid shaft	Blind hollow shaft	Through hollow shaft
Electrical interface	$\begin{array}{c} 4.5 \ V \ \ 5.5 \ V, \ TTL/RS422 \ ^{1)} \\ 10 \ V \ \ 30 \ V, \ TTL/RS422 \ ^{1)} \\ 10 \ V \ \ 27 \ V, \ HTL/Push \ Pull \ ^{1)} \\ 4.5 \ V \ \ 30 \ V, \ TTL/HTL \ universa \end{array}$	1) 2)	
Connection type	M23 male connector, 12-pin, rad M12 male connector, 8-pin, rad Cable, 8-wire, universal, 0.5 m <sup>3</sup> Cable, 8-wire, universal, 3 m <sup>3</sup> Cable, 8-wire, universal, 5 m <sup>3</sup> Cable, 8-wire, universal, 10 m <sup>3</sup> Cable, 8-wire, universal, 10 m <sup>3</sup> Cable with male connector M12 Cable with male connector M23	ial ) , 8-pin, universal, 0.5 m <sup>3)</sup>	
Operating current without load			
4.5 V5.5 V, TTL/RS422	≤ 50 mA		
Max. power consumption without load			
10 V 30 V, TTL/RS422	≤ 0.5 W		
10 V 27 V, HTL/Push Pull	≤ 1 W		
4.5 V 30 V, TTL/HTL universal	≤ 0.5 W		
Load current	≤ 30 mA per channel		
Maximum output frequency	300 kHz <sup>5)</sup>		

<sup>1) 6</sup> channels unless otherwise specified.

<sup>&</sup>lt;sup>2)</sup> Based on an encoder with a connector outlet or a cable with a connector outlet.

<sup>&</sup>lt;sup>3)</sup> Higher values possible by limiting the overall service life.

<sup>4)</sup> Take into account self-heating of 3.2 K per 1000 revolutions/min when designing the working temperature range.

<sup>&</sup>lt;sup>5)</sup> Take into account self-heating of 2.6 K per 1,000 revolutions/min when designing the operating temperature range.

<sup>6)</sup> Maximum speed which does not lead to any harm to the encoder. Impact on the service life and signal quality is possible. Please note the maximum output frequency.

<sup>&</sup>lt;sup>2)</sup> Output level depends on the supply voltage.

<sup>&</sup>lt;sup>3)</sup> The universal cable connection is positioned so that it is possible to lay it without bends in a radial or axial direction.

<sup>4)</sup> M23 male connector with central mounting

<sup>5)</sup> Up to 450 kHz on request.

<sup>6)</sup> Short-circuit of another channel or GND permissible for a maximum of 60 s. No protection in the case of a short-circuit channel of Us.

 $<sup>^{7)}</sup>$  Short-circuit of another channel US or GND permissible for a maximum of 30 s.

<sup>8)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

	Solid shaft	Blind hollow shaft	Through hollow shaft
Reference signal, number	1		
Reference signal, position	90° electric, logically gated with	A and B	
Reverse polarity protection	✓		
Short-circuit protection of the outputs			
4.5 V-5.5 V, TTL/RS422	<b>✓</b> 6)		
10 V 30 V, TTL/RS422	<b>✓</b> <sup>7)</sup>		
10 V 27 V, HTL/Push Pull	<b>✓</b> <sup>7)</sup>		
4.5 V 30 V, TTL/HTL universal	<b>✓</b> <sup>7)</sup>		
MTTFd: mean time to dangerous failure 8)	500 years (EN ISO 13849-1)		

 $<sup>^{\</sup>scriptscriptstyle{1)}}\,6$  channels unless otherwise specified.

# Ambient data

	Solid shaft	Blind hollow shaft	Through hollow shaft	
EMC	According to EN 61000-6-2 and EN 61000-6-3			
Enclosure rating	IP 65 on shaft side (acc. to IEC 60529)		IP 65 on housing side (acc. to IEC 60529) <sup>1)</sup> IP 65 on shaft side (acc. to IEC 60529)	
Permissible relative humidity	90% (condensation of optical s	urfaces not permitted)		
Operating temperature range				
4.5 V-5.5 V, TTL/RS422	-20 °C +85 °C			
10 V 30 V, TTL/RS422	-30 °C +100 °C, at a maximum of 3,000 pulses per revolution -30 °C +85 °C, at more than 3,000 pulses per revolution			
10 V 27 V, HTL/Push Pull	-20 °C +85 °C			
4.5 V 30 V, TTL/HTL universal	-30 °C +100 °C, at a maximum of 3,000 pulses per revolution -30 °C +85 °C, at more than 3,000 pulses per revolution			
Storage temperature range	-40 °C +100 °C, without pa	ckaging		
Resistance to shocks	250 g, 3 ms (according to EN 60068-2-27) EN 60068-2-27) 200 g, 3 ms (according to EN 60068-2-27) 200 g, 3 ms, shaft isolated (according to EN 60068-2-27)			
Resistance to vibrations	30 g/10 Hz 2,000 Hz (according to EN 60068-2-6)			

<sup>&</sup>lt;sup>1)</sup> In an assembled male connector.

 $<sup>^{\</sup>mbox{\tiny 2)}}$  Output level depends on the supply voltage.

<sup>&</sup>lt;sup>3)</sup> The universal cable connection is positioned so that it is possible to lay it without bends in a radial or axial direction.

 $<sup>^{\</sup>mathrm{4)}}\,\mathrm{M23}$  male connector with central mounting

<sup>&</sup>lt;sup>5)</sup> Up to 450 kHz on request.

<sup>6)</sup> Short-circuit of another channel or GND permissible for a maximum of 60 s. No protection in the case of a short-circuit channel of U<sub>s</sub>.

<sup>7)</sup> Short-circuit of another channel US or GND permissible for a maximum of 30 s.

<sup>8)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

# Type code


# Solid shaft

Mechanical design 1 Servo flange, solid shaft, Ø 6 mm, length 10 mm 3 Face mount flange, solid shaft, Ø 6 mm, length 10 mm 4 Face mount flange, solid shaft, Ø 10 mm, length 19 mm Electrical interface A 4.5 ... 5.5 V, TTL/RS-422, 6 channel C 10 ... 30 V, TTL/RS-422, 6 channel E 10 ... 27 V, HTL/Push Pull, 6 channel F 4.5 ... 30 V, TTL/HTL universal, 6 channel Connection type
A Male connector M23, 12-pin, radial
C Male connector M12, 8-pin, radial J Cable, 8-wire universal, 0.5 m K Cable, 8-wire, universal, 1.5 m Cable, 8-wire, universal, 3 m L N Cable, 8-wire, universal, 10 m Cable, 8-wire universal, 0.5 m, with male connector M12 Q Cable, 8-wire, universal, 0.5 m, with male connector M23 Stator coupling/flange design O Flange with 3 x M3 3 x M4 Resolution  $\boxed{0004...5,\!000}$  pulses per revolution possible. For pulses see "Pulses per revolution"  $^{1)}$ D B S 6 0 E - S

F

<sup>1)</sup> Other pulse on request.

#### Through hollow shaft



<sup>&</sup>lt;sup>1)</sup> Order collets for 6 mm (only plastic) 8 mm, 3/8", 10 mm, 12 mm, 1/2", 14 mm and 15 mm separately as accessories (see recommended accessories). No collets are necessary for 5/8" shaft diameter. Also available as isolated design on request.

#### Blind hollow shaft

### Mechanical design B Blind hollow shaft, metal, Ø 8 mm C Blind hollow shaft, metal, Ø 3/8" D Blind hollow shaft, metal, Ø 10 mm E Blind hollow shaft, metal, Ø 12 mm F Blind hollow shaft, metal, Ø 1/2' G Blind hollow shaft, metal, Ø 14 mm H Blind hollow shaft, metal, Ø 15 mm J Blind hollow shaft, metal, Ø 5/8" 1) 2 Blind hollow shaft, Ø 8 mm, isolated 3 Blind hollow shaft, Ø 3/8", isolated 4 Blind hollow shaft, Ø 10 mm, isolated 5 Blind hollow shaft, Ø 1/2", isolated 6 Blind hollow shaft, Ø 12 mm, isolated 7 Blind hollow shaft, Ø 14 mm, isolated 8 Blind hollow shaft, Ø 15 mm, isolated Electrical interface A 4.5 ... 5.5 V, TTL/RS-422, 6 channel C 10 ... 30 V, TTL/RS-422, 6 channel E 10 ... 27 V, HTL/Push Pull, 6 channel F 4.5 ... 30 V, TTL/HTL universal, 6 channel Connection type A Male connector M23, 12-pin, radial Male connector M12, 8-pin, radial Cable, 8-wire, universal, 0.5 m K Cable, 8-wire, universal, 1.5 m Cable, 8-wire, universal, 3 m 1 Cable, 8-wire, universal, 10 m P Cable, 8-wire universal, 0.5 m, with male connector M12 Q Cable, 8-wire, universal, 0.5 m, with male connector M23 Stator coupling/flange design 0 Two-sided stator coupling, slot, screw hole circle 63 mm - 83 mm A Without stator coupling, flange with 4 x M2.5 C Locating pin assembly D Stator coupling, 1-sided, slot, bolt circle 33 mm - 48.5 mm 0004 ... 5,000 pulses per revolution possible. For pulses see "Pulses per revolution" D B S 6 0 E - B

F

<sup>&</sup>lt;sup>1)</sup> Order collets for 6 mm (only plastic) 8 mm, 3/8", 10 mm, 12 mm, 1/2", 14 mm and 15 mm separately as accessories (see recommended accessories). No collets are necessary for 5/8" shaft diameter. Also available as isolated design on request.

# Pulses per revolution

	E
	0004
	0005
	0010
	0020
	0048
	0050
	0060
	0100
	0125
	0128
	0180
	0250
	0360
Pulses per revolution	0500
Pulses per revolution	0512
	0600
	1000
	1024
	1200
	1500
	2000
	2048
	2048 2400
	2400
	2400 2500
	2400 2500 3000

# Ordering information

# Blind hollow shaft

• Shaft diameter: 5/8"

• Connection type: cable, 8-wire, universal, 1.5 m

Through hollow shaft
• Shaft diameter: 5/8"

Electrical interface	Voltage range	Connection type	Pulses per revolution	Туре	Part no.
		Cable with male con-	1,024	DBS60E-TJAQ01024	1069756
		nector M23, 12-pin, universal, 0.5 m	2,048	DBS60E-TJAQ02048	1069757
	4.5 V 5.5 V		1,024	DBS60E-TJAK01024	1069746
TTL/RS422		Cable, 8-wire, universal, 1.5 m	2,048	DBS60E-TJAK02048	1069747
		1.5 111	4,096	DBS60E-TJAK04096	1069748
	10 V 30 V	Cable, 8-wire, universal, 1.5 m	1,024	DBS60E-TJCK01024	1070615
			2,048	DBS60E-TJCK02048	1070616
		Cable, 8-wire, universal, 1.5 m	1,024	DBS60E-TJEK01024	1069758
HTL/Push Pull	10 V 27 V		2,048	DBS60E-TJEK02048	1069759
			4,096	DBS60E-TJEK04096	1069760
TTL/HTL universal	4.5 V 30 V Cable, 8-wire, univers	Cable, 8-wire, universal,	1,024	DBS60E-TJFK01024	1070748
			2,048	DBS60E-TJFK02048	1070749
			4,096	DBS60E-TJFK04096	1070750

# Through hollow shaft clamping at the back

• Shaft diameter: 5/8"

• Connection type: cable, 8-wire, universal, 1.5 m

Electrical interface	Voltage range	Pulses per revolution	Туре	Part no.
	4.5 V 5.5 V	1,024	DBS60E-RJAK01024	1069710
		2,048	DBS60E-RJAK02048	1069711
TTL/RS422		4,096	DBS60E-RJAK04096	1069712
	10 V 30 V	1,024	DBS60E-RJCK01024	1070609
		2,048	DBS60E-RJCK02048	1070610
HTL/Push Pull	10 V 27 V	1,024	DBS60E-RJEK01024	1069713
	10 V 27 V	2,048	DBS60E-RJEK02048	1069714
TTL/HTL universal	45V 20V	1,024	DBS60E-RJFK01024	1070744
	4.5 V 30 V	2.048	DBS60E-RJFK02048	1070745

# Solid shaft, servo flange

• **Shaft diameter:** 6 mm (other diameters available on request)

Electrical interface	Voltage range	Connection type	Pulses per revolution	Туре	Part no.
	4.5 V 5.5 V	Cable, 8-wire, universal, 1.5 m	1,000	DBS60E-S1AK01000	1069715
			2,000	DBS60E-S1AK02000	1069716
TTL/RS422	10 V 30 V	Cable, 8-wire, universal, 1.5 m	1,000	DBS60E-S1CK01000	1070611
	10 V 30 V	Cable, 8-wire, universal, 1.5 m	2,000	DBS60E-S1CK02000	1070612
HTL/Push Pull 1	10 V 27 V	Cable, 8-wire, universal, 1.5 m	1,000	DBS60E-S1EK01000	1069717
	10 V 27 V		2,000	DBS60E-S1EK02000	1069718


# Solid shaft, face mount flange

- Shaft diameter: 10 mm (other diameters available on request)
- Connection type: cable, 8-wire, universal, 1.5 m


Electrical interface	Voltage range	Pulses per revolution	Туре	Part no.		
	4.5 V 5.5 V	1,000	DBS60E-S4AK01000	1069719		
		2,000	DBS60E-S4AK02000	1069720		
TTL/RS422		5,000				
	10 V 30 V	1,000	DBS60E-S4CK01000	1070613		
	10 V 30 V	2,000	DBS60E-S4CK02000	1070614		
		1,000	DBS60E-S4EK01000	1069722		
HTL/Push Pull	10 V 27 V	2,000	DBS60E-S4EK02000	1069723		
		5,000	DBS60E-S4EK05000	1069724		
TTL/HTL universal	4 E V 20 V	1,000	DBS60E-S4FK01000	1070746		
	4.5 V 30 V	2,000	DBS60E-S4FK02000	1070747		

# Mounting suggestion for servo flange

Mounting suggestion for small servo clamp (part number 2029166)




Mounting suggestion for half-shell servo clamp (part number 2029165)




# Dimensional drawings (dimensions in mm)


Solid shaft Ø 6 mm, servo flange, male connector connection (S1)




Solid shaft  $\emptyset$  6 mm, servo flange, cable connection





# Solid shaft Ø 10 mm, face mount flange, male connector connection (S4)






Solid shaft Ø 6 mm, face mount flange, male connector connection (S3)






#### Solid shaft Ø 10 mm, face mount flange, cable connection (S4)




Solid shaft Ø 6 mm, face mount flange, cable connection (S3)




F


Blind hollow shaft, male connector connection, two-sided stator coupling, slot, screw hole circle 63 mm - 83 mm



Blind hollow shaft, male connector connection, no stator coupling




Blind hollow shaft, male connector connection, with locating pin assembly





Installation example for blind hollow shaft







Blind hollow shaft, male connector connection, stator coupling, 1-sided, slot, bolt circle 33 mm - 48.5 mm








Installation example for blind hollow shaft




Customer-side


Zero pulse mark on flange under stator coupling

Blind hollow shaft, cable connection, two-sided stator coupling, slot, screw hole circle 63 mm - 83 mm







Installation example for blind hollow shaft



Customer-side

Blind hollow shaft, cable connection, no stator coupling






Installation example for blind hollow shaft




Customer-side

zero pulse mark

# Blind hollow shaft, cable connection, with locating pin assembly




# Installation example for blind hollow shaft




Customer-side

Blind hollow shaft, cable connection, stator coupling, 1-sided, slot, bolt circle 33 mm - 48.5 mm




Installation example for blind hollow shaft




Customer-side


F


Through hollow shaft clamping at the back, male connector connection, two-sided stator coupling, slot, screw hole circle 63 mm – 83 mm







Through hollow shaft clamping at the back, male connector connection, no stator coupling












Installation example for through hollow shaft

F





# Through hollow shaft clamping at the back, male connector connection, with locating pin assembly







Through hollow shaft clamping at the back, male connector connection, one-sided stator coupling, slot, screw hole circle 33 mm - 48.5 mm












Through hollow shaft clamping at the back, cable connection, two-sided stator coupling, slot, screw hole circle 63 mm - 83 mm




Installation example for through hollow shaft




Through hollow shaft clamping at the back, cable connection, no stator coupling






Through hollow shaft clamping at the back, cable connection, with locating pin assembly














Through hollow shaft clamping at the back, cable connection, one-sided stator coupling, slot, screw hole circle 33 mm - 48.5 mm















Through hollow shaft clamping at the front, male connector connection, two-sided stator coupling, slot, screw hole circle 63 mm – 83 mm






### Through hollow shaft clamping at the front, male connector connection, no stator coupling






Customer-side


Through hollow shaft, male connector connection, with locating pin assembly






Customer-side


Through hollow shaft, male connector connection, stator coupling, 1-sided, slot, bolt circle 33 mm - 48.5 mm






Customer-side


Through hollow shaft clamping at the front, cable connection, two-sided stator coupling, slot, screw hole circle 63 mm - 83 mm




Installation example for through hollow shaft




Through hollow shaft clamping at the front, cable connection, no stator coupling







### Through hollow shaft, cable connection, with locating pin assembly










Through hollow shaft, cable connection, stator coupling, 1-sided, slot, bolt circle 33 mm - 48.5 mm







Installation example for through hollow shaft




F


### Connection type

### 8-core cable

View of M12 device connector on cable/housing




View of M23 device connector on cable cable/housing




Colour of wires	Pin 12-pole in M12	Pin 12-pole in M23	Signal OC	Signal TTL; HTL	Explanation
Brown	1	6	Not connected	A-	Signal line
White	2	5	A	Α	Signal line
Black	3	1	Not connected	B-	Signal line
Pink	4	8	В	В	Signal line
Yellow	5	4	Not connected	Z-	Signal line
Lilac	6	3	Z	Z	Signal line
Blue	7	10	GND	GND	Ground connection of the Encoder
Red	8	12	+Us	+Us	Supply voltage
-	-	9	Not connected	Not connected	Not connected
-	-	2	Not connected	Not connected	Not connected
-	-	11	Not connected	Not connected	Not connected
-	-	7	Not connected	Not connected	Not connected
Screen	Screen	Screen	Screen	Screen	Screen (Screen connected to Encoder housing.

### Viewing number of resolutions




### Hollow shaft, clamping at front



Zero pulse is active when screw of clamping is in line with zero pulse mark on flange or housing mark Zero pulse mark on flange Attention!


If stator coupling is mounted, the zero pulse mark can be hidden by the stator coupling

### Hollow shaft, clamping at back



Zero pulse is active when screw of clamping is in line with zero pulse mark on flange or housing mark

### Solid shaft




F

## F

### Signal outputs

Signal outputs for electrical interfaces TTL and HTL



Supply voltage	Output
4.5 5.5 V	TTL
10 30 V	TTL
10 27 V	HTL
4.5 30 V	TTL/HTL universal

CW with view on the encoder shaft in direction "A", compare dimensional drawing.

### Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
()	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

### Flanges

### Flange plate

Figure	Brief description	Туре	Part no.
	Two-sided stator coupling, screw hole circle diameter 63 mm, slot width 3.2 mm	BEF-DS-09	2076214
	Two-sided stator coupling, slot, slot radius 63 mm – 83 mm, slot width 3.2 mm	BEF-DS-10	2076215
	One-sided stator coupling, slots, slot radius 32.75 mm – 142.65 mm, slot width 4.5 mm	BEF-DS-11	2076216
	One-sided stator coupling, slot, slot radius 33 mm – 48.5 mm, slot width 5.1 mm	BEF-DS-12	2076217
	Flange adapter (for hollow shaft) for locating pin assembly (PIN 4 mm)	BEF-DS-13	2076218
	One-sided stator coupling, slot, slot radius 32.1 mm – 37.6 mm, slot width 4.5 mm	BEF-DS-14	2076678
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10 $$	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-063REC	2034225

F

### Other mounting accessories

### Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
(	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
1	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 500 mm	BEF-MR006050R	2055225
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm	BEF-MR010020R	2055224
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm $$	BEF-MR010030R	2049278
	Measuring wheel with O-ring (NBR70) for 10 mm solid shaft, circumference 500 mm $$	BEF-MR010050R	2055227
	0-ring for measuring wheels (circumference 200 mm)	BEF-0R-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-0R-083-050	2064076
	O-ring for measuring wheels (circumference 500 mm)	BEF-OR-145-050	2064074

### Mounting bell

Figure	Brief description	Туре	Part no.
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

### Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

### Shaft adaptation

### Collets and clamping rings

Figure	Brief description	Туре	Part no.
	Metal collet for hollow shaft, shaft diameter 8 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-008-M	2076219
	Metal collet for hollow shaft, shaft diameter 3/8 $^{\rm H}$ (9.525 mm), outer diameter 5/8 $^{\rm H}$ (15.875 mm), metal	SPZ-58Z-38Z-M	2076224
	Metal collet for hollow shaft, shaft diameter 10 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-010-M	2076220
	Metal collet for hollow shaft, shaft diameter 12 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-012-M	2076221
	Metal collet for hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-12Z-M	2076225
	Metal collet for hollow shaft, shaft diameter 14 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-014-M	2076222

Figure	Brief description	Туре	Part no.
	Metal collet for hollow shaft, shaft diameter 15 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-015-M	2076223
	Plastic isolated collet for hollow shaft, shaft diameter 6 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-006-P	2076228
	Plastic isolated collet for hollow shaft, shaft diameter 8 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-008-P	2076229
	Plastic isolated collet for hollow shaft, shaft diameter $3/8$ " (9.525 mm), outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-38Z-P	2076226
	Plastic isolated collet for hollow shaft, shaft diameter 10 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-010-P	2076230
	Plastic isolated collet for hollow shaft, shaft diameter 12 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-012-P	2076231
	Plastic isolated collet for hollow shaft, shaft diameter $1/2$ " (12.7 mm), outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-12Z-P	2076227
	Plastic isolated collet for hollow shaft, shaft diameter 14 mm, outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-014-P	2076232
	Plastic isolated collet for hollow shaft, shaft diameter 15 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-015-P	2076233

### Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
The contract of the contract o	Bellows coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $+/-$ 4°; max. speed 10,000 rpm, $-$ 30 °C to $+$ 120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $+/-$ 4°; max. speed 10,000 rpm, $-$ 30 °C to $+$ 120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial +/- 0.25 mm, axial +/- 0.4 mm, angular +/- 4°; max. revolutions 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10$ °C to +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-10$ °C to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
(c)	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C to $+80$ °C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C to +80° Celsius, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

### Connectors

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight Head B: cable	5 m	DOL-1208-G05MAC1	6032867
A0	Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869
	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm $^{1)}$	2 m	DOL-2312-G02MLA3	2030682
		7 m	DOL-2312-G07MLA3	2030685
_		10 m	DOL-2312-G10MLA3	2030688
		15 m	DOL-2312-G15MLA3	2030692
-		20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
		1.5 m	DOL-2312-G1M5MA3	2029212
	Head As famala compostery MOO 10 min advanight	3 m	DOL-2312-G03MMA3	2029213
	Head A: female connector, M23, 12-pin, straight Head B: cable	5 m	DOL-2312-G05MMA3	2029214
	Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup>	10 m	DOL-2312-G10MMA3	2029215
	+ 2 x 0.5 mm <sup>2</sup> + 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217

<sup>1)</sup> Warning! Only in combination with electrical interfaces A, C, E and P.

### Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-G	6027538

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , $\emptyset$ 5.6 mm		LTG-2308-MWENC	6027529
<u></u>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm		LTG-2411-MW	6027530
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516

### Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B:  Operating temperature:  -20 °C +130 °C	STE-2312-G	6027537

<sup>→</sup> For additional accessories, please see page K-668 onwards



# HIGH RESOLUTION, PROGRAMMABLE ENCODER FOR DEMANDING APPLICATIONS



### **Product description**

The DFS60 is a high-resolution incremental encoder with a diameter of 60 mm. It offers a wide variety of mechanical and electric interfaces and can also be programmed by the customer if required. Programming of the output signal and zero pulse is a unique feature for the

market. The high enclosure rating, wide temperature range, and large ball bearing distance ensure extreme reliability, making the DFS60 the ideal encoder for industrial applications in harsh environments.

### At a glance

- · Short installation depth
- · High resolution of up to 16 bits
- Optional programming: output voltage, zero pulse position, zero impulse width and pulse count.
- Connection: radial or axial cable outlet, M23 or M12 male connector, axial or radial.
- Electrical interfaces: 5 V & 24 V TTL/ RS-422, 24 V HTL/Push Pull
- Mechanical interfaces: face mount flange or servo flange, blind hollow shaft or through hollow shaft
- · Remote zero set possible

### Your benefits

- Reduction of storage costs and downtimes due to programmability by the customer
- The wide range of different mechanical and electrical interfaces enables the optimum adaptation of the encoder to the application-specific installation situation
- Excellent concentricity even at high speeds
- High resolution of up to 16 bits ensures precise measurements for demanding applications

- Long-term and reliable operation thanks to a high enclosure rating, temperature resistance and bearing lifetime
- The ability to program using the PGT-08-S programming software and the PGT-10-Pro display programming device enables fast and flexible adaptation of the encoder to customer requirements
- Programmable zero pulse position simplifies installation



### Additional information

Fields of application	F-163
Detailed technical data	F-163
Viewing number of resolutions	F-167
Type code	F-167
Dimensional drawings	F-174
Proposed fitting	F-182
PIN assignment	F-182
Interfaces	F-183
Recommended accessories	F-185

→ www.mysick.com/en/DFS60

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



### Fields of application

 Applications in factory and logistics automation for measuring position, speed, and distance: e.g., in printing machines, textile machines, wood processing, packaging machinery

### Detailed technical data

### Performance

	Eco	Basic	Advanced
Pulses per revolution 1) 2)	100 2,048	1 10,000	1 65,536
Pulses per revolution at sin/cos 1.0 V <sub>ss</sub>	-	1,024	-
Measurement step	90° electrical/pulses per revolu	ution	
Measuring step deviation at non-binary number of lines			
Pulses 1 99	-	± 0.08°	± 0.04°
Pulses 100 10,000	± 0.2°	± 0.01°	± 0.008°
Pulses > 10,000	-		± 0.002°
Measuring step deviation at binary number of lines			
Pulses 1 64	-	± 0.05°	± 0.03°
Pulses 128 8,192	± 0.15°	± 0.008°	± 0.008°
Pulses 16,384 65,536	-		± 0.0015°
Reference signal			
Number	1		
Location	90°, electric, logically gated wit	th A and B/sine and cosine	
Error limits	± 0.3°	± 0.05°	± 0.03°

 $<sup>^{\</sup>mbox{\tiny 1)}}$  See maximum viewing number of resolutions

### Electrical data

	Eco	Basic	Advanced
Electrical interface	4.5 V 5.5 V, TTL/RS422		
	10 V 32 V, HTL/Push Pull		
	10 V 32 V, TTL/RS422		
	-	4.5 V 5.5 V, sin/cos 1.0 V <sub>SS</sub>	
	_	4.5 V 32 V, HTL/Push Pull, 0-	SET on M23 male connector 2)
	-	4.5 V 5.5 V, TTL/RS422, 0-SE	ET on M23 male connector 2)
	-	4.5 V 32 V, TTL/RS422, 0-SE	T on M23 male connector 2)
	-	4.5 V 32 V, TTL/HTL program	mable 1)
	-	4.5 V 32 V, TTL/HTL program connector <sup>1) 2)</sup>	mable, 0-SET on M23 male

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Factory setting, output level TTL.

<sup>&</sup>lt;sup>2)</sup> For a detailed list see "Pulses per revolution"

<sup>3)</sup> Under mechanical zero set width.

<sup>&</sup>lt;sup>2)</sup> Only with device variants with M23 male connector outlet in conjunction with the electrical interfaces M,U,V and W.

<sup>3)</sup> Under mechanical zero set width.

<sup>&</sup>lt;sup>4)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

 $<sup>^{\</sup>rm 5)}$  Short-circuit of another channel  $\rm U_S$  or GND permissible for a maximum of 30 s.

<sup>6)</sup> Short-circuit of another channel or GND permissible for a maximum of 30 s.

<sup>&</sup>lt;sup>7)</sup> TTL programming with  $\geq$  5.5 V: Short-circuit of another channel or GND permissible for a maximum of 30 s.

 $<sup>^{(8)}</sup>$  HTL or TTL programming with< 5.5 V: Short-circuit of another channel, U $_{
m S}$  or GND permissible for a maximum of 30 s.

<sup>&</sup>lt;sup>9)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

	Eco	Basic	Advanced
Initialization time after power on			
4.5 V 5.5 V, TTL/RS422	40 ms		
10 V 32 V, HTL/Push Pull	40 ms		
10 V 32 V, TTL/RS422	40 ms		
$4.5\mathrm{V}\dots5.5\mathrm{V}$ , $\mathrm{sin/cos}1.0\mathrm{V_{SS}}$	-	40 ms	-
4.5 V 32 V, HTL/Push Pull, 0-SET	-	Max. 30 ms	
4.5 V 5.5 V, TTL/RS422, 0-SET	-	Max. 30 ms	
4.5 V 32 V, TTL/RS422, 0-SET	-	Max. 30 ms	
4.5 V 32 V, TTL/HTL programmable	-	Max. 30 ms/32 ms <sup>3)</sup>	
4.5 V 32 V, TTL/HTL programmable, 0-SET	-	Max. 30 ms/32 ms <sup>3)</sup>	
0-set function		H - active (L = 0 3 V, H = 4	U <sub>s</sub> V)
	Cable, 8-wire, universal, 1.5 m Cable, 8-wire, universal, 3 m <sup>4)</sup> Cable, 8-wire, universal, 5 m <sup>4)</sup> M12 male connector, 8-pin, rac M12 male connector, 8-pin, axi M23 male connector, 12-pin, rac M23 male connector, 12-pin, axi	lial al adial	
Max. load current	≤ 30 mA		
Operating current without load	40 mA		
Load resistance			
4.5 V 5.5 V, $\sin/\cos 1.0 V_{SS}$	-	min. 120 Ω	-
Max. power consumption without load			
10 V 32 V, HTL/Push Pull	0.5 W		
10 V 32 V, TTL/RS422	0.5 W		
4.5 V 32 V, HTL/Push Pull, 0-SET	-	0.7 W	
4.5 V 5.5 V, TTL/RS422, 0-SET	-	0.7 W	
4.5 V 32 V, TTL/RS422, 0-SET	-	0.7 W	
4.5 V 32 V, TTL/HTL programmable	-	0.7 W	
4.5 V 32 V, TTL/HTL programmable, 0-SET	-	0.7 W	
Maximum output frequency			
TTL/RS422	300 kHz	600 kHz	820 kHz
HTL/Push Pull	300 kHz	600 kHz	820 kHz
HTL/Push Pull, 0-SET	300 kHz	600 kHz	820 kHz
	300 kHz	600 kHz	820 kHz
TTL/RS422, 0-SET			
	-	600 kHz	820 kHz
		600 kHz 200 kHz	820 kHz

<sup>1)</sup> Factory setting, output level TTL.

<sup>&</sup>lt;sup>2)</sup> Only with device variants with M23 male connector outlet in conjunction with the electrical interfaces M,U,V and W.

<sup>3)</sup> Under mechanical zero set width.

<sup>&</sup>lt;sup>4)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

 $<sup>^{\</sup>rm 5)}$  Short-circuit of another channel  $\rm U_{\rm S}$  or GND permissible for a maximum of 30 s.

 $<sup>^{\</sup>rm 6)}$  Short-circuit of another channel or GND permissible for a maximum of 30 s.

<sup>&</sup>lt;sup>7)</sup> TTL programming with  $\geq$  5.5 V: Short-circuit of another channel or GND permissible for a maximum of 30 s.

 $<sup>^{8)}</sup>$  HTL or TTL programming with< 5.5 V: Short-circuit of another channel, U $_{\rm S}$  or GND permissible for a maximum of 30 s.

<sup>9)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

	Eco	Basic	Advanced
Reverse polarity protection			
4.5 V5.5 V, TTL/RS422	-		
10 V 32 V, HTL/Push Pull	<b>✓</b>		
10 V 32 V, TTL/RS422	<b>✓</b>		
4.5 V 5.5 V, sin/cos 1.0 $\rm V_{SS}$	-		
4.5 V 32 V, HTL/Push Pull, 0-SET	-	<b>✓</b>	
4.5 V 5.5 V, TTL/RS422, 0-SET	-	<b>✓</b>	
4.5 V 32 V, TTL/RS422, 0-SET	-	<b>✓</b>	
4.5 V 32 V, TTL/HTL programmable	-	<b>✓</b>	
4.5 V 32 V, TTL/HTL programmable, 0-SET	-	<b>✓</b>	
Short-circuit protection of the outputs			
4.5 V-5.5 V, TTL/RS422	<b>✓</b> 5)		
10 V 32 V, HTL/Push Pull	<b>✓</b> 5)		
10 V 32 V, TTL/RS422	<b>✓</b> 6)		
4.5 V 32 V, HTL/Push Pull, 0-SET	-	<b>✓</b> 7)	
4.5 V 5.5 V, TTL/RS422, 0-SET	-	<b>✓</b> 7)	
4.5 V 32 V, TTL/RS422, 0-SET	-	<b>✓</b> 8)	
4.5 V 32 V, TTL/HTL programmable	-	<b>✓</b> 7) 8)	
4.5 V 5.5 V, sin/cos 1.0 $V_{\rm SS}$	-	<b>✓</b> 5)	-
4.5 V 32 V, TTL/HTL programmable, 0-SET	-	<b>✓</b> 7) 8)	
MTTFd: mean time to dangerous failure	300 years (EN ISO 13849-1) 9)		

<sup>1)</sup> Factory setting, output level TTL.

### Mechanical data

	Eco	Basic	Advanced
Shaft diameter			
Face mount flange	6 mm x 10 mm <sup>1)</sup>		
Servo flange	10 mm x 19 mm <sup>1)</sup>		
Blind hollow shaft, through hollow shaft $^{2)}$	6 mm, 8 mm, 10 mm, 12 mm,	14 mm, 15 mm, 3/8", 1/2", 5/8	1
Mass 3)			
Solid shaft	0.3 kg		
Blind hollow shaft, through hollow shaft	0.2 kg		
Shaft material	Stainless steel		
Flange material	Aluminum 4)		
Housing material	Aluminum die cast 4)		

<sup>1)</sup> Other diameter, lengths, and spread shafts on request.

<sup>2)</sup> Only with device variants with M23 male connector outlet in conjunction with the electrical interfaces M,U,V and W.

<sup>3)</sup> Under mechanical zero set width.

<sup>&</sup>lt;sup>4)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

 $<sup>^{\</sup>rm 5)}$  Short-circuit of another channel  $\rm U_S$  or GND permissible for a maximum of 30 s.

 $<sup>^{\</sup>rm 6)}$  Short-circuit of another channel or GND permissible for a maximum of 30 s.

 $<sup>^{7)}</sup>$  TTL programming with  $\geq$  5.5 V: Short-circuit of another channel or GND permissible for a maximum of 30 s.

 $<sup>^{8)}</sup>$  HTL or TTL programming with< 5.5 V: Short-circuit of another channel,  $U_S$  or GND permissible for a maximum of 30 s.

<sup>&</sup>lt;sup>9)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

 $<sup>^{\</sup>rm 2)}$  Clamping on the back of the shaft on request.

<sup>&</sup>lt;sup>3)</sup> Relates to devices with cable outlet.

<sup>4)</sup> Stainless steel on request.

<sup>&</sup>lt;sup>5)</sup> Take into account self-heating of 3.3 K per 1,000 revolutions/min when designing the operating temperature range.

	Eco	Basic	Advanced
Start up torque			
Solid shaft	0.5 Ncm (+20 °C)		
Blind hollow shaft, through hollow shaft	0.8 Ncm (+20 °C)		
Operating torque			
Solid shaft	0.3 Ncm (+20 °C)		
Blind hollow shaft, through hollow shaft	0.6 Ncm (+20 °C)		
Permissible shaft movement, axial static/dynamic			
Blind hollow shaft, through hollow shaft	± 0.5 mm, ± 0.2 mm		± 0.5 mm, ± 0.01 mm
Permissible shaft movement, radial static/dynamic			
Blind hollow shaft, through hollow shaft	± 0.3 mm, ± 0.1 mm		± 0.3 mm, ± 0.05 mm
Permissible shaft loading			
Solid shaft	80 N (radial) 40 N (axial)		
Maximum operating speed			
Solid shaft	9,000 / min <sup>5)</sup>		
Blind hollow shaft, through hollow shaft	6,000 / min <sup>5)</sup>		
Rotor moment of inertia			
Solid shaft	6.2 gcm <sup>2</sup>		
Blind hollow shaft, through hollow shaft	40 gcm <sup>2</sup>		
Bearing lifetime	3.6 x 10 <sup>10</sup> revolutions		
Max. angular acceleration	5 x 10 <sup>5</sup> rad/s <sup>2</sup>		

 $<sup>^{\</sup>mbox{\scriptsize 1)}}$  Other diameter, lengths, and spread shafts on request.

### Ambient data

	Eco	Basic	Advanced
EMC 1)	According to EN 61000-6-2 and	I EN 61000-6-3	
Enclosure rating as per IEC 60529			
On the shaft	IP 65 <sup>2)</sup>		
On the housing, male connector outlet 3)	IP 67 (IP 65 for through hollow	shaft)	
On the housing, cable outlet	IP 67 (IP 65 for through hollow shaft)		
Permissible relative humidity	90% (condensation of optical s	urfaces not permitted)	
Operating temperature range	0 °C +85 °C		
Storage temperature range	-40 °C +100 °C, without pa	ckaging	
Resistance to shocks according to EN 60068-2-27	50 g	70 g	100 g
Resistance to vibration according to EN 60068-2-6	20 g, 10 Hz 2,000 Hz	30 g, 10 Hz 2,000 Hz	

<sup>1)</sup> For interfaces 10 ... 32 V, TTL/RS422 and 10 ... 32 V, HTL/Push Pull according to EN 61000-6-2 and EN 61000-6-4, devices in class A

 $<sup>^{\</sup>rm 2)}$  Clamping on the back of the shaft on request.

<sup>&</sup>lt;sup>3)</sup> Relates to devices with cable outlet.

<sup>4)</sup> Stainless steel on request.

<sup>&</sup>lt;sup>5)</sup> Take into account self-heating of 3.3 K per 1,000 revolutions/min when designing the operating temperature range.


<sup>&</sup>lt;sup>2)</sup> IP 67 on request.

<sup>3)</sup> When mating connector is inserted.


<sup>4)</sup> When cables are fixed in place.

<sup>5)</sup> When cables can be moved.

### Viewing number of resolutions



Type code Solid shaft, programmable



<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.

The following features can be programmed:

Pulses per revolution from 1 ... 65,536 using the programming tools PGT-08-S or PGT-10-Pro

Electrical zero-pulse width 90°, 180°, 270° using the programming tools PGT-08-S or PGT-10-Pro

Mechanical zero-pulse width 1° ... 359° using the programming tool PGT-10-Pro


Output voltage levels for TTL or HTL using the programming tools PGT-08-S or PGT-10-Pro

Counting direction CW/CCW using the programming tools PGT-08-S or PGT-10-Pro

0-SET function using the programming tools PGT-08-S or PGT-10-Pro

0-SET function via PIN 7 of the M23 male connector by applying  $\rm U_s$  for at least 250 ms.


### Solid shaft, not programmable



<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.

F

### Blind hollow shaft, programmable



<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.


The following features can be programmed:

Pulses per revolution from 1 ... 65,536 using the programming tools PGT-08-S or PGT-10-Pro Electrical zero-pulse width 90°,  $180^\circ$ ,  $270^\circ$  using the programming tools PGT-08-S or PGT-10-Pro Mechanical zero-pulse width 1° ...  $359^\circ$  using the programming tool PGT-10-Pro Output voltage levels for TTL or HTL using the programming tools PGT-08-S or PGT-10-Pro Counting direction CW/CCW using the programming tools PGT-08-S or PGT-10-Pro 0-SET function using the programming tools PGT-08-S or PGT-10-Pro 0-SET function via PIN 7 of the M23 male connector by applying  $U_s$  for at least 250 ms.

F

<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.

### Through hollow shaft, programmable



<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.

The following features can be programmed:

Pulses per revolution from 1 ... 65,536 using the programming tools PGT-08-S or PGT-10-Pro

Electrical zero-pulse width 90°, 180°, 270° using the programming tools PGT-08-S or PGT-10-Pro

Mechanical zero-pulse width 1° ... 359° using the programming tool PGT-10-Pro

Output voltage levels for TTL or HTL using the programming tools PGT-08-S or PGT-10-Pro

Counting direction CW/CCW using the programming tools PGT-08-S or PGT-10-Pro

0-SET function using the programming tools PGT-08-S or PGT-10-Pro

O-SET function via PIN 7 of the M23 male connector by applying U<sub>s</sub> for at least 250 ms

<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.


### Pulses per revolution 1)


	E	B <sup>2)</sup>	<b>A</b> <sup>2)</sup>
	00100	00100	00100
	00200	00200	00200
	00250	00250	00250
	00256	00300	00300
	00314	00314	00314
	00360	00360	00360
	00500	00500	00500
	00512	00512	00512
	00720	00720	00720
	01000	01000	01000
	01024	01024	01024
	01250	01250	01250
Pulses per revolution	02000	02000	02000
	02048	02048	02048
		02500	02500
		03600	03600
		04000	04000
		04096	04096
		05000	05000
		07200	07200
		08192	08192
		10000	10000
			16384
			32768
			65536

 $<sup>^{1)}</sup>$ The electrical interface N (Sin/Cox 1.0  $\rm V_{SS}$ ) can only be ordered with 1,024 pulses per revolution.

<sup>&</sup>lt;sup>2)</sup> Additional available upon request.

Face mount flange, cable output






25°±2°

◎ Ø 0.1 C

General tolerances according to ISO 2768-mk ① Cable diameter = 5.6 mm +/- 0.2 mm bend radius = 30 mm

Face mount flange, radial cable outlet M12 and M23




M12 x 1

M23 x 1

General tolerances according to ISO 2768-mk




### Face mount flange, axial cable outlet M12 and M23



General tolerances according to ISO 2768-mk


### Servo flange, cable outlet



General tolerances according to ISO 2768-mk


① Cable diameter = 5.6 mm +/- 0.2 mm bend radius = 30 mm

### Servo flange, radial cable outlet M12 and M23




General tolerances according to ISO 2768-mk


### Servo flange, axial cable outlet M12 and M23



General tolerances according to ISO 2768-mk

### Blind hollow shaft, cable outlet






General tolerances according to ISO 2768-mk

① Cable diameter = 5.6 mm +/- 0.2 mm bend radius = 30 mm


Type Blind hollow shaft	XF7 shaft diameter	xj7 shaft diameter
DFS60x-BAxxxxxxxx	6 mm	
DFS60x-BBxxxxxxxx	8 mm	
DFS60x-BCxxxxxxxx	3/8"	
DFS60x-BDxxxxxxxxx	10 mm	
DFS60x-BExxxxxxxx	12 mm	Provided by customer
DFS60x-BFxxxxxxxx	1/2"	
DFS60x-BGxxxxxxxx	14 mm	
DFS60x-BHxxxxxxxx	15 mm	
DFS60x-BJxxxxxxxx	5/8"	



General tolerances according to ISO 2768-mk

Type Blind hollow sha	XF7 shaft diameter aft	xj7 shaft diameter
DFS60x-BAxxxxx	xxx 6 mm	
DFS60x-BBxxxxxx	xxx 8 mm	
DFS60x-BCxxxxxx	xxx 3/8"	
DFS60x-BDxxxxxx	xxx 10 mm	
DFS60x-BExxxxx	xxx 12 mm	Provided by customer
DFS60x-BFxxxxxx	xxx 1/2"	
DFS60x-BGxxxxxx	xxx 14 mm	
DFS60x-BHxxxxxx	xxx 15 mm	
DFS60x-BJxxxxxx	xxx 5/8"	


### Blind hollow shaft, axial cable outlet M12 and M23




General tolerances according to ISO 2768-mk

Type Blind hollow shaft	XF7 shaft diameter	xj7 shaft diameter
DFS60x-BAxxxxxxxx	6 mm	
DFS60x-BBxxxxxxxxx	8 mm	
DFS60x-BCxxxxxxxx	3/8"	
DFS60x-BDxxxxxxxxx	10 mm	
DFS60x-BExxxxxxxx	12 mm	Provided by customer
DFS60x-BFxxxxxxxx	1/2"	
DFS60x-BGxxxxxxxx	14 mm	
DFS60x-BHxxxxxxxxx	15 mm	
DFS60x-BJxxxxxxxx	5/8"	

## Through hollow shaft, cable outlet






F

General tolerances according to ISO 2768-mk

1 Cable diameter = 5.6 mm +/- 0.2 mm bend radius = 30 mm

Type Through hollow shaft	XF7 shaft diameter	xj7 shaft diameter
DFS60x-TAxxxxxxxx	6 mm	
DFS60x-TBxxxxxxxx	8 mm	
DFS60x-TCxxxxxxxx	3/8"	
DFS60x-TDxxxxxxxxx	10 mm	
DFS60x-TExxxxxxxx	12 mm	Provided by customer
DFS60x-TFxxxxxxxxx	1/2"	
DFS60x-TGxxxxxxxx	14 mm	
DFS60x-THxxxxxxxx	15 mm	
DFS60x-TJxxxxxxxxx	5/8"	

## Through hollow shaft, radial cable outlet M12 and M23




General tolerances according to ISO 2768-mk

① Cable diameter = 5.6 mm +/-0.2 mm bend radius = 30 mm


Type Through hollow shaft	XF7 shaft diameter	xj7 shaft diameter
DFS60x-TAxxxxxxxx	6 mm	
DFS60x-TBxxxxxxxx	8 mm	
DFS60x-TCxxxxxxxx	3/8"	
DFS60x-TDxxxxxxxx	10 mm	
DFS60x-TExxxxxxxx	12 mm	Provided by customer
DFS60x-TFxxxxxxxxx	1/2"	
DFS60x-TGxxxxxxxx	14 mm	
DFS60x-THxxxxxxxxx	15 mm	
DFS60x-TJxxxxxxxxx	5/8"	

## **Proposed fitting**

Mounting suggestion for small servo clamp (part number 2029166)



Mounting suggestion for half-shell servo clamp (part number 2029165)




All dimensions in mm (inch)


## PIN assignment

#### Cable, 8-wire

View of M12 male device connector on encoder



View of M23 male device connector on encoder




PIN, 8-pin, M12 male connector	PIN, 12-pin, M23 male connector	Color of the wires for encoders with cable outlet	TTL/HTL signal	Sin/cos 1.0 V <sub>SS</sub>	Explanation
1	6	Brown	_A	COS-	Signal wire
2	5	White	A	COS+	Signal wire
3	1	Black	_B	SIN-	Signal wire
4	8	Pink	В	SIN+	Signal wire
5	4	Yellow	_z	_z	Signal wire
6	3	Violet	Z	Z	Signal wire
7	10	Blue	GND	GND	Ground connection of the encoder
8	12	Red	+U <sub>s</sub>	+U <sub>s</sub>	Supply voltage (volt-free to housing)
-	9	-	n.c.	n.c.	Not assigned
-	2	-	n.c.	n.c.	Not assigned
-	11	-	n.c.	n.c.	Not assigned
-	7 1)	-	0-SET 1)	n.c.	Set zero pulse 1)
Screen	Screen	Screen	Screen	Screen	Screen connected to housing on encoder side.  Connected to ground on control side.

<sup>&</sup>lt;sup>1)</sup> For electrical interfaces only: M, U, V, W with 0-SET function on PIN 7 on M23 male connector. The 0-SET input is used to set the zero pulse on the current shaft position. If the 0-SET input is connected to U<sub>S</sub> for longer than 250 ms after it had previously been unassigned for at least 1,000 ms or had been connected to the GND, the current position of the shaft is assigned to the zero pulse signal "Z".

#### **Interfaces**


Signal outputs for electrical interfaces TTL and HTL



Supply voltage	Output
4.5 5.5 V	TTL
10 32 V	TTL
10 32 V	HTL

 $\mbox{CW}$  with view on the encoder shaft in direction "A", compare dimensional drawing.


Electrical zero pulse width  $90^{\circ}$ ,  $180^{\circ}$  or  $270^{\circ}$ , programmable Width of the zero pulse in relation to a pulse period.



CW with view on the encoder shaft in direction "A," compare dimensional drawing.

Supply voltage	Output
4.5 32 V	HTL/TTL programmable


Mechanical zero pulse width 1° to 359°, programmable Width of the zero pulse in relation to a mechanical revolution of the shaft.



Supply voltage	Output
4.5 5.5 V	Sin/cos 1.0 V <sub>SS</sub>

Signals **before** difference at 120  $\Omega$  load and U<sub>S</sub> = 5 V

Signal diagram for clockwise shaft rotation, looking in direction "A" (shaft)




Interface signals Sin+, SIN-, COS+, COS- Signals before difference at 120  $\Omega$  load Signal offset Differential analog 0.5  $V_{SS} \pm 20\%$  2.5  $V \pm 10\%$ 

Interface signals Z, $\overline{Z}$	Signals before difference at 120 $\Omega$ load
Digital, differential	Low: 1.75 V ± 15%; High: 2.9 V ± 15%

Signals after difference at 120  $\Omega$  load and U<sub>S</sub> = 5 V

Signal diagram for clockwise shaft rotation, looking in direction "A" (shaft)



## Recommended accessories

## Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
T.	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

## Flanges

## Flange plate

Figure	Brief description	Туре	Part no.
	Standard two-sided stator coupling, with screw hole circle diameter 63 mm, slot width 3.2 mm, 10.4 mm high	BEF-DS00XFX	2056812
	One-sided stator coupling, slot, slot radius 33 mm – 48.5 mm, slot width 5.1 mm	BEF-DS01DFS/VFS	2047428
	One-sided stator coupling, slot, slot radius 32.25 mm – 141.75 mm, slot width 5.1 mm	BEF-DS02DFS/VFS	2047430
.10	One-sided stator coupling, slot, slot radius 33 mm – 211.9 mm, slot width 5.1 mm	BEF-DS03DFS/VFS	2047431
	Two-sided stator coupling, with screw hole circle diameter 72 mm, slot width 3.2 mm, 16.5 mm high	BEF-DS05XFX	2057423
	Two-sided stator coupling, with screw hole circle diameter 72 mm, slot width 3.2 mm, 10.4 mm high	BEF-DS07XFX	2059368
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-063REC	2034225
0)	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161

## Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
<b>(a)</b>	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 500 mm	BEF-MR006050R	2055225
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm	BEF-MR010020R	2055224
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 500 mm	BEF-MR010050R	2055227
	O-ring for measuring wheels (circumference 200 mm)	BEF-0R-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-OR-083-050	2064076
	O-ring for measuring wheels (circumference 500 mm)	BEF-OR-145-050	2064074

## Modular measuring wheel system

Brief description	Туре	Part no.
Measuring wheel system, desired mounting position: left, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-1	2071958
Measuring wheel system, desired mounting position: right, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-2	2071957

## Mounting bell

Figure	Brief description	Туре	Part no.
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

## Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166



#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Clamping ring for metal hollow shaft, metal	BEF-KR-M	2064709
97	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912,1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872

## Shaft adaptation

## Collets and clamping rings

Figure	Brief description	Туре	Part no.
	PEEK conductor insulation (shaft diameter 8 mm, outer diameter 10 mm)	PEEK CONDUCTOR INSULATION	2065642
	PEEK conductor insulation (shaft diameter 10 mm, outer diameter 12 mm)	PEEK CONDUCTOR INSULATION	2064571
	PEEK conductor insulation (shaft diameter 11 mm, outer diameter 12.7 mm)	PEEK CONDUCTOR INSULATION	2077319
	PEEK conductor insulation (shaft diameter 12 mm, outer diameter 14 mm)	PEEK CONDUCTOR INSULATION	2064573
	PEEK conductor insulation (shaft diameter 1/2"(12.7 mm), outer diameter 15 mm)	PEEK CONDUCTOR INSULATION	2064572
	Metal collet for hollow shaft, shaft diameter 8 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-008-M	2076219
	Metal collet for hollow shaft, shaft diameter $3/8$ " (9.525 mm), outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-38Z-M	2076224
760	Metal collet for hollow shaft, shaft diameter 10 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-010-M	2076220
	Metal collet for hollow shaft, shaft diameter 12 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-012-M	2076221
	Metal collet for hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-12Z-M	2076225
	Metal collet for hollow shaft, shaft diameter 14 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-014-M	2076222
	Metal collet for hollow shaft, shaft diameter 15 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-015-M	2076223
	Plastic isolated collet for hollow shaft, shaft diameter 6 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-006-P	2076228
	Plastic isolated collet for hollow shaft, shaft diameter 8 mm, outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-008-P	2076229
	Plastic isolated collet for hollow shaft, shaft diameter $3/8$ " (9.525 mm), outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-38Z-P	2076226
	Plastic isolated collet for hollow shaft, shaft diameter 10 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-010-P	2076230
	Plastic isolated collet for hollow shaft, shaft diameter 12 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-012-P	2076231
	Plastic isolated collet for hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-12Z-P	2076227
	Plastic isolated collet for hollow shaft, shaft diameter 14 mm, outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-014-P	2076232
	Plastic isolated collet for hollow shaft, shaft diameter 15 mm, outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-015-P	2076233

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
Nan-	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $+/-$ 4°; max. speed 10,000 rpm, $-$ 30 °C to $+$ 120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial +/- 0.25 mm, axial +/- 0.4 mm, angular +/- 4°; max. revolutions 10,000 rpm, -30 ° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum	KUP-1012-B	5312984
	clamping hubs  Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-$ 10 °C to $+$ 80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
0	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-10$ °C to +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter $8\ mm\ /\ 10\ mm$ , maximum shaft offset: radial $\pm\ 0.3\ mm$ , axial $\pm\ 0.2\ mm$ , angular $\pm\ 3^\circ$ ; torsion spring rigidity $38\ Nm/wheel$ ; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, –10 °C to +80 °C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^{\circ}$ to $+80^{\circ}$ Celsius, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
<b>(</b>	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702

## Connectivity

## Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		0.5 m	DOL-0J08-G0M5AA3	2046873
_	Head A: female connector, JST, 8-pin, straight	1.5 m	DOL-0J08-G1M5AA3	2046874
	Head B: cable  Cable: incremental, suitable for drag chain, PUR, halogen-free, shielded,	3 m	DOL-0J08-G03MAA3	2046875
	4 x 2 x 0.15 mm², Ø 5.6 mm	5 m	DOL-0J08-G05MAA3	2046876
		10 m	DOL-0J08-G10MAA3	2046877
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight Head B: cable	5 m	DOL-1208-G05MAC1	6032867
-	Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869
		2 m	DOL-2312-G02MLA3	2030682
		7 m	DOL-2312-G07MLA3	2030685
_	Head A: female connector, M23, 12-pin, straight	10 m	DOL-2312-G10MLA3	2030688
	Head B: cable  Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup>	15 m	DOL-2312-G15MLA3	2030692
•	+ 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
		1.5 m	DOL-2312-G1M5MA3	2029212
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA3	2029213
-	Head B: cable	5 m	DOL-2312-G05MMA3	2029214
	Cable: incremental, suitable for drag chain, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm <sup>1)</sup>	10 m	DOL-2312-G10MMA3	2029215
	2.70.5 11111 - 1.70.14 11111 , 97.5 11111	20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217
		2 m	DOL-2312-G02MLD1	2062202
		7 m	DOL-2312-G07MLD1	2062203
_	Head A: female connector, M23, 12-pin, straight	10 m	DOL-2312-G10MLD1	2062204
	Head B: cable  Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup>	15 m	DOL-2312-G15MLD1	2062205
	+ 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>2)</sup>	20 m	DOL-2312-G20MLD1	2062206
		25 m	DOL-2312-G25MLD1	2062207
		30 m	DOL-2312-G30MLD1	2062208
		1.5 m	DOL-2312-G1M5MD1	2062240
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMD1	2062243
99	Head B: cable	5 m	DOL-2312-G05MMD1	2062244
	Cable: incremental, suitable for drag chain, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm <sup>2)</sup>	10 m	DOL-2312-G10MMD1	2062245
	- ZAGIO IIIII - ZAGIZTIIIII , D LO IIIII	20 m	DOL-2312-G20MMD1	2062246
		30 m	DOL-2312-G30MMD1	2062247

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Warning! Only in combination with electrical interfaces A, C, E and P.

 $<sup>^{\</sup>rm 2)}$  Warning! Only in combination with electrical interfaces U, V, W and M.

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature: -40 °C +85 °C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-G	6027538
(F)-()	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057

## Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , $\emptyset$ 5.6 mm	By the meter	LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm		LTG-2411-MW	6027530
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2612-MW	6028516

## Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	STE-1208-GA01	6044892
The same of the sa	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B:  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	STE-2312-G01	2077273

## Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, JST, 8-pin, straight	0.35 m	STL-2312-GM35AA3	2061621
The second	Head B: male connector, M23, 12-pin, straight Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm <sup>2</sup> ,	1 m	STL-2312-G01MAA3	2061622
175.39	Ø 5.6 mm	2 m	STL-2312-G02MAA3	2061504
	Head A: female connector, connector system, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: PVC, shielded, can be used for encoders with cable outlet in conjunction with PGT-10-Pro	0.5 m	DSL-0D08-G0M5AC3	2061739
	Head A: female connector, M12, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, 4 x 2 x 0.08 mm <sup>2</sup>	0.5 m	DSL-2D08-G0M5AC3	2046579
	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, 4 x 2 x 0.08 mm <sup>2</sup>	0.5 m	DSL-3D08-G0M5AC3	2046580

## Other accessories

## Programming and configuration tools

Figure	Brief description	Туре	Part no.
	Programming unit USB, for programmable SICK Encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoder.	PGT-08-S	1036616
A III III Y	Programming unit display for programmable SICK DFS60, VFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254

<sup>→</sup> For additional accessories, please see page K-668 onwards

# ENCODER WITH A LARGE HOLLOW SHAFT FOR HARSH AMBIENT CONDITIONS





## **Product description**

The high-resolution DGS34/DGS35 hollow shaft incremental encoder family is a reliable solution for extremely demanding encoder applications. With a large

hollow shaft diameter of up to 1 to 1/8" or 30 mm, they are very well suited for direct assembly on the motor shaft

#### At a glance

- Incremental encoder with 3.5" diameter
- · Electrical interface
- 5 V TTL / RS422
- 8 ... 24 V TTL / RS422
- 8 ... 24 V, HTL/Push Pull

- 8 ... 24 V, Open Collector
- Blind hollow shaft for shaft diameters of 30 mm; 1", ½",5/8", ¾", 7/8"
- Cable outlet with length of 1 m, 1.5 m, 3 m, 5 m, 10 m
- Number of lines: 120 ... 16,384

#### Your benefits

- The high output frequency means that no mechanical reduction is required
- Hollow shaft design requires no couplings or mounting brackets
- Large selection of stator couplings available for almost every AC asynchronous motor

( (

#### Additional information

Fields of application F-193
Detailed technical dataF-193
Type code
Ordering informationF-196
Dimensional drawingsF-197
PIN assignmentF-199
Recommended accessories F-199

→ www.mysick.com/en/DGS35

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

- Crane winches
- · Stages and theater
- Steel industry

- Elevators
- Packaging industry

## Detailed technical data

## Performance

Pulses (Z) per revolution 1), 2)	120 16,384 <sup>2)</sup>
Measurement step	90° electrical/pulses per revolution
Reference signal	
Number	1
Location	$90^\circ$ electrical, logically gated with A and B or $180^\circ$ electrical, logically gated with B-(see electrical interface)
Error limits	45/Z°
Measurement step deviation	45/Z°

 $<sup>^{\</sup>mbox{\tiny 1)}}$  3,000 rpm (2,200 rpm for 8,192 and 16,384 pulses per revolution).

#### Mechanical data

Shaft diameter	
DGS34 blind hollow shaft DGS35 through hollow shaft	
Shaft material	Brass
Flange material	Aluminum
Housing material	Aluminum
Mass 1)	1.1 kg
Start up torque at 20 °C	9.0 Ncm
Operating torque at 20 °C	7.0 Ncm
Permissible shaft movement of the drive element, static/dynamic	0.5 mm / 0.1 mm radial 0.5 mm / 0.5 mm axial
Max. angular acceleration	$1 \times 10^5  \text{rad/s}^2$
Max. operating speed 2)	3,000 rpm
Rotor moment of inertia	490 gcm <sup>2</sup>
Bearing lifetime	4.5 x 10° revolutions

<sup>1)</sup> Relates to devices with cable outlet.

## Electrical data

Electrical interfaces	4.5 5.5 V, TTL/RS422, 3487, zero pulse width, 180° 8 24 V, TTL/RS422, 3487, zero pulse width, 180° 8 24 V, HTL/Push Pull, 7272, zero pulse width, 180° 8 24 V, Open Collector, 7273, zero pulse width, 180° 4.5 5.5 V, TTL/RS422, 3487, zero pulse width, 90° (only 10,000 and 16,384 pulses possible) 8 24 V, TTL/RS422, 3487, zero pulse width, 90° (only 10,000 and 16,384 pulses possible) 8 24 V, HTL/Push Pull, 7272, zero pulse width, 90° (only 10,000 and 16,384 pulses possible) 8 24 V, Open Collector, 7273, zero pulse width, 90° (only 10,000 and 16,384 pulses possible)
Connection type	Cable, 11-wire, radial, 1.0 m Cable, 11-wire, radial, 1.5 m Cable, 11-wire, radial, 3.0 m Cable, 11-wire, radial, 5 m Cable, 11-wire, radial, 10 m (not possible with Open Collector outputs) MS male connector, 10-pin, radial

 $<sup>^{\</sup>rm 2)}$  For a detailed list of pulses per revolution, see table "Pulses per revolution"

 $<sup>^{2)}</sup>$  3,000 rpm (2,200 rpm for 8,192 and 16,384 pulses per revolution).

Maximum output frequency	≤300 kHz (1 to 8,192 pulses); ≤600 kHz (>8,192 pulses)
Load current	
4.5 V5.5 V, TTL/RS422	40 mA
8 24 V, TTL/RS422; 8 24 V, HTL/Push Pull	40 mA
8 24 V, Open Collector	20 mA
Operating current without load	
8 24 V	100 mA
4.5 5.5 V	120 mA
Reverse polarity protection	Yes
Short-circuit protection of the outputs	
4.5 V5.5 V, TTL/RS422, 3487	No
8 V24 V, TTL/RS422, 3487	No
8 24 V, HTL/Push Pull, 7272	Yes
8 24 V, Open Collector, 7273	Yes
4.5 V5.5 V, TTL/RS422, 3487	No
8 V24 V, TTL/RS422, 3487	No
8 24 V, HTL/Push Pull, 7272	Yes
8 24 V, Open Collector, 7273	Yes

## Ambient data

EMC	EN 61000-6-2, 61000-6-3
Enclosure rating	
On the housing, male connector outlet $^{\mbox{\tiny 1}\mbox{\tiny )}}$	IP 66
On the housing, cable outlet	IP 66
Permissible relative humidity	95%, condensation of optical surfaces not permitted
Operating temperature range	-20+70 °C
Storage temperature range	-30 +85 °C
Resistance	
To shocks	50 g/11 ms
To vibrations	20 g/ 5 2,000 Hz

<sup>1)</sup> When mating connector is inserted.

## Type code

## Mechanical design Blind hollow shaft 1) 5 Through hollow shaft 1) **Electrical interface 1** 4.5 ... 5.5 V, TTL/RS422, 3487 <sup>2)</sup>, reference signal 180 **2** 8 ... 24 V, 5 V, 3487 <sup>2)</sup>, reference signal 90 <sup>3)</sup> **3** 8 ... 24 V, 5 V, 3487 <sup>2)</sup>, reference signal 180 **4** 8 ... 24 V, 8/24 V, 7272 <sup>2)</sup>, reference signal 90 <sup>3)</sup> **5** 8 ... 24 V, 8/24 V, 7272 <sup>2)</sup>, reference signal 180 **8** 8 ... 24 V, Open Collector, 7273 <sup>2)</sup>, reference signal 90 <sup>3)</sup> **9** 8 ... 24 V, Open Collector, 7272 <sup>2)</sup>, reference signal 180 5 V, 5 V, 3487 <sup>2)</sup>, reference signal 90 <sup>3)</sup> Mechanical design H | T1 stator coupling, shaft diameter Ø 1" Stator coupling via customer's own locating pin, shaft diameter Ø 1" T1 stator coupling, shaft diameter Ø 30 mm Stator coupling via customer's own locating pin, shaft diameter Ø 30 mm **Connection type** Cable, 11-wire, radial, 1 m K Cable, 11-wire, radial, 1.5 m Cable, 11-wire, radial, 3 m M Cable, 11-wire, radial, 5 m N Cable, 11-wire, radial, 10 m (not in conjunction with the electrical interfaces 8 and 9) 4 MS male connector, 10-pin, radial **Pulses** Always 5 characters in clear text

GS

#### Pulses per revolution

Pulses per revolution	120	3,600
	360	4,096
	600	5,000
	1,024	8,192
	2000	10,000
	2,048	16,384
	2,500	

 $<sup>^{1)}</sup>$  Order collets for 7/8", 24 mm, 25 mm, 18 mm, 20 mm and 22 mm as an additional accessory, see "Recommended accessories" on page F-199.

<sup>&</sup>lt;sup>2)</sup> IC module.

 $<sup>^{3)}</sup>$  10,000 and 16,384 pulses per revolution only available with 90  $^{\circ}$  reference signal.

## Ordering information

## DGS34 blind hollow shaft


Electrical interface	Mechanical design	Connection type	Туре	Part no.
4.5 5.5 V, TTL/RS422, 3487, reference signal 180	Stator coupling via customer's own locating pin, shaft diameter Ø 30 mm	MS male connector, 10-pin, radial	DGS34-1L402048	7101744
8 24 V, 8/24 V, 7272, refer-	Stator coupling via customer's own locating pin, shaft diameter Ø 1"	MS male connector, 10-pin, radial	DGS34-5J404096	7102201
ence signal 180	Stator coupling via customer's own locating pin, shaft diameter Ø 30 mm	Cable, 12-wire, radial, 1.5 m	DGS34-5LK02048	7101764

## DGS35 through hollow shaft

Electrical interface	Mechanical design	Connection type	Туре	Part no.
	Stator coupling via customer's own locating pin, shaft diameter Ø 1"	Cable, 12-wire, radial, 3 m	DGS35-1JL01024	7134504
		MS male connector, 10-pin, radial	DGS35-1K402048	7130548
	T1 stator coupling, shaft diameter Ø 30 mm	Cable, 12-wire, radial, 1.5 m	DGS35-1KK01024	1049552
4.5 5.5 V, TTL/RS422, 3487,	<b>9</b> 30 mm	Cable, 12-wire, radial, 1.5 III	DGS35-1KK02500	1055330
reference signal 180		MS male connector, 10-pin, radial	DGS35-1L401024	7101683
	Stator coupling via customer's	ivis male connector, 10-pin, radial	DGS35-1L402048	7101684
	own locating pin, shaft diameter		DGS35-1LK01024	7101698
	Ø 30 mm	Cable, 12-wire, radial, 1.5 m	DGS35-1LK02048	7101699
			DGS35-1LK08192	7101701
	Stator coupling via customer's own locating pin, shaft diameter Ø 1"	MS male connector, 10-pin, radial	DGS35-3J401024	7126765
	T1 stator coupling, shaft diameter Ø 30 mm	MS male connector, 10-pin, radial	DGS35-3K401024	1058110
0 04 V 5 V 2407			DGS35-3K402048	1060264
8 24 V, 5 V, 3487, reference signal 180		Cable, 12-wire, radial, 1.5 m	DGS35-3KK01024	1057039
			DGS35-3KK02048	1062810
	Stator coupling via customer's own locating pin, shaft diameter	MS male connector, 10-pin, radial	DGS35-3L402048	1062795
		Cable, 12-wire, radial, 1.5 m	DGS35-3LK02048	1062354
	Ø 30 mm	Cable, 12-wire, radial, 3 m	DGS35-3LL01024	1055112
	T1 stator coupling, shaft diameter Ø 1"	Cable, 12-wire, radial, 1.5 m	DGS35-5HK00120	7130703
			DGS35-5K401024	7134312
	<b>-4</b>	MS male connector, 10-pin, radial	DGS35-5K402048	1062811
8 24 V, 8/24 V, 7272, reference signal 180	T1 stator coupling, shaft diameter Ø 30 mm	ivis male connector, 10-pin, radial	DGS35-5K402500	7134638
			DGS35-5K405000	7130624
		Cable, 12-wire, radial, 1.5 m	DGS35-5KK01024	1058301
	Stator coupling via customer's own locating pin, shaft diameter Ø 30 mm	MS male connector, 10-pin, radial	DGS35-5L401024	7101688
		Cable 12 wire radial 1.5 m	DGS35-5LK04096	7101705
		Cable, 12-wire, radial, 1.5 m	DGS35-5LK08192	7101706

## Dimensional drawings (dimensions in mm)


## Through hollow shaft




Hollow shaft	Shaft diameter	Min. shaft insertion depth
1/2"	12.67 mm / 12.7 mm	25.4 mm
5/8"	15.85 mm / 15.88 mm	25.4 mm
3/4"	19.02 mm / 19.05 mm	25.4 mm
7/8"	22.2 mm / 22.23 mm	25.4 mm
1.0"	25.37 mm / 25.4 mm	25.4 mm
1 1/8"	28.55 mm / 28.58 mm	45.47 mm
M30	29.96 mm / 29.98 mm	46 mm

## Spring plate stator coupling

T1 (slotted hole for 3/8" bolt on 2.5 to 3.875 radius to fit AC motor fan cover)



## Signal outputs



## Electrical interfaces

C.,	nnh	wal	tage	
Эu	ppiy	VUI	lage	

4.75 ... 5.25 V

8.0 ... 24.0 V

8.0 ... 24.0 V

F

## PIN assignment

## MS3102, 10-pin



PIN, 10-pin	Wire colors	Explanation
Α	White	A
В	Pink	В
C	Violet	M
н	Brown	Ā
1	Black	B
J	Yellow	$\overline{M}$
D	Red	+V <sub>S</sub>
F	Blue	GND
G	N/A	Housing grounding
N/A	N/A	Screen

## Recommended accessories

## Mounting systems

Shaft adaptation

Collets and clamping rings

Brief description	Shaft diam- eter	Туре	Part no.
For T1 stator couplings with 1" hollow shaft diameters (mechanical interfaces H, J)	7/8"	SPZ-7E8-DD35-AD	7102158
For 30 mm stator couplings with 30 mm hollow shaft diameters (mechanical interfaces K, I) $$	24 mm	SPZ-024-MD35-AD	7130587
	25 mm	SPZ-025-MD35-AD	7130588
	18 mm	SPZ-018-DD35-AD	7130585
For T1 stator couplings with 1" hollow shaft diameters (mechanical interfaces H, J)	20 mm	SPZ-020-DD35-AD	7130529
	22 mm	SPZ-022-DD35-AD	7130586

## Connectivity

Plug connectors and cables

Brief description	Length of cable	Туре	Part no.
Female cable connector, MS 3105, 10-pin, straight	-	DOS-MS10-G	7102129
	1.5 m	DOL-MS10-G1M5MA2	7102130
	3.0 m	DOL-MS10-G03MMA2	7102131
Cable, MS 3105, 10-pin, straight, 11-wire, 4 x 2 x 0.25 + 2 x 0.5 + 1 x 0.14 mm²,	5.0 m	DOL-MS10-G05MMA2	7102132
with shielding, cable diameter 7.5 mm	10.0 m	DOL-MS10-G10MMA2	7102133
	20.0 m	DOL-MS10-G20MMA2	7102134
	30.0 m	DOL-MS10-G30MMA2	7102135
Data cable by the meter 4 x 2 x 0.15 mm $^{\!2}$ with shielding, Ø 5.6 mm	-	LTG-2308-MWENC	6027529
Data cable by the meter 4 x 2 x 0.25 mm $^2$ + 2 x 0.5 mm $^2$ + 1 x 0.14 mm $^2$ with shielding, Ø 7.5 mm		LTG-2411-MW	6027530
Data cable by the meter 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm² with shielding, suitable for drag chain, Ø 7.8 mm	-	LTG-2512-MW	6027531

<sup>→</sup> For additional accessories, please see page K-668 onwards

F

## RUGGED, HIGH-PERFORMANCE MEASURING WHEEL INCREMENTAL ENCODER





### **Product description**

The DKV60 compact measuring wheel encoder is a low-cost solution for determining position and speed directly on conveyor belts or rollers. The DKV60 consists of an incremental encoder, a mea-

suring roller, an installation plate, and a cable guide and it is pre-assembled upon delivery. Two different measuring wheel surfaces ensure the encoder can adapt to the surface to be measured.

#### At a glance

- Complete, pre-assembled measuring system
- Measuring wheel with knurl or O-ring for adaptation to the measuring surface
- Mounting bracket made from anti-corrosive spring steel
- High resolution up to 0.1 mm (1 ... 2,000 pulses/revolution)
- Electrical interfaces: Open Collector NPN, TTL/RS-422 or HTL/Push Pull
- Connection via cable outlet, for radial or axial use with open ends or fitted with an M12 connector

#### Your benefits

- Complete system with universal mounting clamps and integrated cable guidance enables simple and quick mounting
- Spring steel mounting clamps allow high level of measurement accuracy when deflecting the measuring wheel in X and Y directions
- Low-cost encoder with outstanding quality
- Withstands harsh environments due to a high IP protection class, a non-corrosive mounting bracket and a rugged housing
- Compact dimensions enable simple installation even where space is cramped



#### Additional information

Fields of application F-203
Detailed technical dataF-203
Type code
Ordering informationF-204
Dimensional drawingsF-205
PIN assignmentF-206
Signal outputs F-206
Proposed fittingF-207
Recommended accessories F-208

→ www.mysick.com/en/DKV60\_measuring\_wheel\_encoder

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

 Measurement of position and speed directly on conveyor belts in wood processing machines, steel and metal processing machines, storage and conveyors, sorting systems and conveyor belts, textile machines, printing and paper machines

#### Detailed technical data

#### Performance

Pulses per revolution	1 2,000 <sup>1)</sup>
Error limits knurled surface	±0.5 mm
Error limits O-ring surface	± 4 mm
Initialization time	40 s
Resolution	0.1 mm 200 mm
Smallest measuring step	0.025 mm 50 mm

<sup>1)</sup> Pulses per 200 mm

#### Mechanical data

Mechanical design	Measuring drum, knurled surface Measuring drum, 0 ring surface
Mass	0.42 kg
Maximum operating speed	1,500 rpm
Bearing lifetime	2 x 10^9 revolutions

## Electrical data

Electrical interface	4.5 5.5 V, TTL/RS 422, 6 channel 10 30 V, HTL/Push Pull, 6 channel
Connection type	Cable, 1.5 m Cable with male connector, M12, 8-pin, 1.5 m
Operating current without load	40 mA
Supply voltage	4.5 V 5.5 V 10 V 30 V
Max. load current	≤ 30
Reference signal, number	1
Reference signal, position	90° electric, logically gated with A and B
MTTFd: mean time to dangerous failure	600 years (EN ISO 13849-1) <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

#### Ambient data

EMC	EN 61000-6-3, EN 61000-6-2
Enclosure rating (IEC 60529)	IP 65
Air humidity	90% 1)
Operating temperature range	-10 °C +60 °C
Storage temperature range	-40 °C +70 °C, without packaging
Resistance to shocks	50 g/ 7 ms (EN 60068-2-27)
Resistance to vibrations	20 g / 10 Hz 2,000 Hz (EN 60068-2-6)

<sup>1)</sup> Condensation of optical surfaces not permitted.

## Ordering information

## Measuring drum, knurled surface

Electrical interface	Connection type	Range of pulses per revolution	Туре	Part no.
	Cable, 1.5 m	3 <sup>1)</sup>	DKV60-E1K00003	1035767
HTL/Push Pull	O-bl- M40 O-i- 4.5	200 1)	DKV60-E1P00200	1036071
	Cable, M12, 8-pin, 1.5 m	<b>1,000</b> <sup>1)</sup>	DKV60-E1P01000	1050657
TTL /DC 400	Cable, 1.5 m	20 1)	DKV60-A1K00020	1035039
TTL/RS422	Cable, M12, 8-pin, 1.5 m	200 1)	DKV60-A1P00200	1035745

<sup>1)</sup> Pulses per 200 mm

## Measuring drum, O-ring surface

Electrical interface	Connection type	Range of pulses per revolution	Туре	Part no.
LITE /Durah Dull	Cable, 1.5 m	200 1)	DKV60-E2K00200	1035052
HTL/Push Pull	Cable, M12, 8-pin, 1.5 m	200 1)	DKV60-E2P00200	1037803
TTL/RS422	Cable, 1.5 m	200 1)	DKV60-A2K00200	1035044
	Cable, M12, 8-pin, 1.5 m	2,000 1)	DKV60-A2P02000	1036587


<sup>1)</sup> Pulses per 200 mm




 $<sup>^{1)}</sup>$  The universal cable outlet is positioned so that it is possible to lay it without bends in a radial and axial direction.


## Dimensional drawings (dimensions in mm)


## Measuring drum, knurled surface






## Measuring drum, O ring surface





## PIN assignment


View of male connector, device side



PIN, 8-pin, M12 male connector	Wire colors	TTL/HTL signal	Explanation
1	Brown	Ā	Signal wire
2	White	A	Signal wire
3	Black	B	Signal wire
4	Pink	В	Signal wire
5	Yellow	Z	Signal wire
6	Violet	Z	Signal wire
7	Blue	GND	Ground connection of the encoder
8	Red	+U <sub>S</sub>	Supply voltage, volt-free to housing
Screen	Screen	Screen	Screen connected to housing on encoder side.


## Signal outputs

F




## Proposed fitting

## Preload spring arm



#### Maximum deflection





## Recommended accessories

## Mounting systems

Other mounting accessories

Measuring wheels and measuring wheel systems

Brief description	Туре	Part no.
O-ring set for DKV60 encoder	O-RING SET DKV60	6032709

## Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
70	Head A: female connector, M12, 8-pin, straight Head B: cable Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm², Ø 7.0 mm	2 m	DOL-1208-G02MAC1	6032866
		5 m	DOL-1208-G05MAC1	6032867
		10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869

## Female connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^{\circ}$ C +85 $^{\circ}$ C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057

## Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15$ mm², Ø 5.6 mm		LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm		LTG-2411-MW	6027530
_	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516

## Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: Operating temperature: –20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40  ^{\circ}\text{C} \dots +125  ^{\circ}\text{C}$	STE-2312-G01	2077273

<sup>→</sup> For additional accessories, please see page K-668 onwards

## HIGH-RESOLUTION, PROGRAMMABLE MEASURING WHEEL INCREMENTAL ENCODER





### **Product description**

The DFV60 high-resolution measuring wheel encoder is an extremely rugged solution for determining position and speed directly on the conveyor belt, even in applications where the measuring surface is subject to high levels of vibrations. The DFV60 consists of an

incremental encoder with a mounting arm and two measuring wheels. The spring arm is available as an accessory. Extensive programmability of output signal, zero pulse and line numbers from 1 to 65,536 enable customer-specific adaptations.

#### At a glance

- · Rotating spring arm for universal use
- 300 mm wheel circumference with 0 ring made from NBR70
- Mounting arm and measuring wheels made from aluminum
- Programmable output voltage, zero pulse position, zero pulse width and number of pulses
- Connection: radial M12 connector outlet or radial/axial cable outlet
- Electrical interfaces: 5 V & 24 V TTL/ RS-422, 24 V HTL/Push Pull
- · Remote zero set possible

#### Your benefits

- Universal-use spring arm ensures fast and simple mounting
- The high level of spring tension enables use in harsh ambient conditions
- Reduction of storage costs and downtimes due to programmability
- Option to insert cable outlet in radial or axial direction enables customer-specific cable solutions
- Excellent concentricity, even at high speeds
- Long-term and reliable operation thanks to a high enclosure rating, temperature resistance and bearing lifetime
- The ability to program using the PGT-08 programming software and the PGT-10-Pro display programming device enables fast and flexible adaptation of the encoder to customer requirements
- Programmable zero pulse position simplifies installation

## $\epsilon$

## Additional information

Fields of application F-211
Detailed technical data F-211
Type code
Ordering informationF-212
Dimensional drawings F-213
PIN assignmentF-214
Signal outputs
Zero pulse width
Recommended accessories F-216

→ www.mysick.com/en/DFV60\_measuring\_wheel\_encoder

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

 Measurement of position and speed directly on conveyor belts in wood processing machines, steel and metal processing machines, storage and conveyors, sorting systems and conveyor belts, textile machines, printing and paper machines

#### Detailed technical data

#### Performance

Pulses per revolution	1 65,536, programmable
Error limits 0-ring surface	± 0.03 mm
Measuring step deviation at non-binary number of lines	
Pulses 1 99	± 0.04°
Pulses 100 10,000	± 0.008°
Pulses > 10,000	± 0.002°
Measuring step deviation at binary number of lines	
Pulses 1 64	± 0.008°
Pulses 128 8,192	± 0.03°
Pulses 16,384 65,536	± 0.0015°
Initialization time	30 ms

#### Mechanical data

Mechanical design	2 measuring wheels, 0 ring surface
Mass	0.5 kg
Maximum operating speed	3,000 rpm <sup>1)</sup>
Bearing lifetime	3 x 10^9 revolutions
Spring deflection spring arm	40 mm
Preload spring arm	20 mm

 $<sup>^{1)}</sup>$  Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

#### Electrical data


Electrical interface	4.5 V 32 V
	TTL/HTL programmable, (factory setting: TTL)
Connection type	Male connector, M12, 8-pin, radial
	Cable, universal, 1.5 m
	Cable, universal, 3 m
	Cable, universal, 5 m
Operating current without load	40 mA
Supply voltage	4.5 V 32 V
Load current	≤ 30 mA
Power consumption	0.7 W (without load)
Maximum output frequency	≤ 820 kHz
Reference signal, number	1
Reference signal, position	90° electric, logically gated with A and B (programmable, see zero pulse width)
MTTFd: mean time to dangerous failure	300 years (EN ISO 13849-1) <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

EMC	EN 61000-6-3, EN 61000-6-2
Enclosure rating (IEC 60529)	IP 65
Air humidity	90% 1)
Operating temperature range	-20 °C +100 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	70 g/ 6 ms (EN 60068-2-27)
Resistance to vibrations	30 g/ 2,000 Hz 10 Hz (EN 60068-2-6)

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Condensation of optical surfaces not permitted.

## Type code




## Ordering information

## 2 measuring wheels, 0 ring surface

Electrical interface	Connection type	Range of pulses per revolution	Туре	Part no.
	Cable, universal, 1.5 m	65,536	DFV60A-22PK65536	1051331
TTI /IITI muaguamanahla	Cable, universal, 3 m	65,536	DFV60A-22PL65536	1051334
TTL/HTL programmable	Cable, universal, 5 m	65,536	DFV60A-22PM65536	1051337
	Plug connector, M12, 8-pin, radial	65,536	DFV60A-22PC65536	1051309


## Dimensional drawings (dimensions in mm)

#### Connector outlet




General tolerances according to ISO 2768-mk


#### Cable outlet



General tolerances according to ISO 2768-mk

DFV60 with 2056155 mounted spring arm (available as an accessory)






General tolerances according to ISO 2768-mk

## PIN assignment


#### Cable, 8-wire

View of M12 male device connector on encoder




PIN, 8-pin, M12 male connector	Color of the wires for encoders with cable outlet	TTL/HTL signal	Explanation
1	Brown	Ā	Signal wire
2	White	A	Signal wire
3	Black	B	Signal wire
4	Pink	В	Signal wire
5	Yellow	Z	Signal wire
6	Violet	Z	Signal wire
7	Blue	GND	Ground connection of the encoder
8	Red	+U <sub>S</sub>	Supply voltage (volt-free to housing)
Screen	Screen	Screen	Screen connected to housing on encoder side.  Connected to ground on control side.

## Signal outputs



CCW with view on the measuring wheel, see dimensional drawing.

### Zero pulse width 90 m, 180° or 270°, programmable



CCW with view on the measuring wheel, see dimensional drawing.

### Recommended accessories

### Mounting systems

Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
	Measuring wheel with O-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278

#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Spring arm / mounting arm for DFV60	DFV60 sprung arm	2056155

### Connectivity

### Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight	5 m	DOL-1208-G05MAC1	6032867
	Head B: cable Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm², Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869

### Female connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature:  -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , Ø 5.6 mm		LTG-2308-MWENC	6027529
>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	Dutha	LTG-2411-MW	6027530
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2612-MW	6028516

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature:  -40 °C +85 °C	STE-1208-GA01	6044892
9-16-	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B:  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40  ^{\circ}\text{C} \dots +125  ^{\circ}\text{C}$	STE-2312-G01	2077273

#### Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, connector system, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: PVC, shielded, can be used for encoders with cable outlet in conjunction with PGT-10-Pro	0.5 m	DSL-0D08-G0M5AC3	2061739
	Head A: female connector, M12, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, 4 x 2 x 0.08 mm <sup>2</sup>	0.5 m	DSL-2D08-G0M5AC3	2046579
	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, $4 \times 2 \times 0.08 \text{ mm}^2$	0.5 m	DSL-3D08-G0M5AC3	2046580

### Other accessories

### Programming and configuration tools

Figure	Brief description	Туре	Part no.
	Programming unit USB, for programmable SICK Encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoder.	PGT-08-S	1036616
V m.m A	Programming unit display for programmable SICK DFS60, VFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254

<sup>→</sup> For additional accessories, please see page K-668 onwards

F



### **ABSOLUTE ENCODERS**

### Flexible, compact and reliable – absolute encoders made to measure!

Absolute encoders generate information about position, angle and rotation counts in type-specific angle steps. For this, a unique code pattern is assigned to each angle increment. The number of code patterns available per revolution determines the resolution. Each code pattern forms a unique reference, and is therefore an absolute position. There is therefore no need for a reference run after switching on. A singleturn encoder measures the absolute position within a

revolution. A multiturn encoder not only provides the position within a revolution but also the number of revolutions.

### Your benefits

- Optical and magnetic variants for the widest range of requirements
- Reduced maintenance costs thanks to magnetic, wearless scanning in single and multiturn design
- High level of productivity due to optical encoders with a high level of precision and fast calculation of positions
- Rugged design for maximum system availability, even in extreme ambient conditions
- Absolutely compact specially suited in cases where installation space is tight
- Flexible integration in all common networks







	Applications		
	AHS/AHM36 SSI		ATM60 SSI
	AHS/AHM36 CANopen		ATM60 CANopen
milie	AFS/AFM60 SSI	8	ATM60 DeviceNet
(e	AFS/AFM60 EtherNet/IP G-312 Intelligent, powerful, precise	0) 100:	ATM90 SSI
(e	AFS/AFM60 PROFINET	83	ATM90 PROFIBUS
(e	AFS/AFM60 EtherCAT®		ARS60 SSI/Parallel
Te	A3M60 PROFIBUS		ACS/ACM36
	ATM60 PROFIBUS	To.	ACM60

Absolute encoders can be used in any factory and logistics automation setting, where shaft rotational movement requires absolute detection. Depending on the protocol of each interface, additional information, such as speed or diagnostic data, can also be provided.


Palletizer system - positioning the gripper



For example, plastic bottles are stacked in multiple layers on pallets in a palletizer system. The gripper of the pallet handling machine must be positioned in the X and Y directions. An absolute encoder is used to determine the position of the gripper.

Multiturn absolute encoders with an Ethernet-based interface from the AFM60 product family can be used for this type of application. Or alternatively, you could also used an encoder with a SSI interface, such as the AFM60 SSI.

### Bottling plant - positioning of the turntable and conveyor belt



In the bottling line shown here, bottles are collected in the rotating turntable filling stations from the left-hand side and are filled as they rotate. Once full, the bottles are placed on a conveyor belt. The position and speed of the rotating turntable and the conveyor belt are monitored using an absolute encoder.

This application is ideal for multiturn absolute encoders with fieldbus interfaces and round axis functionality, such as the A3M60 PROFIBUS. The speed of the conveyor belt can be detected using an absolute encoder. Or alternatively, you can use an absolute encoder with a combined interface, such as the SSI + Incremental to detect the speed and position of the conveyor belt.

Cranes - calculating the lift height of the gripper



When moving and loading logs using cranes, you must be able to detect the height of the gripper. An absolute encoder mounted on the drum is ideal for this purpose. An additional absolute encoder is mounted on the gripper itself to calculate the opening angle in use.

With its Ethernet-based fieldbus interfaces Ethernet/IP, EtherCAT®, or PROFINET, the multiturn AFM60 absolute encoder is especially well suited to this application. The position and velocity, as well as other parameters, can simultaneously be transmitted. A singleturn AFS60 absolute encoder with an EtherNet-based interface can be used to calculate the gripper opening.

### PRODUCT FAMILY OVERVIEW









Flexible, smart, compact



AHS/AHM36 CANopen

Flexible, smart, compact

Electrical interface SSI CANopen	
Resolution Up to a maximum of 14-bit singleturn and 12-bit Up to a maximum of 14-bit singleturn and 12-bit multiturn Up to a maximum of 14-bit singleturn and 12-bit	
Mechanical interfaceSolid shaft, servo flangeSolid shaft, servo flangeSolid shaft, face mount flangeSolid shaft, face mount flangeBlind hollow shaftBlind hollow shaft	
Connection type Universal male connector Universal cable Universal cable Universal cable	
Ambient temperature	
Enclosure rating Up to IP 67 Up to IP 67	
Programmable   V	

At a glance



- Compact 36 mm absolute encoder with max. 26 bits (singleturn: 14 bits, multiturn: 12 bits)
- Face mount flange, servo flange, blind hollow shaft
- Rotating M12 male connector or rotating cable outlet
- SSI interface
- Programmable SSI version: Resolution, preset value, etc. can be programmed (depending on the type)
- Protection class up to IP67 (depending on the type)
- Operating temperature: -40 °C ... +100 °C (depending on the type)

→ G-232

- Compact 36 mm absolute encoder with max. 26 bits (singleturn: 14 bits, multiturn: 12 bits)
- Face mount flange, servo flange, blind hollow shaft
- Rotating M12 male connector or rotating cable outlet
- CANopen interface with programmable configuration
- Diagnostic functions: temperature, operating time, etc. (depending on the type)
- Protection class up to IP67 (depending on the type)
- Operating temperature: -40 °C ... +85 °C (depending on the type)

→ G-252

**Detailed information** 





#### AFS/AFM60 SSI

Precise, flexible, versatile



#### AFS/AFM60 EtherNet/IP

Intelligent, powerful, precise

SSI/Gray SSI/Gray + Incremental, HTL SSI/Gray + Incremental, TTL SSI/Gray + Sin/Cos, 1,024 periods SSI/Gray, programmable SSI/Gray + Incremental TTL/HTL, programmable SSI/Gray + Sin/Cos, 1,024 periods, programmable	EtherNet/IP
Up to a maximum of 18-bit singleturn and 12-bit multiturn	Up to a maximum of 18-bit singleturn and 12-bit multiturn
Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft Through hollow shaft	Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft
Radial male connector Universal cable Radial cable	Axial male connector
-40 °C +100 °C	-40 °C +85 °C
Up to IP 67	Up to IP 67
✓	<b>√</b>

- High-resolution absolute encoder with up to 30 bits (AFM60) or 18 bits (AFS60)
- Face mount flange, servo flange, blind hollow shaft or through hollow shaft
- SSI, SSI + incremental or SSI + sin/cos interface
- Resolution, preset, etc. can be programmed (depending on the type)
- Connectivity: M12 or M23 male connector or cable outlet
- Enclosure rating: IP 67 (housing), IP 65 (shaft)
- Operating temperature: -40 °C ... +100 °C (depending on the type)

- High-resolution, 30-bit absolute encoder
- Integrated web server and FTP server
- DLR (Device Level Ring)
- · Function module
- Comprehensive diagnostic functions
- IP addressing via software and hardware
- Round axis functionality (transmission calculation)

→ G-268 → G-312







**AFS/AFM60 PROFINET** 

Intelligent, powerful, precise



AFS/AFM60 EtherCAT®

Intelligent, powerful, precise

#### **Technical data overview**

**Electrical interface** Resolution

Mechanical interface

**Connection type** Ambient temperature **Enclosure rating** Programmable

**PROFINET** Up to a maximum of 18-bit singleturn and 12-bit multiturn Solid shaft, servo flange Solid shaft, face mount flange

> Axial male connector -40 °C ... +85 °C Up to IP 67

Blind hollow shaft

EtherCAT®

Up to a maximum of 18-bit singleturn and 12-bit multiturn

Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft Axial male connector -40 °C ... +85 °C Up to IP 67

At a glance

- High-resolution 30-bit absolute encoder (18-bit singleturn and 12-bit multiturn)
- · Face mount flange, servo flange and blind hollow shaft
- Connection type: 3 x M12 axial male connector
- PROFINET-IO-RT interface
- · Less than 5 ms data update time
- · Round axis functionality
- · Alarms, warnings and diagnostics functions for speed, position, temperature, operating time, etc.
- · Status display via 5 LEDs

- High-resolution 30-bit absolute encoder (18-bit singleturn and 12-bit multiturn)
- Face mount flange, servo flange and blind hollow shaft
- Connection type: 3 x M12 axial male con-
- On the fly data transmission rate in  $\mu s$  range
- EtherCAT® interface CoE (CiA DS-301) Device profile (CiA DS-406)
- · Round axis functionality
- Alarms, warnings and diagnostics functions for speed, position, temperature, operating time, etc.
- Status display via 5 LEDs
- Up to 16 adjustable electronic cam switches

**Detailed information** 





#### **A3M60 PROFIBUS**

Compact, rugged, powerful



#### **ATM60 PROFIBUS**

Reliable, established, and modular

PROFIBUS	PROFIBUS
Up to a maximum of 14-bit singleturn and 17-bit multiturn	Up to a maximum of 13-bit singleturn and 13-bit multiturn
Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft	Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft
Axial male connector	Bus connection adapters
-30 °C +80 °C	-20 °C +80 °C
Up to IP 67	Up to IP 67
<b>v</b>	-

- Rugged absolute multiturn encoder with up to 31 bits (14-bit singleturn and 17-bit multiturn)
- Face mount flange, servo flange or blind hollow shaft
- Compact design (<70 mm)
- Integrated PROFIBUS interface with DP V0, V1, and V2 functionality (depending on type)
- Connectivity: 3 x M12 male connectors
- Protection class up IP 67
- Operating temperature: -30 °C ... +80 °C (depending on the type)
- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount flange, servo flange, blind hollow shaft, and extensive adapter accessories
- Zero-set and preset functions via hardware or software
- Electrical interface: PROFIBUS DP as per IEC61158 / RS 485, electrically isolated
- Electronically adjustable, configurable resolution
- Magnetic scanning

→ G-372







ATM60 SSI

Reliable, established, and modular



**ATM60 CANopen** 

Reliable, established, and modular

Technical data overview		
Electrical interface	SSI	CANopen
Resolution	Up to a maximum of 13-bit singleturn and 13-bit multiturn	Up to a maximum of 13-bit singleturn and 13-bit multiturn
Mechanical interface	Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft	Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft
Connection type	Radial male connector Radial cable	Bus connection adapters
Ambient temperature	-20 °C +85 °C	−20 °C +80 °C
Enclosure rating	Up to IP 67	Up to IP 67
Programmable	<b>✓</b>	<b>✓</b>

At a glance

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount flange, servo flange, blind hollow shaft, and extensive adapter accessories
- Zero-set and preset functions via hardware or software
- Electrical interface: SSI with gray or binary code type
- Electronically adjustable, configurable resolution
- Round axis function (optional) also for non-binary resolutions (per revolution) and decimal numbers (number of revolutions)
- · Magnetic scanning

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount, servo flange, blind hollow shaft, adapter accessories
- Zero-set and preset functions via hardware/ software
- Electrical interface: CAN specification 2. 0B, electrically isolated; DS 301, V4.01, DSP 406, V2.0, Class 2
- Electronically adjustable, configurable resolution
- Network status info via duo LED
- · Magnetic scanning

Detailed information → G-398 → G-412







#### ATM60 DeviceNet

Reliable, established, and modular



ATM90 SSI

Reliable, established, and modular

DeviceNet	SSI
Up to a maximum of 13-bit singleturn and 13-bit multiturn	Up to a maximum of 13-bit singleturn and 13-bit multiturn
Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft	Through hollow shaft
Bus connection adapters	Radial male connector Radial cable
-20 °C +80 °C	-20 °C +70 °C
Up to IP 67	IP 65
V	V

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount, servo flange, blind hollow shaft, and adapter accessories
- Zero-set and preset functions via hardware/software
- Electrical interface: CAN/DeviceNet specification 2.0B, electrically isolated; device profile: Generic [0]
- Electronically adjustable, configurable resolution
- · Network status info via duo LED
- · Magnetic scanning

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: through hollow shaft with shallow installation depth
- Zero-set and preset functions via hardware or software
- · Electrical interface: SSI with gray or binary code type
- Electronically adjustable, configurable resolution
- · Magnetic scanning

→ G-424

→ G-436









Reliable, established, and modular



ARS60 SSI/Parallel

Reliable and established

Technical data overview			
Electrical interface	PROFIBUS	SSI/Gray SSI/Gray capped Parallel/Gray Parallel/Gray capped Parallel/BIN Parallel/BCD	
Resolution	Up to a maximum of 13-bit singleturn and 13-bit multiturn	Up to a maximum of 13 bit	
Mechanical interface	Through hollow shaft	Solid shaft, servo flange Solid shaft, face mount flange Blind hollow shaft Through hollow shaft	
Connection type	3 x radial male connectors 3 x radial PG	Radial male connector Axial male connector Radial cable Axial cable	
Ambient temperature	−20 °C +80 °C	−20 °C +85 °C	
Enclosure rating	IP 65	Up to IP 66	
Programmable	<b>∨</b>	-	
At a glance			

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: through hollow shaft with shallow installation depth
- Zero-set and preset functions via hardware or software
- Electrical interface: PROFIBUS DP as per IEC61158 / RS-485, electrically isolated
- · Electronically adjustable, configurable resolution
- · Magnetic scanning

- Absolute singleturn encoder
- Resolution: up to 15 bits (32,768 steps)
- · Electrical interface: SSI with gray or gray capped code type
- Electrical interface: Parallel with gray, gray capped, binary, BCD code type
- Zero-set function
- · Mechanical interfaces: face mount flange, servo flange, blind and through hollow shaft
- Enclosure rating up to IP 66

**Detailed information** 



## FLEXIBLE, SMART, COMPACT



### **Product description**

The AHS/AHM36 SSI absolute encoder product family provides increased flexibility due to its mechanical adaptation, electrical connectivity, and SSI communication. With their rotating male connector or cable outlets as well as the various mounting hole patterns and adapter flanges, these encoders are suitable for nearly any application. The encoders are able to connect to a wide range of controls due to a programming tool that can be used to make individual adjustments

to the structure of the SSI protocol, in addition to adjusting the singleturn/multiturn resolution, the counting direction, and other parameters. Thanks to the large operating temperature range from -40 °C ... +100 °C and the protection class up to IP67, this encoder family can be used in harsh ambient conditions. The rugged, reliable, fully magnetic sensor system provides a maximum resolution of 14 bits for the singleturn variant and 26 bits for the multiturn variant.

### At a glance

- Compact 36 mm absolute encoder with max. 26 bits (singleturn: 14 bits, multiturn: 12 bits)
- Face mount flange, servo flange, blind hollow shaft
- Rotating M12 male connector or rotating cable outlet
- SSI interface

- · Programmable SSI version: Resolution, preset value, etc. can be programmed (depending on the type)
- · Protection class up to IP67 (depending on the type)
- Operating temperature: -40 °C ... +100 °C (depending on the type)

### Your benefits

- Simple, time-saving mechanical installation due to a rotating male connector or cable outlet, various mounting hole patterns, and many different shafts
- Simple and flexible electrical installation with various configuration options and adjustable SSI protocol structure (programmable SSI version)
- · Easy setup for various applications allowing binary, non-binary, and non-integer resolutions with the round axis functionality (programmable SSI version)
- Reliable operation in harsh environments thanks to the rugged, reliable, fully magnetic sensor system
- · Space-efficient and cost-effective design that is suitable for applications where space is tight
- · High performance at a cost-efficient price







### More information

Fields of application
Detailed technical dataG-233
Type code
Ordering information
Dimensional drawingsG-239
Proposed fitting
PIN assignment
Singleturn signal outputs G-245
Multiturn signal outputs
Recommended accessories G-249

→ www.mvsick.com/en/AHS AHM36 SSI

For more information, simply enter the link or scan the OR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



### Fields of application

• Measures the absolute position in various industries, machines, and tools, including automated guided systems (AGS), industrial trucks, commercial vehicles, packaging

machines, logistics applications, machine construction and medical technology

#### Detailed technical data

#### Performance

	Basic	Advanced			
Max. number of steps per revolution	4,096 (12 bit)	16,384 (14 bit)			
Max. number of revolutions					
Absolute singleturn	1	1			
Absolute multiturn	4,096 (12 bit)				
Resolution					
Absolute singleturn					
Non-programmable	256, 360, 512, 720, 1,024, 2,048, 3,600, 4,096	256, 360, 512, 720, 1,024, 2,048, 3,600, 4,096, 8,192, 16,384			
Programmable 1)	-	1 16,384			
Absolute multiturn					
Non-programmable	8x12 bit, 9x12 bit, 10x12 bit, 11x12 bit, 12x12 bit	8x12 bit, 9x12 bit, 10x12 bit, 11x12 bit, 12x12 bit, 13x12 bit, 14x12 bit			
Programmable 1)	-	0x0 bit 14x12 bit			
Error limits	± 0.35° (at 20 °C)				
Repeatability	± 0.25° (at 20 °C)	± 0.2° (at 20 °C)			
Measuring increment (360 °/ number of steps per revolution)	± 0.09°	± 0.022°			
Initialization time	100 ms <sup>2)</sup>				

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Can be programmed using SICK programming tools.

#### Interfaces

	Basic	Advanced
Electrical interface	SSI	
Code type		
Non-programmable	Gray	
Programmable	-	Gray, binary
Code sequence		
Non-programmable	CW/CCW, configurable via cable	
Programmable	-	CW/CCW, configurable via Programming Tool or cable
Interface signals	Clock +, Clock -, Data +, Data-	
Max. clock frequency	60 kHz 2 MHz <sup>1)</sup>	
Set (electronic adjustment)	H active (L = 0 3 V, H = 4 Us V)	
CW/CCW (counting sequence when turning)	L active (L = 0 1 V, H = 2 Us V)	
Configuration data	-	Number of steps per revolution, number of revolutions (multiturn only), PRESET, counting direction, code type, offset, position bits, position of error bit, round axis functionality (multiturn version only), SSI mode
Position forming time	125 µs	

<sup>1)</sup> Min. LOW level (Clock +) 500 ns.

<sup>&</sup>lt;sup>2)</sup> Position can be read after this period.

	Basic	Advanced
Connection type	M12 male connector, 8-pin, universal Cable, 8-wire, universal, 0.5 m Cable, 8-wire, universal, 1.5 m Cable, 8-wire, universal, 3 m Cable, 8-wire, universal, 5 m	
Operating voltage range	4.5 V DC 32 V DC	
Max. power consumption without load	≤ 1.5 W	
Reverse polarity protection	<b>v</b>	
MTTFd: mean time to dangerous failure 1)	230 years (EN ISO 13849-1)	

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

#### Mechanical data

	Basic	Advanced		
Shaft diameter				
Solid shaft	6 mm, 1/4", 8 mm, 3/8", 10 mm			
Blind hollow shaft	6 mm, 1/4", 8 mm, 3/8", 10 mm			
Start up torque				
Solid shaft	0.5 Ncm (at 20 °C)	1 Ncm (at 20 °C)		
Blind hollow shaft	0.5 Ncm (at 20 °C)	1 Ncm (at 20 °C)		
Operating torque				
Solid shaft	< 0.5 Ncm (at 20 °C)	< 1 Ncm (at 20 °C)		
Blind hollow shaft	< 0.5 Ncm (at 20 °C)	< 1 Ncm (at 20 °C)		
Permissible shaft loading				
Solid shaft	40 N (radial) 20 N (axial)			
Permissible shaft movement, static/dy-	2014 (axiai)			
namic				
Blind hollow shaft	$\pm$ 0.3 mm / $\pm$ 0.1 mm radial			
Many an austing an and	$\pm$ 0.3 mm / $\pm$ 0.1 mm axial			
Max. operating speed	0.000 1)	6,000 rpm <sup>2), 3)</sup>		
Singleturn	9,000 rpm <sup>1)</sup>	· · · ·		
Multiturn	6,000 rpm <sup>1)</sup>	6,000 rpm <sup>2), 3)</sup>		
Bearing lifetime	3.6 x 10 <sup>8</sup> revolutions			
	2.0 x 10 <sup>9</sup> revolutions			
Shaft material	Stainless steel			
Flange material	Aluminum			
Housing material	Zinc			
Cable material	PUR			
Mass				
	,			
Blind hollow shaft	0.12 kg (related to encoder with connector outlet)			

<sup>1)</sup> Take into account self-heating of 3.5 K per 1,000 revolutions/min when designing the operating temperature range.

<sup>&</sup>lt;sup>2)</sup> Take into account self-heating of 5.5 K per 1,000 revolutions/min when designing the operating temperature range.

 $<sup>^{\</sup>mbox{\tiny 3)}}$  For Advanced type encoders, the shaft seal must be inspected regularly.

	Basic	Advanced
Rotor moment of inertia		
Solid shaft	2.5 gcm <sup>2</sup>	
Blind hollow shaft	15 gcm <sup>2</sup>	
Max. angular acceleration	≤ 500,000 rad/s²	

 $<sup>^{1)}</sup>$  Take into account self-heating of 3.5 K per 1,000 revolutions/min when designing the operating temperature range.

### Ambient data

	Basic	Advanced	
EMC	According to EN 61000-6-2 and EN 61000-6-3		
Enclosure rating	IP 65 on housing side (acc. to IEC 60529) $^{1)}$ IP 66 + IP 67, on housing side (acc. to IEC 60529) $^{1)}$ IP 66 + IP 67, on shaft side (acc. to IEC 60529) $^{2)}$ IP 66 + IP 67, on shaft side (acc. to IEC 60529) $^{2)}$		
Permissible relative humidity	90% (condensation not permitted)		
Operating temperature range	-20 °C +70 °C	-40 °C +100 °C	
Storage temperature range	-40 °C +100 °C, without packaging		
Resistance to shocks	100 g/6 ms (according to EN 60068-2-27)		
Resistance to vibrations	20 g/10 Hz 2,000 Hz (according to EN 60068-2-6)		

 $<sup>^{\</sup>mbox{\tiny 1)}}$  In an assembled male connector.


 $<sup>^{2)}</sup>$  Take into account self-heating of 5.5 K per 1,000 revolutions/min when designing the operating temperature range.

 $<sup>^{\</sup>scriptsize\textrm{3)}}$  For Advanced type encoders, the shaft seal must be inspected regularly.

 $<sup>^{\</sup>rm 2)}\,\mbox{For Advanced}$  type encoders, the shaft seal must be inspected regularly.

### Type code

### Singleturn




<sup>1)</sup> Flange adapters can be used for additional mechanical interfaces, see Mounting suggestions.

 $<sup>^{\</sup>rm 2)}$  Permissible shaft load lower than figure list in technical data.

<sup>3)</sup> NRTL certificate only valid for operating temperatures from -40 °C ... + 85 °C.

<sup>&</sup>lt;sup>4)</sup> Number of steps for non-programmable devices: Basic: 256, 360, 512, 720, 1,024, 2,048, 3,600, 4,096 Advanced: 256, 360, 512, 720, 1,024, 2,048, 3,600, 4,096, 8,192, 16,384. Other steps available on request. Number of steps for programmable devices (Advanced only): 16,384, programmable using Programming Tool.

#### Multiturn



 $<sup>^{1)}</sup>$  Flange adapters can be used for additional mechanical interfaces, see Mounting suggestions from page 17.

<sup>&</sup>lt;sup>2)</sup> Permissible shaft load lower than figure list in technical data.

 $<sup>^{3)}</sup>$  NRTL certificate only valid for operating temperatures from -40 °C ... + 85 °C.

<sup>&</sup>lt;sup>4)</sup> Resolution for non-programmable devices: Basic: 8x12, 9x12, 10x12, 11x12, 12x12. Advanced: 8x12, 9x12, 10x12, 11x12, 12x12, 13x12, 14x12. Other resolutions on request. Resolution for programmable devices (Advanced only): 14x12, programmable using Programming Tool.

<sup>&</sup>lt;sup>5)</sup> Protection class on shaft side always IP65.

### Ordering information

Absolute singleturn, solid shaft, servo flange

• Electrical interface: SSI

Shaft diameter	Connection type	Number of steps	Resolution	Programmable	Туре	Part no.
6 x 12 mm	M12 male connector, 8-pin, universal	4,096	4,096 x 1	-	AHS36B- S1AC004096	1066017
6 x 12 mm	M12 male connector, 8-pin, universal	≤ 16,384	16,384 x 1	~	AHS36A- S1PC016384	1066014
	Cable, 8-wire, universal, 1.5 m	≤ 16,384	16,384 x 1	•	AHS36A- S1PK016384	1066013

Absolute multiturn, solid shaft, servo flange

• Electrical interface: SSI

Shaft diameter	Connection type	Number of steps	Resolution	Programmable	Туре	Part no.
6 x 12 mm	M12 male connector, 8-pin, universal	4,096	4,096 x 4,096	-	AHM36B- S1AC012x12	1066012
6 x 12 mm	M12 male connector, 8-pin, universal	≤ 16,384	16,384 x 4,096	~	AHM36A- S1PC014x12	1066009
	Cable, 8-wire, universal, 1.5 m	≤ 16,384	16,384 x 4,096	•	AHM36A- S1PK014x12	1066008

Absolute singleturn, solid shaft, face mount flange

• Electrical interface: SSI

Shaft diameter	Connection type	Number of steps	Resolution	Programmable	Туре	Part no.
8 x 12 mm	M12 male connector, 8-pin, universal	16,384	16,384 x 1	-	AHS36A- S5AC016384	1067269

Absolute multiturn, solid shaft, face mount flange

• Electrical interface: SSI

Shaft diameter	Connection type	Number of steps	Resolution	Programmable	Туре	Part no.
6 x 12 mm	M12 male connector, 8-pin, universal	≤ 16,384	16,384 x 4,096	~	AHM36A- S3PC014x12	1066007
6 X 12 111111	Cable, 8-wire, universal, 1.5 m	≤ 16,384	16,384 x 4,096	~	AHM36A- S3PK014x12	1066006

Absolute singleturn, blind hollow shaft

• Electrical interface: SSI

Shaft diameter	Connection type	Number of steps	Resolution	Programmable	Туре	Part no.
6 mm	M12 male connector, 8-pin, universal	≤ 16,384	16,384 x 1	V	AHS36A- BAPC016384	1066016
O IIIIII	Cable, 8-wire, universal, 1.5 m	≤ 16,384	16,384 x 1	~	AHS36A- BAPK016384	1066015


### Absolute multiturn, blind hollow shaft

#### • Electrical interface: SSI


Shaft diameter	Connection type	Number of steps	Resolution	Programmable	Туре	Part no.
6 mm	M12 male con- nector, 8-pin, universal	≤ 16,384	16,384 x 4,096	V	AHM36A- BAPC014x12	1066011
	Cable, 8-wire, universal, 1.5 m	≤ 16,384	16,384 x 4,096	<b>v</b>	AHM36A- BAPK014x12	1066010

### Dimensional drawings (dimensions in mm)

Solid shaft, servo flange, M12 male connector



#### Solid shaft, servo flange, cable output




X = Measuring point for operating temperature


Bend radius of cable; R = 30 mm

8015560/2015-09-01 Subject to change without notice

### Solid shaft, servo flange, for adapting to 1.25 m Ecoline wire draw mechanism, SD mechanical design




### Solid shaft, face mount flange, M12 male connector



#### X = Measuring point for operating temperature


#### Solid shaft, face mount flange, cable output



X = Measuring point for operating temperature

Bend radius of cable; R = 30 mm


#### Blind hollow shaft, M12 male connector



X = Measuring point for operating temperature

Customer's own shaft: insertion depth of at least 15 mm to max. of 22 mm, from contact surface, from stator coupling, recommended shaft tolerance of k7

### Blind hollow shaft, cable outlet




Bend radius of cable; R = 30 mm

Customer's own shaft: insertion depth of at least 15 mm to max. of 22 mm, from contact surface, from stator coupling, recommended shaft tolerance of k7

G-241

### Proposed fitting


Solid shaft, face mount flange with flange adapter, centering hub D20 to D50 (BEF-FA-020-050, 2072297)



X = Measuring point for operating temperature

Sample order for 6 mm shaft diameter: AHx36x-S3xx0xxxxx + BEF-FA-020-050 (adapter is not pre-assembled)


Solid shaft, face mount flange with flange adapter, centering hub D20 to D36 (BEF-FA-020-036, 2072298)



X = Measuring point for operating temperature

Sample order for 10 mm shaft diameter: AHx36x-SCxx0xxxxx + BEF-FA-020-036 (adapter is not pre-assembled)

Solid shaft, face mount flange with flange adapter, centering hub D20 to D36, 2 mm high (BEF-FA-020-036-002, 2072296)




X = Measuring point for operating temperature

Sample order for 6 mm shaft diameter: AHx36x-S3xx0xxxxx + BEF-FA-020-036-002 (adapter is not pre-assembled)




### Solid shaft, face mount flange with flange adapter, centering hub D20 to D24 (BEF-FA-020-024, 2072294)



X = Measuring point for operating temperature

Sample order for 6 mm shaft diameter: AHx36x-S3xx0xxxxx + BEF-FA-020-024 (adapter is not pre-assembled)

Solid shaft, face mount flange with flange adapter, centering hub D20 to D30 (BEF-FA-020-030, 2072295)




X = Measuring point for operating temperature

 $Sample\ order\ for\ 10\ mm\ shaft\ diameter:\ AHx36x-SCxx0xxxxx + BEF-FA-020-030\ (adapter\ is\ not\ pre-assembled)$ 

### PIN assignment

View of M12 male device connector on encoder



PIN, 8-pin, M12 male connector	Wire colors, cable outlet	Signal	Explanation
1	Brown	Data-	Interface signals
2	White	Data+	Interface signals
3	Black	V/R	Sequence for direction of rotation
4	Pink	SET	Electronic adjustment
5	Yellow	Clock+	Interface signals
6	Lilac	Clock-	Interface signals
7	Blue	GND	Ground connection
8	Red	+US	Operating voltage
Screen	Screen	Screen	Screen connected to housing on encoder side. Connected to ground on control side.


V/R Forwards / Reverse: This input programs the counting direction for the encoder. When it is not connected, this input is set to HIGH. If the encoder shaft is rotated clockwise (to the right) as viewed when facing the shaft, it counts in ascending order. If it should count in ascending order when the shaft is rotated counterclockwise (to the left), then this connection must be permanently set to LOW level (GND).

shaft is rotated counterclockwise (to the left), then this confliction must be permanently set to LOW level (GND).

SET This input is for electronic zeroing. If the SET cable is set to US for more than 250 ms, the mechanical position corresponds to the O value, i. e., the predetermined SET value.

### Singleturn signal outputs

### Singleturn SSI data format



Cycle 1-14: position bits Cycle 15: errorbit

#### Non-programmable encoder

Non-programmable encoders always output the SSI position MSB-justified (left-justified).

- 14 bits + 1 errorbit are always output (irrespective of the type and resolution selected)
- For resolutions below 14 bits, non-assigned bits are filled with 0.

#### Programmable encoder

- Per default, programmable encoders output the SSI position MSB-justified (left-justified).
- The operating modes "binary" and "non-binary" can be selected to set the resolution.
- All formats (left and right-justified) can be covered by shifting the bits in the programming interface accordingly using the arrow keys.

#### **Errorbit**

ERROR: general error This bit is set as soon as an error occurs in the encoder. This bit remains set as long as the error is present. In non-programmable encoders, the errorbit is always output as the 15th bit. In programmable encoders, it can also be output as the 15th bit or can be transmitted directly after the position bits.

#### The evaluation of the errorbit must be implemented in the control unit.

The errorbit output need not be used by the control unit.

If the errorbits cannot be evaluated in the control unit, the control unit must be set to the encoder resolution.

The errorbits must then be masked out at the control.

#### SSI mode:

Non-programmable encoders work in asynchronous SSI mode.

In programmable encoders, the programming interface enables users to choose between asynchronous and synchronous SSI mode. Asynchronous SSI mode is selected as the default setting.

#### Asynchronous SSI mode:


The position is always formed and made available every 125  $\mu$ s. The time for calculating the position is not related to the master clock. In asynchronous SSI mode, the break between two clock bursts must remain constant with a maximum deviation of  $\pm$  20% and must not exceed 600 ms.

#### Synchronous SSI mode:

The position is formed in sync with the master clock output, i.e., the time of the position values is related to the time of the master clock.


The position formation process begins 20  $\mu$ s following the end of a clock burst. The position is then made available after 125  $\mu$ s. The next position is formed a further 20  $\mu$ s after the end of the subsequent clock burst. The break between two clock bursts must be at least 150  $\mu$ s.

#### Programming interface and legend



### Multiturn signal outputs

#### Multiturn SSI data format



Cycle 1-12: multiturn position bits
Cycle 13-26: singleturn position bits

Cycle 27: errorbit

#### Non-programmable encoder

Non-programmable encoders always output the SSI position MSB-justified (left-justified).

- For non-programmable multiturn encoders, the number of revolutions is set to a fixed 4,096 (12 bits).
- 26 bits + 1 errorbit are always output (irrespective of the type and resolution selected).

For resolutions below 26 bits, non-assigned bits are filled with 0.

#### Programmable encoder

- Per default, programmable encoders output the SSI position MSB-justified (left-justified).
- The operating modes "binary", "non-binary" and "round axis functionality" can be selected to set the resolution.
- All formats (left and right-justified, 25 bit mode and fir-tree format) can be covered by shifting the bits in the programming interface accordingly using the arrow keys.

#### **Errorbit**

ERROR: general error This bit is set as soon as an error occurs in the encoder. This bit remains set as long as the error is present. In non-programmable encoders, the errorbit is always output as the 27th bit. In programmable encoders, it can also be output as the 27th bit or can be transmitted directly after the position bits.

#### The evaluation of the errorbit must be implemented in the control unit.

The errorbit output need not be used by the control unit.

If the errorbits cannot be evaluated in the control unit, the control unit must be set to the encoder resolution.

The errorbits must then be masked out at the control.

#### SSI mode:

Non-programmable encoders work in asynchronous SSI mode.

In programmable encoders, the programming interface enables users to choose between asynchronous and synchronous SSI mode. Asynchronous SSI mode is selected as the default setting.

#### Asynchronous SSI mode:

The position is always formed and made available every 125  $\mu$ s. The time for calculating the position is not related to the master clock. In asynchronous SSI mode, the break between two clock bursts must remain constant with a maximum deviation of  $\pm$  20% and must not exceed 600 ms.

### Synchronous SSI mode:


The position is formed in sync with the master clock output, i.e., the time of the position values is related to the time of the master clock.

The position formation process begins 20  $\mu$ s following the end of a clock burst. The position is then made available after 125  $\mu$ s. The next position is formed a further 20  $\mu$ s after the end of the subsequent clock burst. The break between two clock bursts must be at least 150  $\mu$ s.

The programmable multi-turn encoder supports the gear functions for rotary axes (endless shaft). Here, the number of revolutions is set a break; a total number of steps is also set. The total number of steps is distributed over the set number of revolutions, e. g. 100 steps to 12.5 revolutions (see example for the programming interface on the next page).

The round axis functionality can be used to implement a number for the overall resolution that is not a 2n multiple of the number of steps per revolution. It is also possible to set a non-integer number both for the number of revolutions and for the number of steps per revolution.

#### Programming interface and legend



# Recommended accessories

### Mounting systems

Mounting brackets and plates

### Mounting bracket

Figure	Brief description	Туре	Part no.
	Mounting bracket for encoder with centering hub 20 mm, including mounting kit for face mount flange	BEF-WF-20	2066393

Dimensional drawings → page K-725

### Flanges

Figure	Brief description	Туре	Part no.
	Stator coupling on hole circle 63 mm	BEF-DS08	2072206
9	Flange adapter centering hub D20 to D24	BEF-FA-020-024	2072294
	Flange adapter centering hub D20 to D30	BEF-FA-020-030	2072295
	Flange adapter centering hub D20 to D36	BEF-FA-020-036	2072298
	Flange adapter centering hub D20 to D36, 2 mm high	BEF-FA-020-036-002	2072296
	Flange adapter centering hub D20 to D50	BEF-FA-020-050	2072297

Dimensional drawings → page K-725

### Other mounting accessories

### Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	O-ring for measuring wheels (circumference 200 mm)	BEF-0R-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-0R-083-050	2064076

Dimensional drawings → page K-725

#### Servo clamps

Figure	Brief description	Туре	Part no.
	Servo clamps, small, for servo flange (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-RESOL	2039082

Dimensional drawings → page K-725



### Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, –30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-$ 30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30$ °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30$ °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30°C +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial +/- $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C +80 °C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
(io	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, –10 °C +80 °C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

Dimensional drawings → page K-725

### Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight	5 m	DOL-1208-G05MAC1	6032867
- 40	Head B: cable Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869

Dimensional drawings → page K-725

Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: -40 °C +85 °C	DOS-1208-GA01	6045001



Dimensional drawings → page K-725

#### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature: -40 °C +85 °C	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537

Dimensional drawings → page K-725

#### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15~\text{mm}^2$ , Ø 5.6 mm	By the	LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	meter	LTG-2612-MW	6028516

Dimensional drawings → page K-725

#### Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: PUR, halogen-free, shielded, 4 x 2 x 0.15 mm²	0.5 m	DSL-2D08-G0M5AC2	2048439

Dimensional drawings → page K-725

### Other accessories

### Programming and configuration tools

Figure	Brief description	Туре	Part no.
	Programming unit USB, for programmable SICK encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoder.	PGT-08-S	1036616
V m . m A	Programming unit display for programmable SICK DFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards

## FLEXIBLE, SMART, COMPACT



#### **Product description**

The AHS/AHM36 CANopen absolute encoder product family provides increased flexibility and diagnostics due to its mechanical adaptation, electrical connectivity, and CANopen communication. With their rotating male connector or cable outlets as well as the various mounting hole patterns and adapter flanges, these encoders are suitable for nearly any application. Individual adjustments can be made to the singleturn/multiturn resolution, the counting direction, and other parameters when integrating the encoders into the CANopen network. The encoder also communicates diagnostic data such as temperature or operating time. Thanks to the large operating temperature range from -40 °C ... +85 °C and the protection class up to IP67, this encoder family can be used in harsh ambient conditions. The rugged, reliable, fully magnetic sensor system provides a maximum resolution of 14 bits for the singleturn variant and 26 bits for the multiturn variant.

#### At a glance

- · Compact 36 mm absolute encoder with max. 26 bits (singleturn: 14 bits, multiturn: 12 bits)
- Face mount flange, servo flange, blind hollow shaft
- Rotating M12 male connector or rotating cable outlet
- CANopen interface with programmable configuration
- Diagnostic functions: temperature, operating time, etc. (depending on the type)
- Protection class up to IP67 (depending on the type)
- Operating temperature: -40 °C ... +85 °C (depending on the type)

#### Your benefits

- Simple, time-saving mechanical installation due to a rotating male connector or cable outlet, various mounting hole patterns, and many different shafts
- Simple network installation with various configuration options
- Intelligent diagnostic functions evaluate maintenance intervals for the entire system, thereby increasing system reliability
- · Easy setup for various applications allowing binary, non-binary, and non-integer resolutions with the round axis functionality (advanced version)
- Reliable operation in harsh environments thanks to the rugged, reliable, fully magnetic sensor system
- · Space-efficient and cost-effective design that is suitable for applications where space is tight
- · High performance at a cost-efficient price





1) UL 508 compliant.

#### More information

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawingsG-260
Proposed fitting
PIN assignment
Recommended accessories G-265

→ www.mvsick.com/en/AHS AHM36 CANopen

For more information, simply enter the link or scan the OR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

• Measures the absolute position in various industries, machines, and tools, including automated guided systems (AGS), industrial trucks, commercial vehicles, packaging

machines, logistics applications, machine construction and medical technology

#### Detailed technical data

#### Performance

	Basic	Advanced
Max. number of steps per revolution	4,096 (12 bit)	16,384 (14 bit)
Max. number of revolutions		
Absolute singleturn	1	
Absolute multiturn	4,096 (12 bit)	
Resolution <sup>1)</sup>		
Absolute singleturn	12 bit	14 bit
Absolute multiturn	12 bit x 12 bit	14 bit x 12 bit
Error limits	± 0.35° (at 20 °C)	
Repeatability	± 0.25° (at 20 °C)	± 0.2° (at 20 °C)
Measuring increment (360°/number of steps per revolution)	0.09°	0.022°
Initialization time	2 s <sup>2)</sup>	

<sup>&</sup>lt;sup>1)</sup> Programmable options via control unit.

#### Interfaces

	Basic	Advanced	
Electrical interface	CANopen		
Bus interface	CANopen®		
Encoder profile	CANopen CiA DS-301, V4.02 CiA DSP-305 LSS Encoder Profile: - CiA DS-406, V3.2 Class C2		
Address setting	0 127, default: 5		
Data transmission rate (baud rate)	20 kbit/s 1,000 Mbit/s factory setting:	125 kbit/s	
PDO data	Position, speed, temperature		
Configuration data	Number of steps per revolution, number of revolutions, PRESET, counting direction, sampling rate for speed monitoring, unit for output of the speed value	Number of steps per revolution, number of revolutions, PRESET, counting direction, sampling rate for speed monitoring, unit for output of the speed value, round axis functionality (multiturn version only), electronic cams (2 channels x 8 cams)	
Available diagnostic data	-	Current, minimum and maximum temperature, maximum speed, power-on counter, operating hours counter, power-on/motion, counter of direction changes/number of movements cw/number of movements ccw, minimum and maximum operating voltage	
Status information	CANopen status via status LED		
Bus termination	Via external terminator 1)		

<sup>1)</sup> See accessories.

<sup>&</sup>lt;sup>2)</sup> Position can be read after this period.

	Basic	Advanced
Connection type	M12 male connector, 5-pin, universal Cable, 5-wire, universal, 0.5 m Cable, 5-wire, universal, 1.5 m Cable, 5-wire, universal, 3 m Cable, 5-wire, universal, 5 m	
Max. power consumption (without load)	1.5 W	
Operating voltage range	10 V DC 30 V DC	
Reverse polarity protection	V	
MTTFd: mean time to dangerous failure 1)	270 years (EN ISO 13849-1)	

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

#### Mechanical data

	Basic	Advanced
Shaft diameter		
Solid shaft	6 mm, 1/4", 8 mm, 3/8", 10 mm	
Blind hollow shaft	6 mm, 1/4", 8 mm, 3/8", 10 mm	
Start up torque		
Solid shaft	0.5 Ncm (at 20 °C)	1 Ncm (at +20 °C)
Blind hollow shaft	0.5 Ncm (at 20 °C)	1 Ncm (at +20 °C)
Operating torque		
Solid shaft	< 0.5 Ncm (at 20 °C)	< 1 Ncm (at 20 °C)
Blind hollow shaft	< 0.5 Ncm (at 20 °C)	< 1 Ncm (at 20 °C)
Permissible shaft loading		
Solid shaft	40 N (radial) 20 N (axial)	
Permissible shaft load, static dynamic		
Blind hollow shaft	$\pm$ 0.3 mm/ $\pm$ 0.1 mm radial $\pm$ 0.3 mm/ $\pm$ 0.1 mm axial	
Max. operating speed		
Singleturn	9,000 rpm <sup>1)</sup>	6,000 rpm <sup>2), 3)</sup>
Multiturn	6,000 rpm <sup>1)</sup>	6,000 rpm <sup>2), 3)</sup>
Bearing lifetime		
Solid shaft	3.6 x 10 <sup>8</sup> revolutions	
Blind hollow shaft	2.0 x 10° revolutions	
Shaft material	Stainless steel	
Flange material	Aluminum	
Housing material	Zinc	

<sup>&</sup>lt;sup>1)</sup> Take into account self-heating of 3.5 K per 1,000 revolutions/min when designing the operating temperature range.

<sup>&</sup>lt;sup>2)</sup> Take into account self-heating of 5.5 K per 1,000 revolutions/min when designing the operating temperature range.

<sup>&</sup>lt;sup>3)</sup> For Advanced type encoders, the shaft seal must be inspected regularly.

Basic	Advanced
PUR	
0.12 kg (related to devices with connector outle	t)
0.12 kg (related to devices with connector outle	t)
2.5 gcm <sup>2</sup>	
15 gcm <sup>2</sup>	
≤ 500,000 rad/s²	
	PUR  0.12 kg (related to devices with connector outle 0.12 kg (related to devices with connector outle 2.5 gcm <sup>2</sup> 15 gcm <sup>2</sup>

 $<sup>^{1)}</sup>$  Take into account self-heating of 3.5 K per 1,000 revolutions/min when designing the operating temperature range.

#### Ambient data

	Basic	Advanced	
EMC	According to EN 61000-6-2 and EN 61000-6-3		
Enclosure rating	IP 65 on housing side (acc. to IEC 60529) <sup>1)</sup> IP 65 on shaft side (acc. to IEC 60529)	IP 66 + IP 67, on housing side (according to IEC 60529) <sup>1)</sup> IP 66 + IP 67, on shaft side (according to IEC 60529) <sup>2)</sup>	
Permissible relative humidity	90% (condensation not permitted)		
Operating temperature range	-20 °C +70 °C	-40 °C +85 °C	
Storage temperature range	-40 °C +100 °C, without packaging		
Resistance to shocks	100 g, 6 ms (according to EN 60068-2-27)		
Resistance to vibrations	20 g, 10 Hz 2,000 Hz (according to EN 60068-2-6)		


<sup>1)</sup> In an assembled male connector.

 $<sup>^{2)}</sup>$  Take into account self-heating of 5.5 K per 1,000 revolutions/min when designing the operating temperature range.

<sup>&</sup>lt;sup>3)</sup> For Advanced type encoders, the shaft seal must be inspected regularly.

<sup>&</sup>lt;sup>2)</sup> For Advanced type encoders, the shaft seal must be inspected regularly.

#### Singleturn




<sup>&</sup>lt;sup>1)</sup> Flange adapters can be used for additional mechanical interfaces, see Mounting suggestions.

 $<sup>^{\</sup>rm 2)}$  Permissible shaft load lower than figure list in technical data.

<sup>&</sup>lt;sup>3)</sup> Number of steps programmable via control unit.

#### Multiturn



- $^{1)}$  Flange adapters can be used for additional mechanical interfaces, see Mounting suggestions.
- $^{\rm 2)}$  Permissible shaft load lower than figure list in technical data.
- 3) Protection class on shaft side always IP 65.
- <sup>4)</sup> Programmable options for resolution via control unit.

G-257

#### Ordering information

Absolute singleturn, solid shaft, servo flange

• Electrical interface: CANopen

• Programmable: ✓

Shaft diameter	Connection type	Number of steps	Resolution	Туре	Part no.
	M12 male connector,	≤ 4,096	4,096 x 1	AHS36B- S1CC004096	1066005
6 x 12 mm	5-pin, universal	≤ 16,384	16,384 x 1	AHS36A- S1CC016384	1066002
	Cable, 5-wire, universal, 1.5 m	≤ 16,384	16,384 x 1	AHS36A- S1CK016384	1066001

Absolute multiturn, solid shaft, servo flange

• Electrical interface: CANopen

Programmable:

Shaft diameter	Connection type	Number of steps	Resolution	Туре	Part no.
	M12 male connector,	≤ 4,096	4,096 x 4,096	AHM36B- S1CC012x12	1065992
6 x 12 mm	5-pin, universal	≤ 16,384	16,384 x 4,096	AHM36A- S1CC014x12	1065993
	Cable, 5-wire, universal, 1.5 m	≤ 16,384	16,384 x 4,096	AH- M36A-S1CK014x12	1065994

Absolute singleturn, solid shaft, face mount flange

• Electrical interface: CANopen

• Programmable: ✓

Number of steps: ≤ 16,384
 Resolution: 16,384 x 1

Shaft diameter	Connection type	Туре	Part no.
8 x 12 mm	M12 male connector, 5-pin, universal	AHS36A- S5CC016384	1067268

Absolute multiturn, solid shaft, face mount flange

• Electrical interface: CANopen

Programmable: ✓

Number of steps: ≤ 16,384
 Resolution: 16,384 x 4,096

Shaft diameter	Connection type	Туре	Part no.
6 x 12 mm	M12 male connector, 5-pin, universal	AHM36A- S3CC014x12	1065999
	Cable, 5-wire, universal, 1.5 m	AHM36A- S3CK014x12	1066000



## Absolute singleturn, blind hollow shaft

• Electrical interface: CANopen

• Programmable: ✓

• Number of steps:  $\leq 16,384$ • **Resolution:** 16,384 x 1

Shaft diameter	Connection type	Туре	Part no.
	M12 male connector, 5-pin, universal	AHS36A- BACC016384	1066004
6 mm	Cable, 5-wire, universal, 1.5 m	AHS36A- BACK016384	1066003

#### Absolute multiturn, blind hollow shaft

• Electrical interface: CANopen


• Programmable: ✓

• Number of steps:  $\leq 16,384$ • Resolution: 16,384 x 4,096


	Shaft diameter	Connection type	Туре	Part no.
	6 mm	M12 male connector, 5-pin, universal	AHM36A- BACC014x12	1065990
		Cable, 5-wire, universal, 1.5 m	AHM36A- BACK014x12	1065991

#### Dimensional drawings (dimensions in mm)

#### Solid shaft, servo flange, M12 male connector



#### Solid shaft, servo flange, cable output




X = Measuring point for operating temperature

Bend radius of cable; R = 30 mm




## G

#### Solid shaft, face mount flange, M12 male connector



X = Measuring point for operating temperature


#### Solid shaft, face mount flange, cable output



X = Measuring point for operating temperature


Bend radius of cable; R = 30 mm

#### Blind hollow shaft, M12 male connector



Customer's own shaft: insertion depth of at least 15 mm to max. of 22 mm, from contact surface, from stator coupling, recommended shaft tolerance of k7

#### Blind hollow shaft, cable outlet




Bend radius of cable; R = 30 mm

Customer's own shaft: insertion depth of at least 15 mm to max. of 22 mm, from contact surface, from stator coupling, recommended shaft tolerance of k7

# G

#### Proposed fitting


Solid shaft, face mount flange with flange adapter, centering hub D20 to D50 (BEF-FA-020-050, 2072297)



X = Measuring point for operating temperature

Sample order for 6 mm shaft diameter: AHx36x-S3xx0xxxxx + BEF-FA-020-050 (adapter is not pre-assembled)


Solid shaft, face mount flange with flange adapter, centering hub D20 to D36 (BEF-FA-020-036, 2072298)



X = Measuring point for operating temperature

Sample order for 10 mm shaft diameter: AHx36x-SCxx0xxxxx + BEF-FA-020-036 (adapter is not pre-assembled)


Solid shaft, face mount flange with flange adapter, centering hub D20 to D36, 2 mm high (BEF-FA-020-036-002, 2072296)



X = Measuring point for operating temperature

Sample order for 6 mm shaft diameter: AHx36x-S3xx0xxxxx + BEF-FA-020-036-002 (adapter is not pre-assembled)


Solid shaft, face mount flange with flange adapter, centering hub D20 to D24 (BEF-FA-020-024, 2072294)



X = Measuring point for operating temperature

Sample order for 6 mm shaft diameter: AHx36x-S3xx0xxxxx + BEF-FA-020-024 (adapter is not pre-assembled)

Solid shaft, face mount flange with flange adapter, centering hub D20 to D30 (BEF-FA-020-030, 2072295)



X = Measuring point for operating temperatu

Sample order for 10 mm shaft diameter: AHx36x-SCxx0xxxxx + BEF-FA-020-030 (adapter is not pre-assembled)

#### PIN assignment

View of M12 male device connector on encoder



PIN	Signal	Wire color	Function
1	CAN shield	White	Screen
2	VDC	Red	Encoder supply voltage: 10 30 V DC
3	GND/CAN GND	Blue	O V (GND)
4	CAN high	Black	CAN signal
5	CAN low	Pink	CAN signal
Housing	_	_	Screen

#### Recommended accessories

#### Mounting systems

Mounting brackets and plates

#### Mounting bracket

Figure	Brief description	Туре	Part no.
	Mounting bracket for encoder with centering hub 20 mm, including mounting kit for face mount flange	BEF-WF-20	2066393

Dimensional drawings → page K-725

#### Flanges

#### Flange plate

Figure	Brief description	Туре	Part no.
	Stator coupling on hole circle 63 mm	BEF-DS08	2072206
0	Flange adapter centering hub D20 to D24	BEF-FA-020-024	2072294
	Flange adapter centering hub D20 to D30	BEF-FA-020-030	2072295
	Flange adapter centering hub D20 to D36	BEF-FA-020-036	2072298
9(3)	Flange adapter centering hub D20 to D36, 2 mm high	BEF-FA-020-036-002	2072296
	Flange adapter centering hub D20 to D50	BEF-FA-020-050	2072297

Dimensional drawings → page K-725

#### Other mounting accessories

#### Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	0-ring for measuring wheels (circumference 200 mm)	BEF-0R-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-OR-083-050	2064076

Dimensional drawings → page K-725

#### Servo clamps

Figure	Brief description	Туре	Part no.
	Servo clamps, small, for servo flange (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-RESOL	2039082

Dimensional drawings → page K-725

#### Shaft adaptation

#### Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, –30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
i Tem	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-$ 30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30$ °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30$ °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, –10 °C +80° C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

Dimensional drawings → page K-725

## Connectivity

#### Adapters and distributors

#### T-piece

Figure	Brief description	Туре	Part no.
So	CANopen, T-piece	DSC- 1205T000025KM0	6030664

Dimensional drawings → page K-725

#### Plug connectors and cables

#### Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 5-pin, straight	2 m	DOL-1205-G02MY	6053041
	Head B: cable  Cable: suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm²	5 m	DOL-1205-G05MY	6053042
40 %	+ 1 x 0.34 mm <sup>2</sup> , Ø 6.7 mm A-coded	10 m	DOL-1205-G10MY	6053043

Dimensional drawings → page K-725

#### Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 5-pin, straight Head B: male connector, M12, 5-pin, straight Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm, A-coded	2 m	DSL-1205-G02MY	6053044
10		5 m	DSL-1205-G05MY	6053045
		10 m	DSL-1205-G10MY	6053046

Dimensional drawings → page K-725

#### Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
6	Head A: female connector, M12, 5-pin, straight, shielded, for cable diameter 4.5 mm 7 mm Head B: -	DOS-1205-GA	6027534

Dimensional drawings → page K-725

#### Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
0	Head A: male connector, M12, 5-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1205-GA	6027533

Dimensional drawings → page K-725

#### Other plug connectors and cables

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, shielded Cable: terminator	STE-1205-GKEND	6037193

Dimensional drawings → page K-725



<sup>→</sup> For additional accessories, please see page K-668 onwards

## PRECISE, FLEXIBLE, VERSATILE







#### **Product description**

With a high resolution of 18 bits (AFS60) or 30 bits (AFM60) and a large selection of programmable parameters, the AFS60 absolute singleturn encoder and the AFM60 absolute multiturn encoder set new standards when it comes to rotary encoders. The high resolution combined with the high IP protection class enables use in a multitude of industrial applications. Both encoders are equipped with the SSI interface while the AFM60 is also available with the SSI + Incremental and

SSI + Sin/Cos combined interfaces. A shaft bearing distance of 30 mm means the AFS60/AFM60 product family has significantly better rotation accuracy than encoders with blocked ball bearings. Yet despite their large bearing distance, the AFS60/AFM60 have a compact design. The AFS and AFM60 SSI can be programmed via the same PC-based programming tool (PGT-08-S) or the hand-held PGT-10-Pro programming tool.

#### At a glance

- High-resolution absolute encoder with up to 30 bits (AFM60) or 18 bits (AFS60)
- Face mount flange, servo flange, blind hollow shaft or through hollow shaft
- SSI, SSI + incremental or SSI + sin/ cos interface
- Resolution, offset, etc. can be programmed (depending on the type)
- Connectivity: M12 or M23 male connector or cable outlet
- Enclosure rating: IP67 (housing), IP65 (shaft)
- Operating temperature:
   -40 °C ... +100 °C (depending on the type)

#### Your benefits

- The programmability of the encoder results in reduced storage, high machine availability, and easy installation
- Precise positioning thanks to high resolutions
- Large selection of mechanical interfaces and electrical contacting options: suitable for all applications
- Suitable for applications with limited space (extremely short installation depth of 30 mm)
- Excellent concentricity properties due to long bearing distance
- Suitable programming tools are available as accessories for every application

# 

#### More information

Fields of application
Detailed technical data
Viewing number of resolutions $G-273$
Ordering information
Dimensional drawingsG-292
PIN assignment
Signal outputs
Interfaces
Recommended accessories G-306



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

• Measurement of absolute position using one or more revolutions in various machines and systems such as tool machines, packaging systems, wood processing machines, presses, printing machines

#### Detailed technical data

#### Performance

	Eco	Basic	Advanced	
Max. number of steps per revolution (SSI interface) <sup>1)</sup>	4,096	32,768	262,144	
Max. number of revolutions				
Absolute singleturn	1			
Absolute multiturn	4,096			
Resolution				
Absolute singleturn	12 bit	15 bit	18 bit	
Absolute multiturn	12 x 12 bit	15 x 12 bit	18 x 12 bit	
Error limits	± 0.2°	± 0.05°	± 0.03°	
Repeatability	0.002°			
Measurement increment deviation				
1 399 (steps per revolution)	± 0.2°	± 0.08°	± 0.04°	
400 40,000 (steps per revolution)	± 0.2°	± 0.01°	± 0.008°	
> 40,000 (steps per revolution)	-		± 0.002°	
Measuring increment (360 °/ number of steps per revolution)	0.09°	0.01°	0.014°	
Initialization time	50 ms <sup>2)</sup>			
Position forming time	< 1 µs			

<sup>1)</sup> See maximum viewing number of resolutions

<sup>&</sup>lt;sup>2)</sup> Position can be read after this period.

	Eco	Basic	Advanced		
Electrical interface	SSI				
Signal offset	2.5 V ± 10%				
Code type	Gray				
Configurable code sequence	CW/CCW				
Measurement increment					
360°/number of steps	0.09°	0.01°	0.0014°		
Number of steps per revolution					
AFS60 and AFM60 1)	4,096	32,768	262144		
Number of revolutions (AFM60)	4,096				
Measurement increment deviation					
Number of steps per revolution					
1399	± 0.2°	± 0.08°	± 0.04°		
400 40,000	± 0.2°	± 0.01°	± 0.008°		
> 40,000	-		± 0.002°		
Clock+, Clock-, Data+, Data-					
SSI max. clock frequency 2 MHz, and min. LOW level (Clock+): 500 ns	1 MHz	2 MHz	2 MHz		
SET (electronic adjustment)	H active (L = $0 - 3 \text{ V}$ ; H = $4 - \text{U}$	S V)			
V/R (counting sequence when turning)	L active (L = $0 - 1.5 \text{ V}$ ; H = $2.0 - U_S \text{ V}$ )				
Incremental interface TTL/HTL/program- mable (AFM60 SSI + incremental)					
Number of lines per revolution	1/4 of number of SSI steps per	revolution			
Measurement increment	90° electric/number of lines				
Measurement increment deviation					
Number of steps per revolution 1 99	± 0.2°	± 0.08°	± 0.04°		
Number of steps per revolution 100 10,000	± 0.2°	± 0.01°	± 0.008°		
Number of steps per revolution > 10,000	-		± 0.002°		
Interface signals A, Ā, B, B	Digital, differential				
Max. output frequency	300 kHz	600 kHz	820 kHz		
Load current	30 mA				
Incremental interface sine/cosine 4.5 V 5.5 V, sine 0.5 V <sub>ss</sub> (AFM60 SSI + sin/cos)					
Number of lines per revolution	1,024				
Max. output frequency	200 kHz				
Load resistance	Min. 120 Ω				
Interface signals	Analog, differential				
Sin+, Sin-, Cos+, Cos-					
	0.5 V <sub>PP</sub> ± 20%				
Sin+, Sin-, Cos+, Cos-	0.5 V <sub>pp</sub> ± 20% 2.5 V ± 10%				

 $<sup>^{\</sup>mbox{\tiny 1)}}$  See maximum viewing number of resolutions

#### Electrical data

	Eco	Basic	Advanced
Connection type	M23 male connector, 12-pin, radia M12 male connector, 8-pin, radia Cable, 8-wire, universal, 1.5 m <sup>1)</sup> Cable, 8-wire, universal, 3 m <sup>1)</sup> Cable, 8-wire, universal, 5 m <sup>1)</sup> Cable, 8-wire, universal, 10 m <sup>1)</sup> Cable, 12-wire, radial, 1.5 m <sup>2)</sup> Cable, 12-wire, radial, 3 m <sup>2)</sup> Cable, 12-wire, radial, 5 m <sup>2)</sup>	al	
Power consumption	0.5 W (without load)		
Operating voltage range	4.5 V DC 32 V DC		
Min. load resistance	-		≥ 120 Ω
Maximum output frequency	-		≤ 200 kHz
Code type	Gray		
Code sequence	CW/CCW, configurable		
Reverse polarity protection	<b>✓</b>		
MTTFd: mean time to dangerous failure	250 years (EN ISO 13849-1) 3)		

<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

#### Mechanical data

	Eco	Basic	Advanced
Shaft diameter			
Face mount flange	10 mm x 19 mm		
Servo flange	6 mm x 10 mm		
Blind hollow shaft, through hollow shaft	8, 10, 12, 14, 15 mm and 3/8"	, 1/2", 5/8" <sup>1)</sup>	
Shaft material	Stainless steel		
Flange material	Aluminum		
Housing material	Aluminum die-cast		
Mass <sup>2)</sup>			
Face mount flange, servo flange	0.3 kg		
Blind hollow shaft, through hollow shaft	0.2 kg		
Start up torque at 20 °C			
Face mount flange, servo flange	0.5 Ncm		
Blind hollow shaft, through hollow shaft	0.8 Ncm		
Operating torque at 20 °C			
Face mount flange, servo flange	0.3 Ncm		
Blind hollow shaft, through hollow shaft	0.6 Ncm		
Permissible shaft movement, axial static/dynamic			
Blind hollow shaft, through hollow shaft	± 0.5 mm, ± 0.2 mm		± 0.5 mm, ± 0.1 mm

 $<sup>^{\</sup>mbox{\tiny 1)}}\,5/8"$  not available for multiturn.

<sup>&</sup>lt;sup>2)</sup> No UL certificate.

<sup>3)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

<sup>&</sup>lt;sup>2)</sup> Relates to devices with cable outlet.

 $<sup>^{3)}</sup>$  Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

	Eco	Basic	Advanced
Permissible shaft movement, radial static/dynamic			•
Blind hollow shaft, through hollow shaft	$\pm$ 0.3 mm/ $\pm$ 0.1 mm		$\pm$ 0.3 mm/ $\pm$ 0.05 mm
Permissible shaft loading			
Face mount flange, servo flange	80 N (radial) 40 N (axial)		
Maximum operating speed 3)			
Face mount flange, servo flange	9,000 rpm		
Blind hollow shaft	6,000 rpm		
Through hollow shaft	9,000 rpm		
Rotor moment of inertia			
Face mount flange, servo flange	6.2 gcm <sup>2</sup>		
Blind hollow shaft, through hollow shaft	40 gcm <sup>2</sup>		
Bearing lifetime	3.0 x 10 <sup>9</sup> revolutions		
Max. angular acceleration	≤ 500,000 rad/s²		

 $<sup>^{\</sup>mbox{\tiny 1)}}\,5/8"$  not available for multiturn.

#### Ambient data

	Eco	Basic	Advanced		
EMC	According to EN 61000-6-2 an	According to EN 61000-6-2 and EN 61000-6-3 1)			
Enclosure rating					
On the shaft	IP 65				
On the housing, male connector outlet 2)	IP 67				
On the housing, cable outlet	IP 67				
Permissible relative humidity	90% (condensation of optical surfaces not permitted)				
Operating temperature range	0 °C +85 °C -40 °C <sup>3)</sup> +100 °C				
Storage temperature range	-40 °C +100 °C, without packaging				
Resistance to shocks (according to EN 60068-2-27)	50 g/ 6 ms	70 g/ 6 ms	60 g/ 6 ms		
Resistance to vibration (according to EN 60068-2-6)	20 g/ 10 Hz 2,000 Hz	30 g/ 10 Hz 2,000 Hz	20 g/ 10 Hz 2,000 Hz		

 $<sup>^{\</sup>scriptsize 1)}$  The EMC according to the standards quoted is achieved if shielded cables are used.


<sup>&</sup>lt;sup>2)</sup> Relates to devices with cable outlet.

<sup>3)</sup> Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

<sup>&</sup>lt;sup>2)</sup> In an assembled male connector.

 $<sup>^{\</sup>rm 3)}$  When cables are fixed in place.

#### Maximum viewing number of resolutions depends on the selected number of steps per revolution



The maximum speed depends on the type of shaft.

## Ordering information

Type code AFS60 SSI absolute encoder, singleturn, solid shaft

	Тур	е								
	E	Туре	Type E (see technical data on page G-269)							
	В	Туре	Type B (see technical data on page G-269)							
	Α	Туре	e A (	see	tech	nica	al data on page G-269)			
				Ме	cha	nical	l design			
				1	Sei	vo f	flange, solid shaft, 6 x 10 mm			
				4	Fac	e m	nount flange, solid shaft, 10 x 19 mm			
					Ele	ctric	cal interface			
					Α	4.5	5 32 V SSI/Gray			
					T	Co	nnection type			
						Α	Male connector M23, 12-pin, radial			
						С	Male connector M12, 8-pin, radial			
						K	Cable, 8-wire, universal, 1.5 m 1)			
						L	Cable, 8-wire, universal, 3 m <sup>1)</sup>			
						М	Cable, 8-wire, universal, 5 m <sup>1)</sup>			
							Resolution			
							Number of steps per revolution, selection depends on type, see below.			
	$\downarrow$			$\downarrow$	Ų.	Ų.	<b>+ + + + +</b>			
A F S 6 0		-	S		A	ľ				

<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

#### Number of steps per revolution

• Type E 1)

000256	8 bit	001024	10 bit	004096	12 bit
000512	9 bit	002048	11 bit		

• Type B 1)

000256	8 bit	002048	11 bit	016384	14 bit
000512	9 bit	004096	12 bit	032768	15 bit
001024	10 bit	008192	13 bit		

<sup>1)</sup> Others available on request.

• Type A 1)

000256	8 bit	002048	11 bit	016384	14 bit	131072	17 bit
000512	9 bit	004096	12 bit	032768	15 bit	262144	18 bit
001024	10 bit	008192	13 bit	065536	16 bit		

<sup>1)</sup> Others available on request.


#### Example orders

• Servo flange

Servo flange design	Туре
Type E, M12 male connector, 8-pin, radial, number of steps per revolution 1,024 (10 bit)	AFS60E-S1AC001024

#### • Face mount flange

Face mount flange design	Туре
Type E, M12 male connector, 8-pin , radial, number of steps per revolution 1,024 (10 bit)	AFS60E-S4AC001024



<sup>&</sup>lt;sup>1)</sup> Number of steps from 256 to 262144 can be programmed by the customer. Factory setting for Type B: 032768; Type A: 262144.

#### Example orders

#### · Servo flange

	Servo flange design	Туре	Part no.
	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFS60B-S1PA032768	1037493
	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFS60B-S1PC032768	1037494
Type B	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFS60B-S1PK032768	1037495
	Cable, 8-wire, universal, 3 m, number of steps per revolution 32,768	AFS60B-S1PL032768	1037496
	Cable, 8-wire, universal, 5 m, number of steps per revolution 32,768	AFS60B-S1PM032768	1037497
	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFS60A-S1PA262144	1037498
	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFS60A-S1PC262144	1037499
Type A	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFS60A-S1PK262144	1037500
	Cable, 8-wire, universal, 3 m, number of steps per revolution 262144	AFS60A-S1PL262144	1037501
	Cable, 8-wire, universal, 5 m, number of steps per revolution 262144	AFS60A-S1PM262144	1037502

#### • Face mount flange

	Face mount flange design	Туре	Part no.
	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFS60B-S4PA032768	1037483
	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFS60B-S4PC032768	1037484
Type B	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFS60B-S4PK032768	1037485
	Cable, 8-wire, universal, 3 m, number of steps per revolution 32,768	AFS60B-S4PL032768	1037486
	Cable, 8-wire, universal, 5 m, number of steps per revolution 32,768	AFS60B-S4PM032768	1037487
	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFS60A-S4PA262144	1037488
	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFS60A-S4PC262144	1037489
Type A	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFS60A-S4PK262144	1037490
	Cable, 8-wire, universal, 3 m, number of steps per revolution 262144	AFS60A-S4PL262144	1037491
	Cable, 8-wire, universal, 5 m, number of steps per revolution 262144	AFS60A-S4PM262144	1037492

<sup>&</sup>lt;sup>2)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

#### Туре E Type E (see technical data on page G-269) **B** Type B (see technical data on page G-269) A Type A (see technical data on page G-269) Mechanical design 1 Servo flange, solid shaft, 6 x 10 mm Face mount flange, solid shaft, 10 x 19 mm **Electrical interface** A 4.5 ... 32 V SSI/Gray **Connection type** Male connector M23, 12-pin, radial Male connector M12, 8-pin, radial Cable, 8-wire, universal, 1.5 m 1) Cable, 8-wire, universal, 3 m 1) Cable, 8-wire, universal, 5 m 1) Resolution Number of steps per revolution, selection depends on type, see below. A F M 6 0 S Α

Number of steps per revolution x 4,096 (12 bit)

Type E

000256	8 bit	001024	10 bit	004096	12 bit
000512	9 bit	002048	11 bit		
• Type P					

Type B

000256	8 bit	002048	<b>11</b> bit	016384	14 bit	
000512	9 bit	004096	12 bit	032768	15 bit	
001024	10 bit	008192	13 bit			

• Type A

71							
000256	8 bit	002048	<b>11</b> bit	016384	14 bit	131072	17 bit
000512	9 bit	004096	12 bit	032768	15 bit	262144	18 bit
001024	10 bit	008192	13 bit	065536	16 bit		

#### Example orders

• Servo flange

Servo flange design	Туре
Type E, cable, 8-wire, universal, 1.5 m, number of steps per revolution 4,096 (12 bits)	AFM60E-S1AK004096


· Face mount flange

Face mount flange design	Туре
Type E, cable, 8-wire, universal, 1.5 m, number of steps per revolution 4,096 (12 bits)	AFM60E-S4AK004096

<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

G

Type code AFM60 SSI/gray + incremental and SSI/gray + sin/cos, absolute encoder, multiturn, 4,096 revolutions, solid shaft



Number of steps per revolution x 4,096 (12 bit), number of incremental lines in brackets

008192

• Type E

000256	8 bit (64)	001024	10 bit (256)	004096	12 bit (1024)
000512	9 bit (128)	002048	11 bit (512)		
Type B					
iype b					
000256	8 bit (64)	002048	11 bit (512)	016384	14 bit (4096)
000512	9 bit (128)	004096	12 bit (1024)	032768	15 bit (8192)
001024	10 bit (256)	008192	13 bit (2048)		
<ul> <li>Type A</li> </ul>					
000256	8 bit (64)	002048	11 bit (512)	016384	14 bit (4096)
000512	9 bit (128)	004096	12 bit (1024)	032768	15 bit (8192)

13 bit (2048)

#### Example orders

10 bit (256)

001024

Servo flange

Servo flange design	Туре
Type E, 4.5 32 V, SSI/gray + incremental, TTL, M23 male connector, 12-pin , radial, number of steps per revolution 2,048 (11 bit)	AFM60E-S1TA002048


065536

16 bit (16384)

Face mount flange

Face mount flange design	Туре
Type E, 4.5 32 V, SSI/gray + incremental, TTL, M23 male connector, 12-pin , radial, number of steps per revolution 2,048 (11 bit)	AFM60E-S4TA002048

17 bit (32768) 18 bit (65536)



<sup>1)</sup> Number of steps from 256 (8 bit) to 262144 (18 bit) can be programmed by the customer. Factory setting for Type B: 032768; Type A: 262144.

#### Example orders


· Servo flange

	Servo flange design	Туре	Part no.
	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-S1PA032768	1037513
	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFM60B-S1PC032768	1037514
Type B	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFM60B-S1PK032768	1037515
	Cable, 8-wire, universal, 3 m, number of steps per revolution 32,768	AFM60B-S1PL032768	1037516
	Cable, 8-wire, universal, 5 m, number of steps per revolution 32,768	AFM60B-S1PM032768	1037517
	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-S1PA262144	1037518
	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFM60A-S1PC262144	1037519
Type A	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFM60A-S1PK262144	1037520
	Cable, 8-wire, universal, 3 m, number of steps per revolution 262144	AFM60A-S1PL262144	1037521
	Cable, 8-wire, universal, 5 m, number of steps per revolution 262144	AFM60A-S1PM262144	1037522

#### · Face mount flange

	Face mount flange design	Туре	Part no.
	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-S4PA032768	1037503
	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFM60B-S4PC032768	1037504
Type B	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFM60B-S4PK032768	1037505
	Cable, 8-wire, universal, 3 m, number of steps per revolution 32,768	AFM60B-S4PL032768	1037506
	Cable, 8-wire, universal, 5 m, number of steps per revolution 32,768	AFM60B-S4PM032768	1037507
	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-S4PA262144	1037508
	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFM60A-S4PC262144	1037509
Type A	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFM60A-S4PK262144	1037510
	Cable, 8-wire, universal, 3 m, number of steps per revolution 262144	AFM60A-S4PL262144	1037511
	Cable, 8-wire, universal, 5 m, number of steps per revolution 262144	AFM60A-S4PM262144	1037512

<sup>&</sup>lt;sup>2)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.



<sup>&</sup>lt;sup>1)</sup> Number of steps from 256 (8 bit) to 262144 (18 bit) can be programmed by the customer. Factory setting for Type B: 032768; Type A: 262144. Number of incremental lines is always 1/4 of the number of SSI/gray lines.

#### Example orders


#### • Servo flange

	Servo flange design	Туре	Part no.
Туре В	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-S1RA032768	1052835
Type A	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-S1RA262144	1052837
Type B	4.5 32 V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-S1SA032768	1054220
Type A	4.5 32 V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-S1SA262144	1054219

#### · Face mount flange

	Face mount flange design	Туре	Part no.
Type B	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-S4RA032768	1052833
Type A	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-S4RA262144	1052624
Type B	4.5 32 V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-S4SA032768	1054222
Type A	4.5 32 V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-S4SA262144	1054221

#### Type code AFS60 SSI absolute encoder, singleturn, hollow shaft



<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

#### Number of steps per revolution

Type E <sup>1)</sup>

000256	8 bit	001024	10 bit	004096	12 bit
000512	9 bit	002048	11 bit		
• Type B <sup>1)</sup>					
000256	8 bit	002048	11 bit	016384	14 bit
000512	9 bit	004096	12 bit	032768	15 bit

008192

Type A <sup>1)</sup>

001024

000256	8 bit
000512	9 bit
001024	10 bit

10 bit

002048	<b>11</b> bit
004096	12 bit
008192	13 bit

13 bit

016384	14 bit
032768	15 bit
065536	16 bit

131072	17 bit
262144	18 bit

<sup>1)</sup> Others available on request.

<sup>1)</sup> Others available on request.

#### Example orders


• Blind hollow shaft

Blind hollow shaft design	Туре
Type E, hollow shaft design 8 mm, M12 male connector, 8-pin , radial, number of steps per revolution 1,024 (10 bit)	AFS60E-BBAC001024

• Through hollow shaft

Through hollow shaft design	Туре
Type E, hollow shaft design 8 mm, M12 male connector, 8-pin , radial, number of steps per revolution 1,024 (10 bit)	AFS60E-TBAC001024

#### Type code AFS60 SSI absolute encoder, singleturn, hollow shaft, programmable



<sup>1)</sup> Number of steps from 256 to 262144 can be programmed by the customer. Factory setting for Type B: 032768; Type A: 262144.

<sup>&</sup>lt;sup>2)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

# Example orders 1)

#### • Blind hollow shaft

	Blind hollow shaft design	Туре
	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFS60B-BxPA032768
Type B	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFS60B-BxPC032768
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFS60B-BxPK032768
	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFS60A-BxPA262144
Type A	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFS60A-BxPC262144
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFS60A-BxPK262144

 $<sup>^{\</sup>mbox{\tiny 1)}}\,x$  stands for hollow shaft diameters B to J, please enter corresponding letters in position 9.

#### • Through hollow shaft

	Through hollow shaft design	Туре
	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFS60B-TxPA032768
Type B	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFS60B-TxPC032768
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFS60B-TxPK032768
	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFS60A-TxPA262144
Type A	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFS60A-TxPC262144
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFS60A-TxPK262144

 $<sup>^{\</sup>mbox{\tiny 1)}}\,x$  stands for hollow shaft diameters B to J, please enter corresponding letters in position 9.

Туре

E Type E (see technical data on page G-269)

<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

001024

Number of steps per revolution x 4,096 (12 bit)

8 bit

## Type E 000256

000512	9 bit	002048	11 bit		
• Type B					
000256	8 bit	002048	11 bit	016384	14 bit
000512	9 bit	004096	12 bit	032768	15 bit
001024	10 bit	008192	13 bit		

10 bit

• Type A							
000256	8 bit	002048	11 bit	016384	14 bit	131072	17 bit
000512	9 bit	004096	12 bit	032768	15 bit	262144	18 bit
001024	10 bit	008192	13 bit	065536	16 bit		

004096

12 bit


#### Example orders

• Blind hollow shaft

Blind hollow shaft design	Туре
Type E, hollow shaft diameter 8 mm cable, 8-wire, universal, 1.5 m, number of steps per revolution 4,096 (12 bits)	AFM60E-BBAK004096

• Through hollow shaft

Through hollow shaft design	Туре
Type E, hollow shaft diameter 8 mm cable, 8-wire, universal, 1.5 m, number of steps per revolution 4,096 (12 bits)	AFM60E-TBAK004096



Number of steps per revolution x 4,096 (12 bit), number of incremental lines in brackets

004096

008192

Type E

000512

001024

000256	8 bit (64)	001024	10 bit (256)	004096	12 bit (1024)
000512	9 bit (128)	002048	11 bit (512)		
• Type B					
000256	8 bit (64)	002048	11 bit (512)	016384	14 bit (4096)
000512	9 bit (128)	004096	12 bit (1024)	032768	15 bit (8192)
001024	10 bit (256)	008192	13 bit (2048)		
• Type A					
000256	8 bit (64)	002048	11 bit (512)	016384	14 bit (4096)

12 bit (1024)

13 bit (2048)

032768

065536

15 bit (8192)

16 bit (16384)

G

9 bit (128)

10 bit (256)

17 bit (32768)

18 bit (65536)

131072

262144

#### Example orders


• Blind hollow shaft


Blind hollow shaft design	Туре
Type E, hollow shaft diameter 8 mm, 4.5 32 V, SSI/gray + incremental, TTL, M23 male connector, 12-pin , radial, number of steps per revolution 2,048 (11 bit)	AFM60E-BBTA002048

• Through hollow shaft

Through hollow shaft design	Туре
Type E, hollow shaft diameter 8 mm, 4.5 32 V, SSI/gray + incremental, TTL, M23 male connector, 12-pin , radial, number of steps per revolution 2,048 (11 bit)	AFM60E-TBTA002048

Type code AFM60 SSI/gray absolute encoder, multiturn, 4,096 revolutions, hollow shaft, programmable





<sup>&</sup>lt;sup>2)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction.

# Example orders 1)

# Blind hollow shaft


	Blind hollow shaft design	Туре
Type B	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-BxPA032768
	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFM60B-BxPC032768
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFM60B-BxPK032768
Туре А	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-BxPA262144
	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFM60A-BxPC262144
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFM60A-BxPK262144

 $<sup>^{1)}\,</sup>x$  stands for hollow shaft diameters B to H, please enter corresponding letters in position 9.

# • Through hollow shaft

	Through hollow shaft design	Туре
Туре В	M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-TxPA032768
	M12 male connector, 8-pin, radial, number of steps per revolution 32,768	AFM60B-TxPC032768
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 32,768	AFM60B-TxPK032768
Type A	M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-TxPA262144
	M12 male connector, 8-pin, radial, number of steps per revolution 262144	AFM60A-TxPC262144
	Cable, 8-wire, universal, 1.5 m, number of steps per revolution 262144	AFM60A-TxPK262144

 $<sup>^{1)}\,</sup>x$  stands for hollow shaft diameters B to H, please enter corresponding letters in position 9.



<sup>&</sup>lt;sup>1)</sup> Number of steps from 256 (8 bit) to 262144 (18 bit) can be programmed by the customer. Factory setting for Type B: 032768; Type A: 262144. Number of incremental lines is always 1/4 of the number of SSI/gray lines.

# Example orders 1)

# • Blind hollow shaft

	Blind hollow shaft design	Туре
Type B	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-BxRA032768
Type A	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-BxRA262144
Type B	4.5 32 V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-BxSA032768
Type A	$4.5 \dots 32 \text{ V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin, } \\ \text{radial, number of steps per revolution 262144}$	AFM60A-BxSA262144

 $<sup>^{\</sup>mbox{\tiny $1$}}\mbox{x}$  stands for hollow shaft diameters B to H, please enter corresponding letters in position 9.

# • Through hollow shaft


	Through hollow shaft design	Туре
Туре В	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-TxRA032768
Type A	4.5 32 V, SSI/gray + incremental, programmable, M23 male connector, 12-pin , radial, number of steps per revolution 262144	AFM60A-TxRA262144
Type B	4.5 32 V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin, radial, number of steps per revolution 32,768	AFM60B-TxSA032768
Type A	$4.5 \dots 32 \text{ V, SSI/gray, programmable, + sin/cos, 1,024 periods, M23 male connector, 12-pin, } \\ \text{radial, number of steps per revolution 262144}$	AFM60A-TxSA262144


 $<sup>^{1)}</sup>$  x stands for hollow shaft diameters B to H, please enter corresponding letters in position 9.

# Dimensional drawings (dimensions in mm)

# Face mount flange


Universal cable outlet






General tolerances according to DIN ISO 2768-mk 1 Cable  $\varnothing$  = 5.6 mm  $\pm$  0.2 mm bend radius R = 30 mm


Radial cable outlet for AFM60 SSI + incremental and AFM60 SSI + sin/cos





General tolerances according to DIN ISO 2768-mk

## M12 and M23 cable outlet




General tolerances according to DIN ISO 2768-mk

G-293


# Servo flange


Universal cable outlet



General tolerances according to DIN ISO 2768-mk 1 Cable Ø = 5.6 mm  $\pm$  0.2 mm bend radius R = 30 mm


Radial cable outlet for AFM60 SSI + incremental and AFM60 SSI + sin/cos






General tolerances according to DIN ISO 2768-mk

## M12 and M23 cable outlet




General tolerances according to DIN ISO 2768-mk

Mounting suggestion for small servo clamp part number 2029166




General tolerances according to DIN ISO 2768-mk


Mounting suggestion for half-shell servo clamp part number 2029165



# Blind hollow shaft

# Universal cable outlet





## **Customer-side**


General tolerances according to DIN ISO 2768-mk 1 Cable Ø = 5.6 mm  $\pm$  0.2 mm bend radius R = 30 mm

XF7 = Encoder shaft diameter, see type code

xj7 = Shaft diameter, on the customer side



# Radial cable outlet for AFM60 SSI + incremental and AFM60 SSI + sin/cos




#### **Customer-side**

General tolerances according to DIN ISO 2768-mk

XF7 = Encoder shaft diameter, see type code

xj7 = Shaft diameter, on the customer side

## M12 and M23 cable outlet





# Customer-side

General tolerances according to DIN ISO 2768-mk XF7 = Encoder shaft diameter, see type code xj7 = Shaft diameter, on the customer side

# Through hollow shaft

## Universal cable outlet





## **Customer-side**


General tolerances according to DIN ISO 2768-mk


① Cable Ø = 5.6 mm  $\pm$  0.2 mm bend radius R = 30 mm

XF7 = Encoder shaft diameter, see type code

xj7 = Shaft diameter, on the customer side

Radial cable outlet for AFM60 SSI + incremental and AFM60 SSI + sin/cos






General tolerances according to DIN ISO 2768-mk

XF7 = Encoder shaft diameter, see type code

xj7 = Shaft diameter, on the customer side



## M12 and M23 cable outlet



#### **Customer-side**

General tolerances according to DIN ISO 2768-mk

XF7 = Encoder shaft diameter, see type code


xj7 = Shaft diameter, on the customer side

3

# PIN assignment

- V/R Forwards/Reverse: This input programs the counting direction for the encoder. When it is not connected, this input is set to HIGH. If the encoder shaft is rotated clockwise (to the right) as viewed when facing the shaft, it counts in ascending order. If it should count in ascending order when the shaft is rotated counterclockwise (to the left), then this connection must be permanently set to LOW level (GND).
- SET This input is for electronic zeroing. If the SET cable is set to  $U_s$  for more than 250 ms after it had previously been unassigned for at least 1,000 ms or had been connected to GND, the mechanical position corresponds to the O value, i.e., the predetermined SET value.

M12 male connector, 8-pin and cable outlet, cable, 8-wire SSI/gray



View of M12 male device connector on encoder

Pin	Wire colors	SSI signal	Explanation
1	Brown	Data-	Interface signals
2	White	Data+	Interface signals
3	Black	V/R	Sequence in direction of rotation
4	Pink	SET	Electronic adjustment
5	Yellow	Clock+	Interface signals
6	Violet	Clock -	Interface signals
7	Blue	GND	Ground connection
8	Red	+U <sub>s</sub>	Operating voltage
		Screen	Screen connected to housing on encoder side. Connected to ground on control side.

# M23 male connector, 12-pin SSI/gray



View of M23 male device connector on encoder

Pin	Signal	Explanation
1	GND	Ground connection
2	Data+	Interface signals
3	Clock+	Interface signals
4	N. C.	Not connected
5	N. C.	Not connected
6	N. C.	Not connected
7	N. C.	Not connected
8	$U_s$	Operating voltage
9	SET	Electronic adjustment
10	Data-	Interface signals
11	Clock-	Interface signals
12	V/R̄	Sequence in direction of rotation
	Screen	Screen connected to housing on encoder side. Connected to ground on control side.

# M23 male connector, 12-pin and cable outlet, cable, 12-wire SSI/gray + incremental


Pin	Wire colors	Signal	Explanation
1	Red	+U <sub>s</sub>	Operating voltage
2	Blue	GND	Ground connection
3	Yellow	Clock+	Interface signal
4	White	Data+	Interface signal
5	Orange	SET	Electronic adjustment
6	Brown	Data-	Interface signal
7	Violet	Clock-	Interface signal
8	Black	B	Signal wire
9	Orange/black	V/R̄	Sequence in direction of rotation
10	Green	Ā	Signal wire
11	Gray	Α	Signal wire
12	Pink	В	Signal wire
		Screen	Screen connected to housing on encoder side. Connected to ground on control side.

# M23 male connector, 12-pin and cable outlet, cable, 12-wire SSI/gray + sin/cos

Pin	Wire colors	Signal	Explanation
1	Red	+U <sub>s</sub>	Operating voltage
2	Blue	GND	Ground connection
3	Yellow	Clock+	Interface signal
4	White	Data+	Interface signal
5	Orange	SET	Electronic adjustment
6	Brown	Data-	Interface signal
7	Violet	Clock-	Interface signal
8	Black	Sin-	Signal wire
9	Orange/black	V/R̄	Sequence in direction of rotation
10	Green	Cos-	Signal wire
11	Gray	Cos+	Signal wire
12	Pink	Sin+	Signal wire
		Screen	Screen connected to housing on encoder side. Connected to ground on control side.

## Signal outputs

# Singleturn SSI data format



#### Bit 1-18: Position bits

- . LSB: Least significant bit
- . MSB: Most significant bit

#### Bit 19-21: Errorbits

- ERRDIG: Error message concerning speed. If this error occurs during the position forming process, it is displayed through the ERRDIG bit.
- · ERRSI: Light source error.
- ERRSYNC: Contamination of the code disk or read system. A error has occurred during the position detection process since the last SSI data transmission. The errorbit is deleted during the next data transmission.

## Evaluation of the error bits must be realized in the PLC.

The error bits output do not have to be used by the PLC.


#### Example

If the absolute value encoder is adjusted to a resolution of 13 bits, 16 bits are output: 13 databits and 3 errorbits.

If the errorbits cannot be evaluated in the PLC, the control unit must be set to an encoder resolution of 13 bits. The errorbits must then be masked out at the control.

### Multiturn SSI data format

#### 30 bits




Bits 1–12: Multiturn position bits

Bits 13-30: Singleturn position bits

Bits 31-33: Errorbits

## 27 bits



Bit 1-12: Multiturn position bits

Bits 13-27: Singleturn position bits

Bits 28-30: Errorbits

#### Errorbits

- ERRDIG: Error message concerning speed. If this error occurs during the position forming process, it is displayed through the ERRDIG bit.
- ERRSI: Light source error.
- ERRSYNC: Contamination of the code disk or read system. A error has occurred during the position detection process since the last SSI data transmission. The errorbit is deleted during the next data transmission.

#### Evaluation of the error bits must be realized in the PLC.

The error bits output do not have to be used by the PLC. The multiturn resolution is fixed to 12 bits.

#### Example

If the absolute value encoder is adjusted to a resolution of 27 bits, 30 bits are output: 27 databits and 3 errorbits.

If the errorbits cannot be evaluated in the PLC, the control unit must be set to an encoder resolution of 27 bits. The errorbits must then be masked out at the control.


## **Interfaces**

# Electrical interfaces sin/cos 1.0 V<sub>ss</sub>

Supply voltage	Output
4.5 32 V	Sine 0.5 V <sub>ss</sub>

# Signals **before** difference at $120 \Omega$ load


Signal diagram for clockwise shaft rotation, looking in direction "A" (shaft)




Interface signals Sin, Sin, Cos, Cos	Signals before difference at 120 $\Omega$ load	Signal offset
Differential analog	0.5 V <sub>SS</sub> ± 20%	2.5 V ± 10%

# Signal after difference at $120 \Omega$ load

Signal diagram for clockwise shaft rotation, looking in direction "A" (shaft)



Incremental signal outputs for clockwise shaft rotation, looking in direction "A" (see dimensional drawing)



# Recommended accessories

# Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
(,	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

## Flanges

## Flange plate


Figure	Brief description	Туре	Part no.
U	Standard stator coupling	BEF-DS00XFX	2056812
	Stator coupling, 16.5 mm high	BEF-DS05XFX	2057423
U	Stator coupling with hole circle diameter 63 mm	BEF-DS07XFX	2059368
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-063REC	2034225
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161

Dimensional drawings → page K-725

## Other mounting accessories

# Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
0	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989



Dimensional drawings → page K-725

### Modular measuring wheel system

Brief description	Туре	Part no.
Measuring wheel system, desired mounting position: left, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-1	2071958
Measuring wheel system, desired mounting position: right, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-2	2071957

Dimensional drawings → page K-725

#### Mounting bell

Figure	Brief description	Туре	Part no.	
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987	

Dimensional drawings → page K-725

#### Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

Dimensional drawings → page K-725

### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
-91	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591



# Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
(Time-	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30$ °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10$ °C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-$ 10 °C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, -30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, –30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^{\circ}$ $+80^{\circ}$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986



# Connectivity

# Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight Head B: cable	5 m	DOL-1208-G05MAC1	6032867
-	Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869
		0.5 m	DOL-0J08-G0M5AA6	2048589
_	Head A: female connector, JST, 8-pin, straight	1.5 m	DOL-0J08-G1M5AA6	2048590
The state of the s	Head B: cable  Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm²,	3 m	DOL-0J08-G3M0AA6	2048591
	Ø 5.6 mm	5 m	DOL-0J08-G5M0AA6	2048593
		10 m	DOL-0J08-G10MAA6	2048594
		0.5 m	DOL-2308-G0M5AA6	2048595
_	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm²,	1.5 m	DOL-2308-G1M5AA6	2048596
		3 m	DOL-2308-G03MAA6	2048597
	Ø 5.6 mm <sup>1)</sup>	5 m	DOL-2308-G05MAA6	2048598
		10 m	DOL-2308-G10MAA6	2048599
		1.5 m	DOL-2312-G1M5MD2	2062284
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMD2	2062300
-	Head B: cable	5 m	DOL-2312-G05MMD2	2062301
	Cable: suitable for drag chain, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm <sup>2</sup> )	10 m	DOL-2312-G10MMD2	2062302
	1 1 A O.14 HHH -, W 7.0 HHH /	20 m	DOL-2312-G20MMD2	2062303
		30 m	DOL-2312-G30MMD2	2062304

 $<sup>^{1)}</sup>$  Suitable for SSI interfaces, not suitable for SSI + Incremental or SSI + Sin/Cos interfaces.

 $<sup>^{\</sup>rm 2)}$  Suitable for SSI + Incremental and SSI + Sin/Cos interfaces.

# Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^{\circ}$ C $+85~^{\circ}$ C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	DOS-2312-W01	2072580
	Head A: female connector, M23, 21-pin, straight, shielded, for cable diameter 5.5 mm 12 mm Head B: -	DOS-2321-G	6027539

Dimensional drawings → page K-725

# Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15\ mm^2$ , Ø 5.6 mm	By the meter	LTG-2308-MWENC	6027529
<b></b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2612-MW	6028516

Dimensional drawings → page K-725

## Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature: -40 °C +85 °C	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537



## Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: PUR, halogen-free, shielded, 4 x 2 x 0.15 mm <sup>2</sup>	0.5 m	DSL-2D08-G0M5AC2	2048439
	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm $^2$ 1)	0.5 m	DSL-3D08-G0M5AC2	2048440
	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight, 8-wire <sup>2)</sup>	0.5 m	DSL-3D08-G0M5AC4	2059270

 $<sup>^{1)}</sup>$  Suitable for use with SSI interfaces, not suitable for use with SSI + Incremental interface or SSI + Sin/Cos.

Dimensional drawings → page K-725

## Other accessories

# Programming and configuration tools

Figure	Brief description	Туре	Part no.
	Programming unit USB, for programmable SICK encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoder.	PGT-08-S	1036616
A M · M V	Programming unit display for programmable SICK DFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards

 $<sup>^{\</sup>rm 2)}\,\mbox{Suitable}$  for use with SSI + Incremental or SSI + Sin/Cos interfaces.

# INTELLIGENT, POWERFUL, PRECISE







## **Product description**

The AFS60 and AFM60 EtherNet/IP encoders from SICK are the first sensors of their kind to feature an active web server as well as to make their function blocks available for fieldbus integration. Mechanical engineers, integrators and end customers all benefit from features including simple commissioning, significantly reduced configuration time and direct, continuous access to the encoder via the machine's HMI user interface.

Furthermore, the encoders are equipped with an FTP server, which allows a direct firmware update. The web server configuration option opens up brand-new opportunities for commissioning, service and maintenance by operating personnel who have different capabilities and levels of interface knowledge

## At a glance

- High-resolution, 30-bit absolute encoder
- Integrated web server and FTP server
- DLR (Device Level Ring)
- · Function module

Your benefits

- Integrated web server for easy configuration without the need for specialized interface knowledge
- FTP server for firmware updates directly on site and in existing systems
- DLR (Device Level Ring) for enhanced system throughput thanks to redundant network communication
- Status display via five duo LEDs on the sensor for a quick initial indication of the operational status
- Comprehensive diagnosis via the 32bit fault header

- Comprehensive diagnostic functions
- IP addressing via software or hardware
- Round axis functionality (transmission calculation)
- Round axis functionality for full scalability for binary and non-binary resolutions as well as not complete multiturn revolutions (transmission calculation).
- Individual IP address via DHCP or pre-defined IP address via DEC switches







## More information

Fields of application
Detailed technical dataG-313
Maximum viewing number of
resolutions
Ordering information
Sales kits
Dimensional drawings
PIN assignment
Recommended accessories G-325



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

- · Palletizing systems
- Storage systems
- Packaging
- Hydraulic presses

- · Printing machines
- Robots
- · Rotary tables

## Detailed technical data

# Performance

Max. number of steps per revolution, AFS60 and AFM60	262,144 (18 bit) (maximum viewing number of resolutions, page G-315)	
Max. number of revolutions		
AFS60	1	
AFM60	4,096 (12 bit)	
Resolution		
AFS60	18 bit	
AFM60	30 bit	
Error limits	± 0.03°	
Repeatability	± 0.002°	
Measurement increment deviation	± 0.002°	
Measuring increment (360 °/ number of steps per revolution)	0.001°	
Initialization time	Approx. 12 s	

# Interfaces

Electrical interface	EtherNet/IP
Transfer rate	10/100 MBit/s
RPI (requested packet interval)	5 750 ms
Transmission media	CAT 5e cable
DLR (Device Level Ring)	V
Encoder profile	0 x 22
Configuration data	Number of steps per revolution, number of revolutions, PRESET, counting direction, sampling rate for speed monitoring, unit for outputting the speed, acceleration, and temperature, output of scaleable limit values such as: position ranges, speed, acceleration, number of movements cw/ccw, direction chances, operating hours for power-on/motion, round axis functionality (only multiturn version), heartbeat
Available diagnostic data	Current, minimum and maximum temperature, maximum speed, power-on counter, operating hours counter for power-on/motion, counter of direction changes/number of movements cw/number of movements ccw, minimum and maximum operating voltage, signal monitoring for single and multiturn

## Electrical data

Operating voltage range	10 V DC 30 V DC
Max. power consumption without load	≤ 3 W
Reverse polarity protection	<b>✓</b>
MTTFd: mean time to dangerous failure	80 years (EN ISO 13849-1) 1)

<sup>&</sup>lt;sup>4)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

# Mechanical data

Operating speed 1)		
Solid shaft	9,000 rpm (maximum viewing number of resolutions, page G-315)	
Blind hollow shaft	6,000 rpm (maximum viewing number of resolutions, page G-315)	
Mass	0.2 kg	
Permissible shaft load, solid shaft	80 N (radial); 40 N (axial)	
Permissible shaft movement of the drive element, blind hollow shaft	$\pm$ 0.3 / $\pm$ 0.05 mm (radial, static/dynamic) $\pm$ 0.5 / $\pm$ 0.1 mm (axial, static/dynamic)	
Rotor moment of inertia		
Solid shaft	≤ 6.2 gcm <sup>2</sup>	
Blind hollow shaft	≤ 40 gcm²	
Bearing lifetime	3 x 10 <sup>9</sup> revolutions	
Start up torque at 20 °C		
Solid shaft	0.5 Ncm	
Blind hollow shaft	0.8 Ncm	
Operating torque at 20 °C		
Solid shaft	0.3 Ncm	
Blind hollow shaft	0.6 Ncm	
Max. angular acceleration	$5 \times 10^5 \text{ rad/s}^2$	
Shaft diameter		
Face mount flange, solid shaft	10 x 19 mm, 3/8"	
Servo flange, solid shaft	6 x 10 mm	
Blind hollow shaft, AFM60	8, 10, 12, 14, 15 mm, 1/4", 1/2", 3/8"	
Blind hollow shaft, AFS60	8, 10, 12, 14, 15 mm, 1/4", 1/2", 3/8", 5/8"	
Shaft material	Stainless steel	
Flange material		
Solid shaft	Aluminum	
Blind hollow shaft, AFM60	Aluminum	
Blind hollow shaft, AFS60	Zinc die cast	
Housing material	Aluminum	

<sup>&</sup>lt;sup>1)</sup> Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

# Ambient data

EMC	(according to EN 61000-6–2 and EN 61000-6-3) $^{\rm 1)}$
Enclosure rating as per IEC 60529	
Protection class housing side with connector outlet	IP 67, with mating connector fitted or sealing caps
Shaft	IP 65
Permissible relative humidity	90% (condensation of optical surfaces not permitted)
Operating temperature range	-40 °C +85 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks (according to EN 60068-2-27)	100 g, 6 ms
Resistance to vibration (according to EN 60068-2-6)	30 g, 10 Hz 2,000 Hz


 $<sup>^{\</sup>mbox{\tiny $1$}}$  The EMC according to the standards quoted is achieved if shielded cables are used.

# Maximum viewing number of resolutions

The maximum singleturn resolution (= 18 bit) can be operated with the maximum operating speed (blind hollow shaft 6,000 rpm and solid shaft 9,000 rpm).

## Ordering information

Type code AFS absolute encoder, singleturn, solid shaft




 $<sup>^{1)}</sup>$  Number of steps programmable via control unit: Type A = 2 to 262144.

### Example orders

Mechanical design	Туре	Part no.
Servo flange, Ø 6 mm, length 10 mm	AFS60A-S1IB262144	1055362
Face mount flange, Ø 10 mm, length 19 mm	AFS60A-S4IB262144	1055364


Type code AFM, multiturn absolute encoder, solid shaft



<sup>1)</sup> Programmable options for resolution via control unit.

## Example orders

Mechanical design	Туре	Part no.
Servo flange, Ø 6 mm, length 10 mm	AFM60A-S1IB018x12	1055331
Face mount flange, Ø 10 mm, length 19 mm	AFM60A-S4IB018x12	1055334




 $<sup>^{1)}</sup>$  Number of steps programmable via control unit: Type A = 2 to 262144.

## Example orders

Mechanical design	Туре	Part no.
Blind hollow shaft, 10 mm	AFS60A-BDIB262144	1055356
Blind hollow shaft, 12 mm	AFS60A-BEIB262144	1055358
Blind hollow shaft 15 mm	AFS60A-BHIB262144	1055360

Type code AFM, multiturn absolute encoder, blind hollow shaft



 $<sup>^{\</sup>scriptscriptstyle (1)}$  Programmable options for resolution via control unit.

### Example orders

Mechanical design	Туре	Part no.
Blind hollow shaft, 10 mm	AFM60A-BDIB018x12	1055325
Blind hollow shaft, 12 mm	AFM60A-BEIB018x12	1055326
Blind hollow shaft 15 mm	AFM60A-BHIB018x12	1055328

## Sales kits

## Sales kit 01

## EtherNet/IP encoder

- + 1 M12 male cable connector, 4-pin, angled, (STE-1204-WE, part number 6048152)
- + 1 M12 female cable connector, 4-pin, angled, (DOS-1204-W, part number 6007303)

	Encoder type (singleturn)	Description	Туре	Part no.
	AFS60A-S1IB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1IB sales kit 01	1057693
	AFS60A-S4IB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4IB sales kit 01	1057718
a Company	AFS60A-BDIB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDIB sales kit 01	1057719
	AFS60A-BEIB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEIB sales kit 01	1057720
	AFS60A-BHIB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHIB sales kit 01	1057721

	Encoder type (multiturn)	Description	Туре	Part no.
	AFM60A-S1IB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1IB sales kit 01	1057722
	AFM60A-S4IB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4IB sales kit 01	1057723
0	AFM60A-BDIB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDIB sales kit 01	1057724
0	AFM60A-BEIB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEIB sales kit 01	1057725
	AFM60A-BHIB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHIB sales kit 01	1057726

# Sales kit 02

## EtherNet/IP encoder

- + 1 M12 male cable connector, 4-pin, angled, pre-wired with 5 m cable (STL-1204-W05ME90, part number 6047913)
- + 1 M12 female cable connector, 4-pin, angled, pre-wired with 5 m cable (DOL-1204-W05MC, part number 6025904)

	Encoder type (singleturn)	Description	Туре	Part no.
a	AFS60A-S1IB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1IB sales kit 02	1057737
	AFS60A-S4IB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4IB sales kit 02	1057738
	AFS60A-BDIB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDIB sales kit 02	1057739
	AFS60A-BEIB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEIB sales kit 02	1057740
	AFS60A-BHIB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHIB sales kit 02	1057741

	Encoder type (multiturn)	Description	Туре	Part no.
	AFM60A-S1IB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1IB sales kit 02	1057742
	AFM60A-S4IB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4IB sales kit 02	1057743
	AFM60A-BDIB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDIB sales kit 02	1057744
11	AFM60A-BEIB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEIB sales kit 02	1057745
	AFM60A-BHIB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHIB sales kit 02	1057746

## Sales kit 03

### EtherNet/IP encoder

- + 2 M12 male cable connectors, 4-pin, angled, (STE-1204-WE, part number 6048152)
- + 1 M12 female cable connector, 4-pin, angled, (DOS-1204-W, part number 6007303)

	Encoder type (singleturn)	Description	Туре	Part no.
	AFS60A-S1IB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1IB sales kit 03	1057727
	AFS60A-S4IB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4IB sales kit 03	1057728
	AFS60A-BDIB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDIB sales kit 03	1057729
	AFS60A-BEIB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEIB sales kit 03	1057730
	AFS60A-BHIB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHIB sales kit 03	1057731

	Encoder type (multiturn)	Description	Туре	Part no.
	AFM60A-S1IB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1IB sales kit 03	1057732
	AFM60A-S4IB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4IB sales kit 03	1057733
a	AFM60A-BDIB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDIB sales kit 03	1057734
	AFM60A-BEIB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEIB sales kit 03	1057735
	AFM60A-BHIB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHIB sales kit 03	1057736

# Sales kit 04

# EtherNet/IP encoder

- + 2 M12 male cable connectors, 4-pin, angled, pre-wired with 5 m cable (STL-1204-W05ME90, part number 6047913)
- +1 M12 female cable connector, 4-pin, angled, pre-wired with 5 m cable (DOL-1204-W05MC, part number 6025904)


	Encoder type (singleturn)	Description	Туре	Part no.
T v	AFS60A-S1IB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1IB sales kit 04	1057747
	AFS60A-S4IB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4IB sales kit 04	1057748
	AFS60A-BDIB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDIB sales kit 04	1057749
	AFS60A-BEIB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEIB sales kit 04	1057750
	AFS60A-BHIB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHIB sales kit 04	1057751

	Encoder type (multiturn)	Description	Туре	Part no.
<b>a</b>	AFM60A-S1IB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1IB sales kit 04	1057752
	AFM60A-S4IB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4IB sales kit 04	1057753
	AFM60A-BDIB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDIB sales kit 04	1057754
	AFM60A-BEIB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEIB sales kit 04	1057755
	AFM60A-BHIB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHIB sales kit 04	1057756

# Dimensional drawings (dimensions in mm)


# Face mount flange

### Round shaft



General tolerances according to DIN ISO 2768-mk


## Flat shaft



General	tolerances	according	to DIN	150 2	768-mk
---------	------------	-----------	--------	-------	--------


Diameter X f7	у
Face mount flange, 10 x 19 mm	9 mm
Face mount flange, 10 x 19 mm, round	-
Face mount flange, 3/8", round	-
Face mount flange, 3/8"	0.35"

# Servo flange




General tolerances according to DIN ISO 2768-mk

Mounting suggestion for small servo clamp (part number 2029166)




General tolerances according to DIN ISO 2768-mk

Mounting suggestion for half-shell servo clamp (part number 2029165)




# Blind hollow shaft




General tolerances according to DIN ISO 2768-mk

# Mounting suggestion



General tolerances according to DIN ISO 2768-mk xj7 = Shaft diameter, on the customer side



Diameter X F7				
AFS60 singleturn absolute encoder	AFM60 multiturn absolute encoder			
Blind hollow shaft 1/4"	Blind hollow shaft 1/4"			
Blind hollow shaft, 8 mm	Blind hollow shaft, 8 mm			
Blind hollow shaft, 3/8"	Blind hollow shaft, 3/8"			
Blind hollow shaft, 10 mm	Blind hollow shaft, 10 mm			
Blind hollow shaft, 12 mm	Blind hollow shaft, 12 mm			
Blind hollow shaft 1/2"	Blind hollow shaft 1/2"			
Blind hollow shaft, 14 mm	Blind hollow shaft, 14 mm			
Blind hollow shaft 15 mm	Blind hollow shaft 15 mm			
Blind hollow shaft, 5/8"				


# PIN assignment

# M12 - 4 x D coding



Port 1				
Signal	T x D+	R x D+	T x D-	R x D-
Pin	1	2	3	4

Port 2				
Signal	T x D+	R x D+	T x D-	R x D-
Pin	1	2	3	4



#### M12 - 4 x A coding



Power supply				
Signal	10 30 V	Not connected	GND	Not connected
Pin	1	2	3	4



# Recommended accessories

# Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
T.	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

# Flanges

# Flange plate

Figure	Brief description	Туре	Part no.
uÇ)	Standard stator coupling	BEF-DS00XFX	2056812
4	Stator coupling, one-sided, 81 mm long with slot	BEF-DS01DFS/VFS	2047428
0	Stator coupling, one-sided, 179 mm long with slot	BEF-DS02DFS/VFS	2047430
• 10	Stator coupling, one-sided, 248 mm long with slots	BEF-DS03DFS/VFS	2047431
	Stator coupling, 16.5 mm high	BEF-DS05XFX	2057423
uÇ)	Stator coupling with hole circle diameter 63 mm	BEF-DS07XFX	2059368
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225



# Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
A	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 500 mm	BEF-MR006050R	2055225
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm	BEF-MR010020R	2055224
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 500 mm	BEF-MR010050R	2055227
	O-ring for measuring wheels (circumference 200 mm)	BEF-0R-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-OR-083-050	2064076

Dimensional drawings → page K-725

# Modular measuring wheel system

Brief description	Туре	Part no.
Measuring wheel system, desired mounting position: left, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-1	2071958
Measuring wheel system, desired mounting position: right, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-2	2071957

Dimensional drawings → page K-725

## Mounting bell

Figure	Brief description	Туре	Part no.
<b>6</b>	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

# Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166



#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
97	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

# Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, –30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
Tames .	Bellows coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-$ 30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10^\circ$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
60	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-10^\circ$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30°C +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
1.0	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^\circ$ +80° C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986



# Connectivity

#### Power supply

	Power supply (A-coded)
Mechanical parameters	
Number of pins	4
Cable diameter	4.7 mm
Minimum bend radius, secured in place	47 mm
Minimum bend radius, movable	47 mm
Maximum length of cable between participants	100 m
Material	
Outer sheath	PUR
Conductor	Bare copper strand
Color of outer sheath	Black RAL 9005
Cable parameters	
AWG	22
Wire cross-section	0.34 mm <sup>2</sup>
Wire colors	Brown, white, blue, black
Conductor resistance	≤ 58 Ω/km
Temperature range	
·	-50 °C +80 °C
Moving	-25 °C +80 °C
Specific features	
Flame resistance	UL horizontal flame test/CSA FT2
Halogen-free state	PUR halogen-free
Microbe resistance	Excellent
Hydrolysis resistance	Excellent

# Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight	2 m	DOL-1204-G02MC	6025900
	Head B: cable	5 m	DOL-1204-G05MC	6025901
	Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded,	10 m	DOL-1204-G10MC	6025902
	4 x 0.34 mm², Ø 4.7 mm	25 m	DOL-1204-G25MC	6034751
Head A: female connector, Head B: cable Cable: for power supply, su 4 x 0.34 mm², Ø 4.7 mm	Hood As formale connector M12. A nin angled	2 m	DOL-1204-W02MC	6025903
	, , , ,	5 m	5 m DOL-1204-W05MC 60	6025904
	Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded,	10 m	DOL-1204-W10MC	6025905
	4 X U.34 Min*, ½ 4.7 Min	25 m DOL-1204-W25MC	6034754	

# M12 round screw system

	Data cable (D-coded)
Mechanical parameters	
Number of pins	4
Cable diameter	6.4 mm
Minimum bend radius, secured in place	26 mm
Minimum bend radius, movable	26 mm
Maximum length of cable between participants	100 m
Material	
Outer sheath	PUR
Conductor	Bare copper strand
Color of outer sheath	Water blue RAL 5021
Electrical parameters	
Transmission properties (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)
Cable parameters	
Cable structure	2 x 2 x AWG26/7 PIMF
Wire cross-section	
	White-green, white-orange
	≤ 150 Ω/km
Shield	Braided tin-plated copper wires
Temperature range	
	-20 °C +80 °C
S .	-20 °C +80 °C
Specific features	A
Flame resistance	According to IEC 60332-1-2
Halogen-free state	According to IEC 60754-1
Oil resistance	According to DIN EN 60811-2-1
Other resistance	Microbe resistance in accordance with VDE 0282 Part 10 Hydrolysis resistance in accordance with DIN 53504
Smoke density	According to IEC 61034
•	

# Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	STL-1204-G02ME90	6045284
The last	Head B: cable Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	5 m	STL-1204-G05ME90	6045285
		10 m	STL-1204-G10ME90	6045286
		2 m	STL-1204-W02ME90	6047912
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: cable Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	5 m	STL-1204-W05ME90	6047913
		10 m	STL-1204-W10ME90	6047914
		25 m	STL-1204-W20ME90	6047915

Dimensional drawings → page K-725

#### Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm Head B: -	DOS-1204-GE	6048153
	Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm $\dots$ 6.5 mm Head B: -	DOS-1204-W	6007303



Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm Head B: -	DOS-1204-WE	6048154

Dimensional drawings → page K-725

#### Other plug connectors and cables

Figure	Brief description	Туре	Part no.
00	Head A: female connector, M12, 4-pin, D-coded Head B: female connector, RJ45, 8-pin Cable: shielded Switch cabinet feedthrough	Feedthrough female connector Ethernet RJ45	6048180

Dimensional drawings → page K-725

#### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, RJ45, 8-pin, straight, shielded, for cable diameter 4.5 mm 8 mm Head B: -	STE-0J08-GE	6048150
0	Head A: male connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1204-GE01	6048151
	Head A: male connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1204-WE	6048152

Dimensional drawings → page K-725

# Connection cables with male and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-1204-G02ME90	6045222
6	Head B: male connector, M12, 4-pin, straight, D-coded	5 m	SSL-1204-G05ME90	6045277
	Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	10 m	SSL-1204-G10ME90	6045279
	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-1204-H02ME90	6047908
6	Head B: male connector, M12, 4-pin, straight, D-coded	5 m	SSL-1204-H05ME90	6047909
	Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	10 m	SSL-1204-H10ME90	6047910
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: male connector, M12, 4-pin, angled, D-coded Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m	SSL-1204-W02ME	6050632
(A) (A)		5 m	SSL-1204-W05ME	6050633
		10 m	SSL-1204-W10ME	6050634
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-2J04-G02ME60	6047916
	Head B: male connector, RJ45, 8-pin, straight	5 m	SSL-2J04-G05ME60	6047917
-		10 m	SSL-2J04-G10ME60	6047918
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: male connector, RJ45, 8-pin, straight Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m	SSL-2J04-H02ME	6047911
0		5 m	SSL-2J04-H05ME	6045287
		10 m	SSL-2J04-H10ME	6045288

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards

# INTELLIGENT, POWERFUL, PRECISE







## **Product description**

Intelligent diagnostic functions and rapid data transfer: High-resolution AFS/ AFM60 PROFINET absolute encoders represent high-precision measurement of absolute position and speed in the area of industrial automation. Comprehensive functions for diagnosing parameters such as temperature or operating time and early error detection increase network reliability. Various configuration options, such as modification of resolution, rotational direction or unit of speed measurement simplify installation and enable customized adjustment to each application. Their compact design makes AFS/AFM60 PROFINET absolute encoders suitable for use even in applications with tight space available. Embedded switch technology ensures maximum system and equipment availability and therefore helps increase productivity

#### At a glance

- · High-resolution 30-bit absolute encoder (18-bit singleturn and 12-bit multiturn)
- Face mount flange, servo flange and blind hollow shaft
- Connection type: 3 x M12 axial male connector
- · PROFINET-IO-RT interface
- Less than 5 ms data update time
- · Round axis functionality
- · Alarms, warnings and diagnostics functions for speed, position, temperature, operating time, etc.
- · Status display via 5 LEDs

#### Your benefits

- · Increased productivity as a result of intelligent diagnostics functions and rapid data transfer
- Increase in network reliability due to early error detection
- Simple installation with various configuration options
- · Flexible, easy setup and high resolutions for various applications with binary, integer and "decimal point" values based on round axis function-
- · Maximum system availability through embedded switch technology
- · Compact and cost-efficient design



#### More information

Fields of application
Detailed technical data
Maximum viewing number of
resolutions
Ordering information
Sales kits
Dimensional drawings
PIN assignment
Recommended accessories G-344

→ www.mvsick.com/en/AFS AFM60 PROFINET

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

· Measurement of absolute position and speed in various machines and systems used in industrial automation as well as production and process technology, for example: warehouse systems, packaging machines, hydraulic presses, printing machines, robots, rotating tables

#### Detailed technical data

#### Performance

Max. number of steps per revolution, AFS60 and AFM60	262,144 (18 bit) (maximum viewing number of resolutions, page G-335)
Max. number of revolutions	
AFM60	4,096 (12 bit)
AFS60	1
Resolution	
AFM60	18 x 12 bit
AFS60	18 bit
Error limits	≤ 0.03°
Repeatability	≤ 0.002°
Measurement increment deviation	± 0.002°
Measuring increment (360 °/ number of steps per revolution)	0.001°
Initialization time	Approx. 12 s

#### Interfaces

Electrical interface	PROFINET
Transfer rate	10/100 MBit/s
Transmission media	CAT 5e cable
Encoder profile	V4.1 Class3
Configuration data	Number of steps per revolution, number of revolutions, PRESET, counting direction, sampling rate for speed monitoring, unit for output of the speed value, round axis functionality (multiturn version only)
Available diagnostic data	Current, minimum and maximum temperature, maximum speed, power-on counter, operating hours counter, power-on/motion, counter of direction changes/number of movements cw/number of movements ccw, maximum operating voltage

#### Electrical data

Power consumption max.	3.0 W
Operating voltage range with reverse polarity protection	10 30 V
Reverse polarity protection	V
MTTFd: mean time to dangerous failure	80 years (EN ISO 13849-1) <sup>1)</sup>

<sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

# Mechanical data

Operating speed 1)	
Solid shaft	9,000 rpm (maximum viewing number of resolutions, page G-335)
Blind hollow shaft	6,000 rpm (maximum viewing number of resolutions, page G-335)
Mass	0.2 kg
Permissible shaft load, solid shaft	80 N (radial); 40 N (axial)
Permissible shaft movement of the drive element, blind hollow shaft	$\pm$ 0.3 / $\pm$ 0.05 mm (radial, static/dynamic) $\pm$ 0.5 / $\pm$ 0.1 mm (axial, static/dynamic)
Rotor moment of inertia	
Solid shaft	≤ 6.2 gcm <sup>2</sup>
Blind hollow shaft	≤ 40 gcm²
Bearing lifetime	3 x 10 <sup>9</sup> revolutions
Start up torque at 20 °C	
Solid shaft	0.5 Ncm
Blind hollow shaft	0.8 Ncm
Operating torque at 20 °C	
Solid shaft	0.3 Ncm
Blind hollow shaft	0.6 Ncm
Max. angular acceleration	$5 \times 10^5 \text{ rad/s}^2$
Shaft diameter	
Face mount flange, solid shaft	10 x 19 mm
Servo flange, solid shaft	6 x 10 mm
Blind hollow shaft, AFM60	8, 10, 12, 14, 15 mm, 1/4", 1/2", 3/8"
Blind hollow shaft, AFS60	8, 10, 12, 14, 15 mm, 1/4", 1/2", 3/8", 5/8"
Shaft material	Stainless steel
Flange material	
Solid shaft	Aluminum
Blind hollow shaft, AFM60	Aluminum
Blind hollow shaft, AFS60	Zinc die cast
Housing material	Aluminum

<sup>1)</sup> Take into account self-heating of 3.3 K per 1,000 revolutions/min when designing the operating temperature range.

# Ambient data

EMC	According to EN 61000-6–2 and EN 61000-6–3 <sup>1)</sup>
Enclosure rating (as per IEC 60529)	IP 65, on the shaft side IP 67, on the housing side <sup>2)</sup>
Permissible relative humidity	90% (condensation of optical surfaces not permitted)
Operating temperature range	-40 °C +85 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks (according to EN 60068-2-27)	100 g/ 6 ms
Resistance to vibration (according to EN 60068-2-6)	30 g/ 10 Hz 2,000 Hz

 $<sup>^{\</sup>mbox{\tiny 1)}}$  The EMC according to the standards quoted is achieved if shielded cables are used.


 $<sup>^{\</sup>mbox{\tiny 2)}}$  When mating connector is inserted.

# Maximum viewing number of resolutions

The maximum singleturn resolution (= 18 bit) can be operated with the maximum operating speed (blind hollow shaft 6,000 rpm and solid shaft 9,000 rpm).

#### Ordering information

Type code AFS absolute encoder, singleturn, solid shaft




<sup>&</sup>lt;sup>1)</sup> Number of steps programmable via control unit: Type A = 2 to 262144.

#### Example orders

Mechanical design	Туре	Part no.
Solid shaft, servo flange, Ø 6 mm, length 10 mm	AFS60A-S1NB262144	1059051
Solid shaft, face mount flange, Ø 10 mm, length 19 mm	AFS60A-S4NB262144	1059050

Type code AFM, multiturn absolute encoder, solid shaft




 $<sup>^{\</sup>mbox{\tiny 1)}}$  Programmable options for resolution via control unit.

#### Example orders

Mechanical design	Туре	Part no.
Solid shaft, servo flange, Ø 6 mm, length 10 mm	AFM60A-S1NB018x12	1059040
Solid shaft, face mount flange, Ø 10 mm, length 19 mm	AFM60A-S4NB018x12	1059039

G

Type code AFS singleturn absolute encoder, solid shaft




<sup>1)</sup> Number of steps programmable via control unit: Type A = 2 to 262144.

#### Example orders

Mechanical design	Туре	Part no.
Blind hollow shaft, Ø 8 mm	AFS60A-BBNB262144	1059049
Blind hollow shaft, Ø 3/8"	AFS60A-BCNB262144	1059048
Blind hollow shaft, Ø 10 mm	AFS60A-BDNB262144	1059047
Blind hollow shaft, Ø 12 mm	AFS60A-BENB262144	1059046
Blind hollow shaft Ø 1/2"	AFS60A-BFNB262144	1059045
Blind hollow shaft, Ø 14 mm	AFS60A-BGNB262144	1059044
Blind hollow shaft, Ø 15 mm	AFS60A-BHNB262144	1059043
Blind hollow shaft, Ø 5/8"	AFS60A-BJNB262144	1059042
Blind hollow shaft Ø 1/4"	AFS60A-BKNB262144	1059041





 $^{\scriptscriptstyle{(1)}}$  Programmable options for resolution via control unit.

#### Example orders

Mechanical design	Туре	Part no.
Blind hollow shaft, Ø 8 mm	AFM60A-BBNB018x12	1059038
Blind hollow shaft, Ø 3/8"	AFM60A-BCNB018x12	1059036
Blind hollow shaft, Ø 10 mm	AFM60A-BDNB018x12	1059035
Blind hollow shaft, Ø 12 mm	AFM60A-BENB018x12	1059034
Blind hollow shaft Ø 1/2"	AFM60A-BFNB018x12	1059033
Blind hollow shaft, Ø 14 mm	AFM60A-BGNB018x12	1059032
Blind hollow shaft, Ø 15 mm	AFM60A-BHNB018x12	1059031
Blind hollow shaft Ø 1/4"	AFM60A-BKNB018x12	1059029



#### Sales kits

#### Sales kit 01

#### PROFINET encoder

- + Female connector, supply voltage, angled (DOS-1204-W, part number. 6007303)
- + Male cable connector, PROFINET signal, angled, (STE-1204-WZ, part number 6048262)

	Encoder type (singleturn)	Description	Туре	Part no.
a Company	AFS60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1NB sales kit 01	1059352
	AFS60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4NB sales kit 01	1059356
	AFS60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDNB sales kit 01	1059357
	AFS60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BENB sales kit 01	1059358
	AFS60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHNB sales kit 01	1059359

	Encoder type (multiturn)	Description	Туре	Part no.
a	AFM60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1NB sales kit 01	1059360
	AFM60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4NB sales kit 01	1059361
	AFM60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFM60A-BDNB sales kit 01	1059362
	AFM60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFM60A-BENB sales kit 01	1059363
	AFM60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFM60A-BHNB sales kit 01	1059364

# Sales kit 02

#### PROFINET encoder

- + Female cable connector, supply voltage, angled, pre-wired with 5 m cable (DOL-1204-W05MC, part number 6025904)
- + Female cable connector, PROFINET signal, angled, pre-wired with 5 m cable (STL-1204-W05MZ90, part number 6048257)

	Encoder type (singleturn)	Description	Туре	Part no.
0	AFS60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1NB sales kit 02	1059365
	AFS60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4NB sales kit 02	1059366
	AFS60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDNB sales kit 02	1059368
	AFS60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BENB sales kit 02	1059369
	AFS60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHNB sales kit 02	1059370

	Encoder type (multiturn)	Description	Туре	Part no.
	AFM60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1NB sales kit 02	1059372
	AFM60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4NB sales kit 02	1059373
	AFM60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFM60A-BDNB sales kit 02	1059375
	AFM60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFM60A-BENB sales kit 02	1059376
	AFM60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFM60A-BHNB sales kit 02	1059377



#### Sales kit 03

#### PROFINET encoder

- + Female connector, supply voltage, angled (DOS-1204-W, part number. 6007303)
- + 2 male cable connectors, PROFINET signal, angled, (STE-1204-WZ, part number 6048262)

	Encoder type (singleturn)	Description	Туре	Part no.
a	AFS60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1NB sales kit 03	1059379
	AFS60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4NB sales kit 03	1059380
	AFS60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDNB sales kit 03	1059381
	AFS60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BENB sales kit 03	1059382
	AFS60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHNB sales kit 03	1059383

	Encoder type (multiturn)	Description	Туре	Part no.
0	AFM60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1NB sales kit 03	1059384
	AFM60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4NB sales kit 03	1059385
	AFM60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFM60A-BDNB sales kit 03	1059386
	AFM60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFM60A-BENB sales kit 03	1059387
	AFM60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFM60A-BHNB sales kit 03	1059388

# Sales kit 04

#### PROFINET encoder


- + Female cable connector, supply voltage, angled, pre-wired with 5 m cable (DOL-1204-W05MC, part number 6025904)
- + 2 female cable connectors, PROFINET signal, angled, pre-wired with 5 m cable (STL-1204-W05MZ90, part number 6048257)

	Encoder type (singleturn)	Description	Туре	Part no.
	AFS60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1NB sales kit 04	1059426
1 40	AFS60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4NB sales kit 04	1059427
	AFS60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDNB sales kit 04	1059428
IIIv	AFS60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BENB sales kit 04	1059429
	AFS60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHNB sales kit 04	1059430

	Encoder type (multiturn)	Description	Туре	Part no.
	AFM60A-S1NB262144	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1NB sales kit 04	1059431
1 49	AFM60A-S4NB262144	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4NB sales kit 04	1059433
	AFM60A-BDNB262144	Blind hollow shaft, Ø 10 mm	AFM60A-BDNB sales kit 04	1059434
111	AFM60A-BENB262144	Blind hollow shaft, Ø 12 mm	AFM60A-BENB sales kit 04	1059437
	AFM60A-BHNB262144	Blind hollow shaft, Ø 15 mm	AFM60A-BHNB sales kit 04	1059439

# Dimensional drawings (dimensions in mm)


#### Face mount flange



General tolerances according to DIN ISO 2768-mk


G

#### Servo flange




General tolerances according to DIN ISO 2768-mk

Mounting suggestion for small servo clamp (part number 2029166)




General tolerances according to DIN ISO 2768-mk

Mounting suggestion for half-shell servo clamp (part number 2029165)






# Mounting suggestion



General tolerances according to DIN ISO 2768-mk  $x_j$ 7 = Shaft diameter, on the customer side



Diameter X F7	
AFS60 singleturn absolute encoder	AFM60 multiturn absolute encoder
Blind hollow shaft 1/4"	Blind hollow shaft 1/4"
Blind hollow shaft, 8 mm	Blind hollow shaft, 8 mm
Blind hollow shaft, 3/8"	Blind hollow shaft, 3/8"
Blind hollow shaft, 10 mm	Blind hollow shaft, 10 mm
Blind hollow shaft, 12 mm	Blind hollow shaft, 12 mm
Blind hollow shaft 1/2"	Blind hollow shaft 1/2"
Blind hollow shaft, 14 mm	Blind hollow shaft, 14 mm
Blind hollow shaft 15 mm	Blind hollow shaft 15 mm

Blind hollow shaft, 5/8"

G


# PIN assignment

# M12 - 4-pin (D-coded)



Port 1				
Signal	T x D+	R x D+	T x D-	R x D-
Pin	1	2	3	4
Wire colors	Yellow	White	Orange	Blue

Port 2				
Signal	T x D+	R x D+	T x D-	R x D-
Pin	1	2	3	4
Wire colors	Yellow	White	Orange	Blue



M12 - 4-pin (A-coded)



Supply voltage						
Signal	U <sub>s</sub> 10 30 V	Not as- signed	GND	Not as- signed		
Pin	1	2	3	4		
Wire colors	Brown	White	Blue	Black		

# Recommended accessories

# Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
<b>(,</b> ]	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

# Flanges

## Flange plate

Figure	Brief description	Туре	Part no.
UÇ	Standard stator coupling	BEF-DS00XFX	2056812
4	Stator coupling, one-sided, 81 mm long with slot	BEF-DS01DFS/VFS	2047428
	Stator coupling, one-sided, 179 mm long with slot	BEF-DS02DFS/VFS	2047430
	Stator coupling, one-sided, 248 mm long with slots	BEF-DS03DFS/VFS	2047431
	Stator coupling, 16.5 mm high	BEF-DS05XFX	2057423
	Stator coupling with hole circle diameter 63 mm	BEF-DS07XFX	2059368
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161



# Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
<b>(a)</b>	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
( ~ )	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm	BEF-MR010020R	2055224
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 500 mm	BEF-MR010050R	2055227
	O-ring for measuring wheels (circumference 200 mm)	BEF-0R-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-OR-083-050	2064076

Dimensional drawings → page K-725

# Modular measuring wheel system

Brief description	Туре	Part no.
Measuring wheel system, desired mounting position: left, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-1	2071958
Measuring wheel system, desired mounting position: right, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-2	2071957

Dimensional drawings → page K-725

# Mounting bell

Figure	Brief description	Туре	Part no.
6	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

#### Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166



#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
-97	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

Dimensional drawings → page K-725

# Shaft adaptation

# Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
Marc.	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10^{\circ}$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
0	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-10^\circ$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30°C +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702

G

-	3	
	7	

Figure	Brief description	Туре	Part no.
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^{\circ}$ $+80^{\circ}$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

# Connectivity

#### Power supply

	Power supply (A-coded)
Mechanical parameters	
Number of pins	4
Cable diameter	4.7 mm
Minimum bend radius, secured in place	47 mm
Minimum bend radius, movable	47 mm
Maximum length of cable between participants	100 m
Material	
Outer sheath	PUR
Conductor	Bare copper strand
Color of outer sheath	Black RAL 9005
Cable parameters	
AWG	22
Wire cross-section	0.34 mm <sup>2</sup>
Wire colors	Brown, white, blue, black
Conductor resistance	≤ 58 Ω/km
Temperature range	
	-50 °C +80 °C
	-25 °C +80 °C
Specific features	
	UL horizontal flame test/CSA FT2
Halogen-free state	
Microbe resistance	
Hydrolysis resistance	Excellent

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded, 4 x 0.34 mm², Ø 4.7 mm	2 m	DOL-1204-G02MC	6025900
		5 m	DOL-1204-G05MC	6025901
100		10 m	DOL-1204-G10MC	6025902
		25 m	DOL-1204-G25MC	6034751
	Head A: female connector, M12, 4-pin, angled Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded, 4 x 0.34 mm², Ø 4.7 mm	2 m	DOL-1204-W02MC	6025903
10		5 m	DOL-1204-W05MC	6025904
		10 m	DOL-1204-W10MC	6025905
		25 m	DOL-1204-W25MC	6034754



	Data cable
Mechanical parameters	
Number of pins	4
Coding type	D-coded
Cable diameter	6.50 mm
Minimum bend radius, secured in place	19.5 mm
Minimum bend radius, movable	45.5 mm
Maximum length of cable between participants	100 m
Material	
Cable material	PVC
Conductor	Tin-plated copper strand
Cable color	Green RAL 6018
Electrical parameters	
Transmission properties (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)
Cable parameters	
Signal type	PROFINET
Cable structure	1x4xAWG22/7; SF/Q
Wire colors	White, yellow, blue, orange
Wire cross-section	0.34 mm <sup>2</sup>
Conductor resistance	≤ 120 Ω/km
Shielding	Braided tin-plated copper wires
Temperature range	
Male connector, pre-wired with cable	
	-25 °C +60 °C
Moving	-5 °C +50 °C
M12 connector	
Ambient temperature (operation)	-40 °C +85 °C
RJ45 connector	
Ambient temperature (operation)	-10 °C +60 °C
Specific features	
Flame resistance	According to IEC 60332-1

# Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 4-pin, straight, D-coded Head B: cable Cable: PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m	STL-1204-G02MZ90	6048247
-		5 m	STL-1204-G05MZ90	6048248
		10 m	STL-1204-G10MZ90	6048249
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: cable Cable: PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m	STL-1204-W02MZ90	6048256
		5 m	STL-1204-W05MZ90	6048257
9		10 m	STL-1204-W10MZ90	6048258
		25 m	STL-1204-W25MZ90	6048259

# Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm	DOS-1204-GZ	6048263
	Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm $\dots$ 6.5 mm Head B: -	DOS-1204-W	6007303
	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm	DOS-1204-WZ	6048264

Dimensional drawings → page K-725

# Other plug connectors and cables

Figure	Brief description	Туре	Part no.
00	Head A: female connector, M12, 4-pin, D-coded Head B: female connector, RJ45, 8-pin Cable: shielded Switch cabinet feedthrough	Feedthrough female connector Ethernet RJ45	6048180

Dimensional drawings → page K-725

#### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, RJ45, 4-pin, straight, shielded, for cable diameter 4.5 mm 8 mm	STE-0J04-GZ	6048260
0	Head A: male connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm	STE-1204-GZ	6048261
	Head A: male connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm	STE-1204-WZ	6048262



#### Connection cables with male and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-1204-F02MZ90	6048250
0	Head B: male connector, M12, 4-pin, straight	5 m	SSL-1204-F05MZ90	6048251
	Cable: PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-1204-F10MZ90	6048252
_	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-1204-G02MZ90	6048241
6	Head B: male connector, M12, 4-pin, straight Cable: PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	5 m	SSL-1204-G05MZ90	6048242
		10 m	SSL-1204-G10MZ90	6048243
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: male connector, M12, 4-pin, angled, D-coded Cable: PUR, halogen-free, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m	SSL-1204-W02MZ	6050635
(A) (A)		5 m	SSL-1204-W05MZ	6050636
		10 m	SSL-1204-W10MZ	6050637
_	Head A: male connector, RJ45, 4-pin, straight, D-coded Head B: male connector, M12, 4-pin, angled	2 m	SSL-2J04-F02MZ	6048253
		5 m	SSL-2J04-F05MZ	6048254
	Cable: PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-2J04-F10MZ	6048255
_	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-2J04-G02MZ60	6048244
	Head B: male connector, RJ45, 4-pin, straight Cable: PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	5 m	SSL-2J04-G05MZ60	6048245
		10 m	SSL-2J04-G10MZ60	6048246

<sup>→</sup> For additional accessories, please see page K-668 onwards

# INTELLIGENT, POWERFUL, PRECISE







# **Product description**

Intelligent diagnostic functions and rapid data transfer: High-resolution AFS/AFM60 EtherCAT® absolute encoders represent high-precision measurement of absolute position and speed in the area of industrial automation. Comprehensive functions for diagnosing parameters such as temperature or operating time and early error detection increase network reliability. Various configuration options, such as modification of resolu-

tion, rotational direction or unit of speed measurement simplify installation and enable customized adjustment to each application. Their compact design also makes AFS/AFM60 EtherCat® absolute encoders suitable for applications in confined spaces. Embedded switch technology ensures maximum system and equipment availability and thus contributes to increased productivity.

#### At a glance

- High-resolution 30-bit absolute encoder (18-bit singleturn and 12-bit multiturn)
- Face mount flange, servo flange and blind hollow shaft
- Connection type: 3 x M12 axial male connector
- On the fly data transmission rate in µs range
- EtherCAT® interface CoE (CiA DS-301)
   Device profile (CiA DS-406)
- Round axis functionality
- Alarms, warnings and diagnostics functions for speed, position, temperature, operating time, etc.
- Status display via 5 LEDs
- Up to 16 adjustable electronic cam switches

#### Your benefits

- Increased productivity as a result of intelligent diagnostics functions and rapid data transfer
- Increase in network reliability due to early error detection
- Simple installation with various configuration options
- Flexible, easy setup and high resolutions for various applications with binary, integer and "decimal point" values based on round axis functionality
- Maximum system availability through embedded switch technology
- · Compact and cost-efficient design



## More information

Fields of application
Detailed technical data
Maximum viewing number of
resolutions
Ordering information
Sales kits
Dimensional drawings
PIN assignment
Recommended accessories G-364

→ www.mysick.com/en/AFS\_AFM60\_EtherCAT

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# G

# Fields of application

 Measurement of absolute position and speed in various machines and systems used in industrial automation as well as production and process technology, for example: warehouse systems, packaging machines, hydraulic presses, printing machines, robots, rotating tables

#### Detailed technical data

#### Performance

Max. number of steps per revolution, AFS60 and AFM60	262,144 (18 bit) (maximum viewing number of resolutions, page G-355)
Max. number of revolutions	
AFM60	4,096 (12 bit)
AFS60	1
Resolution	
AFM60	18 x 12 bit
AFS60	18 bit
Error limits	≤ 0.03°
Repeatability	≤ 0.002°
Measurement increment deviation	≤ 0.002°
Measuring increment (360 °/ number of steps per revolution)	0.001°
Cycle time	250 $\mu s$ to 100 ms $^{1)}$
Initialization time	Approx. 12 s
1) - 500 050 5	

 $<sup>^{1)}</sup>$   $\leq$  500  $\mu$ s to 250 $\mu$ s in Fast Data Exchange mode.

#### Interfaces

Electrical interface	EtherCAT®
Bus interface	EtherCAT, CoE (CiA DS-301) 1)
Encoder profile	CiA DS-406
Transfer rate	10/100 MBit/s
Transmission media	CAT 5e cable
Configuration data	Number of steps per revolution, number of revolutions, PRESET, counting direction, sampling rate for speed monitoring, unit for output of the speed value, round axis functionality (multiturn version only), electronic cams (2 channels x 8 cams), single or multi access mode, fast data exchange mode
Available diagnostic data	Current, minimum and maximum temperature, maximum speed, positioning monitoring, power-on counter, operating hours counter for power-on/motion, counter of direction changes/number of movements cw/number of movements ccw, minimum and maximum operating voltage, signal monitoring for single and multiturn

<sup>&</sup>lt;sup>1)</sup> EtherCAT® is a registered trademark and patented technology licensed by Beckhoff Automation GmbH, Germany.

#### Electrical data

Operating voltage range	10 V DC 30 V DC
Max. power consumption without load	≤ 3 W
Reverse polarity protection	<b>v</b>
MTTFd: mean time to dangerous failure	80 years (EN ISO 13849-1) 1)

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

# Mechanical data

Operating speed 1)		
Solid shaft	9,000 rpm (maximum viewing number of resolutions, page G-355)	
Blind hollow shaft	6,000 rpm (maximum viewing number of resolutions, page G-355)	
Mass	0.2 kg	
Permissible shaft load, solid shaft	80 N (radial); 40 N (axial)	
Permissible shaft movement of the drive element, blind hollow shaft	$\pm$ 0.3 / $\pm$ 0.05 mm (radial, static/dynamic) $\pm$ 0.5 / $\pm$ 0.1 mm (axial, static/dynamic)	
Rotor moment of inertia		
Solid shaft	≤ 6.2 gcm <sup>2</sup>	
Blind hollow shaft	≤ 40 gcm <sup>2</sup>	
Bearing lifetime	3 x 10° revolutions	
Start up torque at 20 °C		
Solid shaft	0.5 Ncm	
Blind hollow shaft	0.8 Ncm	
Operating torque at 20 °C		
Solid shaft	0.3 Ncm	
Blind hollow shaft	0.6 Ncm	
Max. angular acceleration	$5 \times 10^5 \text{ rad/s}^2$	
Shaft diameter		
Face mount flange, solid shaft	10 x 19 mm	
Servo flange, solid shaft	6 x 10 mm	
Blind hollow shaft, AFM60	8, 10, 12, 14, 15 mm, 1/4", 1/2", 3/8"	
Blind hollow shaft, AFS60	8, 10, 12, 14, 15 mm, 1/4", 1/2", 3/8", 5/8"	
Shaft material	Stainless steel	
Flange material		
Solid shaft	Aluminum	
Blind hollow shaft, AFM60	Aluminum	
Blind hollow shaft, AFS60	Zinc die cast	
Housing material	Aluminum	

<sup>1)</sup> Take into account self-heating of 3.3 K per 1,000 revolutions/min when designing the operating temperature range.

# Ambient data

EMC	According to EN 61000-6–2 and EN 61000-6–3 $^{1)}$
Enclosure rating (as per IEC 60529) <sup>2)</sup>	IP 65, on the shaft side IP 67, on the housing side
Permissible relative humidity	90% (condensation of optical surfaces not permitted)
Operating temperature range	-40 °C +85 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks (according to EN 60068-2-27)	100 g, 6 ms
Resistance to vibration (according to EN 60068-2-6)	30 g, 10 Hz 2,000 Hz

 $<sup>^{\</sup>mbox{\tiny $1$}}$  The EMC according to the standards quoted is achieved if shielded cables are used.

 $<sup>^{\</sup>mbox{\tiny 2)}}$  When mating connector is inserted.


# J

#### Maximum viewing number of resolutions

The maximum singleturn resolution (= 18 bit) can be operated with the maximum operating speed (blind hollow shaft 6,000 rpm and solid shaft 9,000 rpm).

#### Ordering information

Type code AFS absolute encoder, singleturn, solid shaft




<sup>&</sup>lt;sup>1)</sup> Number of steps programmable via control unit: Type A = 2 to 262144.

#### Example orders

Mechanical design	Туре	Part no.
Solid shaft, servo flange, Ø 6 mm, length 10 mm	AFS60A-S1EB262144	1059072
Solid shaft, face mount flange, Ø 10 mm, length 19 mm	AFS60A-S4EB262144	1059071

Type code AFM, multiturn absolute encoder, solid shaft




 $<sup>^{\</sup>mbox{\tiny 1)}}$  Programmable options for resolution via control unit.

#### Example orders

Mechanical design	Туре	Part no.
Solid shaft, servo flange, Ø 6 mm, length 10 mm	AFM60A-S1EB018x12	1059061
Solid shaft, face mount flange, Ø 10 mm, length 19 mm	AFM60A-S4EB018x12	1059060

Type code AFS singleturn absolute encoder, solid shaft




 $<sup>^{1)}</sup>$  Number of steps programmable via control unit: Type A = 2 to 262144.

#### Example orders

Mechanical design	Туре	Part no.
Blind hollow shaft, Ø 8 mm	AFS60A-BBEB262144	1059070
Blind hollow shaft, Ø 3/8"	AFS60A-BCEB262144	1059069
Blind hollow shaft, Ø 10 mm	AFS60A-BDEB262144	1059068
Blind hollow shaft, Ø 12 mm	AFS60A-BEEB262144	1059067
Blind hollow shaft Ø 1/2"	AFS60A-BFEB262144	1059066
Blind hollow shaft, Ø 14 mm	AFS60A-BGEB262144	1059065
Blind hollow shaft, Ø 15 mm	AFS60A-BHEB262144	1059064
Blind hollow shaft, Ø 5/8"	AFS60A-BJEB262144	1059063
Blind hollow shaft Ø 1/4"	AFS60A-BKEB262144	1059062

G



 $<sup>^{\</sup>mbox{\tiny 1)}}$  Programmable options for resolution via control unit.

#### Example orders

Mechanical design	Туре	Part no.
Blind hollow shaft, Ø 8 mm	AFM60A-BBEB018x12	1059059
Blind hollow shaft, Ø 3/8"	AFM60A-BCEB018x12	1059058
Blind hollow shaft, Ø 10 mm	AFM60A-BDEB018x12	1059057
Blind hollow shaft, Ø 12 mm	AFM60A-BEEB018x12	1059056
Blind hollow shaft Ø 1/2"	AFM60A-BFEB018x12	1059055
Blind hollow shaft, Ø 14 mm	AFM60A-BGEB018x12	1059054
Blind hollow shaft, Ø 15 mm	AFM60A-BHEB018x12	1059053
Blind hollow shaft Ø 1/4"	AFM60A-BKEB018x12	1059052



#### Sales kits

#### Sales kit 01

#### EtherCAT® encoder

- + Female connector, supply voltage, angled (DOS-1204-W, part number. 6007303)
- + Male cable connector, EtherCAT® signal, angled, (STE-1204-WZ, part number 6048262)

	Encoder type (singleturn)	Description	Туре	Part no.
	AFS60A-S1EB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1EB sales kit 01	1060469
	AFS60A-S4EB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4EB sales kit 01	1060470
0	AFS60A-BDEB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDEB sales kit 01	1060471
	AFS60A-BEEB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEEB sales kit 01	1060472
	AFS60A-BHEB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHEB sales kit 01	1060473

	Encoder type (multiturn)	Description	Туре	Part no.
	AFM60A-S1EB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1EB sales kit 01	1060474
	AFM60A-S4EB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4EB sales kit 01	1060475
0	AFM60A-BDEB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDEB sales kit 01	1060476
0	AFM60A-BEEB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEEB sales kit 01	1060477
	AFM60A-BHEB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHEB sales kit 01	1060478

# Sales kit 02

# EtherCAT® encoder

- + Female cable connector, supply voltage, angled, pre-wired with 5 m cable (DOL-1204-W05MC, part number 6025904)
- + Female cable connector, EtherCAT® signal, angled, pre-wired with 5 m cable (STL-1204-W05MZ90, part number 6048257)

	Encoder type (singleturn)	Description	Туре	Part no.
	AFS60A-S1EB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1EB sales kit 02	1060479
	AFS60A-S4EB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4EB sales kit 02	1060480
	AFS60A-BDEB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDEB sales kit 02	1060481
	AFS60A-BEEB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEEB sales kit 02	1060482
	AFS60A-BHEB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHEB sales kit 02	1060483

	Encoder type (multiturn)	Description	Туре	Part no.
a	AFM60A-S1EB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1EB sales kit 02	1060484
	AFM60A-S4EB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4EB sales kit 02	1060485
	AFM60A-BDEB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDEB sales kit 02	1060486
	AFM60A-BEEB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEEB sales kit 02	1060487
	AFM60A-BHEB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHEB sales kit 02	1060488



# Sales kit 03

#### EtherCAT® encoder

- + Female connector, supply voltage, angled (DOS-1204-W, part number. 6007303)
- + 2 male cable connectors, EtherCAT® signal, angled, (STE-1204-WZ, part number 6048262)

	Encoder type (singleturn)	Description	Туре	Part no.
a	AFS60A-S1EB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1EB sales kit 03	1060489
	AFS60A-S4EB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4EB sales kit 03	1060490
	AFS60A-BDEB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDEB sales kit 03	1060491
	AFS60A-BEEB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEEB sales kit 03	1060492
	AFS60A-BHEB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHEB sales kit 03	1060493

	Encoder type (multiturn)	Description	Туре	Part no.
0	AFM60A-S1EB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1EB sales kit 03	1060495
	AFM60A-S4EB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4EB sales kit 03	1060496
	AFM60A-BDEB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDEB sales kit 03	1060497
	AFM60A-BEEB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEEB sales kit 03	1060498
	AFM60A-BHEB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHEB sales kit 03	1060499

# Sales kit 04

# EtherCAT® encoder


- + Female cable connector, supply voltage, angled, pre-wired with 5 m cable (DOL-1204-W05MC, part number 6025904)
- + 2 female cable connectors, EtherCAT® signal, angled, pre-wired with 5 m cable (STL-1204-W05MZ90, part number 6048257)

	Encoder type (singleturn)	Description	Туре	Part no.
1 v	AFS60A-S1EB262144	Solid shaft, servo flange, 6 x 10 mm	AFS60A-S1EB sales kit 04	1060500
	AFS60A-S4EB262144	Solid shaft, face mount flange, 10 x 19 mm	AFS60A-S4EB sales kit 04	1060501
	AFS60A-BDEB262144	Blind hollow shaft, Ø 10 mm	AFS60A-BDEB sales kit 04	1060502
	AFS60A-BEEB262144	Blind hollow shaft, Ø 12 mm	AFS60A-BEEB sales kit 04	1060503
	AFS60A-BHEB262144	Blind hollow shaft, Ø 15 mm	AFS60A-BHEB sales kit 04	1060504

	Encoder type (multiturn)	Description	Туре	Part no.
1	AFM60A-S1EB018x12	Solid shaft, servo flange, 6 x 10 mm	AFM60A-S1EB sales kit 04	1060505
	AFM60A-S4EB018x12	Solid shaft, face mount flange, 10 x 19 mm	AFM60A-S4EB sales kit 04	1060506
	AFM60A-BDEB018x12	Blind hollow shaft, Ø 10 mm	AFM60A-BDEB sales kit 04	1060507
	AFM60A-BEEB018x12	Blind hollow shaft, Ø 12 mm	AFM60A-BEEB sales kit 04	1060508
	AFM60A-BHEB018x12	Blind hollow shaft, Ø 15 mm	AFM60A-BHEB sales kit 04	1060509

## Dimensional drawings (dimensions in mm)


#### Face mount flange



General tolerances according to DIN ISO 2768-mk


G

#### Servo flange




General tolerances according to DIN ISO 2768-mk

Mounting suggestion for small servo clamp (part number 2029166)




General tolerances according to DIN ISO 2768-mk

Mounting suggestion for half-shell servo clamp (part number 2029165)




#### Blind hollow shaft




General tolerances according to DIN ISO 2768-mk

## Mounting suggestion



General tolerances according to DIN ISO 2768-mk  $x_j$ 7 = Shaft diameter, on the customer side



Diameter X F7	
AFS60 singleturn absolute encoder	AFM60 multiturn absolute encoder
Blind hollow shaft 1/4"	Blind hollow shaft 1/4"
Blind hollow shaft, 8 mm	Blind hollow shaft, 8 mm
Blind hollow shaft, 3/8"	Blind hollow shaft, 3/8"
Blind hollow shaft, 10 mm	Blind hollow shaft, 10 mm
Blind hollow shaft, 12 mm	Blind hollow shaft, 12 mm
Blind hollow shaft 1/2"	Blind hollow shaft 1/2"
Blind hollow shaft, 14 mm	Blind hollow shaft, 14 mm
Blind hollow shaft 15 mm	Blind hollow shaft 15 mm
Blind hollow shaft, 5/8"	

G


## PIN assignment

## M12 - 4-pin (D-coded)



Port 1				
Signal	T x D+	R x D+	T x D-	R x D-
Pin	1	2	3	4
Wire colors	Yellow	White	Orange	Blue

Port 2					
Signal	T x D+	R x D+	T x D-	R x D-	
Pin	1	2	3	4	
Wire colors	Yellow	White	Orange	Blue	



M12 - 4-pin (A-coded)



Supply voltage					
Signal	U <sub>s</sub> 10 30 V	Not as- signed	GND	Not as- signed	
Pin	1	2	3	4	
Wire colors	Brown	White	Blue	Black	

## Recommended accessories

## Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
<b>(,</b> ]	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

## Flanges

## Flange plate

Figure	Brief description	Туре	Part no.
uÇ)	Standard stator coupling	BEF-DS00XFX	2056812
	Stator coupling, one-sided, 81 mm long with slot	BEF-DS01DFS/VFS	2047428
	Stator coupling, one-sided, 179 mm long with slot	BEF-DS02DFS/VFS	2047430
.10	Stator coupling, one-sided, 248 mm long with slots	BEF-DS03DFS/VFS	2047431
	Stator coupling, 16.5 mm high	BEF-DS05XFX	2057423
	Stator coupling with hole circle diameter 63 mm	BEF-DS07XFX	2059368
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161



## Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
( ~ )	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm	BEF-MR010020R	2055224
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 500 mm	BEF-MR010050R	2055227
	O-ring for measuring wheels (circumference 200 mm)	BEF-0R-053-040	2064061
	O-ring for measuring wheels (circumference 300 mm)	BEF-0R-083-050	2064076

Dimensional drawings → page K-725

## Modular measuring wheel system

Brief description	Туре	Part no.
Measuring wheel system, desired mounting position: left, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-1	2071958
Measuring wheel system, desired mounting position: right, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-2	2071957

Dimensional drawings → page K-725

## Mounting bell

Figure	Brief description	Туре	Part no.
6	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

### Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166



#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
97	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

Dimensional drawings → page K-725

## Shaft adaptation

## Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, –30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
il.	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10^{\circ}$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-10^\circ$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30°C +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
10	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30°C +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, –30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702

G

1	
	7

Figure	Brief description	Туре	Part no.
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^{\circ}$ $+80^{\circ}$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

## Connectivity

#### Power supply

	Power supply (A-coded)
Mechanical parameters	
Number of pins	4
Cable diameter	4.7 mm
Minimum bend radius, secured in place	47 mm
Minimum bend radius, movable	47 mm
Maximum length of cable between participants	100 m
Material	
Outer sheath	PUR
Conductor	Bare copper strand
Color of outer sheath	Black RAL 9005
Cable parameters	
AWG	22
Wire cross-section	0.34 mm <sup>2</sup>
Wire colors	Brown, white, blue, black
Conductor resistance	≤ 58 Ω/km
Temperature range	
Fixed in place	-50 °C +80 °C
Moving	-25 °C +80 °C
Specific features	
Flame resistance	UL horizontal flame test/CSA FT2
Halogen-free state	PUR halogen-free
Microbe resistance	Excellent
Hydrolysis resistance	Excellent

## Plug connectors and cables

## Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight	2 m	DOL-1204-G02MC	6025900
	Head B: cable	5 m	DOL-1204-G05MC	6025901
	Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded, 4 x 0.34 mm², Ø 4.7 mm	10 m	DOL-1204-G10MC	6025902
4		25 m	DOL-1204-G25MC	6034751
	Head A: female connector, M12, 4-pin, angled Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded,	2 m	DOL-1204-W02MC	6025903
		5 m	DOL-1204-W05MC	6025904
		10 m	DOL-1204-W10MC	6025905
	4 x 0.34 mm², Ø 4.7 mm	25 m	DOL-1204-W25MC	6034754



	Data cable
Mechanical parameters	
Number of pins	4
Coding type	D-coded D-coded
Cable diameter	6.50 mm
Minimum bend radius, secured in place	19.5 mm
Minimum bend radius, movable	45.5 mm
Maximum length of cable between participants	100 m
Material	
Cable material	PVC
Conductor	Tin-plated copper strand
Cable color	Green RAL 6018
Electrical parameters	
Transmission properties (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)
Cable parameters	
Signal type	EtherCAT®
Cable structure	1x4xAWG22/7; SF/Q
Wire colors	White, yellow, blue, orange
Wire cross-section	0.34 mm <sup>2</sup>
Conductor resistance	≤ 120 Ω/km
Shielding	Braided tin-plated copper wires
Temperature range	
Male connector, pre-wired with cable	
	-25 °C +60 °C
	−5 °C +50 °C
M12 connector	
Ambient temperature (operation)	-40 °C +85 °C
RJ45 connector	
Ambient temperature (operation)	-10 °C +60 °C
Specific features	
Flame resistance	According to IEC 60332-1

## Connecting cables with male connector

Figure	Brief description		Туре	Part no.
_	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	STL-1204-G02MZ90	6048247
	Head B: cable	5 m	STL-1204-G05MZ90	6048248
C	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	STL-1204-G10MZ90	6048249
Head B: cable	Head A: male connector, M12, 4-pin, angled, D-coded Head B: cable Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m	STL-1204-W02MZ90	6048256
		5 m	STL-1204-W05MZ90	6048257
		10 m	STL-1204-W10MZ90	6048258
		25 m	STL-1204-W25MZ90	6048259

## Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm	DOS-1204-GZ	6048263
	Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm $\dots$ 6.5 mm Head B: -	DOS-1204-W	6007303
	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm	DOS-1204-WZ	6048264

Dimensional drawings → page K-725

## Other plug connectors and cables

Figure	Brief description	Туре	Part no.
00	Head A: female connector, M12, 4-pin, D-coded Head B: female connector, RJ45, 8-pin Cable: Ethernet, EtherCAT, shielded Switch cabinet feedthrough	Feedthrough female connector Ethernet RJ45	6048180

Dimensional drawings → page K-725

#### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, RJ45, 4-pin, straight, shielded, for cable diameter 4.5 mm 8 mm	STE-0J04-GZ	6048260
Co	Head A: male connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm	STE-1204-GZ	6048261
	Head A: male connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1204-WE	6048262



#### Connection cables with male and male connector

Figure	Brief description		Туре	Part no.
_	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-1204-F02MZ90	6048250
0	Head B: male connector, M12, 4-pin, straight	5 m	SSL-1204-F05MZ90	6048251
War-	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	10 m	SSL-1204-F10MZ90	6048252
_	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-1204-G02MZ90	6048241
6	Head B: male connector, M12, 4-pin, straight	5 m	SSL-1204-G05MZ90	6048242
6	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	10 m	SSL-1204-G10MZ90	6048243
	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-1204-W02MZ	6050635
(a) (a)	Head B: male connector, M12, 4-pin, angled, D-coded Cable: PROFINET, EtherCAT, PUR, halogen-free, shielded, 4 x 0.34 mm², Ø 6.5 mm	5 m	SSL-1204-W05MZ	6050636
		10 m	SSL-1204-W10MZ	6050637
_	Head A: male connector, RJ45, 4-pin, straight, D-coded	2 m	SSL-2J04-F02MZ	6048253
	Head B: male connector, M12, 4-pin, angled	5 m	SSL-2J04-F05MZ	6048254
<b>4</b>	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-2J04-F10MZ	6048255
_	Head A: male connector, M12, 4-pin, straight, D-coded Head B: male connector, RJ45, 4-pin, straight Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m	SSL-2J04-G02MZ60	6048244
		5 m	SSL-2J04-G05MZ60	6048245
		10 m	SSL-2J04-G10MZ60	6048246

<sup>→</sup> For additional accessories, please see page K-668 onwards

# COMPACT, RUGGED, POWERFUL





## **Product description**

The A3M60 PROFIBUS is an extremely rugged absolute multiturn encoder with a 60 mm housing. Maximum reliability even in the harshest of ambient conditions is attained by means of magnetic scanning, both with singleturn and multiturn detection. New singleturn technology combines the durability of a magnetic sensor with high resolutions, previously only possible with optical systems. The innovative gearless multiturn technology keeps the number of moving compo-

nents on the A3M60 to a minimum. This results in a longer service life with low maintenance costs and consequently, optimum system availability. The highly compact technology in single and multiturn detection provides the user a space-saving and cost-efficient solution. Together with the integrated PROFIBUS interface, the A3M60 is particularly suited for applications where installation space is tight

#### At a glance

- Rugged absolute multiturn encoder with up to 31 bits (14-bit singleturn and 17-bit multiturn)
- Face mount flange, servo flange or blind hollow shaft
- Compact design (<70 mm)
- Integrated PROFIBUS interface with DP V0, V1, and V2 functionality (depending on type)
- Connectivity: 3 x M12 male connectors
- Protection class up to IP67
- Operating temperature: -30 to +80 °C (depending on type)

#### Your benefits

- Maximum system availability, even under extreme ambient conditions
- Reduced maintenance costs due to wear-free magnetic singleturn and multiturn scanning
- Space-saving and cost-efficient design
   the best solution, particularly when
   installation space is limited
- High productivity thanks to fast communication and position calculation
- Immune to contamination and condensation – ideal for tough ambient conditions
- High performance at a cost-efficient price



#### More information

Fields of application
Detailed technical data
Type code
Ordering information
Sales kits
Dimensional drawings
PIN assignment
Recommended accessories G-380

→ www.mysick.com/en/A3M60\_PR0FIBUS

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

 Measurement of absolute position in various machines and systems such as pallet handling machines, high-bay warehouses, cranes, presses, printing machines

#### Detailed technical data

#### Performance

	Basic	Advanced
Max. number of steps per revolution	8,192	16,384
Max. number of revolutions	8,192	131,072
Resolution	13 bit x 13 bit	14 bit x 17 bit
Error limits	± 0.5°, (at room temperature)	± 0.35°, (at room temperature)
Repeatability	± 0.25°, at room temperature	$\pm~0.15^{\circ}$ , at room temperature
Measuring step (360 °/ number of steps per revolution)	0.022°	
Initialization time	Approx. 1 s 1)	

<sup>1)</sup> Corresponds to the amount of time that passes after connecting the supply voltage until the data word can be read in correctly.

#### Interfaces

	Basic	Advanced
Electrical interface	PROFIBUS DP	
Bus interface	PROFIBUS (RS485)	
Data protocol	PROFIBUS DP VO	PROFIBUS DP V0 and DP V1 + V2
Data transmission rate (baud rate)	≤ 12 MBaud	
Bus termination	Through DIP switch or external resistor	
Status information	Through status LEDs	
SET (electronic adjustment)	Via PRESET pushbutton or protocol	
Configuration data	Number of steps per revolution, number of revolutions, PRESET, counting direction	Number of steps per revolution, number of revolutions, PRESET, counting direction, sampling rate for calculating position, unit for output of the speed value, round axis functionality
Available diagnostic data	-	Maximum speed, power-on counter, operating hours counter power-on/motion, counter of direction changes/number of movements cw/number of movements

#### Electrical data

Operating voltage range	10 V 32 V
Power consumption max.	1.5 W
Reverse polarity protection	<b>v</b>
MTTFd: mean time to dangerous failure	60 years (EN ISO 13849-1) 1)

<sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

## Mechanical data

	Basic	Advanced
Shaft diameter		
Face mount flange	10 x 19 mm	
Servo flange	6 x 10 mm	
Blind hollow shaft	8, 10, 12, 14, 15 mm and 3/8", 1/2", 5/8"	
Shaft material	Stainless steel	

G

Flange material	Aluminum	
Housing material	Aluminum	
Mass		
Face mount flange, servo flange	0.28 kg	
Blind hollow shaft	0.28 kg	
Start up torque at 20 °C		
Face mount flange, servo flange	1 Ncm with shaft seal	
Blind hollow shaft	1 Ncm	2 Ncm
Operating torque at 20 °C		
Face mount flange, servo flange	0.8 Ncm	0.8 Ncm
Blind hollow shaft	0.8 Ncm	1.6 Ncm
Permissible shaft loading		
Face mount flange, servo flange	80 N radial 40 N axial	
Permissible shaft movement of the drive element, static/dynamic		
Blind hollow shaft	$\pm$ 0.3/ $\pm$ 0.1 mm radial $\pm$ 0.5/ $\pm$ 0.2 mm axial	
Max. angular acceleration	≤ 500,000 rad/s²	
Operating speed		
Face mount flange, servo flange	6,000 rpm	9,000 rpm
Blind hollow shaft	6,000 rpm	9,000 rpm
Self-warming at maximum speed		
Face mount flange	30k	30k
Servo flange	15k	25k
Blind hollow shaft	45k	35k
Rotor moment of inertia		
Face mount flange, servo flange	11.4 gcm <sup>2</sup>	
Blind hollow shaft	20.8 gcm <sup>2</sup>	
Bearing lifetime	3 x 10 <sup>9</sup> revolutions	

## Ambient data

	Basic	Advanced
EMC	According to EN 61000-6-2 and EN 61000-6-3	
Enclosure rating (as per IEC 60529) 1)	IP 67, housing IP 65, shaft	IP 67, housing IP 67, shaft
Permissible relative humidity	95% (condensation not permitted)	
Operating temperature range	-10 °C +70 °C	-30 °C +80 °C
Storage temperature range	-40 °C +100 °C	
Resistance to shocks (according to EN 60068-2-27)	100 g/6 ms	
Resistance to vibration (according to EN 60068-2-6)	30 g/10 Hz 2,000 Hz	

<sup>1)</sup> When mating connector is inserted.

## Ordering information

Mechanical design/shaft diameter	Resolution	Туре	Part no.
Solid shaft, face mount flange, Ø 10 mm, length 19 mm	8,192 x 8,192	A3M60B-S4PB013X13	1038826
Solid shaft, servo flange, Ø 6 mm, length 10 mm	8,192 x 8,192	A3M60B-S1PB013X13	1051018
Blind hollow shaft / 8 mm	8,192 x 8,192	A3M60B-BBPB013X13	1051016
Blind hollow shaft, / 10 mm	8,192 x 8,192	A3M60B-BDPB013X13	1038824
Blind hollow shaft, / 12 mm	8,192 x 8,192	A3M60B-BEPB013X13	1038825
Blind hollow shaft / 15 mm	8,192 x 8,192	A3M60B-BHPB013X13	1051017
Blind hollow shaft / 3/8"	8,192 x 8,192	A3M60B-BCPB013X13	1053327
Blind hollow shaft / 1/2"	8,192 x 8,192	A3M60B-BFPB013X13	1053328
Blind hollow shaft / 14 mm	8,192 x 8,192	A3M60B-BGPB013X13	1051325
Blind hollow shaft / 5/8"	8,192 x 8,192	A3M60B-BJPB013X13	1053329
Solid shaft, face mount flange, Ø 10 mm, length 19 mm	16,384 x 131,072	A3M60A-S4PB014X17	1053341
Solid shaft, servo flange, Ø 6 mm, length 10 mm	16,384 x 131,072	A3M60A-S1PB014X17	1053342
Blind hollow shaft / 8 mm	16,384 x 131,072	A3M60A-BBPB014X17	1053330
Blind hollow shaft / 3/8"	16,384 x 131,072	A3M60A-BCPB014X17	1053334
Blind hollow shaft / 10 mm	16,384 x 131,072	A3M60A-BDPB014X17	1053331
Blind hollow shaft / 12 mm	16,384 x 131,072	A3M60A-BEPB014X17	1053332
Blind hollow shaft / 1/2"	16,384 x 131,072	A3M60A-BFPB014X17	1053335
Blind hollow shaft / 14 mm	16,384 x 131,072	A3M60A-BGPB014X17	1053336
Blind hollow shaft / 15 mm	16,384 x 131,072	A3M60A-BHPB014X17	1053333
Blind hollow shaft / 5/8"	16,384 x 131,072	A3M60A-BJPB014X17	1053337

 $<sup>^{1)}</sup>$  Number of steps programmable via control unit: Type A = 2 to 262144.

#### Sales kits

#### Sales kit 01

#### A3M60 PROFIBUS

- + M12 female cable connector, 4-pin, angled, (DOS-1204-W, part number 6007303)
- + PROFIBUS IN: M12 female cable connector, 5-pin, angled, shielded (DOS-1205-WQ, part number 6041429)

	Encoder type (singleturn)	Description	Туре	Part no.
	A3M60B-S4PB013x13	Solid shaft, face mount flange, 10 x 19 mm	A3M60B-S4P sales kit 01	1052488
	A3M60B-S1PB013x13	Solid shaft, servo flange, 6 x 10 mm	A3M60B-S1P sales kit 01	1052489
	A3M60B-BBPB013x13	Blind hollow shaft, Ø 8 mm	A3M60B-BBP sales kit 01	1052477
CC	A3M60B-BDPB013x13	Blind hollow shaft, Ø 10 mm	A3M60B-BDP sales kit 01	1052478
<b>•</b> (g)	A3M60B-BEPB013x13	Blind hollow shaft, Ø 12 mm	A3M60B-BEP sales kit 01	1052479
	A3M60B-BHPB013x13	Blind hollow shaft, Ø 15 mm	A3M60B-BHP sales kit 01	1052486
	A3M60B-BGPB013x13	Blind hollow shaft, Ø 14 mm	A3M60B-BGP sales kit 01	1053975

## Sales kit 02

#### A3M60 PROFIBUS

- + M12 female cable connector, 5-pin, angled, (DOL-1202-W05MC, part number 6042067)
- + PROFIBUS IN: M12 female cable connector, 5-pin, angled (DOL-1205-W05MQ, part number 6041423)

	Encoder type (singleturn)	Description	Туре	Part no.
	A3M60B-S4PB013x13	Solid shaft, face mount flange, 10 x 19 mm	A3M60B-S4P sales kit 02	1052492
	A3M60B-S1PB013x13	Solid shaft, servo flange, 6 x 10 mm	A3M60B-S1P sales kit 02	1052506
	A3M60B-BBPB013x13	Blind hollow shaft, Ø 8 mm	A3M60B-BBP sales kit 02	1052490
6	A3M60B-BDPB013x13	Blind hollow shaft, Ø 10 mm	A3M60B-BDP sales kit 02	1052491
T T	A3M60B-BEPB013x13	Blind hollow shaft, Ø 12 mm	A3M60B-BEP sales kit 02	1052493
	A3M60B-BHPB013x13	Blind hollow shaft, Ø 15 mm	A3M60B-BHP sales kit 02	1052494
	A3M60B-BGPB013x13	Blind hollow shaft, Ø 14 mm	A3M60B-BGP sales kit 02	1053976

G

#### Sales kit 03

#### A3M60 PROFIBUS

- + M12 female cable connector, 4-pin, angled, (DOS-1204-W, part number 6007303)
- + PROFIBUS IN: M12 female cable connector, 5-pin, angled, shielded, B-coded (DOS-1205-WQ, part number 6041429)
- + PROFIBUS OUT: M12 male cable connector, 5-pin, angled (STE-1205-WQ, part number 6041428)

	Encoder type (singleturn)	Description	Туре	Part no.
	A3M60B-S4PB013x13	Solid shaft, face mount flange, 10 x 19 mm	A3M60B-S4P sales kit 03	1052513
	A3M60B-S1PB013x13	Solid shaft, servo flange, 6 x 10 mm	A3M60B-S1P sales kit 03	1052514
	A3M60B-BBPB013x13	Blind hollow shaft, Ø 8 mm	A3M60B-BBP sales kit 03	1052507
	A3M60B-BDPB013x13	Blind hollow shaft, Ø 10 mm	A3M60B-BDP sales kit 03	1052508
<b>=</b> 0	A3M60B-BEPB013x13	Blind hollow shaft, Ø 12 mm	A3M60B-BEP sales kit 03	1052509
	A3M60B-BHPB013x13	Blind hollow shaft, Ø 15 mm	A3M60B-BHP sales kit 03	1052510
	A3M60B-BGPB013x13	Blind hollow shaft, Ø 14 mm	A3M60B-BGP sales kit 03	1053977

#### Sales kit 04


#### A3M60 PROFIBUS

- + M12 female cable connector, 5-pin, angled, (DOL-1202-W05MC, part number 6042067)
- + PROFIBUS IN: M12 female cable connector, 5-pin, angled (DOL-1205-W05MQ, part number 6041423)
- + PROFIBUS OUT: M12 male cable connector, 5-pin, angled (STL-1205-W05MQ, part number 6041426)

	Encoder type (singleturn)	Description	Туре	Part no.
	A3M60B-S4PB013x13	Solid shaft, face mount flange, 10 x 19 mm	A3M60B-S4P sales kit 04	1052519
	A3M60B-S1PB013x13	Solid shaft, servo flange, 6 x 10 mm	A3M60B-S1P sales kit 04	1052520
	A3M60B-BBPB013x13	Blind hollow shaft, Ø 8 mm	A3M60B-BBP sales kit 04	1052515
(G)	A3M60B-BDPB013x13	Blind hollow shaft, Ø 10 mm	A3M60B-BDP sales kit 04	1052516
TIT	A3M60B-BEPB013x13	Blind hollow shaft, Ø 12 mm	A3M60B-BEP sales kit 04	1052517
	A3M60B-BHPB013x13	Blind hollow shaft, Ø 15 mm	A3M60B-BHP sales kit 04	1052518
	A3M60B-BGPB013x13	Blind hollow shaft, Ø 14 mm	A3M60B-BGP sales kit 04	1053978


## Dimensional drawings (dimensions in mm)

#### Face mount flange




General tolerances according to DIN ISO 2768-mk

#### Servo flange



General tolerances according to DIN ISO 2768-mk

#### Blind hollow shaft



General tolerances according to DIN ISO 2768-mk

XF7 = Encoder shaft diameter, see type code


xj7 = Shaft diameter, on the customer side

## PIN assignment



PROFIBUS IN

## PROFIBUS IN




PIN	Explanation
1	Not assigned
2	PROFIBUS Data A
3	Not assigned
4	PROFIBUS Data B
5	Screen

#### WARNING: Connect screen to housing.

## **PROFIBUS OUT**

5-pin B-coded




PIN	Explanation
1	+5 V (2P5) <sup>1)</sup>
2	PROFIBUS Data A
3	0 V (2M) <sup>1)</sup>
4	PROFIBUS Data B
5	Screen

 $<sup>^{\</sup>mbox{\tiny 1)}}$  For external bus termination.

#### WARNING: Connect screen to housing.

## Supply voltage



PIN	Explanation
1	Operating voltage
2	Do not connect
3	Ground (0 V)
4	Do not connect
5	Not assigned

## Recommended accessories

## Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
()	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

#### Flanges

## Flange plate



Figure	Brief description	Туре	Part no.
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225
(1)	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161

## Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
<b>(a)</b>	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278

Dimensional drawings → page K-725

## Mounting bell

Figure	Brief description	Туре	Part no.
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

## Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

Dimensional drawings → page K-725

#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
9)	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

## Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
(Time-	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, $-30^{\circ}$ C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial ± 0.25 mm, axial ± 0.4 mm, angular ± 4°; max. revolutions 10,000 rpm, -30° C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10^\circ$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-10^\circ$ C +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, -30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, -30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ °C +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^{\circ}$ $+80^{\circ}$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986



## Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M12, 5-pin, angled	5 m	DOL-1202-W05MC	6042067
	Head B: cable Cable: for power supply, PUR, halogen-free, shielded, 3 x 0.34 mm², Ø 4.2 mm	10 m	DOL-1202-W10MC	6042068
	Head A: female connector, M12, 5-pin, straight	5 m	DOL-1205-G05MAC	6036384
	Head B: cable  Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded,	10 m	DOL-1205-G10MAC	6036385
W	5 x 0.34 mm <sup>2</sup> , Ø 5.9 mm	20 m	DOL-1205-G20MAC	6036386
	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm	5 m	DOL-1205-G05MQ	6026006
		10 m	DOL-1205-G10MQ	6026008
		12 m	DOL-1205-G12MQ	6032636
		15 m	DOL-1205-G15MQ	6032637
		20 m	DOL-1205-G20MQ	6032638
		30 m	DOL-1205-G30MQ	6032639
		50 m	DOL-1205-G50MQ	6032861
	Head A: female connector, M12, 5-pin, angled, B-coded	5 m	DOL-1205-W05MQ	6041423
	Head B: cable  Cable: suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm	10 m	DOL-1205-W10MQ	6041425

Dimensional drawings → page K-725

## Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded Head B: cable	5 m	STL-1205-G05MQ	6026005
	Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm Wire shielding: AL-PT foil, total shield, tin-plated C shield	10 m	STL-1205-G10MQ	6026007
A) 6		12 m	STL-1205-G12MQ	6032635
11	Head A: male connector, M12, 5-pin, angled, B-coded Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm	5 m	STL-1205-W05MQ	6041426
		10 m	STL-1205-W10MQ	6041427

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -	DOS-1204-G	6007302
	Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm $\dots$ 6.5 mm Head B: -	DOS-1204-W	6007303
	Head A: female connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -	DOS-1205-GQ	6021353
	Head A: female connector, M12, 5-pin, angled, B-coded, shielded, for cable diameter 4 mm 8 mm Head B: -	DOS-1205-WQ	6041429

Dimensional drawings → page K-725

## Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm	By the meter	LTG-2102-MW	6021355

## Other plug connectors and cables

Figure	Brief description	Туре	Part no.
	A3M60 accessories sales set comprising: Female cable connector supply voltage M12 angled (6007303) Female cable connector M12 angled (6041429) Male cable connector M12 angled (6041428)	DOS-3XM12-W	2058177
	Head A: male connector, M12, 4-pin, straight, B-coded Cable: terminator	STE-END-Q	6021156

Dimensional drawings → page K-725

## Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -	STE-1205-GQ	6021354
	Head A: male connector, M12, 5-pin, angled, B-coded, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1205-WQ	6041428

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards

G

## RELIABLE, ESTABLISHED, AND MODULAR





### **Product description**

The ATM60 PROFIBUS absolute multiturn encoder from SICK provides reliable positional and speed information even in harsh ambient conditions, with a resolution of up to 26 bits. This product family, which is proven in its field, is based on the principle of magnetic measurement. The 13 bit singleturn range is scanned by a sensor using permanent magnetic elements. The 13 bit multiturn range consists of a magnetic reduction gear.

Equipped with a zero set pushbutton, the encoder can be easily set to zero or to any other user-programmed value on site. The connection adapter, which can be removed from the device, enables simple user maintenance and mounting. With its magnetic scanning, rugged IP 67-rated housing and high level of resistance to shock and vibration, the ATM60 is optimally suited for use in harsh conditions.

#### At a glance

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount flange, servo flange, blind hollow shaft, and extensive adapter accessories
- Zero-set and preset functions via hardware or software
- Electrical interface: PROFIBUS DP as per IEC61158 / RS 485, electrically isolated.
- Electronically adjustable, configurable resolution
- Magnetic scanning

#### Your benefits

- Fewer variants are required since one freely programmable encoder offers all singleturn and multiturn resolutions
- Easy setup due to various connectivity options (3x PG, 3x M12)
- Maintenance-free encoder, long service life
- Application flexibility due to easily interchangeable collets for the blind hollow shaft
- Quick commissioning using the zero set/preset function either at the press of the button on the device or via software
- Increased productivity due to highly reliable shock and vibration resistance
- Worldwide availability and service ensure quick and reliable customer service





#### More information

Fields of application
Detailed technical dataG-387
Type code
Ordering information
Dimensional drawingsG-390
PIN assignment
Mandatory accessories
Recommended accessories G-394



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# G

## Fields of application

 Measurement of absolute position in various machines and system such as wind power and solar plants, material transport equipment, textile machines, packaging systems, rollers, harbor facilities, printing machines

#### Detailed technical data

#### Performance

Max. number of steps per revolution	≤ 8,192
Max. number of revolutions	≤ 8,192
Resolution	13 bit x 13 bit
Error limits	± 0.25°
Repeatability	0.1°
Measurement step	0.043°
Initialization time	1,250 ms <sup>1)</sup>

<sup>1)</sup> Valid positional data can be read once this time has elapsed.

#### Interfaces

Electrical interface	PROFIBUS
Bus interface	PROFIBUS DP, RS-485 1) 2) 3)
Set (electronic adjustment)	Via PRESET pushbutton or protocol
Data protocol	Profile for encoder (07hex) - Class 2
Address setting	0 127, DIP switch or protocol
Data transmission rate (baud rate)	9.6 kBaud to 12 Mbaud, autodetect
Status information	LED green (running), LED red (bus activity)
Bus termination	DIP switch 4)

<sup>&</sup>lt;sup>1)</sup> EN 50 170-2.

#### Electrical data

Connection type	Bus adapter with cable screw fixings or round connectors 1)
Operating voltage range	10 V 32 V
Max. power consumption without load	≤ 2 W
MTTFd: mean time to dangerous failure	150 years (EN ISO 13849-1) <sup>2)</sup>

<sup>1)</sup> Please order the Profibus adapter separately.

#### Mechanical data

Shaft diameter		
	Face mount flange	10 mm x 19 mm
	Servo flange	6 mm x 10 mm
	Blind hollow shaft	6 mm, 8 mm, 10 mm, 12 mm, 14 mm, 15 mm, 1/4", 3/8", 1/2" $^{\rm 1)}$
Mass 2)		0.59 kg
Shaft material		Stainless steel
Flange material		Aluminum

<sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.

<sup>2)</sup> DIN 19245 Part 1-3.

 $<sup>^{\</sup>scriptsize\textrm{3)}}$  Electrically isolated through optocoupler.

 $<sup>^{\</sup>rm 4)}$  Should only be connected in the final device.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

<sup>&</sup>lt;sup>2)</sup> Relates to devices with cable outlet.

<sup>&</sup>lt;sup>3)</sup> Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range



<sup>2)</sup> Relates to devices with cable outlet.

#### Ambient data


EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating	IP 67 with shaft seal (acc. to IEC 60529) $^{1)}$ IP 43 without shaft seal, not sealed on encoder flange (acc. to IEC 60529) $^{1)}$ IP 66 without shaft seal, sealed on encoder flange (acc. to IEC 60529) $^{1)}$
Permissible relative humidity	98%
Operating temperature range	-20 °C +85 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	100 g, 6 ms (according to EN 60068-2-27)
Resistance to vibrations	20 g, 10 Hz 2,000 Hz (according to EN 60068-2-6)

<sup>1)</sup> When mating connector is inserted.



<sup>3)</sup> Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

## Type code



<sup>&</sup>lt;sup>1)</sup> Order collet for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.

## Ordering information

## Solid shaft, face mount flange

Shaft diam- eter	Electrical interface	Connection type	Number of steps	Resolution	Programma- ble	Туре	Part no.
Ø 10 mm, length 19 mm	10 V 32 V, PROFIBUS	Bus adapter with cable screw fixings or round connec- tors	≤ 8,192	8,192 x 8,192	V	ATM60-P4H13X13	1030013

## Solid shaft, servo flange

Shaft diam- eter	Electrical interface	Connection type	Number of steps	Resolution	Programma- ble	Туре	Part no.
Ø 6 mm, length 10 mm	10 V 32 V, PROFIBUS	Bus adapter with cable screw fixings or round connec- tors	≤ 8,192	8,192 x 8,192	V	ATM60-P1H13X13	1030014


## Blind hollow shaft

Shaft diam- eter	Electrical interface	Connection type	Number of steps	Resolution	Programma- ble	Туре	Part no.
6 mm, 8 mm, 10 mm, 12 mm, 14 mm, 15 mm 1/4", 3/8", 1/2" 1)	10 V 32 V, PROFIBUS	Bus adapter with cable screw fixings or round connec- tors	≤ 8,192	8,192 x 8,192	v	ATM60-PAH13X13	1030015

<sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.


## Dimensional drawings (dimensions in mm)

#### Face mount flange




General tolerances according to DIN ISO 2768-mk

#### Servo flange



General tolerances according to DIN ISO 2768-mk





General tolerances according to DIN ISO 2768-mk

Terminal strip	Male connector, 4 pin	Male connector, 5 pin	Female connector, 5 pin	Sigi
1	1	-	-	U <sub>s</sub> (24 V)
2	3	-	-	0 V (GND)
3	-	-	4	В
4	-	-	2	Α
5	-	4	-	В
6	-	2	-	Α
7	-	-	1	2P5 <sup>2)</sup>
8	-	-	3	2M <sup>2)</sup>
-	2	1	-	N. C.
-	4	3	-	N. C.
_	-	5	5	Screen

<sup>1)</sup> Encoders with a PROFIBUS adapter are equipped with screws (metric/PG) for connecting bus and supply cables. The adapter is unscrewed from the full device to connect the cables. The following figure shows how the pins are assigned within the adapter.

Signal

Explanation

Operating voltage 10 ... 32 V

B cable PROFIBUS DP (out) A cable PROFIBUS DP (out) B cable PROFIBUS DP (in) A cable PROFIBUS DP (in)


+ 5 V (potential free)

0 V (potential free)

Housing potential

Ground (0 V)

 $<sup>^{2)}</sup>$  Use for external bus terminations or to supply the sender/receiver with a optical fiber transmission.



- ① = Internal plug connector to the encoder
- ② = External connection to the bus


## Mandatory accessories


## Adapters and distributors


## Bus adapters

Figure	Brief description	Туре	Part no.
	PROFIBUS DP, connection adapter KR3, 3 x PG	AD-ATM60-KA3PR	2029225
03	PROFIBUS DP, connection adapter SR3, 3 x M12, 5-pin	AD-ATM60-SR3PR	2031985

## AD-ATM60-KA3PR










General tolerances according to DIN ISO 2768-mk

#### AD-ATM60-SR3PR







General tolerances according to DIN ISO 2768-mk

### Shaft adaptation

## Collets and clamping rings

Figure	Brief description	Туре	Part no.
	Collet for blind hollow shaft, shaft diameter 6 mm, external diameter 15 mm	SPZ-006-AD-A	2029174
	Collet for blind hollow shaft, shaft diameter 8 mm, external diameter 15 mm	SPZ-008-AD-A	2029176
	Collet for blind hollow shaft, shaft diameter 10 mm, external diameter 15 mm	SPZ-010-AD-A	2029178
	Collet for blind hollow shaft, shaft diameter 12 mm, external diameter 15 mm	SPZ-012-AD-A	2029179
	Collet for blind hollow shaft, shaft diameter 14 mm, external diameter 15 mm	SPZ-014-AD-A	2048863
	Collet for blind hollow shaft, shaft diameter 1/2" (12.7 mm), external diameter 15 mm	SPZ-1E2-AD-A	2029180
	Collet for blind hollow shaft, shaft diameter 1/4" (6.35 mm), external diameter 15 mm	SPZ-1E4-AD-A	2029175
	Collet for blind hollow shaft, shaft diameter 3/8" (9.525 mm), external diameter 15 mm	SPZ-3E8-AD-A	2029177

#### Recommended accessories

## Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
()	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

## Flanges

#### Flange plate

Figure	Brief description	Туре	Part no.
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161

Dimensional drawings → page K-725

## Other mounting accessories

### Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
0	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
(	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278

Dimensional drawings → page K-725

#### Mounting bell

Figure	Brief description	Туре	Part no.
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987



## Servo clamps

Figure	Brief description	Туре	Part no.
()	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

Dimensional drawings → page K-725

#### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
-91	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

Dimensional drawings → page K-725

## Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, –30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408

Figure	Brief description	Туре	Part no.
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30°C +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
(Cir	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, -10° to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ ° to $+80$ °C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

Dimensional drawings → page K-725

# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		5 m	DOL-1205-G05MQ	6026006
		10 m	DOL-1205-G10MQ	6026008
	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm	12 m	DOL-1205-G12MQ	6032636
		15 m	DOL-1205-G15MQ	6032637
		20 m	DOL-1205-G20MQ	6032638
		30 m	DOL-1205-G30MQ 6032639	6032639
		50 m	DOL-1205-G50MQ	6026006 6026008 6032636 6032637 6032638
	Head A: female connector, M12, 4-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PVC, unshielded, $4 \times 0.25 \text{ mm}^2$ , $\emptyset$ 5.0 mm	5 m	DOL-1204-G05M	6009866

Dimensional drawings → page K-725

Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm <sup>2</sup> , Ø 8.0 mm Wire shielding: AL-PT foil, total shield, tin-plated C shield	5 m	STL-1205-G05MQ	6026005
		10 m	STL-1205-G10MQ	6026007
		12 m	STL-1205-G12MQ	6032635

### Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -	DOS-1204-G	6007302
	Head A: female connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -	DOS-1205-GQ	6021353

Dimensional drawings → page K-725

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm	By the meter	LTG-2102-MW	6021355

### Other plug connectors and cables

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 4-pin, straight, B-coded Cable: terminator	STE-END-Q	6021156

Dimensional drawings → page K-725

### Male connectors (ready to assemble)

Figure	Figure Brief description		Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -	STE-1205-GQ	6021354

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards





The ATM60 absolute multiturn encoder from SICK has an SSI data interface and provides reliable positional information even in harsh ambient conditions, with a resolution of up to 26 bits. This product family, which is proven in its field, is based on the principle of magnetic measurement. The 13 bit singleturn range is scanned by a sensor using permanent magnetic elements. The 13 bit multiturn

**Product description** 

range consists of a magnetic reduction gear. Equipped with a zero set pushbutton, the encoder can be easily set to zero or to any other user-programmed value on site. Configuration of the SSI encoder is easy using the RS422 interface. With its magnetic scanning, rugged IP 67-rated housing and high level of resistance to shock and vibration, the ATM60 is optimally suited for use in harsh conditions.

### At a glance

- · Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount flange, servo flange, blind hollow shaft, and extensive adapter accessories
- Zero-set and preset functions via hardware or software
- · Electrical interface: SSI with gray or binary code type
- · Electronically adjustable, configurable resolution
- · Round axis function (optional) also for non-binary resolutions (per revolution) and decimal numbers (number of revolutions)
- Magnetic scanning

### Your benefits

- · Fewer variants are required since one freely programmable encoder offers all singleturn and multiturn resolu-
- Easy setup due to various electrical connection adapters (cable, M23)
- Maintenance-free encoder, long service life
- Application flexibility due to easily interchangeable collets for the blind hollow shaft
- · Quick commissioning using the zero set/preset function either at the press of the button on the device or via
- Increased productivity due to highly reliable shock and vibration resistance
- Worldwide availability and service ensure quick and reliable customer service



### More information

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawings
PIN assignment
Mandatory accessories
Recommended accessories G-406

→ www.mvsick.com/en/ATM60 SSI

For more information, simply enter the link or scan the OR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

• Measurement of absolute position in various machines and system such as wind power and solar plants, material

transport equipment, textile machines, packaging systems, rollers, harbor facilities, printing machines

### Detailed technical data

### Performance

Max. number of steps per revolution	≤ 8,192
Max. number of revolutions	≤ 8,192
Resolution	13 x 12 bit or 12 x 13 bit
Error limits	± 0.25°
Repeatability	0.1°
Measurement step	0.043°
Initialization time	1,050 ms <sup>1)</sup>

<sup>1)</sup> Valid positional data can be read once this time has elapsed.

### Interfaces

Electrical interface	SSI
Signal wire	Potential-free with a 12-pin M23 male connector for the housing or a 12-wire cable
Interface signals	Clock +, Clock -, Data +, Data- 1) Programming interface: RS-422
Clock frequency	1 MHz <sup>2)</sup>
Set (electronic adjustment)	H active (L = 0 - 4.7 V, H = 10 - Us V)
CW/CCW (counting sequence when turning)	L active (L = 0 - 1.5 V, H = 2.0 - Us V)
Configuration data	Number of steps per revolution Number of revolutions Code type Electronic adjustment

<sup>1)</sup> For higher clock frequencies, choose synchronous SSI.

### Electrical data

Operating voltage range	10 V 32 V
Max. power consumption without load	≤ 0.8 W
Code type	Gray, binary
Code sequence	CW/CCW
Supply voltage	10 32 V
Reverse polarity protection	V
MTTFd: mean time to dangerous failure	150 years (EN ISO 13849-1) 1)

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

G

<sup>&</sup>lt;sup>2)</sup> Min. LOW level (Clock +): 500 ns.

### Mechanical data

Shaft diameter	
Face mount flange	10 x 19 mm
Servo flange	6 x 10 mm
Blind hollow shaft 1)	6, 8, 10, 12, 14, 15 mm and 1/4", 3/8", 1/2"
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum
Mass <sup>2)</sup>	
Face mount flange, servo flange	0.5 kg
Blind hollow shaft	0.4 kg
Start up torque at 20 °C	
Face mount flange, servo flange	2.5 Ncm with shaft seal
Face mount flange, servo flange	0.5 Ncm without shaft seal
Blind hollow shaft	1.2 Ncm with shaft seal
Operating torque at 20 °C	
Face mount flange, servo flange	1.8 Ncm with shaft seal
Face mount flange, servo flange	0.3 Ncm without shaft seal
Blind hollow shaft	0.8 Ncm with shaft seal
Permissible shaft loading	
Face mount flange, servo flange	300 N radial 50 N axial
Permissible shaft movement of the drive element, static/dynamic	
Blind hollow shaft	$\pm$ 0.3/ $\pm$ 0.1 mm radial $\pm$ 0.5/ $\pm$ 0.2 mm axial
Max. angular acceleration	$\leq 500,000 \text{ rad/s}^2$
Operating speed 3)	
Face mount flange, servo flange	6,000 rpm
Blind hollow shaft	3,000 rpm
Rotor moment of inertia	
Face mount flange, servo flange	35 gcm <sup>2</sup>
Blind hollow shaft	55 gcm <sup>2</sup>
Bearing lifetime	3.6 x 10° revolutions

<sup>&</sup>lt;sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.

### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating (as per IEC 60529) 1)	IP 67, with shaft seal IP 43, without shaft seal, not sealed on encoder flange IP 65, without shaft seal, not sealed on encoder flange
Permissible relative humidity	98%
Operating temperature range	-20 °C +85 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	100 g/6 ms (according to EN 60068-2-27)
Resistance to vibrations	20 g / 10 Hz - 2,000 Hz (according to EN 60068-2-6)

<sup>1)</sup> When mating connector is inserted.

 $<sup>^{\</sup>mbox{\tiny 2)}}$  Relates to devices with cable outlet.

 $<sup>^{</sup>m 3)}$  Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

### Type code

### **Electrical interface** A 10 V...32 V, SSI/RS422 Mechanical design 1 Solid shaft, servo flange, Ø 6 mm, length 10 mm 4 Solid shaft, face mount flange, Ø 10 mm, length 19 mm A Blind hollow shaft 1) **Connection type** A Male connector M23, 12-pin, radial outlet Cable, 12-wire, radial outlet, 1.5 m Cable, 12-wire, radial outlet, 3.0 m M Cable, 12-wire, radial outlet, 5.0 m Cable, 12-wire, radial outlet, 10.0 m Resolution can be programmed by the customer using the programming tool PGT 01 2),3) Factory setting:12 bit singleturn x 12 bit multiturn 2) Т M 6 0 Α 1 2 1 2 X

### Ordering information

### Solid shaft, servo flange

Shaft diameter: 6 mm, length 10 mm
 Electrical interface: 10 V ... 32 V, SSI

Number of steps: ≤ 4,096
 Resolution: 4,096 x 4,096

Programmable: ✓

Connection type	Туре	Part no.
M23 male connector, 12-pin, radial	ATM60-A1A12X12	1030005
Cable, 12-wire, radial, 1.5 m	ATM60-A1K12X12	1030006
Cable, 12-wire, radial, 3 m	ATM60-A1L12X12	1030007
Cable, 12-wire, radial, 5 m	ATM60-A1M12X12	1030008
Cable, 12-wire, radial, 10 m	ATM60-A1N12X12	1032925

### Solid shaft, face mount flange

Shaft diameter: 10 mm, length 19 mm
 Electrical interface: 10 V ... 32 V, SSI

Number of steps: ≤ 4,096Resolution: 4,096 x 4,096

Programmable:

Connection type	Туре	Part no.
M23 male connector, 12-pin, radial	ATM60-A4A12X12	1030001
Cable, 12-wire, radial, 1.5 m	ATM60-A4K12X12	1030002
Cable, 12-wire, radial, 3 m	ATM60-A4L12X12	1030003
Cable, 12-wire, radial, 5 m	ATM60-A4M12X12	1030004
Cable, 12-wire, radial, 10 m	ATM60-A4N12X12	1032915

<sup>1)</sup> Order collet for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.

<sup>&</sup>lt;sup>2)</sup> Ex-works configuration: 4,096 steps x 4,096 revolutions, Gray-Code, Set = 0. Other configurations on request.

<sup>3)</sup> Maximum permissible resolution: 25 bit (12 bit singleturn x 13 bit multiturn or 13 bit singleturn x 12 bit multiturn).

• Electrical interface: 10 V ... 32 V, SSI


Number of steps: ≤ 4,096
 Resolution: 4,096 x 4,096

Programmable: ✓

Connection type	Туре	Part no.
M23 male connector, 12-pin, radial	ATM60-AAA12X12	1030009
Cable, 12-wire, radial, 1.5 m	ATM60-AAK12X12	1030010
Cable, 12-wire, radial, 3 m	ATM60-AAL12X12	1030011
Cable, 12-wire, radial, 5 m	ATM60-AAM12X12	1030012
Cable, 12-wire, radial, 10 m	ATM60-AAN12X12	1033169


### Dimensional drawings (dimensions in mm)

Face mount flange, male connector



General tolerances according to DIN ISO 2768-mk


Face mount flange, cable



G


### General tolerances according to DIN ISO 2768-mk

### Servo flange, male connector



General tolerances according to DIN ISO 2768-mk

### Servo flange, cable




General tolerances according to DIN ISO 2768-mk

G-403

General tolerances according to DIN ISO 2768-mk

Blind hollow shaft, cable



General tolerances according to DIN ISO 2768-mk



### PIN assignment

PIN	Signal	Wire colors (cable outlet)	Explanation
1	GND	Blue	Ground connection
2	Data +	White	Interface signals
3	Clock +	Yellow	Interface signals
4	R x D +	Gray	RS-422 programming cable
5	R x D -	Green	RS-422 programming cable
6	T x D +	Pink	RS-422 programming cable
7	T x D -	Black	RS-422 programming cable
8	U <sub>s</sub>	Red	Operating voltage
9	SET 1)	Orange	Electronic adjustment
10	Data -	Brown	Interface signals
11	Clock -	Violet	Interface signals
12	V/¯R <sup>2)</sup>	Orange/black	Sequence in direction of rotation
	Screen		Housing potential

<sup>&</sup>lt;sup>1)</sup> SET = This input activates the electronic zero set. If the SET cable is set to US for more than 100 ms, the mechanical position corresponds to the O value, i.e., the predetermined SET value.

<sup>&</sup>lt;sup>2)</sup> V/R = Forwards/Reverse: This input programs the counting direction for the encoder. When it is not connected, this input is set to HIGH. If the encoder shaft is rotated clockwise (to the right) as viewed when facing the shaft, it counts in ascending order. If it should count in ascending order when the shaft is rotated counterclockwise (to the left), then this connection must be permanently set to LOW level (GND).



View of M23 male device connector on encoder

G

### Mandatory accessories

Shaft adaptation

Collets and clamping rings

Figure	Brief description	Туре	Part no.
	Collet for blind hollow shaft, shaft diameter 6 mm, external diameter 15 mm	SPZ-006-AD-A	2029174
	Collet for blind hollow shaft, shaft diameter 8 mm, external diameter 15 mm	SPZ-008-AD-A	2029176
	Collet for blind hollow shaft, shaft diameter 10 mm, external diameter 15 mm	SPZ-010-AD-A	2029178
	Collet for blind hollow shaft, shaft diameter 12 mm, external diameter 15 mm	SPZ-012-AD-A	2029179
	Collet for blind hollow shaft, shaft diameter 14 mm, external diameter 15 mm	SPZ-014-AD-A	2048863
	Collet for blind hollow shaft, shaft diameter 1/2" (12.7 mm), external diameter 15 mm	SPZ-1E2-AD-A	2029180
	Collet for blind hollow shaft, shaft diameter 1/4" (6.35 mm), external diameter 15 mm	SPZ-1E4-AD-A	2029175
	Collet for blind hollow shaft, shaft diameter 3/8" (9.525 mm), external diameter 15 mm	SPZ-3E8-AD-A	2029177

Dimensional drawings → page K-725

### Recommended accessories

### Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
<u>(, )</u>	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725



### Flanges

### Flange plate

Figure	Brief description	Туре	Part no.
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225
0)	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161

### Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278

Dimensional drawings → page K-725

### Mounting bell

Figure	Brief description	Туре	Part no.
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

### Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

Dimensional drawings → page K-725

### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
-91	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

1	7	٦.
U	L	5
	e.	

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
Tim-	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, –30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°, max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
(0	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
410	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, -10° to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10$ ° to $+80$ °C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

# Connectivity

### Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		1.5 m	DOL-2312-G1M5MA1	2029200
Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 t + 2 x 0.14 mm², Ø 7.8 mm	Hoad At fomale connector M22, 12 nin, ctraight	3 m	DOL-2312-G03MMA1	2029201
		5 m	DOL-2312-G05MMA1	2029202
	Cable: suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup>	10 m	DOL-2312-G10MMA1	2029203
	+ 2 X 0.14 mm², Ø 7.8 mm	20 m	DOL-2312-G20MMA1	2029204
		30 m	DOL-2312-G30MMA1	2029205

Dimensional drawings → page K-725

Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	DOS-2312-W01	2072580
	Head A: female connector, M23, 21-pin, straight, shielded, for cable diameter 5.5 mm $\dots$ 12 mm Head B: -	DOS-2321-G	6027539

Dimensional drawings → page K-725

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15~\text{mm}^2$ , Ø 5.6 mm	By the meter	LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	By the meter	LTG-2411-MW	6027530
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.25 mm $^2$ + 2 x 0.5 mm $^2$ + 2 x 0.14 mm $^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<b>&gt;</b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2612-MW	6028516

### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40  ^{\circ}\text{C} \dots +125  ^{\circ}\text{C}$	STE-2312-G01	2077273

Dimensional drawings → page K-725

### Other accessories

Programming and configuration tools

Figure Brief description		Туре	Part no.
三二:	Programming tool for ATM60, ATM90 and KH53 SSI	PGT-01-S	1030111

<sup>→</sup> For additional accessories, please see page K-668 onwards

G

# RELIABLE, ESTABLISHED, AND MODULAR





### **Product description**

The ATM60 CANopen absolute multiturn encoder from SICK provides reliable positional and speed information even in harsh ambient conditions, with a resolution of up to 26 bits. This product family, which is proven in its field, is based on the principle of magnetic measurement. The 13 bit singleturn range is scanned by a sensor using permanent magnetic elements. The 13 bit multiturn range consists of a magnetic reduction gear. Equipped with a zero set pushbutton, the encoder can be easily set to zero or

to any other user-programmed value on site. The connection adapter, which can be removed from the device, enables simple user maintenance and mounting. With its magnetic scanning, rugged IP 67-rated housing and high level of resistance to shock and vibration, the ATM60 is optimally suited for use in harsh conditions.

### At a glance

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount, servo flange, blind hollow shaft, adapter accessories
- Zero-set and preset functions via hardware/software
- Electrical interface: CAN specification
   2. 0B, electrically isolated; DS 301,
   V4.01, DSP 406, V2.0, Class 2
- Electronically adjustable, configurable resolution
- Network status info via duo LED
- Magnetic scanning

### Your benefits

- Fewer variants are required since one freely programmable encoder offers all singleturn and multiturn resolutions
- Easy setup due to various connectivity options (1 to 3x PG, 2x M12)
- Maintenance-free encoder, long service life
- Application flexibility due to easily interchangeable collets for the blind hollow shaft
- Quick commissioning using the zero set/preset function either at the press of the button on the device or via software
- Increased productivity due to highly reliable shock and vibration resistance
- Worldwide availability and service ensure quick and reliable customer service



### More information

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawings
PIN assignment
Mandatory accessories
Recommended accessories G-419

→ www.mysick.com/en/ATM60\_CANopen

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# G

### Fields of application

• Measurement of absolute position in various machines and system such as wind power and solar plants, material

transport equipment, textile machines, packaging systems, rollers, harbor facilities, printing machines

### Detailed technical data

### Performance

Max. number of steps per revolution	≤ 8,192
Max. number of revolutions	≤ 8,192
Resolution	13 bit x 13 bit
Error limits	± 0.25°
Repeatability	0.1°
Measurement step	0.043°
Initialization time	1,250 ms <sup>1)</sup>

<sup>1)</sup> Valid positional data can be read once this time has elapsed.

### Interfaces

Electrical interface	ISO-DIN 11898, electrically isolated <sup>1) 2)</sup>
Bus interface	CANopen
Set (electronic adjustment)	Via PRESET pushbutton or protocol
Data protocol	Communication profile DS 301 V4.0, device profile DSP 406 V 2.0
Address setting (NODE ID)	0 63, DIP switch or protocol
Data transmission rate (baud rate)	10 ; 20; 50; 125; 250; 500 kBaud 1 MBaud; DIP switch or protocol,
Status information	2-color LED for CAN controller status
Bus termination	DIP switch <sup>2)</sup>

<sup>1)</sup> CAN High Speed.

### Electrical data

Connection type	Bus adapter with cable screw fixings or round connectors 1)
Operating voltage range	10 V 32 V
Max. power consumption without load	≤ 2 W
Reverse polarity protection	V
MTTFd: mean time to dangerous failure	150 years (EN ISO 13849-1) <sup>2)</sup>

<sup>1)</sup> Please order the CANbus adapter separately.

<sup>&</sup>lt;sup>2)</sup> CAN specification 2.0 B.

<sup>&</sup>lt;sup>3)</sup> Should only be connected in the final device.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

### Mechanical data

Shaft diameter	
Face mount flange	10 x 19 mm
Servo flange	6 x 10 mm
Blind hollow shaft 1)	6, 8, 10, 12, 14, 15 mm and 1/4", 3/8", 1/2"
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum
Mass <sup>2)</sup>	
Face mount flange, servo flange	0.59 kg
Blind hollow shaft	0.59 kg
Start up torque at 20 °C	
Face mount flange, servo flange	2.5 Ncm with shaft seal
Face mount flange, servo flange	0.5 Ncm without shaft seal
Blind hollow shaft	1.2 Ncm with shaft seal
Operating torque at 20 °C	
Face mount flange, servo flange	1.8 Ncm with shaft seal
Face mount flange, servo flange	0.3 Ncm without shaft seal
Blind hollow shaft	0.8 Ncm with shaft seal
Permissible shaft loading	
Face mount flange, servo flange	300 N radial 50 N axial
Permissible shaft movement of the drive element, static/dynamic	
Blind hollow shaft	$\pm$ 0.3/ $\pm$ 0.1 mm radial $\pm$ 0.5/ $\pm$ 0.2 mm axial
Max. angular acceleration	$\leq 500,000 \text{ rad/s}^2$
Operating speed <sup>3)</sup>	
Face mount flange, servo flange	6,000 rpm
Blind hollow shaft	3,000 rpm
Rotor moment of inertia	
Face mount flange, servo flange	35 gcm <sup>2</sup>
Blind hollow shaft	55 gcm <sup>2</sup>
Bearing lifetime	3.6 x 10° revolutions

<sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.

### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating	IP 67 with shaft seal (acc. to IEC 60529) <sup>1)</sup> IP 43 without shaft seal, not sealed on encoder flange (acc. to IEC 60529) IP 66 without shaft seal, sealed on encoder flange (acc. to IEC 60529)
Permissible relative humidity	98%
Operating temperature range	-20°C +85°C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	100 g, 6 ms (according to EN 60068-2-27)
Resistance to vibrations	20 g, 10 Hz 2,000 Hz (according to EN 60068-2-6)

<sup>1)</sup> When mating connector is inserted.

<sup>&</sup>lt;sup>2)</sup> Relates to devices with cable outlet.

<sup>&</sup>lt;sup>3)</sup> Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

### Type code

# Electrical interface C CANopen with interface adapter Mechanical design 1 Solid shaft, servo flange, Ø 6 mm, length 10 mm 4 Solid shaft, face mount flange, Ø 10 mm, length 19 mm A Blind hollow shaft 1) Connection type H Please order CANbus adapter separately, see recommended accessories. Resolution can be programmed by the customer Factory setting:13 bit singleturn x 13 bit multiturn

### Ordering information

### Solid shaft, servo flange

Shaft diameter	Electrical inter- face	Connection type	Number of steps	Resolution	Туре	Part no.
Ø 6 mm, length 10 mm	10 V 32 V, CANopen	Bus adapter with cable screw fixings or round connec- tors	≤ 8,192	8,192 x 8,192	ATM60-C1H13X13	1030025

### Solid shaft, face mount flange

Shaft diameter	Electrical inter- face	Connection type	Number of steps	Resolution	Туре	Part no.
Ø 10 mm, length 19 mm	10 V 32 V, CANopen	Bus adapter with cable screw fixings or round connectors	≤ 8,192	8,192 x 8,192	ATM60-C4H13X13	1030024

### Blind hollow shaft


Shaft diameter	Electrical inter- face	Connection type	Number of steps	Resolution	Туре	Part no.
6 mm, 8 mm, 10 mm, 12 mm, 14 mm, 15 mm, 1/4", 3/8", 1/2" <sup>1)</sup>	10 V 32 V, CANopen	Bus adapter with cable screw fixings or round connectors	≤ 8,192	8,192 x 8,192	ATM60-CAH13X13	1030026

<sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.

<sup>&</sup>lt;sup>1)</sup> Order collet for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.


### Dimensional drawings (dimensions in mm)

### Face mount flange



General tolerances according to DIN ISO 2768-mk


### Servo flange



General tolerances according to DIN ISO 2768-mk



### Blind hollow shaft




General tolerances according to DIN ISO 2768-mk

### PIN assignment


Terminal st	rip Male device co	onnector Signal	Explanation
1	1	Shield	Screen
2	2	U <sub>s</sub> (24 V)	Operating voltage 10 32 V
3	3	GND (COM)	0 V (Gnd)
4	4	CAN <sub>H</sub>	CAN bus signal high
5	5	CAN <sub>L</sub>	CAN bus signal low
6	-	CAN <sub>H</sub>	CAN bus signal high
7	-	CAN <sub>L</sub>	CAN bus signal low
8	-	GND (COM)	0 V (Gnd)
9	-	U <sub>s</sub> (24 V)	Operating voltage 10 - 32 V


### Connection adapter




- Α = Internal plug connector to the encoder
- В = External connections to the bus

### M12 male device connector (connection adapter)







N/US (male contact)


# Mandatory accessories


### Adapters and distributors


### Bus adapters

Figure	Brief description	Туре	Part no.
	CANopen connection adapter KR1, 1 x PG	AD-ATM60-KR1CO	2029230
	CANopen connection adapter KR2, 2 x PG	AD-ATM60-KR2CO	2029231
OS TO	CANopen connection adapter KR3, 3 x PG	AD-ATM60-KR3CO	2029232
15	CANopen connection adapter SR1, 1 x M12, 5-pin	AD-ATM60-SR1CO	2031686
	CANopen connection adapter SR2, 2 x M12, 5-pin	AD-ATM60-SR2CO	2020935


### AD-ATM60-KRxCO










### AD-ATM60-SR1CO









### AD-ATM60-SR2CO







G

### Shaft adaptation

### Collets and clamping rings

Figure	Brief description	Туре	Part no.
	Collet for blind hollow shaft, shaft diameter 6 mm, external diameter 15 mm	SPZ-006-AD-A	2029174
	Collet for blind hollow shaft, shaft diameter 8 mm, external diameter 15 mm	SPZ-008-AD-A	2029176
	Collet for blind hollow shaft, shaft diameter 10 mm, external diameter 15 mm	SPZ-010-AD-A	2029178
1	Collet for blind hollow shaft, shaft diameter 12 mm, external diameter 15 mm	SPZ-012-AD-A	2029179
	Collet for blind hollow shaft, shaft diameter 14 mm, external diameter 15 mm	SPZ-014-AD-A	2048863
	Collet for blind hollow shaft, shaft diameter 1/2" (12.7 mm), external diameter 15 mm	SPZ-1E2-AD-A	2029180
	Collet for blind hollow shaft, shaft diameter 1/4" (6.35 mm), external diameter 15 mm	SPZ-1E4-AD-A	2029175
	Collet for blind hollow shaft, shaft diameter 3/8" (9.525 mm), external diameter 15 mm	SPZ-3E8-AD-A	2029177

Dimensional drawings → page K-725

### Recommended accessories

### Mounting systems

Mounting brackets and plates

### Mounting bracket

Figure	Brief description	Туре	Part no.
T	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

### Flanges

### Flange plate

Figure	Brief description	Туре	Part no.
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161

### Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
<b>(a)</b>	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
(~)	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278

Dimensional drawings → page K-725

### Mounting bell

Figure	Brief description	Туре	Part no.
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

### Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

Dimensional drawings → page K-725

### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
-91	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591



# G

### Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
itian-	Bellows coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
0	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
10	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, -10° to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^\circ$ to +80 °C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

# Connectivity

Plug connectors and cables

Female connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 5-pin, straight, shielded, for cable diameter 4.5 mm 7 mm Head B: -	DOS-1205-GA	6027534

Dimensional drawings → page K-725

### Cables (ready to assemble)

Figure	Brief description	Туре	Part no.
///	Head A: cable Head B: cable Cable: suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² Wire shielding: AL-PT foil, total shield, tin-plated C shield	By the meter	LTG-2804-MW

### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
0	Head A: male connector, M12, 5-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1205-GA	6027533

Dimensional drawings → page K-725

### Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
1	Head A: female connector, M12, 5-pin, straight Head B: male connector, M12, 5-pin, straight Cable: drop cable, PUR, halogen-free, unshielded, 2 x 0.34 mm², Ø 6.9 mm	6 m	DSL-1205-G06MK	6028327

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards



# RELIABLE, ESTABLISHED, AND MODULAR





### **Product description**

The ATM60 DeviceNet absolute multiturn encoder from SICK provides reliable positional and speed information even in harsh ambient conditions, with a resolution of up to 26 bits. This product family, which is proven in its field, is based on the principle of magnetic measurement. The 13 bit singleturn range is scanned by a sensor using permanent magnetic elements. The 13 bit multiturn range consists of a magnetic reduction gear.

Equipped with a zero set pushbutton, the encoder can be easily set to zero or to any other user-programmed value on site. The connection adapter, which can be removed from the device, enables simple user maintenance and mounting. With its magnetic scanning, rugged IP 67-rated housing and high level of resistance to shock and vibration, the ATM60 is optimally suited for use in harsh conditions.

### At a glance

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: face mount, servo flange, blind hollow shaft, and adapter accessories
- Zero-set and preset functions via hardware/software
- Electrical interface:CAN/DeviceNet specification 2.0B, electrically isolated; device profile: Generic [0]
- Electronically adjustable, configurable resolution
- Network status info via duo LED
- · Magnetic scanning

### Your benefits

- Fewer variants are required since one freely programmable encoder offers all singleturn and multiturn resolutions
- Easy setup due to various connectivity options (1 to 2x PG, 1 to 2x M12)
- Maintenance-free encoder, long service life
- Application flexibility due to easily interchangeable collets for the blind hollow shaft
- Quick commissioning using the zero set/preset function either at the press of the button on the device or via software
- Increased productivity due to highly reliable shock and vibration resistance
- Worldwide availability and service ensure quick and reliable customer service



### More information

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawings
PIN assignment
Mandatory accessories
Recommended accessories G-431



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



### Fields of application

• Measurement of absolute position in various machines and system such as wind power and solar plants, material

transport equipment, textile machines, packaging systems, rollers, harbor facilities, printing machines

### Detailed technical data

### Performance

Max. number of steps per revolution	≤ 8,192
Max. number of revolutions	≤ 8,192
Resolution	13 bit x 13 bit
Error limits	± 0.25°
Repeatability	0.1°
Measurement step	0.043°
Initialization time	1,250 ms <sup>1)</sup>

<sup>1)</sup> Valid positional data can be read once this time has elapsed.

### Interfaces

Electrical interface	DeviceNet
Bus interface	DeviceNet ISO-DIN 11898, electrically isolated 1) 2)
Set (electronic adjustment)	Via PRESET pushbutton or protocol
Data protocol	DeviceNet Specification Release 2.0
Address setting	0 63, DIP switch or protocol
Data transmission rate (baud rate)	125, 250, 500 kBaud DIP switch or protocol
Status information	Network status LED, 2-colors
Bus termination	DIP switch 3)

<sup>1)</sup> CAN High Speed.

### Electrical data

Connection type	Bus adapter with cable screw fixings or round connectors 1)
Operating voltage range	10 V 32 V
Max. power consumption without load	≤ 2 W
Reverse polarity protection	<b>v</b>
MTTFd: mean time to dangerous failure	150 years (EN ISO 13849-1) <sup>2)</sup>

<sup>1)</sup> Please order the DeviceNet adapter separately.

G

<sup>&</sup>lt;sup>2)</sup> CAN specification 2.0 B.

 $<sup>^{\</sup>mbox{\scriptsize 3)}}$  Should only be connected in the final device.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

### Mechanical data

Shaft diameter	
Face mount flange	10 x 19 mm
Servo flange	6 x 10 mm
Blind hollow shaft 1)	6, 8, 10, 12, 14, 15 mm and 1/4", 3/8", 1/2"
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum
Mass <sup>2)</sup>	
Face mount flange, servo flange	0.59 kg
Blind hollow shaft	0.59 kg
Start up torque at 20 °C	
Face mount flange, servo flange	2.5 Ncm with shaft seal
Face mount flange, servo flange	0.5 Ncm without shaft seal
Blind hollow shaft	1.2 Ncm with shaft seal
Operating torque at 20 °C	
Face mount flange, servo flange	1.8 Ncm with shaft seal
Face mount flange, servo flange	0.3 Ncm without shaft seal
Blind hollow shaft	0.8 Ncm with shaft seal
Permissible shaft loading	
Face mount flange, servo flange	300 N radial 50 N axial
Permissible shaft movement of the drive element, static/dynamic	
Blind hollow shaft	$\pm$ 0.3/ $\pm$ 0.1 mm radial $\pm$ 0.5/ $\pm$ 0.2 mm axial
Max. angular acceleration	≤ 500,000 rad/s²
Operating speed 3)	
Face mount flange, servo flange	6,000 rpm
Blind hollow shaft	3,000 rpm
Rotor moment of inertia	
Face mount flange, servo flange	35 gcm <sup>2</sup>
Blind hollow shaft	55 gcm <sup>2</sup>
Bearing lifetime	3.6 x 109 revolutions

<sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.

### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating (as per IEC 60529)	IP 67, with shaft seal IP 43, without shaft seal, not sealed on encoder flange IP 66, without shaft seal, not sealed on encoder flange
Permissible relative humidity	98%
Operating temperature range	-20 °C +85 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	100 g/6 ms (according to EN 60068-2-27)
Resistance to vibrations	20 g / 10 Hz - 2,000 Hz (according to EN 60068-2-6)

 $<sup>^{\</sup>rm 2)}$  If the shaft seal has been removed by the customer.

### Type code

# Electrical interface D DeviceNet specification, release 2.0 Mechanical design 1 Solid shaft, servo flange, Ø 6 mm, length 10 mm 4 Solid shaft, face mount flange, Ø 10 mm, length 19 mm Blind hollow shaft 1) Connection type H Please order DeviceNet adapter separately, see recommended accessories. Resolution can be programmed by the customer Factory setting:13 bit singleturn x 13 bit multiturn A T M 6 O - D H 1 3 x 1 3

### Ordering information

### Solid shaft, servo flange

Shaft diameter	Electrical inter- face	Connection type	Number of steps	Resolution	Туре	Part no.
Ø 10 mm, length 19 mm	10 V 32 V, DeviceNet	Bus adapter with cable screw fixings or round connectors	≤ 8,192	8,192 x 8,192	ATM60-D1H13X13	1030018

### Solid shaft, face mount flange

Shaft diameter	Electrical inter- face	Connection type	Number of steps	Resolution	Туре	Part no.
Ø 10 mm, length 19 mm	10 V 32 V, DeviceNet	Bus adapter with cable screw fixings or round connectors	≤ 8,192	8,192 x 8,192	ATM60-D4H13X13	1030017


### Blind hollow shaft

Shaft diameter	Electrical inter- face	Connection type	Number of steps	Resolution	Туре	Part no.
6 mm, 8 mm, 10 mm, 12 mm, 14 mm, 15 mm, 1/4", 3/8", 1/2" <sup>1)</sup>	10 V 32 V, DeviceNet	Bus adapter with cable screw fixings or round connec- tors	≤ 8,192	8,192 x 8,192	ATM60-DAH13X13	1030019

<sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.


<sup>&</sup>lt;sup>1)</sup> Order collet for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.

### Face mount flange



General tolerances according to DIN ISO 2768-mk


### Servo flange



General tolerances according to DIN ISO 2768-mk



### Servo flange




General tolerances according to DIN ISO 2768-mk

### PIN assignment


Terminal strip	Male device connector	Signal	Explanation
1	1	Shield	Screen
2	2	U <sub>S</sub> (24 V)	Operating voltage 10 - 32 V
3	3	GND (COM)	0 V (Gnd)
4	4	CAN <sub>H</sub>	CAN bus signal high
5	5	CAN <sub>L</sub>	CAN bus signal low
6	-	CAN <sub>H</sub>	CAN bus signal high
7	-	CAN <sub>L</sub>	CAN bus signal low
8	-	GND (COM)	0 V (Gnd)
9	-	U <sub>S</sub> (24 V)	Operating voltage 10 32 V


### Connection adapter




- ① = Internal plug connector to the encoder
- ② = External connections to the bus

### M12 male device connector (connection adapter)







N/US (male contact)


# Mandatory accessories


### Adapters and distributors


### Bus adapters

Figure	Brief description	Туре	Part no.
	DeviceNet connection adapter KR1, 1 x PG	AD-ATM60-KR1DN	2029228
	DeviceNet connection adapter KR2, 2 x PG	AD-ATM60-KR2DN	2029229
	DeviceNet connection adapter SR1, 1 x M12, 5-pin	AD-ATM60-SR1DN	2029226
	DeviceNet connection adapter SR2, 2 x M12, 5-pin	AD-ATM60-SR2DN	2029227


### AD-ATM60-KRxDN









### AD-ATM60-SRxDN







### Shaft adaptation

### Collets and clamping rings

Figure	Brief description	Туре	Part no.
	Collet for blind hollow shaft, shaft diameter 6 mm, external diameter 15 mm	SPZ-006-AD-A	2029174
	Collet for blind hollow shaft, shaft diameter 8 mm, external diameter 15 mm	SPZ-008-AD-A	2029176
	Collet for blind hollow shaft, shaft diameter 10 mm, external diameter 15 mm	SPZ-010-AD-A	2029178
	Collet for blind hollow shaft, shaft diameter 12 mm, external diameter 15 mm	SPZ-012-AD-A	2029179
	Collet for blind hollow shaft, shaft diameter 14 mm, external diameter 15 mm	SPZ-014-AD-A	2048863
	Collet for blind hollow shaft, shaft diameter 1/2" (12.7 mm), external diameter 15 mm	SPZ-1E2-AD-A	2029180
	Collet for blind hollow shaft, shaft diameter 1/4" (6.35 mm), external diameter 15 mm	SPZ-1E4-AD-A	2029175
	Collet for blind hollow shaft, shaft diameter 3/8" (9.525 mm), external diameter 15 mm	SPZ-3E8-AD-A	2029177



### Recommended accessories

### Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
( ) _	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

### Flanges

### Flange plate

Figure	Brief description	Туре	Part no.
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
6	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225
0)	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161

Dimensional drawings → page K-725

### Other mounting accessories

### Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
<b>(a)</b>	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
(%)	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278



### Mounting bell

Figure	Brief description	Туре	Part no.
<b>(5)</b>	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

### Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

Dimensional drawings → page K-725

### Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
9)	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

Dimensional drawings → page K-725



### Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°, max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
0	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
(c)	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, -10° to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^\circ$ to +80 °C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

Dimensional drawings → page K-725

# Connectivity

Plug connectors and cables

Female connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 5-pin, straight, shielded, for cable diameter 4.5 mm 7 mm Head B: -	DOS-1205-GA	6027534

Dimensional drawings → page K-725

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
///	Head A: cable Head B: cable Cable: suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² Wire shielding: AL-PT foil, total shield, tin-plated C shield	By the meter	LTG-2804-MW	6028328

### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
0	Head A: male connector, M12, 5-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1205-GA	6027533

Dimensional drawings → page K-725

### Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
1	Head A: female connector, M12, 5-pin, straight Head B: male connector, M12, 5-pin, straight Cable: drop cable, PUR, halogen-free, unshielded, 2 x 0.34 mm², Ø 6.9 mm	6 m	DSL-1205-G06MK	6028327

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards



# RELIABLE, ESTABLISHED, AND MODULAR





### **Product description**

The ATM90 with SSI data interface complements the through hollow shaft variants in the ATM60 product family. The ATM90 operates reliably even under harsh ambient conditions. Its rugged mechanical design ensures maximum reliability and a long service life. Magnetic singleturn scanning allows a maximum resolution of up to 13 bits within one revolution. The number of revolutions, maximum of 13 bit, is output and

recorded using a mechanical and almost completely wear-free transmission. This means that the ATM90 can be operated without a battery. A shallow installation depth of 60 mm combined with high shock and vibration resistance enable the ATM90 to be used in applications with high mechanical stress and distinct climate fluctuations

### At a glance

- Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: through hollow shaft with shallow installation depth
- Zero-set and preset functions via hardware or software
- Electrical interface: SSI with gray or binary code type
- Electronically adjustable, configurable resolution
- · Magnetic scanning

### Your benefits

- Fewer variants are required since one freely programmable encoder offers all singleturn and multiturn resolutions
- Easy setup due to various electrical connection adapters (cable, M23)
- Maintenance-free encoder, long service life
- Quick commissioning using the zero set/preset function either at the press of the button on the device or via software
- Increased productivity due to highly reliable shock and vibration resistance
- Worldwide availability and service ensure quick and reliable customer service



### More information

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawings
PIN assignment
Recommended accessories G-442

→ www.mysick.com/en/ATM90\_SSI

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

• Measurement of absolute position in various machines and system such as wind power and solar plants, material

transport equipment, textile machines, packaging systems, rollers, harbor facilities, printing machines

### Detailed technical data

### Performance

Max. number of steps per revolution	≤ 8,192
Max. number of revolutions	≤ 8,192
Resolution	13 x 12 or 12 x 13 bit
Error limits	± 0.25°
Repeatability	0.1°
Measurement step	0.043°
Initialization time	1,050 ms <sup>1)</sup>

<sup>1)</sup> Valid positional data can be read once this time has elapsed.

### Interfaces

Electrical interface	SSI
Signal wire	Potential-free with a 12-pin M23 male connector for the housing or a 12-wire cable
Interface signals	Clock +, Clock -, Data +, Data- 1) Programming interface: RS-422
Clock frequency	1 MHz <sup>2)</sup>
Set (electronic adjustment)	H active (L = 0 - 4.7 V, H = 10 - Us V)
CW/CCW (counting sequence when turning)	L active (L = 0 - 1.5 V, H = 2.0 - Us V)
Configuration data	Number of steps per revolution Number of revolutions Code type Electronic adjustment

<sup>1)</sup> For higher clock frequencies, choose synchronous SSI.

### Electrical data

Operating voltage range	10 V 32 V
Max. power consumption without load	≤ 0.8 W
Code type	Gray, binary
Code sequence	CW/CCW
Reverse polarity protection	V
MTTFd: mean time to dangerous failure	150 years (EN ISO 13849-1) <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

<sup>&</sup>lt;sup>2)</sup> Min. LOW level (Clock +): 500 ns.

### Mechanical data

Shaft diameter	
Through hollow shaft	12, 16 mm and 1/2"
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum
Mass <sup>1)</sup>	0.8 kg
Start up torque at 20 °C	0.5 Ncm
Operating torque at 20 °C	0.4 Ncm
Max. angular acceleration	≤ 600,000 rad/s²
Max. operating speed 2)	2,000 rpm
Rotor moment of inertia	152.77 gcm <sup>2</sup>
Bearing lifetime	3.6 x 109 revolutions

 $<sup>^{\</sup>scriptscriptstyle{1)}}$  Relates to devices with cable outlet.


### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating	IP 65 with shaft seal (acc. to IEC 60529) 1)
Permissible relative humidity	98%
Operating temperature range	-20 °C +70 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	100 g/6 ms (according to EN 60068-2-27)
Resistance to vibrations	20 g / 10 Hz - 2,000 Hz (according to EN 60068-2-6)

<sup>1)</sup> When mating connector is inserted.

# Type code

### Type code



<sup>&</sup>lt;sup>1)</sup> Ex-works configuration: 4,096 steps x 4,096 revolutions, Gray-Code, Set = 0. Other configurations on request.

 $<sup>^{2)}</sup>$  Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

<sup>&</sup>lt;sup>2)</sup> Maximum permissible resolution: 25 bit (12 bit singleturn x 13 bit multiturn or 13 bit singleturn x 12 bit multiturn).

# Ordering information

# Through hollow shaft


• Electrical interface: 10 V ... 32 V, SSI

• Number of steps:  $\leq 4,096$ • **Resolution:** 4,096 x 4,096

• Programmable: ✓

Shaft diameter	Connection type	Туре	Part no.
	Cable, 12-wire, radial, 1.5 m	ATM90-AUK12X12	1030035
4 (0)	Cable, 12-wire, radial, 3 m	ATM90-AUL12X12	1030036
1/2"	Cable, 12-wire, radial, 5 m	ATM90-AUM12X12	1030037
	M23 male connector, 12-pin, radial	ATM90-AUA12X12	1030034
	Cable, 12-wire, radial, 1.5 m	ATM90-ATK12X12	1030031
40	Cable, 12-wire, radial, 3 m	ATM90-ATL12X12	1030032
12 mm	Cable, 12-wire, radial, 5 m	ATM90-ATM12X12	1030033
	M23 male connector, 12-pin, radial	ATM90-ATA12X12	1030030
	Cable, 12-wire, radial, 1.5 m	ATM90-AXK12X12	1030039
40	Cable, 12-wire, radial, 3 m	ATM90-AXL12X12	1030040
16 mm	Cable, 12-wire, radial, 5 m	ATM90-AXM12X12	1030041
	M23 male connector, 12-pin, radial	ATM90-AXA12X12	1030038

# Dimensional drawings (dimensions in mm)



General tolerances according to DIN ISO 2768-mk

① Min. bend radius 40 mm

 $\ @$  Encoder stator coupling through customer's  $\emptyset$  6 mm cylindrical pin, DIN EN 28734

### PIN assignment

PIN	Signal	Wire colors (cable outlet)	Explanation
1	GND	Blue	Ground connection
2	Data +	White	Interface signals
3	Clock +	Yellow	Interface signals
4	R x D +	Gray	RS-422 programming cable
5	R x D -	Green	RS-422 programming cable
6	T x D +	Pink	RS-422 programming cable
7	T x D -	Black	RS-422 programming cable
8	U <sub>s</sub>	Red	Operating voltage
9	SET	Orange	Electronic adjustment
10	Data -	Brown	Interface signals
11	Clock -	Violet	Interface signals
12	V/¯R	Orange/black	Sequence in direction of rotation
	Screen		Housing potential



View of M23 male device connector on encoder

- V/¯R This input programs the counting direction for the encoder. When it is not connected, this input is set to HIGH. If the encoder shaft is rotated clockwise (to the right) as viewed when facing the shaft, it counts in ascending order. If it should count in ascending order when the shaft is rotated counterclockwise (to the left), then this connection must be permanently set to LOW level (GND).
- SET This input is for electronic zeroing. If the SET cable is set to  $\rm U_S$  for more than 100 ms, the mechanical position corresponds to the O value, i.e., the predetermined SET value.

Plug connectors and cables

Recommended accessories

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
Head B: Cable: s	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	1.5 m	DOL-2312-G1M5MA1	2029200
		3 m	DOL-2312-G03MMA1	2029201
		5 m	DOL-2312-G05MMA1	2029202
		10 m	DOL-2312-G10MMA1	2029203
		20 m	DOL-2312-G20MMA1	2029204
		30 m	DOL-2312-G30MMA1	2029205

Dimensional drawings → page K-725

Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057
(F)	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm Head B: - Operating temperature: -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 21-pin, straight, shielded, for cable diameter 5.5 mm $\dots$ 12 mm Head B: -	DOS-2321-G	6027539

Dimensional drawings → page K-725

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , $\emptyset$ 5.6 mm	By the meter	LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	By the meter	LTG-2411-MW	6027530
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<b></b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 2 x 0.14 mm <sup>2</sup> , Ø 7.8 mm	By the meter	LTG-2612-MW	6028516

### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	STE-2312-G01	2077273

Dimensional drawings → page K-725

### Other accessories

Programming and configuration tools

Figure	Brief description	Туре	Part no.
三二:	Programming tool for ATM60, ATM90 and KH53 SSI	PGT-01-S	1030111

<sup>→</sup> For additional accessories, please see page K-668 onwards

# RELIABLE, ESTABLISHED, AND MODULAR





### **Product description**

The ATM90 PROFIBUS complements the through hollow shaft variants in the ATM60 product family. The ATM90 operates reliably even under harsh ambient conditions. Its rugged mechanical design ensures maximum reliability and a long service life. Magnetic singleturn scanning allows a maximum resolution of up to 13 bits within one revolution. The number of revolutions, maximum of 13 bit, is output and recorded using

a mechanical and almost completely wear-free transmission. This means that the ATM90 can be operated without a battery. A shallow installation depth of 60 mm combined with high shock and vibration resistance enable the ATM90 to be used in applications with high mechanical stress and distinct climate fluctuations

### At a glance

- · Extremely rugged, tried-and-tested absolute multiturn encoder with a resolution of up to 26 bits
- Mechanical interface: through hollow shaft with shallow installation depth
- Zero-set and preset functions via hardware or software
- · Electrical interface: PROFIBUS DP as per IEC61158 / RS-485, electrically isolated
- · Electronically adjustable, configurable resolution
- · Magnetic scanning

### Your benefits

- · Fewer variants are required since one freely programmable encoder offers all singleturn and multiturn resolutions
- Easy setup due to various electrical connection adapters (cable, M23)
- Maintenance-free encoder, long service life
- · Quick commissioning using the zero set/preset function either at the press of the button on the device or via software
- Increased productivity due to highly reliable shock and vibration resis-
- Worldwide availability and service ensure quick and reliable customer service



### More information

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawings
PIN assignment
Recommended accessories G-451

→ www.mvsick.com/en/ATM90 PROFIBUS

For more information, simply enter the link or scan the OR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# G

# Fields of application

• Measurement of absolute position in various machines and system such as wind power and solar plants, material

transport equipment, textile machines, packaging systems, rollers, harbor facilities, printing machines

### Detailed technical data

### Performance

Max. number of steps per revolution	≤ 8,192
Max. number of revolutions	8,192
Resolution	13 bit x 13 bit
Error limits	± 0.25°
Repeatability	0.1°
Measurement step	0.043°
Initialization time	1,250 ms <sup>1)</sup>

<sup>1)</sup> Valid positional data can be read once this time has elapsed.

### Interfaces

Electrical interface	PROFIBUS
Bus interface	PROFIBUS DP, RS-485 <sup>1) 2) 3)</sup>
Set (electronic adjustment)	Via PRESET pushbutton or protocol
Data protocol	Profile for encoder (07hex) - Class 2
Address setting	0 127, DIP switch or protocol
Data transmission rate (baud rate)	9.6 kBaud to 12 Mbaud, autodetect
Status information	LED green (running), LED red (bus activity)
Bus termination	DIP switch 4)

<sup>&</sup>lt;sup>1)</sup> EN 50 170-2.

### Electrical data

Connection type	Bus adapter with 3 x M14 screw fixings Bus adapter with 3 cable screw fixings
Operating voltage range	10 V 32 V
Max. power consumption without load	≤ 2 W
Reverse polarity protection	V
MTTFd: mean time to dangerous failure	150 years (EN ISO 13849-1) <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

<sup>&</sup>lt;sup>2)</sup> DIN 19245 Part 1-3.

<sup>&</sup>lt;sup>3)</sup> Electrically isolated through optocoupler.

<sup>&</sup>lt;sup>4)</sup> Should only be connected in the final device.

### Mechanical data


12, 16 mm and 1/2"
Stainless steel
Aluminum
Aluminum
0.6 kg
0.8 kg
0.5 Ncm
0.4 Ncm
≤ 600,000 rad/s²
3,000 rpm
153 gcm <sup>2</sup>
3,6 x 109 revolutions

<sup>1)</sup> Relates to devices with cable outlet.

### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating	IP 65 with shaft seal (acc. to IEC 60529)
Permissible relative humidity	98%
Operating temperature range	-20 °C +80 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	6 g/20 ms (according to EN 60068-2-27)
Resistance to vibrations	20 g/ 10 Hz 2,000 Hz

# Type code



<sup>&</sup>lt;sup>2)</sup> Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

# Ordering information

### Through hollow shaft


• Electrical interface: 10 V ... 32 V, PROFIBUS

Number of steps: ≤ 8,192
 Resolution: 8,192 x 8,192

Shaft diameter	Connection type	Туре	Part no.
4 /011	Bus adapter with 3 cable screw fixings	ATM90-PUG13X13	1030046
1/2"	Bus adapter with 3 x M14 screw fixings	ATM90-PUF13X13	1030043
12 mm	Bus adapter with 3 cable screw fixings	ATM90-PTG13X13	1030045
12 111111	Bus adapter with 3 x M14 screw fixings	ATM90-PTF13X13	1030042
16 mm	Bus adapter with 3 cable screw fixings	ATM90-PXG13X13	1030047
10 11111	Bus adapter with 3 x M14 screw fixings	ATM90-PXF13X13	1030044


# Dimensional drawings (dimensions in mm)

### Cable outlet



General tolerances according to DIN ISO 2768-mk

### Connector outlet



# General tolerances according to DIN ISO 2768-mk

① Minimum bend radius 40 mm

Hollow shaft	D1	D2	D3
12 mm	12.0 <sup>h7</sup>	12.0 <sup>F7</sup>	29.5
1/2"	12.7 <sup>h7</sup>	12.7 <sup>F7</sup>	29.5
16 mm	16.0 <sup>h7</sup>	16.0 <sup>F7</sup>	32.0

C-1	Stator coupling via cylindrical pin, (customer), Ø $\rm 6_{m6}$ as per DIN EN ISO 8734
C-2	Drive shaft (customer)
X-1	3x screw fixings for cable connection, metric M16 x 1.5, SW 17
A	When looking at the base plate (is used to define the direction of rotation)


# PIN assignment

# PROFIBUS DP (in/out)

PIN	:	Signal Explanation
1	RTS	Request To Send 1)
2	A	A cable PROFIBUS DP
3	N. C.	Not connected
4	В	B cable PROFIBUS DP
5	2M	O V (potential free) 2)
6	2P5	+ 5 V (potential free) 2)
7	N. C.	Not connected

<sup>&</sup>lt;sup>1)</sup> Use for external bus terminations or to supply the sender/receiver with a optical fiber transmission.

N. C. = Not connected.




# $U_{s}$

PIN	Signal	Explanation
1	U <sub>s</sub> (24 V)	Operating voltage
2	N. C.	Not connected
3	GND (0 V)	0 V (Gnd)
4	N. C.	Not connected
5	RTS	Request To Send 1)
6	N. C.	Not connected
7	N. C.	Not connected

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Signal is optional, serves to detect the direction of an optical fiber connection.

N. C. = Not connected.




 $<sup>^{\</sup>rm 2)}$  Signal is optional, serves to detect the direction of an optical fiber connection.

# Connection adapter

PIN	Signal	Explanation
1	U <sub>s</sub> (24 V)	Operating voltage
2	GND (0 V)	0 V (Gnd)
3	В	B cable PROFIBUS DP (out)
4	A	A cable PROFIBUS DP (out)
5	В	B cable PROFIBUS DP (in)
6	A	A cable PROFIBUS DP (in)
7	2P5	+ 5 V (potential free) 1)
8	2M	O V (potential free) 1)
9	RTS	Request To Send 2)

 $<sup>^{1)}</sup>$  Use for external bus terminations or to supply the sender/receiver with a optical fiber transmission.

 $<sup>^{\</sup>rm 2)}$  Signal is optional, serves to detect the direction of an optical fiber connection.



### Recommended accessories

# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		5 m	DOL-1205-G05MQ	6026006
	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm	10 m	DOL-1205-G10MQ	6026008
100		12 m	DOL-1205-G12MQ	6032636
		15 m	DOL-1205-G15MQ	6032637
		20 m	DOL-1205-G20MQ	6032638
		30 m	DOL-1205-G30MQ	6032639
		50 m	DOL-1205-G50MQ	6032861

Dimensional drawings → page K-725

### Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm Wire shielding: AL-PT foil, total shield, tin-plated C shield	5 m	STL-1205-G05MQ	6026005
		10 m	STL-1205-G10MQ	6026007
		12 m	STL-1205-G12MQ	6032635

Dimensional drawings → page K-725

### Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm $\dots$ 6 mm Head B: -	DOS-1204-G	6007302
	Head A: female connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm $\dots$ 9 mm Head B: -	DOS-1205-GQ	6021353
	Head A: female connector, M14, 7-pin, straight, shielded, for cable diameter 4 mm 8 mm Head B: -	DOS-1507-G	6027536

Dimensional drawings → page K-725

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm	By the meter	LTG-2102-MW	6021355

### Other plug connectors and cables

Figure	Brief description	Туре	Part no.
	Sales kit consisting of: 2 M14 male cable connectors, 7-pin (6027535) 1 M14 female cable connector, 7-pin (6027535)	DSC-1507-G	2029199

### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -	STE-1205-GQ	6021354
	Head A: male connector, M14, 7-pin, straight, shielded, for cable diameter 4 mm 8 mm Head B: -	STE-1507-G	6027535

Dimensional drawings → page K-725

<sup>→</sup> For additional accessories, please see page K-668 onwards

# **RELIABLE AND ESTABLISHED**





### **Product description**

The modular setup of its CoreTech technology enables the compact ARS60 absolute singleturn encoder to provide a customized solution for all applications. All common mechanical variants

are available with any number of steps between 2 and 32,768 and are either equipped with an SSI or parallel output, making the ARS60 a universal solution for nearly any application requirements

### At a glance

- Absolute singleturn encoder
- Resolution: up to 15 bit (32,768 steps)
- Electrical interface: SSI with gray or gray capped code type
- Electrical interface: Parallel with gray, gray capped, binary, BCD code type
- · Zero-set function

- Mechanical interfaces: face mount flange, servo flange, blind and through hollow shaft
- Enclosure rating: Up to IP66

### Your benefits

- Programmable resolution (up to 15 bit)
- Simple zero point adjustment directly on the encoder at the touch of a button or on a connecting wire (cable version)
- Suitable for all mounting methods thanks individual mechanical interfaces
- Application flexibility due to easily interchangeable collets for the blind hollow shaft and through hollow shaft



### More information

Fields of application
Detailed technical data
Ordering information
Dimensional drawings
PIN assignment
Signal outputs
Recommended accessories G-468

→ www.mysick.com/en/ARS60\_SSI\_Parallel

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



- · Electronics and solar industry
- Textile machinery
- Packaging industry
- High-bay warehouses

- Woodworking machines
- Mechanical engineering
- Automotive industry
- Material handling

### Detailed technical data

### Performance

Number of steps per revolution	00002 32,768 (see ordering information)
Max. number of revolutions	1
Error limits	
Binary number of steps	0.035°
Non-binary number of steps	0.046°
Repeatability	0.005°
Measurement step deviation	
Binary number of steps	0.005°
Non-binary number of steps	0.016°
Measurement step	360° / Number of lines per revolution
Initialization time	80 ms <sup>1)</sup>

 $<sup>^{\</sup>mbox{\tiny 1)}}\mbox{\sc Valid}$  positional data can be read once this time has elapsed.

### Electrical data

Electrical interface	SSI or parallel
Control input switching level	Logic H = $0.7 \times U_S$ Logic L = $0 \times \times 0.3 \times U_S$
Operation of SET button 1)	100 ms
Operating voltage range	10 V DC 32 V DC
Operating current	
SSI	Typ. 60 mA
Parallel	Typ. 90 mA
Code sequence	CW, increasing, when viewing the clockwise rotating shaft
Reverse polarity protection	V
MTTFd: mean time to dangerous failure	300 years (EN ISO 13849-1) <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

### Mechanical data

Shaft diameter	
Face mount flange	10 x 19 mm
Servo flange	6 x 10 mm
Blind hollow shaft 1)	6, 8, 10, 12, 14, 15 mm and 1/4", 3/8", 1/2"
Through hollow shaft 1)	6, 8, 10, 12 mm and 1/4", 3/8", 1/2"
Shaft material	Stainless steel
Flange material	Aluminum
Housing material	Aluminum
Mass <sup>2)</sup>	0.3 kg
Start up torque at 20 °C	
Face mount flange	0.4 Ncm
Servo flange	0.25 Ncm
Blind hollow shaft	0.6 Ncm
Through hollow shaft	2.2 Ncm
Operating torque at 20 °C	
Face mount flange	0.3 Ncm
Servo flange	0.2 Ncm
Blind hollow shaft	0.4 Ncm
Through hollow shaft	1.6 Ncm
Permissible shaft loading	
Face mount flange, servo flange	10 N radial 50 N axial
Permissible shaft movement of the drive element, static/dynamic	
Blind hollow shaft, through hollow shaft	$\pm$ 0.3/ $\pm$ 0.1 mm radial $\pm$ 0.5/ $\pm$ 0.2 mm axial
Max. angular acceleration	≤ 500,000 rad/s²
Operating speed 3)	
Face mount flange, servo flange	6,000 rpm with shaft seal 10,000 rpm without shaft seal, if the shaft seal has been removed by the customer
Blind hollow shaft, through hollow shaft	3,000 rpm
Rotor moment of inertia	
Face mount flange	54 gcm <sup>2</sup>
Servo flange	48 gcm <sup>2</sup>
Blind hollow shaft, through hollow shaft	See Figure 1 below.
Bearing lifetime	3,6 x 10° revolutions

<sup>1)</sup> Order collets for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories. No collets are necessary for 15 mm shaft diameter.

<sup>&</sup>lt;sup>2)</sup> Relates to devices with cable outlet.

<sup>&</sup>lt;sup>3)</sup> Take into account self-warming of 3.3 K per 1,000 rpm when designing operating temperature range

# G

### Ambient data

EMC	(according to EN 61000-6-2 and EN 61000-6-3) 1)
Enclosure rating (as per IEC 60529) <sup>2)</sup>	
Face mount flange, servo flange, blind hollow shaft: male connector outlet	IP 65
Face mount flange, servo flange, blind hollow shaft: cable outlet	IP 66
Through hollow shaft: male connector outlet	IP 64
Through hollow shaft: cable outlet	IP 64
Permissible relative humidity	90% (condensation of optical surfaces not permitted)
Operating temperature range	-20 °C +85 °C
Storage temperature range	-40 °C +100 °C
Resistance to shocks	50 g/ 11 ms (as per EN 60068-2-27)
Resistance to vibrations	20 g / 10 Hz - 2,000 Hz (according to EN 60068-2-6)

 $<sup>^{\</sup>scriptsize 1)}$  The EMC according to the standards quoted is achieved if shielded cables are used.

# Ordering information

Type code: ARS60 SSI, through hollow shaft

# Electrical interface A 10 ... 32 V, SSI/Gray B 10 ... 32 V, SSI/Gray, capped Mechanical design D Through hollow shaft 1) Connection type A Male connector M23, 12-pin, radial outlet K Cable, 11-wire, radial outlet, 1.5 m L Cable, 11-wire, radial outlet, 3.0 m Cable, 11-wire, radial outlet, 5.0 m Resolution Any number of steps from 00002 to 32768 possible. Always 5 characters in clear text.

### Example orders


· Through hollow shaft

Through hollow shaft design	Туре
10 32 Volt, SSI, Gray, M23 male connector, 12-pin, radial, number of steps 8,192	ARS60-ADA08192

<sup>&</sup>lt;sup>2)</sup> When mating connector is inserted.

<sup>&</sup>lt;sup>1)</sup> Order collet for 6, 8, 10 and 12 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories).

### Type code: ARS60 parallel, through hollow shaft



<sup>1)</sup> Order collet for 6, 8, 10 and 12 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories).

### Example orders

• Through hollow shaft

Through hollow shaft design	Туре
10 32 Volt, Parallel, Gray, M23 male connector, 21-pin, radial, number of steps 8,192	ARS60-FDA08192

<sup>&</sup>lt;sup>2)</sup> For the following interfaces: 10 ... 32 V Parallel Gray; 10 ... 32 V Parallel Gray capped; 10 ... 32 V Parallel BIN. 00002 to 07999 steps possible for the electrical interface: 10 ... 32 V, Parallel BCD. Always 5 characters in clear text.

### Type code: ARS60 SSI

# **Electrical interface** A 10 ... 32 V, SSI/Gray B 10 ... 32 V, SSI/Gray, capped Mechanical design 4 | Solid shaft, face mount flange, Ø 10 mm, length 19 mm 1 Solid shaft, servo flange, Ø 6 mm, length 10 mm A Blind hollow shaft 1) Connection type Male connector M23, 12-pin, radial outlet M23 male connector, 12-pin, axial outlet Cable, 11-wire, radial outlet, 1.5 m K Cable, 11-wire, radial outlet, 3.0 m M Cable, 11-wire, radial outlet, 5.0 m R Cable, 11-wire, axial outlet, 1.5 m Cable, 11-wire, axial outlet, 3.0 m T Cable, 11-wire, axial outlet, 5.0 m Resolution Any number of steps from 00002 to 32768 possible. Always 5 characters in clear text. A R S 6 0

### Example orders

· Face mount flange

Face mount flange design	Туре
10 32 Volt, SSI, Gray, M23 male connector, 12-pin, radial, number of steps 8,192	ARS60-A4A08192

· Servo flange

Servo flange design	Туре
10 32 Volt, SSI, Gray, M23 male connector, 12-pin, radial, number of steps 8,192	ARS60-A1A08192

· Blind hollow shaft

Blind hollow shaft design	Туре
10 32 Volt, SSI, Gray, M23 male connector, 12-pin, radial, number of steps 8,192	ARS60-AAA08192



<sup>&</sup>lt;sup>1)</sup> Order collet for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.

### Type code: ARS60 parallel

### **Electrical interface**

F 10 ... 32 V, Parallel, Gray

G 10 ... 32 V, Parallel, Gray, capped

H 10 ... 32 V, Parallel, BIN

J 10 ... 32 V, Parallel, BCD

### Mechanical design

4 Solid shaft, face mount flange, Ø 10 mm, length 19 mm

1 Solid shaft, servo flange, Ø 6 mm, length 10 mm

A Blind hollow shaft 1)

### Connection type

A Male connector, M23, 21-pin, radial outlet

B Male connector, M23, 21-pin, axial outlet

K Cable, 22-wire, radial outlet, 1.5 m

L Cable, 22-wire, radial outlet, 3.0 m

M Cable, 22-wire, radial outlet, 5.0 m


R Cable, 22-wire, axial outlet, 1.5 m

S Cable, 22-wire, axial outlet, 3.0 m

T Cable, 22-wire, axial outlet, 5.0 m

### Resolution

Any number of steps from 00002 to 32768 possible. Always 5 characters in clear text. <sup>2)</sup>



<sup>&</sup>lt;sup>1)</sup> Order collet for 6, 8, 10, 12 and 14 mm or 1/4", 3/8" and 1/2" as separate extra accessories (see recommended accessories). No collets are necessary for 15 mm shaft diameter.

### Example orders

· Servo flange

Servo flange design	Туре
10 32 Volt, Parallel, Gray, M23 male connector, 21-pin, radial, number of steps 8,192	ARS60-F1A08192

· Face mount flange

Face mount flange design	Туре
10 32 Volt. Parallel. Grav. M23 male connector. 21-pin. radial. number of steps 8.192	ARS60-F4A08192

Blind hollow shaft

Blind hollow shaft design	Туре
10 32 Volt, Parallel, Grav. M23 male connector, 21-pin, radial, number of steps 8.192	ARS60-FAA08192




<sup>&</sup>lt;sup>2)</sup> For the following interfaces: 10 ... 32 V Parallel Gray; 10 ... 32 V Parallel Gray capped; 10 ... 32 V Parallel BIN. 00002 to 07999 steps possible for the electrical interface: 10 ... 32 V, Parallel BCD. Always 5 characters in clear text.

# G

### Dimensional drawings (dimensions in mm)


### Servo flange, radial



# General tolerances according to ISO 2768-mk

① R = min. bend radius 40 mm


### Servo flange, axial



### General tolerances according to ISO 2768-mk


① R = min. bend radius 40 mm

### Face mount flange, radial




### General tolerances according to ISO 2768-mk

① R = min. bend radius 40 mm




### Blind hollow shaft, axial




### General tolerances according to ISO 2768-mk

① R = min. bend radius 40 mm



### Through hollow shaft, radial



### General tolerances according to ISO 2768-mk


- ① R = min. bend radius 40 mm
- $\ensuremath{\mathfrak{D}}$  Min. shaft insertion depth 15 mm

G-463

# PIN assignment

Pin assignment for design with 12-pin male connector; SSI interface

Signal	12-pin male device connector	11-wire cable outlet
GND	1	Blue
Data (+)	2	White
Clock (+)	3	Yellow
N. C.	4	-
V/¯R	5	Pink
N. C.	6	-
N. C.	7	-
$U_S$	8	Red
SET	9	Orange
Data (-)	10	Brown
Clock (-)	11	Violet
N. C.	12	-



View of 12-pin M23 device connector on SSI encoder

### Pin assignment for design with 21-pin male connector, single; parallel interface

PIN	Wire colors at cable outlet	Binary	Gray	BCD	Explanation
1	Violet	20	$G_0$	2º v.10º	
2	White/brown	2 <sup>1</sup>	$G_\mathtt{1}$	2 <sup>1</sup> v.10 <sup>0</sup>	
3	White/green	<b>2</b> <sup>2</sup>	$G_2$	2 <sup>2</sup> v.10 <sup>0</sup>	
4	White/yellow	2 <sup>3</sup>	$G_3$	2 <sup>3</sup> v.10 <sup>0</sup>	
5	White/gray	24	$G_4$	2º v.10¹	
6	White/pink	25	$G_5$	2 <sup>1</sup> v.10 <sup>1</sup>	
7	White/blue	2 <sup>6</sup>	$G_6$	2 <sup>2</sup> v.10 <sup>1</sup>	
8	White/red	27	G <sub>7</sub>	2 <sup>3</sup> v.10 <sup>1</sup>	
9	White/black	28	$G_8$	2º v.10²	
10	Brown/green	2 <sup>9</sup>	$G_9$	$2^1 \text{ v.} 10^2$	
11	Brown/yellow	210	G <sub>10</sub>	2 <sup>2</sup> v.10 <sup>2</sup>	
12	Brown/gray	211	G <sub>11</sub>	2 <sup>3</sup> v.10 <sup>2</sup>	Data cables Outputs
13	Brown/pink	212	G <sub>12</sub>	2º v.10³	Catpate
14	Brown/blue	2 <sup>13</sup>	G <sub>13</sub>	2 <sup>1</sup> v.10 <sup>3</sup>	
15	Brown/red	214	G <sub>14</sub>	2 <sup>2</sup> v.10 <sup>3</sup>	
16	Green	Parity	Parity	Parity	
17	Pink	Store_	Store_	Store_	
18	Yellow	Enable_	Enable_	Enable_	
19	Brown	V/R_	V/R_	V/R_	
1)	Gray	SET	SET	SET	
20	Blue	GND	GND	GND	
21	Red	U <sub>s</sub>	U <sub>s</sub>	U <sub>s</sub>	
Housing		Screen	Screen	Screen	

<sup>1)</sup> Set cable only possible at cable outlet.

U<sub>s</sub> Encoder's supply voltage (always observe the encoder's type label prior to commissioning).

GND Encoder ground connection; electrically isolated from the housing. The voltage relating to GND is U<sub>s</sub>.


V/R\_ Forwards/Reverse: This input programs the counting direction for the encoder. When it is not connected, this input is set to HIGH. If the encoder shaft is rotated clockwise (to the right) as viewed when facing the drive shaft, it counts in ascending order. If it should count in ascending order when the shaft is rotated counterclockwise (to the left), then this connection must be permanently set to LOW level (GND).

Enable\_ This input activates the data output driver if a LOW level is connected. When it is not connected, this input is set to LOW. The outputs are in tri-state mode when the level is HIGH.

Store\_ This input stores the encoder data in gray code when connecting a LOW level. This helps to prevent read errors if the output data is requested in binary code. If this input is set to LOW, the data at the encoder output is stable, regardless of whether the input shaft is rotating. When it is not connected, this input is set to HIGH.

Parity This output supplies a HIGH level when the checksum is even.

SET This input is for electronic zeroing. If the SET cable is set to  $U_S$  for more than 100 ms, the mechanical position corresponds to the value 0.




View of 21-pin M23 device connector on parallel encoder

### Signal outputs

### SSI data format for resolutions $\leq 8,192 (1-13 \text{ bit})$

In order to ensure compatibility with the data formats available on the market, the ARS60 distinguishes between two data formats: The first data format is for encoders with resolutions up to 13 bit.

This is the standard data format for the singleturn absolute encoder.




SSI data format for resolutions > 8,192 (14 and 15 bit)

All data is transmitted MSB-justified. Two errorbits follow the 15 data bits.

### Error 1 (E1) = Position error


An error has occurred during the position detection process since the last SSI transmission. This errorbit is deleted during the next SSI transmission.

Error 2 (E2) = Sender monitoring



Parallel interface (output driver 7272 push pull)

- Tri-state-compatible
- Short-circuit protected
- Reverse polarity protection
- Integrated transient protection diodes





# Technical data for parallel interface

Id <sub>H</sub> max. at +85 C ,8 nF load 6,000 rpm	30 mA
Id <sub>L</sub> max. at +85 °C ,8 nF load 6,000 rpm	30 mA
Output saturation level (H level)	
At Id <sub>H</sub>	10 mA 2.8 V
U <sub>S</sub> -Ud <sub>H</sub>	30 mA 3.0 V
Output saturation level (L level)	
At Id <sub>L</sub>	10 mA 0.4 V
$Ud_L$	30 mA 2.0 V
Position repeatability (depending on encoder resolution and output code)	
Parallel gray code	60 μs
Parallel BIN code	60 μs
Parallel BCD code	200 μs

# Recommended accessories

# Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
()	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164

Dimensional drawings → page K-725

#### Flanges

#### Flange plate

Figure	Brief description	Туре	Part no.
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-050	2029160
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225
(1)	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161



Dimensional drawings → page K-725

# Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Brief description	Туре	Part no.
<b>(a)</b>	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988
0	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678
	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989
	Measuring wheel with O-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222
	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634
	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278

Dimensional drawings → page K-725

# Mounting bell

Figure	Brief description	Туре	Part no.
	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987

Dimensional drawings → page K-725

## Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

Dimensional drawings → page K-725

## Miscellaneous

Figure	Brief description	Туре	Part no.
	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872
97	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728
	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591

# Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
Tim-	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983
	Bellows coupling, shaft diameter 10 mm/12 mm; maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984
	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406
	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°, max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179
0	Bar coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407
	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178
	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/ wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408
	Double-loop coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0610-D	5326697
	Double-loop coupling, shaft diameter 8 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-0810-D	5326704
	Double-loop coupling, shaft diameter 10 mm/10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1010-D	5326703
	Double-loop coupling, shaft diameter 10 mm/12 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, -30° to +80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702
	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, -10° to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985
	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^{\circ}$ to $+80^{\circ}$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986

Dimensional drawings → page K-725



# Connectivity

## Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		1.5 m	DOL-2312-G1M5MA2	2029206
	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm $^2$ + 2 x 0.14 mm $^2$ , Ø 7.8 mm $^4$	3 m	DOL-2312-G03MMA2	2029207
-		5 m	DOL-2312-G05MMA2	2029208
		10 m	DOL-2312-G10MMA2	2029209
		20 m	DOL-2312-G20MMA2	2029210
		30 m	DOL-2312-G30MMA2	2029211
		1.5 m	DOL-2321-G1M5PA4	2029218
	Head A: female connector, M23, 21-pin, straight Head B: cable Cable: PUR, halogen-free, shielded, 20 x 0.14 mm², 2 x 0.25 mm², Ø 7.8 mm²)	3 m	DOL-2321-G03MPA4	2029219
		5 m	DOL-2321-G05MPA4	2029220
		10 m	DOL-2321-G10MPA4	2029221
		20 m	DOL-2321-G20MPA4	2029222

<sup>1)</sup> For ARS60 SSI.

Dimensional drawings → page K-725

## Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: - Operating temperature: -40 °C +125 °C	DOS-2312-G02	2077057
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm Head B: - Operating temperature: –20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M23, 21-pin, straight, shielded, for cable diameter 5.5 mm 12 mm Head B: -	DOS-2321-G	6027539
1 let	Head A: female connector, D-Sub, 37-pin, straight, shielded Head B: -	DOS-0D37-G	2029224

Dimensional drawings → page K-725



<sup>&</sup>lt;sup>2)</sup> For ARS60 Parallel.

## Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15$ mm <sup>2</sup> , Ø 5.6 mm	By the meter	LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	By the meter	LTG-2411-MW	6027530
_	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.25$ mm <sup>2</sup> + $2\times0.5$ mm <sup>2</sup> + $2\times0.14$ mm <sup>2</sup> , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<b>\</b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2612-MW	6028516
	Head A: cable Head B: cable Cable: PUR, halogen-free, shielded, 20 x 0.14 mm², 2 x 0.25 mm², Ø 7.8 mm	By the meter	LTG-2622-MW	6027532

## Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
100	Head A: male connector, D-Sub, 15-pin, straight, shielded Head B: -	STE-0D15-G	2029223
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40  ^{\circ}\text{C} \dots +125  ^{\circ}\text{C}$	STE-2312-G01	2077273

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards



# COMPACT, UNIVERSAL, INTUITIVE







#### **Product description**

The ACS36 (singleturn) and ACM36 (multiturn) encoder families have an analog interface with a maximum resolution of up to 3,723 steps (for singleturn and multiturn). Using the teach-in function on the membrane keyboard, the measuring

range can be intuitively programmed directly on the device in just a few clicks. A current signal of 4–20 mA or a voltage signal of 0–10 V is output depending on the device version.

#### At a glance

- Compact 36 mm absolute encoder with up to 3,723 steps (for singleturn and multiturn)
- · Servo flange
- · Radial cable outlet
- Analog interface 4 to 20 mA or 0 to 10 V
- Programming via keypad on the encoder
- IP 65 protection class
- Operating temperature: -30 °C ... +80 °C

#### Your benefits

- Intuitive configuration of the measuring range directly on the device using membrane keyboard (teach-in function) saves time and requires no special expertise.
- The compact size (36-mm format) allows the encoder to be used in confined spaces and thus provides greater freedom for development and machine design.
- The analog interfaces (current/ voltage) offer a low-cost solution for detecting the position and path, and thereby help to reduce overall system costs.

# $\epsilon$

#### **Additional Information**

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawings
PIN assignment
Electrical wiring
Resolution diagram
Recommended accessories G-479

→ www.mysick.com/en/ACS\_ACM36

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

Measurement of the absolute position in a variety of industries, machines and equipment, for example:

- Automatically guided vehicle systems (AGS)
- Industrial trucks
- · Commercial vehicles

- Packaging
- Logistics applications
- Mechanical engineering
- Medical technology

#### Detailed technical data

# Performance

	ACS36-K1K0-K01	ACS36-L1K0-K01	ACM36-K1K0-K01	ACM36-L1K0-K01
Max. number of revolutions	1		16	
Resolution per measuring step	5.4 40.2 $\mu$ A <sup>1)</sup>	$2.7 \dots 25.1$ mV $^{1)}$	5.2 µA 1)	2.7 mV <sup>1)</sup>
Measuring range	0° 360°, programma	able	0° 5,760°, programmable	
Minimum measuring range	35° 336°			
Accuracy	$\pm0.2$ %, based on the programmed angle			

 $<sup>^{1)}\</sup>mbox{See}$  measuring step diagram/calculation formula for details.

#### Interfaces

	ACS36-K1K0-K01	ACS36-L1K0-K01	ACM36-K1K0-K01	ACM36-L1K0-K01
Electrical interface	Analog, 4 mA 20 mA	Analog, 0 V 10 V	Analog, 4 mA 20 mA	Analog, 0 V 10 V

## Mechanical data

	ACS36-K1K0-K01	ACS36-L1K0-K01	ACM36-K1K0-K01	ACM36-L1K0-K01
Length of the shaft	12.4 mm			
Mass	0.1 kg			
Shaft material	Stainless steel 1,4305			
Flange material	AIMgSi			
Housing design	36 mm			
Housing material	AIMgSi			
Cable material	PVC			
Start up torque	0.5 Ncm (+20 °C)			
Operating torque	0.2 Ncm (+20 °C)			
Permissible shaft loading	20 N (axial) 40 N (radial)			
Maximum operating speed	3,000 rpm		10,000 rpm	
Rotor moment of inertia	10 gcm <sup>2</sup>			
Bearing lifetime	1 x 10^6 revolutions			
Max. angular acceleration	≤ 500,000 rad/s²			

#### Electrical data

	ACS36-K1K0-K01	ACS36-L1K0-K01	ACM36-K1K0-K01	ACM36-L1K0-K01
Connection type	Cable, radial, 1.5 m			
Operating voltage range	19 V DC 33 V DC			
Current consumption	< 80 mA			
Min. load resistance	-	≥ 10 kΩ	-	≥ 10 kΩ
Max. load resistance	≤ 600 Ω	-	≤ 600 Ω	_

 $<sup>^{1)}</sup>$ Factory setting is CW – CCW can be programmed on the encoder




#### Ambient data


EMC	EN 61000-6-2, EN 61000-6-4
Enclosure rating	IP 65
Permissible relative humidity	90%
Operating temperature range	-30 °C +80 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	25 g, 11 ms (EN 60068-2-27)
Resistance to vibrations	4 g, 5 Hz 100 Hz (EN 60068-2-6)

# Type code

# Singleturn



#### Multiturn



# G


# Ordering information

Shaft diameter: 6 mm, 12.4 mm
Connection type: cable, radial, 1.5 m

Electrical interface	Number of steps	Resolution	Туре	Part no.
Analog, 4 mA 20 mA	2,979	0.09° 0.12° 1)	ACS36-K1K0-K01	6053311
Analog, 0 V 10 V	3,723	0.09° 0.10° 1)	ACS36-L1K0-K01	6052345
Analog, 4 mA 20 mA	2,979	0.11° 1.93° 1)	ACM36-K1K0-K01	6039751
Analog, 0 V 10 V	3,723	0.09° 1.55° 1)	ACM36-L1K0-K01	6039752

<sup>1)</sup> See resolution diagram.


# Dimensional drawings (dimensions in mm)



## PIN assignment


gn	+24 V
ws	Output
br	0 V

## **Electrical wiring**



3 wire technique power output

At a supply voltage of 18 V, the internal resistance of the measuring device must not exceed 600 Ohm.




Voltage output


For an accurate measurement, the internal resistance of the measuring device must be equal to 10 kOhm.

# Resolution diagram

#### Singleturn, power output



#### Singleturn, voltage output



Number of steps in angle range Steps (4 ... 20 mA) = 2979


number of steps in angle range Steps =  $\frac{Angle \times 1024}{360^{\circ}}$ 

Number of steps in angle range Steps (0 ... 10 V) = 3723

#### Multiturn, power output


Steps =  $\frac{Angle \times 4096}{360^{\circ}}$ 

#### Resolution ACM36



Number of steps in angle range Stens (0 ... 10 V) = 2979

## Multiturn, voltage output



Number of steps in angle range Steps (0 ... 10 V) = 3723

## Recommended accessories

# Mounting systems

Shaft adaptation

Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
	Bellows coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
(i	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, -10° to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985

Dimensional drawings → page K-725

# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		1.5 m	DOL-1205-G1M5ACS- CO	6049451
	Head A: female connector, M12, 5-pin, straight, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm	3 m	DOL-1205-G03MACS- CO	6049452
		5 m	DOL-1205-G05MACS- CO	6049453
		10 m	DOL-1205-G10MACS- CO	6049454

G

Figure	Brief description	Length of cable	Туре	Part no.
		1.5 m	DOL-1205- W1M5ACSCO	6049455
	Head A: female connector, M12, 5-pin, angled, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm	3 m	DOL-1205- W03MACSCO	6049456
		5 m	DOL-1205- W05MACSCO	6049457
		10 m	DOL-1205- W10MACSCO	6049458

Dimensional drawings → page K-725

#### Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	DOS-1205-G	6009719

Dimensional drawings → page K-725

#### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	STE-1205-G	6022083

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards

G

# COMPACT, UNIVERSAL, INTUITIVE





## **Product description**

The ACM60 (multiturn) encoder family has an analog interface with a maximum overall resolution of up to 13,107 steps. Using the teach-in function on the membrane keyboard, the measuring range can be intuitively programmed directly

on the device with just a few clicks. A current signal of 4–20 mA or a voltage signal of 0–10 V is output depending on the device version.

#### At a glance

- Compact 60 mm absolute encoder with up to 13,107 steps
- · Servo flange
- Radial connector outlet
- Analog interface 4 to 20 mA or 0 to 10 V
- Programming via keypad on the encoder
- IP 68 protection class
- Operating temperature: -30 °C ... +80 °C

#### Your benefits

- Intuitive configuration of the measuring range directly on the device using membrane keyboard (teach-in function) saves time and requires no special expertise.
- The compact size (including M12 connection technology) allows the encoder to be used in confined spaces and thus provides greater freedom for development and machine design.
- The analog interfaces (current/ voltage) offer a low-cost solution for detecting the position and path, and thereby help to reduce overall system costs.

# $\epsilon$

#### **Additional Information**

Fields of application
Detailed technical data
Type code
Ordering information
Dimensional drawings
PIN assignment
Electrical wiring
Resolution diagram
Recommended accessories G-487

→ www.mysick.com/en/ACM60

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

Measurement of the absolute position in a variety of industries, machines and equipment, for example:

- Automatically guided vehicle systems (AGS)
- · Industrial trucks
- · Commercial vehicles

- Packaging
- Logistics applications
- Mechanical engineering
- Medical technology

#### Detailed technical data

## Performance

	ACM60B-S1KE13x06 ACM60B-S1LE13x06	
Number of revolutions	64	
Resolution per measuring step	$1.5 \dots 8.8~\mu A^{\ 1)}$ $0.8 \dots 5.5~mV^{\ 1)}$	
Measuring range	0° 23,040°, programmable	
Minimum measuring range	640°	
Accuracy	± 0.1%, based on the programmed angle	

 $<sup>^{\</sup>mbox{\tiny 1)}}\mbox{See}$  measuring step diagram/calculation formula for details.

#### Interfaces

	ACM60B-S1KE13x06	ACM60B-S1LE13x06
Electrical interface	Analog, 4 mA 20 mA	Analog, 0 V 10 V

#### Mechanical data

Length of the shaft	10 mm
Mass	0.4 kg
Shaft material	Stainless steel
Flange material	Aluminum
Housing design	60 mm
Housing material	Aluminum die cast
Start up torque	0.05 Ncm (+20 °C)
Operating torque	0.3 Ncm (+20 °C)
Permissible shaft loading	30 N (axial) 60 N (radial)
Maximum operating speed	10,000 rpm
Rotor moment of inertia	30 gcm <sup>2</sup>
Bearing lifetime	2 x 10^9 revolutions
Max. angular acceleration	≤ 500,000 rad/s²

# Electrical data


	ACM60B-S1KE13x06	ACM60B-S1LE13x06
Connection type	M12 male connector, 5-pin, radial	
Operating voltage range	18 V DC 33 V DC	
Current consumption	< 80 mA	
Min. load resistance	-	≥ 10 kΩ
Max. load resistance	≤ 600 Ω	-
Code sequence	CW 1)	
Reverse polarity protection	V	
Electrical wiring	3- or 4-wire, see figure	4-wire, see figure

<sup>1)</sup> Factory setting is CW - CCW can be programmed on the encoder

# Ambient data

EMC	EN 61000-6-2, EN 61000-6-4
Enclosure rating	IP 68
Permissible relative humidity	90%
Operating temperature range	-30 °C +80 °C
Storage temperature range	-40 °C +100 °C, without packaging
Resistance to shocks	25 g, 11 ms (EN 60068-2-27)
Resistance to vibrations	4 g, 5 Hz 100 Hz (EN 60068-2-6)

# Type code



# Ordering information

• Shaft diameter: 6 mm, 10 mm

• Connection type: M12 male connector, 5-pin, radial


Electrical interface	Number of steps	Resolution	Туре	Part no.
Analog, 4 mA 20 mA	≤ 10,486	0.35° 2.20° 1)	ACM60B-S1KE13x06	6045312
Analog, 0 V 10 V	≤ 13,107	0.35° 1.76° 1)	ACM60B-S1LE13x06	6045313

<sup>1)</sup> See resolution diagram.



# G

# Dimensional drawings (dimensions in mm)




## PIN assignment




1	GND
2	24 V
3	Output GND
4	Output 4 20 mA
5	n.c.

# **Electrical wiring**


#### Power output





3 Leitertechnik Stromausgang 4 Leitertechnik Stromausgang

At a supply voltage of 18 V, the internal resistance of the measuring device must not exceed 600 ohm.



Voltage output

For an accurate measurement, the internal resistance of the measuring device must be equal to 10 kOhm.


# Resolution diagram

#### Power output

Resolution (Steps)

0°640°





Programmable angle (degrees)

3,686°


Calculation formula for number of steps in angle range Steps =  $\frac{Angle \times 1024}{360^{\circ}}$ 


Number of steps in angle range

Steps (0 ... 10 V) = 10485

23,040°

# Voltage output





Calculation formula for number of steps in angle range

Steps =  $\frac{Angle \times 1024}{360^{\circ}}$ 

Number of steps in angle range Steps (0 ... 10 V) = 13107

## Recommended accessories

# Mounting systems

Shaft adaptation

Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981
	Bellows coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30° to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982
(i	Spring washer coupling, shaft diameter 6 mm/10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, -10° to +80°C, max. torque 60 Ncm; material: aluminum flange, fiber-glass reinforced polyamide membrane and tempered steel coupling pin	KUP-0610-F	5312985

Dimensional drawings → page K-725

# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		1.5 m	DOL-1205-G1M5ACS- CO	6049451
	Head A: female connector, M12, 5-pin, straight, A-coded Head B: cable	3 m	DOL-1205-G03MACS- CO	6049452
	Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm $^2$ , Ø 5.9 mm	5 m	DOL-1205-G05MACS- CO	6049453
		10 m	DOL-1205-G10MACS- CO	6049454
		1.5 m	DOL-1205- W1M5ACSCO	6049455
	Head A: female connector, M12, 5-pin, angled, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $5 \times 0.34 \text{ mm}^2$ , Ø 5.9 mm	3 m	DOL-1205- W03MACSCO	6049456
		5 m	DOL-1205- W05MACSCO	6049457
		10 m	DOL-1205- W10MACSCO	6049458

Dimensional drawings → page K-725

Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	DOS-1205-G	6009719

Dimensional drawings → page K-725

## Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	STE-1205-G	6022083

Dimensional drawings → page K-725

→ For additional accessories, please see page K-668 onwards

G



# SAFETY ENCODERS

#### Safety in motion – functional safety encoders

SICK's reliable encoders assist in the implementation of safety functions, facilitating safe and efficient machine operation. This is backed up by SICK's many years of safety expertise, an international service and training network, and a range of optimized system solutions. Functional safety encoders generate information about position, angle, and revolution counts, with a particular emphasis on mechanical and electrical safety. By offering these encoders along with

reliable control solutions, SICK can offer all of the various components required for the implementation of comprehensive safety solutions under one roof.

#### Your benefits

- Optimal protection for persons, machinery, and systems
- Certified safety products for compliance with legal requirements

- Enhanced efficiency and productivity thanks to reliable drive monitoring
- Increased machine availability afforded by a rugged, fail-safe design
- Perfect adaptation to application-specific requirements due to wide range of variants
- Intelligent system layout thanks to compact design
- Time and cost savings due to simple and efficient device implementation





Applications
DFS60S Pro



# TYPICAL SAFETY ENCODER APPLICATIONS

Incremental encoders for functional safety generate information about position, angle, and revolution counts. When combined with a safe evaluation unit, this enables users to meet the safety function requirements set out in IEC61800-5-2. Safety encoders can be used in a variety of applications in factory and logistics automation.

Safe monitoring of automated guided systems



The safety encoder provides information on the speed and rotational direction of the driver and thus on the speed and direction of the automated guided system.

As shown here, the encoder can be installed directly on the motor or, alternatively, on an axle. Hollow shaft encoders are normally used for automated guided systems.

The safety encoder is connected to a central safety controller, e.g., on the Flexi Soft Drive Monitor, enabling you to monitor the speed and brake ramp of the automated guided system. As a result, the safety laser scanner's protective fields can be adapted to suit the conditions at hand.



# Safety functions in stationary machines



Stationary machines are often equipped with mechanical solutions, such as doors or flaps, to separate the user from hazardous points. When working on machines in maintenance or setup mode, the safe speed monitor reduces the risk of injury and increases productivity.

To achieve this, the machine speed is reduced and monitored for safety, enabling the operator to conduct manual work safely in the hazardous area.

The DFS60S Pro safety encoder provides information on the speed and rotational direction of the axis and enables the corresponding safety functions to be carried out.

# Safe drive monitoring in asynchronous motors



The DFS60S Pro safety encoder is the ideal solution for safe drive monitoring, particularly in versatile asynchronous motors. Equipped with a sine-cosine interface, the incremental encoder can be used for both functional safety and in automation and safety technology.





# PRODUCT FAMILY OVERVIEW



Technical data overview  Safety integrity level  Performance level  PL d (EN ISO 13849)  Category  3 (EN ISO 13849)  Encoder interface  4.5 V 32 V, SinCos 1.0 V <sub>ss</sub> (differential)  Mechanical design  Solid shaft, flattened, servo flange Solid shaft, flattened, face mount flange Solid shaft with feather key, servo flange Solid shaft with feather key, face mount flange Blind hollow shaft with feather key groove Through hollow shaft with feather key groove  Connection type  M23 male connector, 12-pin M12 male connector, 8-pin Cable, 8-wire (depends on type)  Operating temperature range  -30 °C +95 °C (depends on type)  IP 65 (as per IEC 60529)		
Performance level Category 3 (EN ISO 13849)  Encoder interface 4.5 V 32 V, SinCos 1.0 V <sub>SS</sub> (differential)  Mechanical design Solid shaft, flattened, servo flange Solid shaft, flattened, face mount flange Solid shaft with feather key, servo flange Solid shaft with feather key, face mount flange Solid shaft with feather key groove Through hollow shaft with feather key groove Through hollow shaft with feather key groove  Connection type  M23 male connector, 12-pin M12 male connector, 8-pin Cable, 8-wire (depends on type)  Operating temperature range  -30 °C +95 °C (depends on type)  Enclosure rating	Technical data overview	
Category Encoder interface 4.5 V 32 V, SinCos 1.0 V <sub>SS</sub> (differential)  Mechanical design Solid shaft, flattened, servo flange Solid shaft, flattened, face mount flange Solid shaft with feather key, servo flange Solid shaft with feather key, face mount flange Solid shaft with feather key froove Through hollow shaft with feather key groove Through hollow shaft with feather key groove  Connection type  M23 male connector, 12-pin M12 male connector, 8-pin Cable, 8-wire (depends on type)  Operating temperature range Enclosure rating  IP 65	Safety integrity level	SIL2 (IEC 61508), SILCL2 (IEC 62061)
Encoder interface  4.5 V 32 V, SinCos 1.0 V <sub>SS</sub> (differential)  Mechanical design  Solid shaft, flattened, servo flange Solid shaft, flattened, face mount flange Solid shaft with feather key, servo flange Solid shaft with feather key, face mount flange Blind hollow shaft with feather key groove Through hollow shaft with feather key groove  Connection type  M23 male connector, 12-pin M12 male connector, 8-pin Cable, 8-wire (depends on type)  Operating temperature range  -30 °C +95 °C (depends on type)  Enclosure rating	Performance level	PL d (EN ISO 13849)
Mechanical design  Solid shaft, flattened, servo flange Solid shaft, flattened, face mount flange Solid shaft with feather key, servo flange Solid shaft with feather key, face mount flange Blind hollow shaft with feather key groove Through hollow shaft with feather key groove  Connection type  M23 male connector, 12-pin M12 male connector, 8-pin Cable, 8-wire (depends on type)  Operating temperature range Enclosure rating  IP 65	Category	3 (EN ISO 13849)
Solid shaft, flattened, face mount flange Solid shaft with feather key, servo flange Solid shaft with feather key, face mount flange Blind hollow shaft with feather key groove Through hollow shaft with feather key groove  Connection type  M23 male connector, 12-pin M12 male connector, 8-pin Cable, 8-wire (depends on type)  Operating temperature range  -30 °C +95 °C (depends on type)  Enclosure rating	Encoder interface	4.5 V 32 V, SinCos 1.0 V <sub>ss</sub> (differential)
M12 male connector, 8-pin Cable, 8-wire (depends on type)  Operating temperature range Enclosure rating  M12 male connector, 8-pin Cable, 8-wire (depends on type)  Fig. 195 °C (depends on type)  IP 65	Mechanical design	Solid shaft, flattened, face mount flange Solid shaft with feather key, servo flange Solid shaft with feather key, face mount flange Blind hollow shaft with feather key groove
Enclosure rating IP 65	Connection type	M12 male connector, 8-pin
	Operating temperature range	-30 °C +95 °C (depends on type)
	Enclosure rating	

#### At a glance

- Encoders for functional safety technology: SIL2 (IEC 61508), SILCL2 (EN 62061), PL d (EN ISO 13849)
- Electrical interface: 4.5 V ... 32 V;  $\sin/\cos 1 V_{ss}$ ; 1,024 periods
- Face mount flange or servo flange, blind hollow shaft or through hollow shaft (assembly options with feather key)
- Universal cable outlet, M23 or M12 male connector, axial or radial
- Enclosure rating: IP 65
- Operating temperature: -30 °C ... +95 °C (depends on type)

Detailed information	-> 11.40
Detailed information	→ H-490



# SAFE, EASY, FLEXIBLE: ENCODERS FOR FUNC-TIONAL SAFETY



#### **Product description**

Safe electrical and mechanical design, easy system implementation, and flexible application possibilities. The DFS60S Pro is an incremental encoder for functional safety. It supports safety functions that conform to IEC 61800-5-2. The high enclosure rating, wide temperature

range, and wide-set ball bearings are the key to enhanced durability. They make the DFS60S Pro the universal motion control sensor for stationary and mobile safety applications.

#### At a glance

- Encoders for functional safety technology: SIL2 (IEC 61508), SILCL2 (EN 62061), PL d (EN ISO 13849)
- Electrical interface:
   4.5 V ... 32 V; sin/cos 1 V<sub>pp</sub>; 1,024 periods
- Face mount flange or servo flange, blind hollow shaft or through hollow shaft (assembly options with feather key)
- Universal cable outlet, M23 or M12 male connector, axial or radial
- Enclosure rating: IP 65
- Operating temperature range:
   -30 °C ... +95 °C

#### Your benefits

- Certified safety solution that ensures the best possible protection for persons, machinery, and systems
- Easy and practical implementation of safety functions using an all-in-one solution, safety functions with the Flexi Soft Drive monitor by SICK: safe stop 1 (SS1), safe stop 2 (SS2), safe operating stop (SOS), safe speed monitoring (SSM), safely limited speed (SLS), safe direction (SDI), safe brake control (SBC)
- Positive and non-positive connections for mechanical reliability
- Certified safety products reduce the scope of safety engineering
- Versatile connection options for high levels of flexibility and straightforward implementation
- Compact size for compatibility with applications in which installation space is limited









#### Additional information

Detailed technical data H-497
Type code
Ordering information
Dimensional drawings
Interface signals
PIN and wire allocation
Recommended accessories H-514



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Detailed technical data

#### Performance

Number of sine/cosine periods per revolution	1,024
Measurement increment	$0.3$ angular seconds for interpolation of the sine/cosine signals with e.g. 12 $bit^{1)}$
Typ. integral non-linearity	Typ. ± 45 angular seconds (with slackened stator coupling)
Differential non-linearity	± 7 angular seconds
Reference signal, number	1
Reference signal, position	90°, electric, logically gated with sine and cosine

<sup>1)</sup> Not safety-related.

## Mechanical data

	Solid shaft, servo flange	Solid shaft, face mount flange	Blind hollow shaft	Through hollow shaft	
Mechanical design	Solid shaft, flattened / key groove (depending		Blind hollow shaft with feather key groove	Through hollow shaft with feather key groove	
Shaft diameter	6 mm	10 mm	6 mm 8 mm 3/8" 10 mm 12 mm 1/2" 14 mm 15 mm 5/8" (depending on type)	nm 5" mm mm 2" mm mm	
Length of the shaft	10 mm	19 mm	-		
Shaft material	Stainless steel				
Flange material	Aluminum		Zinc die cast		
Housing material	Aluminum die cast				
Mass	Approx. 0.3 kg <sup>1)</sup>		Approx. 0.25 kg <sup>1)</sup>		
Start up torque	≤ 0.5 Ncm (at 20 °C)		≤ 0.8 Ncm (at 20 °C)		
Operating torque	≤ 0.3 Ncm (at 20 °C)		≤ 0.6 Ncm (at 20 °C)		
Permissible shaft loading	80 N (radial) 40 N (axial)		_		
Permissible shaft movement, static			± 0.3 mm (radial) ± 0.5 mm (axial)		
Permissible shaft movement, dynamic	-		± 0.05 mm (radial) ± 0.1 mm (axial)		
Max. angular acceleration	$\leq$ 500,000 rad/s <sup>2</sup>				
Maximum operating speed	Maximum operating speed 9,000 rpm <sup>2)</sup>		6,000 rpm <sup>2)</sup>		
Rotor moment of inertia	8 gcm <sup>2</sup> 5		56 gcm <sup>2</sup>		
Bearing lifetime	3.6 x 10^9 revolutions	3)			

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Relates to encoder with connector outlet.



<sup>&</sup>lt;sup>2)</sup> Take into account self-heating of 3.0 K per 1,000 revolutions/min at the operating temperature measuring point when designing the operating temperature range.

 $<sup>^{\</sup>scriptscriptstyle{(3)}}$  At maximum speed and temperature.

#### Electrical data

	Solid shaft, servo flange	Solid shaft, face mount flange	Blind hollow shaft	Through hollow shaft
Electrical interface	4.5 V 32 V, SinCos 1.	.0 V <sub>ss</sub> (differential)		
Connection type	M23 male connector, 12-pin, radial M23 male connector, 12-pin, axial M12 male connector, 8-pin, radial M12 male connector, 8-pin, radial M12 male connector, 8-pin, radial M12 male connector, 8-pin, axial Cable, 8-wire, universal, 0.5 m 1) Cable, 8-wire, universal, 1.5 m 1) Cable, 8-wire, universal, 1.5 m 1) Cable, 8-wire, universal, 3 m 1) Cable, 8-wire, universal, 5 m 1) Cable, 8-wire, universal, 10 m 1)		-pin, radial , 0.5 m <sup>1)</sup> , 1.5 m <sup>1)</sup> , 3 m <sup>1)</sup> , 5 m <sup>1)</sup>	
Initialization time	50 ms <sup>2)</sup>			
Maximum output frequency	≤ 153.6 kHz			
Load resistance	≥ 120 Ω			
Max. power consumption without load	≤ 0.7 W			
Reverse polarity protection	<b>√</b>			
Protection class	III (according to DIN EN 61140)			
Contamination rating	ation rating 2			
Short-circuit protection of the outputs	<b>✓</b> 3)			

<sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction. UL approval not available.

#### Safety characteristics

Safety integrity level	SIL2 (IEC 61508), SILCL2 (IEC 62061) 1)
Category	3 (EN ISO 13849)
Test rate	Not required
Maximum demand rate	Continuous (analog signals)
Performance level	PL d (EN ISO 13849) 1)
PFHd: Probability of dangerous failure per hour	1.7 x 10 <sup>-8 2)</sup>
T <sub>M</sub> (mission time)	20 years (EN ISO 13849)
Safety-related measuring increment	0.09°, quadrature analysis
Safety-related accuracy	± 0.09°

<sup>&</sup>lt;sup>1)</sup> For more detailed information on the exact configuration of your machine/system, please consult your local SICK subsidiary.

<sup>&</sup>lt;sup>2)</sup> The stated values apply to a diagnostic degree of coverage of 99%, which must be achieved by the external drive system, and an operating temperature of 95 °C.



 $<sup>^{\</sup>rm 2)}$  After this period valid signals can be read.

<sup>&</sup>lt;sup>3)</sup> Short-circuit to another channel or GND permitted for max. 30 sec. In the case of US ≤ 12 V additional short-circuit to US permitted for max. 30 sec.


#### Ambient data

EMC	According to EN 61000-6-2, EN 61000-6-3, and IEC 61326-3-1
Enclosure rating	IP 65 (according to IEC 60529) 1)
Permissible relative humidity	90%, condensation not permitted
Operating temperature range	
M23 male connector, 12-pin	-30 °C +95 °C <sup>2)</sup>
M12 male connector, 8-pin	-30 °C +95 °C <sup>2)</sup>
Cable, 8-wire	-30 °C +85 °C <sup>2)</sup>
Storage temperature range	-30 °C +85 °C, without packaging
Resistance to shocks	100 g, 6 ms (according to EN 60068-2-27) $^{\rm 3)}$
Resistance to vibrations	
M23 male connector, 12-pin	10 g, 10 Hz 1,000 Hz (EN 60068-2-6) <sup>4)</sup>
M12 male connector, 8-pin	30 g, 10 Hz 1,000 Hz (EN 60068-2-6) <sup>4)</sup>
Cable, 8-wire	30 g, 10 Hz 1,000 Hz (EN 60068-2-6) 3)

<sup>1)</sup> At least IP 65 when male connector connection has mating connector inserted.

#### Type code

#### Solid shaft



<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction. UL approval not available.




<sup>&</sup>lt;sup>2)</sup> Take into account self-heating of 3.0 K per 1,000 revolutions/min at the operating temperature measuring point when designing the operating temperature range.

<sup>&</sup>lt;sup>3)</sup> Checked during operation using vector length monitoring.

 $<sup>^{\</sup>mbox{\tiny 4)}}$  Checked during operation using vector length monitoring. Includes mating connector.

#### Hollow shaft



<sup>&</sup>lt;sup>1)</sup> The universal cable outlet is positioned so that it is possible to lay it without bends in a radial or axial direction. UL approval not available.

## **Ordering information**

Other device versions available here → www.mysick.com/en/DFS60S\_Pro

#### Solid shaft, flattened, face mount flange

Shaft diameter: 10 mm
Shaft length: 19 mm
Shaft mounting: M4 thread



Connection type	Туре	Part no.
M23 male connector, 12-pin, radial	DFS60S-S40A01024	1069518
M12 male connector, 8-pin, radial	DFS60S-S40C01024	1069519
Cable, 8-wire, universal, 1.5 m	DFS60S-S40K01024	1069520

## Solid shaft with feather key, face mount flange

Shaft diameter: 10 mm
Shaft length: 19 mm
Shaft mounting: M4 thread

Connection type	Туре	Part no.
M23 male connector, 12-pin, radial	DFS60S-SE0A01024	1069521
M12 male connector, 8-pin, radial	DFS60S-SE0C01024	1067912
Cable, 8-wire, universal, 1.5 m	DFS60S-SE0K01024	1067913

# Solid shaft, flattened, servo flange

• Shaft diameter: 6 mm Shaft length: 10 mm • Shaft mounting: M4 thread

Connection type	Туре	Part no.
M23 male connector, 12-pin, radial	DFS60S-S10A01024	1069522
M12 male connector, 8-pin, radial	DFS60S-S10C01024	1069517
Cable, 8-wire, universal, 1.5 m	DFS60S-S10K01024	1069523

# Solid shaft with feather key, servo flange

• Shaft diameter: 6 mm • Shaft length: 10 mm • Shaft mounting: M4 thread

Connection type	Туре	Part no.
M23 male connector, 12-pin, radial	DFS60S-SD0A01024	1067910
M12 male connector, 8-pin, radial	DFS60S-SD0C01024	1069524
Cable, 8-wire, universal, 1.5 m	DFS60S-SD0K01024	1069525

# Blind hollow shaft with feather key groove

Shaft diameter	Connection type	Туре	Part no.
10 mm	M23 male connector, 12-pin, radial	DFS60S-BD0A01024	1069535
	M12 male connector, 8-pin, radial	DFS60S-BD0C01024	1067915
	Cable, 8-wire, universal, 1.5 m	DFS60S-BD0K01024	1069536
12 mm	M23 male connector, 12-pin, radial	DFS60S-BE0A01024	1069537
	M12 male connector, 8-pin, radial	DFS60S-BE0C01024	1069538
	Cable, 8-wire, universal, 1.5 m	DFS60S-BE0K01024	1069539
14 mm	M23 male connector, 12-pin, radial	DFS60S-BG0A01024	1069540
	M12 male connector, 8-pin, radial	DFS60S-BG0C01024	1069541
	Cable, 8-wire, universal, 1.5 m	DFS60S-BG0K01024	1069542


# Through hollow shaft with feather key groove


Shaft diameter	Connection type	Туре	Part no.
6 mm	M23 male connector, 12-pin, radial	DFS60S-TA0A01024	1067914
10 mm	M23 male connector, 12-pin, radial	DFS60S-TD0A01024	1069526
	M12 male connector, 8-pin, radial	DFS60S-TD0C01024	1069527
	Cable, 8-wire, universal, 1.5 m	DFS60S-TD0K01024	1067916
12 mm	M23 male connector, 12-pin, radial	DFS60S-TE0A01024	1069528
	M12 male connector, 8-pin, radial	DFS60S-TE0C01024	1069529
	Cable, 8-wire, universal, 1.5 m	DFS60S-TE0K01024	1069530
14 mm	M23 male connector, 12-pin, radial	DFS60S-TG0A01024	1069531
	M12 male connector, 8-pin, radial	DFS60S-TG0C01024	1069532
	Cable, 8-wire, universal, 1.5 m	DFS60S-TG0K01024	1069534





## Dimensional drawings (dimensions in mm)

Solid shaft, face mount flange, male connector connection, radial










- (A) Measuring point working temperature (freely selectable, respectively circumferential at the cover shell, aprro. 3 mm (0.12) away from the flange)
- (B) Measuring point vibration (respectively at the housing face, approx. 3 mm (0.12) away from the cover)

General tolerances as per DIN ISO 2768-mk




#### Solid shaft, face mount flange, male connector connection, axial



General tolerances as per DIN ISO 2768-mk




## Solid shaft, face mount flange, cable connection




General tolerances according to DIN ISO 2768-mk Cable diameter =  $5.6\pm0.2$  mm; R bend radius = min. 7.5 x cable outer diameter



## Solid shaft, servo flange, male connector connection, radial






- (A) Measuring point working temperature (freely selectable, respectively circumferential at the cover shell, aprro. 3 mm (0.12) away from the flange)
- (B) Measuring point vibration (respectively at the housing face, approx. 3 mm (0.12) away from the cover)

General tolerances as per DIN ISO 2768-mk




## Solid shaft, servo flange, male connector connection, axial





General tolerances as per DIN ISO 2768-mk



## Solid shaft, servo flange, cable connection








- (A) Measuring point working temperature (freely selectable, respectively circumferential at the cover shell, aprro. 3 mm (0.12) away from the flange)
- (B) Measuring point vibration (respectively at the housing face, approx. 3 mm (0.12) away from the cover)


General tolerances as per DIN ISO 2768-mk Cable diameter =  $5.6\pm0.2$  mm; bend radius R = min. 7.5 x diameter cable

Mounting suggestion for small servo clamp (part number 2029166)



All dimensions in mm (inch)


Mounting suggestion for half-shell servo clamp (part number 2029165)



All dimensions in mm (inch)



## Blind hollow shaft, male connector connection





## General tolerances as per DIN ISO 2768-mk


XF7 shaft diameter	xj7 shaft diameter
6 mm	
8 mm	
3/8"	
10 mm	
12 mm	Provided by customer
1/2"	
14 mm	
15 mm	
5/8"	



## Blind hollow shaft, cable connection







- (A) Measuring point working temperature (freely selectable, respectively circumferential at the cover shell, aprro. 3 mm (0.12) away from the flange)
- (B) Measuring point vibration (respectively at the housing face, approx. 3 mm (0.12) away from the cover)


General tolerances as per DIN ISO 2768-mk

Cable diameter =  $5.6 \pm 0.2$  mm; bend radius R = min. 7.5 x diameter cable

XF7 shaft diameter	xj7 shaft diameter
6 mm	
8 mm	
3/8"	
10 mm	
12 mm	Provided by customer
1/2"	
14 mm	
15 mm	
5/8"	



## Through hollow shaft, male connector connection





General tolerances as per DIN ISO 2768-mk


XF7 shaft diameter	xj7 shaft diameter
6 mm	
8 mm	
3/8"	
10 mm	
12 mm	Provided by customer
1/2"	
14 mm	
15 mm	
5/8"	



## Through hollow shaft, cable connection








General tolerances according to DIN ISO 2768-mk Cable diameter =  $5.6\pm0.2$  mm; R bend radius = min. 7.5 x cable outer diameter

XF7 shaft diameter	xj7 shaft diameter
6 mm	
8 mm	
3/8"	
10 mm	
12 mm	Provided by customer
1/2"	
14 mm	
15 mm	
5/8"	



## Interface signals

SIN/COS interface signals before differential generation




For clockwise shaft rotation, looking in direction "A" (see dimensional drawing)

Signal	Interface signals	Interface signals before differential generation With 120 $\Omega$ load	Signal offset	Supply voltage	Output
+ SIN - SIN + COS - COS	Analog, differential	0.5 V <sub>pp</sub> ± 20%	2.5 V ± 10%	4.5 V 32 V	Sine 0.5 V <sub>PP</sub>

Signal	Interface signals	Interface signals before differential generation $\mbox{With 120} \ \Omega \ \mbox{load}$
Z Z	Digital, differential	Low: 1.75 V ± 15%, High: 2.90 V ± 15%

## SIN/COS interface signals after differential generation



For clockwise shaft rotation, looking in direction "A" (see dimensional drawing)




## PIN and wire allocation

View of the M23 male connector plug-in face



View of the M12 male connector plug-in face



PIN M12 male connector, 8-pin	PIN M23 male connector, 12-pin	Wire colors Cable connection	Signal	Explanation
1	6	Brown	COS -	Signal
2	5	White	COS +	Signal
3	1	Black	SIN -	Signal
4	8	Pink	SIN +	Signal
5	4	Yellow	Z_	Signal (do not use for safe- ty-related operating modes)
6	3	Violet	Z	Signal (do not use for safe- ty-related operating modes)
7	10	Blue	GND	Ground connection
8	12	Red	US	Supply voltage (volt-free to housing)
-	9	-	N. C.	Not connected
-	2	-	N. C.	Not connected
-	11	-	N. C.	Not connected
	7	-	N. C.	Not connected
Shielding	Shielding	Shielding	Shielding	Shield connected with encoder housing Connected to ground on control side

## Cable information

Permissible length of cable at maximum output frequency depending on the supply voltage:

Connection type	+ US	Max. length of cable <sup>1</sup>
M12	4.5 V5.0 V	50 m
	5.0 V7.0 V	100 m
M23	7.0 V30 V	150 m
	4.5 V5.0 V	50 m - (4 x length of encoder cable)
Cable outlet	5.0 V7.0 V	100 m - (4 x length of encoder cable)
	7.0 V30 V	150 m - (4 x length of encoder cable)

 $<sup>^{1)}</sup>$  Data cable 4 x 2 x 0.25 mm2+ 2 x 0.5 mm2 + 1 x 0.14 mm $^{2}$  with shielding (for US, GND 2 x 0.5 mm $^{2}$ ), part. no. 6027530



## Recommended accessories

The accessories are part of the safety-related function chain and must be assessed and validated accordingly by the user. This is not an integral part of the safety assessment carried out by SICK.

## Mounting systems

## Flanges

## Flange plate

Figure	Brief description	Туре	Part no.
0	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-050	2029160
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163
	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-063REC	2034225
<b>(1)</b>	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161
	Stator coupling, one-sided, 179 mm long with slot	On request	On request 1)

<sup>&</sup>lt;sup>1)</sup> For more detailed information, please consult your local SICK subsidiary. The stator coupling is mounted ex works. The customer is not permitted to replace the stator coupling

## Other mounting accessories

## Servo clamps

Figure	Brief description	Туре	Part no.
	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165
900	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166

## Miscellaneous

Figure	Brief description	Туре	Part no.
	1 M4x16 cylinder head screw and 1 2x2x6 feather key acc. to DIN 6885	BEF-MK-SE01	2073617



## Shaft adaptation

## Shaft couplings

Figure	Brief description	Туре	Part no.
	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, -30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub, for use with feather key	KUP-0606-BP	2075379
	Bellows coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-$ 30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub, for use with feather key	KUP-0610-BP	2075375
	Bellows coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-$ 30 °C +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub, for use with feather key	KUP-1010-BP	2075373
	Bellows coupling, shaft diameter 6 mm $/$ 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-$ 30 °C $+$ 120° C, max. torque 80 Ncm; material: stainless steel bellows, fixed with two setscrews each	KUP-0606-BS	2075378
	Bellows coupling, shaft diameter 6 mm / 10 mm, bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-$ 30 °C +120° C, max. torque 80 Ncm; material: stainless steel bellows, fixed with two setscrews each	KUP-0610-BS	2075377
	Bellows coupling, shaft diameter 10 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-30^\circ$ +120° C, max. torque 80 Ncm; material: stainless steel bellows, fixed with two setscrews each	KUP-1010-BS	2075376

## Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight Head B: cable	5 m	DOL-1208-G05MAC1	6032867
-	Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
		20 m	DOL-1208-G20MAC1	6032869
		2 m	DOL-2312-G02MLA3	2030682
	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm $^{1)}$	7 m	DOL-2312-G07MLA3	2030685
_		10 m	DOL-2312-G10MLA3	2030688
		15 m	DOL-2312-G15MLA3	2030692
		20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
		1.5 m	DOL-2312-G1M5MA3	2029212
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA3	2029213
700	Head B: cable	5 m	DOL-2312-G05MMA3	2029214
	Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm $^{\rm 1)}$	10 m	DOL-2312-G10MMA3	2029215
		20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217



## Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight, A coded, incremental, SSI, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^{\circ}\text{C} +85~^{\circ}\text{C}$	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057

## Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15~\text{mm}^2$ , Ø 5.6 mm		LTG-2308-MWENC	6027529
<b>\</b>	Head A: cable Head B: cable Cable: SSI, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	Dytho	LTG-2411-MW	6027530
_	Head A: cable Head B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2612-MW	6028516

## Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 8-pin, straight, A coded, incremental, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^\circ\text{C} \dots +85~^\circ\text{C}$	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40~^{\circ}\text{C} \dots +125~^{\circ}\text{C}$	STE-2312-G01	2077273

<sup>→</sup> For additional accessories, please see page K-668 onwards







## **WIRE DRAW ENCODERS**

## Wire draw encoders - made-to-measure solutions for your applications

Wire draw encoders consist of a wire draw mechanism and an encoder. The rotation of the drum is proportional to the length being measured and is recorded by an encoder, which then outputs the data. This allows for positioning on linear measuring sections. SICK's wire draw encoders provide a large selection of interfaces, which enable simple system integration in applications in demanding industrial environments.

Different performance classes make it possible to select a device that ideally suits the application at hand.

## Your benefits

- From basic configuration to heavy-duty encoders, the wide range of SICK wire draw encoders is suitable for a very broad variety of applications
- SICK wire draw encoders offer the right interface for each application due to their modular design

- A large selection of measuring lengths from 1.25 m to 50 m
- 3 different designs EcoLine,
   Compact, HighLine suitable for any application
- Unlike other linear measuring systems, wire draw encoders do not require precise linear guidance
- Resolutions of up to 0.001 mm enable very precise measurements
- · Simple commissioning



Applications
EcoLine
Compact
HighLine

## TYPICAL WIRE DRAW ENCODERS APPLICATIONS


Automated guided systems - positioning of lift height and measurement of fork width



Automated guided systems are fully automated vehicles that are primarily used for transporting goods. SICK sensors give the vehicles guidance and protect them against danger. Height positioning of the lifting surface and measurement of the fork width can also be automated. Wire draw encoders are particularly reliable at these tasks.

BCG wire draw encoders from the EcoLine product family can be used to calculate lift height with a measured length of up to 10 m. They are specifically designed for this purpose and their slim design, light weight and flexible mounting options facilitate vehicle loading. A special rope outlet nozzle also prevents damage from shock and vibration. The BCG EcoLine product family can pick up the smallest variants of fork width measurements up to 1.25 m.

Lifts - flush placement of platform and target level



Within logistics processes, such as in the automotive industry, levels often have to be passed over to continue to convey goods. Lifts are used for this purpose, and their platforms must be accurately positioned flush to the target level.

This positioning is primarily carried out with SICK wire draw encoders. The HighLine product family is suited for measuring lengths over 10 m. Through its rugged design and high reproducibility, particularly accurate positioning is possible. Like the EcoLine product family, it is suited for measuring lengths over 10 m.

## Overhead conveyors – positioning vehicle bodies



Overhead conveyors are used in the automotive industry to position vehicle bodies. The exact height of the bodies must be calculated to ensure a smooth assembly process.

The BCG wire draw encoders from the EcoLine product family, with their 3 m measured length are perfect for this type of application. They are characterized by slim design, numerous interfaces, and flexible mounting options.


## Scissor lifts – positioning platforms at working height



Scissor lifts are used, for example, in the automotive industry for vehicle assembly. It is important that the scissor lifts are at the ideal working height for the operators.

Wire draw encoders from the EcoLine or Compact product families are used for positioning platforms. Both are characterized by their compact designs and high precision. The EcoLine product family has a high degree of modularity in terms of measuring lengths, interfaces and mounting options.

## PRODUCT FAMILY OVERVIEW



Technical data overview			
Sub-product family	BCG	PFG	
Measuring length	≤ 10 m	≤ 10 m	
Resolution	Up to 0.001 mm	Up to 0.001 mm	
Reproducibility	≤ 0.2 mm	≤ 0.2 mm	
Electrical interface	4 mA 20 mA, analog 0 V 10 V analog SSI CANopen DeviceNet PROFIBUS EtherNet/IP PROFINET EtherCAT®	4.5 V5.5 V, TTL/RS422 HTL/Push Pull	
Modularity (wire draw mechanism and encoder)	<b>V</b>	<b>✓</b>	

## At a glance

- Measured lengths of 1.25 m ... 10 m
- Modular measuring system with a wide selection of interfaces/measuring lengths
- Very small, slim housing (55 mm ... 190 mm) with spring integrated in the measurement drum
- Light yet shock-proof and temperature-resistant plastic housing
- Analog interface with teach-in function available on the encoder

Detailed information →1.528





Compac

Compact, rugged design - with integrated encoder



HighLine

Rugged design measures distances up to 50 m - the heavy-duty wire draw encoder

BKS	XKS	PKS	BTF	PRF
≤ 5 m	≤ 5 m	≤ 5 m	≤ 50 m	≤ 50 m
Up to 0.295 μm	Up to 0.295 μm	Up to 0.295 μm	Up to 0.001 mm	Up to 0.001 mm
0.15°	0.15°	0.15°	≤ 5 mm	≤ 5 mm
SSI	7 V 12 V, HIPERFACE®	4.5 V5.5 V, TTL/RS422	4 mA 20 mA, analog 0 V 10 V analog SSI CANopen DeviceNet PROFIBUS EtherNet/IP PROFINET EtherCAT®	4.5 V5.5 V, TTL/RS422 10 V 32 V, HTL/Push Pull
-	-	-	V	V

- Measuring lengths from 2 m ... 5 m
- Integrated measuring system
- Compact housing (90 mm x 90 mm x 90 mm)
- Incremental and absolute versions
- High resolution

- Measuring lengths: 2 m ... 50 m
- Modular measuring system with a wide selection of interfaces/measuring lengths
- Very rugged system (dirt scraper, integrated brushes)
- High-quality winding mechanism and wire input
- · High enclosure rating
- High resistance to shock and vibrations
- Extremely high resolution possible
- Expandable using external accessories

**→** I-590

→ I-576

1-525

## **SELECTION GUIDE**


		Measuring le	nu deb [un]							
		weasuring in	engtn [m]							
		1.25	8	ю	ro	10	50	30	20	
EcoLine	e	[	· ·	(.)	Δ)	ч	· · ·	(1)	4)	
9										
	BCG05	•								
i	BCG08			•						
	BCG13				•					
	BCG19					•				
Å	PFG05	•								
	PFG08			•						
-0	PFG13				•					
	PFG19					•				
Compa	ıct									
	BKS		•		•					
	XKS		•		•					
	PKS		•		•					
HighLir	ne									
	BTF08		•	•						
	BTF13				•	•	•	•		
	BTF19								•	
	PRF08		•	•						
Ca	PRF13				•	•	•	•		
	PRF19								•	

<sup>1)</sup> Optional, on request.

<sup>&</sup>lt;sup>2)</sup> Up to 20 m measuring length analog interface available.

Interfaces	;											Page
Analog		Absolute							_	Incremer	ntal	
0 V 10 V	4 mA 20 mA	SSI	PROFIBUS	DeviceNet	CANopen	EtherNet/IP	EtherCAT®	PROFINET	HIPERFACE®	토	Ę	
•	•	•			•							<b>→</b> I-528
•	•	•	•	•	•	•	•	•	1)			<b>→</b> I-528
•	•	•	•	•	•	•	•	•	1)			<b>→</b> I-528
•	•	•	•	•	•	•	•	•	1)			<b>→</b> I-528
										•	•	<b>→</b> I-528
										•	•	<b>→</b> I-528
										•	•	<b>→</b> I-528
										•	•	<b>→</b> I-528
												<b>→</b> I-576
												<b>→</b> I-576
												<b>→</b> I-576
•	•	•	•	•	•	•	•	•	1)			<b>→</b> I-590
2)	2)	•	•	•	•	•	•	•	1)			<b>→</b> I-590
		•	•	•	•	•	•	•	1)			<b>→</b> I-590
										•	•	<b>→</b> I-590
										•	•	<b>→</b> I-590
										•	•	<b>→</b> I-590

# MODULAR WIRE DRAW ENCODERS IN MINIATURE DESIGN





## **Product description**

The slim design of the EcoLine family is ideal for applications with limited space. Its modularity makes it suitable for a large selection of measuring lengths, interfaces and encoders. Due to the spring integrated into the drum as well as the adaption without coupling, it is possible

to achieve high precision and stability. The special nozzle serves to protect the measuring wire from damage caused by vibration. The intuitive teach-in function provided in analog options also enables easy system integration.

## At a glance

- Measured lengths of 1.25 m to 10 m
- Modular measuring system with a wide selection of interfaces/measuring lengths
- Very small, slim housing (55 mm to 190 mm) with spring integrated in the measurement drum
- Light yet shock-proof and temperature-resistant plastic housing
- Analog interface with teach-in function available on the encoder

## Your benefits

- Space- and cost-saving design thanks to slimline mechanics
- Numerous combinations of interfaces and measuring lengths
- Advanced programming options lead to a reduction in the number of variants, save costs, and reduce storage
- Quick and easy commissioning thanks to analog interface and option to use low-cost interface card



Fields of application 1-529
Detailed technical data I-529
Type code
Ordering information I-541
Dimensional drawings I-544
Recommended accessories I-568

→ www.mysick.com/en/EcoLine

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

- Measuring fork height and tilt in automated guided systems
- Height measurement in small warehouse systems
- Applications in medical technology (operating tables, MRT)
- Height measurement of scissor lift tables

Height measurement of overhead conveyors in the automotive industry

## Detailed technical data

## BCG

#### Performance

	BCG05 0 m 1.25 m	BCG08 0 m 3 m	BCG13 0 m 5 m	BCG19 0 m 10 m
Measuring range	0 m - 1.25 m	0 m 3 m	0 m 5 m	0 m 10 m
Reproducibility	Max. 0.2 mm <sup>1)</sup>	Max. 0.3 mm <sup>1)</sup>	Max. 0.5 mm <sup>1)</sup>	Max. 1 mm <sup>1)</sup>
Linearity	Max. ± 2 mm <sup>1)</sup>		Max. ± 3 mm <sup>1)</sup>	Max. ± 6 mm <sup>1)</sup>
Hysteresis	Max. 0.5 mm <sup>1)</sup>	Max. 1.2 mm <sup>1)</sup>	Max. 1.5 mm <sup>1)</sup>	Max. 3 mm <sup>1)</sup>
Resolution (wire draw + encoder)				
Analog	4 20 mA = 0.05 mm; 0 10 V = 0.04 mm <sup>2) 3)</sup>	4 20 mA = 0.08 mm; 0 10 V = 0.06 mm <sup>2) 3)</sup>	4 20 mA = 0.13 mm; 0 10 V = 0.10 mm <sup>2) 3)</sup>	4 20 mA = 0.05 mm; 0 10 V = 0.04 mm <sup>2) 3)</sup>
SSI	0.02 mm (AHM36) <sup>2) 3)</sup>	0.06 mm (AFM60E) <sup>2) 3)</sup> 0.03 mm (AFM60B, AHM36) <sup>2) 3)</sup>	0.1 mm (AFM60E) <sup>2) 3)</sup> 0.05 mm (AFM60B, AHM36) <sup>2) 3)</sup>	0.14 mm (AFM60E) <sup>2) 3)</sup> 0.07 mm (AFM60B, AHM36) <sup>2) 3)</sup>
CANopen	0.01 mm (AHM36) <sup>2) 3)</sup>	0.03 mm (ATM60) <sup>2) 3)</sup> 0.01 mm (AHM36) <sup>2) 3)</sup>	0.05 mm (ATM60) <sup>2) 3)</sup> 0.02 mm (AHM36) <sup>2) 3)</sup>	0.07 mm (ATM60) <sup>2) 3)</sup> 0.03 mm (AHM36) <sup>2) 3)</sup>
DeviceNet	-	0.03 mm <sup>2) 3)</sup>	0.05 mm <sup>2) 3)</sup>	0.07 mm <sup>2) 3)</sup>
PROFIBUS	-	0.03 mm <sup>2) 3)</sup>	0.05 mm <sup>2) 3)</sup>	0.07 mm <sup>2) 3)</sup>
EtherNet/IP	-	0.001 mm <sup>2) 3)</sup>		0.002 mm <sup>2) 3)</sup>
PROFINET	-	0.001 mm <sup>2) 3)</sup>		0.002 mm <sup>2) 3)</sup>
EtherCAT®	-	0.001 mm <sup>2) 3)</sup>		0.002 mm <sup>2) 3)</sup>

 $<sup>^{\</sup>scriptscriptstyle{1)}}\!$  Value applies to wire draw mechanics.

<sup>&</sup>lt;sup>2)</sup> The values shown here are rounded.

<sup>3)</sup> Sample calculation based on the BCG08 with PROFINET: 230 mm (length of wire draw per revolution - see mechanical data): 262,144 ( steps per revolution) = 0.001 mm (resolution from the combination wire draw + encoder)

## Interfaces

	BCG05	BCG08	BCG13	BCG19
F	0 m 1.25 m	0 m 3 m	0 m 5 m	0 m 10 m
Encoder	Absolute encoders			
Electrical interface	See type code			
Connection type	See type code			
Clock frequency				
Analog	32 kHz	4.444 (4.514.005)		
SSI	2 MHz (AHM36)	1 MHz (AFM60E) 2 MHz (AFM60B, AHM3	s6)	
Address setting		Z WITZ (AT WOOD, AT IWIS	,,,,	
CANopen	0 127 (AHM36)	0 63 (ATM60) 0 127 (AHM36)		
DeviceNet	_	0 63, DIP switch or p	rotocol	
PROFIBUS	_	0 127, DIP switch		
EtherNet/IP	_	Via DHCP / DEC switch	es	
PROFINET	-	Via DCP		
Protocol				
CANopen	Communication profile DS 301 V4.02 (AHM36)	Communication profile Communication profile	DS 301 V4.0 (ATM60) DS 301 V4.02 (AHM36)	
DeviceNet	_	DeviceNet Specification	Release 2.0	
PROFIBUS	_	PROFIBUS DP VO		
EtherNet/IP	_	EtherNet/IP IEC 61784	-1	
PROFINET	-	PROFINET IO / RT Class	В	
EtherCAT®	-	EtherCAT, CoE (CiA DS-3	301)	
Bus termination				
CANopen	Via external terminator (AHM36)	Via DIP switches (ATM6 Via external terminator	,	
DeviceNet	-	Via DIP switches		
PROFIBUS	-	Via DIP switches		
Set (electronic adjustment)				
Analog	Teach-in functionality			
SSI	H active (L = $0 - 3 \text{ V}$ ; H = $4.0 - U_S \text{ V}$ ) (AHM36)	Via SET cable (AFM60) H active (L = 0 - 3 V; H	= 4.0 - U <sub>S</sub> V) (AHM36)	
CANopen	Via PRESET pushbuttor	or protocol		
DeviceNet	-	Via PRESET pushbuttor	or protocol	
PROFIBUS	-	Via PRESET pushbuttor	or protocol	
EtherNet/IP	-	Via PRESET pushbuttor	or protocol	
PROFINET	-	Via PRESET pushbuttor	or protocol	
EtherCAT®	-	Via PRESET pushbuttor	or protocol	
Encoder profile				
CANopen	CiA DS-406, V3.2 Class C2 (AHM36)	Device profile DSP 406 CiA DS-406, V3.2 Class	, ,	
DeviceNet	-	Generic Profile		
PROFIBUS	-	Encoder profile version	1.1 Class 1 and Class2	
EtherNet/IP	-	0 x 22		
PROFINET	-	V4.1 class3		
EtherCAT®	-	CiA DS-406		

## Electrical data

	BCG05	BCG08	BCG13	BCG19
	0 m 1.25 m	0 m 3 m	0 m 5 m	0 m 10 m
Initialization time				
Analog	< 2 ms <sup>1)</sup>	≤ 2 ms <sup>1)</sup>		
SSI	≥ 50 ms (AHM36) <sup>1)</sup>	Approx. 50 ms (AFM60) ≥ 50 ms (AHM36) 1)	1)	
CANopen	2 s (AHM36) 1)	Approx. 12 s (ATM60) $^{1)}$ $\geq$ 2 s (AHM36) $^{1)}$		
DeviceNet	-	Approx. 12 s 1)		
PROFIBUS	_	Approx. 1 s 1)		
EtherNet/IP	_	Approx. 12 s 1)		
PROFINET	_	Approx. 12 s 1)		
EtherCAT®	_	Approx. 12 s 1)		
Supply voltage				
Analog	19 V 33 V			18 V 33 V
SSI	4.5 V 32 V (AHM36)	4.5 V 32 V (AFM60, A	HM36)	
CANopen	10 V 30 V (AHM36)	10 V 32 V (ATM60) 10 V 30 V (AHM36)		
DeviceNet	_	10 V 32 V		
PROFIBUS	_	10 V 32 V		
EtherNet/IP	_	10 V 30 V		
PROFINET	_	10 V 30 V		
EtherCAT®	-	10 V 30 V		
Code type				
SSI	Gray, binary (AHM36)	Gray (AFM60) Gray, binary (AHM36)		
Power consumption				
Analog	2 W			
SSI	1.5 W (AHM36)	0.7 W (AFM60E, AFM60 1.5 W (AHM36)	OB)	
CANopen	1.5 W (AHM36)	2 W (ATM60) 1.5 W (AHM36)		
DeviceNet	-	2 W		
PROFIBUS	-	1.5 W		
EtherNet/IP	-	3 W		
PROFINET	-	3 W		
EtherCAT®	-	3 W		
MTTFd: mean time to dangerous failure				
SSI	230 years (AHM36) <sup>2) 3)</sup>	250 years (AFM60) $^{2) \ 3)}$ 230 years (AHM36) $^{2) \ 3)}$		
CANopen	270 years (AHM36)	150 years (ATM60) $^{2) (3)}$ 270 years (AHM36) $^{2) (3)}$		
DeviceNet	-	150 years <sup>2) 3)</sup>		
PROFIBUS	-	60 years <sup>2) 3)</sup>		
EtherNet/IP	-	80 years <sup>2) 3)</sup>		
PROFINET	-	80 years <sup>2) 3)</sup>		
EtherCAT®	-	80 years <sup>2) 3)</sup>		
1) Valid positional data can be measured once this time h				

<sup>1)</sup> Valid positional data can be measured once this time has elapsed.

<sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

 $<sup>^{\</sup>rm 3)}$  This value relates to the connected encoder only.

## Mechanical data

	BCG05 0 m 1.25 m	BCG08 0 m 3 m	BCG13 0 m 5 m	BCG19 0 m 10 m		
Mass (incl. encoder)	0 III 1.25 III	0 III 3 III	0 III 5 III	0 III 10 III		
Analog	200 g	650 g	1.2 kg	2.3 kg		
SSI	200 g (AHM36)	510 g (AFM60) 370 g (AHM36)	1.06 kg (AFM60) 920 g (AHM36)	2.16 kg (AFM60) 2.02 kg (AHM36)		
CANopen	200 g (AHM36)	840 g (ATM60) 370 g (AHM36)	1.39 kg (ATM60) 920 g (AHM36)	2.49 kg (ATM60) 2.02 kg (AHM36)		
DeviceNet	_	840 g	1.39 kg	2.49 kg		
PROFIBUS	_	530 g	1.08 kg	2.18 kg		
EtherNet/IP	_	450 g	1 kg	2.1 kg		
PROFINET	_	450 g	1 kg	2.1 kg		
EtherCAT®	_	450 g	1 kg	2.1 kg		
Mass (mechanism)	80 g	250 g	800 g	1.9 kg		
Measuring wire material	Highly flexible steel wire, 1.4401 stainless steel V4A / PA12, sheathed	Highly flexible steel wir	e, 1.4401 stainless stee	el V4A		
Mass (measuring wire)	0.58 g/m	1.2 g/m				
Material, wire draw mechanism housing	Plastic, Noryl					
Wire draw lengths per revolution	150 mm	230 mm	385 mm	555 mm		
Spring return force	Approx. 1 N to approx. 1.4 N <sup>1)</sup>	Approx. 5 N to approx. 6.3 N <sup>1)</sup>	Approx. 4.5 N to approx. 7 N <sup>1)</sup>	Approx. 9 N to approx. 12 N 1)		
Service life of wire draw mechanism	1 mio. cycles <sup>2)</sup>					
Actual wire draw length	1.45 m	3.2 m	5.2 m	10.2 m		
Measuring wire diameter	0.45 mm	0.55 mm				
Wire acceleration	10 m/s <sup>2</sup>		4 m/s <sup>2</sup>	8 m/s <sup>2</sup>		
Traversing speed	4 m/s					
Integrated encoder						
Analog	ACM36			ACM60		
SSI	AHM36 SSI	AFM60 SSI AHM36 SSI				
CANopen	AHM36 CANopen	ATM60 CANopen AHM36 CANopen				
DeviceNet	-	ATM60 DeviceNet				
PROFIBUS	-	A3M60				
EtherNet/IP	-	AFM60 EtherNet/IP				
PROFINET	-	AFM60 PROFINET				
EtherCAT®	-	AFM60 EtherCAT®				
Number of steps per revolution						
SSI	8,192 (AHM36)	4,096 (AFM60E) 8,192 (AFM60B, AHM3	36)			
CANopen	16,384 (AHM36)	8,192 (ATM60) 16,384 (AHM36)				
DeviceNet	-	8,192				
PROFIBUS	-	8,192				
EtherNet/IP	-	262,144				
PROFINET	-	262,144				
EtherCAT®	_	262,144				

 $<sup>^{\</sup>mbox{\tiny 1)}}$  These values were measured at an ambient temperature of 25  $^{\circ}\text{C}.$  There may be variations at other temperatures.

 $<sup>^{2)}\,\</sup>mathrm{A}$  cycle is made up of a wire intake and outake.

	BCG05 0 m 1.25 m	BCG08 0 m 3 m	BCG13 0 m 5 m	BCG19 0 m 10 m
Article number encoder				
Analog	6039751 6039752			6045312 6045313
SSI	1068328 (AHM36)	1037649 (AFM60E) 1037863 (AFM60B) 1037438 (AFM60E) 1068330 (AHM36)		1037869 (AFM60E) 1037863 (AFM60B) 1037868 (AFM60E) 1068330 (AHM36)
CANopen	1067977 (AHM36)	1030025 (ATM60) 1065999 (AHM36)		
DeviceNet	-	1030018		
PROFIBUS	-	1051018		
EtherNet/IP	-	1055331		
PROFINET	-	1059040		
EtherCAT®	-	1059061		
Integrated mechanics	MRA-G055-101D4	MRA-G080-103D3	MRA-G130-105D3	MRA-G190-110D3
Article number mechanics	5324019	5322778	5322779	5326242

 $<sup>^{1)}</sup>$  These values were measured at an ambient temperature of 25  $^{\circ}$ C. There may be variations at other temperatures.

## Ambient data

	BCG05 0 m 1.25 m	BCG08 0 m 3 m	BCG13 0 m 5 m	BCG19 0 m 10 m
EMC	According to EN 61000	According to EN 61000-6-2 and EN 61000-6-3		
Enclosure rating (encoder)				
Analog	IP 65			
SSI	IP 66 / IP 67, on housing side (acc. to IEC 60529) (AHM36) IP 66 / IP 67, on shaft side (acc. to IEC 60529) (AHM36)	IP 67 (AFM60) IP 66 / IP 67, on housin IP 66 / IP 67, on shaft s	• ,	, · · · · · · · · · · · · · · · · · · ·
CANopen	IP 66 / IP 67, on housing side (acc. to IEC 60529) (AHM36) IP 66 / IP 67, on shaft side (acc. to IEC 60529) (AHM36)	IP 67 (ATM60) IP 66 / IP 67, on housin IP 66 / IP 67, on shaft s	• ,	, · · · · · · · · · · · · · · · · · · ·
DeviceNet	-	IP 67		
PROFIBUS	-	IP 67		
EtherNet/IP	-	IP 67		
PROFINET	-	IP 67		
EtherCAT®	-	IP 67		
Enclosure rating (mechanism)	IP 50			

 $<sup>^{\</sup>mbox{\tiny 2)}}\,\mbox{A}$  cycle is made up of a wire intake and outake.

	BCG05 0 m 1.25 m	BCG08 0 m 3 m	BCG13 0 m 5 m	BCG19 0 m 10 m
Resistance to shocks (according to				
EN 60068-2-27)				
Analog	50 g, 6 ms			
SSI	100 g, 6 ms (AHM36)	50 g, 6 ms (AFM60E) 70 g, 6 ms (AFM60B) 100 g, 6 ms (AHM36)		
CANopen	100 g, 6 ms (ATM60, AHM36)			
DeviceNet	-	100 g, 6 ms		
PROFIBUS	-	80 g, 6 ms		
EtherNet/IP	-	100 g, 6 ms		
PROFINET	-	100 g, 6 ms		
EtherCAT®	-	100 g, 6 ms		
Resistance to vibration (according to EN 60068-2-6)				
	20 g, 10 Hz 2,000 Hz (AHM36)	20 g, 10 Hz 2,000 Hz 30 g, 10 Hz 2,000 Hz		
·	20 g, 10 Hz 2,000 H			
DeviceNet		C, ,		
PROFIBUS				
	- 30 g, 10 Hz 2,000 Hz			
PROFINET				
EtherCAT®	_	30 g, 10 Hz 2,000 Hz		
	4 g, sine 5 Hz 100 H	z (as per EN 60068-2-6)		
Operating temperature range (encoder)	00.00			
· ·		-30 °C +80 °C		
551	-40 °C +100 °C (AHM36)	0 °C +85 °C (AFM60 -30 °C +100 °C (AFM -40 °C +100 °C (AHM	M60B)	
CANopen	-40 °C +85 °C (AHM36)	-20 °C +85 °C (ATM) -40 °C +85 °C (AHM)		
DeviceNet	-	-20°C +85°C		
PROFIBUS	-	-10 °C +70 °C		
EtherNet/IP	-	-30 °C +85 °C		
PROFINET	-	-30 °C +85 °C		
EtherCAT®	-	-30 °C +85 °C		
Operating temperature range (mechanical)	-30 °C +70 °C			
Operating temperature range (combination)				
Analog	-30 °C +70 °C			
SSI	-30 °C +70 °C (AHM36)	0 °C +70 °C (AFM60 -30 °C +70 °C (AFM	60B, AHM36)	
CANopen	-30 °C +70 °C	-20 °C +70 °C (ATM) -30 °C +70 °C (AHM)	′	
DeviceNet	-	-20 °C +70 °C		
PROFIBUS	-	-10 °C +70 °C		
EtherNet/IP	-	-30 °C +70 °C		
PROFINET	-	-30 °C +70 °C		
EtherCAT®	-	-30 °C +70 °C		

	BCG05 0 m 1.25 m	BCG08 0 m 3 m	BCG13 0 m 5 m	BCG19 0 m 10 m
Relative humidity/condensation				
SSI	90% (AHM36) 1)	90% (AFM60, AHM36) <sup>1</sup>	.)	
CANopen	90% (AHM36) <sup>1)</sup>	98% (ATM60) <sup>1)</sup> 90% (AHM36) <sup>1)</sup>		
DeviceNet	-	98% 1)		
PROFIBUS	-	95% 1)		
EtherNet/IP	-	90% 1)		
PROFINET	-	90% 1)		
EtherCAT <sup>®</sup>	-	90% 1)		

<sup>&</sup>lt;sup>1)</sup> Condensation of optical surfaces not permitted.

## PFG

#### Performance

	PFG05 0 m 1.25 m	PFG08 0 m 3 m	PFG13 0 m 5 m	PFG19 0 m 10 m
Measuring range	0 m - 1.25 m	0 m 3 m	0 m 5 m	0 m 10 m
Reproducibility	Max. 0.2 mm <sup>1)</sup>	Max. 0.3 mm <sup>1)</sup>	Max. 0.5 mm <sup>1)</sup>	Max. 1 mm <sup>1)</sup>
Linearity	Max. ± 2 mm <sup>1)</sup>		Max. ± 3 mm <sup>1)</sup>	Max. ± 6 mm <sup>1)</sup>
Hysteresis	Max. 0.5 mm <sup>1)</sup>	Max. 1.2 mm <sup>1)</sup>	Max. 1.5 mm <sup>1)</sup>	Max. 3 mm <sup>1)</sup>
Resolution (wire draw + encoder)	0.06 mm <sup>2) 3)</sup>	0.014 mm <sup>2) 3)</sup>	0.023 mm <sup>2) 3)</sup>	0.034 mm <sup>2) 3)</sup>

<sup>1)</sup> Value applies to wire draw mechanics.

## Interfaces

Encoder	Incremental encoders
Electrical interface	See type code
Connection type	See type code

#### Electrical data

	PFG05 0 m 1.25 m	PFG08 0 m 3 m	PFG13 0 m 5 m	PFG19 0 m 10 m
Maximum output frequency	≤ 300 kHz	≤ 800 kHz		
Reference signal, position	90° electric, logical- ly gated with A and B	90°, electric, logically gated with A and B/sine and cosine		
Reference signal, number	Electric, logically gated with A and B	1		
Maximum load current	≤ 30 mA			
Initialization time	≤ 3 ms ¹)	$\leq$ 32 ms, 30 ms, at mechanical zero pulse width $^{1)}$		1 <sup>1)</sup>
Supply voltage	7 V 30 V	4.5 V 32 V		
Power consumption	0.5 W	0.7 W		
MTTFd: mean time to dangerous failure	600 years <sup>2) 3)</sup>	300 years <sup>2) 3)</sup>		

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Valid positional data can be measured once this time has elapsed.

<sup>&</sup>lt;sup>2)</sup> The values shown here are rounded.

<sup>&</sup>lt;sup>3)</sup> Sample calculation based on the PFG08 with HTL Push Pull: 230 mm (length of wire draw per revolution - see mechanical data): 16,384 ( steps per revolution) = 0.014 mm (resolution from the combination wire draw + encoder)

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532

<sup>&</sup>lt;sup>3)</sup> This value relates to the connected encoder only.

## Mechanical data

	PFG05 0 m 1.25 m	PFG08 0 m 3 m	PFG13 0 m 5 m	PFG19 0 m 10 m
Mass (incl. encoder)	230 g	550 g	1.1 kg	2.2 kg
Mass (mechanism)	80 g	250 g	800 g	1.9 kg
Measuring wire material	Highly flexible steel wire, 1.4401 stainless steel V4A / PA12, sheathed	Highly flexible steel wire, 1.4401 stainless steel V4A		
Mass (measuring wire)	0.58 g/m	1.2 g/m		
Material, wire draw mechanism housing	Plastic, Noryl			
Wire draw lengths per revolution	150 mm	230 mm	385 mm	555 mm
Spring return force	1 N 1.4 N $^{1)}$	5 N 6.3 N <sup>1)</sup>	4.5 N 7 N <sup>1)</sup>	9 N 12 N <sup>1)</sup>
Service life of wire draw mechanism	1 mio. cycles 2)			
Actual wire draw length	1.45 m	3.2 m	5.2 m	10.2 m
Measuring wire diameter	0.45 mm	0.55 mm		
Wire acceleration	10 m/s <sup>2</sup>		4 m/s <sup>2</sup>	8 m/s <sup>2</sup>
Traversing speed	4 m/s			
Integrated encoder	DBS36 Core	DFS60		
Pulses per revolution				
Programmable	-	65,536		
Non-programmable	2,500	16,384		
Article number encoder				
TTL/RS422	1064245	1037566 1037565		
HTL/Push Pull	1064246	1037616 1037615		
TTL/HTL programmable	-	1036761 1036760		
Integrated mechanics	MRA-G055-101D4	MRA-G080-103D3	MRA-G130-105D3	MRA-G190-110D3
Article number mechanics	5324019	5322778	5322779	5326242

<sup>&</sup>lt;sup>1)</sup> These values were measured at an ambient temperature of 25 °C. There may be variations at other temperatures.

 $<sup>^{\</sup>rm 2)}\,{\rm A}$  cycle is made up of a wire intake and outake.

## Ambient data

	PFG05 0 m 1.25 m	PFG08 0 m 3 m	PFG13 0 m 5 m	PFG19 0 m 10 m
EMC	According to EN 61000-6-2 and EN 61000-6-3 (class A)	According to EN 61000-6-2 and EN 61000-6-3		
Enclosure rating (encoder)	IP 65	IP 67		
Enclosure rating (mechanism)	IP 50			
Resistance to shocks (as per EN 60068-2-27)	100 g, 6 ms	60 g, 6 ms		
Resistance to vibration (according to EN 60068-2-6)	20 g, 10 Hz 2,000 H.	Hz		
Operating temperature range (encoder)				
TTL/RS422	-20 °C +85 °C	-40 °C +100 °C		
HTL/Push Pull	-20 °C +85 °C	-40 °C +100 °C		
TTL/HTL programmable	-	-40 °C +100 °C		
Operating temperature range (mechanical)	-30 °C +70 °C			
Operating temperature range (combination)				
TTL/RS422	-20 °C +70 °C	-30 °C +70 °C		
HTL/Push Pull	-20 °C +70 °C	-30 °C +70 °C		
TTL/HTL programmable	-	-30 °C +70 °C		
Relative humidity/condensation	90% 1)			

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Condensation of optical surfaces not permitted.


## Type code

## EcoLine absolute

Size  0 5 55 mm (only in combination with measuring length 01) 0 8 80 mm (only in combination with measuring length 03) 1 3 130 mm (only in combination with measuring length 05) 1 9 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
Electrical interface  A SSI C CANopen 1) D DeviceNet 1) E EtherCAT® H HIPERFACE® (on request) K SSI + SinCos (on request) L SSI + incremental HTL (on request) I EtherNet/IP N PROFINET P PROFIBUS R SSI + incrementally programmable (on request) SSI + sinCos programmable (on request) SSI + sinCos programmable (on request) SSI + sinCos programmable (on request) SSI + incremental TTL (on request)
Connection type  A M23 male connector, 12-pin, radial (only in combination with interface A and construction sizes 08, 13 and 19)  Male connector, 3 x M12, axial (only in combination with the electrical interfaces E, I, N, and P with axial outlet in construction sizes 08, 13 and 19)  C M12 male connector, 8-pin, radial (only in combination with interface A and construction sizes 08, 13 and 19)  Hale connector for fieldbus adapter (only in combination with the electrical interfaces C and D with radial outlet in construction sizes 08, 13 and 19)  K Cable, 8-wire, universal, 1.5 m (on request)  L Cable, 8-wire, universal, 3.0 m (on request)  M Cable, 8-wire, universal, 5.0 m (on request)  N Male connector, 1 x M12, 8-pin, universal (only in combination with interface A)  Male connector, 1 x M12, 5-pin, universal (only in combination with interface C)
Measuring length
Resolution coefficient  5
B C G 1 M 1 M 1 M 1 M 1 Please order fieldbus adapter for CANopen and DeviceNet with radial outlet separately.

 $<sup>^{1\!\!/}</sup>$  Please order fieldbus adapter for CANopen and DeviceNet with radial outlet separately.

#### **EcoLine analog**



# Ordering information

Measuring range	Electrical interface	Connection type	Туре	Part no.
	4 mA 20 mA, analog	0.11.0 : ".1.4.5	BCG05-K1KM01PP	6039745
	0 V to 10 V analog	Cable, 3-wire, radial, 1.5 m	BCG05-L1KM01PP	6039746
0 m - 1,25 m	SSI	Male connector, 1 x M12, 8-pin, universal	BCG05-A1NM0155	1068864
	CANopen	Male connector, 1 x M12, 5-pin, universal <sup>2)</sup>	BCG05-C1QM0199	1068865
	4 mA 20 mA, analog	Cable, 3-wire, radial, 1.5 m	BCG08-K1KM03PP	6039747
	0 V to 10 V analog	ouble, o wife, fadial, 1.5 m	BCG08-L1KM03PP	6039748
		M12 male connector, 8-pin, radial	BCG08-A1CM0318	1054129
		WIZ male connector, o pm, radial	BCG08-A1CM0336	1054131
	SSI	M23 male connector, 12-pin, radial	BCG08-A1AM0318	1061025
		Male connector, 1 x M12, 8-pin, universal	BCG08-A1NM0336	1068866
0 m 3 m	CANopen	Male connector, 1 x M12, 5-pin, universal 2)	BCG08-C1QM0371	1068867
	олиорен	Bus adapter with cable screw fixings or round connectors 1)	BCG08-C1HM0336	1061026
	DeviceNet	Bus adapter with cable screw fixings or round connectors 1)	BCG08-D1HM0336	1061027
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BCG08-P1BM0336	1052618
	PROFINET		BCG08-N1BM0399	1061028
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BCG08-I1BM0399	1061029
	EtherCAT®		BCG08-E1BM0399	1061030
	4 mA 20 mA, analog	Cable, 3-wire, radial, 1.5 m	BCG13-K1KM05PP	6039749
	0 V to 10 V analog	Cable, 5-wire, radial, 1.5 III	BCG13-L1KM05PP	6039750
		M12 male connector, 8-pin, radial	BCG13-A1CM0511	1061031
		W12 maic connector, o-pin, radial	BCG13-A1CM0521	1061032
	SSI	M23 male connector, 12-pin, radial	BCG13-A1AM0511	1061033
		Male connector, 1 x M12, 8-pin, universal	BCG13-A1NM0521	1068868
0 m 5 m	CANopen	Male connector, 1 x M12, 5-pin, universal 2)	BCG13-C1QM0543	1068869
	CANOPEII	Bus adapter with cable screw fixings or round connectors 1)	BCG13-C1HM0521	1061034
	DeviceNet	Bus adapter with cable screw fixings or round connectors 1)	BCG13-D1HM0521	1061035
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BCG13-P1BM0521	1052619
	PROFINET	0.140	BCG13-N1BM0599	1061036
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BCG13-I1BM0599	1061037
	EtherCAT®		BCG13-E1BM0599	1061038

<sup>1)</sup> Order adapter separately.


 $<sup>^{\</sup>mbox{\tiny 2)}}$  Only in conjunction with AHM36 CANopen.

Measuring range	Electrical interface	Connection type	Туре	Part no.
	4 mA 20 mA, analog	1 x M12 male connector, 5-pin,	BCG19-K1EM10PP	6048294
	0 V to 10 V analog	radial	BCG19-L1EM10PP	6048295
		M40 male connector O min radial	BCG19-A1CM1007	1061039
	SSI	M12 male connector, 8-pin, radial	BCG19-A1CM1015	1061040
		Male connector, 1 x M12, 8-pin, universal	BCG19-A1NM1015	1068870
	CANopen	Male connector, 1 x M12, 5-pin, universal 2)	BCG19-C1QM1029	1068871
0 m 10 m		Bus adapter with cable screw fixings or round connectors 1)	BCG19-C1HM1015	1061041
	DeviceNet	Bus adapter with cable screw fixings or round connectors 1)	BCG19-D1HM1015	1061042
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BCG19-P1BM1015	1052620
	PROFINET		BCG19-N1BM1099	1061043
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BCG19-I1BM1099	1061044
	EtherCAT®		BCG19-E1BM1099	1061045

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Order adapter separately.

 $<sup>^{\</sup>mbox{\tiny 2)}}$  Only in conjunction with AHM36 CANopen.

#### **EcoLine incremental**




Measuring range	Electrical interface	Connection type	Туре	Part no.
0 m 1 25 m	4.5 V5.5 V, TTL/RS422	Cable Quire universal 1.5 m	PFG05-A1KM0160	1060972
0 m 1,25 m	HTL/Push Pull	Cable, 8-wire, universal, 1.5 m	PFG05-E1KM0160	1060971
		M12 male connector, 8-pin, radial	PFG08-A1CM0371	1060974
	4.5 V5.5 V, TTL/RS422	M23 male connector, 12-pin, radial	PFG08-A1AM0371	1060977
		M12 male connector, 8-pin, radial	PFG08-E1CM0371	1060979
0 m 3 m	HTL/Push Pull	M23 male connector, 12-pin, radial	PFG08-E1AM0371	1060981
	TTL/HTL, programmable	M12 male connector, 8-pin, radial	PFG08-P1CM03PP	1060984
		M23 male connector, 12-pin, radial	PFG08-P1AM03PP	1075495
		M12 male connector, 8-pin, radial	PFG13-A1CM0544	1061015
	4.5 V5.5 V, TTL/RS422	M23 male connector, 12-pin, radial PFG13-A1AM05	PFG13-A1AM0544	1061016
		M12 male connector, 8-pin, radial	PFG13-E1CM0544	1061017
0 m 5 m	HTL/Push Pull	M23 male connector, 12-pin, radial	PFG13-E1AM0544	1061018
		M12 male connector, 8-pin, radial	PFG13-P1CM05PP	1061019
	TTL/HTL, programmable	M23 male connector, 12-pin, radial	PFG13-P1AM05PP	1075498


Measuring range	Electrical interface	Connection type	Туре	Part no.
		M12 male connector, 8-pin, radial	PFG19-A1CM1029	1061020
	4.5 V5.5 V, TTL/RS422	M23 male connector, 12-pin, radial	PFG19-A1AM1029	1061021
		M12 male connector, 8-pin, radial	PFG19-E1CM1029	1061022
0 m 10 m	HTL/Push Pull	M23 male connector, 12-pin, radial	PFG19-E1AM1029	1061023
		M12 male connector, 8-pin, radial	PFG19-P1CM10PP	1061024
	TTL/HTL, programmable	M23 male connector, 12-pin, radial	PFG19-P1AM10PP	1075581

# Dimensional drawings (dimensions in mm)


### BCG05 Analog




### BCG08 Analog




### BCG13 Analog







### BCG19 Analog (M12 male connector outlet)




#### BCG08 SSI (M12 male connector outlet)




### BCG08 SSI (M23 male connector outlet)




### BCG13 SSI (M12 male connector outlet)




### BCG13 SSI (M23 male connector outlet)





### BCG19 SSI (M12 male connector outlet)






#### BCG19 SSI (M23 male connector outlet)







### BCG08 CANopen, DeviceNet




### BCG13 CANopen, DeviceNet




### BCG19 CANopen, DeviceNet





### BCG05 SSI, CANopen







# BCG08 SSI, CANopen







# BCG13 SSI, CANopen






### BCG19 SSI, CANopen







### BCG08 PROFIBUS





### BCG013 PROFIBUS






### **BCG19 PROFIBUS**







#### BCG08 EtherNet/IP, EtherCAT®, PROFINET





# BCG13 EtherNet/IP, EtherCAT®, PROFINET







### BCG19 EtherNet/IP, EtherCAT®, PROFINET







#### PFG05







### PFG08 (M12 male connector outlet)







PFG08 (M23 male connector outlet)







PFG13 (M12 male connector outlet)







PFG13 (M23 male connector outlet)







### PFG12 (M12 male connector outlet)






### PFG08 (M23 male connector outlet)





### Deflection roller design

With the aid of deflection rollers, it is possible to guide the measuring wire of wire draw encoders over edges and around corners without significantly affecting the life time of the wire draw encoder. In this case, it must be considered that the designs of the deflection roller and of the measuring wire must be compatible in order to avoid damage to the system.



- D = groove base diameter.
- d = diameter of the wire incl. coating.
- r = groove radius = 0.53 x d
- a = groove opening angle =  $60^{\circ}$

- The groove radius should not be too small recommendation: 0.53 x diameter of the wire cable
- The groove opening angle should be neither too small nor too large recommendation: 60°
- In order to ensure the longest possible system life, the deflection roller material should be neither too soft nor too hard **recommended material: polyamide**
- The groove base diameter of the deflection roller should not be too small see table for recommendations

#### **EcoLine**


Length	Measuring wire, PA- sheathed	Diameter of the measuring wire	Structure of the measuring wire (strands x cords)	Min. groove base diameter
1.25 m	PA12	0.45 mm	7 x 7	25 mm
3 m	-	0.55 mm	1 x 19	40 mm
5 m	-	0.55 mm	1 x 19	40 mm
10 m	-	0.55 mm	1 x 19	40 mm

### HighLine


Length	Measuring wire, PA- sheathed	Diameter of the measuring wire	Structure of the measuring wire (strands x cords)	Min. groove base diameter
2 m	-	1.35 mm	7 x 19	35 mm
3 m	-	1.35 mm	7 x 19	35 mm
5 m	-	1.35 mm	7 x 19	35 mm
10 m	-	1.35 mm	7 x 19	35 mm
20 m		0.81 mm	7 x 7	35 mm
30 m		0.81 mm	7 x 7	35 mm
50 m		1.35 mm	7 x 19	35 mm

### Installation of deflection rollers


# General notes on the installation of deflection rollers



The deflection roller should always be installed in a way which ensures that running is smooth. The deflection roller should ideally have an integrated ball bearing.



The smaller the deflection angle ( $\alpha$ ) achieved by a deflection roller, the less wear will appear on the measuring wire and therefore the longer the service life of the wire draw mechanism.




If two or more deflection rollers are needed, then the deflection rollers should always be installed at a distance from one another. The requisite distance between the deflection rollers must be accurately defined on site, accounting for specific customer requirements.

#### Wire sag

If the measuring wire is pulled out in a horizontal direction, this creates sag that becomes more pronounced as the wire length increases. This has particular implications for applications with obstacles that could get in the way of the moving measuring wire. However, the change in length that results from the sag, and the measurement error this leads to, are negligible.

#### Calculating the wire sag

The mass of the free-hanging measuring wire creates weight-related force, and this causes the wire to bend into a hyperbola-shaped line. The tension force in the measuring wire acts against the sag. As the measurement length increases, so too does the tension force as a result of the spring drive. We can imagine the hyperbola shape in a simplified format that looks approximately like a triangle.



The weight-related force of the measuring wire can be calculated using Formula A.

The spring rate of the spring drive is calculated using **Formula B**.

Formula C determines the sag of the measuring wire (the results of Formula A and Formula B are required in order to calculate the wire sag).

**Formula D** is used for calculating the measurement error.

The values found in real life will differ from the theoretical values that are calculated, as the measuring wire itself demonstrates a certain amount of resistance against the sag.

#### Formula A

# $F_{G} = 0.5 \times m_{L} \times g \times L$

F<sub>G</sub> = weight-related force of the measuring wire [N]

 $m_L$ = length-related mass of the measuring wire [Kg/m]

g = gravitational acceleration 9.81  $[m/s^2]$ 

L = free length of the measuring wire

#### Formula B

$$c = \frac{F_{s \max} - F_{s \min}}{L_{\max}}$$

c = spring rate of the spring drive [N/m]

 $F_{S max}$  = maximum tensile force in the wire [N]

F<sub>S min</sub>= minimum tensile force in the wire [N]

#### Formula C

$$h = \frac{L^2 x g x m_L}{8 x (c x L + F_{min})}$$

n = wire sag [mm]

c = spring rate of the spring drive [N/m]

 $F_{S\,min}$  = minimum tensile force in the measuring wire [N]

g = gravitational acceleration 9.81 [m/s<sup>2</sup>]

m<sub>L</sub> = length-related mass of the measuring wire [Kg/m]

L = free length of the measuring wire [m]

#### Formula D

$$f = \sqrt{L^2 + 4 h^2} - L$$

f = measurement error [m]

h = wire sag [m]

= free length of the measuring wire [m]

### Recommended accessories

# Mounting systems

Flanges

Flange plate

Figure	Brief description	Туре	Part no.
	Flange adapter for EcoLine wire draw mechanisms, adaption of face mount flange with centering hub 20 mm to 50 mm servo flange	BEF-FA-020-050-007	2073774

### Other mounting accessories

Figure	Brief description	Туре	Part no.
0	Joint ball for insertion in wire end ring with 20 mm diameter	Joint ball for BTF/ PRF/MRA wire draw	5318683

### Wire draw mechanism

Wire draw mechanism for servo flange encoder

Figure	Brief description	Mea- suring length	Туре	Part no.
9	Ecoline wire draw mechanism for 36 series servo flange With 6 mm shaft	1.25 m	MRA-G055-101D4	5324019
0		3.0 m	MRA-G080-103D3	5322778
2.	Ecoline wire draw mechanism for 60 series servo flange With 6 mm shaft	5.0 m	MRA-G130-105D3	5322779
Š		10.0 m	MRA-G190-110D3	5326242

# Connectivity

Adapters and distributors

T-piece

Figure	Brief description	Туре	Part no.
S	CANopen, T-piece	DSC- 1205T000025KM0	6030664

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
\	Head A: female connector, M12, 5-pin, angled	5 m	DOL-1202-W05MC	6042067
	Head B: cable Cable: for power supply, PUR, halogen-free, shielded, $3 \times 0.34 \text{ mm}^2$ , $\emptyset 4.2 \text{ mm}^2$	10 m	DOL-1202-W10MC	6042068

 $<sup>^{1)}\,\</sup>mbox{Warning!}$  Only in combination with electrical interfaces A, C, E and P.

Head A: female connector, M12, 4-pin, straight	Figure	Brief description	Length of cable	Туре	Part no.
Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshield- ed. 4 x 0.34 mm³, 0 4.7 mm  2 m DOL:1204-G25MC 6035902 2 m DOL:1204-W02MC 6025903 2 m DOL:1204-W02MC 6025903 2 m DOL:1204-W02MC 6025903 2 m DOL:1204-W02MC 6025903 3 m DOL:1204-W02MC 6025903 4 mr³, 0 4.7 mm  2 m DOL:1204-W02MC 6025903 4 mr³, 0 4.7 mm  2 m DOL:1204-W02MC 6025903 4 mr³, 0 4.7 mm  2 m DOL:1204-W02MC 6025903 4 mr³, 0 4.7 mm  2 m DOL:1204-W02MC 6025903 4 mr³, 0 4.7 mm  2 m DOL:1204-W02MC 6025903 4 mr³, 0 4.7 mm  2 m DOL:1204-W02MC 6025903 4 mr³, 0 4.7 mm  2 m DOL:1204-W02MC 6035903 4 mr³, 0 4.7 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 4.7 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 5.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 5.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 5.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 5.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 5.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 5.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 6.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 6.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 6.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 6.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 6.9 mm  2 m DOL:1205-G05MAC 6036383 4 mr³, 0 6.9 mm  3 m DOL:1205-G05MAC 6036383 4 mr³, 0 6.9 mm  5 m DOL:1205-G05MQ 6036383 5 m DOL:1205-G05MQ 6032633 5 mr³, 0 m		Hand Astronala annuatan MOO Anin atmidda	2 m	DOL-1204-G02MC	6025900
ed, 4 x 0.34 mm², Ø 4.7 mm  25 m DOL1204 625MC 6034751 Head A: female connector, M12, 4-pin, angled Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshield-cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 4.7 mm  Head A: female connector, M12, 5-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead A: female connector, M12, 5-pin, angled, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead A: female connector, M12, 5-pin, straight Head B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Lead A: female connector, M12, 5-pin, straight Lead B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.6 mm  Lead A: female connector, M12, 5-pin, straight Lead B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.6 mm  Lead A: female connector, M12, 5-pin, straight Lead B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.0 mm  Lead A: female connector, M12, 5-pin, straight Lead B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.0 mm  Lead A: female connector, M12, 5-pin, straight Lead B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.			5 m	DOL-1204-G05MC	6025901
Head A: female connector, M12, 4-pin, angled   2 m   DOL-1204-W25MC   6025908   Cable: for prower supply, suitable for drag chain, PUR, halogen-free, unshielded, 4 x 0.34 mm², 0 4.7 mm   DOL-1204-W25MC   6025908   DOL-1204-W25MC   6025908   DOL-1204-W25MC   6034754   DOL-1205-G05MAC   6034754   DOL-1205-G05MAC   6034754   DOL-1205-G05MAC   6034754   DOL-1205-G05MAC   6034754   DOL-1205-G05MAC   Colorable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², 0 5.9 mm   DOL-1205-G05MAC   DOL-1205-G05MAC   Colorable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², 0 5.9 mm   DOL-1205-G05MAC   DOL-1205-G05MAC   Colorable   Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², 0 5.9 mm   DOL-1205-G05MAC   DOL-1205-G05MAC   DOL-1205-G05MAC   Colorable   Colorable   POR-18US, suitable for drag chain, PUR, halogen-free, shielded   Dol-1205-G05MAC   Colorable   DOL-1205-G05MAC   Colorable   Colorable   POR-18US, suitable for drag chain, PUR, halogen-free, shielded   Dol-1205-G05MAC   Colorable   Colorable   POR-18US, suitable for drag chain, PUR, halogen-free, shielded   Dol-1205-G05MAC   Colorable   Col	1		10 m	DOL-1204-G10MC	6025902
Head A: female connector, M12, 4-pin, angled Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded, 4 x 0.34 mm², 0 4.7 mm Dol.1204-W10MC 6025904 ed, 4 x 0.34 mm², 0 4.7 mm Dol.1205-ga05MAC 6036384 head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², 0 5.9 mm Dol.1205-ga05MAC 6036384 Dol.1205-ga05MAC		ed, 4 x 0.34 mm², Ø 4.7 mm	25 m	DOL-1204-G25MC	6034751
Head B: cable   Cab		Head A: female connector M12 4-nin angled	2 m	DOL-1204-W02MC	6025903
ed, 4 x 0.34 mm², Ø 4.7 mm  25 m D0L:1204-W25MC 6034754  Head At female connector, M12, 5 pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  1.5 m D0L:1205-G03MAC 6036384 D0L:1205-G03MAC 60363884 D0L:1205-G03MAC 60363884 D0L:1205-G03MACS 60049452 C0 m D0L:1205-G03MACS 6049452 C0 m D0L:1205-C0 molecular for free shielded, 5 x 0.34 mm², Ø 5.9 mm  D0L:1205- 6049452 C0 m D0L:1205-C0 molecular for free shielded, 5 x 0.34 mm², Ø 5.9 mm  D0L:1205- 6049452 C0 m D0L:1205-C0 molecular for free shielded, 5 x 0.34 mm², Ø 5.6 mm  D0L:1205- 6049452 C0 m D0L:1205-C0 molecular for free shielded, 5 x 0.34 mm², Ø 5.6 mm  D0L:1205- 6049452 C0 m D0L:1205-C0 molecular for free shielded, 2 x 0.15 mm², Ø 5.6 mm  D0L:1205-C0 molecular for free free shielded, 2 x 0.34 mm², Ø 5.6 mm  D0L:1205-G05MA 6048596 D0L:1205-G05MA 604		·	5 m	DOL-1204-W05MC	6025904
Head A: female connector, M12, 5-pin, straight   5 m   D0L1205-G00MAC   6036384   Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 20 m   D0L1205-G10MAC   6036384   D0L1205-G10MAC   6036384   D0L1205-G10MAC   6036384   D0L1205-G10MAC   6036384   D0L1205-G10MAC   6036384   D0L1205-G01MAC   Co	10		10 m	DOL-1204-W10MC	6025905
Head & female connector, M12, 5-pin, angled, A-coded Head & female connector, M12, 5-pin, straight, A-coded Head & female connector, M12, 5-pin, angled, A-coded Head & female connector, M12, 5-pin, straight Cabie: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², 0 5.9 mm    D0L-1205-G03MACS-	ed, 4 x 0.34 mm <sup>2</sup> , Ø 4.7 mm	eu, 4 x 0.34 mm-, 9 4.7 mm	25 m	DOL-1204-W25MC	6034754
Cabie: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  Dol.1205-620MAC 6036388	\\		5 m	DOL-1205-G05MAC	6036384
5 x 0.34 mm², θ 5.9 mm  20 m DOL.1205-G20MAC 6036388  1.5 m DOL.1205-G3MACS- 6049451  Cable: sultable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², θ 5.9 mm  DOL.1205-G03MACS- 6049452  DOL.1205-G03MACS- 6049452  DOL.1205-G03MACS- 6049452  10 m DOL.1205-G10MACS- 6049452  1.5 m DOL.1205-G10MACS- 6049452  DOL.1205-G10MACS- 6049442  DOL.1205-G10MACS- 6049442  DOL.1205-G10MACS- 6049442  DOL.1205-G10MACS- 6049442  DOL.1205-G10MACS- 6049442			10 m	DOL-1205-G10MAC	6036385
Head A: female connector, M12, 5-pin, straight, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm  D0L:1205-G05MACS- C0 D0L:1205-G10MACS- C0	W		20 m	DOL-1205-G20MAC	6036386
Head A: female connector, M23, 12-pin, straight   Head A: female connector, M24, 5-pin, straight   Head A: female connector, M12, 5-pin, straight   Head A: female connector, M23, 12-pin, straight   Head A: female connector, M24, 5-pin, straight   Head A: female connector, M25, 5-pin, straight   Head A: female connector, M25, 5-pin, straight   Head A: female connector, M25, 5-pin, straight   Head A: female connector, M12, 5-pin, angled, B-coded   Head A: female connector, M12, 5-pin, angled, B-coded   Head A: female connector, M12, 5-pin, straight   Head A: fe			1.5 m	CO	6049451
0		Head B: cable	3 m	CO	6049452
1.5 m Dol-1205- W1MSACSCO 6049456 W1MSACSCO 6049456 W1MSACSCO 6049456 W03MACSCO 6049456 W03MACSCO 6049456 W03MACSCO 6049456 W03MACSCO 6049456 W03MACSCO 6049457 Dol-1205- W05MACSCO 6049457 Dol-1205- W10MACSCO 6049457 Dol-1205- W05MACSCO 6049456 Dol-1205- W05MACSCO 6049457 Dol-1205- W05MACSCO 6049458 Dol-1205-		· •	5 m	CO	6049453
Head A: female connector, M12, 5-pin, angled, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², 05.9 mm  D01.1205- W05MACSCO 5 m D01.1205- W05MACSCO 10 m D01.1205- W05MACSCO 10 m D01.2308-G0M5AA6 2048596 Head A: female connector, M23, 12-pin, straight Head B: cable Cable: SSI, suitable for drag chain, PVC, shielded, 4 x 2 x 0.15 mm², 0 5.6 mm D01.2308-G0MAA6 2048596 5 m D01.2308-G0MAA6 2048596 10 m D01.2308-G0MAA6 2048596 5 m D01.2308-G0MAA6 2048596 10 m D01.2205-G05MQ 6026006 10 m D01.2205-G10MQ 6026006 10 m D01.1205-G10MQ 6026006 10 m D01.1205-G10MQ 6032636 10 m D01.1205-G20MQ 6032636 10 m D01.1205-G20MQ 6032636 10 m D01.1205-G30MQ 6032636 10 m			10 m	CO	6049454
Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm    Mo3MACSCO			1.5 m	W1M5ACSCO	6049455
### ### ### ### ### ### ### ### ### ##		Head B: cable	3 m	W03MACSCO	6049456
Head A: female connector, M12, 5-pin, straight Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm Head A: female connector, M12, 5-pin, straight Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm Head A: female connector, M12, 5-pin, straight Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² Head B: cable		Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm²,	5 m	W05MACSC0	6049457
Head A: female connector, M23, 12-pin, straight Head B: cable Cable: SSI, suitable for drag chain, PVC, shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm  D0L-2308-G03MAA6 2048598 5 m D0L-2308-G05MAA6 2048598 10 m D0L-2308-G10MAA6 2048598 10 m D0L-2308-G10MAA6 2048598 10 m D0L-2308-G10MAA6 2048598 10 m D0L-1205-G05MQ 6026008 10 m D0L-1205-G10MQ 6026008 10 m D0L-1205-G10MQ 6032638 10 m D0L-1205-G10MQ 6032638 10 m D0L-1205-G15MQ 6032638 10 m D0L-1205-G10MQ 6032638 10 m D0L-1205-G10MQ 6032638 10 m D0L-1205-G20MQ 6032638 10 m D0L-1205-G20MQ 6032638 10 m D0L-1205-G30MQ 6032861 10 m D0L-1205-G30MQ 6032638 10 m D0L-1205-G30MQ 6032			10 m		6049458
Head A: female connector, M23, 12-pin, straight Head B: cable Cable: SSI, suitable for drag chain, PVC, shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm  D0L-2308-G05MAA6 2048598 10 m D0L-2308-G10MAA6 2048598 10 m D0L-1205-G05MQ 6026006 10 m D0L-1205-G10MQ 6026006 10 m D0L-1205-G10MQ 6026006 10 m D0L-1205-G12MQ 6032636 15 m D0L-1205-G12MQ 6032636 2 x 0.34 mm², Ø 8.0 mm  D0L-1205-G12MQ 6032636 15 m D0L-1205-G20MQ 6032636 30 m D0L-1205-G30MQ 6032636 30 m D0L-1205-G30MQ 6032636 50 m D0L-1205-G30MQ 6032861 10 m D0L-1205-W10MQ 6041423 10 m D0L-1205-G05MY 6053041 10 m D0L-1205-G05MY 6053041 10 m D0L-1205-G05MY 6053041 10 m D0L-1205-G05MY 6053041 10 m D0L-1205-G05MY 6053042 10 m D0L-1205-G05MY 6053042 10 m D0L-1205-G05MY 6053042					
Cable: SSI, suitable for drag chain, PVC, shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm  5 m D0L-2308-G10MAA6 2048598 10 m D0L-2308-G10MAA6 2048598 5 m D0L-1205-G05MQ 6026006 10 m D0L-1205-G10MQ 6026008 10 m D0L-1205-G12MQ 6032636 10 m D0L-1205-G20MQ 6032636 10 m		Head A: female connector, M23, 12-pin, straight	1.5 m	DOL-2308-G1M5AA6	2048596
10 m DoL-2308-G05MAA6 2048598 10 m DoL-2308-G10MAA6 2048598 5 m DoL-1205-G05MQ 6026006 10 m DoL-1205-G10MQ 6026006 10 m DoL-1205-G12MQ 6032636 15 m DoL-1205-G12MQ 6032636 15 m DoL-1205-G12MQ 6032636 2 x 0.34 mm², Ø 8.0 mm 20 m DoL-1205-G20MQ 6032636 30 m DoL-1205-G20MQ 6032638 30 m DoL-1205-G30MQ 6032638 50 m DoL-1205-G50MQ 6032861 50 m DoL-1205-G50MQ 6032861 50 m DoL-1205-W05MQ 6041423 50 m DoL-1205-W05MQ 6053041 50 m DoL-1205-G05MY 6053042 50 m DoL-1205-G05MY 6053042 50 m DoL-1205-G05MY 6053042			3 m	DOL-2308-G03MAA6	2048597
Head A: female connector, M12, 5-pin, straight Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm  Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm  Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm  Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm   5 m  DOL-1205-G05MQ 6032636 50 m DOL-1205-G50MQ 6032861 5 m DOL-1205-W10MQ 6041425 5 m DOL-1205-G02MY 6053041 6053042		Cable. Soi, Saltable for drag chall, 1 vo, Silledad, 4 x 2 x 0.15 illili , 5 5.6 illili			2048598
Head A: female connector, M12, 5-pin, straight Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm  Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 2 m DoL-1205-G20MQ 6032638  50 m DoL-1205-G30MQ 6032638  50 m DoL-1205-G50MQ 6032861  The connector of					2048599
Head A: female connector, M12, 5-pin, straight Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm  12 m DOL-1205-G12MQ 6032636 15 m DOL-1205-G20MQ 6032638 30 m DOL-1205-G20MQ 6032638 50 m DOL-1205-G30MQ 6032861 50 m DOL-1205-G50MQ 6032861 6032638 50 m DOL-1205-G50MQ 6032861 6041423 6041423 6053041 6053041 6053042 6053042 6053043					
Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm  15 m DOL-1205-G15MQ 6032637 20 m DOL-1205-G20MQ 6032638 30 m DOL-1205-G30MQ 6032638 50 m DOL-1205-G50MQ 6032861 50 m DOL-1205-W05MQ 6041423 Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm  Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm  10 m DOL-1205-G10MY 6053042					6026008
Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm  15 m DOL-1205-G15MQ 6032638 20 m DOL-1205-G20MQ 6032638 30 m DOL-1205-G30MQ 6032638 50 m DOL-1205-G50MQ 6032861 50 m DOL-1205-W05MQ 6041423 Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm  Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm  10 m DOL-1205-G10MY 6053042	11			,	
30 m DOL-1205-G30MQ 6032639 50 m DOL-1205-G50MQ 6032861 50 m DOL-1205-G50MQ 6032861 Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm  30 m DOL-1205-G30MQ 6032639 50 m DOL-1205-W05MQ 6041423 50 m DOL-1205-W10MQ 6041423 50 m DOL-1205-G02MY 6053041	1	Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded,		,	
Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm  Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm  50 m DOL-1205-G50MQ 6032861  10 m DOL-1205-W10MQ 6041425  10 m DOL-1205-G02MY 6053041  5 m DOL-1205-G05MY 6053042	* •	2 x 0.34 mm <sup>2</sup> , Ø 8.0 mm			
Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm  Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm  5 m  DOL-1205-W05MQ 6041423  6053041  5 m  DOL-1205-G02MY 6053042					
Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm  Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm  10 m  DOL-1205-W10MQ 6041425 5 m DOL-1205-G02MY 6053042		Head Asfamala connector MAQ E nin and d David			
Ø 7.8 mm       2 m       DOL-1205-G02MY       6053041         Head B: cable       5 m       DOL-1205-G05MY       6053042         Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm²       5 m       DOL-1205-G05MY       6053042         + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm       10 m       DOL-1205-G10MY       6053043		Head B: cable			6041423
Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm  10 m DOL-1205-G10MY 6053043				,	
+ 2 x 0.25 mm <sup>2</sup> + 1 x 0.34 mm <sup>2</sup> , Ø 6.7 mm		Head B: cable			
A-CUUEU	10	· · · · · · · · · · · · · · · · · · ·			6053042

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Warning! Only in combination with electrical interfaces A, C, E and P.

Figure	Brief description	Length of cable	Туре	Part no.
	Head As famely connector M12. Onin atraight	2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight  Head B: cable	5 m	DOL-1208-G05MAC1	6032867
- TO	Cable: incremental, suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> ,	10 m	DOL-1208-G10MAC1	6032868
	Ø 7.0 mm	20 m	DOL-1208-G20MAC1	6032869
	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm $^{1)}$	2 m	DOL-2312-G02MLA3	2030682
		7 m	DOL-2312-G07MLA3	2030685
_		10 m	DOL-2312-G10MLA3	2030688
		15 m	DOL-2312-G15MLA3	2030692
•		20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
		1.5 m	DOL-2312-G1M5MA3	2029212
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA3	2029213
-	Head B: cable	5 m	DOL-2312-G05MMA3	2029214
	Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	10 m	DOL-2312-G10MMA3	2029215
	T 2 X O.3 IIIIII T 1 X O.14 IIIIII P, W 1.0 IIIIII 7	20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217

<sup>&</sup>lt;sup>1)</sup> Warning! Only in combination with electrical interfaces A, C, E and P.

### Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded	5 m	STL-1205-G05MQ	6026005
	Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded,	10 m	STL-1205-G10MQ	6026007
0	2 x 0.34 mm², Ø 8.0 mm Wire shielding: AL-PT foil, total shield, tin-plated C shield	12 m	STL-1205-G12MQ	6032635
	Head A: male connector, M12, 5-pin, angled, B-coded	5 m	STL-1205-W05MQ	6041426
6	Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x $0.64~\text{mm}^2$ , Ø $7.8~\text{mm}$	10 m	STL-1205-W10MQ	6041427
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	STL-1204-G02ME90	6045284
The state of	Head B: cable	5 m	STL-1204-G05ME90	6045285
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	10 m	STL-1204-G10ME90	6045286
		2 m	STL-1204-W02ME90	6047912
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: cable	5 m	STL-1204-W05ME90	6047913
8 400	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm	10 m	STL-1204-W10ME90	6047914
		25 m	STL-1204-W20ME90	6047915
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	STL-1204-G02MZ90	6048247
(C) -44	Head B: cable	5 m	STL-1204-G05MZ90	6048248
	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	STL-1204-G10MZ90	6048249
		2 m	STL-1204-W02MZ90	6048256
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: cable	5 m	STL-1204-W05MZ90	6048257
1	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	STL-1204-W10MZ90	6048258
		25 m	STL-1204-W25MZ90	6048259

# Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm $\dots$ 6 mm Head B: -	DOS-1204-G	6007302
<b>40</b>	Head A: female connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	DOS-1205-G	6009719
	Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm $\dots$ 6.5 mm Head B: -	DOS-1204-W	6007303
	Head A: female connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^{\circ}$ C +85 $^{\circ}$ C	DOS-1208-GA01	6045001
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -20 °C +130 °C	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: - Operating temperature: -40 °C +125 °C	DOS-2312-G02	2077057
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature: -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M12, 5-pin, straight, B-coded, shielded, PROFIBUS, for cable diameter 4 mm $\dots$ 9 mm Head B: -	DOS-1205-GQ	6021353
	Head A: female connector, M12, 5-pin, angled, B-coded, shielded, PROFIBUS, for cable diameter 4 mm $\dots$ 8 mm Head B: -	DOS-1205-WQ	6041429
6	Head A: female connector, M12, 5-pin, straight, shielded, CANopen, DeviceNet, for cable diameter 4.5 mm $\dots$ 7 mm Head B: -	DOS-1205-GA	6027534
	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm 8 mm Head B: -	DOS-1204-GE	6048153
	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm 8 mm Head B: -	DOS-1204-WE	6048154
	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm $\dots$ 8 mm	DOS-1204-GZ	6048263
	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm 8 mm	DOS-1204-WZ	6048264

### Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm		LTG-2102-MW	6021355
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , $\emptyset$ 5.6 mm		LTG-2308-MWENC	6027529
<u></u>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	By the meter	LTG-2411-MW	6027530
_	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2512-MW	6027531
<b>\</b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25$ mm <sup>2</sup> + $2 \times 0.5$ mm <sup>2</sup> + $2 \times 0.14$ mm <sup>2</sup> , Ø 7.8 mm		LTG-2612-MW	6028516

### Other plug connectors and cables

Figure	Brief description	Туре	Part no.
	A3M60 accessories sales set comprising: Female cable connector supply voltage M12 angled (6007303) Female cable connector M12 angled (6041429) Male cable connector M12 angled (6041428)	DOS-3XM12-W	2058177
00	Head A: female connector, M12, 4-pin, D-coded Head B: female connector, RJ45, 8-pin Cable: shielded Switch cabinet feedthrough	Feedthrough female connector Ethernet RJ45	6048180
1	Head A: male connector, M12, 4-pin, straight, B-coded Cable: PROFIBUS terminator	STE-END-Q	6021156

# Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	STE-1205-G	6022083
0	Head A: male connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -	STE-1205-GQ	6021354
	Head A: male connector, M12, 8-pin, straight, A encoded, shielded, for cable diameter 4 mm 8 mm  Head B: -  Operating temperature: -40 °C +85 °C	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	STE-2312-G01	2077273
	Head A: male connector, M12, 5-pin, angled, B-coded, shielded, PROFIBUS, for cable diameter 4 mm $\dots$ 8 mm Head B: -	STE-1205-WQ	6041428

Figure	Brief description	Туре	Part no.
Co	Head A: male connector, M12, 5-pin, straight, A encoded, shielded, CANopen, DeviceNet, for cable diameter 4 mm 8 mm Head B: -	STE-1205-GA	6027533
	Head A: male connector, M12, 5-pin, straight, shielded Cable: CANopen terminator	STE-1205-GKEND	6037193
	Head A: male connector, RJ45, 8-pin, straight, shielded, EtherNet/IP, for cable diameter 4.5 mm $\dots$ 8 mm Head B: -	STE-0J08-GE	6048150
Co	Head A: male connector, M12, 4-pin, straight, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm 8 mm Head B: -	STE-1204-GE01	6048151
	Head A: male connector, M12, 4-pin, angled, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm 8 mm Head B: -	STE-1204-WE	6048152
	Head A: male connector, RJ45, 4-pin, straight, shielded, PROFINET, EtherCAT, for cable diameter 4.5 mm 8 mm	STE-0J04-GZ	6048260
Co	Head A: male connector, M12, 4-pin, straight, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm 8 mm	STE-1204-GZ	6048261
	Head A: male connector, M12, 4-pin, angled, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm 8 mm	STE-1204-WZ	6048262

#### Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, 4 x 2 x 0.08 mm <sup>2</sup>	0.5 m	DSL-3D08-G0M5AC3	2046580
	Head A: female connector, M12, 5-pin, straight	2 m	DSL-1205-G02MY	6053044
TO TO	Head B: male connector, M12, 5-pin, straight Cable: CANopen, suitable for drag chain, PUR, halogen-free, shielded,	5 m DSL-1205-	DSL-1205-G05MY	6053045
	2 x 0.34 mm <sup>2</sup> + 2 x 0.25 mm <sup>2</sup> + 1 x 0.34 mm <sup>2</sup> , Ø 6.7 mm, A-coded	10 m	DSL-1205-G10MY	6053046

### Connection cables with male and male connector

Figure	Brief description		Туре	Part no.
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-1204-G02ME90	6045222
C (6)	Head B: male connector, M12, 4-pin, straight, D-coded	5 m	SSL-1204-G05ME90	6045277
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm	10 m	SSL-1204-G10ME90	6045279
	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-1204-H02ME90	6047908
6	Head B: male connector, M12, 4-pin, straight, D-coded	5 m	SSL-1204-H05ME90	6047909
Cable: EtherNet/IP, PUR,	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	10 m	SSL-1204-H10ME90	6047910
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-2J04-G02ME60	6047916
	Head B: male connector, RJ45, 8-pin, straight	5 m	SSL-2J04-G05ME60	6047917
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	10 m	SSL-2J04-G10ME60	6047918
	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-2J04-H02ME	6047911
9	Head B: male connector, RJ45, 8-pin, straight	5 m	SSL-2J04-H05ME	6045287
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	10 m	SSL-2J04-H10ME	6045288
	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-1204-F02MZ90	6048250
	Head B: male connector, M12, 4-pin, straight	5 m	SSL-1204-F05MZ90	6048251
	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-1204-F10MZ90	00 6048252

Figure	Brief description		Туре	Part no.
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-1204-G02MZ90	6048241
(6)	Head B: male connector, M12, 4-pin, straight	5 m	SSL-1204-G05MZ90	6048242
Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mr	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-1204-G10MZ90	6048243
_	Head A: male connector, RJ45, 4-pin, straight, D-coded	2 m	SSL-2J04-F02MZ	6048253
	Head B: male connector, M12, 4-pin, angled	5 m	SSL-2J04-F05MZ	6048254
	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-2J04-F10MZ	6048255
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-2J04-G02MZ60	6048244
	Head B: male connector, RJ45, 4-pin, straight	5 m	SSL-2J04-G05MZ60	6048245
	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-2J04-G10MZ60	6048246

### Other accessories

### Spare parts

Figure	Brief description	Туре	Part no.
· 0001111	Spare mounting set for MRA-G190 (10 m EcoLine)	BEF-MK-MRA-G01	5326294

### Programming and configuration tools

Figure	Brief description	Туре	Part no.
	Programming unit <sup>1)</sup> USB, for programmable SICK encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoders.	PGT-08-S	1036616
A SI 'SI Y	Programming unit display for programmable SICK DFS60, VFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254

<sup>&</sup>lt;sup>1)</sup> Can be used with programmable incremental and absolute encoders in conjunction with the corresponding adapter cables.

<sup>→</sup> For additional accessories, please see page K-668 onwards

8015560/2015-09-01 Subject to change without notice

# COMPACT DESIGN - WITH AN INTEGRATED ENCODER



# **Product description**

In the Compact family, the encoder is integrated into the wire draw mechanics. This integration provides the encoder with the best possible protection in harsh

industrial environments These encoders provide a measuring range of up to 5 m with high resolution in an absolute or incremental output.

# At a glance

- Measuring lengths from 2 m to 5 m
- Integrated measuring system
- Compact housing (90 mm x 90 mm x 90 mm)
- · Incremental and absolute versions
- · High resolution

#### Your benefits

- Industrial design: the encoder is integrated in the aluminum housing, making it less susceptible to external damage and thus reducing maintenance time and costs
- Extremely precise measurements by eliminating the coupling between the encoder and the mechanism
- Space-saving installation, since the encoder is directly integrated into the wire draw mechanics.
- Very precise measurements thanks to the high resolution





# More information

Fields of application I-577
Detailed technical data I-577
Type code
Ordering information I-583
Dimensional drawings I-584
Recommended accessories I-588

→ www.mysick.com/en/Compact

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

- Automated guided systems (fork height)
- · Manned forklift trucks
- · Storage and rack operation equipment

- · Wood processing machines
- · Lifting platforms

# Detailed technical data

#### **BKS**

#### Performance

	BKS02 0 m 2 m	BKS05 0 m 5 m
Measuring range	0 m 2 m	0 m 5 m
Linearity	≤ ± 0.7 mm	
Measurement increment	≥ 0.05 mm	
Traversing speed	3.5 m/s	
Typ. repeat accuracy	3 measuring steps	

#### Interfaces

Encoder	Absolute encoder
Electrical interface	12 V 30 V SSI
Connection type	M23 male connector, 12-pin
Clock frequency	1 MHz <sup>1)</sup>
Interface signals	Clock +, Clock -, Data +, Data-

<sup>1)</sup> Min. LOW level (Clock +): 500 ns.

# Electrical data

Initialization time	≥ 200 ms <sup>1)</sup>
Position forming time	0.1 ms
Supply voltage	12 V 30 V
Code sequence	Rising at wire pull-out
Code type	24 bit/gray
MTTFd: mean time to dangerous failure	150 years (EN ISO 13849) <sup>2)</sup>

 $<sup>^{\</sup>mbox{\tiny $1$}\mbox{\sc Valid}}$  Valid positional data can be measured once this time has elapsed.

#### Mechanical data

	BKS02 0 m 2 m	BKS02 0 m 5 m
Mass	1.5 kg	
Measuring wire material	Highly flexible stranded steel (PA 12 sheathed)	
Measuring wire diameter	0.6 mm	
Housing material	Aluminum	
Spring return force	5 N 6 N <sup>1)</sup>	4 N 6 N <sup>1)</sup>
Service life of wire draw mechanism	800,000 cycles <sup>2) 3)</sup>	
Wire acceleration	≤ 20 m/s²	

<sup>1)</sup> These values were measured at an ambient temperature of 25 °C. There may be variations at other temperatures.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

<sup>&</sup>lt;sup>2)</sup> Mean values that depend on the type of load, a cycle is made up of a wire intake and outake.

<sup>3)</sup> At high operating speeds over great lengths, this figure can decrease; at slow operating speeds over short lengths, it can increase.

# Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating (encoder)	IP 52 (as per IEC60529), observe specified installation location
Resistance to shocks (according to EN 60068-2-27)	20 g, 6 ms
Resistance to vibration (according to EN 60068-2-6)	10 g, 10 Hz 2,000 Hz
Operating temperature range (encoder)	-10 °C +70 °C
Storage temperature range	-20 °C +80 °C
Relative humidity/condensation	90% 1)

<sup>1)</sup> Condensation of optical surfaces not permitted.

# XKS

#### Performance

	XKS02 0 m 2 m	XKS05 0 m 5 m
Measuring range	0 m 2 m	0 m 5 m
Period length	1.1953 mm	
Linearity	≤ ± 0.7 mm	
Non-linearity	± 0.1 mm	
Measurement increment 1)	≥ 0.295 µm	
Traversing speed	3.5 m/s	
Wire acceleration	≤ 20 m/s²	
Typ. repeat accuracy	≤ 0.15°	

<sup>1)</sup> With 12 bit resolution.

#### Interfaces

Encoder	Absolute encoder
Electrical interface	7 V 12 V HIPERFACE®
Connection type	M12 male connector, 8-pin
Interface signals	Process data channel SIN, REFSIN, COS, REFCOS: analog, differential Parameter channel RS 485: digital
Number of sine/cosine periods per revolution	128

# Electrical data

Operating current	60 mA (without load)
Output frequency for sine/cosine signals	0 kHz 65 kHz
Available memory area	1,792 bytes
E <sup>2</sup> PROM	2048 Eeprom
Supply voltage	7 V 12 V
Code sequence	Rising at wire pull-out
Code type	Binary
MTTFd: mean time to dangerous failure	250 years (EN ISO 13849) <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

# Mechanical data

	XKS02 0 m 2 m	XKS05 0 m 5 m
Mass	1.5 kg	
Measuring wire material	Highly flexible stranded steel (PA 12 sheathed)	
Measuring wire diameter	0.6 mm	
Housing material	Aluminum	
Spring return force	5 N 6 N <sup>1)</sup>	4 N 6 N <sup>1)</sup>
Service life of wire draw mechanism	800,000 cycles <sup>2) 3)</sup>	
Wire acceleration	≤ 20 m/s²	

 $<sup>^{1)}</sup>$  These values were measured at an ambient temperature of 25  $^{\circ}$  C. There may be variations at other temperatures.

#### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating (encoder)	IP 52 (as per IEC 60529), observe specified installation location
Resistance to shocks (according to EN 60068-2-27)	20 g, 6 ms
Resistance to vibration (according to EN 60068-2-6)	10 g, 10 Hz 2,000 Hz
Operating temperature range (encoder)	-10 °C +70 °C
Storage temperature range	-20 °C +80 °C
Relative humidity/condensation	90% 1)

 $<sup>^{\</sup>scriptscriptstyle 1)}$  Condensation of optical surfaces not permitted.

<sup>&</sup>lt;sup>2)</sup> Mean values that depend on the type of load, a cycle is made up of a wire intake and outake.

<sup>&</sup>lt;sup>3)</sup> At high operating speeds over great lengths, this figure can decrease; at slow operating speeds over short lengths, it can increase.

# **PKS**

#### Performance

	PKS02 0 m 2 m	PKS05 0 m 5 m
Measuring range	0 m 2 m	0 m 5 m
Linearity	≤ ± 0.7 mm	
Measurement increment 1)	≥ 0.05 mm	
Traversing speed	3.5 m/s	
Wire acceleration	≤ 20 m/s²	
Typ. repeat accuracy	3 measuring steps	

 $<sup>^{1)}</sup>$  Based on the assumption that the control/counter evaluates the edges of pulses A and B.

#### Interfaces

Encoder	Incremental encoders
Electrical interface	4.5 V 5.5 V TTL/RS422
Connection type	M23 male connector, 12-pin

#### Electrical data

Operating current	60 mA (without load)
Reference signal	1/765 measuring steps
Maximum load current	≤ 20 mA
Initialization time	≥ 40 ms <sup>1)</sup>
Supply voltage	4.5 V 5.5 V
MTTFd: mean time to dangerous failure	400 years (EN ISO 13849) <sup>2)</sup>

<sup>1)</sup> Valid positional data can be measured once this time has elapsed.

# Mechanical data

	PKS02 0 m 2 m	PKS05 0 m 5 m
Mass	1.5 kg	
Measuring wire material	Highly flexible stranded steel (PA 12 sheathed)	
Measuring wire diameter	0.6 mm	
Housing material	Aluminum	
Spring return force	5 N 6 N <sup>1)</sup>	4 N 6 N <sup>1)</sup>
Service life of wire draw mechanism	800,000 cycles <sup>2) 3)</sup>	
Wire acceleration	≤ 20 m/s²	

 $<sup>^{1)}</sup>$  These values were measured at an ambient temperature of 25  $^{\circ}$  C. There may be variations at other temperatures.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

 $<sup>^{\</sup>rm 2)}$  Mean values that depend on the type of load, a cycle is made up of a wire intake and outake.

<sup>3)</sup> At high operating speeds over great lengths, this figure can decrease; at slow operating speeds over short lengths, it can increase.


#### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating (encoder)	IP 52 (as per IEC 60529), observe specified installation location
Resistance to shocks (according to EN 60068-2-27)	20 g, 6 ms
Resistance to vibration (according to EN 60068-2-6)	10 g, 10 Hz 2,000 Hz
Operating temperature range (encoder)	-10 °C +70 °C
Storage temperature range	-20 °C +80 °C
Relative humidity/condensation	90% 1)


<sup>1)</sup> Condensation of optical surfaces not permitted.

# Type code


# Compact absolute BKS



#### Compact absolute XKS



# **Compact incremental PKS**




# Ordering information

Measuring range	Electrical interface	Connection type	Туре	Part no.
	SSI	M23 male connector, 12-pin, radial	BKS09-ATBM0220	1035240
0 m 2 m	7 V 12 V, HIPERFACE®	M12 male connector, 8-pin, radial	XKS09-HTBM0227	1035436
	4.5 V5.5 V, TTL/RS422	M23 male connector, 12-pin, radial	PKS09-ATBM0220	1035242


Measuring range	Electrical interface	Connection type	Туре	Part no.
	SSI	M23 male connector, 12-pin, radial	BKS09-ATBM0520	1035241
0 m 5 m	7 V 12 V, HIPERFACE®	M12 male connector, 8-pin, radial	XKS09-HTBM0527	1035437
	4.5 V5.5 V, TTL/RS422	M23 male connector, 12-pin, radial	PKS09-ATBM0520	1035243

# Dimensional drawings (dimensions in mm)

# BKS and PKS




# XKS



# Deflection roller design

With the aid of deflection rollers, it is possible to guide the measuring wire of wire draw encoders over edges and around corners without significantly affecting the life time of the wire draw encoder. In this case, it must be considered that the designs of the deflection roller and of the measuring wire must be compatible in order to avoid damage to the system.



- D = groove base diameter.
- d = diameter of the wire incl. coating.
- r = groove radius = 0.53 x d
- $\alpha$  = groove opening angle =  $60^{\circ}$

- The groove radius should not be too small recommendation: 0.53 x diameter of the wire cable
- The groove opening angle should be neither too small nor too large recommendation: 60°
- In order to ensure the longest possible system life, the deflection roller material should be neither too soft nor too hard **recommended material: polyamide**
- The groove base diameter of the deflection roller should not be too small see table for recommendations

#### **EcoLine**


Length	Measuring wire, PA- sheathed	Diameter of the measuring wire	Structure of the measuring wire (strands x cords)	Min. groove base diameter
1.25 m	PA12	0.45 mm	7 x 7	25 mm
3 m	-	0.55 mm	1 x 19	40 mm
5 m	-	0.55 mm	1 x 19	40 mm
10 m	-	0.55 mm	1 x 19	40 mm

# HighLine


Length	Measuring wire, PA- sheathed	Diameter of the measuring wire	Structure of the measuring wire (strands x cords)	Min. groove base diameter
2 m	-	1.35 mm	7 x 19	35 mm
3 m	-	1.35 mm	7 x 19	35 mm
5 m	-	1.35 mm	7 x 19	35 mm
10 m	-	1.35 mm	7 x 19	35 mm
20 m		0.81 mm	7 x 7	35 mm
30 m		0.81 mm	7 x 7	35 mm
50 m		1.35 mm	7 x 19	35 mm

# Installation of deflection rollers


# General notes on the installation of deflection rollers



The deflection roller should always be installed in a way which ensures that running is smooth. The deflection roller should ideally have an integrated ball bearing.



The smaller the deflection angle ( $\alpha$ ) achieved by a deflection roller, the less wear will appear on the measuring wire and therefore the longer the service life of the wire draw mechanism.




If two or more deflection rollers are needed, then the deflection rollers should always be installed at a distance from one another. The requisite distance between the deflection rollers must be accurately defined on site, accounting for specific customer requirements.

#### Wire sag

If the measuring wire is pulled out in a horizontal direction, this creates sag that becomes more pronounced as the wire length increases. This has particular implications for applications with obstacles that could get in the way of the moving measuring wire. However, the change in length that results from the sag, and the measurement error this leads to, are negligible.

#### Calculating the wire sag

The mass of the free-hanging measuring wire creates weight-related force, and this causes the wire to bend into a hyperbola-shaped line. The tension force in the measuring wire acts against the sag. As the measurement length increases, so too does the tension force as a result of the spring drive. We can imagine the hyperbola shape in a simplified format that looks approximately like a triangle.



The weight-related force of the measuring wire can be calculated using Formula A.

The spring rate of the spring drive is calculated using Formula B.

Formula C determines the sag of the measuring wire (the results of Formula A and Formula B are required in order to calculate the wire sag).

**Formula D** is used for calculating the measurement error.

The values found in real life will differ from the theoretical values that are calculated, as the measuring wire itself demonstrates a certain amount of resistance against the sag.

### Formula A

# F<sub>G</sub> = 0.5 x m<sub>1</sub> x g x L

F<sub>G</sub> = weight-related force of the measuring wire [N]

 $m_L$ = length-related mass of the measuring wire [Kg/m]

g = gravitational acceleration 9.81 [m/s<sup>2</sup>]

L = free length of the measuring wire

#### Formula B

$$c = \frac{F_{s max} - F_{s min}}{L_{max}}$$

= spring rate of the spring drive [N/m]

 $F_{S max}$  = maximum tensile force in the wire [N]

 $F_{S min}$ = minimum tensile force in the wire [N]

### Formula C

$$h = \frac{L^2 x g x m_L}{8 x (c x L + F_{min})}$$

n = wire sag [mm]

c = spring rate of the spring drive [N/m]

 $F_{S\,min}$  = minimum tensile force in the measuring wire [N]

g = gravitational acceleration 9.81 [m/s<sup>2</sup>]

m<sub>L</sub> = length-related mass of the measuring wire [Kg/m]

L = free length of the measuring wire [m]

#### Formula D

$$f = \sqrt{L^2 + 4 h^2} - L$$

f = measurement error [m]

h = wire sag [m]

= free length of the measuring wire [m]

# Recommended accessories

# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
		2 m	DOL-2312-G02MLA5	2030680
		7 m	DOL-2312-G07MLA5	2030683
	Head A: female connector, M23, 12-pin, straight	10 m	DOL-2312-G10MLA5	2030686
-	Head B: cable	15 m	DOL-2312-G15MLA5	2030690
	Cable: SSI, PUR, shielded	20 m	DOL-2312-G20MLA5	2030693
		25 m	DOL-2312-G25MLA5	2030697
		30 m	DOL-2312-G30MLA5	2030700
		1.5 m	DOL-2312-G1M5MA1	2029200
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA1	2029201
Gar.	Head B: cable	5 m	DOL-2312-G05MMA1	2029202
	Cable: SSI, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup>	10 m	DOL-2312-G10MMA1	2029203
	+ 2 x 0.5 mm <sup>2</sup> + 2 x 0.14 mm <sup>2</sup> , Ø 7.8 mm	20 m	DOL-2312-G20MMA1	2029204
		30 m	DOL-2312-G30MMA1	2029205
	Head As famale compostor MAO Onin atwaight	2 m	DOL-1208-G02MAC1	6032866
	Head A: female connector, M12, 8-pin, straight Head B: cable	5 m	DOL-1208-G05MAC1	6032867
-	Cable: incremental, suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm <sup>2</sup> , Ø 7.0 mm	10 m	DOL-1208-G10MAC1	6032868
	7.0 IIIII	20 m	DOL-1208-G20MAC1	6032869
		2 m	DOL-2312-G02MLA3	2030682
		7 m	DOL-2312-G07MLA3	2030685
	Head A: female connector, M23, 12-pin, straight	10 m	DOL-2312-G10MLA3	2030688
	Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup>	15 m	DOL-2312-G15MLA3	2030692
	+ 1 x 0.14 mm², Ø 7.8 mm <sup>1)</sup>	20 m	DOL-2312-G20MLA3	2030695
		25 m	DOL-2312-G25MLA3	2030699
		30 m	DOL-2312-G30MLA3	2030702
		1.5 m	DOL-2312-G1M5MA3	2029212
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA3	2029213
70-	Head B: cable	5 m	DOL-2312-G05MMA3	2029214
	Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	10 m	DOL-2312-G10MMA3	2029215
		20 m	DOL-2312-G20MMA3	2029216
		30 m	DOL-2312-G30MMA3	2029217

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Warning! Only in combination with electrical interfaces A, C, E and P.

# Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 8-pin, straight Head B: - Cable: shielded	DOS-1208-GA	6028369

Figure	Brief description	Туре	Part no.
Mes	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-20~^{\circ}\text{C}$ $+130~^{\circ}\text{C}$	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057
(F)	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature: -20 °C +130 °C	DOS-2312-W01	2072580

# Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15$ mm², Ø 5.6 mm	By the meter	LTG-2308-MWENC	6027529
<u></u>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm		LTG-2411-MW	6027530
_	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2512-MW	6027531
<b>\</b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2612-MW	6028516
	Cable: unshielded		LTG-3208-MW	6032870

# Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40  ^{\circ}\text{C} \dots +125  ^{\circ}\text{C}$	STE-2312-G01	2077273

<sup>→</sup> For additional accessories, please see page K-668 onwards

# RUGGED DESIGN MEASURES DISTANCES UP TO 50 M - THE HEAVY-DUTY WIRE DRAW ENCODER







# **Product description**

With wire draw lengths from 2 m to 50 m, the HighLine series of wire draw encoders have enormous range. Thanks to guide rollers, the HighLine series enables flexible measurement paths - even around obstacles. Their rugged housing

and dirt-resistant brush assemblies allow the encoder to be used in the toughest of environments, including dust, shock and vibration, which ensure a long service lifetime.

#### At a glance

- Measuring lengths: 2 m to 50 m
- Modular measuring system with a wide selection of interfaces/measuring lengths
- Very rugged system (dirt scraper, integrated brushes)
- High-quality winding mechanism and wire input
- · High enclosure rating
- High resistance to shock and vibrations
- · Extremely high resolution possible
- Expandable using external accessories

#### Your benefits

- Reliable solution for use in harsh ambient conditions
- Long service life due to rugged industrial housing
- Quick and easy installation without the need for precise linear guidance
- Low integration and maintenance costs
- Customization option reduces storage costs
- Quick and easy commissioning thanks to analog interface and option to use low-cost interface card



#### More information

Fields of application I-591
Detailed technical data I-591
Type code
Ordering information I-606
Dimensional drawings I-607
Recommended accessories I-630

→ www.mysick.com/en/HighLine

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



# Fields of application

- · Positioning of storage and retrieval systems
- Positioning grippers and trolleys with cranes
- Automated guided systems

- Elevators
- Lifting platforms
- Presses

#### Detailed technical data

# BTF

#### Performance

	BTF08 0 m 2 m	BTF08 0 m 3 m	BTF08 0 m 5 m	BTF13 0 m 10 m	BTF13 0 m 20 m	BTF13 0 m 30 m	BTF19 0 m 50 m
Measuring range	0 m 2 m	0 m 3 m	0 m 5 m	0 m 10 m	0 m 20 m	0 m 30 m	0 m 50 m
Reproducibility	Max. 0.2 mm <sup>1)</sup>	Max. 0.3 mm <sup>1)</sup>	Max. 0.5 mm <sup>1)</sup>	Max. 1 mm <sup>1)</sup>	Max. 2 mm <sup>1)</sup>	Max. 3 mm <sup>1)</sup>	Max. 5 mm <sup>1)</sup>
Linearity	Max. ± 2 mm <sup>1) 2)</sup>	Max. ± 3 mm <sup>1) 2)</sup>		Max. ± 6 mm <sup>1) 2)</sup>	Max. ± 10 mm <sup>1) 2)</sup>	Max. ± 15 mm <sup>1) 2)</sup>	Max. ± 24 mm <sup>1) 2)</sup>
Hysteresis	Max. 1 mm <sup>1)</sup>	Max. 1.5 mm <sup>1)</sup>	Max. 2 mm <sup>1)</sup>	Max. 4 mm <sup>1)</sup>	Max. 6 mm <sup>1)</sup>	Max. 8 mm <sup>1)</sup>	Max. 10 mm <sup>1)</sup>
Resolution (wire draw + encoder)							
Analog	4 20 mA = 0.02 mm; 0 10 V = 0.02 mm <sup>3) 4)</sup>		4 20 mA = 0 0 10 V = 0.0	,	-		
SSI	0.025 (ATM60) 0.02 (AHM36)		0.05 mm (ATM 0.04 mm (AHM		0.1 mm (ATM60) <sup>3) 4)</sup> 0.06 mm (AHM36) <sup>3) 4)</sup>		
CANopen	0.02 mm (ATM60) <sup>3) 4)</sup> 0.01 mm (AHM36) <sup>3) 4)</sup>		0.04 mm (ATM 0.02 mm (AHM		0.06 mm (ATM60) <sup>3) 4)</sup> 0.03 mm (AHM36) <sup>3) 4)</sup>		
DeviceNet	0.02 mm <sup>3) 4)</sup>		0.04 mm <sup>3) 4)</sup>		0.06 mm <sup>3) 4)</sup>		
PROFIBUS	0.02 mm <sup>3) 4)</sup>		0.04 mm <sup>3) 4)</sup>		0.06 mm <sup>3) 4)</sup>		
EtherNet/IP	0.001 mm <sup>3) 4)</sup>				0.002 mm <sup>3) 4)</sup>		
PROFINET	0.001 mm <sup>3) 4)</sup>						0.002 mm <sup>3) 4)</sup>
EtherCAT®	0.001 mm <sup>3) 4)</sup>						0.002 mm <sup>3) 4)</sup>

 $<sup>^{\</sup>scriptscriptstyle{1)}}$  Value applies to wire draw mechanics.

#### Interfaces

	BTF08 0 m 2 m	BTF08 0 m 3 m	BTF08 0 m 5 m	BTF13 0 m 10 m	BTF13 0 m 20 m	BTF13 0 m 30 m	BTF19 0 m 50 m
Encoder	Absolute encod	er					
Electrical interface	See type code						
Connection type	See type code						
Clock frequency							
Analog	32 kHz					-	
SSI	1 MHz (ATM60) 2 MHz (AHM36						
Address setting							

<sup>&</sup>lt;sup>2)</sup> Value applies under consideration of the exact length of the measuring wire per revolution (located on the wire draw mechanism's label).

<sup>&</sup>lt;sup>3)</sup> The values shown here are rounded.

<sup>&</sup>lt;sup>4)</sup> Sample calculation based on the BTF08 with PROFINET: 200 mm (length of wire draw per revolution - see mechanical data): 262,144 (steps per revolution) = 0.001 mm (resolution from the combination wire draw + encoder)

	BTF08	BTF08	BTF08	BTF13	BTF13	BTF13	BTF19			
	0 m 2 m	0 m 3 m	0 m 5 m	0 m 10 m	0 m 20 m	0 m 30 m	0 m 50 m			
CANopen	0 63 (ATM60 0 127 (AHM3									
DeviceNet	· ·	•								
PROFIBUS	0 127, DIP s	·								
EtherNet/IP										
PROFINET	Via DCP	Via DCP								
Protocol	110 501	na Dor								
CANopen		Communication profile DS 301 V4.0 (ATM60) Communication profile DS 301 V4.02 (AHM36)								
DeviceNet		cification Releas								
PROFIBUS	·		file for encoders	(07hex) - Class	2 (ATM60 PROF	TBUS)				
EtherNet/IP	EtherNet/IP IEC	61784-1								
PROFINET	PROFINET IO /	RT Class B								
EtherCAT®	EtherCAT, CoE	CiA DS-301)								
Bus termination										
CANopen		Via DIP switches (ATM60) Via external terminator (AHM36)								
DeviceNet	Via DIP switche	s								
PROFIBUS	Via DIP switche	s								
Set (electronic adjustment)										
Analog	Teach-in function	onality				-				
SSI	Via SET cable ( H active (L = 0	,	· U <sub>S</sub> V) (AHM36)							
CANopen	Via PRESET pu	shbutton or prof	cocol							
DeviceNet	Via PRESET pu	shbutton or prof	cocol							
PROFIBUS	Via PRESET pu	shbutton or prof	cocol							
EtherNet/IP	Via PRESET pu	shbutton or prof	cocol							
PROFINET	Via PRESET pu	shbutton or prof	cocol							
EtherCAT®	Via PRESET pu	shbutton or prot	cocol							
Encoder profile										
CANopen	Device profile DSP 406 V 2.0 (ATM60) CiA DS-406, V3.2 Class C2 (AHM36)									
DeviceNet	Generic Profile									
PROFIBUS	Encoder profile BUS)	version 1.1 Cla	ss 1 and Class2	(A3M60), profile	e for encoders (0	)7hex) - Class 2	(ATM60 PROFI-			
EtherNet/IP	0 x 22									
PROFINET	V4.1 class3									
EtherCAT®	CiA DS-406									

# Electrical data

	BTF08 0 m 2 m	BTF08 0 m 3 m	BTF08 0 m 5 m	BTF13 0 m 10 m	BTF13 0 m 20 m	BTF13 0 m 30 m	BTF19 0 m 50 m		
Initialization time					'		'		
Analog	≤ 2 ms <sup>1)</sup>								
SSI		Approx. 1,050 ms (ATM60) <sup>1)</sup> LOO ms (AHM36) <sup>1)</sup>							
CANopen	Approx. 12 s (A 2 s (AHM36) 1)	TM60) 1)							
DeviceNet	Approx. 12 s 1)								
PROFIBUS	Approx. 1 s (A3	M60), approx. 1	.2 s (ATM60 PRO	FIBUS) 1)					
EtherNet/IP	Approx. 12 s 1)								
PROFINET	Approx. 12 s 1)								
EtherCAT®	Approx. 12 s 1)								
Supply voltage									
Analog	18 V 33 V					_			
SSI	4.5 V DC 32 10 V 32 V (A								
CANopen	10 V 32 V (A	10 V 32 V (ATM60) 10 V 30 V (AHM36)							
DeviceNet	10 V 32 V								
PROFIBUS	10 V 32 V								
EtherNet/IP	10 V 30 V								
PROFINET	10 V 30 V								
EtherCAT®	10 V 30 V								
Code type									
SSI	Gray (ATM60) Gray, binary (Al-	HM36)							
Power consumption									
Analog	2 W					_			
SSI	0.8 W (ATM60) 1.5 W (AHM36)								
CANopen	2 W (ATM60) 1.5 W (AHM36)	2 W (ATM60)							
DeviceNet									
PROFIBUS	1,5 W (A3M60) 2 W (ATM60 PROFIBUS)								
EtherNet/IP	3 W	3 W							
PROFINET	3 W	3 W							
EtherCAT®	3 W								
1) Valid positional data can be measure		a alanced							

<sup>&</sup>lt;sup>1)</sup> Valid positional data can be measured once this time has elapsed.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

 $<sup>^{\</sup>rm 3)}$  This value relates to the connected encoder only.

	BTF08 0 m 2 m	BTF08 0 m 3 m	BTF08 0 m 5 m	BTF13 0 m 10 m	BTF13 0 m 20 m	BTF13 0 m 30 m	BTF19 0 m 50 m	
MTTFd: mean time to dangerous failure								
SSI	• '	150 years (ATM60) <sup>2) 3)</sup> 230 years (AHM36) <sup>2) 3)</sup>						
CANopen	,	150 years (ATM60) <sup>2) 3)</sup> 270 years (AHM36) <sup>2) 3)</sup>						
DeviceNet	150 years <sup>2) 3)</sup>							
PROFIBUS	,	60 years (A3M60) <sup>2) 3)</sup> 150 years (ATM60 PROFIBUS) <sup>2) 3)</sup>						
EtherNet/IP	80 years <sup>2) 3)</sup>							
PROFINET	80 years <sup>2) 3)</sup>							
EtherCAT®	80 years <sup>2) 3)</sup>							

 $<sup>^{\</sup>mbox{\tiny $1$}\mbox{\sc Valid}}$  Valid positional data can be measured once this time has elapsed.

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

 $<sup>^{\</sup>rm 3)}$  This value relates to the connected encoder only.

# Mechanical data

	BTF08	BTF08	BTF08	BTF13	BTF13	BTF13	BTF19		
	0 m 2 m	0 m 3 m	0 m 5 m	0 m 10 m	0 m 20 m	0 m 30 m	0 m 50 m		
Mass (incl. encoder)				10 111	20111	00111	00 111		
Analog	1.7 kg	1.9 kg	3.2 kg	3.9 kg	5.4 kg	-			
SSI	1.8 kg (ATM60) 1.42 kg (AHM36)	2 kg (ATM60) 1.62 kg (AHM36)	3.3 kg (ATM60) 2.92 kg (AHM36)	4 kg (ATM60) 3.62 kg (AHM36)	5.5 kg (ATM60) 5.12 kg (AHM36)	6.7 kg (ATM60) 6.32 kg (AHM36)	17 kg (ATM60) 16.62 kg (AHM36)		
CANopen	1.89 kg (ATM60) 1.42 kg (AHM36)	2.09 kg (ATM60) 1.62 kg (AHM36)	3.39 kg (ATM60) 2.92 kg (AHM36)	4.09 kg (ATM60) 3.62 kg (AHM36)	5.59 kg (ATM60) 5.12 kg (AHM36)	6.79 kg (ATM60) 6.32 kg (AHM36)	17.09 kg (ATM60) 16.62 kg (AHM36)		
DeviceNet	1.89 kg	2.09 kg	3.39 kg	4.09 kg	5.59 kg	6.79 kg	17.09 kg		
PROFIBUS	1.58 kg (A3M60) 1.89 kg (ATM60 PROFIBUS)	1.78 kg (A3M60) 2.09 kg (ATM60 PROFIBUS)	3.08 kg (A3M60) 3.39 kg (ATM60 PROFIBUS)	3.78 kg (A3M60) 4.09 kg (ATM60 PROFIBUS)	5.28 kg (A3M60) 5.59 kg (ATM60 PROFIBUS)	6.48 kg (A3M60) 6.79 kg (ATM60 PROFIBUS)	16.78 kg (A3M60) 17.09 kg (ATM60 PROFIBUS)		
EtherNet/IP	1.5 kg	1.7 kg	3 kg	3.7 kg	5.2 kg	6.4 kg	16.7 kg		
PROFINET	1.5 kg	1.7 kg	3 kg	3.7 kg	5.2 kg	6.4 kg	16.7 kg		
EtherCAT®	1.5 kg	1.7 kg	3 kg	3.7 kg	5.2 kg	6.4 kg	16.7 kg		
Mass (mechanism)	1.3 kg	1.5 kg	2.8 kg	3.5 kg	5 kg	6.2 kg	16.5 kg		
Measuring wire material	Highly flexible steel wire, 1.4401 stainless steel V4A								
Mass (measuring wire)	7.1 g/m				2.6 g/m		7.1 g/m		
Material, wire draw mecha- nism housing	Aluminum (and die cast	odized), zinc	Aluminum (and	odized), plastic		Aluminum (anodized), zinc die cast			
Wire draw lengths per revo- lution	200 mm <sup>1)</sup>		334.1 mm <sup>1)</sup>		332.4 mm <sup>1)</sup>		491.5 mm <sup>1)</sup>		
Spring return force	6 N 14 N <sup>2)</sup>		15 N 20 N <sup>2)</sup>	10 N 20 N <sup>2)</sup>			18 N 37 N <sup>2)</sup>		
Service life of wire draw mechanism	1 mio. cycles <sup>3</sup>								
Actual wire draw length	2.2 m	3.2 m	5.2 m	10.2 m	20.2 m	30.2 m	50.2 m		
Measuring wire diameter	1.35 mm				0.81 mm		1.35 mm		
Wire acceleration	40 m/s <sup>2</sup>		$70 \text{ m/s}^2$	40 m/s <sup>2</sup>	$30 \text{ m/s}^2$	$15 \text{ m/s}^2$	18 m/s <sup>2</sup>		
Traversing speed	4 m/s								
Integrated encoder									
Analog	ACM60					-			
SSI	ATM60 SSI AHM36 SSI								
CANopen	ATM60 CANop								
DeviceNet	ATM60 Device	Net							
PROFIBUS	A3M60, ATM60	O PROFIBUS							
EtherNet/IP	AFM60 EtherN	et/IP							
PROFINET	AFM60 PROFIN	NET							
EtherCAT®	AFM60 EtherC	AT®							

 $<sup>^{1)}</sup>$  The data shown here are average values. The exact lengths are listed on the label for the wire draw mechanism.

 $<sup>^{\</sup>rm 2)}$  These values were measured at an ambient temperature of 25  $^{\circ}\text{C}.$  There may be variations at other temperatures.

 $<sup>^{\</sup>scriptscriptstyle{(3)}}\,\mathrm{A}$  cycle is made up of a wire intake and outake.

	BTF08 0 m 2 m	BTF08 0 m 3 m	BTF08 0 m 5 m	BTF13 0 m 10 m	BTF13 0 m 20 m	BTF13 0 m 30 m	BTF19 0 m 50 m		
Number of steps per revo- lution									
SSI	8,000 (ATM60) 8,192 (AHM36		6,680 (ATM60) 8,192 (AHM36		4,900 (ATM60) 8,192 (AHM36)				
CANopen	8,192 (ATM60) 16,384 (AHM36)								
DeviceNet	8,192								
PROFIBUS	8,192								
EtherNet/IP	262,144								
PROFINET	262,144	52,144							
EtherCAT®	262,144	52,144							
Article number encoder									
Analog	6045312 6045313			-					
SSI	1034293 (ATM	60)	1034294 (ATM	1034294 (ATM60)		1034295 (ATM60)			
	1068330 (AHN	136)							
CANopen	1030025 (ATM 1065999 (AHM								
DeviceNet	1030018								
PROFIBUS	1051018 (A3N 1030014 (ATM								
EtherNet/IP	1055331								
PROFINET	1059040	1059040							
EtherCAT®	1059061								
Integrated mechanics	MRA-F080- 102D2	MRA-F080- 103D2	MRA-F130- 105D2	MRA-F130- 110D2	MRA-F130- 120D1	MRA-F130- 130D1	MRA-F190- 150D2		
Article number mechanics	6028625	6030125	6028626	6028627	6028628	6028629	6028630		

 $<sup>^{1)}</sup>$  The data shown here are average values. The exact lengths are listed on the label for the wire draw mechanism.

# Ambient data

	BTF08 0 m 2 m	BTF08 0 m 3 m	BTF08 0 m 5 m	BTF13 0 m 10 m	BTF13 0 m 20 m	BTF13 0 m 30 m	BTF19 0 m 50 m		
EMC	According to EN	According to EN 61000-6-2 and EN 61000-6-3							
Enclosure rating (encoder)									
Analog	IP 65	P 65							
SSI		IP 67 (ATM60) IP 66 / IP 67, on the housing side (as per IEC 60529) (AHM36) IP 66 / IP 67, on the shaft side (as per IEC 60529) (AHM36)							
CANopen		_	ide (as per IEC 6 (as per IEC 605	, , , ,					
DeviceNet	IP 67								
PROFIBUS	IP 67								
EtherNet/IP	IP 67								
PROFINET	IP 67								
EtherCAT®	IP 67								

 $<sup>^{2)}</sup>$  These values were measured at an ambient temperature of 25  $^{\circ}$ C. There may be variations at other temperatures.

 $<sup>^{\</sup>scriptsize 3)}\,\mathrm{A}$  cycle is made up of a wire intake and outake.

	BTF08	BTF08	BTF08	BTF13	BTF13	BTF13	BTF19			
	0 m 2 m	0 m 3 m	0 m 5 m	0 m	0 m	0 m	0 m			
				<b>1</b> 0 m	20 m	30 m	50 m			
Enclosure rating (mechanism)	IP 64						IP 31			
Resistance to shocks (as per EN 60068-2-27)										
Analog	50 g, 6 ms					-				
SSI		0 g, 6 ms (ATM60) 00 g, 6 ms (AHM36)								
CANopen	100 g, 6 ms									
DeviceNet	100 g, 6 ms									
PROFIBUS	100 g, 6 ms									
EtherNet/IP	100 g, 6 ms									
PROFINET	100 g, 6 ms									
EtherCAT®	100 g, 6 ms									
Resistance to vibrations (as per EN 60068-2-6)										
SSI	20 g, 10 Hz :	2,000 Hz (ATM6	60, AHM36)							
CANopen	20 g, 10 Hz	2,000 Hz								
DeviceNet	20 g, 10 Hz	2,000 Hz								
PROFIBUS	30 g, 10 Hz 2	2,000 Hz								
EtherNet/IP	30 g, 10 Hz 2	2,000 Hz								
PROFINET	30 g, 10 Hz 2	2,000 Hz								
EtherCAT®	30 g, 10 Hz	2,000 Hz								
Analog	4 g, sine 5 Hz .	100 Hz				-				
Operating temperature range (encoder)										
Analog	-30 °C +80	°C				-				
SSI	-20 °C +85 -40 °C +10									
CANopen	-20 °C +85 -40 °C +85	°C (ATM60 CAN °C (AHM36 CAI								
DeviceNet	-20 °C +85	°C								
PROFIBUS		-10 °C +70 °C (A3M60) -20 °C +85 °C (ATM60 PROFIBUS)								
EtherNet/IP	-30 °C +85	-30 °C +85 °C								
PROFINET	-30 °C +85	-30 °C +85 °C								
EtherCAT®	-30 °C +85	°C								
Operating temperature range (mechanical)	-30 °C +70	°C								

	BTF08 0 m 2 m	BTF08 0 m 3 m	BTF08 0 m 5 m	BTF13 0 m 10 m	BTF13 0 m 20 m	BTF13 0 m 30 m	BTF19 0 m 50 m		
Operating temperature range (combination)									
Analog	-30 °C +70	°C				-			
SSI	-20 °C +70 -30 °C +70	` ,							
CANopen	-20 °C +70 -30 °C +70	`	. ,						
DeviceNet	-20 °C +70	°C							
PROFIBUS	-10 °C +70 -20 °C +70	,	FIBUS)						
EtherNet/IP	-30 °C +70	°C							
PROFINET	-30 °C +70	°C							
EtherCAT®	-30 °C +70	°C							
Relative humidity/condensation									
SSI	90% (ATM60, A	HM36) 1)							
CANopen	98% (ATM60) 1)								
	90% (AHM36) <sup>1</sup>	)							
DeviceNet	98% 1)								
PROFIBUS	,	95% ¹) (A3M60) 98% ¹) (ATM60)							
EtherNet/IP	90% 1)								
PROFINET	90% 1)								
EtherCAT®	90% 1)								

<sup>1)</sup> Condensation of optical surfaces not permitted.

#### **PRF**

#### Performance

	PRF08	PRF08	PRF13	PRF13	PRF13	PRF13	PRF19
	0 m	0 m	0 m	0 m	0 m	0 m	0 m
	2 m	3 m	5 m	10 m	20 m	30 m	50 m
Measuring range	0 m 2 m	0 m 3 m	0 m 5 m	0 m 10 m	0 m 20 m	0 m 30 m	0 m 50 m
Reproducibility	Max.	Max.	Max.	Max.	Max.	Max.	Max.
	0.2 mm <sup>1)</sup>	0.3 mm <sup>1)</sup>	0.5 mm <sup>1)</sup>	1 mm <sup>1)</sup>	2 mm <sup>1)</sup>	3 mm <sup>1)</sup>	5 mm <sup>1)</sup>
Linearity	Max. ± 2 mm <sup>1) 2)</sup>	Max. ± 3 mm <sup>1) 2)</sup>		Max. ± 6 mm <sup>1) 2)</sup>	Max. $\pm$ 10 mm <sup>1) 2)</sup>	Max. ± 15 mm <sup>1) 2)</sup>	Max. ± 24 mm <sup>1) 2)</sup>
Hysteresis	Max.	Max.	Max.	Max.	Max.	Max.	Max.
	1 mm <sup>1)</sup>	1.5 mm <sup>1)</sup>	2 mm <sup>1)</sup>	4 mm <sup>1)</sup>	6 mm <sup>1)</sup>	8 mm <sup>1)</sup>	10 mm <sup>1)</sup>
Resolution (wire draw + encoder)	0.1 mm <sup>3) 4)</sup>		0.2 mm <sup>3) 4)</sup>				0.4 mm <sup>3) 4)</sup>

<sup>1)</sup> Value applies to wire draw mechanics.

#### Interfaces

Encoder	Incremental encoders
Electrical interface	See type code
Connection type	See type code

#### Electrical data

Maximum output frequency	≤ 600 kHz
Reference signal, position	Electric, logically gated with A and B
Reference signal, number	1 electric, logically gated with A and B
Maximum load current	≤ 30 mA
Initialization time	$\leq$ 32 ms, 30 ms, at mechanical zero pulse width $^{1)}$ $^{1)}$
Supply voltage	4.5 V 32 V
Power consumption	0.7 W
MTTFd: mean time to dangerous failure	300 years <sup>2) 3)</sup>

<sup>1)</sup> Valid positional data can be measured once this time has elapsed.

# Mechanical data

	PRF08 0 m 2 m	PRF08 0 m 3 m	PRF13 0 m 5 m	PRF13 0 m 10 m	PRF13 0 m 20 m	PRF13 0 m 30 m	PRF19 0 m 50 m
Mass (incl. encoder)	1.6 kg	1.8 kg	3.1 kg	3.8 kg	5.3 kg	6.5 kg	16.8 kg
Measuring wire material	Highly flexible steel wire, 1.4401 stainless steel V4A						
Mass (measuring wire)	7.1 g/m				2.6 g/m		7.1 g/m
Material, wire draw mechanism housing	Aluminum (ar die cast	nodized), zinc	Aluminum (anodized), plastic		Aluminum (anodized), zinc die cast		

 $<sup>^{1)}</sup>$  The data shown here are average values. The exact lengths are listed on the label for the wire draw mechanism.

<sup>2)</sup> Value applies under consideration of the exact length of the measuring wire per revolution (located on the wire draw mechanism's label).

<sup>3)</sup> The values shown here are rounded.

<sup>&</sup>lt;sup>4)</sup> Sample calculation based on the PRF08 with HTL Push Pull: 200 mm (length of wire draw per revolution - see mechanical data): 2,000 (steps per revolution) = 0.1 mm (resolution from the combination wire draw + encoder)

<sup>&</sup>lt;sup>2)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

<sup>3)</sup> This value relates to the connected encoder only.

<sup>&</sup>lt;sup>2)</sup> These values were measured at an ambient temperature of 25 °C. There may be variations at other temperatures.

<sup>3)</sup> A cycle is made up of a wire intake and outake.

<sup>&</sup>lt;sup>4)</sup> The fitted DFS60 encoders are programmed with the specified number of lines and interface ex-works. Separate programming devices are available for the DFS60 encoders and can be used to adjust the electrical interface (TTL/HTL) and the number of lines (up to a maximum of 10,000 lines) in accordance with the customer's requirements.

	PRF08 0 m 2 m	PRF08 0 m 3 m	PRF13 0 m 5 m	PRF13 0 m 10 m	PRF13 0 m 20 m	PRF13 0 m 30 m	PRF19 0 m 50 m
Wire draw lengths per revolution	200 mm 1)		334.1 mm <sup>1)</sup>		332.4 mm <sup>1)</sup>		491.5 mm <sup>1)</sup>
Spring return force	6 N 14 N <sup>2</sup>	)	15 N 20 N	2)			18 N 37 N <sup>2)</sup>
Service life of wire draw mechanism	1 mio. cycles <sup>3)</sup>						
Actual wire draw length	2.2 m	3.2 m	5.2 m	10.2 m	20.2 m	30.2 m	50.2 m
Measuring wire diameter	1.35 mm				0.81 mm		1.35 mm
Wire acceleration	40 m/s <sup>2</sup>		$70 \text{ m/s}^2$	$40 \text{ m/s}^2$	30 m/s <sup>2</sup>	15 m/s <sup>2</sup>	$18 \text{ m/s}^2$
Traversing speed	4 m/s						
Integrated encoder	DFS60 progr	ammable					
Pulses per revolution	2,000 4)		1,670 <sup>4)</sup>		1,662 4)		1,225 4)
Article number encoder	-						
Integrated mechanics	MRA-F080- 102D2	MRA-F080- 103D2	MRA-F130- 105D2	MRA-F130- 110D2	MRA-F130- 120D1	MRA-F130- 130D1	MRA-F190- 150D2
Article number mechanics	6028625	6030125	6028626	6028627	6028628	6028629	6028630

<sup>1)</sup> The data shown here are average values. The exact lengths are listed on the label for the wire draw mechanism.

#### Ambient data

	PRF08 0 m 2 m	PRF08 0 m 3 m	PRF13 0 m 5 m	PRF13 0 m 10 m	PRF13 0 m 20 m	PRF13 0 m 30 m	PRF19 0 m 50 m
EMC	According to B	EN 61000-6-2	and EN 61000	0-6-3			
Enclosure rating (encoder)	IP 67						
Enclosure rating (mechanism)	IP 64						IP 31
Resistance to shocks (according to EN 60068-2-27)	60 g, 6 ms						
Resistance to vibration (according to EN 60068-2-6)	20 g, 10 Hz	. 2,000 Hz					
Operating temperature range (encoder)	-40 °C +1	00 °C					
Operating temperature range (mechanical)	-30 °C +7	0 °C					
Operating temperature range (combination)	-30 °C +7	0 °C					
Relative humidity/condensation	90% 1)						

 $<sup>^{\</sup>scriptscriptstyle 1)}$  Condensation of optical surfaces not permitted.

<sup>&</sup>lt;sup>2)</sup> These values were measured at an ambient temperature of 25 °C. There may be variations at other temperatures.

 $<sup>^{\</sup>scriptsize\textrm{3)}}\,\textrm{A}$  cycle is made up of a wire intake and outake.

<sup>&</sup>lt;sup>4)</sup> The fitted DFS60 encoders are programmed with the specified number of lines and interface ex-works. Separate programming devices are available for the DFS60 encoders and can be used to adjust the electrical interface (TTL/HTL) and the number of lines (up to a maximum of 10,000 lines) in accordance with the customer's requirements.


# Type code

# HighLine absolute

1 3 130 mm 1 9 190 mm	(only in conjunction with measuring lengths 02 and 03) In (only in conjunction with measuring lengths 05, 10, 20, 30) In (only in conjunction with measuring length 50)  Ctrical interface  SSI  CANopen 10  DeviceNet 10  EtherCAT0  HIPERFACE0 (on request)  SSI + SinCos (on request)  SSI + sinCos (on request)  EtherNet/IP  PROFINET  PROFIBUS 10  SSI + incrementally programmable (on request)  SSI + sinCos programmable (on request)  SSI + sinCos programmable (on request)  SSI + sinCos programmable (on request)  SSI + incremental TTL (on request)
	Connection type  A Male connector, M23, 12-pin, radial (only in combination with interface A)  B Male connector, 3 x M12, axial (only in combination with the electrical interfaces E, I, N, and P with axial outlet)  C Male connector for fieldbus adapters (in combination with interface A)  H Male connector for fieldbus adapters (in combination with the electrical interfaces C, D, and P with radial outlet)  K Cable, 8-wire, universal, 3.0 m (on request)  L Cable, 8-wire, universal, 5.0 m (on request)  M Cable, 8-wire, universal, 5.0 m (on request)  N Male connector, 1 x M12, 8-pin, universal (only in combination with interface A)  Q Male connector, 1 x M12, 5-pin, universal (only in combination with interface C)  Measuring length  O 2 2 meter  O 3 3 meter  O 5 5 meter  1 0 10 meter  2 0 20 meter  3 0 30 meter  5 0 5 meter  Interface / measuring length  A = SSI with connection type A / measuring length 2 m, 3 m  A = SSI with connection type A / measuring length 5 m, 10 m, 20 m, 30 m  A = SSI with connection type N / measuring length 5 m, 10 m, 20 m, 30 m  A = SSI with connection type N / measuring length 5 m, 10 m, 20 m, 30 m  C = CANopen with connection type N / measuring length 5 m, 10 m  A = SSI with connection type N / measuring length 5 m, 10 m, 20 m, 30 m  C = CANopen with connection type H; D = DeviceNet; P = PROFINET / measuring length 5 m, 10 m, 20 m, 30 m  C = CANopen with connection type Q / measuring length 2 m, 3 m  C = CANopen with connection type Q / measuring length 5 m, 10 m, 20 m, 30 m  B = C = CANopen with connection type Q / measuring length 5 m  C = CANopen with connection type Q / measuring length 5 m, 10 m, 20 m, 30 m  B = C = CANopen with connection type Q / measuring length 5 m, 10 m, 20 m, 30 m  B = C = CANopen with connection type Q / measuring length 5 m  B = C = CANopen with connection type Q / measuring length 5 m  B = C = CANopen with connection type B / DeviceNet; P = PROFINET / measuring length 5 m  B = C = CANopen with connection type B / DeviceNet; P = PROFINET / measuring length

<sup>&</sup>lt;sup>1)</sup> Please order fieldbus adapter for CANopen, DeviceNet, and PROFIBUS with radial outlet separately.

# HighLine analog



# Ordering information

Measuring range	Electrical interface	Connection type	Туре	Part no.
	4 mA 20 mA, analog	1 x M12 male connector, 5-pin,	BTF08-K1EM02PP	1060964
	0 V to 10 V analog	radial	BTF08-L1EM02PP	1060965
	SSI	M23 male connector, 12-pin, radial	BTF08-A1AM0240	1034299
0 m 2 m	331	Male connector, 1 x M12, 8-pin, universal	BTF08-A1NM0241	1068884
	CANopen	Male connector, 1 x M12, 5-pin, universal	BTF08-C1QM0282	1068885
	CANOPETI	Bus adapter with cable screw fixings or round connectors, radial $^{1)}$	BTF08-C1HM0241	1034317
	DeviceNet	Bus adapter with cable screw fixings or round connectors, radial $^{1)}$	BTF08-D1HM0241	1034311
	PDOFIDUO	3 x M12 male connectors, 5-pin, axial	BTF08-P1BM0241	1060966
	PROFIBUS	Bus adapter with cable screw fixings or round connectors, radial $^{1)}$	BTF08-P1HM0241	1034305
	PROFINET		BTF08-N1BM0299	1060967
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BTF08-I1BM0299	1060968
	EtherCAT®	u/iui	BTF08-E1BM0299	1060969

<sup>1)</sup> Order adapter separately.

Measuring range	Electrical interface	Connection type	Туре	Part no.
	4 mA 20 mA, analog	1 x M12 male connector, 5-pin,	BTF08-K1EM03PP BTF08-L1EM03PP BTF08-A1AM0340 BTF08-A1NM0341 BTF08-C1QM0382 BTF08-C1HM0341 BTF08-D1HM0341 BTF08-P1BM0341 BTF08-P1BM0349 BTF08-H1BM0399 BTF08-H1BM0399 BTF08-H1BM0399 BTF13-K1EM05PP BTF13-L1EM05PP BTF13-A1AM0520 BTF13-A1AM0524 BTF13-C1QM0549 BTF13-C1HM0525 BTF13-P1BM0525 BTF13-P1BM0525 BTF13-P1BM0525 BTF13-N1BM0599 BTF13-H1BM0599	1060970
	0 V to 10 V analog	radial	BTF08-L1EM03PP	1060973
	SSI	M23 male connector, 12-pin, radial	BTF08-A1AM0340	1034892
	331	Male connector, 1 x M12, 8-pin, universal	BTF08-A1NM0341	1068886
	CANopen	Male connector, 1 x M12, 5-pin, universal	BTF08-C1QM0382	1068887
0 m 3 m	Олгороп	Bus adapter with cable screw fixings or round connectors, radial $^{\mbox{\scriptsize 1}}$	BTF08-C1HM0341	1034895
	DeviceNet	Bus adapter with cable screw fixings or round connectors, radial 1)	BTF08-D1HM0341	1034894
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BTF08-P1BM0341	1060975
	THOTIBOO	Bus adapter with cable screw fixings or round connectors, radial $^{\mbox{\scriptsize 1}}$	BTF08-P1HM0341	1034893
	PROFINET	0.1440	BTF08-N1BM0399	1060976
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BTF08-I1BM0399	1060978
	EtherCAT®		BTF08-E1BM0399	1060980
	4 mA 20 mA, analog	1 x M12 male connector, 5-pin,	BTF13-K1EM05PP	1060982
	0 V to 10 V analog	radial	BTF13-L1EM05PP	1060983
	SSI	M23 male connector, 12-pin, radial	BTF13-A1AM0520	1034300
	331	Male connector, 1 x M12, 8-pin, universal	BTF13-A1NM0524	1068888
	CANopen	Male connector, 1 x M12, 5-pin, universal	BTF13-C1QM0549	1068889
0 m 5 m	Олиорен	Bus adapter with cable screw fixings or round connectors, radial $^{\mbox{\scriptsize 1}}$	BTF13-C1HM0525	1034318
	DeviceNet	Bus adapter with cable screw fixings or round connectors, radial 1)	BTF13-D1HM0525	1034312
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BTF13-P1BM0525	1060985
	FINOFIDUS	Bus adapter with cable screw fixings or round connectors, radial $^{1)}$	BTF13-P1HM0525	1034306
	PROFINET	0.1440	BTF13-N1BM0599	1060986
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BTF13-I1BM0599	1060987
	EtherCAT®		BTF13-E1BM0599	1060988

<sup>1)</sup> Order adapter separately.

Measuring range	Electrical interface	Connection type	Туре	Part no.
	4 mA 20 mA, analog	1 x M12 male connector, 5-pin,	BTF13-K1EM10PP	1060989
	0 V 10 V analog	radial	BTF13-L1EM10PP	1060990
	SSI	M23 male connector, 12-pin, radial	BTF13-A1AM1020	1034301
	331	Male connector, 1 x M12, 8-pin, universal	BTF13-A1NM1024	1068890
	CANopen	Male connector, 1 x M12, 5-pin, universal	BTF13-C1QM1049	1068891
0 m 10 m	CANOPOLI	Bus adapter with cable screw fixings or round connectors, radial $^{1)}$	BTF13-C1HM1025	1034319
	DeviceNet	Bus adapter with cable screw fixings or round connectors, radial 1)	BTF13-D1HM1025	1034313
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BTF13-P1BM1025	1060991
	TROTIBOS	Bus adapter with cable screw fixings or round connectors, radial $^{1)}$	BTF13-P1HM1025	1034307
	PROFINET	2 v M12 made compostave 4 min	BTF13-N1BM1099	1060992
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BTF13-I1BM1099	1060993
	EtherCAT®		BTF13-E1BM1099	1060994
	4 mA 20 mA, analog	1 x M12 male connector, 5-pin,	BTF13-K1EM20PP	1060995
	0 V 10 V analog	radial	BTF13-L1EM20PP	1060996
	SSI	M23 male connector, 12-pin, radial	BTF13-A1AM2020	1034302
	33.	Male connector, 1 x M12, 8-pin, universal	BTF13-A1NM2025	1068892
	CANopen	Male connector, 1 x M12, 5-pin, universal	BTF13-C1QM2049	1068893
0 m 20 m		Bus adapter with cable screw fixings or round connectors, radial <sup>1)</sup>	BTF13-C1HM2025	1034320
	DeviceNet	Bus adapter with cable screw fixings or round connectors, radial 1)	BTF13-D1HM2025	1034314
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BTF13-P1BM2025	1060997
		Bus adapter with cable screw fixings or round connectors, radial <sup>1)</sup>	BTF13-P1HM2025	1034308
	PROFINET	3 x M12 male connectors, 4-pin,	BTF13-N1BM2099	1060998
	EtherNet/IP	axial	BTF13-I1BM2099	1060999
	EtherCAT®		BTF13-E1BM2099	1061000
	SSI	M23 male connector, 12-pin, radial	BTF13-A1AM3020	1034303
		Male connector, 1 x M12, 8-pin, universal	BTF13-A1NM3025	1068894
	CANopen	Male connector, 1 x M12, 5-pin, universal	BTF13-C1QM3049	1068896
	·	Bus adapter with cable screw fixings or round connectors, radial <sup>1)</sup>	BTF13-C1HM3025	1034321
0 m 30 m	DeviceNet	Bus adapter with cable screw fixings or round connectors, radial 1)	BTF13-D1HM3025	1034315
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BTF13-P1BM3025	1061003
		Bus adapter with cable screw fixings or round connectors, radial 1)	BTF13-P1HM3025	1034309
	PROFINET	3 x M12 male connectors, 4-pin,	BTF13-N1BM3099	1061004
	EtherNet/IP	axial	BTF13-I1BM3099	1061005
	EtherCAT®		BTF13-E1BM3099	1061006


<sup>1)</sup> Order adapter separately.

Measuring range	Electrical interface	Connection type	Туре	Part no.
	SSI	M23 male connector, 12-pin, radial	BTF19-A1AM5010	1034304
	331	Male connector, 1 x M12, 8-pin, universal	BTF19-A1NM5017	1068897
	CANopen	Male connector, 1 x M12, 5-pin, universal	BTF19-C1QM5033	1068898
	CANOpen	Bus adapter with cable screw fixings or round connectors, radial 1)	BTF19-C1HM5017	1034322
0 m 50 m	DeviceNet	Bus adapter with cable screw fixings or round connectors, radial 1)	BTF19-D1HM5017	1034316
	PROFIBUS	3 x M12 male connectors, 5-pin, axial	BTF19-P1BM5017	1061009
		Bus adapter with cable screw fixings or round connectors, radial 1)	BTF19-P1HM5017	1034310
	PROFINET		BTF19-N1BM5099	1061010
	EtherNet/IP	3 x M12 male connectors, 4-pin, axial	BTF19-I1BM5099	1061011
	EtherCAT®	3	BTF19-E1BM5099	1061012

<sup>1)</sup> Order adapter separately.

1-605

#### HighLine incremental




# **Ordering information**


• Connection type: M23 male connector, 12-pin, radial

Measuring range	Electrical interface	Туре	Part no.
0 m 2 m	4.5 V5.5 V, TTL/RS422	PRF08-A1AM0240	1034323
0 m 2 m	10 V 32 V, HTL/Push Pull	PRF08-E1AM0240	1034335
0 m 3 m	4.5 V5.5 V, TTL/RS422	PRF08-A1AM0340	1034896
	10 V 32 V, HTL/Push Pull	PRF08-E1AM0340	1034898
0 m 5 m	4.5 V5.5 V, TTL/RS422	PRF13-A1AM0520	1034324
	10 V 32 V, HTL/Push Pull	PRF13-E1AM0520	1034336
0 m 10 m	4.5 V5.5 V, TTL/RS422	PRF13-A1AM1020	1034325
0 III 10 III	10 V 32 V, HTL/Push Pull	PRF13-E1AM1020	1034337
0 m 20 m	4.5 V5.5 V, TTL/RS422	PRF13-A1AM2020	1034326
0 111 20 111	10 V 32 V, HTL/Push Pull	PRF13-E1AM2020	1034338
0 m 30 m	4.5 V5.5 V, TTL/RS422	PRF13-A1AM3020	1034327
0 m 30 m	10 V 32 V, HTL/Push Pull	PRF13-E1AM3020	1034339
0	4.5 V5.5 V, TTL/RS422	PRF19-A1AM5010	1034328
0 m 50 m	10 V 32 V, HTL/Push Pull	PRF19-E1AM5010	1034340


# Dimensional drawings (dimensions in mm)


# BTF08 up to 2 m Analog







BTF08 up to 3 m Analog







BTF13 up to 5 m Analog






BTF13 up to 10 m Analog







# BTF13 up to 20 m Analog





# BTF08 up to 2 m SSI







# BTF08 up to 3 m SSI







# BTF13 up to 5 m SSI







# BTF13 up to 10 m SSI






# BTF13 up to 20 m SSI







BTF13 up to 20 m SSI




# BTF19 up to 50 m SSI




BTF08 up to 2 m CANopen, PROFIBUS, DeviceNet (ATM60)




BTF08 up to 3 m CANopen, PROFIBUS, DeviceNet (ATM60)





BTF13 up to 5 m CANopen, PROFIBUS, DeviceNet (ATM60)






BTF13 up to 10 m CANopen, PROFIBUS, DeviceNet (ATM60)







BTF13 up to 20 m CANopen, PROFIBUS, DeviceNet (ATM60)




BTF13 up to 30 m CANopen, PROFIBUS, DeviceNet (ATM60)




BTF19 up to 50 m CANopen, PROFIBUS, DeviceNet (ATM60)





# BTF08 up to 2 m CANopen, SSI (AHM36)







# BTF08 up to 3 m CANopen, SSI (AHM36)







#### BTF13 up to 5 m CANopen, SSI (AHM36)







# BTF13 up to 10 m CANopen, SSI (AHM36)






#### BTF13 up to 20 m CANopen, SSI (AHM36)







# BTF13 up to 30 m CANopen, SSI (AHM36)




#### BTF19 up to 50 m CANopen, SSI (AHM36)





# BTF08 up to 2 m PR0FIBUS (A3M60)






BTF08 up to 3 m PROFIBUS (A3M60)







# BTF13 up to 5 m PROFIBUS (A3M60)




# BTF13 up to 10 m PROFIBUS (A3M60)







# BTF13 up to 20 m PROFIBUS (A3M60)




#### BTF13 up to 30 m PROFIBUS (A3M60)




# BTF19 up to 50 m PROFIBUS (A3M60)





BTF08 up to 2 m EtherNet/IP, EtherCAT®, PROFINET







BTF08 up to 3 m EtherNet/IP, EtherCAT®, PROFINET







BTF13 up to 5 m EtherNet/IP, EtherCAT®, PROFINET







BTF13 up to 10 m EtherNet/IP, EtherCAT®, PROFINET






BTF13 up to 20 m EtherNet/IP, EtherCAT®, PROFINET






BTF13 up to 30 m EtherNet/IP, EtherCAT®, PROFINET




BTF19 up to 50 m EtherNet/IP, EtherCAT®, PROFINET



#### Deflection roller design

With the aid of deflection rollers, it is possible to guide the measuring wire of wire draw encoders over edges and around corners without significantly affecting the life time of the wire draw encoder. In this case, it must be considered that the designs of the deflection roller and of the measuring wire must be compatible in order to avoid damage to the system.



- D = groove base diameter.
- d = diameter of the wire incl. coating.
- r = groove radius = 0.53 x d
- a = groove opening angle =  $60^{\circ}$

- The groove radius should not be too small recommendation: 0.53 x diameter of the wire cable
- The groove opening angle should be neither too small nor too large recommendation: 60°
- In order to ensure the longest possible system life, the deflection roller material should be neither too soft nor too hard **recommended material: polyamide**
- The groove base diameter of the deflection roller should not be too small see table for recommendations

#### **EcoLine**


Length	Measuring wire, PA- sheathed	Diameter of the measuring wire	Structure of the measuring wire (strands x cords)	Min. groove base diameter
1.25 m	PA12	0.45 mm	7 x 7	25 mm
3 m	-	0.55 mm	1 x 19	40 mm
5 m	-	0.55 mm	1 x 19	40 mm
10 m	-	0.55 mm	1 x 19	40 mm

#### HighLine


Length	Measuring wire, PA- sheathed	Diameter of the measuring wire	Structure of the measuring wire (strands x cords)	Min. groove base diameter
2 m	-	1.35 mm	7 x 19	35 mm
3 m	-	1.35 mm	7 x 19	35 mm
5 m	-	1.35 mm	7 x 19	35 mm
10 m	-	1.35 mm	7 x 19	35 mm
20 m		0.81 mm	7 x 7	35 mm
30 m		0.81 mm	7 x 7	35 mm
50 m		1.35 mm	7 x 19	35 mm

#### Installation of deflection rollers


General notes on the installation of deflection rollers



The deflection roller should always be installed in a way which ensures that running is smooth. The deflection roller should ideally have an integrated ball bearing.



The smaller the deflection angle ( $\alpha$ ) achieved by a deflection roller, the less wear will appear on the measuring wire and therefore the longer the service life of the wire draw mechanism.




If two or more deflection rollers are needed, then the deflection rollers should always be installed at a distance from one another. The requisite distance between the deflection rollers must be accurately defined on site, accounting for specific customer requirements.

#### Wire sag

If the measuring wire is pulled out in a horizontal direction, this creates sag that becomes more pronounced as the wire length increases. This has particular implications for applications with obstacles that could get in the way of the moving measuring wire. However, the change in length that results from the sag, and the measurement error this leads to, are negligible.

#### Calculating the wire sag

The mass of the free-hanging measuring wire creates weight-related force, and this causes the wire to bend into a hyperbola-shaped line. The tension force in the measuring wire acts against the sag. As the measurement length increases, so too does the tension force as a result of the spring drive. We can imagine the hyperbola shape in a simplified format that looks approximately like a triangle.



The weight-related force of the measuring wire can be calculated using Formula A.

The spring rate of the spring drive is calculated using **Formula B**.

Formula C determines the sag of the measuring wire (the results of Formula A and Formula B are required in order to calculate the wire sag).

**Formula D** is used for calculating the measurement error.

The values found in real life will differ from the theoretical values that are calculated, as the measuring wire itself demonstrates a certain amount of resistance against the sag.

#### Formula A

# F<sub>G</sub> = 0.5 x m<sub>1</sub> x g x L

F<sub>G</sub> = weight-related force of the measuring wire [N]

 $m_L$ = length-related mass of the measuring wire [Kg/m]

g = gravitational acceleration 9.81  $[m/s^2]$ 

L = free length of the measuring wire

#### Formula B

$$c = \frac{F_{s \max} - F_{s \min}}{L_{\max}}$$

c = spring rate of the spring drive [N/m]

 $F_{S max}$  = maximum tensile force in the wire [N]

 $F_{S min}$ = minimum tensile force in the wire [N]

#### Formula C

$$h = \frac{L^2 \times g \times m_L}{8 \times (c \times L + F_{min})}$$

n = wire sag [mm]

c = spring rate of the spring drive [N/m]

 $F_{S min}$  = minimum tensile force in the measuring wire [N]

g = gravitational acceleration 9.81 [m/s<sup>2</sup>]

m<sub>L</sub> = length-related mass of the measuring wire [Kg/m]

L = free length of the measuring wire [m]

#### Formula D

$$f = \sqrt{L^2 + 4 h^2} - L$$

f = measurement error [m]

h = wire sag [m]

= free length of the measuring wire [m]

#### Recommended accessories

# Mounting systems

Flanges

Flange plate

Figure	Brief description	Туре	Part no.
	Flange adapter for HighLine wire draw mechanisms, adaption of face mount flange with centering hub 20 mm to 50 mm servo flange	BEF-FA-020-050WDE	2073776

#### Other mounting accessories

Figure	Brief description	Туре	Part no.
	Joint ball for insertion in wire end ring with 20 mm diameter	Joint ball for BTF/ PRF/MRA wire draw	5318683
-C	Additional brush attachment for wire draw mechanism MRA-F080 (2 m and 3 m from the HighLine series)	MRA-F080-B	6045341
1	Wire draw deflection pulley for wire draw mechanism MRA-F080 (2 m and 3 m from HighLine series)	MRA-F080-R	6028632
	Additional brush attachment for wire draw mechanism MRA-F130 (5 m, 10 m, 20 m and 30 m from HighLine series)	MRA-F130-B	6038562
	Wire draw deflection pulley for wire draw mechanism MRA-F130 (5 m, 10 m, 20 m and 30 m from HighLine series)	MRA-F130-R	6028631

#### Wire draw mechanism

Wire draw mechanism for face mount flange encoder

Figure	Brief description	Mea- suring length	Туре	Part no.
		2.0 m	MRA-F080-402D2	6029788
	HighLine wire draw mechanism for 60 series face mount flange with 10 mm shaft	5.0 m	MRA-F130-405D2	6029789
<u> </u>		10.0 m	MRA-F130-410D2	6029790
		20.0 m	MRA-F130-420D1	6029791
		30.0 m	MRA-F130-430D1	6029792
		50.0 m	MRA-F190-450D2	6029793

#### Wire draw mechanism for servo flange encoder

Figure	Brief description	Mea- suring length	Туре	Part no.
		2.0 m	MRA-F080-102D2	6028625
	HighLine wire draw mechanism for 60 series servo flange With 6 mm shaft	3.0 m	MRA-F080-103D2	6030125
Q		5.0 m	MRA-F130-105D2	6028626
		10.0 m	MRA-F130-110D2	6028627
		20.0 m	MRA-F130-120D1	6028628
		30.0 m	MRA-F130-130D1	6028629
		50.0 m	MRA-F190-150D2	6028630

# Connectivity

#### Adapters and distributors

# T-piece

Figure	Brief description	Туре	Part no.
So	CANopen, T-piece	DSC- 1205T000025KM0	6030664

# Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
\	Head A: female connector, M12, 5-pin, angled Head B: cable	5 m	DOL-1202-W05MC	6042067
	Cable: for power supply, PUR, halogen-free, shielded, 3 x 0.34 mm <sup>2</sup> , Ø 4.2 mm	10 m	DOL-1202-W10MC	6042068
	Head A: female connector, M12, 4-pin, straight Head B: cable	2 m	DOL-1204-G02MC	6025900
		5 m	DOL-1204-G05MC	6025901
1	Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshield-	10 m	DOL-1204-G10MC	6025902
	ed, 4 x 0.34 mm², Ø 4.7 mm	25 m	DOL-1204-G25MC	6034751
	Head A: female connector, M12, 4-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PVC, unshielded, 4 x 0.25 mm², Ø 5.0 mm	5 m	DOL-1204-G05M	6009866
	Head A: female connector, M12, 4-pin, angled	2 m	DOL-1204-W02MC	6025903
	Head R: refine connector, M12, 4-pin, angled Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshield- ed, 4 x 0.34 mm², Ø 4.7 mm	5 m	DOL-1204-W05MC	6025904
18		10 m	DOL-1204-W10MC	6025905
		25 m	DOL-1204-W25MC	6034754
11	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, $5 \times 0.34 \text{ mm}^2$ , $\emptyset$ 5.9 mm	5 m	DOL-1205-G05MAC	6036384
		10 m	DOL-1205-G10MAC	6036385
11/1/		20 m	DOL-1205-G20MAC	6036386
		1.5 m	DOL-1205-G1M5ACS- CO	6049451
	Head A: female connector, M12, 5-pin, straight, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm <sup>2</sup> , Ø 5.9 mm	3 m	DOL-1205-G03MACS- CO	6049452
		5 m	DOL-1205-G05MACS- CO	6049453
		10 m	DOL-1205-G10MACS- CO	6049454
		1.5 m	DOL-1205- W1M5ACSCO	6049455
	Head A: female connector, M12, 5-pin, angled, A-coded Head B: cable	3 m	DOL-1205- W03MACSCO	6049456
A. S.	Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm	5 m	DOL-1205- W05MACSCO	6049457
		10 m	DOL-1205- W10MACSCO	6049458

 $<sup>^{\</sup>mbox{\tiny 1)}}$  Warning! Only in combination with electrical interfaces U, V, W and M.

Figure	Brief description	Length of cable	Туре	Part no.
		1.5 m	DOL-2312-G1M5MA1	2029200
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMA1	2029201
-	Head B: cable	5 m	DOL-2312-G05MMA1	2029202
	Cable: SSI, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 2 x 0.14 mm <sup>2</sup> , Ø 7.8 mm	10 m	DOL-2312-G10MMA1	2029203
	+ 2 x 0.3 IIIIII + + 2 x 0.14 IIIIII +, 0 7.8 IIIIII	20 m	DOL-2312-G20MMA1	2029204
		30 m	DOL-2312-G30MMA1	2029205
		5 m	DOL-1205-G05MQ	6026006
		10 m	DOL-1205-G10MQ	6026008
	Head A: female connector, M12, 5-pin, straight	12 m	DOL-1205-G12MQ	6032636
	Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded,	15 m	DOL-1205-G15MQ	6032637
<b>*</b>	2 x 0.34 mm², Ø 8.0 mm	20 m	DOL-1205-G20MQ	6032638
		30 m	DOL-1205-G30MQ	6032639
		50 m	DOL-1205-G50MQ	6032861
11	Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable  Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm	5 m	DOL-1205-W05MQ	6041423
		10 m	DOL-1205-W10MQ	6041425
	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: CANopen, suitable for drag chain, shielded, 2 x 0.34 mm $^2$ + 2 x 0.25 mm $^2$ + 1 x 0.34 mm $^2$ , Ø 6.7 mm A-coded	2 m	DOL-1205-G02MY	6053041
		5 m	DOL-1205-G05MY	6053042
		10 m	DOL-1205-G10MY	6053043
		2 m	DOL-2312-G02MLD1	2062202
		7 m	DOL-2312-G07MLD1	2062203
	Head A: female connector, M23, 12-pin, straight Head B: cable	10 m	DOL-2312-G10MLD1	2062204
	Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup>	15 m	DOL-2312-G15MLD1	2062205
	+ 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	20 m	DOL-2312-G20MLD1	2062206
		25 m	DOL-2312-G25MLD1	2062207
		30 m	DOL-2312-G30MLD1	2062208
		1.5 m	DOL-2312-G1M5MD1	2062240
	Head A: female connector, M23, 12-pin, straight	3 m	DOL-2312-G03MMD1	2062243
1	Head B: cable	5 m	DOL-2312-G05MMD1	2062244
	Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 1 x 0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	10 m	DOL-2312-G10MMD1	2062245
	,	20 m	DOL-2312-G20MMD1	2062246
		30 m	DOL-2312-G30MMD1	2062247

 $<sup>^{1)}\,\</sup>mbox{Warning!}$  Only in combination with electrical interfaces U, V, W and M.

# Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, B-coded	5 m	STL-1205-G05MQ	6026005
	Head B: cable Cable: PROFIBUS, suitable for drag chain, PUR, halogen-free, shielded,	10 m	STL-1205-G10MQ	6026007
	2 x 0.34 mm², Ø 8.0 mm Wire shielding: AL-PT foil, total shield, tin-plated C shield	12 m	STL-1205-G12MQ	6032635
\ \	Head A: male connector, M12, 5-pin, angled, B-coded Head B: cable	5 m	STL-1205-W05MQ	6041426
	Cable: PROFIBUS, suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm	10 m	STL-1205-W10MQ	6041427
	Head A: male connector, M12, 4-pin, straight, D-coded Head B: cable Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m	STL-1204-G02ME90	6045284
The second		5 m	STL-1204-G05ME90	6045285
		10 m	STL-1204-G10ME90	6045286
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: cable Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m	STL-1204-W02ME90	6047912
		5 m	STL-1204-W05ME90	6047913
N. mar		10 m	STL-1204-W10ME90	6047914
		25 m	STL-1204-W20ME90	6047915
	Head A: male connector, M12, 4-pin, straight, D-coded Head B: cable	2 m	STL-1204-G02MZ90	6048247
-		5 m	STL-1204-G05MZ90	6048248
	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	STL-1204-G10MZ90	6048249
		2 m	STL-1204-W02MZ90	6048256
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: cable	5 m	STL-1204-W05MZ90	6048257
	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	STL-1204-W10MZ90	6048258
		25 m	STL-1204-W25MZ90	6048259

# Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -	DOS-1204-G	6007302
	Head A: female connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	DOS-1205-G	6009719
	Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm $\dots$ 6.5 mm Head B: -	DOS-1204-W	6007303
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -20 °C +130 °C	DOS-2312-G	6027538
	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057
	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm  Head B: -  Operating temperature: -20 °C +130 °C	DOS-2312-W01	2072580
	Head A: female connector, M12, 5-pin, straight, B-coded, shielded, PROFIBUS, for cable diameter 4 mm 9 mm Head B: -	DOS-1205-GQ	6021353
	Head A: female connector, M12, 5-pin, angled, B-coded, shielded, PROFIBUS, for cable diameter 4 mm $\dots$ 8 mm Head B: -	DOS-1205-WQ	6041429

Figure	Brief description	Туре	Part no.
	Head A: female connector, M12, 5-pin, straight, shielded, CANopen, DeviceNet, for cable diameter 4.5 mm $\dots$ 7 mm Head B: -	DOS-1205-GA	6027534
	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm 8 mm Head B: -	DOS-1204-GE	6048153
	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm $\dots$ 8 mm Head B: -	DOS-1204-WE	6048154
	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm 8 mm	DOS-1204-GZ	6048263
	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm $\dots$ 8 mm	DOS-1204-WZ	6048264

# Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm		LTG-2102-MW	6021355
	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.15 \text{ mm}^2$ , $\emptyset$ 5.6 mm		LTG-2308-MWENC	6027529
<u></u>	Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm	By the meter	LTG-2411-MW	6027530
_	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		LTG-2512-MW	6027531
<b></b>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25$ mm <sup>2</sup> + $2 \times 0.5$ mm <sup>2</sup> + $2 \times 0.14$ mm <sup>2</sup> , Ø 7.8 mm		LTG-2612-MW	6028516

# Other plug connectors and cables

Figure	Brief description	Туре	Part no.
	A3M60 accessories sales set comprising: Female cable connector supply voltage M12 angled (6007303) Female cable connector M12 angled (6041429) Male cable connector M12 angled (6041428)	DOS-3XM12-W	2058177
00	Head A: female connector, M12, 4-pin, D-coded Head B: female connector, RJ45, 8-pin Cable: shielded Switch cabinet feedthrough	Feedthrough female connector Ethernet RJ45	6048180
The second	Head A: male connector, M12, 4-pin, straight, B-coded Cable: PROFIBUS terminator	STE-END-Q	6021156

#### Male connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: male connector, M12, 5-pin, straight, unshielded, for cable diametes 4 mm 6 mm Head B: -	STE-1205-G	6022083
	Head A: male connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -	STE-1205-GQ	6021354
The	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537
	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	STE-2312-G01	2077273
	Head A: male connector, M12, 5-pin, angled, B-coded, shielded, PROFIBUS, for cable diameter 4 mm 8 mm Head B: -	STE-1205-WQ	6041428
0	Head A: male connector, M12, 5-pin, straight, A encoded, shielded, CANopen, DeviceNet, for cable diameter 4 mm $\dots$ 8 mm Head B: -	STE-1205-GA	6027533
	Head A: male connector, RJ45, 8-pin, straight, shielded, EtherNet/IP, for cable diameter 4.5 mm 8 mm Head B: -	STE-0J08-GE	6048150
Co	Head A: male connector, M12, 4-pin, straight, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm 8 mm Head B: -	STE-1204-GE01	6048151
	Head A: male connector, M12, 4-pin, angled, D-coded, shielded, EtherNet/IP, for cable diameter 4 mm 8 mm Head B: -	STE-1204-WE	6048152
	Head A: male connector, RJ45, 4-pin, straight, shielded, PROFINET, EtherCAT, for cable diameter 4.5 mm 8 mm	STE-0J04-GZ	6048260
0	Head A: male connector, M12, 4-pin, straight, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm 8 mm	STE-1204-GZ	6048261
	Head A: male connector, M12, 4-pin, angled, D-coded, shielded, PROFINET, EtherCAT, for cable diameter 4 mm 8 mm	STE-1204-WZ	6048262

#### Connection cables with female and male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, 4 x 2 x 0.08 mm <sup>2</sup>	0.5 m	DSL-3D08-G0M5AC3	2046580
_	Head A: female connector, M12, 5-pin, straight	2 m	DSL-1205-G02MY	6053044
	Head B: male connector, M12, 5-pin, straight  Cable: CANopen, suitable for drag chain, PUR, halogen-free, shielded,  2 x 0.34 mm <sup>2</sup> + 2 x 0.25 mm <sup>2</sup> + 1 x 0.34 mm <sup>2</sup> , Ø 6.7 mm, A-coded	5 m	DSL-1205-G05MY	6053045
		10 m	DSL-1205-G10MY	6053046

#### Connection cables with male and male connector

Figure	Brief description		Туре	Part no.
	Head A: male connector, M12, 4-pin, straight, D-coded Head B: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-1204-G02ME90	6045222
6		5 m	SSL-1204-G05ME90	6045277
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm	10 m	SSL-1204-G10ME90	6045279
	Head A: male connector, M12, 4-pin, angled, D-coded	2 m	SSL-1204-H02ME90	6047908
6	Head B: male connector, M12, 4-pin, straight, D-coded	5 m	SSL-1204-H05ME90	6047909
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm	10 m	SSL-1204-H10ME90	6047910
	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-2J04-G02ME60	6047916
9	Head B: male connector, RJ45, 8-pin, straight	5 m	SSL-2J04-G05ME60	6047917
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm	10 m	SSL-2J04-G10ME60	6047918
	Head A: male connector, M12, 4-pin, angled, D-coded Head B: male connector, RJ45, 8-pin, straight	2 m	SSL-2J04-H02ME	6047911
0		5 m	SSL-2J04-H05ME	6045287
	Cable: EtherNet/IP, PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm		SSL-2J04-H10ME	6045288
_	Head A: male connector, M12, 4-pin, angled, D-coded Head B: male connector, M12, 4-pin, straight	2 m	SSL-1204-F02MZ90	6048250
@		5 m	SSL-1204-F05MZ90	6048251
No.	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-1204-F10MZ90	6048252
_	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-1204-G02MZ90	6048241
6	Head B: male connector, M12, 4-pin, straight	5 m	SSL-1204-G05MZ90	6048242
-	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-1204-G10MZ90	6048243
	Head A: male connector, RJ45, 4-pin, straight, D-coded	2 m	SSL-2J04-F02MZ	6048253
	Head B: male connector, M12, 4-pin, angled	5 m	SSL-2J04-F05MZ	6048254
	Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	SSL-2J04-F10MZ	6048255
_	Head A: male connector, M12, 4-pin, straight, D-coded	2 m	SSL-2J04-G02MZ60	6048244
	Head B: male connector, RJ45, 4-pin, straight Cable: PROFINET, EtherCAT, PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	5 m	SSL-2J04-G05MZ60	6048245
		10 m	SSL-2J04-G10MZ60	6048246

# Other accessories

#### Spare parts

Figure	Brief description	Туре	Part no.
	Spare mounting set for HighLine wire draw mechanisms for fitting encoders with servo flange	MRA-F-K	6028633

#### Programming and configuration tools

Figure	Brief description	Туре	Part no.
3	Programming unit <sup>1)</sup> USB, for programmable SICK encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoders.	PGT-08-S	1036616
V n. m A	Programming unit display for programmable SICK DFS60, VFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254

<sup>&</sup>lt;sup>1)</sup> Can be used with programmable incremental and absolute encoders in conjunction with the corresponding adapter cables.

<sup>→</sup> For additional accessories, please see page K-668 onwards



# LINEAR ENCODERS

#### Complete non-contact measurement – with SICK linear encoders

Linear encoders consist of a read head (sensor) and a reference scale (measuring element). The non-contact principle of operation means that the position is determined without wear. The sensor uses a unique code pattern to record the absolute position information along the reference scale, and sends this information directly to the evaluation electronics. As a result, there is no need for a reference run. Compact systems with high

resolutions or rugged solutions with very long measured lengths (up to 1,700 m) cover a wide range of application areas.

#### Your benefits


- Excellent reliability less product wear and maintenance
- Maximum precision resolution of up to 1 µm
- · Large selection of measuring lengths from < 0.5 m to 1,700 m is ideal for a broad range of application requirements
- TTK70: Small size, low weight and high traversing speed deliver excellent process dynamics
- KH53: Reliable position determination under harsh conditions (dirt, dust, fog, shock, vibration) reduces downtime due to environmental factors



Applications	
KH53	
TTK70	

# TYPICAL LINEAR ENCODER APPLICATIONS

Cranes - positioning of the trolley and track



The field of application for cranes encompasses nearly all areas of logistics from indoor to outdoor. This means that fine dust in cement factories or seawater from ship-to-shore cranes can quickly become a problem. Resistance to dirt, shock, vibration, and salt water is therefore a basic requirement for crane positioning systems.

The KH53 linear encoder was designed specifically for such ambient conditions. It is used to position the trolley on the crane and to position the path of the crane itself. Due to its excellent repeatability, the largest possible reading distances and a measuring length of up to 1.7 km, the KH53 linear encoder has been successfully used in this area for years.

# Print finishing - positioning cutting tools



High precision is required in the printing industry. After the printing process, the printed documents must be trimmed to the desired size. For this, the cutting blades have to be moved into their respective positions and then lowered. The linear encoder can reliably carry out this precise task.

With its high resolution and reproducibility, the non-contact TTK70 linear encoder is particularly well suited to this application. It has both an incremental and an absolute track and can thus calculate the absolute position and speed. The position is output over an SSI interface, while the speed information is made available with sin/cos signals.

J

# PRODUCT FAMILY OVERVIEW



Technical data overview		
Measuring length	0 m 1,700 m	≤ 4,000 mm
Resolution	0.1 mm	1 μm
Repeatability	0.3 mm, 1 mm	≤ ± 2 μm
Electrical interface	SSI, PROFIBUS DP	SSI
Connection type	Male connector/cable	Male connector
Enclosure rating	IP 65 (IEC 60529) IP 66 (IEC 60529) IP 67 (IEC 60529)	IP 67 (IEC 60529)

Α	t	a	g١	а	n	ce

- Non-contact length measurement maintenance-free, rugged, long service life
- High reproducibility (0.3 mm / 1 mm), high system resolution (0.1 mm)
- · SSI and PROFIBUS interfaces
- Determination of absolute position
- Measuring lengths of up to 1,700 m possible
- Can be used in the harshest ambient conditions
- High traversing speeds of up to 6.6 m/s
- Distance tolerance between read head and measuring element: up to 55 mm ± 20 mm possible

- · Non-contact absolute positioning
- Small, compact read head
- Standard SSI interface, combined with sin/ cos output
- Measuring lengths of up to 4 m possible
- High level of accuracy (± 10 µm)
- High resolution (1 μm)
- High traversing speed of up to 10 m/s

Detailed information

→ J-644

**→** J-660

# FOR THE HARSHEST CONDITIONS - THE HEAVY-DUTY LINEAR ENCODER



#### **Product description**

The POMUX KH53 non-contact linear encoder can measure absolute lengths up to 1,700 m. The encoder consists of two main components: The non-contact read head determines the absolute position using a series of measuring elements attached along the measurement path. Each measuring element consists of a number of permanent magnets. Since the distances between the magnets are unique, they can be used to develop an absolute measuring code. No reference

run is required due to the absolute position being determined. The read head is passed parallel to these measuring elements at a distance of 25 mm or 55 mm. With a measuring length of up to 1,700 m, the KH53 is ideal for use in cranes, in storage and conveyor systems, and for railed vehicles. Due to the non-contact technology, this system works wear-free even in harsh ambient conditions, so that a long lifetime is ensured.

#### At a glance

- Non-contact length measurement
   maintenance-free, rugged, long service life
- High reproducibility (0.3 mm / 1 mm), high system resolution (0.1 mm)
- · SSI and PROFIBUS interfaces
- · Determination of absolute position
- Measuring lengths of up to 1,700 m possible
- Can be used in the harshest ambient conditions
- High traversing speedds of up to 6.6 m/s
- Distance tolerance between read head and measuring element: up to 55 mm ± 20 mm possible

#### Your benefits

- After installation, the system is immediately available and completely maintenance-free, which leads to time and cost savings
- Reliable determination of position under harshest ambient conditions such as the effects of dirt, dust, fog, shock, and vibration
- High efficiency and productivity levels
- Time savings no reference run necessary on initial commissioning due to absolute position measurement
- Accurate positioning even with high mounting tolerances



#### Additional information

Detailed technical data J-645
Ordering information
Dimensional drawings J-651
Pin assignment J-652
Implementation
Switch settings
General information J-655
Position tolerance J-655
Recommended accessories J-656



For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



#### Fields of application

- Position determination for container cranes in container terminals
- · Positioning of the trolley on cranes

Positioning of automated guided vehicles in storage and conveyor systems

#### Detailed technical data

#### Performance

	КН53	KH53 Advanced	
Measuring length	0 m 1,700 m	0 m 548 m	
Measuring range	38 m, 107 m, 354 m, 1,700 m	54 m, 548 m	
Interfaces	SSI and PROFIBUS		
Resolution	0.1 mm		
Reproducibility	0.3 mm	1 mm	
Max. traversing speed 1)	6.6 m/s		
Measurement accuracy 2)	$\pm$ 1000 + ME (Tu $-25$ °C) Tk $\mu m$	$\pm$ 2000 + ME (Tu $-25$ °C) Tk $\mu m$	

<sup>&</sup>lt;sup>1)</sup> An error message appears if the max. traversing speed is exceeded or the read head cannot detect a measuring element (with SSI FF FF E hex).

#### Electrical data

Initialization time	2 s
Position forming time	
SSI	0.8 ms
PROFIBUS	1.1 ms
Supply voltage	10 32 V
Electrical connection	
SSI	Cable
	M23 male connector
PROFIBUS	3 x M12 male connectors
SSI	
RS422 interface for parameterizing	Four wire transmission, asynchronous, full-duplex Data format: 1 start bit, 8 data bits, 1 stop bit, no parity Data protocol: ASCII, Baud rate 9,600
Interface digital, serial	SSI 24 bit, gray
Default setting SSI standard	RS 422 OFF
SSI power consumption	250 mA
PROFIBUS DP	
Electrical interface	RS485 (as per EN 50 170-2 (DIN 19245 Parts 1-3) electrically isolated by optocoupler
Address setting (node number)	0 127 (hex switch or protocol)
Protocol	PROFIBUS DP basic functions (DP-V0)
Bus termination	Via external male connectors
SET (electronic adjustment)	Via protocol
Encoder profile	Profiles for encoders (07hex) - Class 2
Data transmission rate (baud rate)	9.6 kBaud12 Mbaud (autodetect)
Status information	Operation (LED green), bus activity (LED red)
PROFIBUS power consumption in operation	2.5 W
1) A	dust and does not constitute a sofety common out as defined in the Machinesy Divertine Coloulation based on

<sup>1)</sup> According to ISO13849. This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature of 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

<sup>&</sup>lt;sup>2)</sup> Related to the start of a measuring element if a position tolerance of ± 1 mm is maintained based on the nominal distance in the N and Y directions. ME = Length of the measuring element (see illustration on page J-652), Tu = ambient temperature in °C, Tk = coefficient of thermal expansion (see "Mechanical Data" table on page J-646).

MTTFd: mean time to dangerous failure		
SSI	Measuring range up to 38 m: 45 years <sup>1)</sup> Measuring range up to 107 m: 40 years <sup>1)</sup> Measuring range up to 354 m: 31 years <sup>1)</sup> Measuring range up to 1,700 m: 21 years <sup>1)</sup>	Measuring range up to 54 m: 34 years <sup>1)</sup> Measuring range up to 548 m: 22 years <sup>1)</sup>
PROFIBUS	Measuring range up to 38 m: 40 years <sup>1)</sup> Measuring range up to 107 m: 35 years <sup>1)</sup> Measuring range up to 354 m: 28 years <sup>1)</sup> Measuring range up to 1,700 m: 20 years <sup>1)</sup>	Measuring range up to 54 m: 30 years <sup>1)</sup> Measuring range up to 548 m: 20 years <sup>1)</sup>

<sup>&</sup>lt;sup>1)</sup> According to ISO13849. This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature of 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

#### Mechanical data


	КН53	KH53 Advanced
Mass		
Read head 38	2.4 kg	-
Read head 107	2.7 kg	-
Read head 354	3.6 kg	-
Read head 1,700	5.2 kg	-
Read head 54	-	4.4 kg
Read head 548	-	6.7 kg
Measuring element	0.5 kg/m	0.65 kg/m
Length of measuring element	See tables on Page J-647 and Page J-649	
Coefficient of thermal expansion	28 μm/°C/m	
Position tolerance (see diagram on Page J-655)	± 10 mm	± 20 mm
Read head material	AIMgSiPbF28	
Measuring element material	AIMgSiO,5F22	

# Ambient data

EMC 1)	According to EN 61000-6-2 and EN 61000-6-4	
Enclosure rating		
SSI read head with cable	IP 66	
SSI read head with screw-in system	IP 65 (with mating connector fitted)	
Read head with PROFIBUS connectors	IP 67 (with mating connector fitted)	
Operating temperature range	-20 +60 °C	-30 +70 °C
Read head storage temperature range	-40 +85 °C	
Resistance to shocks	According to EN 61000-2-27	
Read head	30 g/10 ms	
Measuring element	50 g / 10 ms	
Resistance to vibrations	According to DIN EN 61000-2-6	
Read head	10 g/20 250 Hz	
Measuring element	30 g / 20 250 Hz	

 $<sup>^{\</sup>scriptsize 1)}$  The EMC according to the standards quoted is achieved if shielded connecting cables are used.

#### SSI ordering information



#### Dimensions and calculation table - KH53

Measuring range up to	Read head length	Length of measuring element including distance	Mounting systems per measuring element (suggestion)
39.90 m	0.886 m	2.304 m Identification letters A1 ≤ A18	4 clamp holders or 8 mounting brackets
107.40 m	1.051 m	1.8688 m Identification letters B1 ≤ B58	3 clamp holders or 6 mounting brackets
351.20 m	1.376 m	2.5088 m Identification letters C1 ≤ C141	4 clamp holders or 8 mounting brackets
1676.40 m	2.026 m	1.9072 m Identification letters D1 ≤ D880	3 clamp holders or 6 mounting brackets

The dimensions given are slightly rounded.

#### Measurement and calculation table - KH53 Advanced

Measuring range up to	Read head length	Length of measuring element including distance	Mounting systems per measuring element (suggestion)
53.50 m	1.58 m	1.408 m Identification letters F1 ≤ F39	3 clamp holders or 6 mounting brackets
546.40 m	2.506 m	2.3552 m Identification letters G1 ≤ G233	4 clamp holders or 8 mounting brackets

The dimensions given are slightly rounded.

#### Calculation example for a measurement distance of 100 m

Selected system with measuring range up to 107 m

Number of measuring elements required = measurement path + length of the read head / length of measurement element (according to table above)

Number of measuring elements required =  $101.051 \, \text{m} / 1.8688 \, \text{m} = 54.07$ 

Ordering amount therefore 55 measuring elements and 55  $\star$  3 = 165 clamp holders

If two separate measurement paths are to be implemented, then please order 2 x 55 measuring elements (not 110 measuring elements)

Attention! For position determination, the read head must not travel beyond the last measuring element.

#### KH53 length measurement systems (absolute, linear)

Measuring range up to 38 meters

Description	Туре	Part no.
Read head 38, SSI, cable 1.5 m	KHK53-AXR00038	1030048
Read head 38, SSI, cable 3.0 m	KHK53-AXS00038	1030049
Read head 38, SSI, cable 5.0 m	KHK53-AXT00038	1030050
Read head 38, SSI, cable 10.0 m	KHK53-AXU00038	1030051
Read head 38, SSI, M23 male, 12 pin	KHK53-AXB00038	1030052
Measuring element up to 38 m, coded <sup>1)</sup>	KHT53-XXX00038	1030055
Measuring element up to 38 m, universally codeable 2)	KHU53-XXX00038	1030056
Assembly gauge 38	KHM53-XXX00038	1030057

<sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

 $<sup>^{\</sup>rm 2)}$  For the temporary replacement of defective, coded measuring elements.

#### Measuring range up to 107 meters

Description	Туре	Part no.
Read head 107, SSI, cable 1.5 m	KHK53-AXR00107	1030058
Read head 107, SSI, cable 3.0 m	KHK53-AXS00107	1030059
Read head 107, SSI, cable 5.0 m	KHK53-AXT00107	1030060
Read head 107, SSI, cable 10.0 m	KHK53-AXU00107	1030061
Read head 107, SSI, M23 male device connector, 12 pin	KHK53-AXB00107	1030062
Measuring element up to 107 m, coded 1)	KHT53-XXX00107	1030065
Measuring element up to 107 m, universally codeable 2)	KHU53-XXX00107	1030066
Assembly gauge 107	KHM53-XXX00107	1030067

<sup>&</sup>lt;sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

### Measuring range up to 354 meters

Description	Туре	Part no.
Read head 354, SSI, cable 1.5 m	KHK53-AXR00107	1030068
Read head 354, SSI, cable 3.0 m	KHK53-AXS00354	1030069
Read head 354, SSI, cable 5.0 m	KHK53-AXT00354	1030070
Read head 354, SSI, cable 10.0 m	KHK53-AXU00354	1030071
Read head 354, SSI, M23 male device connector, 12 pin	KHK53-AXB00354	1030072
Measuring element up to 354 m, coded 1)	KHT53-XXX00354	1030075
Measuring element up to 354 m, universally codeable <sup>2)</sup>	KHU53-XXX00354	1030076
Assembly gauge 354	KHM53-XXX00354	1030077

<sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

#### Measuring range up to 1,700 meters

Description	Туре	Part no.
Read head 1700, SSI, cable 1.5 m	KHK53-AXR01700	1030078
Read head 1700, SSI, cable 3.0 m	KHK53-AXS01700	1030079
Read head 1700, SSI, cable 5.0 m	KHK53-AXT01700	1030080
Read head 1700, SSI, cable 10.0 m	KHK53-AXU01700	1030081
Read head 1700, SSI, M23 male device connector, 12 pin	KHK53-AXB01700	1030082
Measuring element up to 1,700 m, coded 1)	KHT53-XXX01700	1030085
Measuring element up to 1,700 m, universally codeable 2)	KHU53-XXX01700	1030086
Assembly gauge 1700	KHM53-XXX01700	1030087

<sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

## KH53 advanced length measurement systems (absolute, linear)

#### Measuring range up to 54 meters

Description	Туре	Part no.
Read head 54, SSI, cable 5.0 m	KHK53-AXT00054	1035442
Read head 54, SSI, M23 male device connector, 12 pin	KHK53-AXB00054	1035443
Measuring element up to 54 m, coded <sup>1)</sup>	KHT53-XXX00054	1035445
Measuring element up to 54 m, universally codeable 2)	KHU53-XXX00054	1035446
Assembly gauge 54	KHM53-XXX00054	1035447


<sup>&</sup>lt;sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

#### Measuring range up to 548 meters

Description	Туре	Part no.
Read head 548, SSI, cable 5.0 m	KHK53-AXT00548	1035448
Read head 548, SSI, M23 male device connector, 12 pin	KHK53-AXB00548	1035449
Measuring element up to 548 m, coded <sup>1)</sup>	KHT53-XXX00548	1035451
Measuring element up to 548 m, universally codeable 2)	KHU53-XXX00548	1035452
Assembly gauge 548	KHM53-XXX00548	1035453

<sup>&</sup>lt;sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

## PROFIBUS ordering information



#### Dimensions and calculation table - KH53

Measuring range up to	Read head length	Length of measuring element including distance	Mounting systems per measuring element (suggestion)
39.90 m	0.905 m	2.304 m Identification letters A1 ≤ A18	4 clamp holders or 8 mounting brackets
107.40 m	1.070 m	1.8688 m Identification letters B1 ≤ B58	3 clamp holders or 6 mounting brackets
351.20 m	1.395 m	2.5088 m Identification letters C1 ≤ C141	4 clamp holders or 8 mounting brackets
1676.40 m	2.045 m	1.9072 m Identification letters D1 ≤ D880	3 clamp holders or 6 mounting brackets

The dimensions given are slightly rounded.

#### Measurement and calculation table - KH53 Advanced

Measuring range up to	Read head length	Length of measuring element including distance	Mounting systems per measuring element (suggestion)
53.50 m	1.599 m	1.408 m Identification letters F1 $\leq$ F39	3 clamp holders or 6 mounting brackets
546.40 m	2.525 m	2.3552 m	4 clamp holders or 8 mounting brackets

The dimensions given are slightly rounded.

 $<sup>^{\</sup>rm 2)}$  For the temporary replacement of defective, coded measuring elements.

 $<sup>^{\</sup>rm 2)}$  For the temporary replacement of defective, coded measuring elements.

#### Calculation example for a measurement distance of 100 m

Selected system with measuring range up to 107 m

Number of measuring elements required = measurement path + length of the read head / length of measurement element (according to table above)

Number of measuring elements required = 101.070 m / 1.8688 m = 54.08

Ordering amount therefore 55 measuring elements and 55 \* 3 = 165 clamp holders

If two separate measurement paths are to be implemented, then please order 2 x 55 measuring elements (not 110 measuring elements)

Attention! For position determination, the read head must not travel beyond the last measuring element.

#### KH53 length measurement systems (absolute, linear)

#### Measuring range up to 38 meters

Description	Туре	Part no.
Read head 38, PROFIBUS DP	KHK53-PXF00038	1036163
Measuring element up to 38 m, coded 1)	KHT53-XXX00038	1030055
Measuring element up to 38 m, universally codeable 2)	KHU53-XXX00038	1030056
Assembly gauge 38	KHM53-XXX00038	1030057

<sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

#### Measuring range up to 107 meters

Description	Туре	Part no.
Read head 107, PROFIBUS DP	KHK53-PXF00107	1036164
Measuring element up to 107 m, coded <sup>1)</sup>	KHT53-XXX00107	1030065
Measuring element up to 107 m, universally codeable 2)	KHU53-XXX00107	1030066
Assembly gauge 107	KHM53-XXX00107	1030067

<sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

#### Measuring range up to 354 meters

Description	Туре	Part no.
Read head 354, PROFIBUS DP	KHK53-PXF00354	1036165
Measuring element up to 354 m, coded 1)	KHT53-XXX00354	1030075
Measuring element up to 354 m, universally codeable 2)	KHU53-XXX00354	1030076
Assembly gauge 354	KHM53-XXX00354	1030077

<sup>1)</sup> When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

#### Measuring range up to 1,700 meters

Description	Туре	Part no.
Read head 1700, PROFIBUS DP	KHK53-PXF01700	1036166
Measuring element up to 1,700 m, coded 1)	KHT53-XXX01700	1030085
Measuring element up to 1,700 m, universally codeable 2)	KHU53-XXX01700	1030086
Assembly gauge 1700	KHM53-XXX01700	1030087

 $<sup>^{1)}</sup>$  When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

## KH53 advanced length measurement systems (absolute, linear)

#### Measuring range up to 54 meters

Description	Туре	Part no.
Read head 54, PROFIBUS DP	KHK53-PXF00054	1036167
Measuring element up to 54 m, coded 1)	KHT53-XXX00054	1035445
Measuring element up to 54 m, universally codeable 2)	KHU53-XXX00054	1035446
Assembly gauge 54	KHM53-XXX00054	1035447


 $<sup>^{1)}</sup>$  When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .

#### Measuring range up to 548 meters

Description	Туре	Part no.
Read head 548, PROFIBUS DP	KHK53-PXF00548	1036168
Measuring element up to 548 m, coded 1)	KHT53-XXX00548	1035451
Measuring element up to 548 m, universally codeable 2)	KHU53-XXX00548	1035452
Assembly gauge 548	KHM53-XXX00548	1035453

 $<sup>^{1)}</sup>$  When ordering replacements for individual defective measuring elements, please enter the code for the measuring element in question .


## Dimensional drawing SSI read head (dimensions in mm)




 $<sup>^{\</sup>rm 2)}$  For the temporary replacement of defective, coded measuring elements.

<sup>&</sup>lt;sup>2)</sup> For the temporary replacement of defective, coded measuring elements.

## Dimensional drawing PROFIBUS read head (dimensions in mm)



## Dimensional drawing for measuring element



## Pin assignment for SSI interface

View of M23 male device connector on SSI encoder




PIN	Signal	Wire colors (cable outlet)	Explanation
1	GND	Blue	Ground connection
2	Data +	White	Interface signals
3	Clock +	Yellow	Interface signals
4	R x D +	Gray	RS-422 programming cables
5	R x D -	Green	RS-422 programming cables
6	T x D +	Pink	RS-422 programming cables
7	T x D -	Black	RS-422 programming cables
8	+ U <sub>s</sub>	Red	Operating voltage
9	N. C.	Orange	Not connected
10	Data -	Brown	Interface signals
11	Clock -	Violet	Interface signals
12	N. C.	-	Not connected

N. C. = Not Connected.

Other interfaces on request.

# Pin assignment for PROFIBUS interface



Male connector, 4 pin	Male connector, 5 pin	Female connector 5 pin	Signal	Explanation
1	-	-	U <sub>S</sub> (24 V)	Operating voltage 10 32 V
3	-	-	O V (GND)	Ground (O V)
-	-	4	В	B cable PROFIBUS DP (out)
-	-	2	Α	A cable PROFIBUS DP (out)
-	4	-	В	B cable PROFIBUS DP (in)
-	2	-	Α	A cable PROFIBUS DP (in)
-	-	1	2P5 <sup>1)</sup>	+ 5 V (potential free)
-	-	3	2M 1)	O V (potential free)
4	1	-	Not connected	-
2	3	-	Not connected	-
-	5	5	Screen	Housing potential

<sup>&</sup>lt;sup>1)</sup> Use for external bus termination.

#### **Implementation**

#### DP functionalities

according to PROFIBUS-DP basic functionalities.

#### DP services

- Data exchange (Write\_Read\_Data)
- Address allocation (Set\_Slave\_Address)
- Control commands (Global\_Control)
- Reading inputs (Read\_Inputs)
- · Reading outputs (Read\_Outputs)
- Reading diagnostic data (Slave\_Diagnosis)
- Sending parameter data (Set Param)
- · Checking configuration data (Chk\_Config)

#### Communication

· Cyclic master-slave data traffic.

#### Safety mechanisms


- Transfer of data with HD = 4.
- · Time monitoring of data traffic.

#### Configuration

Settings according to encoder profile

- Counting direction (CW, CCW)
- · Class 2 functionality (ON, OFF)
- Scaling function (ON, OFF)
- "Activation of SSA service" 2)
- Selection of the station address<sup>2)</sup>

<sup>2)</sup> Manufacturer specific function.



## Setting: - Counting direction

- Via hardware via hex switch S2
- Via software via telegram

Count direction increasing:

Movement of the encoder from profile item n in the direction of profile item n+1

## Configuration

Setting the formats (IN/OUT) for the cyclic data exchange through a configuration byte (K-1).

2 words IN/OUT data (I-1/0-1) 1)

4 words IN/OUT data (I-1, I-2, I-3/0-1) 2)

#### Data exchange: - Input data (IN)

I-1 Position value 1) 4 bytes

I-2 Speed (0.1 m/min) 2) 2 bytes

I-3 Time stamp 2) 2 bytes

## Data exchange: - Output data (out)

0-1 PRESET - Value 1) 4 bytes

#### Diagnostic information

 Station related diagnostic (63 bytes according to encoder profile Class 2)

#### Setting: - PRESET value

The PRESET function is used for commissioning and the allocation of a particular position value to current physical positioning.

The following settings are possible:

• Via software: - (see Output Data)

## Setting: - Station address

- Via hardware via hex switch S1/S2
- Via software via telegram

Setting by software only occurs with prior activation of the "SSA service".

Device specific file (\*.GS\_)

The \*.GS\_ file is designed for automatic commissioning of the encoder. Within it all the characteristic features of the device are defined.

STEG05F6.GSD German STEG05F6.GSE English

<sup>1)</sup> In accordance with encoder profile.

## Switch settings

The following settings are possible via hex switches:

S1/S2 Address setting (0 ... 127)

S2 Counting direction (CW/CCW)

Access is via a screw connection on the side of the read head male connector.

Status information via LEDs

LED-1 Bus activity (red)

LED-2 Operating voltage (green)

#### **General** information

The KH53 PROFIBUS is an absolute length measurement system with a resolution of 100  $\mu m.$  The bus coupling is inside the encoder and is an interface connection as PROFIBUS DP slave according to EN 50170 Vol. 2. Implementation is with the Siemens PROFIBUS ASIC SPC3.

The KH53 PROFIBUS contains all Class 2 functionalities according to the encoder profile (V1.1)

Implementation of the encoder is as a DP slave with the DP basic functions.


Conformity with PROFIBUS DP is ensured by a PNO certified test center.

The following options are available:

• M12 plug connector system


#### Position tolerances

Start of measurement path




End of measurement path

Connector or cable outlet always at this position



The operating reliability and accuracy of the measuring system depends on (amongst other things) compliance with the position tolerances. Magnetic or magnetizable materials are not permitted within 80 mm of the encoder or the measuring element.


#### **KH53**




All dimensions in mm (inch)

- ① Read head
- 2 Measuring element


#### KH53 Advanced





All dimensions in mm (inch)

- ① Read head
- 2 Measuring element



Only use non ferro-magnetic materials for the assembly base of the read head. A separation distance of 80 mm must be observed for ferro-magnetic materials (e.g., iron).

#### Recommended accessories

#### Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Brief description	Туре	Part no.
	Mounting bracket for KH53 measuring elements, without mounting hardware for the base	BEF-WK-KHT53	2029159

#### Clamp and alignment brackets

Terminal brackets

Figure	Brief description	Туре	Part no.
	Spacer for KH53 measuring elements, without mounting hardware for the base	BEF-KHA-KHT53	2042468

## Connectors

## Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: M12 female connector, 4-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PVC, unshielded, 4 x 0.25 mm², Ø 5.0 mm	5 m	DOL-1204-G05M	6009866
	Head A: M12 female connector, 5-pin, straight Head B: cable	5 m	DOL-1205-G05MQ	6026006
100	Cable: suitable for drag chain, PROFIBUS DP, PUR, halogen-free, shielded, $2 \times 0.34 \text{ mm}^2$ , Ø $8.0 \text{ mm}$	10 m	DOL-1205-G10MQ	G-G10MQ 6026008
		1.5 m	DOL-2312-G1M5MA1	2029200
	Hood At M22 formula compactor 12 nin attaight	3 m	DOL-2312-G03MMA1	2029201
	Head A: M23 female connector, 12-pin, straight Head B: cable	5 m	DOL-2312-G05MMA1	2029202
	Cable: SSI, RS-422, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup>	10 m	DOL-2312-G10MMA1	2029203
	+ 2 x 0.5 mm <sup>2</sup> + 2 x 0.14 mm <sup>2</sup> , Ø 7.8 mm	20 m	DOL-2312-G20MMA1	2029204
		30 m	DOL-2312-G30MMA1	2029205

## Connecting cables with male connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: M12 male connector, 5-pin, straight, B-coded	5 m	STL-1205-G05MQ	6026005
6	Head B: cable  Cable: PROFIBUS DP, suitable for drag chain, PUR, halogen-free, shielded,	10 m	STL-1205-G10MQ	6026007
	$2 \times 0.34 \text{ mm}^2$ , Ø $8.0 \text{ mm}$ Wire shielding: AL-PT foil, total shield, tin-plated C shield	12 m	STL-1205-G12MQ	

## Female connectors (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: M12 female connector, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm $\dots$ 6 mm Head B: -	DOS-1204-G	6007302
	Head A: M12 female connector, 5-pin, straight, B-coded, PROFIBUS DP, shielded, for cable diameter 4 mm 9 mm Head B: -	DOS-1205-GQ	6021353
	Head A: M23 female connector, 12-pin, straight, HIPERFACE®, SSI, incremental, shielded, for cable diameter 5.5 mm 10.5 mm Head B: Operating temperature: $-20$ °C $+130$ °C	DOS-2312-G	6027538

## Cables (ready to assemble)

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: cable Head B: cable Cable: PROFIBUS DP, suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm		LTG-2102-MW	6021355
_	Head A: cable Head B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm	By the meter	LTG-2512-MW	6027531
<u></u>	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516

## Other plug connectors and cables

Figure	Brief description	Туре	Part no.
	Head A: M12 male connector, 4-pin, straight, B-coded Cable: PROFIBUS DP, terminator	STE-END-Q	6021156

## Male connector (ready to assemble)

Figure	Brief description	Туре	Part no.
	Head A: M12 male connector, 5-pin, straight, B-coded, PROFIBUS DP, shielded, for cable diameter 4 mm 9 mm Head B: -	STE-1205-GQ	6021354
	Head A: M23 male connector, 12-pin, straight, HIPERFACE®, SSI, incremental, RS-422, shielded, for cable diameter 5.5 mm 10.5 mm Head B:  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537

## Additional accessories

Programming and configuration tools

Figure	Brief description	Туре	Part no.
=3:	Programming tool for ATM60, ATM90 and KH53 SSI	PGT-01-S	1030111

<sup>→</sup> For additional accessories, please see page K-668 onwardsw

8015560/2015-09-01 Subject to change without notice

# COMPACT ABSOLUTE LINEAR ENCODER WITH HIGH RESOLUTION



## **Product description**

The TTK70 non-contact linear encoder consists of a compact read head and a magnetic tape. The magnetic tape is equipped with a magnetic partition and forms the measurement scale. The partition consists of an incremental and an absolute track (two-track tape). To calculate the absolute position value, the

read head detects both the absolute and incremental components. The position value is directly output for further processing.

The TTK70 has an SSI output for absolute positioning and an incremental Sin/Cos output for recording speed in real time.

#### At a glance

- · Non-contact absolute positioning
- · Small, compact read head
- Standard SSI interface, combined with sin/cos output
- Measuring lengths of up to 4 m possible
- High level of accuracy (± 10 µm)
- High resolution (1 µm)
- High traversing speed of up to 10 m/s

#### Your benefits

- · Easy integration into existing systems
- Small size, low weight and high traversing speed deliver excellent process dynamics
- After installation, the system is immediately available and completely maintenance-free, which leads to time and cost savings
- Immune to environmental factors such as contamination and condensation, ensuring increased reliability
- Real-time speed determination plus absolute positioning due to Sin/Cos and SSI output



#### Additional information

Detailed technical data J-661
Ordering information
Dimensional drawings J-663
Position tolerance J-663
PIN and wire allocationJ-664
Interfaces J-665
Recommended accessories I-666

→ www.mysick.com/en/TTK70

For more information, simply enter the link or scan the QR code and get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



## Fields of application

 Extremely wide range of positioning tasks in mounting and handling systems, robotics, automation, machine tool and production systems, metal and steel processing, electronics and solar industry, packaging industry, wood processing industry

#### Detailed technical data

#### Performance

Measuring length	Max. 4,000 mm
Magnetic tape length	Measurement length + 80 mm
Resolution	1 μm
Period length	1 mm
Traversing speed	
Static operation (SSI)	< 2 m/s
Dynamic operation (Sin/Cos)	< 10 m/s
Repeatability	Max. ± 2 μm
System accuracy	± 10 µm
Electrical interface	SSI + Sin/Cos
Connection type	Male connector, M12, 12-pin

#### Mechanical data

Dimensions	See dimensional drawing
Mass	
Read head	0.08 kg
Magnetic tape	0.18 kg/m
Material	
Read head	Zinc die cast
Magnetic tape	17410 Hard ferrite 9/28 P
Substrate tape	Stainless steel

## Electrical data

Electrical interfaces	
SSI	24 bit, gray
Sin/Cos	1 V <sub>SS</sub>
Supply voltage	4.5 30 V
Max. power consumption	Max. 1.2 W
Operating current (no load)	55 mA
MTTFd: mean time to dangerous failure 1)	65 years (EN ISO 13849)

<sup>&</sup>lt;sup>1)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of devices, average ambient temperature 40 °C, frequency of use 8,760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

## Ambient data


Operating temperature range	
	-30 °C +85 °C
	-20 °C +70 °C
iviagnetic tape	-20 C +70 C
Storage temperature range	
Read head	-40 °C +85 °C
Magnetic tape	-30 °C +80 °C
Relative humidity / condensation	100%, condensation permitted
Resistance to shocks	30 g / 6 ms (EN 60068-2-27)
Resistance to vibrations	20 g / 10 Hz 2,000 Hz (EN 60068-2-6)
EMC	EN 61000-6-2, EN 61000-6-3
Enclosure rating	IP 67, with mating connector fitted
Temperature coefficient of magnetic tape	$(11 \pm 1) \mu m/K/m$
Maximum permitted ambient field strength <sup>1)</sup>	$<$ 3 kA/m to 4 kA/m (3.8 mT $\dots$ 5 mT); to ensure accuracy values are maintained
Maximum permitted field strength	< 150 kA/m (< 190 mT); to ensure the magnetic tape is not irreparably damaged

<sup>&</sup>lt;sup>1)</sup> The maximum permitted external field influence is reached when the position value deviates from the original value (without external field influence) by more than 5 μm. This value is reached when, at the sensor location, a field strength of 3 kA/m to 4 kA/m (3.8 mT ... 5 mT) occurs in addition to the field strength of the magnetic tape.

# Ordering information


System part	Magnetic tape length	Туре	Part no.
Read head	-	TTK70-AXA0-K02	1038033
	0.5 m	MVM-0M5-2MC- MKLB	6037415
	1 m	MVM-01M-2MC- MKLB	6037417
	1.5 m	MVM-1M5-2MC- MKLB	6037418
Magnetia tana	2 m		6037419
Magnetic tape	2.5 m	MVM-2M5-2MC- MKLB	6037420
	3 m	MVM-03M-2MC- MKLB	6037421
	3.5 m	MVM-3M5-2MC- MKLB	6037422
	4 m	MVM-04M-2MC- MKLB	6037423

## Dimensional drawings (dimensions in mm)




## Position tolerance

General tolerances according to ISO 2768-mk



## PIN and wire allocation

M12 male connector, 12-pin SSI + Sin/Cos



PIN	Color	Signal	Explanation
1	Orange-black	Reconciliation	For internal purposes only / connect to GND
2	White	SSI data +	Signal wire
3	Brown	SSI data -	Signal wire
4	Violet	SSI clock -	Signal wire
5	Red	+U <sub>s</sub>	Operating voltage
6	Gray	/Sin	Signal wire
7	Green	Sin	Signal wire
8	Pink	/Cos	Signal wire
9	Black	Cos	Signal wire
10	Orange	SET 1)	Electronic adjustment
11	Yellow	SSI clock +	Signal wire
12	Blue	GND	Ground connection

<sup>&</sup>lt;sup>1)</sup> SET This input activates the electronic zero set. If the SET wire is connected to U<sub>s</sub> for more than 1.2 seconds after it had previously been unassigned or connected to GND, the position of the encoder above the magnetic tape corresponds to the value 0.


Attention! The SET input must be connected to GND or not be connected when the encoder is switched on. If electronic zeroing is performed using the SET input, the synchronization between the SSI and Sin/Cos signals is lost.

Shield connected to housing on encoder side. Connected to ground on control side.

#### **Interfaces**

#### SSI interface

#### Data format



#### Bit 1-24: Position bits

LSB: Least significant bitMSB: Most significant bit

#### Bit 25-26: Errorbits

- ERRORBIT 1: Error message concerning distance between read head and magnetic tape. This bit is set in the SSI data stream if
  the maximum permitted distance between the read head and the magnetic tape is exceeded. The output position
  value is invalid.
- ERRORBIT 2: Error message concerning working temperature. This bit is set in the SSI data stream if the sensor is operating above its maximum permitted working temperature.

#### Errorbits must evaluated in the PLC.

The errorbits do not have to be used by the PLC. To be able to evaluate the errorbits, the PLC must send at least 26 clock pulses per clock pulse train. A maximum of 31 clock pulses must not be exceeded. If more than 26 pulses are sent, the additional bits are output with "0".


If the errorbits cannot be evaluated in the PLC, the control unit must be set to an encoder resolution of 24 bits.

## Sin/Cos interface 1 V<sub>SS</sub>

Supply voltage	Output
4.5 30 V	Sine 0.5 V <sub>SS</sub>

## Signals **before** difference at 120 $\Omega$ load at U<sub>s</sub> = 5 V


Signal diagram with read head moving in direction of arrow



Interface signals $\sin$ , $\overline{\sin}$ , $\cos$ , $\overline{\cos}$	Signals before difference at 120 $\Omega$ load	Signal offset
Differential analog	0.5 V <sub>SS</sub> ± 10%	2.5 V ± 5%

# Signals after difference at 120 $\Omega$ load at $\rm U_S$ = 5 $\rm V$

Signal diagram with read head moving in direction of arrow



## Recommended accessories

## Connectors

Plug connectors and cables

Connecting cables with female connector

Figure	Brief description	Length of cable	Туре	Part no.
	Head A: M12 female connector, 12-pin, straight	2 m	DOL-1212-G02MAC1	6053273
	Head B: cable	5 m	DOL-1212-G05MAC1	6053274
	Cable: SSI, PUR, shielded, 12 x 0.14 mm², Ø 8.5 mm	10 m	DOL-1212-G10MAC1	6053275
	Suitable for use with drag chains	20 m	DOL-1212-G20MAC1	6053276
113	Head A: female connector, M12, 12-pin, angled	2 m	DOL-1212-W02MAC1	6039824
	Head B: cable Cable: SSI, PUR, shielded, 12 x 0.14 mm², Ø 8.5 mm	5 m	DOL-1212-W05MAC1	6039825
		10 m	DOL-1212-W10MAC1	6039826
	Suitable for use with drag chains	20 m	DOL-1212-W20MAC1	6039827

<sup>→</sup> For additional accessories, please see page K-668 onwards



# **ACCESSORIES**

## SICK connects - Original connection and mounting system for encoders

A perfectly configured connection and mounting system is essential for the optimal integration of encoders. Only reliable mechanical installation and signal transmission guarantee the best possible measurement results. Furthermore, high-quality components with a long service life help to reduce costs in the long term.





Incremental encoders	670
Absolute encoders	686
Safety encoders	716
Wire draw encoders	720
Linear encoders	722
Dimensional drawings	725



# Incremental encoders

## Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
9	→ K-748	Mounting bracket for encoder with centering hub 20 mm, including mounting kit for face mount flange	BEF-WF-20	2066393	•	-	-	-	-	-	-	-	-
1	→ K-749	Mounting bracket for encoder with centering hub 25 mm, including mounting kit for face mount flange	BEF-WF-25	2032621	-	-	•	-	-	-	-	-	-
0	→ K-749	Mounting bracket for encoder with centering hub 30 mm, including mounting kit for face mount flange	BEF-WF-30	2066391	_	•	-	-	-	-	-	-	-
<b>(, -</b>	→ K-750	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	BEF-WF-36	2029164	-	-	-	•	•	-	-	-	-

## Flanges

## Flange plate

Figure	Dimensional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-738	Two-sided stator coupling, screw hole circle diameter 63 mm, slot width 3.2 mm	BEF-DS-09	2076214	-	-	_	•	-	-	-	-	-
	→ K-739	Two-sided stator coupling, slot, slot radius 63 mm to 83 mm, slot width 3.2 mm	BEF-DS-10	2076215	-	-	_	•	-	_	-	-	-
	→ K-739	One-sided stator coupling, slots, slot radius 32.75 mm to 142.65 mm, slot width 4.5 mm	BEF-DS-11	2076216	-	-	_	•	-	-	-	-	-
	→ K-740	One-sided stator coupling, slot, slot radius 33 mm to 48.5 mm, slot width 5.1 mm	BEF-DS-12	2076217				•					
	→ K-740	Flange adapter (for hollow shaft) for locating pin assembly (PIN 4 mm)	BEF-DS-13	2076218	-	-	_	•	-	-	-	-	-
	→ K-740	One-sided stator coupling, slot, slot radius 32.1 mm to 37.6 mm, slot width 4.5 mm	BEF-DS-14	2076678	-	-	-	•	-	-	-	-	-

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
		Chandand to a side database a condition			BB	80	¥	DB	딤	90	90	즈	님
mŽ)	→ K-752	Standard two-sided stator coupling, with screw hole circle diameter 63 mm, slot width 3.2 mm, 10.4 mm high	BEF-DS00XFX	2056812	-	-	-	-	•	-	-	-	-
	→ K-753	One-sided stator coupling, slot, slot radius 33 mm to 48.5 mm, slot width 5.1 mm	BEF-DS01DFS/VFS	2047428	-	-	-	-	•	-	-	_	-
0	→ K-741	One-sided stator coupling, slot, slot radius 32.25 mm to 141.75 mm, slot width 5.1 mm	BEF-DS02DFS/VFS	2047430	-	-	-	-	•	-	-	-	-
• ()	→ K-742	One-sided stator coupling, slot, slot radius 33 mm to 211.9 mm, slot width 5.1 mm	BEF-DS03DFS/VFS	2047431	-	-	-	-	•	-	-	-	-
	→ K-742	Two-sided stator coupling, with screw hole circle diameter 72 mm, slot width 3.2 mm, 16.5 mm high	BEF-DS05XFX	2057423	-	-	-	-	•	-	-	-	-
uÇ)	→ K-743	Two-sided stator coupling, with screw hole circle diameter 72 mm, slot width 3.2 mm, 10.4 mm high	BEF-DS07XFX	2059368	-	-	-	-	•	-	-	-	-
	→ K-743	Two-sided stator coupling, screw hole diameter 42 to 46 mm, slot width 3.2 mm	BEF-DS-DBS36	2066301	•	-	-	-	-	-	-	-	-
E.	→ K-744	Flange adapter, adaption of face mount flange with centering hub 20 mm to 33 mm servo flange, aluminum	BEF-FA-020-033	2066312	•	-	-	-	-	-	-	-	-
0	→ K-744	Flange adapter, adaption of face mount flange with 25 mm cen- tering hub to size 60 face mount flange with 36 mm centering hub, aluminum	BEF-FA-025-036	2034226	-	_	•	-	_	-	-	_	-
	→ K-744	Flange adapter, adaption of face mount flange with centering hub 25 mm to 50 mm servo flange, aluminum	BEF-FA-025-050	2032622	-	-	•	-	-	-	-	-	-
	→ K-744	Flange adapter, adaption of face mount flange with 25 mm centering hub to 60 mm square mounting plate, aluminum	BEF-FA-025-060RCA	2032623	-	-	•	-	-	-	-	-	-
Ŋ	→ K-744	Flange adapter, adaptation of face mount flange with 25 mm centering hub to 60 mm square mounting plate with shock absorbers, alumi- num	BEF-FA-025-060RSA	2032624	_	_	•	-	-	-	-	_	-
4	→ K-744	Flange adapter, adaption of face mount flange with 25 mm centering hub to 63 mm square mounting plate, aluminum	BEF-FA-025-063-REC	2033631	-	-	•	-	-	-	-	_	-
0	→ K-753	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-050	2029160	-	-	-	•	•	-	-	-	-



Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-060REC	2029162	_	-	_	•	•	-	_	-	_
	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, alumi- num	BEF-FA-036-060RSA	2029163	-	-	-	•	•	-	-	-	-
	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10	BEF-FA-036-063REC	2034225	-	-	-	•	•	-	-	-	-
	→ K-753	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161	-	-	-	•	•	-	-	-	-

## Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-746	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020	5312988	-	-	-	•	•	-	-	-	-
0	→ K-746	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	BEF-MR-010020G	5318678	-	-	_	•	•	-	-	-	-
	→ K-746	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	BEF-MR-010050	5312989	-	-	-	•	•	-	-	-	-



Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-747	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	BEF-MR006020R	2055222	•	-	-	•	•	-	-	-	-
	→ K-747	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	BEF-MR006030R	2055634	•	-	-	•	•	-	-	-	-
	→ K-747	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 500 mm	BEF-MR006050R	2055225	•	-	-	•	•	-	-	-	-
	→ K-747	Measuring wheel with 0-ring (NBR70) for 8 mm solid shaft, circumference 200 mm	BEF-MR008020R	2055223	-	•	-	-	-	-	-	-	-
	→ K-747	Measuring wheel with 0-ring (NBR70) for 8 mm solid shaft, circumference 300 mm	BEF-MR008030R	2055635	-	•	-	_	-	-	-	-	-
	→ K-747	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm	BEF-MR010020R	2055224	-	-	-	•	•	-	-	-	-
	→ K-747	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	BEF-MR010030R	2049278	-	-	-	•	•	-	-	-	•
	→ K-747	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 500 mm	BEF-MR010050R	2055227	-	-	-	•	•	_	-	-	-
	-	O-ring for measuring wheels (circumference 200 mm)	BEF-OR-053-040	2064061	•	•	-	•	•	-	-	-	-
	-	O-ring for measuring wheels (circumference 300 mm)	BEF-OR-083-050	2064076	•	•	-	•	•	-	-	-	•
	-	O-ring for measuring wheels (circumference 500 mm)	BEF-OR-145-050	2064074	•	•	-	•	•	-	-	-	-
	-	O-ring set for DKV60 encoder	0-RING SET DKV60	6032709	-	-	-	-	-	-	-	•	-

## Modular measuring wheel system

Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
→ K-747	Measuring wheel system, desired mounting position: left, for DBS50E-S5	BEF-MRS-08-1	2071956	-	•	-	-	-	-	-	-	-
→ K-748	Measuring wheel system, desired mounting position: right, for DBS50E-S5	BEF-MRS-08-2	2071953	-	•	-	-	-	-	-	-	_
→ K-769	Measuring wheel system, desired mounting position: left, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-1	2071958	-	-	-	•	•	-	-	-	-
→ K-769	Measuring wheel system, desired mounting position: right, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	BEF-MRS-10-2	2071957	-	-	-	•	•	-	-	-	-

# Mounting bells

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-746	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	BEF-MG-50	5312987	-	-	-	•	•	-	-	-	-

## Servo clamps

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-755	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165	-	-	-	•	•	-	-	_	-
<b>3 3 3</b>	→ K-756	Servo clamps, small, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-RESOL	2039082	•	•	-	-	-	-	-	_	_
	→ K-755	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166	-	-	-	•	•	-	_	_	-

## Miscellaneous

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	-	Clamping ring for metal hollow shaft, metal	BEF-KR-M	2064709	-	-	-	-	•	-	-	-	-
-91	→ K-745	Bearing block for hollow shaft encoder, including fixing screws	BEF-FA-B12-010	2042728	-	-	-	•	•	-	-	-	_
	→ K-745	Bearing block for servo and face mount flange encoder	BEF-FA-LB1210	2044591	-	-	_	•	•	-	_	-	-



Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	_	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	BEF-MK-LB	5320872	_	-	-	•	•	-	-	-	-
	→ K-754	Flange adapter (adapts size 60 face mount flange encoder to bearing block with part number 2044591)	BEF-FA-036-050-019	2063378	-	-	-	•	•	-	-	-	-
1	-	Spring arm / mounting arm for DFV60	DFV60 sprung arm	2056155	-	-	-	-	-	-	-	-	•

## Shaft adaptation

## Collets and clamping rings

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-757	PEEK conductor insulation (shaft diameter 8 mm, outer diameter 10 mm)	PEEK CONDUCTOR INSULATION	2065642	-	-	-	-	•	-	-	-	-
	→ K-758	PEEK conductor insulation (shaft diameter 10 mm, outer diameter 12 mm)	PEEK CONDUCTOR INSULATION	2064571	-	-	-	-	•	-	-	-	-
	→ K-757	PEEK conductor insulation (shaft diameter 11 mm, outer diameter 12.7 mm)	PEEK CONDUCTOR INSULATION	2077319	-	_	-	-	•	-	-	-	-
	→ K-757	PEEK conductor insulation (shaft diameter 12 mm, outer diameter 14 mm)	PEEK CONDUCTOR INSULATION	2064573	-	_	-	-	•	-	-	_	-
	→ K-757	PEEK conductor insulation (shaft diameter 1/2"(12.7 mm), outer diameter 15 mm)	PEEK CONDUCTOR INSULATION	2064572	_	_	-	-	•	-	-	_	-
	→ K-758	Collet for blind hollow shaft, shaft diameter 5 mm, outer diameter 8 mm	SPZ-005-AD-A	2066991	•	-	-	-	-	-	-	-	-
	→ K-758	Collet for blind hollow shaft, shaft diameter 6 mm, outer diameter 8 mm	SPZ-006-DD36-A	2056390	•	-	-	-	-	-	-	-	-



Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-751	Metal collet for hollow shaft, shaft diameter 8 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-008-M	2076219	-	-	-	•	•	-	-	-	-
	→ K-751	Metal collet for hollow shaft, shaft diameter 3/8" (9.525 mm), outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-38Z-M	2076224	-	-	-	•	•	-	-	-	-
Ma	→ K-751	Metal collet for hollow shaft, shaft di- ameter 10 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-010-M	2076220	-	-	-	•	•	-	-	-	-
	→ K-751	Metal collet for hollow shaft, shaft diameter 12 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-012-M	2076221	-	-	_	•	•	-	-	-	-
	→ K-751	Metal collet for hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-12Z-M	2076225	-	-	-	•	•	-	-	-	-
	→ K-751	Metal collet for hollow shaft, shaft diameter 14 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-014-M	2076222	-	-	-	•	•	-	-	-	-
	→ K-752	Metal collet for hollow shaft, shaft diameter 15 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-015-M	2076223	-	-	-	•	•	-	-	-	-
	→ K-750	Plastic isolated collet for hollow shaft, shaft diameter 6 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-006-P	2076228	-	-	_	•	•	-	-	-	_
	→ K-750	Plastic isolated collet for hollow shaft, shaft diameter 8 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-008-P	2076229	-	-	-	•	•	-	-	-	-
	→ K-750	Plastic isolated collet for hollow shaft, shaft diameter 3/8" (9.525 mm), outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-38Z-P	2076226	-	-	-	•	•	-	-	-	-
	→ K-750	Plastic isolated collet for hollow shaft, shaft diameter 10 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-010-P	2076230	-	-	-	•	•	-	-	-	-
	→ K-750	Plastic isolated collet for hollow shaft, shaft diameter 12 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-012-P	2076231	-	-	-	•	•	-	-	-	-
	→ K-750	Plastic isolated collet for hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-12Z-P	2076227	-	_	_	•	•	-	-	-	-
	→ K-751	Plastic isolated collet for hollow shaft, shaft diameter 14 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-014-P	2076232	-	-	-	•	•	-	-	-	-
	→ K-751	Plastic isolated collet for hollow shaft, shaft diameter 15 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-015-P	2076233	-	-	-	•	•	-	-	-	-



## Shaft couplings

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-756	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial ± 0.25 mm, axial ± 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0606-B	5312981	•	-	-	•	•	-	-	-	Г
	→ K-756	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial ± 0.25 mm, axial ± 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub	KUP-0610-B	5312982	•	-	-	•	•	-	-	-	-
	→ K-756	Bellows coupling, shaft diameter 10 mm/10 mm; maximum shaft offset: radial +/- 0.25 mm, axial +/- 0.4 mm, angular +/- 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1010-B	5312983	-	-	-	•	•	-	-	-	-
	→ K-756	Bellows coupling, shaft diameter 10 mm / 12 mm; maximum shaft offset: radial +/- 0.25 mm, axial +/- 0.4 mm, angular +/- 4°; max. revolutions 10,000 rpm, -30° to +120°C, max. torque 80 Ncm; material: stainless steel bellows, aluminum clamping hubs	KUP-1012-B	5312984	-	-	-	•	•	-	-	-	-



Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-756	Bar coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial ± 0.3 mm, axial ± 0.2 mm, angle ± 3°; max. speed 10,000 rpm, -10° to +80°C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0606-S	2056406	•	-	-	•	•	-	-	-	-
	→ K-756	Bar coupling, shaft diameter 6 mm / 8 mm, maximum shaft offset radial ± 0.3 mm, axial ± 0.2 mm, angle ± 3°, max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0608-S	5314179	•	•	•	•	•	-	-	-	-
	→ K-756	Bar coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial ± 0.3 mm, axial ± 0.2 mm, angular ± 3°; max. speed 10,000 rpm, -10° to +80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0610-S	2056407	•	-	-	•	•	-	-	-	-
	→ K-756	Bar coupling, shaft diameter 8 mm / 8 mm, maximum shaft offset radial ± 0.3 mm, axial ± 0.2 mm, angle ± 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0808-S	5314177	-	•	•	-	-	-	-	_	-
	→ K-756	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-0810-S	5314178	-	•	•	•	•	-	-	-	-
	→ K-756	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial ± 0.3 mm, axial ± 0.2 mm, angle ± 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub	KUP-1010-S	2056408	-	_	-	•	•	-	-	_	-



Figure	Dimensional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
T.	→ K-757	Spring washer coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^\circ$ to $+80^\circ$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-0610-F	5312985	•	-	-	•	•	-	-	-	-
	→ K-757	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial ± 0.3 mm, axial ± 0.4 mm, angular ± 2.5°; max. speed 12,000 rpm, -10° to +80° C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin	KUP-1010-F	5312986	-	-	-	•	•	-	-	-	-
	→ K-756	Double-loop coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, -30 °C to +80 °C, max. torque 1.5 Nm; material: polyure-thane, galvanized steel flange	KUP-0610-D	5326697	•	-	-	•	•	-	-	-	-
	→ K-756	Double-loop coupling, shaft diameter 8 mm / 10 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, -30 °C to +80 °C, max. torque 1.5 Nm; material: polyure-thane, galvanized steel flange	KUP-0810-D	5326704	_	•	•	•	•	-	-	-	_
	→ K-756	Double-loop coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, -30 °C to +80 °C, max. torque 1.5 Nm; material: polyure-thane, galvanized steel flange	KUP-1010-D	5326703	-	-	-	•	•	-	-	-	-
	→ K-756	Double-loop coupling, shaft diameter 10 mm / 12 mm, maximum shaft offset: radial ± 2.5 mm, axial ± 3 mm, angular ± 10°; max. speed 3,000 rpm, -30 °C to +80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange	KUP-1012-D	5326702	-	-	-	•	•	-	-	-	-



# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Dimensional drawing, see page	Brief description	Length of cable	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
		Head A: female connector,	0.5 m	DOL-0J08-G0M5AA3	2046873	-	-	-	-	•	-	-	-	•
		JST, 8-pin, straight Head B: cable	1.5 m	DOL-0J08-G1M5AA3	2046874	-	-	-	-	•	-	-	-	•
and a	→ K-725	Cable: incremental,	3 m	DOL-0J08-G03MAA3	2046875	-	-	-	-	•	-	-	-	•
		suitable for drag chain, PUR, halogen-free, shield-	5 m	DOL-0J08-G05MAA3	2046876	-	-	-	-	•	-	-	-	•
		ed, 4 x 2 x 0.15 mm <sup>2</sup> , Ø 5.6 mm	10 m	DOL-0J08-G10MAA3	2046877	-	-	-	-	•	-	-	-	•
		Head A: female connector, M12, 8-pin, straight	2 m	DOL-1208-G02MAC1	6032866	•	•	•	•	•	-	-	•	•
		Head B: cable	5 m	DOL-1208-G05MAC1	6032867	•	•	•	•	•	-	-	•	•
70	→ K-725	Cable: suitable for drag chain, PVC, shielded,	10 m	DOL-1208-G10MAC1	6032868	•	•	•	•	•	-	-	•	•
		4 0 005 0	20 m	DOL-1208-G20MAC1	6032869	•	•	•	•	•	-	-	•	•
		Head A: female connector, M23, 12-pin, straight Head B: cable	2 m	DOL-2312-G02MLA3	2030682	•	•	•	•	•	-	-	•	•
			7 m	DOL-2312-G07MLA3	2030685	•	•	•	•	•	-	-	•	•
_			10 m	DOL-2312-G10MLA3	2030688	•	•	•	•	•	-	-	•	•
	→ K-725	Cable: incremental, PUR,	15 m	DOL-2312-G15MLA3	2030692	•	•	•	•	•	-	-	•	•
		shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 1 x	20 m	DOL-2312-G20MLA3	2030695	•	•	•	•	•	-	-	•	•
		0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	25 m	DOL-2312-G25MLA3	2030699	•	•	•	•	•	-	-	•	•
			30 m	DOL-2312-G30MLA3	2030702	•	•	•	•	•	-	-	•	•
		Head A: female connector,	1.5 m	DOL-2312-G1M5MA3	2029212	•	•	•	•	•	-	-	•	•
		M23, 12-pin, straight Head B: cable	3 m	DOL-2312-G03MMA3	2029213	•	•	•	•	•	-	-	•	•
	→ K-725	Cable: incremental, suit-	5 m	DOL-2312-G05MMA3	2029214	•	•	•	•	•	-	-	•	•
		able for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup>	10 m	DOL-2312-G10MMA3	2029215	•	•	•	•	•	-	-	•	•
		+ 2 x 0.5 mm <sup>2</sup> + 1 x	20 m	DOL-2312-G20MMA3	2029216	•	•	•	•	•	-	-	•	•
		0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>1)</sup>	30 m	DOL-2312-G30MMA3	2029217	•	•	•	•	•	-	-	•	
			2 m	DOL-2312-G02MLD1	2062202	-	-	-	-	•	-	-	-	_
		Head A: female connector, M23, 12-pin, straight	7 m	DOL-2312-G07MLD1	2062203	-	-	-	-	•	-	-	-	-
		Head B: cable	10 m	DOL-2312-G10MLD1	2062204	-	-	-	-		-	-	-	-
	→ K-725	Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup>	15 m	DOL-2312-G15MLD1	2062205	-	-	-	-	•	-	-	-	-
		+ 2 x 0.5 mm <sup>2</sup> + 1 x	20 m	DOL-2312-G20MLD1	2062206	-	-	-	-	•	-	-	-	-
		0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>2)</sup>	25 m	DOL-2312-G25MLD1	2062207	-	-	-	-	•	-	-	-	-
			30 m	DOL-2312-G30MLD1	2062208	-	-	-	-		-	-	-	_

<sup>1)</sup> Warning! Only in combination with electrical interfaces A, C, E and P.

 $<sup>^{\</sup>rm 2)}$  Warning! Only in combination with electrical interfaces U, V, W and M.



Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
		Head A: female connector,	1.5 m	DOL-2312-G1M5MD1	2062240	-	-	-	-	•	-	-	-	-
		M23, 12-pin, straight	3 m	DOL-2312-G03MMD1	2062243	-	-	-	-	•	-	-	-	-
-	→ K-726	Head B: cable Cable: incremental, suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup>	5 m	DOL-2312-G05MMD1	2062244	-	-	-	-	•	-	-	-	-
	→ N-120		10 m	DOL-2312-G10MMD1	2062245	-	-	-	-	•	-	-	-	-
		+ 2 x 0.5 mm <sup>2</sup> + 1 x	20 m	DOL-2312-G20MMD1	2062246	-	-	-	-	•	-		-	-
		0.14 mm <sup>2</sup> , Ø 7.8 mm <sup>2)</sup>	30 m	DOL-2312-G30MMD1	2062247	-	-	_	-	•	-	-	-	-

 $<sup>^{\</sup>rm 1)}$  Warning! Only in combination with electrical interfaces A, C, E and P.

#### Female connectors (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-726	Head A: female connector, M12, 8-pin, straight, A coded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: -40 °C +85 °C	DOS-1208-GA01	6045001	•	•	•	•	•	-	-	•	•
	→ K-726	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -20 °C +130 °C	DOS-2312-G	6027538	•	•	•	•	•	-	-	•	•
(F-0)	→ K-727	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm Head B: - Operating temperature: -20 °C +130 °C	DOS-2312-W01	2072580	•	•	•	•	•	-	-	•	•
	→ K-726	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	DOS-2312-G02	2077057	•	•	-	•	•	-	-	-	•



 $<sup>^{\</sup>rm 2)}$  Warning! Only in combination with electrical interfaces U, V, W and M.

## Cables (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
		Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm		LTG-2308-MWENC	6027529	•	•	•	•	•	-	-	•	•
<u></u>		Head A: cable Head B: cable Cable: PUR, shielded, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 1 x 0.14 mm <sup>2</sup> , Ø 7.5 mm		LTG-2411-MW	6027530	•	•	•	•	•	-	_	•	•
	-	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm	By the meter	LTG-2512-MW	6027531	•	•	•	•	•	-	-	•	•
<u></u>		Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516	•	•	•	•	•	-	-	•	•

## Male connector (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-727	Head A: male connector, M12, 8-pin, straight, A coded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: -40 °C +85 °C	STE-1208-GA01	6044892	•	•	•	•	•	-	-	•	•



Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	→ K-727	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -20 °C +130 °C	STE-2312-G	6027537	•	•	•	•	•	-	-	•	•
	→ K-727	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	STE-2312-G01	2077273	•	•	•	•	•	-	-	•	•

#### Connection cables with female and male connector

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
		Head A: female connector, JST, 8-pin, straight	0.35 m	STL-2312-GM35AA3	2061621	-	-	-	-	•	-	-	-	•
	→ K-727	Head B: male connector, M23, 12-pin, straight Cable: suitable for drag chain, PUR, halogen-free,	1 m	STL-2312-G01MAA3	2061622	-	-	-	-	•	-	-	-	•
		shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm	2 m	STL-2312-G02MAA3	2061504	-	-	-	-	•	-	-	-	•
	-	Head A: female connector, connector system, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: PVC, shielded, can be used for encoders with cable outlet in conjunction with PGT-10-Pro	0.5 m	DSL-0D08-G0M5AC3	2061739	-	-	-	-	•	-	-	-	•
	-	Head A: female connector, M12, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, 4 x 2 x 0.08 mm <sup>2</sup>	0.5 m	DSL-2D08-G0M5AC3	2046579	-	-	-	-	•	-	-	-	•
	-	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: shielded, 4 x 2 x 0.08 mm <sup>2</sup>	0.5 m	DSL-3D08-G0M5AC3	2046580	-	-	-	-	•	-	-	-	•

# Additional accessories

Programming and configuration tools

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DBS36 Core	DBS50 Core	DKS40	DBS60 Core	DFS60	DGS34	DGS35	DKV60 measuring wheel encoder	DFV60 measuring wheel encoder
	-	Programming unit USB, for pro- grammable SICK encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programma- ble encoders.	PGT-08-S	1036616	_	_	-	-	•	-	_	-	•
A B' B V	-	Programming unit display for programmable SICK DFS60, VFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254	-	-	-	-	•	-	-	-	•





# Absolute encoders

# Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Dimen- sional drawing, see page	Brief description	
1	→ K-748	Mounting bracket for encoder with centering hub 20 mm, including mounting kit for face mount flange	
()	→ K-750	Mounting bracket for encoder with centering hub 36 mm, including mounting kit for face mount flange	



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60	
BEF-WF-20	2066393	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BEF-WF-36	2029164	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-	



# Flanges

## Flange plate

Figure	Dimen- sional drawing, see page	Brief description
u C	→ K-752	Standard stator coupling
40	→ K-753	Stator coupling, one-sided, 81 mm long with slot
0	→ K-741	Stator coupling, one-sided, 179 mm long with slot
.0	→ K-742	Stator coupling, one-sided, 248 mm long with slots
	→ K-742	Stator coupling, 16.5 mm high
	→ K-743	Stator coupling with 63 mm hole circle diameter
	→ K-770	Stator coupling with 63 mm slot radius
0	→ K-770	Flange adapter centering hub D20 to D24
	→ K-771	Flange adapter centering hub D20 to D30
	→ K-771	Flange adapter centering hub D20 to D36
	→ K-772	Flange adapter centering hub D20 to D36, 2 mm high
0	→ K-772	Flange adapter centering hub D20 to D50
0	→ K-753	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 $\times$ 10
6 6	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 $\times$ 10
	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum
	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x 10



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROHBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
BEF-DS00XFX	2056812	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	-
BEF-DS01DFS/VFS	2047428	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	_
BEF-DS02DFS/VFS	2047430	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	-
BEF-DS03DFS/VFS	2047431	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	-
BEF-DS05XFX	2057423	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	_
BEF-DS07XFX	2059368	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	-
BEF-DS08	2072206	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-FA-020-024	2072294	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	_
BEF-FA-020-030	2072295	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-FA-020-036	2072298	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-FA-020-036-002	2072296	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-FA-020-050	2072297	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-FA-036-050	2029160	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-FA-036-060REC	2029162	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	_
BEF-FA-036-060RSA	2029163	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-FA-036-063REC	2034225	-	-	•	•	•	•	•	•	•	•	•	-	-	•	_	-



Figure	Dimen- sional drawing, see page	Brief description	
	→ K-753	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	

# Other mounting accessories

Measuring wheels and measuring wheel systems

Figure	Dimen- sional drawing, see page	Brief description	
<b>(a)</b>	→ K-746	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	
0	→ K-746	Measuring wheel with ridged plastic surface (Hytrel) for 10 mm solid shaft, circumference 200 mm	
	→ K-746	Measuring wheel with smooth plastic surface (Hytrel) for 10 mm solid shaft, circumference 500 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 200 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 300 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 6 mm solid shaft, circumference 500 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 8 mm solid shaft, circumference 200 mm	
( ~ )	→ K-747	Measuring wheel with 0-ring (NBR70) for 8 mm solid shaft, circumference 300 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 8 mm solid shaft, circumference 500 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 200 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 300 mm	
	→ K-747	Measuring wheel with 0-ring (NBR70) for 10 mm solid shaft, circumference 500 mm	
	-	O-ring for measuring wheels (circumference 200 mm)	
	-	O-ring for measuring wheels (circumference 300 mm)	
	-	O-ring for measuring wheels (circumference 500 mm)	

## Modular measuring wheel system

Dimen- sional drawing, see page	Brief description	
→ K-769	Measuring wheel system, desired mounting position: left, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	
→ K-769	Measuring wheel system, desired mounting position: right, for DBS60-S4, DFS60-S4, AFS60-S4, and AFM60-S4	



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROHBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
BEF-FA-036-100	2029161	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
BEF-MR-010020	5312988	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-MR-010020G	5318678	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-MR-010050	5312989	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-MR006020R	2055222	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•
BEF-MR006030R	2055634	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•
BEF-MR006050R	2055225	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•
BEF-MR008020R	2055223	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	_
BEF-MR008030R	2055635	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-MR008050R	2055226	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-MR010020R	2055224	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-MR010030R	2049278	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-MR010050R	2055227	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-0R-053-040	2064061	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•
BEF-0R-083-050	2064076	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•
BEF-OR-145-050	2064074	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROHBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60	
BEF-MRS-10-1	2071958	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	-	
BEF-MRS-10-2	2071957	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-	-	

# Mounting bells

Figure	Dimen- sional drawing, see page	Brief description	
	→ K-746	Mounting bell for encoders with a servo flange, centering hub 50 mm, including mounting kit	

## Servo clamps

Figure	Dimen- sional drawing, see page	Brief description	
()	→ K-755	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	
3 3 3	→ K-756	Servo clamps, small, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	
999	→ K-755	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	

#### Miscellaneous

Figure	Dimen- sional drawing, see page	Brief description	
	-	Clamping ring for metal hollow shaft, metal	
9)	→ K-745	Bearing block for hollow shaft encoder, including fixing screws	
	→ K-745	Bearing block for servo and face mount flange encoder	
	-	Mounting kit for servo flange encoder on the bearing block, 1 bar coupling SKPS 1520 06/06 1 hexagon socket wrench SW1.5 DIN 911, 3 mounting eccentric BEMN 1242 49 3 screws M4 x 10 DIN 912, 1 hexagon socket wrench SW3 DIN 911	



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
BEF-MG-50	5312987	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-
Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
BEF-WG-SF050	2029165	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-WK-RESOL	2039082	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BEF-WK-SF	2029166	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	•
Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
BEF-KR-M	2064709	-	-	•	•	•	•	•	-	-	-	-	-	-	-	-	-
BEF-FA-B12-010	2042728	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-
BEF-FA-LB1210	2044591	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	_
BEF-MK-LB	5320872	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	•



Figure	Dimen- sional drawing, see page	Brief description	
	→ K-754	Flange adapter (adapts size 60 face mount flange encoder to bearing block with part number 2044591)	

# Shaft adaptation

Collets and clamping rings

Figure	Dimen- sional drawing, see page	Brief description	
		Collet for blind hollow shaft, shaft diameter 6 mm, outer diameter 15 mm	
		Collet for blind hollow shaft, shaft diameter 8 mm, outer diameter 15 mm	
		Collet for blind hollow shaft, shaft diameter 10 mm, outer diameter 15 mm	
	→ K-773	Collet for blind hollow shaft, shaft diameter 12 mm, outer diameter 15 mm	
	• 11 110	Collet for blind hollow shaft, shaft diameter 14 mm, outer diameter 15 mm	
		Collet for blind hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter 15 mm	
		Collet for blind hollow shaft, shaft diameter $1/4$ " (6.35 mm), outer diameter 15 mm	
		Collet for blind hollow shaft, shaft diameter 3/8" (9.525 mm), outer diameter 15 mm	
		Collet for through hollow shaft, shaft diameter 6 mm, outer diameter 14 mm	
		Collet for through hollow shaft, shaft diameter 8 mm, outer diameter 14 mm	
		Collet for through hollow shaft, shaft diameter 10 mm, outer diameter 14 mm	
	→ K-773	Collet for through hollow shaft, shaft diameter 12 mm, outer diameter 14 mm	
		Collet for through hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter 14 mm	
		Collet for through hollow shaft, shaft diameter $1/4$ " (6.35 mm), outer diameter $14$ mm	
		Collet for through hollow shaft, shaft diameter 3/8" (9.525 mm), outer diameter 14 mm	



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
BEF-FA-036-050-019	2063378	-	-	•	•	•	•	•	•	•	•	•	-	-	•	-	-

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
SPZ-006-AD-A	2029174	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	-
SPZ-008-AD-A	2029176	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	-
SPZ-010-AD-A	2029178	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	-
SPZ-012-AD-A	2029179	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	_
SPZ-014-AD-A	2048863	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	-
SPZ-1E2-AD-A	2029180	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	-
SPZ-1E4-AD-A	2029175	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	-
SPZ-3E8-AD-A	2029177	-	-	-	-	-	-	-	•	•	•	•	-	-	•	-	-
SPZ-006-AD-D	2029192	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
SPZ-008-AD-D	2029194	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
SPZ-010-AD-D	2029196	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
SPZ-012-AD-D	2029197	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
SPZ-1E2-AD-D	2029198	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
SPZ-1E4-AD-D	2029193	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
SPZ-3E8-AD-D	2029195	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-



## Shaft couplings

Figure	Dimen- sional drawing, see page	Brief description
	→ K-756	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub
	→ K-756	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub
	→ K-756	Bellows coupling, shaft diameter $10 \text{ mm} / 10 \text{ mm}$ ; maximum shaft offset: radial $+/- 0.25 \text{ mm}$ , axial $+/- 0.4 \text{ mm}$ , angular $+/- 4^\circ$ ; max. revolutions $10,000 \text{ rpm}$ , $-30^\circ$ to $+120^\circ$ C, max. torque $80 \text{ Ncm}$ ; material: stainless steel bellows, aluminum clamping hubs
	→ K-756	Bellows coupling, shaft diameter $10 \text{ mm} / 12 \text{ mm}$ ; maximum shaft offset: radial $+/- 0.25 \text{ mm}$ , axial $+/- 0.4 \text{ mm}$ , angular $+/- 4^\circ$ ; max. revolutions $10,000 \text{ rpm}$ , $-30^\circ$ to $+120^\circ$ C, max. torque $80 \text{ Ncm}$ ; material: stainless steel bellows, aluminum clamping hubs
	→ K-756	Bar coupling, shaft diameter 6 mm $/$ 6 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, $-10^\circ$ to $+80^\circ$ C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub
	→ K-756	Bar coupling, shaft diameter 6 mm $/$ 8 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°, max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub
	→ K-756	Bar coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; max. speed 10,000 rpm, $-$ 10° to $+$ 80 °C, max. torque 80 Ncm; material: fiber-glass reinforced polyamide, aluminum hub
	→ K-756	Bar coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angular $\pm$ 3°; torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub
	→ K-756	Bar coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset radial $\pm$ 0.3 mm, axial $\pm$ 0.2 mm, angle $\pm$ 3°; max. speed 10,000 rpm, torsion spring rigidity 38 Nm/wheel; material: fiber-glass reinforced polyamide, aluminum hub
	→ K-756	Double-loop coupling, shaft diameter 6 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30 °C to $+$ 80 °C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange
	→ K-756	Double-loop coupling, shaft diameter 8 mm $/$ 10 mm, maximum shaft offset: radial $\pm$ 2.5 mm, axial $\pm$ 3 mm, angular $\pm$ 10°; max. speed 3,000 rpm, $-$ 30°C to $+$ 80°C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange
	→ K-756	Double-loop coupling, shaft diameter $10 \text{ mm} / 10 \text{ mm}$ , maximum shaft offset: radial $\pm 2.5 \text{ mm}$ , axial $\pm 3 \text{ mm}$ , angular $\pm 10^\circ$ ; max. speed 3,000 rpm, $-30^\circ$ C to $+80^\circ$ C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange
	→ K-756	Double-loop coupling, shaft diameter $10 \text{ mm} / 12 \text{ mm}$ , maximum shaft offset: radial $\pm 2.5 \text{ mm}$ , axial $\pm 3 \text{ mm}$ , angular $\pm 10^\circ$ ; max. speed 3,000 rpm, $-30^\circ$ C to $+80^\circ$ C, max. torque 1.5 Nm; material: polyurethane, galvanized steel flange
C	→ K-757	Spring washer coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^\circ$ to $+80^\circ$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin
	→ K-757	Spring washer coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.3 mm, axial $\pm$ 0.4 mm, angular $\pm$ 2.5°; max. speed 12,000 rpm, $-10^\circ$ to $+80^\circ$ C, max. torque 60 Ncm; material: aluminum flange, glass fiber-reinforced polyamide membrane and hardened steel coupling pin



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
KUP-0606-B	5312981	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•
KUP-0610-B	5312982	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•
KUP-1010-B	5312983	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
KUP-1012-B	5312984	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
KUP-0606-S	2056406	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•
KUP-0608-S	5314179	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•
KUP-0610-S	2056407	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•
KUP-0810-S	5314178	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
KUP-1010-S	2056408	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
KUP-0610-D	5326697	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•
KUP-0810-D	5326704	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
KUP-1010-D	5326703	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
KUP-1012-D	5326702	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-
KUP-0610-F	5312985	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•
KUP-1010-F	5312986	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	-



# Connectivity

Adapters and distributors

## Bus adapters

Figure	Dimen- sional drawing, see page	Brief description	
	→ K-728	PROFIBUS DP, connection adapter KR3, 3 x PG	
	→ K-728	PROFIBUS DP, connection adapter SR3, 3 x M12, 5-pin	
		CANopen, connection adapter KR1, 1 x PG	
	→ K-728	CANopen, connection adapter KR2, 2 x PG	
		CANopen, connection adapter KR3, 3 x PG	
03	→ K-728	CANopen, connection adapter SR1, 1 x M12, 5-pin	
	→ K-728	CANopen, connection adapter SR2, 2 x M12, 5-pin	
	→ K-728	DeviceNet, connection adapter KR1, 1 x PG	
	→ N-120	DeviceNet, connection adapter KR2, 2 x PG	
	→ K-728	DeviceNet, connection adapter SR1, 1 x M12, 5-pin	
	7 N-120	DeviceNet, connection adapter SR2, 2 x M12, 5-pin	

## T-piece

Figure	Dimen- sional drawing, see page	Brief description	
S	-	CANopen, T-piece	



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
AD-ATM60-KA3PR	2029225	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-
AD-ATM60-SR3PR	2031985	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	_
AD-ATM60-KR1CO	2029230	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-	_
AD-ATM60-KR2CO	2029231	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-
AD-ATM60-KR3CO	2029232	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-	_
AD-ATM60-SR1CO	2031686	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-	_
AD-ATM60-SR2CO	2020935	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-	_
AD-ATM60-KR1DN	2029228	-	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-
AD-ATM60-KR2DN	2029229	-	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-
AD-ATM60-SR1DN	2029226	-	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-
AD-ATM60-SR2DN	2029227	-	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60	
DSC- 1205T000025KM0	6030664	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	



# Plug connectors and cables

Connecting cables with female connector

Figure	Dimen- sional drawing, see page	Brief description	Length of cable
<b>1</b>	→ K-729	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: suitable for drag chain, shielded, 2 x 0.34 mm² + 2 x 0.25 mm² + 1 x 0.34 mm², Ø 6.7 mm A-coded	2 m 5 m 10 m
70	→ K-725	Head A: female connector, M12, 8-pin, straight Head B: cable Cable: suitable for drag chain, PVC, shielded, $4 \times 2 \times 0.25 \text{ mm}^2$ , Ø 7.0 mm	2 m 5 m 10 m 20 m
The state of the s	→ K-725	Head A: female connector, JST, 8-pin, straight Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm	0.5 m 1.5 m 3 m 5 m 10 m
	→ K-730	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm	0.5 m 1.5 m 3 m 5 m 10 m
	→ K-730	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm	1.5 m 3 m 5 m 10 m 20 m 30 m
	→ K-728	Head A: M12 female connector, 4-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded, 4 x 0.34 mm², Ø 4.7 mm	2 m 5 m 10 m 25 m
	→ K-728	Head A: M12 female connector, 4-pin, angled Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, unshielded, 4 x 0.34 mm², Ø 4.7 mm	2 m 5 m 10 m 25 m
100	→ K-728	Head A: female connector, M12, 5-pin, angled Head B: cable Cable: for power supply, PUR, halogen-free, shielded, 3 x 0.34 mm², Ø 4.2 mm	5 m 10 m

 $<sup>^{1)}</sup>$  Suitable for SSI interfaces, not suitable for SSI + Incremental or SSI + Sin/Cos interfaces.

<sup>4)</sup> For ARS60 Parallel.



<sup>&</sup>lt;sup>2)</sup> Suitable for SSI + Incremental and SSI + Sin/Cos interfaces.

<sup>3)</sup> For ARS60 SSI.

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
		¥	¥	AF	AF	AF	A	A	A	A	A	A	A	A	AF	Ą	A
DOL-1205-G02MY	6053041	-	•	-	-	-	-	-	-	-	•	-	-	-	-	-	-
DOL-1205-G05MY	6053042	-	•	-	-	-	-	-	-	-	•	-	-	-	-	-	-
DOL-1205-G10MY	6053043	-	•	-	-	-	-	-	-	-	•	-	-	-	-	-	-
DOL-1208-G02MAC1	6032866	•	-	•	_	-	_	-	-	-	-	-	-	-	-	-	-
DOL-1208-G05MAC1	6032867	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-1208-G10MAC1	6032868	•	-	•	_	-	-	-	_	-	-	_	-	-	-	-	-
DOL-1208-G20MAC1	6032869	•	_	•	-	-	-	-	_	-	_	_	-	-	-	-	-
DOL-0J08-G0M5AA6	2048589	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-0J08-G1M5AA6	2048590	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-0J08-G3M0AA6	2048591	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-0J08-G5M0AA6	2048593	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-0J08-G10MAA6	2048594	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2308-GOM5AA6	2048595	-	-	<b>1</b> )	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2308-G1M5AA6	2048596	-	-	1)	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2308-G03MAA6	2048597	-	-	1)	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2308-G05MAA6	2048598	-	-	1)	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2308-G10MAA6	2048599	-	-	1)	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2312-G1M5MD2	2062284	-	-	• 2)	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2312-G03MMD2	2062300	-	-	<b>2</b> )	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2312-G05MMD2	2062301	-	-	<b>2</b> )	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2312-G10MMD2	2062302	-	-	<b>2</b> )	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2312-G20MMD2	2062303	-	-	<b>2</b> )	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-2312-G30MMD2	2062304	-	-	<b>2</b> )	-	-	-	-	-	-	-	-	-	-	-	-	-
DOL-1204-G02MC	6025900	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1204-G05MC	6025901	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1204-G10MC	6025902	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1204-G25MC	6034751	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1204-W02MC	6025903	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1204-W05MC	6025904	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1204-W10MC	6025905	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1204-W25MC	6034754	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
DOL-1202-W05MC	6042067	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-
DOL-1202-W10MC	6042068	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-



Figure	Dimen- sional drawing, see page	Brief description	Length of cable
	→ K-729	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm	5 m 10 m 20 m
	→ K-729	Head A: female connector, M12, 5-pin, straight Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm	5 m 10 m 12 m 15 m 20 m 30 m 50 m
//	→ K-729	Head A: female connector, M12, 5-pin, angled, B-coded Head B: cable	5 m
	→ K-728	Cable: suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm  Head A: M12 female connector, 4-pin, straight  Head B: cable  Cable: for power supply, suitable for drag chain, PVC, unshielded, 4 x 0.25 mm², Ø 5.0 mm	10 m
	→ K-730	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm	1.5 m 3 m 5 m 10 m 20 m 30 m
->	→ K-730	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: suitable for drag chain, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm	1.5 m 3 m 5 m 10 m 20 m 30 m
	→ K-732	Head A: M23 female connector, 21-pin, straight Head B: cable Cable: PUR, halogen-free, shielded, 20 x 0.14 mm², 2 x 0.25 mm², Ø 7.8 mm	1.5 m 3 m 5 m 10 m 20 m
	→ K-729	Head A: female connector, M12, 5-pin, straight, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm	1.5 m 3 m 5 m 10 m
	→ K-729	Head A: female connector, M12, 5-pin, angled, A-coded Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 5 x 0.34 mm², Ø 5.9 mm	1.5 m 3 m 5 m 10 m

 $<sup>^{\</sup>rm 1)}$  Suitable for SSI interfaces, not suitable for SSI + Incremental or SSI + Sin/Cos interfaces.

 $<sup>^{\</sup>rm 2)}\,\mbox{Suitable}$  for SSI + Incremental and SSI + Sin/Cos interfaces.

<sup>3)</sup> For ARS60 SSI.

<sup>4)</sup> For ARS60 Parallel.

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROHBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
DOL-1205-G05MAC	6036384	-	_	-	-	-	-	•	-	-	-	_	-	_	_	_	-
DOL-1205-G10MAC	6036385	_	_	_	_	_	_	•	_	-	_	_	_	_	_	_	_
DOL-1205-G20MAC	6036386	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	_
DOL-1205-G05MQ	6026006	-	_	-	-	-	-	•	•	-	-	_	-	•	-	-	-
DOL-1205-G10MQ	6026008	_	-	-	-	-	-	•	•	-	_	-	_	•	-	-	-
DOL-1205-G12MQ	6032636	-	_	-	-	-	-	•	•	-	_	_	-	•	-	-	-
DOL-1205-G15MQ	6032637	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
DOL-1205-G20MQ	6032638	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
DOL-1205-G30MQ	6032639	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
DOL-1205-G50MQ	6032861	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
DOL-1205-W05MQ	6041423	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-
DOL-1205-W10MQ	6041425	_	_	-	-	-	_	•	-	-	_	_	_	-	-	-	-
DOL-1204-G05M	6009866	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-
DOL-2312-G1M5MA1	2029200	_	_	-	_	-	_	_	-	•	_	_	•	-	-	-	-
DOL-2312-G03MMA1	2029201	_	_	-	_	-	_	_	-	•	_	_	•	-	-	-	-
DOL-2312-G05MMA1	2029202	_	_	-	_	-	_	_	-	•	_	_	•	-	-	-	-
DOL-2312-G10MMA1	2029203	_	_	-	_	-	_	_	-	•	_	_	•	-	-	-	-
DOL-2312-G20MMA1	2029204	_	_	-	_	-	_	_	-	•	_	_	•	-	-	-	-
DOL-2312-G30MMA1	2029205	-	-	-	-	-	-	-	-	•	-	-	•	-	-	-	-
DOL-2312-G1M5MA2	2029206	-	-	-	-	-	-	-	-	-	-	-	-	-	●3)	-	-
DOL-2312-G03MMA2	2029207	-	-	-	-	-	-	-	-	-	-	-	-	-	●3)	-	-
DOL-2312-G05MMA2	2029208	-	-	-	-	-	-	-	-	-	-	-	-	-	●3)	-	-
DOL-2312-G10MMA2	2029209	-	-	-	-	-	-	-	-	-	-	-	-	-	●3)	-	-
DOL-2312-G20MMA2	2029210	-	-	-	-	-	-	-	-	-	-	-	-	-	<b>3</b> )	-	-
DOL-2312-G30MMA2	2029211	-	-	-	-	-	-	-	-	-	-	-	-	-	<b>3</b> )	-	-
DOL-2321-G1M5PA4	2029218	-	-	-	-	-	-	-	-	-	-	-	-	-	<b>4</b> )	-	-
DOL-2321-G03MPA4	2029219	-	-	-	-	-	-	-	-	-	-	-	-	-	<b>4</b> )	-	-
DOL-2321-G05MPA4	2029220	-	-	-	-	-	-	-	-	-	-	-	-	-	<b>4</b> )	-	-
DOL-2321-G10MPA4	2029221	-	-	-	-	-	-	-	-	-	-	-	-	-	•4)	-	-
DOL-2321-G20MPA4	2029222	-	-	-	-	-	-	-	-	-	-	-	-	-	• 4)	-	-
DOL-1205-G1M5ACSCO	6049451	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOL-1205-G03MACSC0	6049452	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOL-1205-G05MACSCO	6049453	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOL-1205-G10MACSCO	6049454	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOL-1205-W1M5ACSCO	6049455	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOL-1205-W03MACSCO	6049456	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOL-1205-W05MACSCO	6049457	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOL-1205-W10MACSCO	6049458	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•

# Connecting cables with male connector

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	
		Head A: male connector, M12, 4-pin, straight, D coded	2 m	
The second	→ K-735	Head B: cable Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm	5 m	
		Cubic. Fort, harogen rece, siliciaca, 2 x 2 x c. 14 min , \$ 0.4 min	10 m	
		Head As wells commarker MAC A min sounded Decided	2 m	
	→ K-735	Head A: male connector, M12, 4-pin, angled, D coded Head B: cable	5 m	
		Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm <sup>2</sup> , Ø 6.4 mm	10 m	
			25 m	
		Head A: male connector, M12, 4-pin, straight, D coded	2 m	
6	→ K-735	Head B: cable Cable: PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	5 m	
		Cable. PVC, Sillelded, 4 x 0.54 illill <sup>2</sup> , Ø 6.5 illill	10 m	
			2 m	
	→ K-735	Head A: male connector, M12, 4-pin, angled, D coded Head B: cable	5 m	
	711-755	Cable: PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	10 m	
			25 m	
		Head A: M12 male connector, 5-pin, straight, B coded	5 m	
	→ K-736	Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm <sup>2</sup> , Ø 8.0 mm	10 m	
		Wire shielding: AL-PT foil, total shield, tin-plated C shield	12 m	
11	N I/ 700	Head A: male connector, M12, 5-pin, angled, B-coded	5 m	
1	→ K-736	Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.64 mm², Ø 7.8 mm	10 m	



Туре	Part no.		pen		et/IP	Ē	AT®										
		AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
STL-1204-G02ME90	6045284	-	-	-	•	-	-	-	-	-	-	-	-	_	_	-	_
STL-1204-G05ME90	6045285	-	_	-	•	-	-	_	_	_	_	_	-	_	_	_	_
STL-1204-G10ME90	6045286	-	_	-	•	-	-	_	_	_	_	_	-	_	_	_	_
STL-1204-W02ME90	6047912	-	-	-	•	-	-	-	-	-	-	-	-	_	_	-	_
STL-1204-W05ME90	6047913	-	-	-	•	-	-	-	-	-	-	-	-	_	-	_	-
STL-1204-W10ME90	6047914	-	-	-	•	-	-	-	-	-	-	-	-	_	-	-	-
STL-1204-W20ME90	6047915	-	-	-	•	-	-	-	-	-	-	-	-	_	-	-	-
STL-1204-G02MZ90	6048247	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STL-1204-G05MZ90	6048248	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STL-1204-G10MZ90	6048249	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STL-1204-W02MZ90	6048256	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STL-1204-W05MZ90	6048257	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STL-1204-W10MZ90	6048258	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STL-1204-W25MZ90	6048259	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STL-1205-G05MQ	6026005	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
STL-1205-G10MQ	6026007	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
STL-1205-G12MQ	6032635	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
STL-1205-W05MQ	6041426	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-
STL-1205-W10MQ	6041427	-	-	-	-	-	-	•	-	-	-	-	-	-	_	-	-



## Female connectors (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description
	→ K-731	Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -
	→ K-731	Head A: female connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -
	→ K-731	Head A: female connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm  Head B: -
		Head A: female connector, M12, 4-pin, straight, D-coded, shielded, for cable diameter 4 mm 8 mm
	→ K-731	Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm 6.5 mm Head B: -
AF STATE	→ K-731	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm Head B: -
	→ K-731	Head A: female connector, M12, 4-pin, angled, D-coded, shielded, for cable diameter 4 mm 8 mm
	→ K-731	Head A: female connector, M12, 5-pin, straight, shielded, for cable diameter 4.5 mm 7 mm Head B: -
	→ K-731	Head A: female connector, M12, 5-pin, straight, B-coded, shielded, for cable diameter 4 mm 9 mm Head B: -
	→ K-731	Head A: female connector, M12, 5-pin, angled, B-coded, shielded, for cable diameter 4 mm 8 mm Head B: -
	→ K-726	Head A: female connector, M12, 8-pin, straight, A coded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^{\circ}$ C $+85~^{\circ}$ C
	→ K-731	Head A: female connector, M14, 7-pin, straight, shielded, for cable diameter 4 mm 8 mm Head B: -
	→ K-726	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B:  Operating temperature: -20 °C +130 °C
	→ K-726	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C
(F)=0	→ K-727	Head A: female connector, M23, 12-pin, angled, shielded, for cable diameter 4.2 mm 6.6 mm Head B: Operating temperature: $-20~^{\circ}$ C $+130~^{\circ}$ C
	→ K-732	Head A: female connector, M23, 21-pin, straight, shielded, for cable diameter 5.5 mm 12 mm Head B: -
104	→ K-730	Head A: female connector, D-Sub, 37-pin, straight, shielded Head B: -



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
DOS-1204-G	6007302	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
DOS-1205-G	6009719	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
DOS-1204-GE	6048153	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-
DOS-1204-GZ	6048263	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
DOS-1204-W	6007303	-	-	-	•	•	•	•	-	-	-	-	-	-	-	-	-
DOS-1204-WE	6048154	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-
DOS-1204-WZ	6048264	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
DOS-1205-GA	6027534	-	•	-	-	-	-	-	-	-	•	•	-	-	-	-	-
DOS-1205-GQ	6021353	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
DOS-1205-WQ	6041429	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	_
DOS-1208-GA01	6045001	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DOS-1507-G	6027536	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-	-
DOS-2312-G	6027538	-	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-
DOS-2312-G02	2077057	-	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-
DOS-2312-W01	2072580	-	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-
DOS-2321-G	6027539	-	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-
DOS-0D37-G	2029224	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-



## Cables (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	
		Head A: cable Head B: cable Cable: suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm		
		Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm², Ø 5.6 mm		
<b>\</b>		Head A: cable Head B: cable Cable: PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm		
	-	Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , $\emptyset$ 7.8 mm	By the meter	
<b>\</b>		Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater-resistant, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 2 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm		
		Head A: cable Head B: cable Cable: PUR, halogen-free, shielded, 20 x 0.14 mm², 2 x 0.25 mm², Ø 7.8 mm		
///		Head A: cable Head B: cable Cable: suitable for drag chain, shielded, 2 x 0.34 mm <sup>2</sup> + 2 x 0.25 mm <sup>2</sup> Wire shielding: AL-PT foil, total shield, tin-plated C shield		

## Other plug connectors and cables

Figure	Dimen- sional drawing, see page	Brief description
	-	A3M60 accessories sales set comprising: Female cable connector, supply voltage, M12, angled (6007303) female cable connector, M12, angled (6041429), male cable connector, M12, angled (6041428)
	→ K-731	Sales kit consisting of: 2 x M14 male cable connectors, 7-pin (6027535) 1 x M14 female cable connector, 7-pin (6027535)
00	→ K-733	Head A: female connector, M12, 4-pin, D-coded Head B: female connector, RJ45, 8-pin Cable: shielded Switch cabinet feedthrough
	→ K-735	Head A: M12 male connector, 4-pin, straight, B coded Cable: terminator
	→ K-734	Head A: male connector, M12, 5-pin, straight, shielded Cable: terminator



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
LTG-2102-MW	6021355	-	-	_	-	-	-	•	•	-	-	-	-	•	-	-	-
LTG-2308-MWENC	6027529	•	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-
LTG-2411-MW	6027530	-	-	-	-	-	-	-	-	•	-	-	•	-	•	-	-
LTG-2512-MW	6027531	-	-	-	-	-	-	-	-	•	-	-	•	-	•	-	-
LTG-2612-MW	6028516	•	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-
LTG-2622-MW	6027532	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
LTG-2804-MW	6028328	-	•	-	-	-	-	-	-	-	•	•	-	-	-	-	-

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
DOS-3XM12-W	2058177	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-
DSC-1507-G	2029199	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-	-
Feedthrough female connector Ethernet RJ45	6048180	-	-	-	•	•	•	-	-	-	-	-	-	-	-	-	-
STE-END-Q	6021156	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
STE-1205-GKEND	6037193	-	•	-	-	-	-	-	-	-	•	-	-	-	-	-	-



## Male connector (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	
100	→ K-730	Head A: male connector, D-Sub, 15-pin, straight, shielded Head B: -	
	→ K-734	Head A: male connector, RJ45, 4-pin, straight, shielded, for cable diameter 4.5 mm 8 mm Head A: male connector, RJ45, 8-pin, straight, shielded, for cable diameter 4.5 mm 8 mm Head B: -	
Co	→ K-734	Head A: male connector, M12, 4-pin, straight, D coded, shielded, for cable diameter 4 mm 8 mm Head B: -	
	→ K-734	Head A: male connector, M12, 4-pin, straight, D coded, shielded, for cable diameter 4 mm 8 mm	
1	→ K-734	Head A: male connector, M12, 4-pin, angled, D coded, shielded, for cable diameter 4 mm 8 mm Head B: -	
	→ K-734	Head A: male connector, M12, 4-pin, angled, D coded, shielded, for cable diameter 4 mm 8 mm	
	→ K-734	Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -	
Co	→ K-734	Head A: male connector, M12, 5-pin, straight, A coded, shielded, for cable diameter 4 mm 8 mm Head B: -	
	→ K-734	Head A: male connector, M12, 5-pin, straight, B coded, shielded, for cable diameter 4 mm 9 mm Head B: -	
	→ K-735	Head A: male connector, M12, 5-pin, angled, B coded, shielded, for cable diameter 4 mm 8 mm Head B: -	
	→ K-727	Head A: male connector, M12, 8-pin, straight, A coded, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: $-40~^{\circ}$ C +85 $^{\circ}$ C	
	→ K-731	Head A: male connector, M14, 7-pin, straight, D coded, shielded, for cable diameter 4 mm 8 mm Head B: -	
	→ K-727	Head A: male connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm $\dots$ 10.5 mm Head B: Operating temperature: -20 °C $\dots$ +130 °C	
	→ K-727	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: -40 °C +125 °C	



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
STE-0D15-G	2029223	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-
STE-0J04-GZ	6048260	-	-	-	-	•	•	-	-	-	-	-	-	-	-	_	_
STE-0J08-GE	6048150	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-
STE-1204-GE01	6048151	-	-	-	•	_	-	-	-	-	-	_	-	-	_	_	-
STE-1204-GZ	6048261	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STE-1204-WE	6048152	-	-	-	•	_	-	-	-	-	-	-	-	-	-	-	_
STE-1204-WZ	6048262	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
STE-1205-G	6022083	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•
STE-1205-GA	6027533	-	•	-	-	-	-	-	-	-	•	•	-	-	-	-	-
STE-1205-GQ	6021354	-	-	-	-	-	-	•	•	-	-	-	-	•	-	-	-
STE-1205-WQ	6041428	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-
STE-1208-GA01	6044892	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
STE-1507-G	6027535	-	-	-	-	-	-	-	-	-	-	-	-	•	-	-	-
STE-2312-G	6027537	-	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-
STE-2312-G01	2077273	-	-	•	-	-	-	-	-	•	-	-	•	-	•	-	-



#### Connection cables with male and male connector

Figure	Dimen- sional drawing, see page	Brief description	Length of cable
	→ K-733	Head A: male connector, M12, 4-pin, straight, D coded Head B: male connector, M12, 4-pin, straight, D coded Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m 5 m 10 m
	→ K-733	Head A: male connector, M12, 4-pin, angled, D coded Head B: male connector, M12, 4-pin, straight, D coded Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m 5 m 10 m
	-	Head A: male connector, M12, 4-pin, angled, D coded Head B: male connector, M12, 4-pin, angled, D coded Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m 5 m 10 m
	→ K-733	Head A: male connector, M12, 4-pin, straight, D coded Head B: male connector, RJ45, 8-pin, straight Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m 5 m 10 m
-	→ K-734	Head A: male connector, M12, 4-pin, angled, D coded Head B: male connector, RJ45, 8-pin, straight Cable: PUR, halogen-free, shielded, 2 x 2 x 0.14 mm², Ø 6.4 mm	2 m 5 m 10 m
	→ K-733	Head A: male connector, M12, 4-pin, angled, D coded Head B: male connector, M12, 4-pin, straight Cable: PVC, shielded, 4 x 0.34 mm <sup>2</sup> , Ø 6.5 mm	2 m 5 m 10 m
	→ K-733	Head A: male connector, M12, 4-pin, straight, D coded Head B: male connector, M12, 4-pin, straight Cable: PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m 5 m 10 m
700	-	Head A: male connector, M12, 4-pin, angled, D coded Head B: male connector, M12, 4-pin, angled, D coded Cable: PUR, halogen-free, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m 5 m 10 m
	→ K-733	Head A: male connector, RJ45, 4-pin, straight, D coded Head B: male connector, M12, 4-pin, angled Cable: PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m 5 m 10 m
	-	Head A: male connector, M12, 4-pin, straight, D coded Head B: male connector, RJ45, 4-pin, straight Cable: PVC, shielded, 4 x 0.34 mm², Ø 6.5 mm	2 m 5 m 10 m



Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
SSL-1204-G02ME90	6045222	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-G05ME90	6045277	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-G10ME90	6045279	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-H02ME90	6047908	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-H05ME90	6047909	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-H10ME90	6047910	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-W02ME	6050632	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-W05ME	6050633	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-1204-W10ME	6050634	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-2J04-G02ME60	6047916	_	_	_	•	_	_	_	_	_	_	_	_	_	_	_	_
SSL-2J04-G05ME60	6047917	-	_	_	•	_	_	_	_	_	_	-	_	_	_	_	_
SSL-2J04-G10ME60	6047918	-	_	_	•	_	_	_	_	_	_	-	_	_	_	_	_
SSL-2J04-H02ME	6047911	-	_	_	•	_	_	_	_	_	_	-	_	_	_	_	_
SSL-2J04-H05ME	6045287	-	_	_	•	_	_	_	_	_	_	-	_	_	_	_	_
SSL-2J04-H10ME	6045288	-	_	_	•	_	_	_	_	_	_	-	_	_	_	_	_
SSL-1204-F02MZ90	6048250	-	_	_	_	•	•	_	_	_	_	-	-	-	_	-	-
SSL-1204-F05MZ90	6048251	-	_	_	_	•	•	_	_	_	_	_	_	_	_	_	_
SSL-1204-F10MZ90	6048252	-	_	_	_	•	•	_	_	_	_	_	_	_	_	_	_
SSL-1204-G02MZ90	6048241	-	_	_	_	•	•	_	_	_	_	_	-	_	_	_	_
SSL-1204-G05MZ90	6048242	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
SSL-1204-G10MZ90	6048243	-	-	-	-	•	•	-	_	_	-	-	-	-	_	-	-
SSL-1204-W02MZ	6050635	-	-	-	-	•	•	-	_	_	_	-	-	-	-	-	-
SSL-1204-W05MZ	6050636	-	-	-	-	•	•	-	_	_	-	-	-	-	-	-	-
SSL-1204-W10MZ	6050637	-	_	-	-	•	•	-	-	-	-	-	-	-	-	_	-
SSL-2J04-F02MZ	6048253	-	_	-	-	•	•	-	_	_	_	-	-	-	_	_	-
SSL-2J04-F05MZ	6048254	-	_	-	-	•	•	-	_	_	_	-	-	-	_	-	-
SSL-2J04-F10MZ	6048255	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
SSL-2J04-G02MZ60	6048244	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
SSL-2J04-G05MZ60	6048245	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-
SSL-2J04-G10MZ60	6048246	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-



#### Connection cables with female and male connector

Figure	Dimen- sional drawing, see page	Brief description	Length of cable
		Head A: female connector, M12, 5-pin, straight	2 m
4040	→ K-732	Head B: male connector, M12, 5-pin, straight  Cable: suitable for drag chain, PUR, halogen-free, shielded, 2 x 0.34 mm² + 2 x 0.25 mm²	5 m
		+ 1 x 0.34 mm <sup>2</sup> , Ø 6.7 mm, A coded	10 m
100	→ K-732	Head A: female connector, M12, 5-pin, straight Head B: male connector, M12, 5-pin, straight Cable: drop cable, PUR, halogen-free, unshielded, 2 x 0.34 mm², Ø 6.9 mm	6 m
	-	Head A: female connector, M12, 8-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: PUR, halogen-free, shielded, 4 x 2 x 0.15 mm <sup>2</sup>	0.5 m
	-	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight Cable: suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.15 mm²	0.5 m
	-	Head A: female connector, M23, 12-pin, straight Head B: male connector, D-Sub, 9-pin, straight, 8-wire	0.5 m

 $<sup>^{1)}</sup>$  Suitable for use with SSI interfaces, not suitable for use with SSI + Incremental interface or SSI + Sin/Cos.

#### Additional accessories

## Programming and configuration tools

Figure	Dimen- sional drawing, see page	Brief description	
=::	-	Programming tool for ATM60, ATM90 and KH53 SSI	
	-	Programming unit USB, for programmable SICK encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoders.	
V m . m A	-	Programming unit display for programmable SICK DFS60, VFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	



 $<sup>^{2)}</sup>$  Suitable for use with SSI + Incremental or SSI + Sin/Cos interfaces.

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60
DSL-1205-G02MY	6053044	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DSL-1205-G05MY	6053045	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DSL-1205-G10MY	6053046	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DSL-1205-G06MK	6028327	-	-	-	-	-	-	-	-	-	•	•	-	-	-	-	-
DSL-2D08-G0M5AC2	2048439	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-
DSL-3D08-G0M5AC2	2048440	-	-	<b>1</b> )	-	-	-	-	-	-	-	-	-	-	-	-	-
DSL-3D08-G0M5AC4	2059270	-	-	<b>1</b> 2)	-	-	-	-	-	-	-	-	-	-	-	-	-

Туре	Part no.	AHS/AHM36 SSI	AHS/AHM36 CANopen	AFS/AFM60 SSI	AFS/AFM60 EtherNet/IP	AFS/AFM60 PROFINET	AFS/AFM60 EtherCAT®	A3M60 PROFIBUS	ATM60 PROFIBUS	ATM60 SSI	ATM60 CANopen	ATM60 DeviceNet	ATM90 SSI	ATM90 PROFIBUS	ARS60 SSI/Parallel	ACS/ACM36	ACM60	
PGT-01-S	1030111	-	-	-	-	-	-	-	_	•	-	-	•	_	-	-	-	
PGT-08-S	1036616	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	
PGT-10-Pro	1072254	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	



# Safety encoders

The accessories are part of the safety-related function chain and must be assessed and validated accordingly by the user. This is not an integral part of the safety assessment carried out by SICK.

## Mounting systems

#### Flanges

#### Flange plate

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DFS60S Pro
0	→ K-753	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 50 mm servo flange, aluminum, including 3 flat head screws M4 x 10 $$	BEF-FA-036-050	2029160	•
6 6	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 60 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-060REC	2029162	•
	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 58 mm square mounting plate with shock absorbers, aluminum	BEF-FA-036-060RSA	2029163	•
	→ K-754	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 63 mm square mounting plate, aluminum, including 3 flat head screws M4 x $10$	BEF-FA-036-063REC	2034225	•
	→ K-753	Flange adapter, adaptation of face mount flange with 36 mm centering hub to 100 mm servo flange with 60 mm centering hub, aluminum	BEF-FA-036-100	2029161	•
	→ K-741	Stator coupling, one-sided, 179 mm long with slot	On request	On request 1)	•

<sup>&</sup>lt;sup>1)</sup> For more detailed information, please consult your local SICK subsidiary. The stator coupling is mounted ex works. The customer is not permitted to replace the stator coupling

## Other mounting accessories

#### Servo clamps

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DFS60S Pro
	→ K-755	Half-shell servo clamps (2 pcs.) for servo flanges with a 50 mm centering hub	BEF-WG-SF050	2029165	•
	→ K-755	Servo clamps, large, for servo flanges (clamps, eccentric fastener), 3 pcs., without mounting material	BEF-WK-SF	2029166	•

#### Miscellaneous

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DFS60S Pro
	-	1 M4x16 cylinder head screw and 1 2x2x6 feather key acc. to DIN 6885	BEF-MK-SE01	2073617	•



# Shaft adaptation

# Shaft couplings

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DFS60S Pro
	→ K-755	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub, for use with feather key	KUP-0606-BP	2075379	•
	→ K-755	Bellows coupling, shaft diameter 6 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub, for use with feather key	KUP-0610-BP	2075375	•
	→ K-756	Bellows coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular +/- 4°; max. speed 10,000 rpm, -30 °C to +120 °C, max. torque 80 Ncm; material: stainless steel bellows, aluminum hub, for use with feather key	KUP-1010-BP	2075373	•
	→ K-755	Bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-30^\circ$ to $+120^\circ$ C, max. torque 80 Ncm; material: stainless steel bellows, fixed with two setscrews each	KUP-0606-BS	2075378	•
	→ K-755	Bellows coupling, shaft diameter 6 mm / 10 mm, bellows coupling, shaft diameter 6 mm / 6 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-30^{\circ}$ to +120° C, max. torque 80 Ncm; material: stainless steel bellows, fixed with two setscrews each	KUP-0610-BS	2075377	•
	→ K-756	Bellows coupling, shaft diameter 10 mm / 10 mm, maximum shaft offset: radial $\pm$ 0.25 mm, axial $\pm$ 0.4 mm, angular $\pm$ 4°; max. speed 10,000 rpm, $-30^{\circ}$ to +120° C, max. torque 80 Ncm; material: stainless steel bellows, fixed with two setscrews each	KUP-1010-BS	2075376	•



# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	DFS60S Pro
		Head A: female connector, M12, 8-pin, straight Head B: cable Cable: suitable for drag chain, PVC, shielded, 4 x 2 x 0.25 mm², Ø 7.0 mm	2 m	DOL-1208-G02MAC1	6032866	•
	→ K-725		5 m	DOL-1208-G05MAC1	6032867	•
	→ N-125		10 m	DOL-1208-G10MAC1	6032868	•
			20 m	DOL-1208-G20MAC1	6032869	•
	→ K-725	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, PUR, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 1 x 0.14 mm², Ø 7.8 mm¹)	2 m	DOL-2312-G02MLA3	2030682	•
			7 m	DOL-2312-G07MLA3	2030685	•
_			10 m	DOL-2312-G10MLA3	2030688	•
			15 m	DOL-2312-G15MLA3	2030692	•
			20 m	DOL-2312-G20MLA3	2030695	•
			25 m	DOL-2312-G25MLA3	2030699	•
			30 m	DOL-2312-G30MLA3	2030702	•
	→ K-725	Head A: female connector, M23, 12-pin, straight Head B: cable Cable: incremental, suitable for drag chain, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.8 mm $^{1)}$	1.5 m	DOL-2312-G1M5MA3	2029212	•
			3 m	DOL-2312-G03MMA3	2029213	•
			5 m	DOL-2312-G05MMA3	2029214	•
			10 m	DOL-2312-G10MMA3	2029215	•
			20 m	DOL-2312-G20MMA3	2029216	•
			30 m	DOL-2312-G30MMA3	2029217	•

#### Female connectors (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DFS60S Pro
	→ K-726	Head A: female connector, M12, 8-pin, straight, A coded, incremental, SSI, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: -40 °C +85 °C	DOS-1208-GA01	6045001	•
	→ K-726	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057	•



# Cables (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	DFS60S Pro
	-	Head A: cable Head B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, $4\times2\times0.15$ mm², Ø 5.6 mm		LTG-2308-MWENC	6027529	•
<b>\</b>		Head A: cable Head B: cable Cable: SSI, PUR, shielded, $4 \times 2 \times 0.25 \text{ mm}^2 + 2 \times 0.5 \text{ mm}^2 + 1 \times 0.14 \text{ mm}^2$ , Ø 7.5 mm		LTG-2411-MW	6027530	•
		Head A: cable Head B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm	By the meter	LTG-2512-MW	6027531	•
<u></u>		Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516	•

# Male connector (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	DFS60S Pro
	→ K-727	Head A: male connector, M12, 8-pin, straight, A coded, incremental, shielded, for cable diameter 4 mm 8 mm Head B: - Operating temperature: -40 °C +85 °C	STE-1208-GA01	6044892	•
	→ K-727	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature: -40 °C +125 °C	STE-2312-G01	2077273	•



# Wire draw encoders

# Mounting systems

Flanges

Flange plate

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	EcoLine	Compact	HighLine
	→ K-758	Flange adapter for EcoLine wire draw mechanisms, adaption of face mount flange with centering hub 20 mm to 50 mm servo flange	BEF-FA-020-050-007	2073774	•	-	-
3	→ K-759	Flange adapter for HighLine wire draw mechanisms, adaption of face mount flange with centering hub 20 mm to 50 mm servo flange	BEF-FA-020-050WDE	2073776	-	_	•

# Other mounting accessories

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	EcoLine	Compact	HighLine
	-	Joint ball for insertion in wire end ring with 20 mm diameter	Joint ball for BTF/ PRF/MRA wire draw	5318683	•	-	•
<b>3-0</b>	-	Additional brush attachment for wire draw mechanism MRA-F080 (2 m and 3 m from the HighLine series)	MRA-F080-B	6045341	-	-	•
1	-	Wire draw deflection pulley for wire draw mechanism MRA-F080 (2 m and 3 m from HighLine series)	MRA-F080-R	6028632	-	-	•
	-	Additional brush attachment for wire draw mechanism MRA-F130 (5 m, 10 m, 20 m and 30 m from HighLine series)	MRA-F130-B	6038562	-	-	•
	-	Wire draw deflection pulley for wire draw mechanism MRA-F130 (5 m, 10 m, 20 m and 30 m from HighLine series)	MRA-F130-R	6028631	-	-	•

#### Wire draw mechanism

Wire draw mechanism for face mount flange encoder

Figure	Dimen- sional drawing, see page	Brief description	Mea- suring length	Туре	Part no.	EcoLine	Compact	HighLine
	→ K-761		2.0 m	MRA-F080-402D2	6029788	-	-	•
	→ K-763		5.0 m	MRA-F130-405D2	6029789	-	-	•
1	→ K-763	Trigitative wife draw mechanism for oo series race	10.0 m	MRA-F130-410D2	6029790	-	-	•
	→ K-764		20.0 m	MRA-F130-420D1	6029791	-	-	•
	→ K-764		30.0 m	MRA-F130-430D1	6029792	-	-	•
	→ K-765		50.0 m	MRA-F190-450D2	6029793	-	-	•



# Wire draw mechanism for servo flange encoder

Figure	Dimen- sional drawing, see page	Brief description	Mea- suring length	Туре	Part no.	EcoLine	Compact	HighLine
	→ K-760		2.0 m	MRA-F080-102D2	6028625	-	-	•
	→ K-760		3.0 m	MRA-F080-103D2	6030125	-	-	•
Q	→ K-761	HighLine wire draw mechanism for 60 series servo	5.0 m	MRA-F130-105D2	6028626	-	-	•
	→ K-762	flange	10.0 m	MRA-F130-110D2	6028627	-	-	•
	→ K-762	With 6 mm shaft	20.0 m	MRA-F130-120D1	6028628	-	-	•
	→ K-763		30.0 m	MRA-F130-130D1	6028629	-	-	•
	→ K-765		50.0 m	MRA-F190-150D2	6028630	-	-	•
	→ K-766	Ecoline wire draw mechanism for 36 series servo flange With 6 mm shaft	1.25 m	MRA-G055-101D4	5324019	•	-	-
	→ K-766		3.0 m	MRA-G080-103D3	5322778	•	-	-
200	→ K-767	Ecoline wire draw mechanism for 60 series servo flange With 6 mm shaft	5.0 m	MRA-G130-105D3	5322779	•	-	_
	→ K-768		10.0 m	MRA-G190-110D3	5326242	•	-	-

# Connectivity

Please check the accessories for the encoder in question for information on compatible connectors.

# Additional accessories

# Spare parts

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	EcoLine	Compact	HighLine
@ Q Q Q III	-	Spare mounting set for MRA-G190 (10 m EcoLine)	BEF-MK-MRA-G01	5326294	•	-	-
	-	Spare mounting set for HighLine wire draw mechanisms for fitting encoders with servo flange	MRA-F-K	6028633	-	-	•
	-	Spare mounting set for HighLine wire draw mechanisms for attaching encoders with a face mount flange	MRA-F-L	6030124	-	-	•

#### Programming and configuration tools

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	EcoLine	Compact	HighLine
	-	Programming unit USB, for programmable SICK encoders AFS60, AFM60, DFS60, VFS60, DFV60 and wire draw encoders with programmable encoders.	PGT-08-S	1036616	1)	-	1)
V m. m.A	-	Programming unit display for programmable SICK DFS60, VFS60, DFV60, AFS/AFM60, AHS/AHM36 encoders, and wire draw encoders with DFS60, AFS/AFM60, and AHS/AHM36. Compact dimensions, low weight, and intuitive operation.	PGT-10-Pro	1072254	•	-	•

<sup>1)</sup> Can be used with programmable incremental and absolute encoders in conjunction with the corresponding adapter cables.



# Linear encoders

# Mounting systems

Mounting brackets and plates

Mounting bracket

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	KH53	ПК70
	→ K-737	Mounting bracket for KH53 measuring elements, without mounting hardware for the base	BEF-WK-KHT53	2029159	•	-

# Clamp and alignment brackets

# Clamping brackets

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	KH53	TTK70
	→ K-737	Spacer for KH53 measuring elements, without mounting hardware for the base	BEF-KHA-KHT53	2042468	•	-

# Connectivity

Plug connectors and cables

Connecting cables with female connector

Figure	Dimen- sional	Brief description	Length of	Туре	Part no.		
	drawing, see page		cable			KH53	ТТК70
	→ K-728	Head A: M12 female connector, 4-pin, straight Head B: cable Cable: for power supply, suitable for drag chain, PVC, unshielded, 4 x 0.25 mm², Ø 5.0 mm	5 m	DOL-1204-G05M	6009866	•	-
			5 m	DOL-1205-G05MQ	6026006	•	-
		Head A: female connector, M12, 5-pin, straight Head B: cable Cable: suitable for drag chain, PROFIBUS DP, PUR, halo- gen-free, shielded, 2 x 0.34 mm², Ø 8.0 mm	10 m	DOL-1205-G10MQ	6026008	•	-
			12 m	DOL-1205-G12MQ	6032636	•	-
	→ K-729		15 m	DOL-1205-G15MQ	6032637	•	-
-			20 m	DOL-1205-G20MQ	6032638	•	-
			30 m	DOL-1205-G30MQ	6032639	•	-
			50 m	DOL-1205-G50MQ	6032861	•	-
		Head A: female connector, M23, 12-pin, straight	1.5 m	DOL-2312-G1M5MA1	2029200	•	-
			3 m	DOL-2312-G03MMA1	2029201	•	-
	→ K-730	Head B: cable Cable: SSI, RS-422, suitable for drag chain, PUR, shield-	5 m	DOL-2312-G05MMA1	2029202	•	-
	711-750	ed, 4 x 2 x 0.25 mm <sup>2</sup> + 2 x 0.5 mm <sup>2</sup> + 2 x 0.14 mm <sup>2</sup> ,	10 m	DOL-2312-G10MMA1	2029203	•	-
		Ø 7.8 mm	20 m	DOL-2312-G20MMA1	2029204	•	-
			30 m	DOL-2312-G30MMA1	2029205	•	-
		Head A: female connector, M12, 12-pin, straight	2 m	DOL-1212-G02MAC1	6053273	-	•
	_	Head B: cable Cable: SSI, PUR, shielded, 12 x 0.14 mm <sup>2</sup> , Ø 8.5 mm	5 m	DOL-1212-G05MAC1	6053274	-	•
			10 m	DOL-1212-G10MAC1	6053275	-	•
	Suitable for use with drag chains	20 m	DOL-1212-G20MAC1	6053276	-	•	



Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	KH53	ТТК70
		Head A: female connector, M12, 12-pin, angled Head B: cable	2 m	DOL-1212-W02MAC1	6039824	-	•
	→ K-736		5 m	DOL-1212-W05MAC1	6039825	-	•
	→ N-736	Cable: SSI, PUR, shielded, 12 x 0.14 mm <sup>2</sup> , Ø 8.5 mm	10 m	DOL-1212-W10MAC1	6039826	-	•
		Suitable for use with drag chains	20 m	DOL-1212-W20MAC1	6039827	-	•

# Connecting cables with male connector

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	KH53	ТТК70
		, , , , , , , , , , , , , , , , , , , ,	5 m	STL-1205-G05MQ	6026005	•	-
	→ K-736		10 m	STL-1205-G10MQ	6026007	•	-
		gen-free, shielded, 2 x 0.34 mm <sup>2</sup> , Ø 8.0 mm Wire shielding: AL-PT foil, total shield, tin-plated C shield	12 m	STL-1205-G12MQ	6032635	•	-

# Female connectors (ready to assemble)

Figure	Dimen- sional	Brief description	Туре	Part no.		
	drawing, see page				KH53	TTK70
	→ K-731	Head A: M12 female connector, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -	DOS-1204-G	6007302	•	-
	→ K-731	Head A: M12 female connector, 5-pin, straight, B coded, PROFIB-US DP, shielded, for cable diameter 4 mm 9 mm Head B: -	DOS-1205-GQ	6021353	•	-
	→ K-726	Head A: female connector, M23, 12-pin, straight, HIPERFACE®, SSI, incremental, shielded, for cable diameter 5.5 mm 10.5 mm Head B:  Operating temperature: -20 °C +130 °C	DOS-2312-G	6027538	•	-
	→ K-726	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm  Head B: -  Operating temperature:  -40 °C +125 °C	DOS-2312-G02	2077057	•	-
(HEO)	→ K-727	Head A: M23 female connector, 12-pin, angled, HIPERFACE®, SSI, incremental, shielded, for cable diameter 4.2 mm 6.6 mm Head B:  Operating temperature: -20 °C +130 °C	DOS-2312-W01	2072580	•	-



# Cables (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Length of cable	Туре	Part no.	KH53	TTK70
		Head A: cable Head B: cable Cable: PROFIBUS DP, suitable for drag chain, PUR, shielded, 2 x 0.25 mm², Ø 8.0 mm		LTG-2102-MW	6021355	•	-
	-	Head A: cable Head B: cable Cable: SSI, suitable for drag chain, PUR, halogen-free, shielded, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm	By the meter	LTG-2512-MW	6027531	•	-
<u></u>		Head A: cable Head B: cable Cable: suitable for drag chain, PUR, halogen-free, shielded, UV and saltwater resistant, 4 x 2 x 0.25 mm² + 2 x 0.5 mm² + 2 x 0.14 mm², Ø 7.8 mm		LTG-2612-MW	6028516	•	-

# Other plug connectors and cables

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	KH53	ТТК70
	→ K-735	Head A: M12 male connector, 4-pin, straight, B coded Cable: PROFIBUS DP, terminator	STE-END-Q	6021156	•	-

# Male connector (ready to assemble)

Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	KH53	TTK70
	→ K-734	Head A: M12 male connector, 5-pin, straight, B coded, PROFIBUS DP, shielded, for cable diameter 4 mm 9 mm Head B: -	STE-1205-GQ	6021354	•	_
Par	→ K-727	Head A: M23 male connector, 12-pin, straight, HIPERFACE®, SSI, incremental, RS-422, shielded, for cable diameter 5.5 mm 10.5 mm  Head B:  Operating temperature: -20 °C +130 °C	STE-2312-G	6027537	•	-
	→ K-727	Head A: male connector, M23, 12-pin, straight, for cable diameter 5.5 mm 10.5 mm Head B: - Operating temperature: $-40~^{\circ}\text{C}~~+125~^{\circ}\text{C}$	STE-2312-G01	2077273	•	-

# Additional accessories

# Programming and configuration tools


Figure	Dimen- sional drawing, see page	Brief description	Туре	Part no.	KH53	ПК70
	-	Programming tool for ATM60, ATM90 and KH53 SSI	PGT-01-S	1030111	•	-




# Dimensional drawings (dimensions in mm)

# Dimensional drawings for connection systems


#### DOL-0J08-GxxxAAx




#### DOL-1208-GxxMAC1



#### DOL-2312-GxxMLA3







- ① Black
- ② Gray
- 3 Purple
- 4 Yellow
  5 White
- 6 Brown
- 8 Pink
- 9 Shield
- 10 Blue
- ① Green


#### Red


#### DOL-2312-GxxMLD1





# DOL-2312-GxxxMA3






- ① Black
- ② Gray
- 3 Purple
- 4 Yellow5 White
- 6 Brown
- 7 Orange
- Pink
- Shield
- 10 Blue 11 Green
- 12 Red

- ① Black
- ② Gray
- 3 Purple
- 4 Yellow
- S White
- 6 Brown
- 8 Pink
- 9 Shield
- 10 Blue
- ① Green ② Red




# **Dimensional drawings** ACCESSORIES

#### DOL-2312-GxxxMD1




#### DOS-1208-GA

11




- ① Black
- ② Gray
- 3 Purple
- 4 Yellow
- ⑤ White
- 6 Brown
- ⑦ Orange
- 8 Pink
- 9 Shield
- 10 Blue
- ① Green
- 2 Red


#### DOS-1208-GA01



#### DOS-2312-G





# DOS-2312-G02





#### DOS-2312-W01





#### **Main dimensions**


Plug




#### **Contact arrangement**


Mating view

# STE-2312-G






#### STE-1208-GA01




# STE-2312-G01





Pin insert 12 pin (plug-in face)


#### STL-2312-GxxxAA3







# **Dimensional drawings** ACCESSORIES


#### AD-ATM60-KA3PR AD-ATM60-KRxC0










AD-ATM60-KRxDN AD-ATM60-SR3PR










AD-ATM60-SR1CO AD-ATM60-SRxDN










AD-ATM60-SR2CO








DOL-1202-W05MC







DOL-1204-G05M



#### DOL-1204-GxxMC




#### DOL-1204-WxxMC






#### DOL-1205-GxxMY




female contact M12 x1, straight, shielded

- ① Shield wire
- ② Red
- 3 Black
- White
- 3 Blue

#### DOL-1205-GxxMAC




#### DOL-1205-WxxxACSCO



female connector M 12 x 1, angled, screened

- ① Brown
- 2 White
- 3 Blue
- Black
   Gray


#### DOL-1205-GXXXACSCO




female connector M12 x1, straight, screened

- ① Brown
- ② White
- 3 Blue
- 4 Black
- ⑤ Gray

#### DOL-1205-GxxMQ



#### DOL-1205-WxxMQ





- ② Green
- 4 Red

K-729


# **Dimensional drawings ACCESSORIES**


#### DOL-2308-GxxxAA6





#### DOL-2312-GxxxMD2







- ① Blue
- 2 White
- 3 Yellow
- 8 Red
- 9 Pink
- 10 Brown
- 1 Purple
- 2 Black

- ① Red
- 2 Blue
- 3 Yellow
- 4 White
- ⑤ Orange
- 6 Brown
- 7 Purple
- 8 Black 9 Orange/black
- 10 Green
- ① Gray
- 2 Pink


#### DOL-2312-GxxxMA1







- ① Blue
- ② White
- 3 Yellow
- 4 Gray
- 3 Green
- 6 Pink 7 Black
- 8 Red
- 9 Orange
- 10 Brown
- 1 Purple
- 2 Orange/black


#### DOL-2312-GxxxMA2














⑤ Pink 8 Red


② White 3 Yellow

- 9 Orange
- 10 Brown
- 1 Purple


#### DOS-1204-G




#### DOS-1204-W



#### DOS-1205-G DOS-1205-GA




#### DOS-1205-WQ







#### DOS-1204-Gx




#### DOS-1204-Wx



#### DOS-1205-GQ




# DOS-1507-G DSC-1507-G STE-1507-G





# DOS-2321-G DOL-2321-GxxxPA4



Pin color assignment (applies to all DOL-2321-GxxxPA4)

- ① Violet
- 2 White/brown
- 2 Brown/gray ® Brown/pink
- 3 White/green

- 4 White/yellow
- 14 Brown/blue

(5) Brown/red

⑤ White/gray

16 Green

6 White/pink

7 Pink

7 White/blue


**18** Yellow

8 White/red

- 19 Brown
- White/black


- 10 Brown/green
- 20 Blue
- 1 Brown/yellow
- 2 Red

#### DSL-1205-GxxMY



- ① Shield wire
- ② Red
- 3 Black
- 4 White
- 3 Blue


#### DSL-1205-G06MK






#### Feedthrough female connector Ethernet RJ45







SSL-1204-FxxMZ90 SSL-1204-HxxME90




SSL-1204-GxxME90 SSL-1204-GxxMZ90



SSL-2J04-GxxME60




SSL-2J04-FxxMZ







#### SSL-2J04-HxxME




# STE-0J04-GZ STE-0J08-GE









STE-1204-WE STE-1204-WZ







#### STE-1205-G




#### STE-1205-GA



#### STE-1205-GKEND




#### STE-1205-GQ






#### STE-1205-WQ






#### STE-END-Q




#### STL-1204-GxxME90




- ① White-orange
- ② White-green
- ③ Orange
- 4 Green

#### STL-1204-WxxME90




- ① White-orange
- ② White-green
- 3 Orange
- 4 Green

#### STL-1204-GxxMZ90



- ① Yellow
- ② White
- 3 Orange
- 4 Blue

#### STL-1204-WxxMZ90




- ① Yellow
- ② White
- 3 Orange
- 4 Blue




K-735

# **Dimensional drawings** ACCESSORIES

#### STL-1205-GxxMQ




#### STL-1205-WxxMQ




- ② Green
- 4 Red

#### DOL-1212-WxxMAC1



#### DOL-2312-GxxMLA5




- ① Blue
- ② White
- 3 Yellow
- 8 Red
- 9 Orange10 Brown
- 1 Purple
- 12 Black




# Dimensional drawings for mounting systems

# BEF-KHA-KHT53





#### BEF-WK-KHT53






# BEF-DS-09











#### BEF-DS-10




#### BEF-DS-11






BEF-DS-12









37.6.


# BEF-DS02DFS/VFS







#### BEF-DS03DFS/VFS







#### BEF-DS05XFX










# BEF-DS07XFX






# BEF-DS-DBS36








#### BEF-FA-020-033




#### BEF-FA-025-050


General tolerances according to ISO 2768-mk



# BEF-FA-025-060RSA


General tolerances according to ISO 2768-mk






#### BEF-FA-025-036

General tolerances according to ISO 2768-mk




#### BEF-FA-025-060RCA

General tolerances according to ISO 2768-mk




# BEF-FA-025-063-REC

General tolerances according to ISO 2768-mk







#### BEF-FA-B12-010



#### BEF-FA-LB1210









K-745


#### BEF-MG-50



# BEF-MR-010020 BEF-MR-010020G



#### BEF-MR-010050







#### BEF-MR0xx020R

# 17 (0.67) 8 (0.31) M5 LHX W 4 (0.16)


# BEF-MR0xx030R




# BEF-MR0xx050R




#### BEF-MRS-08-1









# BEF-MRS-08-2






#### BEF-WF-20






#### BEF-WF-25




BEF-WF-30






K-749

# BEF-WF-36




SPZ-58Z-006-P, SPZ-58Z-008-P, SPZ-58Z-010-P, SPZ-58Z-012-P, SPZ-58Z-12Z-P, SPZ-58Z-38Z-P



Ø D F8	ArtNo.
6	2076228
8	2076229
3/8" (9.525)	2076226
10	2076230
12	2076231
1/2" (12.7)	2076227




# SPZ-58Z-008-M, SPZ-58Z-010-M, SPZ-58Z-012-M, SPZ-58Z-014-M, SPZ-58Z-12Z-M, SPZ-58Z-38Z-M



Ø D F7	ArtNo.
8	2076219
3/8" (9.525)	2076224
10	2076220
12	2076221
1/2" (12.7)	2076225
14	2076222


#### SPZ-58Z-014-P SPZ-58Z-015-P






K-751

# SPZ-58Z-015-M




# BEF-DS00XFX






#### BEF-DS01DFS/VFS





BEF-FA-036-050 BEF-FA-036-100






#### BEF-FA-036-050-019







#### BEF-FA-036-060REC



#### BEF-FA-036-060RSA



#### BEF-FA-036-063REC







#### BEF-WG-SF050


# 


#### BEF-WK-SF







# Dimensional drawings for shaft adaptation $\mbox{\scriptsize KUP-0606-Bx}$






#### KUP-0610-Bx









#### KUP-1010-Bx






#### BEF-WK-RESOL




#### KUP-xxxx-B








KUP-0606-S KUP-0610-S KUP-0610-MS KUP-1010-S




KUP-0608-S KUP-0808-S KUP-0810-S














#### KUP-xxxx-F




#### PEEK conductor insulation, 8 x 10 mm




PEEK conductor insulation, 11 x 12.7 mm



#### PEEK conductor insulation, 12 x 14 mm




PEEK conductor insulation, 12.7 x 15 mm






#### PEEK conductor insulation, 10 x 12 mm




#### SPZ-005-AD-A

1 (0.04)




#### SPZ-006-DD36-A




#### BEF-FA-020-050007

Ø 5 F7

Ø 8 h7




Ø 6.5 (3x) (0.26)





#### BEF-FA-020-050WDE







K-759


### Dimensional drawings for additional accessories


#### MRA-F080-102D2






#### MRA-F080-103D2










#### MRA-F080-402D2






#### MRA-F130-105D2










#### MRA-F130-110D2






#### MRA-F130-120D1










#### MRA-F130-130D1







#### MRA-F130-405D2






#### MRA-F130-410D2









#### MRA-F130-420D1






#### MRA-F130-430D1






#### MRA-F190-150D2





#### MRA-F190-450D2







#### MRA-G055-101D4






#### MRA-G080-103D3









#### MRA-G130-105D3








#### MRA-G190-110D3










# Dimensional drawings for other mounting accessories


### BEF-MRS-10-1






#### BEF-MRS-10-2










#### BEF-DS08









#### BEF-FA-020-024








#### BEF-FA-020-030





#### BEF-FA-020-036







#### BEF-FA-020-036-002













#### BEF-FA-020-050













# SPZ-006-AD-A, SPZ-008-AD-A, SPZ-010-AD-A, SPZ-012-AD-A, SPZ-1E2-AD-A, SPZ-1E4-AD-A, SPZ-3E8-AD-A

# 1 (0.04) (0.04) (0.04) (0.04) (0.59) h7

#### SPZ-xxx-AD-D



#### SPZ-014-AD-A





L-774 ENCODERS | SICK



#### Absolute encoders

Absolute encoders generate information about position, angle and rotation counts in type-specific angle steps. For this, a unique code pattern is assigned to each angle increment. The number of code patterns available per revolution determines the resolution. Each code pattern forms a unique reference, and is therefore absolute position information. There is therefore no need for a reference run after switching on. A singleturn encoder measures the absolute position within a revolution but also the number of revolutions.

#### Analog signal - Sin/Cos connection

In signaling theory, an analog signal is an infinite, continuous signal. An analog signal is described as smooth. Outputs depend on the type of device.

- Absolute encoders: a current signal of 4 to 20 mA or a voltage signal of 0 to 10 Volt.
- Incremental encoders: sine-cosine signal
- → Sine-cosine interface on page L-784




#### Baud rate

Gives the signal rate and hence the speed of serial data transfer in bits per second.

#### Bend radius

In cabling terms, the bend radius relates to the smallest curve radius a cable may have when installed, without the cable properties being altered. The bend radius is given in relation to the cable diameter.



#### Binary code

Type of code used to output information on the absolute position.

#### Bus system

A system for transferring data between multiple devices over a common cable. A bus system makes it possible to control all sensors and actuators centrally. Additional information such as process data, service data and diagnostics data can also be exchanged.

Well known examples are:

DeviceNet, PROFIBUS, CANopen, PROFINET, EtherNet/IP, EtherCAT®.

Additional information on bus systems can be found in this glossary under the CANopen, DeviceNet, EtherCAT®, EtherNet/IP, PROFIBUS and PROFINET entries.



#### **CANopen**

CANopen: is a communication protocol based on CAN.
User organization: CiA (CAN in Automation)
More detailed information about this technology is available at:

→ www.can-cia.org



#### Channel

Signal path upon which a signal is output.

#### Code disk

→ Scanning, optical on page L-782

#### Code type

Unique encoding of the measured values according to a defined scheme at the encoder output. In practice, different codes are used for different electrical interfaces, e.g., SSI interface with Gray code.

#### Coefficient of thermal expansion

This describes the behavior of a material in relation to changes of its dimensions as influenced by changes in temperature.

#### Cycle

Service life on page L-783





#### DC (diagnostic coverage)

#### Safety characteristic

Measure of the effectiveness of the diagnostics that can be determined as the ratio of the failure rate of detected dangerous failures to the failure rate of all dangerous failures.

→ See "Guide for Safe Machinery" (8008007)

#### **DeviceNet**

DeviceNet is a CAN based communication protocol.

User organization: ODVA

More detailed information about this technology is available at:

→ www.odva.org



#### Diagnostic functions

Absolute encoders with diagnostic functions provide diagnostic data in addition to standard encoder data (e.g., position). This includes information like the minimum and maximum temperature, an operating hour counter, a counter for changes in direction, and lots more. The diagnostic functions are available in most absolute and wire draw encoders with fieldbus or Ethernet-base fieldbus interfaces.

#### Differential evaluation


Evaluation of signals of an output stage for which the inverted signals are also output. The 1/0 level, or sine/cosine signals are transferred in the form of voltage differences between two cables. In this way, the signal used (the difference) remains uncorrupted as interference normally affects both cables equally.

#### Drum circumference

The resolution in mm of a wire draw encoder can be determined using the circumference of the bobbin and the resolution of the rotary encoder (e.g. 12 bits per revolution).

#### Duty cycle/pulse-pause ration

Errors related to rising to falling signal edges from a squarewave signal will affect the encoder's jitter.





#### **EMC**

Electromagnetic compatibility (EMC) means that technical equipment should not be affected by electromagnetic interference. This is achieved both by limiting sources of interference in devices and by devices being designed to be sufficiently resistant to interference. EMC is regulated by EU Directives and Standards.

#### **Enclosure rating**

The enclosure rating indicates the degree of protection of a machine or sensor against contact and penetration by impurities and water. The enclosure ratings begin with the letters IP, followed by the first digit, which indicates the degree of protection provided against touch and impurities. The second digit describes the protection against penetration by water.

#### **Encoders**

Encoders are sensors for monitoring position, angle and speed. Essentially, encoders can be categorized as rotary or linear. Rotary encoders are sub-divided into incremental and absolute encoders. Linear encoders are further sub-divided into wire draw encoders and non-contact linear encoders.

#### **Error limits**

The error limit is the largest positive or negative deviation of any angle position (absolute) or of a measured angle (incremental) from the true value.

#### EtherCAT®

EtherCAT® is an Ethernet based fieldbus. User organization: EtherCAT® Technology Group More detailed information about this technology is available at:

→ www.ethercat.org



#### EtherNet/IP

EtherNet/IP is an Ethernet based fieldbus.

User organization: ODVA

More detailed information about this technology is available at:

→ www.odva.org





#### **Fieldbus**

Bus system in the process area for direct connection of sensors and actuators that have their own intelligence. Data in digital form is transferred between sensors, actuators and control devices via a fieldbus. This transfer must be as rapid as possible, i.e., in real time. For this, a fixed minimum and maximum response time must be guaranteed.

#### Flange

Part of the encoder for fixing to the customer installation interface. There are various mechanical designs available, for example:



Left: Face mount flange; Right: Servo flange.



Left: blind hollow shaft; Right: Through hollow shaft.

#### Flange adapter

Mechanical adapter for ensuring that an encoder flange is mechanically compatible with the customer's mechanical interface.







Left = Flange adapter for a 36 series face mount flange to a servo flange; Center = Flange adapter for a 20 series face mount flange to a 36 series face mount flange; Right = Special flange adapter.

## G

#### Gray code

Constant code that is also used with the SSI interface. When one value is changed for the next one, the data bit changed is the specific one that will allow data transfer to take place reliably.

#### Gray excess code

If a suitable section is extracted for encoder resolution from the middle of the complete Gray code, this results in the "Gray Excess Code" (capped Gray code). The use of this Gray excess code allows only a single data bit to be altered even when the encoder crosses zero, although the number of steps is not  $2^n$  where n is a whole number.



#### Halogen-free (connectivity)

Cables and wiring are said to be halogen-free if the materials used do not contain salt forming chlorine, fluorine, bromine or iodine. The insulation and sheath materials of these cables consist of polymers based on pure hydrocarbons. When such materials are burned, no corrosive or toxic gases are produced, but only water vapor and carbon dioxide.

#### HIPERFACE®

High Performance Interface (HIPERFACE®) is a hybrid interface developed by SICK that can transfer analog speed values and digital position values. Electrical compatibility is guaranteed by the use of HIPERFACE® as the obligatory interface for all physical parameters.

The advantages of HIPERFACE® are that only one interface is required on the speed regulator for all applications, only one type of signal cabling is needed between the speed regulator and the signal encoder and manual configuration of the speed sensor is not necessary.



#### HIPERFACE DSL®

The High Performance Interface DSL is a pure **D**igital **S**ervo **L**ink interface developed by SICK that provides new servo drive system architecture for HIPERFACE® with a completely new range of options as it is not hybrid (analog/digital), but is completely digital.

Thanks to the innovative and interference-free HIPERFACE DSL® protocol, rugged and reliable communication can be achieved using just two wires that are integrated into the motor cable. In addition, the digital protocol requires a minimum of connection cables between the frequency inverter and the motor feedback system.

The absence of motor feedback connections achieves significant cost savings and distinctly increased performance.



#### HTL Push Pull

High Voltage Transistor Logic functions with a voltage supply in the range 10 and 30 V DC, with 24 V DC being the most common. "Low" is defined as an output of between 0 VDC ... 3 VDC and "high" as between (Us - 3.5 VDC) ... Us.

#### Hysteresis

Hysteresis is defined as the maximum spread of several consecutive positioning processes taken for one point from several different directions under identical conditions.

#### Incremental encoders

Incremental encoders generate information about position, angle and rotation counts. The number of lines per revolution determines the number of impulses that the encoder transmits to the control unit for each revolution. The current position can be determined by the control unit by counting these impulses from a reference point. When the machine is switched on, a reference run to the reference point is required to determine the actual position of the encoder.

#### Initialization time

Amount of time following the supply voltage being connected and the encoder outputting a valid signal.

#### Interface, electrical

Connection point between two devices or systems. The devices or systems on either side of an interface are connected to each other by interface cabling over which data, addresses and control signals are exchanged. The term interface embraces the complete functional, electrical and constructive conditions that make up the point of contact between the devices or systems. Depending on the type of data transfer, a distinction must be made between parallel (e.g., Centronics, IEEE 488) and serial interfaces (e.g., RS-422, RS-423, RS-485) that are designed for differing transfer speeds and distances.


#### Interface, mechanical

→ Flange on page L-777

#### Inverted signal

Reciprocal signal for the suppression of interference impulses when using differential sampling.

→ Differential evaluation on page L-776



 $A = Original signal; \bar{A} = Inverted signal.$ 


## J

#### **Jitter**

From the English verb "to jitter": flicker, tremble; time variation of the output signal resulting from constantly present tolerances.

#### Linear encoders

A linear encoder is used for frictionless length measurement and determining positions. A read head samples a code pattern or the magnetic field of a magnetic scale and outputs the appropriate electric signal.



Principle of operation

#### Linearity

The accuracy of wire draw encoders is described by the linearity. This indicates the maximum deviation for the measurement of a defined measurement distance. In contrast to repeatability, this relates to the measuring range covered and not to a positioning point.

#### Load current

Maximum amount of current permitted to flow through each channel of an incremental encoder.

### M

#### Material resistance, PUR

Flexible silicone and halogen-free cabling with PUR outer sheath: The oil and fire resistance requirements of VDE 0472 are fulfilled. Can be used in drag chain applications with a minimum bend radius. This cabling is most suitable for flexible use in robot technology, for machine tools, as well as for machining production.

#### Material resistance, PVC

Pure PVC cables, suitable for medium mechanical strain in packaging machines as well as for assembly and production lines: good resistance to acids and alkalis and hence ideal for use in the food and beverage industries. Resistance to wear as well as oil and chemical resistance is limited.


#### Maximum output frequency

The maximum encoder output signal frequency, for which the correct sequence of the code values is assured is called the maximum output frequency.

The formula used is as follows:

#### Measurement increment deviation

The measurement increment deviation indicates the maximum measurement deviation from measurement increment to measurement increment. For this, measured values are taken at one or more adjacent positions in the test range and their maximum deviation from the desired value determined.



#### Measurement step

There is a differentiation here between the measurement step for absolute and incremental measurement systems.

#### Incremental measurement systems:

In this case, the measurement step represents the period of the output signal. Here, the number of periods is the same as the number of graduations per revolution on the measurement scale, or a multiple thereof.

#### Absolute measurement systems:

In this case the measurement step is the smallest possible angular movement of the rotor that will produce a change in the output signal.

#### Measuring element

To determine a position, linear encoders require measuring elements that are installed along the entire length of the measurement path. The code pattern is formed by various magnet properties that are scanned by magnetic sensors in the read head



#### Measuring range

The range within which a rotary or linear encoder can produce a valid measurement signal.

#### Measuring wheel

Mechanical assembly that enables rotary encoders to record linear movements. If you wish to use a measuring wheel, you can either use a full measuring wheel system, like the DFV60, or a rotary encoder with a separate measuring wheel accessory.



Complete measuring wheel system.



Left = Measuring wheel with O-Ring surface; Right = Measuring wheel with ribbed plastic surface.

#### MTTFd value (mean time to failure)

#### Safety characteristic

Expected value for the mean time to dangerous failure (ISO 13849-1/EN ISO 13849-1).

→ See "Guide for Safe Machinery" (8008007)

#### Multiple sampling

Increasing the number of impulses for an incremental encoder following evaluation by the customer.

#### Individual sampling

Evaluation of rising signal edges of an encoder channel (A or B).

#### **Dual sampling**

Evaluation of rising and falling signal edges of an encoder channel (A or B).

#### Quadruple sampling

Evaluation of rising and falling signal edges of both encoder channels (A and B).

#### Multiturn (MT)

A type of absolute encoder that in addition to the angular position of the shaft (singleturn) can also definitively determine and output the number of shaft rotations (multiturn).



Example: Magnetic multiturn with gearing.

### N

#### NPN output (Open Collector)


NPN output is an interface based on an output circuit with NPN transistor.



## 0

#### Offset

The difference between the actual physical value and the preset value is described as the offset. This can be both a position offset for position measurement, as well as a voltage offset.



#### **Open Collector**

An open collector is the unconnected collector connection of a transistor, whose emitter is connected to earth and whose collector is connected to the output.

Signals can be output using NPN or PNP transistors.

→ NPN output (Open Collector) on page L-780

→ PNP output (Open Collector) on page L-781

#### Operating torque

The torque required to move a shaft at a constant speed.



#### PFHd (probability of dangerous failure per hour)

#### Safety characteristic

Mean probability of a dangerous failure per hour (1/h).

→ See "Guide for Safe Machinery" (8008007)

#### PL (performance level)

#### Safety characteristic

Discrete level used to specify the ability of the safety-related parts of a control system to perform a safety function under foreseeable conditions (ISO 13849-1/EN ISO 13849-1).

→ See "Guide for Safe Machinery" (8008007)

#### PNP output (Open Collector)

The PNP output is an interface based on an output circuit with a PNP transistor.



### Position forming time

The amount of time following detection of an absolute position until the next absolute position can be detected by the absolute encoder.

#### Preset

For absolute encoders, a preset value can be allocated to the actual physical position value. In the case of an allocation via the set cabling, this equates to the value 0. For programmable absolute encoders, the preset value can be any value within the measuring range.

#### **PROFIBUS**

PROFIBUS is a fieldbus for industrial communications. User organization: PNO (PROFIBUS Nutzerorganisation e.V.) More detailed information about this technology is available at:

→ www.profibus.com



#### PROFINET (Process Field Network)

PROFINET is an Ethernet based fieldbus.

User organization: PNO (PROFIBUS Nutzerorganisation e.V.) More detailed information about this technology is available at:

→ www.profibus.com



#### Programming options for encoders

Many SICK encoders can be programmed by the customer. This means that customers can modify the encoder's parameters to better suit the application in question. The following options are available for programming:

- Hand-held programming tool (for incremental and SSI absolute encoders)
- PC-based programming tool (for incremental and SSI absolute encoders)
- Web-server-based programming (absolute encoders with an EtherNet/IP interface)
- Programming options using the engineering software issued by the manufacturer of the control unit (fieldbus and Ethernet encoders)
- RS-485 programming option (for incremental and SSI absolute encoders)

#### Programming tool

Programming device for configuring encoders. Programming devices for encoders can be used for either incremental encoders or absolute SSI encoders. A variety of programming tools are available, for example the PGT-08-S PC-based programming tool or the PGT-10-P hand-held device.



#### Reference signal

→ Zero pulse on page L-786

#### Repeatability

→ Reproducibility on page L-782

#### Reproducibility

Reproducibility or repeatability is defined as the maximum spread of several consecutive positioning processes taken for one point from one direction under identical conditions.

#### Resolution

The resolution is expressed as the number of impulses/steps per revolution or path units.

Encoder type	Resolution definition
Rotary, incremental	Resolution as number of impulses
Rotary, absolute, singleturn	Resolution as number of steps per revolution
Rotary, absolute, multiturn	The total resolution consists of the number of steps per revolution and the number of revolutions
Linear encoders	Resolution in mm Special for cable pull:
	Circumference of cable drum  Resolution for one revolution of the encoder

If, for example a rotary incremental encoder has a resolution of 12 bits, this means the number of impulses is 4,096.

The formula for calculation is: Number of impulses =  $2^x$ , where x is the resolution in bits.

#### Rotary encoders

A type of encoder that records rotational movements. Rotary encoders are available as incremental encoders and as absolute encoders.

#### Rotation direction, clockwise (cw)

Rotation to the right, when viewing the shaft.

#### Rotation direction, counterclockwise (ccw)

Rotation to the left, when viewing the shaft.

#### Rotor moment of inertia

The moment of inertia that is generated by the rotor mass (made up of the shaft and other parts) in a rotary encoder.

#### RS-485

RS-485 or EIA-485 is an interface standard used for transmitting data. Various electrical interfaces, such as PROFIBUS, are based on the RS-485 standard. Programmable incremental and absolute SSI encoders by SICK can be programmed using RS-485 commands.



#### Safety encoders

SICK safety encoders are encoders for use in functional safety technology. They generate information about position, angle, and revolution counts. Rotary safety encoders are sub-divided into incremental and absolute encoders. When combined with safety controllers, safety encoders support the realization of safety functions. The encoders are certified safety products and are characterized by safety technology parameters such as safety integrity level (SIL) or performance level (PL).




#### Scaling

For programmable encoders, the encoder's actual value is multiplied by a scaling factor. This means that the resolution can be adapted to the application in question.

#### Scanning, magnetic

Position, angle and speed determination for rotary or linear encoders using permanent magnets and appropriate evaluation units to determine the magnetic field. Encoders with magnetic scanning are usually of lower resolution than optical ones.




#### Scanning, optical


Position, angle and speed determination for rotary or linear encoders using LEDs, code patterns and photo-diodes.

The graduation marks (for incremental encoders) or codes (for absolute encoders) are inscribed as digital patterns on a glass, metal or plastic disc and are sampled by a light source (light emitting diode) and photo-diodes.

Encoders with optical scanning are usually of higher resolution than magnetic ones.



1 LED; 2 Lens; 3 Reference point; 4 Code disc; 5 Mask; 6 Photo-diode.



Code discs: Left incremental, right absolute.

#### Service life

For rotary encoders, the service life of the bearings represents the overall service life of the encoder expressed in revolutions. For wire draw encoders, the service life is expressed as the total number of cycles. A cycle is defined as one withdrawal and rewind movement (load cycle).

The service life depends on the type of load. This is influenced by factors such as the environment, the installation location, the measuring range in use, the travel speed and acceleration. If the value of one or more of these influencing factors is in the high range, the service life may be reduced proportionally.

#### Shaft

The component of a rotary encoder that transfers the rotation movement and torque from the application to the sensor unit of the encoder.

#### Shaft coupling


A shaft coupling is for the indirect connection of two shafts to balance radial, axial or angular offset.



From left to right: spring washer coupling, bellows coupling, bar coupling, double-loop coupling.


#### Shaft load capacity, axial

The axial shaft load capability describes the load capacity along the axis of the encoder shaft.



#### Shaft load capacity, radial

The radial shaft load capability describes the load capacity about the radius along the encoder shaft. For this, the point of action must be applied to the end of the shaft.



# Shaft offset, static / shaft movement, dynamic, for hollow shafts

#### Static

Radial and/or axial shaft offset resulting from the tolerance of the customer's flange.

#### Dynamic

Radial and/or axial shaft offset resulting from concentricity errors and measurement changes caused by the temperature and/or clearance of the customer's shaft during operation.

#### Shield

The shielding of equipment or connecting cables is the design-dependent protection of equipment against radiated electromagnetic interference. Sensitivity to radiated electromagnetic interference, as well as the intensity of radiated electromagnetic interference, must be reduced by full shielding so that the encoder can by used properly. This should be extensive and all around.

#### SIL (Safety Integrity Level)

#### Safety characteristic

Discrete level (one out of a possible three) for specifying the safety integrity of the safety functions assigned to the safety-related system, where safety integrity level 3 has the highest level of safety integrity and safety integrity level 1 has the lowest (IEC 62061/EN 62061).

→ See "Guide for Safe Machinery" (8008007)

#### SILCL (SIL claim limit)

#### Safety characteristic

Safety integrity level claim limit (for a subsystem): Maximum SIL that can be claimed for an SRECS subsystem in relation to architectural constraints and systematic safety integrity (IEC 62061/EN 62061).

→ See "Guide for Safe Machinery" (8008007)

#### Silicone-free (connectivity)

Silicone-free connections must be used in certain industrial fields, such as paint shops. The reason for this is that silicones can reduce the effectiveness of or disrupt adhesive or other joints.

#### Sine-cosine interface

Unlike conventional pulse signals, sine-cosine signals are emitted in sine-wave form. These signals can be emitted in a higher resolution, as there is also an option to sample the signals using an analog-digital converter. For this reason also, encoders with sine-cosine interfaces are preferred for demanding servo applications for which a high level of accuracy is required. In addition to the signals, a zero set can also be emitted, from which the absolute position can be calculated.

#### Singleturn (ST)

A type of absolute encoder that can definitively determine and output the angle position within a single revolution.

#### Square-wave signal - HTL/TTL

A square-wave signal refers to a periodic signal that alternates between two values and appears as a square-shaped waveform over time. This signal is used in encoders with incremental interfaces in the form of HTL and TTL signals.

- → HTL Push Pull on page L-778
- → TTL RS-422 on page L-785

#### SSI

A synchronous serial interface is an interface originally developed by Max Stegman GmbH (now SICK) for serial data transfer that makes it possible to transmit absolute positions. The advantage of this type of transfer is that, as well as the time of the recording of the position, the speed of the data transfer can be controlled by this SPS. This guarantees safe transfer.



#### SSI + incremental interface

Combination of an SSI and incremental interface (TTL and HTL). Absolute position data and speed information can be transmitted by this interface. The resolutions of the two interfaces are related to one another.

#### SSI + Sin/Cos interface

Combination of an SSI and sine-cosine interface. Absolute position data and speed information can be transmitted by this interface. The resolutions of the two interfaces are related to one another.

#### Start up torque

The torque required to move a shaft from the rest position in the rotation direction.

#### Stator coupling

The stator coupling compensates for both the radial and axial shaft movements of the drive element as well as installation tolerances without significantly affecting the accuracy of hollow shaft encoders. The stator coupling absorbs the torque derived from the bearing friction during angular acceleration.



#### Suitability for use with drag chains

Drag chain use suitability is the ability of cabling to be used in moving applications. PUR cabling is suitable for drag chain use, but PVC cabling is of limited suitability or completely unsuitable. In the case of PUR cabling, the number of bend cycles is generally greater and the bend radius smaller than with PVC cabling.

#### Surrounding field strength

The surrounding field strength describes the maximum permitted influence of external magnetic fields. These external influences must be within the permitted limits to guarantee interference-free functioning of magnetic (linear) encoders.

### T

#### **TTL RS-422**

In a transistor-transistor logic (TTL), both the logical status and the amplification are carried out by transistors, hence the name.

The TTL output is supplied with either a fixed 5 V voltage or a variable voltage of between 10 and 32 V. For this the low range is defined as the  $\leq$  0.4 V and the high range as  $\geq$  2.4 V.

## U

#### **UL** certification

The body responsible for machine safety in the USA (the OSHA: Occupational Safety and Health Administration) requires the components used in machines and plants to be inspected and certified in accordance with US product safety standards. These inspections and certification processes must be carried out by testing organizations known as NRTLs (Nationally Recognized Testing Laboratory). UL508 is the standard in place for encoders

SICK's encoders are either tested by an Underwriters Laboratory (UL) or by TÜV Rheinland for the North American market (USA and Canada). The inspections carried out by both labs comply with UL508 and are considered equal.






## W

#### Web Server

Customers can use an active web server on a commercial web browser on a PC; laptop, or tablet to configure absolute encoders with Ethernet interfaces. The web server function is currently available with the AFS/AFM60 EtherNet/IP; the function is currently being developed for the AFS/AFM60 PROFINET and EtherCAT.

#### Wire draw encoders

Wire draw encoders are position sensors that function according to the cable extension principle. The sensor system consists of a wire draw mechanism and a rotary encoder. The core component of a wire draw encoder is a bobbin around which a wire is wound in a single layer. Winding is achieved by means of a spring. The resolution of the wire draw encoder can be determined from the relationship between the circumference of the drum and the resolution of the rotary encoder.





L-785

Z

#### Zero pulse


A signal (e.g., channel Z) to determine the zero point of an incremental encoder, that is output once during a rotation of the encoder shaft. The zero set is normally used for the reference run of a machine.





#### Zero pulse width, electrical

Width of the zero set (= length of the high signal) in relation to an impulse period.



### Zero pulse width, mechanical

Width of the zero set (= length of the high signal, occasionally of the low signal as well) in relation to a mechanical rotation of the shaft.

### SICK AT A GLANCE

SICK is a leading manufacturer of intelligent sensors and sensor solutions for industrial applications. With almost 7,000 employees and over 50 subsidiaries and equity investments as well as numerous representative offices worldwide, we are always close to our customers. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in various industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services round out our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

#### Worldwide presence:

Australia, Austria, Belgium, Brazil, Canada, Chile, China, Czech Republic, Denmark, Finland, France, Germany, Great Britain, Hungary, India, Israel, Italy, Japan, Malaysia, Mexico, Netherlands, New Zealand, Norway, Poland, Romania, Russia, Singapore, Slovakia, Slovenia, South Africa, South Korea, Spain, Sweden, Switzerland, Taiwan, Thailand, Turkey, United Arab Emirates, USA, Vietnam.

Detailed addresses and additional representatives → www.sick.com

