



MCS200HW

PROVEN MEASUREMENT TECHNOLOGY FOR
FLUE GAS MONITORING

Analyzers

SICK
Sensor Intelligence.

MCS200HW:

READY FOR MORE STRINGENT FLUE GAS MONITORING


Strict legal limits apply to the flue gas emissions of industrial plants with combustion processes. With the MCS200HW analyzer system from SICK, emissions can be continuously monitored – accurately and very reliably. The MCS200HW simultaneously measures up to 10 infrared-active gas components such as SO₂, NO, NO₂, CO, CO₂, NH₃, N₂O, H₂O, HCl, CH₄ as well as O₂ and can be configured for customer-specific measuring tasks.

The state-of-the-art MCS200HW is quickly installed and easy to operate, is characterized by its low maintenance requirements, and can therefore be recommended as a very cost-effective solution. The measurement technology, which is designed for industrial applications and has a clear modular structure, can be easily extended with an FID measurement module (GMS811 FIDORI) for measuring total carbon concentrations.



Easy access to the device and secure data access

The 12" touch display on the front side of the analyzer cabinet provides a task-based interface for operating the entire MCS200HW analyzer system. The web-based operating concept enables device and location independent access – conveniently and securely – via a web browser. No installation of specific software is required.



Secure data transmission via standardized Modbus® interface

The MCS200HW is certified according to the VDI 4201 standard, which is why the data transmission can take place completely via a digital Modbus® interface. This significantly reduces the installation and integration effort: No special hardware such as analog or digital modules is required for communication with the device.



Emission measurement in your plant

Legal environmental regulations require the continuous monitoring of numerous pollutants and reference values in the exhaust gases of industrial plants. The MCS200HW can continuously measure, at a heated extractive sample point, gas components such as: HCl, CO, NO_x as the sum of NO and NO₂, SO₂, NH₃, O₂, H₂O, CO₂ and TOC/C_{ges}. For normalization, the pressure and temperature parameters are also recorded. The QAL3 thorough check can be carried out without test gas with the certified, integrated calibration filter.

More information

→ www.sick.com/MCS200HW



Monitoring of gas compositions

In industrial plants such as metal and steel works that optimize the combustion system of the finishing furnaces, it is possible to improve the furnace performance and thereby achieve long-term savings for the plant operator. The MCS200HW does so by efficiently and very reliably measuring flue gases such as CO, CO₂, H₂O, NO, NO₂, O₂ and SO₂ at the gas outlet of the furnace.

More information

→ www.sick.com/MCS200HW





MCS200HW Ex:

RELIABLE EMISSION MEASUREMENT – INCLUDING IN EXPLOSION-HAZARDOUS AREAS

In industries with explosion-hazardous areas, a single spark can be disastrous. To meet the stringent requirements on explosion protection, analyzers and measuring devices must be especially rugged and reliable. The MCS200HW Ex is equipped with a pressurized housing for explosion-protection zones according to ATEX Zone 2, IIC T3. The touch display on the front side of the analyzer system – with separate purge air equipment – provides direct access to important functions and settings. And the SOPAS operating software provides a high level of transparency through convenient access from anywhere in your network.

Rugged for harsh Ex conditions:

- Classification for ATEX Zone 2 IIC T3
- Standardized measuring technology for economical CEMS solutions
- Simple and time-saving operation via innovative 12“ touch display
- Consistent operating software with access from anywhere within the connected network





Emission measurements in petrochemical plants and refineries

Central supply equipment in any chemical plant includes boilers, furnaces and combustion systems. The amount and type of gas component emitted are regulated by local authorities in the form of environmental regulations and limit values. That is why O₂, NO_x, CO, SO₂, NH₃, CH₄, HCl, HF and other substances often need to be continuously monitored. The appropriate analyzer solution is dependent on the type of fuel and the combustion process.

More information

→ www.sick.com/MCS200HW



Emission measurement in your plant

Hazardous zones in industries and plants are reclassified on a regular basis. MCS200HW Ex is a rugged and reliable solution with an industry tested and proven measurement technology in a pressurized housing version that meets ATEX Zone 2 requirements.

More information

→ www.sick.com/MCS200HW





ONE ANALYZER SYSTEM, MANY POSSIBILITIES, HIGH EFFICIENCY

Long service life and high measurement certainty

The MCS200HW works according to the measurement principle of an infrared single-beam photometer. Both interference and gas filter correlation methods are used. All parts in contact with the medium are heated above the dew point in order to prevent condensate formation in the analyzer system and to avoid damage due to corrosion. Thus, water-soluble gases such as HCl or NH₃ can be monitored and are not lost through salt formation.

Reliable and cost-effective with very high measurement quality

Thanks to internal adjustment filters, drift checking and adjustment are possible even without a test gas. The reference point position of all infrared-active components can be checked both manually and fully automatically. The reference point check can also be used for quality assurance during operation (QAL3 inspection). Expensive test gases are not necessary and the workload is reduced.



Low maintenance and effective: wear-free gas pumping

An ejector pump conveys the measurement gas from the gas sampling unit of the analyzer system. The device operates without wear and tear: the gas is moved in the system by negative pressure without mechanical stress on the components. Maintenance is minimized, which at the same time reduces running costs.

Tailored configuration for flexibility and efficiency

The analyzer system can be individually configured depending on the measuring task. The costs are based on the respective measuring components used. The result: tailored analyzer system – highly economical and high-performing

Lower costs due to the use of dry test gases

With the MCS200HW, reference point checking and adjustment of HCl and NH₃ are possible for the first time using exclusively dry test gases certified according to EN 15267 and EN 14181. Test gas generators or evaporators for generating wet test gases are no longer required. This saves time and reduces operating costs. Both for operating entities, e.g. when carrying out the regular QAL3 inspections, and for test institutes, e.g. when carrying out the annual surveillance test (AST).

CONDITION MONITORING INCLUDED




The powerful duo doubles the efficiency and fail safety

As the first multi-component analyzer system from SICK, the MCS200HW is already connected to the Monitoring Box and Condition Monitoring services ex works. This gives you the ability to visualize and evaluate the condition data of your plants and sensors at any time and from any location.

Benefit for you

You can immediately start deploying your maintenance staff only when maintenance is actually required and also reduce downtimes to a minimum. And because it is so important, in particular in flue gas systems, that the gas analysis functions properly, the Monitoring Box supports you in complying with strict emission limits.




Thanks to integrated Monitoring Box: effectively plan your service deployments.

With the Monitoring Box from SICK, you obtain virtual access to sensors and plants and can continuously optimize them during operation. The Monitoring Box digitally monitors all integrated devices of your company and detects any changes in the condition of sensors and plants in real time. Faults can thereby

be detected early or avoided altogether. The Monitoring Box not only supports predictive maintenance. It also makes it easier to prepare for service deployments so our service technicians can be on-site in time and with the right spare parts.

STEP BY STEP TO MORE EFFICIENCY



Data analysis and trend forecasting

Diagrams present measurement data and the status of all devices in a clear and understandable way within the dashboard. This allows the data to be quickly analyzed and trends identified.



High plant availability

Analysis of condition data reduces unplanned downtimes and keeps the plant running smoothly.



Quick response

Automatic alerts in e-mails or text messages enable timely action when anomalies or deviations are detected. Solutions and recommended actions are displayed in direct form.



Predictive maintenance

Verification and evaluation of historical data make it possible to schedule maintenance work and optimize the lifetime of spare and wear parts. This saves time and money.

PROVEN MEASUREMENT TECHNOLOGY FOR FLUE GAS MONITORING



Product description

The MCS200HW is a multi-component analyzer system for continuous monitoring of up to 10 IR measurement components in flue gases of industrial combustion plants. The MCS200HW is hot/wet extractive: All parts which touch media, from the gas sampling probe to the cell, are heated above the dew point and therefore protected from corrosion. An integrated oxygen sensor also measures oxygen. As an option, a TOC

measurement can be supplemented via an integrated GMS811 FIDORi (non-Ex variant only). Internal reference point monitoring allows for a quick check of the measured values with test gases. The web display and the task assistant integrated in the software makes operation very easy. MCS200HW Ex allows reliable emission measurement even in explosion-hazardous areas.

At a glance

- Measurement of up to 10 IR components plus O₂ and TOC
- Hot/wet extractive measurement technology
- Wear-free gas distribution through ejector pumps
- Reference point monitoring with internal calibration cells
- Certified digital Modbus® interface
- Web server for platform-independent device control
- Use of dry test gases for HCl and NH₃
- Classification for ATEX Zone 2, IIC T3 Gc

Your benefits

- Reliable measurement results, even for water-soluble gas components
- Only one analyzer necessary for simultaneous monitoring of up to 12 gas components
- Measurement components can be put together flexibly and extended
- Convenient, task-oriented operation
- Remote access without additional software
- High availability due to certified internal third-party monitoring (QAL3) without test gases
- Low service costs thanks to minimal maintenance requirements
- Data transmission through only one interface possible
- Use in explosion-hazardous areas thanks to rugged, pressurized housing



More information

Fields of application	11
Detailed technical data	11
Ordering information	16
Dimensional drawings	16
Accessories	19

→ www.sick.com/MCS200HW

For more information, simply enter the link or scan the QR code to get direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



Fields of application

- Emission monitoring for waste incineration plants as well as power plants and plants with co-incineration, e.g. cement plants
- Measurement of nitrogen oxides (NO, NO₂, N₂O) in nitric acid plants

Detailed technical data

The precise device specifications and product performance data may vary and are dependent on the respective application and customer specifications.

MCS200HW system

Measured values	CH ₄ , CO, CO ₂ , C _{org} , HCl, H ₂ O, NH ₃ , NO, NO ₂ , N ₂ O, O ₂ , SO ₂																								
Performance-tested measurand	CH ₄ , CO, CO ₂ , C _{org} , HCl, H ₂ O, NH ₃ , NO, NO ₂ , N ₂ O, O ₂ , SO ₂																								
Measurement principles	interference filter correlation, gas filter correlation,																								
Measuring distance	8.48 m																								
Gas flow rate	200 l/h ... 400 l/h																								
Measuring ranges	<table> <tr><td>CH₄</td><td>0 ... 70 ppm / 0 ... 700 ppm</td></tr> <tr><td>CO</td><td>0 ... 60 ppm / 0 ... 8.000 ppm</td></tr> <tr><td>CO₂</td><td>0 ... 25 Vol.-% / 0 ... 50 Vol.-%</td></tr> <tr><td>C_{org}</td><td>0 ... 15 mg/m³ / 0 ... 10.000 mg/m³</td></tr> <tr><td>HCl</td><td>0 ... 9 ppm / 0 ... 1.840 ppm</td></tr> <tr><td>H₂O</td><td>0 ... 40 Vol.-%</td></tr> <tr><td>NH₃</td><td>0 ... 15 ppm / 0 ... 650 ppm</td></tr> <tr><td>NO</td><td>0 ... 110 ppm / 0 ... 1.865 ppm</td></tr> <tr><td>NO₂</td><td>0 ... 25 ppm / 0 ... 240 ppm</td></tr> <tr><td>N₂O</td><td>0 ... 50 ppm / 0 ... 1.015 ppm</td></tr> <tr><td>O₂</td><td>0 ... 25 Vol.-%</td></tr> <tr><td>SO₂</td><td>0 ... 26 ppm / 0 ... 875 ppm</td></tr> </table>	CH ₄	0 ... 70 ppm / 0 ... 700 ppm	CO	0 ... 60 ppm / 0 ... 8.000 ppm	CO ₂	0 ... 25 Vol.-% / 0 ... 50 Vol.-%	C _{org}	0 ... 15 mg/m ³ / 0 ... 10.000 mg/m ³	HCl	0 ... 9 ppm / 0 ... 1.840 ppm	H ₂ O	0 ... 40 Vol.-%	NH ₃	0 ... 15 ppm / 0 ... 650 ppm	NO	0 ... 110 ppm / 0 ... 1.865 ppm	NO ₂	0 ... 25 ppm / 0 ... 240 ppm	N ₂ O	0 ... 50 ppm / 0 ... 1.015 ppm	O ₂	0 ... 25 Vol.-%	SO ₂	0 ... 26 ppm / 0 ... 875 ppm
CH ₄	0 ... 70 ppm / 0 ... 700 ppm																								
CO	0 ... 60 ppm / 0 ... 8.000 ppm																								
CO ₂	0 ... 25 Vol.-% / 0 ... 50 Vol.-%																								
C _{org}	0 ... 15 mg/m ³ / 0 ... 10.000 mg/m ³																								
HCl	0 ... 9 ppm / 0 ... 1.840 ppm																								
H ₂ O	0 ... 40 Vol.-%																								
NH ₃	0 ... 15 ppm / 0 ... 650 ppm																								
NO	0 ... 110 ppm / 0 ... 1.865 ppm																								
NO ₂	0 ... 25 ppm / 0 ... 240 ppm																								
N ₂ O	0 ... 50 ppm / 0 ... 1.015 ppm																								
O ₂	0 ... 25 Vol.-%																								
SO ₂	0 ... 26 ppm / 0 ... 875 ppm																								
Certified measuring ranges	<table> <tr><td>CH₄</td><td>0 ... 50 mg/m³ / 0 ... 500 mg/m³</td></tr> <tr><td>CO</td><td>0 ... 75 mg/m³ / 0 ... 10,000 mg/m³</td></tr> <tr><td>CO₂</td><td>0 ... 25% by vol.</td></tr> <tr><td>C_{org}</td><td>0 ... 15 mg/m³ / 0 ... 50 mg/m³ / 0 ... 150 mg/m³ / 0 ... 500 mg/m³</td></tr> <tr><td>HCl</td><td>0 ... 15 mg/m³ / 0 ... 3,000 mg/m³</td></tr> <tr><td>H₂O</td><td>0 ... 40% by vol.</td></tr> <tr><td>NH₃</td><td>0 ... 10 mg/m³ / 0 ... 500 mg/m³</td></tr> <tr><td>NO</td><td>0 ... 150 mg/m³ / 0 ... 2,500 mg/m³</td></tr> <tr><td>NO₂</td><td>0 ... 50 mg/m³ / 0 ... 500 mg/m³</td></tr> <tr><td>N₂O</td><td>0 ... 100 mg/m³ / 0 ... 2,000 mg/m³</td></tr> <tr><td>O₂</td><td>0 ... 25% by vol.</td></tr> <tr><td>SO₂</td><td>0 ... 75 mg/m³ / 0 ... 2,500 mg/m³</td></tr> </table>	CH ₄	0 ... 50 mg/m ³ / 0 ... 500 mg/m ³	CO	0 ... 75 mg/m ³ / 0 ... 10,000 mg/m ³	CO ₂	0 ... 25% by vol.	C _{org}	0 ... 15 mg/m ³ / 0 ... 50 mg/m ³ / 0 ... 150 mg/m ³ / 0 ... 500 mg/m ³	HCl	0 ... 15 mg/m ³ / 0 ... 3,000 mg/m ³	H ₂ O	0 ... 40% by vol.	NH ₃	0 ... 10 mg/m ³ / 0 ... 500 mg/m ³	NO	0 ... 150 mg/m ³ / 0 ... 2,500 mg/m ³	NO ₂	0 ... 50 mg/m ³ / 0 ... 500 mg/m ³	N ₂ O	0 ... 100 mg/m ³ / 0 ... 2,000 mg/m ³	O ₂	0 ... 25% by vol.	SO ₂	0 ... 75 mg/m ³ / 0 ... 2,500 mg/m ³
CH ₄	0 ... 50 mg/m ³ / 0 ... 500 mg/m ³																								
CO	0 ... 75 mg/m ³ / 0 ... 10,000 mg/m ³																								
CO ₂	0 ... 25% by vol.																								
C _{org}	0 ... 15 mg/m ³ / 0 ... 50 mg/m ³ / 0 ... 150 mg/m ³ / 0 ... 500 mg/m ³																								
HCl	0 ... 15 mg/m ³ / 0 ... 3,000 mg/m ³																								
H ₂ O	0 ... 40% by vol.																								
NH ₃	0 ... 10 mg/m ³ / 0 ... 500 mg/m ³																								
NO	0 ... 150 mg/m ³ / 0 ... 2,500 mg/m ³																								
NO ₂	0 ... 50 mg/m ³ / 0 ... 500 mg/m ³																								
N ₂ O	0 ... 100 mg/m ³ / 0 ... 2,000 mg/m ³																								
O ₂	0 ... 25% by vol.																								
SO ₂	0 ... 75 mg/m ³ / 0 ... 2,500 mg/m ³																								
Response time (t₉₀)	≤ 200 s																								
Accuracy	≤ 2% relative to measuring range limit value																								
Sensitivity drift	≤ 3%: within the maintenance interval, relative to the measuring range limit value																								
Zero point drift	< 3% of the measuring range limit value per maintenance interval																								
Reference point drift	< 3% of the measuring range limit value per maintenance interval																								

Detection limit		≤ 2%: relative to measuring range limit value
	TOC measurement	0.05 mg/m ³
Reproducibility		≤ 3.3% relative to measuring range limit value
	O ₂ measurement	≤ 0.2% by vol.
Uncertainty of measurement		≤ 2% of the measuring range limit value
Process temperature		≤ +1,300 °C
Sample gas temperatur		
	Input analyzer system:	≤ +200 °C
Process pressure		850 hPa ... 1,100 hPa
Process gas humidity		≤ 40% by vol.
Ambient temperature		+5 °C ... +40 °C
Storage temperature		-20 °C ... +70 °C
Ambient pressure		850 hPa ... 1,100 hPa
Ambient humidity		≤ 90% relative humidity; non-condensing
Conformities		Approved for systems requiring a permit 2000/76 / EG (17th German Federal Immission Control Act (BlmSchV)) 2001/80 / EC (13th German Federal Immission Control Act (BlmSchV)) 27 th German Federal Immission Control Act (BlmSchV) EN 15267 EN 14181
Electrical safety		CE
Enclosure rating		IP54
Analog outputs		0/4 ... 22 mA, 500 Ω number depends on system configuration
Analog inputs		0/4 ... 22 mA, 100 Ω number depends on system configuration; electrically isolated
Digital outputs		48 V AC, 0.5 A, 35 W / 48 V DC, 0.5 A, 24 W number depends on system configuration; electrically isolated
Digital inputs		3.9 V, 4.5 mA, 0.55 W number depends on system configuration
Modbus		✓
	Type of fieldbus integration	TCP RTU RS-485
PROFIBUS DP		✓
	Note	Option
PROFINET		✓
	Note	Option
Ethernet		✓
	Function	Connection to SOPAS ET software or OPC server
Indication		LC display Status LEDs: "Power," "Failure," and "Maintenance request"
Input		Touchscreen
Operation		Via LC display or SOPAS ET software, multiple operating levels, password-protected
Menu language		German, English
Dimensions (W x H x D)		
	Analyzer cabinet	808 mm x 2.208 mm x 623 mm (Details siehe Maßzeichnungen)
	Mounting plate	699 mm x 1.896 mm x 334 mm (Details siehe Maßzeichnungen)
Weight		
	Analyzer cabinet	approx. 250 kg
Material in contact with media		Stainless steel 1.4571, PTFE, aluminum, coated

Power supply		
	Voltage	115 V AC, ± 10% 230 V AC, ± 10%
	Frequency	50 Hz / 60 Hz
	Power consumption	Analyzer: ≤ 1,000 VA Sample gas line, heated: ≤ 95 VA/m Gas sampling unit: ≤ 450 VA Heated gas sampling pipe: ≤ 450 VA
Auxiliaries		
	Instrument air (zero gas quality):	≤ 350 l/h 6 ... 7 bar; particle size max. 1 µm; oil content max. 0.1 mg/m ³ ; pressure condensation point max. -40 °C, purity class 2 (ISO 8573)
	Instrument air (propellant air for ejector):	≤ 1,300 l/h 5 ... 7 bar; particle size max. 5 µm; oil content max. 1 mg/m ³ ; pressure condensation point max. +3 °C, purity class 3 (ISO 8573)
	Reference gas:	≤ 350 l/h Max. 4 bar; the reference gas must comply with the requirements of the applicable standards and guidelines
Sample connections		
	Measuring gas input	Clamp connection for 6 mm pipes
Auxiliary connections		
	Propellant air for ejector	DN 6/8
	Reference gas	Clamp connection for 6 mm pipes
	Exhaust gas outlet	DN 8/10
Corrective functions		Drift correction and optical monitoring function via adjustment cell
Test functions		Automatic check cycle for zero and reference point
System components		Gas sampling unit Sample gas line Analyzer cabinet
Options		GMS811 FIDORI

System MCS200HW Ex

Measured values	CH ₄ , CO, CO ₂ , C _{org} , HCl, H ₂ O, NH ₃ , NO, NO ₂ , N ₂ O, O ₂ , SO ₂
Performance-tested measurands	CH ₄ , CO, CO ₂ , C _{org} , HCl, H ₂ O, NH ₃ , NO, NO ₂ , N ₂ O, O ₂ , SO ₂
Measurement principles	Interference filter correlation, Gas filter correlation
Measuring distance	8,48 m
Gas flow rate	200 l/h ... 400 l/h
Measuring ranges	
	CH ₄ 0 ... 70 ppm / 0 ... 700 ppm
	CO 0 ... 60 ppm / 0 ... 8.000 ppm
	CO ₂ 0 ... 25 Vol.-% / 0 ... 50 Vol.-%
	C _{org} 0 ... 15 mg/m ³ / 0 ... 10.000 mg/m ³
	HCl 0 ... 9 ppm / 0 ... 1.840 ppm
	H ₂ O 0 ... 40 Vol.-%
	NH ₃ 0 ... 15 ppm / 0 ... 650 ppm
	NO 0 ... 110 ppm / 0 ... 1.865 ppm
	NO ₂ 0 ... 25 ppm / 0 ... 240 ppm
	N ₂ O 0 ... 50 ppm / 0 ... 1.015 ppm
	O ₂ 0 ... 25 Vol.-%
	SO ₂ 0 ... 26 ppm / 0 ... 875 ppm

Certified measuring ranges	CH ₄ 0 ... 50 mg/m ³ / 0 ... 500 mg/m ³ CO 0 ... 75 mg/m ³ / 0 ... 10.000 mg/m ³ CO ₂ 0 ... 25 Vol.-% C _{org} 0 ... 15 mg/m ³ / 0 ... 50 mg/m ³ / 0 ... 150 mg/m ³ / 0 ... 500 mg/m ³ HCl 0 ... 15 mg/m ³ / 0 ... 3.000 mg/m ³ H ₂ O 0 ... 40 Vol.-% NH ₃ 0 ... 10 mg/m ³ / 0 ... 500 mg/m ³ NO 0 ... 150 mg/m ³ / 0 ... 2.500 mg/m ³ NO ₂ 0 ... 50 mg/m ³ / 0 ... 500 mg/m ³ N ₂ O 0 ... 100 mg/m ³ / 0 ... 2.000 mg/m ³ O ₂ 0 ... 25 Vol.-% SO ₂ 0 ... 75 mg/m ³ / 0 ... 2.500 mg/m ³
Response tim (t₉₀)	≤ 200 s
Accuracy	≤ 2 % relative to measuring range end value
Sensitivity drift	≤ 3 %: within the maintenance interval, relative to measuring range full scale
Zero point drift	< 3 %: of the measuring range full scale value per maintenance interval
Reference point drift	< 3 %: of the measuring range full scale value per maintenance interval
Detection limit	≤ 2 %: relative to measuring range end value
TOC measurement	0.05 mg/m ³
Reproducibility	≤ 3.3 %: relative to measuring range end value
O ₂ measurement	≤ 0.2 Vol.-%
Uncertainty of measurement	≤ 2 % of measuring range full scale
Process temperature	≤ +1,300 °C
Sample gas temperature	
Inlet analyzer system	≤ +200 °C
Process pressure	850 hPa ... 1,100 hPa
Process gas humidity	≤ 40 Vol.-%
Ambient temperature	-20 °C ... +50 °C
Storage temperature	-20 °C ... +70 °C
Ambient pressure	850 hPa ... 1,100 hPa
Ambient humidity	≤ 90 % relative humidity; non-condensing
Ex-approvals	
ATEX	Ex II, IIC T3: Analyzer cabinet Ex II, IIC T3: Gas sampling unit Ex I, IIC T3: Sample gas line
Electrical safety	CE
Enclosure rating	IP65
Analog outputs	0/4 ... 22 mA, 500 Ω Number depends on system configuration
Analog inputs	0/4 ... 22 mA, 100 Ω Number depends on system configuration; electrically isolated
Digital outputs	48 V AC, 0,5 A, 35 W / 48 V DC, 0,5 A, 24 W Number depends on system configuration; electrically isolated
Digital inputs	3,9 V, 4,5 mA, 0,55 W Number depends on system configuration


Modbus	✓
Type of fieldbus integration	TCP RTU RS-485
PROFIBUS DP	✓
Remark	Option
PROFINET	✓
Remark	Option
Ethernet	✓
Function	Connection to SOPAS ET software or OPC server
Indication	LC display Status LEDs: "Power," "Failure," and "Maintenance request"
Input	Touchscreen
Operation	Via LC display or SOPAS ET software, multiple operating levels, password-protected
Menu language	German, English
Dimensions (W x H x D)	
Analyzer cabinet	808 mm x 2.208 mm x 623 mm (Details siehe Maßzeichnungen)
Mounting plate	699 mm x 1.896 mm x 334 mm (Details siehe Maßzeichnungen)
Weight	
Analyzer cabinet	approx. 400 kg
Material in contact with media	Stainless steel 1.4571, PTFE, aluminum, coated
Power supply	
Voltage	115 V AC, ± 10% 230 V AC, ± 10%
Frequency	50 Hz / 60 Hz
Power consumption	Analyzer: ≤ 1,000 VA Sample gas line, heated: ≤ 95 VA/m Gas sampling unit: ≤ 450 VA Heated gas sampling pipe: ≤ 450 VA
Auxiliaries	
Instrument air (zero gas quality):	≤ 350 l/h 6 ... 7 bar; particle size max. 1 µm; oil content max. 0.1 mg/m ³ ; pressure condensation point max. -40 °C, purity class 2 (ISO 8573)
Instrument air (propellant air for ejector):	≤ 1,300 l/h 5 ... 7 bar; particle size max. 5 µm; oil content max. 1 mg/m ³ ; pressure condensation point max. +3 °C, purity class 3 (ISO 8573)
Reference gas:	≤ 350 l/h Max. 4 bar; the reference gas must comply with the requirements of the applicable standards and guidelines
Instrument air Ex p (flushing unit)	Max. 4.5 barg (system-side regulation), specification according to ISO 8573-1:5-3-3, particle size: max. 40 µm (Class 5), dew point: ≤ -20 °C (Class 3), oil content: ≤ 1 mg/m ³ (Class 3), air volume: 39,100 l/h
Sample connections	
Measuring gas input	Clamp connection for 6 mm pipes
Auxiliary connections	
Propellant air for ejector	DN 6/8
Reference gas	Clamp connection for 6 mm pipes
Exhaust gas outlet	DN 8/10
Corrective functions	Drift correction and optical monitoring function via adjustment cell
Test functions	Automatic check cycle for zero and reference point
System components	Gas sampling unit Sample gas line Analyzer cabinet

Ordering information




Our regional sales organization will be glad to advise you on which device configuration is best for you.

Dimensional drawings (dimensions in mm)


Mounting plate MCS200HW



MCS200HW system



MCS200HW Ex system



Accessories

Digital Services for Integration

Short description	Type	Part no.:
<ul style="list-style-type: none"> • Application: Condition Monitoring • Description: The Monitoring Box Basic is a scalable digital service for monitoring service and process data. • Hosting: Off-premise: smartservice.sick.com, On-premise: Industrial PC or virtual machine on the user's servers • Type: App • Contract type: SaaS • Contract interval: Annual • Supported products: MCS200HW • Vital data: Operational status, Logbook, temperatures, Optical unit, Printed-circuit board assembly, Operating voltage, Frequencies, Drifts • Version: Release 1 	Monitoring Box MCS200HW Basic	1616023
<ul style="list-style-type: none"> • Application: Condition Monitoring, Data Analytics, Predictive Maintenance • Description: The Monitoring Box Basic is a scalable digital service for monitoring, analyzing and predicting service and process data. • Hosting: Off-premise: smartservice.sick.com, On-premise: Industrial PC or virtual machine on the user's servers • Contract type: SaaS • Contract interval: Annual • Supported products: MCS200HW • Vital data: Operational status, Logbook, temperatures, Optical unit, Printed-circuit board assembly, Operating voltage, Frequencies, Drifts • Version: Proof of Concept 	Monitoring Box MCS200HW Premium	-

SICK AT A GLANCE

SICK is a leading manufacturer of intelligent sensors and sensor solutions for industrial applications. With more than 11,900 employees and over 50 subsidiaries and equity investments, as well as numerous international agencies, SICK is always close to its customers. An extensive range of products and services creates the ideal basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

SICK has extensive experience in various industries and understands their processes and requirements. With intelligent sensors, SICK delivers exactly what the customers need. In application centers in Europe, Asia, and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes SICK a reliable supplier and development partner.

Comprehensive services round out the offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

That is “Sensor Intelligence.”

Worldwide presence:

Australia, Austria, Belgium, Brazil, Canada, Chile, China, Czech Republic, Denmark, Finland, France, Germany, Great Britain, Hungary, Hong Kong, India, Israel, Italy, Japan, Malaysia, Mexico, Netherlands, New Zealand, Norway, Poland, Romania, Russia, Singapore, Slovakia, Slovenia, South Africa, South Korea, Spain, Sweden, Switzerland, Taiwan, Thailand, Turkey, United Arab Emirates, USA, Vietnam.

Detailed addresses and further locations → www.sick.com