

## DeltaPac BRIDGING THE GAP



MultiTask photoelectric sensors

## RELIABLE GAP-LESS SENSING: DeltaPac FROM SICK PERFECTS PRODUCTION

# ON ITS QUEST TO INCREASE EFFICIENCY, SICK IS PROVIDING SOLUTIONS THAT IMPROVE PRODUCT FLOW BY CLOSING THE GAPS ON THE CONVEYOR

Now products can be counted and detected on the conveyor in a way that was not possible before. Without gaps. Without delays. The DeltaPac accurately detects and differentiates between successive packaging items on the fly. This ensures faster, smarter and more economical production. In other words: The DeltaPac is a patented technological world first, implemented in a unique way.

The DeltaPac closes every gap. It eliminates product separation on the conveyor and reduces downtime caused by collision. The DeltaPac is an energy-efficient solution that increases production and requires less hardware, opening up new applications for systems engineering! Deterministic product positioning opens up a new world of automation.

DeltaPac: the new, uniquely efficient photoelectric sensor from SICK.



#### Packaging industry

Consecutive rows of apple juice packaging

2





Click here for the application video www.sick.com/DeltaPac

3

## A SEAMLESS LINE OF BENEFITS: HOW DeltaPac SOLVES THE PACKAGING PROBLEM

The MultiTask photoelectric sensor DeltaPac solves fundamental problems in the packaging industry. Whether it is inefficient idle running or machine downtime and loss of quality due to crashes, the DeltaPac ensures faster and more reliable production with maximum quality.






A prime example of clean production

#### Optimum product flow:

No collisions due to falling packages mean less machine downtime. Time is saved if packaging items are grouped correctly and labels are accurately positioned. Plus, steady production ensures energy efficiency.







Industry learns to count

#### Production that can be monitored:

You always know how many packaging items are in the process. Revolutionary for optimizing production. As a result of this new information, new measures can be implemented that increase efficiency.





A lean production line

#### **Resources saved:**

No more product jams and packages queues. And, no need to separate items before grouping them. This saves on mechanical costs and reduces hardware, which ultimately saves space.





Can be individually adapted to production requirements

#### High flexibility:

Smart Sensor communication via SOPAS-ET opens up new possibilities such as enhanced diagnostics and automatic sensor optimization. There are four different operating modes available. The DeltaPac adapts to the system and the optimization criteria and enables the production system to be clearly differentiated.



Automation creates simplicity

#### Simple operation:

All you have to do is connect and start it up. Pre-configured, automated devices guarantee fast and simple installation and fault-free operation.



# PRODUCTION AT A GLANCE: DeltaPac KNOWS EXACTLY WHAT TYPE OF PACKAGE IS CONVEYED

The unique DeltaPac MultiTask photoelectric sensor is able to detect the widest range of contours. It enables products to be counted without gaps. It is ideal for detecting items typically found in today's packaging industry. Pre-configured, automated sensors detect rounded, rounded out, prism-shaped packaging items, and folded boxes. In addition, the DeltaPac is an IO-Link-compatible sensor, which unlocks further features to maximize application flexibility.

Save time with the quick installation and fault-free operation of the DeltaPac.



#### Rounded, round out and prism-shaped packages:

This range of packaging includes the typical kinds of primary packaging used for beverages, finished products, and health and beauty products, for example. The DeltaPac can reliably detect these objects without any additional sensor settings.

#### Folded boxes:

Due to various DeltaPac versions that have been specifically adjusted at the factory, even transitions that are barely visible can be detected. This includes small edges on secondary packaging: usually folding boxes for items such as medicinal products, cosmetics, and luxury goods with almost rectangular radii.

#### Multiple products:


Different packaging items need to be detected. With maximum sensor performance. The IO-Link-compatible DeltaPac variant is the ideal choice in such cases. Four operating modes are available. All it takes is a click to select the right sensor setting for any type of object. For example, you may need to process highly reflective, prismshaped beverage packaging during the morning shift. When the night shift comes around, all you then need to do is click the option for rectangular folding boxes on the HMI. It's a system that provides maximum flexibility for machinery designed to give a seamless performance. For more detailed information about the options that the four operating modes offer, refer to the "Technical information" available for download at www.sick.de/DeltaPac.


7



With Delta-S-Technology<sup>®</sup>, the DeltaPac can detect items better than the human eye. Although similar in terms of speed, accuracy, and flexibility. Just more reliable. It is a technological world first with unimaginable application possibilities.

# AN OVERVIEW OF Delta-S-TECHNOLOGY<sup>®</sup>: THE NEW PERSPECTIVES IN USE





Energy is balanced

#### Simple yet effective technology:

From side to side, the DeltaPac uses the light beams of four PinPoint 2.0 LEDs to track the contours of packaging edges. If the edge of packaging item is detected by a beam, it reflects the light. Two energy scales each with two receivers re-absorb the light. They identify the changed direction from which the light is reflected. And send corresponding switching signals. From the smallest changes in angles to the tiniest corners and edges to extremely flat angles and transitions with the smallest radii – everything is reliably detected.

#### The unique technology:

The DeltaPac contains the patented Delta-S-Technology<sup>®</sup>: two high-resolution energy scales with the light beams of four PinPoint 2.0 LEDs and SICK's specific SIRIC<sup>®</sup> ASIC technology. And range measurement. It is ideal for gap-free detection of corners, folds, and grooves irrespective of color, object size, surface, and background.

#### Why technology fusion?

The multiple use of technology principles to prevent all types of glare, changes in contrast, unevenness, and reflective interference guarantees reliable detection of all popular types of packaging and folded boxes.







More information at www.sick.com/siric

### **BRIDGING THE GAP**



#### **Product description**

For higher efficiency and quality in the packaging industry, the DeltaPac MultiTask photoelectric sensor utilizes Delta-S technology®, which combines four PinPoint emitters and two receivers with SIRIC® and distance measurement technology. Thanks to the four operating modes available to select with just a click, the sensor is able to detect object contours with radii of up to 20 mm - from any direction. From rectangular, dark-colored folded boxes

#### At a glance

- Delta-S technology®, four PinPoint 2.0 LEDs and two energy scales, combined with SIRIC® and distance measurement technology
- · Able to detect object contours with radii of up to 20 mm in any direction
- For belt speeds up to 3.0 m/s or production rates of up to 200,000 packages per hour


#### Your benefits

- Selective process optimization: information about the number of packages in the process enables better production monitoring
- Better space utilization: no mechanical devices are required to isolate packages, reducing the width of packaging systems and saving space
- Better time management: packages run in push-push mode, which prevents collisions and toppling, and reduces machine downtime

to white, glossy, prism-shaped packaging, objects are detected reliably with a sensing range of 30 to 40 mm. This means that the packaging does not have to be manually separated. Collisions are avoided. For better space and time utilization. The DeltaPac provides information about how many packages are present in the process for full production monitoring. The sensor is also available as a pre-configured device for fast and error-free commissioning.

- · Preconfigured sensors or custom setting of four operating modes via IO-Link
- Compact housing (42 mm x 42 mm x 45 mm) with an IP 67 enclosure rating
- · Stable production for reduced energy consumption
- Fast and intuitive commissioning due to pre-configuration
- · Maximum flexibility in the types of objects used thanks to the option of custom-setting four operating modes via IO-Link
- · Space-saving mounting due to compact housing

#### www.mvsick.com/en/DeltaPac





#### Detailed technical data

#### Features

Sensor principle	Delta-S-Technology
Dimensions (W x H x D)	42 mm x 42 mm x 45 mm
Housing design (light emission)	Rectangular
Sensing range max.	30 mm 40 mm <sup>1)</sup> (depending on type)
Type of light	Visible red light
Light source <sup>2)</sup>	PinPoint LED
Light spot size (distance)	4 x Ø 1 mm (30 mm)
Wave length	635 nm
Operating modes for the following objects	Packaging (e.g. beverages and finished products as well as health and beauty products) / Packaging "Oversize Fit" (e.g. primary packaging for beverages) / Folded Box (e.g. medicinal products, cosmetics and luxury goods) / Folded Box "Slim Fit" (e.g. folding boxes for cigarette packaging) (depending on type)

<sup>1)</sup> The sensing range max. refers to the object leading edge. The individual object leading edges must be within the operating range.

 $^{\scriptscriptstyle 2)}$  Average service life of 100,000 h at  $T_{_{\rm A}}$  = +25  $\,^{\circ}{\rm C}$  .

#### Mechanics/electronics

Supply voltage 1)	10 V DC 30 V DC
Power consumption	$\leq$ 70 mA <sup>2)</sup> $\leq$ 160 mA <sup>2)</sup> (depending on type)
Output current I <sub>max.</sub>	≤ 2 x 100 mA
Connection type	Connector, M12 Cable, 2 m <sup>3)</sup> (depending on type)
Circuit protection	A <sup>4</sup> ) B <sup>5</sup> ) C <sup>6</sup>
Protection class	III
Weight	130 g
IO-Link	<ul><li>✓ (COM2)</li><li>(depending on type)</li></ul>
Housing material	Novodur
Enclosure rating	IP 67
Ambient operating temperature	-40 °C +55 °C
Ambient storage temperature	-40 °C +75 °C
Switching accuracy	≤ 2 x radius
Repeatability	Typ. < 1 mm

<sup>1)</sup> Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

<sup>2)</sup> 70 mA at 24 V; 160 mA at 10 V.

 $^{\rm 3)}$  Do not bend below 0 °C.

 $^{\rm 4)}\,A$  = V  $_{\rm S}$  connections reverse-polarity protected.

 $^{\rm 5)}$  B = inputs and output reverse-polarity protected.

 $^{6)}$  C = interference suppression.

#### Ordering information

Other models available at www.mysick.com/en/DeltaPac

#### WTD20E, for folding boxes

- Object speed max.: 0.6 m/s <sup>2)</sup>
- Switch on delay Q<sub>1</sub> & Q<sub>2</sub>: 80 ms
- Time delay off Q<sub>1</sub>: 80 ms
- Pulse length (Q2): 20 ms
- Background suppression: ≥ 60 mm
- Object height min.:  $\geq$  30 mm <sup>1)</sup>

Object width min.	Radius of the object contour	Key feature of the object	Sensing range	Output type	Connection	Connection diagram	Model name	Part no.
				PNP	Connector M12, 4-pin	Cd-243	WTD20E-V2445	1065772
≥ 10 mm	1 mm 2 mm	edges	30 +/- 2 mm	NPN	Cable, 4-wire, 2 m, PVC	Cd-242	WTD20E-W1145	1065773

<sup>1)</sup> The minimum object height is relevant only for mounting the DeltaPac above the belt.

<sup>2)</sup> See "Object speed in detail".

#### WTD20E, rounded, rounded out and prism shaped packaging

- **Object speed max.:** 1.2 m/s <sup>2)</sup>
- Switch on delay Q<sub>1</sub> & Q<sub>2</sub>: 60 ms
- **Time delay off Q**<sub>1</sub>: 60 ms
- Pulse length (Q2): 20 ms
- Background suppression: ≥ 80 mm
- Object height min.:  $\geq$  50 mm <sup>1)</sup>

Object width min.	Radius of the object contour	Key feature of the object	Sensing range	Output type	Connection	Connection diagram	Model name	Part no.
≥ 20 mm	2 mm 5 mm	rounded edges	30 mm 35 mm					
≥ 30 mm	5 mm 20 mm	rounded out body and prism shaped	30 mm 40 mm	PNP	PNP Connector M12, 4-pin	Cd-243	WTD20E-V2414	1064778
≥ 20 mm	2 mm 5 mm	rounded edges	30 mm 35 mm		Cable.			
≥ 30 mm	5 mm 20 mm	rounded out body and prism shaped	30 mm 40 mm	NPN	4-wire, 2 m, PVC	Cd-242	WTD20E-W1114	1064779

<sup>1)</sup> The minimum object height is relevant only for mounting the DeltaPac above the belt.

 $^{\mbox{\tiny 2)}}$  See "Object speed in detail".

WTD20E, IO-Link for folded boxes, rounded, rounded out and prism shaped packaging <sup>1)</sup>

- Object speed min.: 0.05~m/s ... 0.25~m/s  $^{2)}$
- Object speed max.: 0.6 m/s ... 3 m/s  $^{\scriptscriptstyle 2)}$
- Switch on delay  $\mathbf{Q}_1$  &  $\mathbf{Q}_2$  : 0 ms ... 255 ms
- Time delay off  $\mathbf{Q}_1$ : 0 ms ... 255 ms
- Pulse length (Q2): 0 ms ... 63 ms
- Output type: PNP, IO-Link
- Connection: Connector M12, 4-pin
- Connection diagram: Cd-244


Operating mode <sup>3)</sup>	Key feature of the object	Background suppression	Object height min.	Object width min.	Radius of the object contour	Sensing range	Model name	Part no.	
	rounded edges			≥ 20 mm	2 mm 5 mm	30 mm 35 mm			
Packaging	rounded out body and prism shaped	≥ 80 mm	≥ 50 mm	≥ 30 mm	5 mm	30 mm			
Packaging "Oversize Fit"	shiny, prismatic edges		20 mm	40 mm	WTD20EC-V2499	1073668			
Folded Box	edges	≥ 60 mm	mm ≥ 30 mm	≥ 60 mm ≥ 30 mm		1 mm	30 +/-		
Folded Box "Slim Fit"	edges in un- even surfaces			≥ 10 mm	10 mm 2 mm	2 mm			


<sup>1)</sup> The SOPAS-ET software makes it possible to customize the DeltaPac product properties. For more information about this software, go to www.sick.de/DeltaPac. <sup>2)</sup> See "Object speed in detail".


<sup>2)</sup> See "Technical information" online on the product detail page at "Downloads" in the section "Literature".

#### Dimensional drawings (Dimensions in mm (inch))


#### WTD20E-V/W24xx, connector









#### WTD20E-V/W11xx, cable






- ① Standard direction
- 2 Center of optical axis, sender
- ③ Centre of optical axis, receiver (first energy scale)
- ④ Centre of optical axis, receiver (second energy scale)
- (5) Optical axis, receiver
- © LED indicator orange: status of received light beam, presence signal Q1
- ⑦ Status indicator LED green: power on
- ⑧ Mounting hole
- Onnection (rotatable)
  Onnection (rotatable)




1 Standard direction

- 2 Center of optical axis, sender
- ③ Centre of optical axis, receiver (first energy scale)
- ④ Centre of optical axis, receiver (second energy scale)
- (5) Optical axis, receiver
- 6 LED indicator orange: status of received light beam, presence signal Q1
- ⑦ Status indicator LED green: power on
- 8 Mounting hole
- Onnection (rotatable)
  Onnection
  Onnection

#### **Connection diagram**





#### Sensing range in detail



#### Object speed in detail


#### WTD20E, rounded edges






#### Parameter example, dimensions in mm (inch)

Object width	Object radii	Object speed min.	Object speed max.
75 (2.95)	2 (0.08)	0.15 m/s	1.1 m/s
125 (4.92)	5 (0.20)	0.25 m/s	1.2 m/s



#### WTD20E, rounded out body and prism shaped

Object speed v in m/s 3.0 2.5 2.0 R<sub>5</sub> 1.5 R20 1.0 R20 0.5 R5 0 250 (9.84) 50 100 150 200 300 (1.97) (3.94) (5.91) (7.87) (11.81) Object width w in mm (inch)



#### Parameter example, dimensions in mm (inch)


Object width	Object radii	Object speed min.	Object speed max.
200 (7.87)	5 (0.20)	0.25 m/s	3.0 m/s
250 (9.84)	20 (0.79)	0.75 m/s	3.0 m/s

= R5, Radii of 5 mm


••••• = R20, Radii of 20 mm 

= Working range

= Maximal working range









Object width	Object radii	Productivity min.	Productivity max.
60	5	0.26 m/s	0.77 m/s
(2.36)	(0.20)	(0.85 feet/s)	(2.53 feet/s)
60	20	0.25 m/s*	0.25 m/s*
(2.36)	(0.79)	(0.82 feet/s*)	(0.82 feet/s*)


\* Thanks to optimized sensor logic, it is possible to make use of the maximum operating range in the case of "Oversize Fit" Packaging format for glossy, round, and prism-shaped edges.

Note: Object speeds must be adhered to with precision. A tolerance of just +/- 0.03 m/s is permitted.




WTD20E, edges





= Working range


= Maximal working range



Parameter example, dimensions in mm (inch)


Object width	Object radii	Object speed min.	Object speed max.
25 (0.98)	1 (0.04)	0.05 m/s	0.26 m/s
75 (2.95)	2 (0.08)	0.08 m/s	0.6 m/s

#### WTD20E, edges in uneven surfaces



= R1, Radii of 1 mm R2, Radii of 2 mm

= Maximal working range



#### Parameter example, dimensions in mm (inch)

Object width	Object radii	Productivity min.	Productivity max.
10	1	0.05 m/s*	0.6 m/s*
(0.39)	(0.04)	(0.16 feet/s*)	(1.97 feet/s*)

\* Thanks to optimized sensor logic, the sensor can be operated with a switch-on and switch-off delay of 1 ms in the case of the "Slim Fit" Folded Box format for edges on uneven surfaces. The operating range equates to the maximum operating range in this case.

Note: In applications, shiny embossing must be avoided by installing the sensors as appropriate. Embossing and shiny surfaces themselves do not restrict how the sensor operates.

#### Accessories DeltaPac

#### Plug connectors and cables

Connecting cable (female connector-open) M12, 4-pin, PVC

#### • Enclosure rating: IP 67

Figure	Connection type head A	Connection type head B	Cable length	Model name	Part no.
			2 m	DOL-1204-G02M	6009382
	Female connector, M12, 4-pin, straight	Cable	5 m	DOL-1204-G05M	6009866
		Cable	10 m	DOL-1204-G10M	6010543
			15 m	DOL-1204-G15M	6010753
		Cable	2 m	DOL-1204-W02M	6009383
	Female connector, M12,		5 m	DOL-1204-W05M	6009867
4-pin, angled	4-pin, angled		10 m	DOL-1204-W10M	6010541
te -			15 m	DOL-1204-W15M	6036474

Connection cable (male-female connector) M12, 4-pin, PVC

#### • Enclosure rating: IP 67

Figure	Connection type head A	Connection type head B	Cable length	Model name	Part no.
	Female connector, M12, 4-pin, straight		2 m	DSL-1204-G02M	6022567
			5 m	DSL-1204-G05M	6022569
		Connector, M12, 4-pin, straight	0.6 m	DSL-1204-G0M6	6022565
0			10 m	DSL-1204-G10M	6034406
			1.5 m	DSL-1204-G1M5	6034822
			20 m	DSL-1204-G20M	6034407

#### Universal bar clamp systems

Figure	Description	Material	Model name	Part no.
S.	Universal bar clamp for mounting bars with 12 mm diameter	Zinc diecast	BEF-KHS-KH3	5322626
6	Plate N10 for universal clamp bracket	Zinc plated steel (sheet), Diecast zinc (clamp)	BEF-KHS-N11N	2071081
	Mounting bar, straight, 200 mm	Steel, zinc coated	BEF-MS12G-A	4056054
	Mounting bar, straight, 300 mm	Steel, zinc coated	BEF-MS12G-B	4056055
$\langle$	Mounting bar, L-shaped, 150 mm x 150 mm	Steel, zinc coated	BEF-MS12L-A	4056052
	Mounting bar, L-shaped, 250 x 250 mm	Steel, zinc coated	BEF-MS12L-B	4056053
5	Mounting bar, Z-shaped, 150 mm x 70 mm x 150 mm	Steel, zinc coated	BEF-MS12Z-A	4056056
	Mounting bar, Z-shaped, 150 mm x 70 mm x 250 mm	Steel, zinc coated	BEF-MS12Z-B	4056057
0	Bar clamp for bar diameter of 12 mm (fix- ing the mounting rod)	Aluminum	BEF-RMC-D12	5321878

#### **Cleaning agent**


Figure	Description	Model name	Part no.
	Plastic cleaner and care product, anti-static	Plastic cleaner	5600006
	35 cm x 35 cm	Lens cloth	4003553

#### Other accessories


Figure	Model	Model name	Part no.
	1.0 - 7.0 mm	Radius gauge	5328155
	7.0 - 15.0 mm	Radius gauge	5328157
	15.5 - 25.0 mm	Radius gauge	5328158

DOL-1204-WxxM


#### Dimensional drawings plug connectors and cables DOL-1204-GxxM



#### DSL-1204-GxxM, DSL-1204-GxMx



#### 26.5 (1.04) 12 (0.47) M12 × 1 1.5 (0.06 3/blu 6 2/wht 31 (1.22) 12 (0.47)



44,3

⊕∳⊕


13


 $\oplus$ 

19,5


49,5

Dimensional drawings universal bar clamp systems BEF-KHS-KH3





1.5 (0.06) x 45°




# 2,5

35



**BEF-KHS-N11N** 

Ma



BEF-MS12L-(N)A: A = 200 mm, B = 150 mm BEF-MS12L-(N)B: A = 250 mm, B = 250 mm

BEF-MS12G-(N)A: A = 200 mm BEF-MS12G-(N)B: A = 300 mm


1.5 (0.06) x 45°

A

BEF-MS12Z-A BEF-MS12Z-B


BEF-MS12G-B

Ø 12 (Ø 0.47)




BEF-MS12Z-(N)A: A = 150 mm, B = 70 mm, C = 150 mm BEF-MS12Z-(N)B: A = 150 mm, B = 70 mm, C = 250 mm BEF-MS12L-(N)B: A = 250 mm, B = 2

BEF-RMC-D12



### WWW.MYSICK.COM - SEARCH ONLINE AND ORDER

Search online quickly and safely - with the SICK "Finders"



**Product Finder:** We can help you to quickly target the product that best matches your application.

**Applications Finder:** Select the application description on the basis of the challenge posed, industrial sector, or product group.

**Literature Finder:** Go directly to the operating instructions, technical information, and other literature on all aspects of SICK products.

Efficiency – with the E-Commerce-Tools from SICK



#### Find out prices and availability

Determine the price and possible delivery date of your desired product simply and quickly at any time.

#### Request or view a quote

You can have a quote generated online here. Every quote is confirmed to you via e-mail.

#### Order online

You can go through the ordering process in just a few steps.

### FOR SAFETY AND PRODUCTIVITY: SICK LIFETIME SERVICES

SICK LifeTime Services is a comprehensive set of high-quality services provided to support the entire life cycle of products and applications from system design all the way to upgrades. These services increase the safety of people, boost the productivity of machines and serve as the basis for our customers' sustainable business success.





#### Consulting & Design

Globally available experts for cost-effective solutions



Product & System Support Fast and reliable, by telephone or on location



Verification & Optimization

Checks and recommendations for increased availability

# PETROFS I

Upgrade & Retrofits Uncovers new potential for machines and systems



### Training & Education

Employee qualification for increased competitiveness

### SICK AT A GLANCE

SICK is a leading manufacturer of intelligent sensors and sensor solutions for industrial applications. With almost 7,000 employees and over 50 subsidiaries and equity investments as well as numerous representative offices worldwide, we are always close to our customers. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in various industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services round out our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

#### Worldwide presence:

Australia, Austria, Belgium, Brazil, Canada, Chile, China, Czech Republic, Denmark, Finland, France, Germany, Great Britain, Hungary, India, Israel, Italy, Japan, Malaysia, Mexico, Netherlands, New Zealand, Norway, Poland, Romania, Russia, Singapore, Slovakia, Slovenia, South Africa, South Korea, Spain, Sweden, Switzerland, Taiwan, Thailand, Turkey, United Arab Emirates, USA, Vietnam.

Detailed addresses and additional representatives -> www.sick.com

