



FLOWSIC600-XT

CUSTODY TRANSFER NATURAL GAS MEASUREMENT WITH
INTELLIGENT DIAGNOSTIC FUNCTIONS

Gas flow meters

SICK
Sensor Intelligence.

FLAWSIC600-XT: THE PERFECT MATCH

As the market leader for reliable and highly precise ultrasonic gas flow measuring instruments, the question we have to ask ourselves is this: How can we get even stronger? And the answer is actually rather simple – the way for us to improve is to listen attentively to the individual requirements of the people that use our products and adapt them accordingly.

With four device versions available, the FLOWSIC600-XT can take on any challenge – whether it is being used as a stand-alone or system solution – and delivers best measurement performance. Its trend-setting design houses some impressive and innovative internal features: i-diagnostics™ for smart application diagnostics with a built-in solution wizard, and PowerIn Technology™, which continues to take measurements for up to three weeks in the event of a mains voltage failure. The FLOWSIC600-XT features an ideal combination of maximum measurement accuracy, long-term stability, and unparalleled operational safety, yet is not at all complicated to use.





Measurement data reliability and availability

The FLOWSIC600 flow measurement technology already provided absolute long-term stability in extreme ambient conditions, and now the FLOWSIC600-XT combines the features of its predecessor with unprecedented usability. Throughout its entire service life, it meets every requirement for safe, stable, and custody transfer gas quantity measurement. Measurement and diagnostics data as well as status changes can be recorded permanently in six accessible data archives. The FLOWSIC600-XT further ensures that measurements continue to be taken and data is stored even in the event of a mains voltage failure, thanks to PowerIn Technology™.

Simple device integration – even in compact systems

Here at SICK in Germany, we are constantly further developing the ultrasonic technology. The FLOWSIC600-XT boasts the best measurement technology available today, meaning it delivers highly precise measurement results. It is MID certified and compliant with ISO 17089 and AGA9 and compatible with its predecessor FLOWSIC600. It can be integrated successfully into any system. Plus, the new FLOWSIC600-XT Forte meets the requirements of compact installations and is certified to OIML R 137 class 0.5.

Quick and easy device commissioning and checking


i-diagnostics™ helps make device commissioning and checking quick and easy. Furthermore i-diagnostics™ provides extended flow meter and application diagnostics during operation. Should maintenance ever be required, the intelligent solution wizard provides support. The built-in infrared interface means measured value and diagnostics data can be accessed in no time, making servicing quick and efficient.

Easy and fast data access

i-diagnostics™ – effective and efficient device and application diagnostics

Automatic measured value correction for changing operating conditions


PowerIn Technology™ – data security guaranteed



FLWSIC600-XT – ALWAYS THE RIGHT GAS FLOW METER FOR YOUR APPLICATION


Every ultrasonic gas flow meter of the FLOW SIC600-XT product family is designed for custody transfer gas flow measurement and satisfy the requirements of all current national and international standards. Four device variants are available, whereby every gas flow meter satisfies very special performance requirements. The selection requirements on a gas flow meter are not always the same. This performance-oriented classifica-

tion of the FLOW SIC600-XT, -XT Forte, -XT 2plex and -XT Quatro is therefore helpful as the first step in focusing and solving tasks and meeting customer requirements in a unique manner. No matter which type you chose, every FLOW SIC600-XT can be easily installed into all custody transfer applications with a nominal width between 3 and 48 inches. Connection to all conventional flow computers on the market is also easy.



FLWSIC600-XT

The FLOW SIC600-XT is the proven all-rounder for all natural gas custody transfer applications. 15 years of field experience with the FLOW SIC600 flowed into this 4-path technology.



FLWSIC600-XT Forte

A lot of meter for so little space. The FLOW SIC600-XT Forte offers 8 paths on two different path levels thereby delivering the highest measurement accuracy. It is automatically the first choice for installations in plants with short inlet and outlet zones.



FLWSIC600-XT 2plex

The very compact FLOW SIC600-XT 2plex combines a gas flow meter for custody transfer with a control measurement device, and features extended diagnostic functionality thanks to its additional independent measurement path.



FLWSIC600-XT Quatro


For redundant measurements in custody transfer of natural gas, the FLOW SIC600-XT Quatro combines two measurement devices in one – with an installation length equivalent to that of a single device.

GAS QUALITY INDICATOR (GQI)*

Today's gas market is served by a large number of different gas suppliers. With FLOWSIC600-XT, plant and network operators are prepared for this challenge. The gas flow meter is not only officially approved for up to 30% hydrogen content in the natural gas (according to MID), it comes with a Gas Quality Indicator that allows the hydrogen content in the natural gas to be monitored. If the configured limit value is exceeded due to fluctuations in the gas qualities, the FLOWSIC600-XT reports this automatically to a control center. This enables changes in the hydrogen content and therefore also the heating value to be

detected in real time and substantial savings in time and costs to be achieved.

The Gas Quality Indicator, which is based on the i-diagnostic™ technology, assists in optimizing the network balance. It thereby makes a significant contribution to guaranteeing the contractually agreed gas qualities when measuring the gas quality using a gas chromatograph or measuring the hydrogen content is not possible.



* not yet available in all sales regions (as at 03/2023)

FLOWgate™ – THE INTUITIVELY DESIGNED OPERATING SOFTWARE


FLOWgate™ intelligently links the diagnostic data and presents them in a processed form.

The quick status function provides immediate information about the current status of the application, and if a warning limit is reached, the solution wizard can be used to analyze the problem at the click of a button. In order to get a quick overview or analysis, each user can put together measured values and diagnostics parameters as required in the measure value overview, and then amend or save their overview. FLOWgate™ provides online or offline access to the FLOWSIC600-XT and

therefore to all the measured value and diagnostic data at any time via a PC or a tablet.

The graphic preparation of trend analyses simplifies evaluation of the measurement sequence and gives information about changes to the process. The report manager can be used to create compact diagnostic, maintenance and calibration reports at any time.

Different assistance functions, such as for commissioning, considerably simplify device operation.



THE PERFECT MATCH



More information

- Fields of application 9
- Detailed technical data 9
- Measuring ranges 12
- Ordering information 13
- Dimensional drawings 13
- Mounting instructions 17

Product description

As the successor to the successful FLOWSIC600, the FLOWSIC600-XT ultrasonic gas flow measuring instrument is setting new standards in its market segment. The FLOWSIC600-XT is available in variants with 4, 4+1, 4+4, and 8 measurement paths to meet the requirements of every application, whether it is being used as a stand-alone or system solution. In addition to the OIML R 137 Class 1.0 requirements, the FLOWSIC600-XT meets the requirements of Class 0.5

At a glance

- User-friendly product family
- Automatic correction of pressure and temperature influences
- Available for all operating conditions
- PowerIn Technology™ for reliable backup operation
- Intelligent application diagnostics with i-diagnostics™

Your benefits

- Low measurement uncertainty in every application
- High measurement data reliability and availability
- The right ultrasonic gas flow meter for every application – without compromise

and AGA9 in their entirety. The FLOWSIC600-XT contains i-diagnostics™ – an intelligent application diagnostics function – and PowerIn Technology™, which enables continuous measurement operation for up to three weeks in the event of a mains voltage failure. These functions help ensure usability and unparalleled operational safety – and what's more, the equipment offers the very best possible measurement accuracy and long-term stability.

- Can be extended to include flow computers using connect-and-go technology
- Measuring capability up to 30% H₂ in the natural gas
- Gas Quality Indicator for quantifying the H₂ content

- Simple device integration – even in compact systems
- Quick and easy commissioning and checking
- Cost-effective quantification of the H₂ content in natural gas

→ www.sick.com/FLWSIC600-XT
 For more information, simply visit the above link to obtain direct access to technical data, CAD design models, operating instructions, software, application examples, and much more.



Fields of application

- Custody transfer measurement of natural gas with up to 30% H₂
- Transport and storage of gas
- Onshore and offshore applications
- Gas production applications with H₂S and CO₂ content

Detailed technical data

The precise device specifications and product performance data may vary and are dependent on the respective application and customer specifications.

System

Measurands	Volumetric flow, a. c., volume a. c., gas velocity, speed of sound, optional volume correction via integrated EVC	
Number of measuring paths	4 4+1 (2plex) 4+4 (Quatro) 8 (Forte) 2 (without metrological approval)	
Measurement principle	Ultrasonic transit time difference measurement	
Measuring medium	Natural gas (with up to 30% hydrogen), air, natural gases containing increased levels of CO ₂ , N ₂ , H ₂ S, O ₂	
Measuring ranges	Q _{min}	176 cf/h ... 26,456 cf/h
	Q _{max}	35,314 cf/h ... 4,237,760 cf/h
	Measuring ranges depend on nominal pipe size	
Repeatability	≤ 0.05% of the measured value (typical) ≤ 0.1% of the measured value for 2-path type	
Accuracy	Typical error limits Q ₁ ... Q _{max} (Q _{min} ... Q ₁)	
	4-path and 8-path type	≤ ± 0.5% (± 1.0%) dry calibrated
	4-path and 8-path type	≤ ± 0.2% (± 0.5%) After flow calibration and adjustment with constant factor. Without uncertainty of the calibration test facility.
	4-path and 8-path type	≤ ± 0.1% (± 0.2%) After flow calibration and adjustment using polynomial or piecewise correction. Without uncertainty of the calibration test facility.
	2-path type	≤ ± 1.5% (± 3.0%) dry calibrated
	2-path type	≤ ± 0.5% (± 1.0%) After flow calibration and adjustment. Without uncertainty of the calibration test facility.
Min. pipe requirements	4-path type	According to OIML Class 1.0: with straight inlet zone of ≥ 10D or ≥ 5D with flow conditioner According to OIML Class 0.5: with straight inlet zone of ≥ 10D and flow conditioner
	8-path type	According to OIML Class 1.0: with straight inlet zone of ≥ 2D According to OIML Class 0.5: with straight inlet zone of ≥ 5D
	2-path type	According to OIML Class 1.5: with straight inlet zone of ≥ 50D or ≥ 20D with flow conditioner For details, see the operating instructions
Diagnostic functions	i-diagnostics™	Integrated device diagnostics, and advanced intelligent device and application diagnostics via FLOWgate™ operating software
Gas temperature	-51 °F ... +356 °F -321 °F ... +446 °F (with offset SPU)	
Operating pressure	0 psi(g) ... 6527 psi(g)	

Nominal pipe size	3" ... 56" / DN 80 ... DN 1400 2" ... 56" / DN 50 ... DN 1400 (2-path type)
Ambient temperature	-51 °F ... +158 °F -76 °F ... +158 °F with electronics enclosure
Storage temperature	-40 °F ... +158 °F -76 °F ... +158 °F meter body only
Ambient humidity	≤ 95% Relative humidity; non-condensing
Conformities	OIML R 137-1&2:2012 (class 0.5) OIML D 11:2013 ISO 17089-1 AGA Report No. 9 MID: 2014/32 / EU PED: 2014/68 / EU AMSE B16.5, B16.47A/B ATEX: 2014/34 / EU EMC: 2014/30 / EU GOST 8.611-2013 GOST 8.733-2011 CPA (JJG1030-2007) CPA: JJG1030-2007 PCEC: GB 3836.1-2010, GB 3836.2-2010, GB 3836.4-2010, GB/T 3836.22-2017
Ex approvals	<p>IECEX Ex db ia op is [ia Ga] IIA/IIC T4 Gb Ex db eb ia op is [ia Ga] IIA/IIC T4 Gb Ex ia op is IIA/IIC T4 Ga</p> <p>ATEX II 2 (1) G Ex db ia op is [ia Ga] IIA/IIC T4 Gb II 2 (1) G Ex db eb ia op is [ia Ga] IIA/IIC T4 Gb II 1G Ex ia op is IIA/IIC T4 Ga</p> <p>NEC/CEC (US/CA) Explosion-proof/non-explosive: CI I, Div. 1 Group D, T4 Ex db ia [ia Ga] IIA T4 Gb / CI I, Zone 1 AEx db ia op is [ia Ga] IIA T4 Gb CI I, Div. 1 Groups B, C, D, T4 Ex db ia [iaGa] IIC T4 Gb / CI I, Zone 1 AEx db ia op is [ia Ga] IIC T4 Gb Intrinsic safety: CI I, Div. 1 Group D T4 Ex ia IIA T4 Ga / CI I, Zone 0, AEx ia op is IIA T4 Ga CI I, Div. 1 Groups A, B, C, D, T4 Ex ia IIC T4 Ga / CI I, Zone 0, AEx ia op is IIC T4 Ga</p>
Enclosure rating	IP66 / IP67
Analog outputs	1 output: 4 mA ... 20 mA, ≤ 250 Ω Active/passive, galvanically isolated
Digital outputs	4 outputs: 2 x status, 2 x pulse ≤ 30 V, 50 mA Passive, galvanically isolated, open collector or conforming to NAMUR (DIN EN 60947-5-6), f _{max} = 10 kHz
Modbus	✓
Type of fieldbus integration	TCP RTU RS-485 (3x) ASCII RS-485 (3x)
Ethernet	✓
Note	Option
HART	✓
Note	HART master for connecting external pressure and temperature transmitter
Optical interface	✓
Note	Service interface (IR, according to IEC 62056-21)
Serial	✓
Note	Encoder

Operation	Via display and FLOWgate™ software
Dimensions (W x H x D)	See dimensional drawings and tables
Weight	See “Dimensions” table
Material in contact with media	Low temperature carbon steel, stainless steel, duplex steel
Electrical connection	
Voltage	Galvanically isolated: 12 V DC ... 24 V DC Intrinsic safety: 6 V DC ... 16 V DC PowerIn Technology™ with backup battery (2,400 mAh, 10.8 V), optional
Power consumption	0.45 W ... 2.45 W Depending on the selected electronics configuration
Integrated components	Integrated pressure sensor and temperature sensor for correcting pressure and temperature influences (option)

Volume correction

Correction method	PTZ (optionally integrated)
Compressibility	SGERG88 AGA 8 Gross method 1 AGA 8 Gross method 2 AGA NX-19 AGA NX-19 mod. NX-19 mod. (GOST) GOST 30319.2-2015 Fixed value
Data archives	1 diagnostic archive (6,000 entries) 2 configurable measuring period archives (6,000 entries each)
Log books	Event log book (1,000 entries) Parameter log book (200 entries) Metrology log book (50 entries)

Measuring ranges

Measuring ranges, imperial, conversion of MID-approved values into imperial units (rounded)

Nominal size	Extended flow range according to MID/AGA9 and OIML Class 0.5*				
	Standard flow range according to MID/AGA9				Maximum flow rate for non-custody application cf/h Extended Q _{max}
	Extended minimum flow rate	Standard minimum flow rate	Transition flow rate	Maximum flow rate	
	cf/h	cf/h	cf/h	cf/h	
	Extended Q _{min}	Standard Q _{min}	Q _t	Standard Q _{max}	
3" (DN 80)	180	280	1,400	23,000	35,000
4" (DN 100)	290	460	2,300	35,300	56,000
6" (DN 150)	570	710	3,500	88,000	106,000
8" (DN 200)	710	1,130	5,700	141,300	159,000
10" (DN 250)	880	1,800	8,500	230,000	247,000
12" (DN 300)	1,200	2,300	10,900	276,000	283,000
14" (DN 350)	1,600	2,800	14,800	353,000	354,000
16" (DN 400)	2,100	4,200	19,400	459,000	495,000
18" (DN 450)	3,500	4,600	24,700	565,000	602,000
20" (DN 500)	4,600	7,100	30,000	706,000	708,000
22" (DN 550)	5,300	9,200	35,000	848,000	850,000
24" (DN 600)	6,400	11,300	42,000	989,000	1,133,000
26" (DN 650)	8,500	15,900	49,000	1,130,000	1,240,000
28" (DN 700)	9,900	23,000	60,000	1,271,000	1,420,000
30" (DN 750)	11,300	23,000	67,000	1,413,000	1,590,000
32" (DN 800)	12,700	28,300	78,000	1,519,000	1,770,000
34" (DN 850)	14,200	31,800	88,000	1,660,000	1,950,000
36" (DN 900)	15,900	35,300	99,000	1,801,000	2,337,000
38" (DN 950)	17,700	38,800	109,000	1,978,000	2,479,000
40" (DN 1000)	19,500	42,400	120,000	2,119,000	2,833,000
42" (DN 1050)	21,200	45,900	134,000	2,296,000	3,010,000
44" (DN 1100)	23,000	49,400	145,000	2,472,000	3,187,000
46" (DN 1150)	24,800	53,000	159,000	2,543,000	3,364,000
48" (DN 1200)	26,600	56,500	170,000	2,825,000	3,541,000
52" (DN 1300)	31,800	60,000	198,000	3,178,000	3,885,000
56" (DN 1400)	35,300	63,600	230,000	3,532,000	4,238,000

For an installation configuration with flow conditioner, the maximum allowed gas velocity in the pipe is limited to 131 ft/s.


* Q_{min} values may vary (see OIML R137 certificate)

Ordering information


Our regional sales organization will be glad to advise you on which device configuration is best for you.

Dimensional drawings


FLWSIC600-XT and FLWSIC600-XT Forte



FLWSIC600-XT 2plex and FLWSIC600-XT Quatro



FLWSIC600-XT: 3" type for up to Class 600 / PN100 pressure levels



Nominal pipe size	Connection flange	Standard	Weight ¹⁾	Length (A)	Hight ²⁾ (B)	Flange diameter (C)	Width of measuring section (D)	Internal diameter (E)	
			[lbs]	[inch]	[inch]	[inch]	[inch]	[inch]	
3"	Cl. 150	ANSI B16.5	275.58	15.75	17.87	7.48	8.07	2.87	
	Cl. 300		286.60		17.87				8.27
	Cl. 600		286.60		17.87				8.27
	Cl. 900		286.60		18.15				9.45
DN 80	PN 16	DIN 2633	233.69	15.75	17.87	7.87	8.07	2.87	
	PN 63	DIN 2636	233.69		17.87				8.46
	PN 100	DIN 2637	233.69		17.87				9.06
4"	Cl. 150	ANSI B16.5	401.24	19.69	19.29	9.06	9.76	3.74	
	Cl. 300		418.88		19.29				10.04
	Cl. 600		440.93		19.29				10.83
	Cl. 900		242.51		19.29				11.42
DN 100	PN 16	DIN 2633	392.42	19.69	19.29	8.66	9.76	3.74	
	PN 63	DIN 2636	414.47		19.29				9.84
	PN 100	DIN 2637	414.47		19.29				10.43
6"	Cl. 150	ANSI B16.5	282.19	17.72	21.26	11.02	12.99	5.59	
	Cl. 300		319.67		21.26				12.60
	Cl. 600		374.79		21.26				13.98
	Cl. 900		524.70	29.53	21.26				14.96
DN 150	PN 16	DIN 2633	308.65	17.72	21.26	11.22	12.99	5.59	
	PN 63	DIN 2636	357.15		21.26				13.58
	PN 100	DIN 2637	388.01		21.26				13.98
8"	Cl. 150	ANSI B16.5	562.18	23.62	24.29	13.58	16.34	7.48	
	Cl. 300		608.48		24.29				14.96
	Cl. 600		696.66		24.29				16.54
	Cl. 900		793.66		24.29				18.50
DN 200	PN 16	DIN 2633	573.20	23.62	24.29	13.39	16.34	7.48	
	PN 63	DIN 2636	656.98		24.29				16.34
	PN 100	DIN 2637	793.66		24.29				16.93
10"	Cl. 150	ANSI B16.5	831.14	29.53	27.20	15.94	16.54	9.25	
	Cl. 300		906.10		27.20				17.52
	Cl. 600		1069.24		27.20				20.08
	Cl. 900		1164.04		27.20				21.46
DN 250	PN 16	DIN 2633	844.37	29.53	27.20	15.94	16.54	9.25	
	PN 63	DIN 2636	956.81		27.20				18.50
	PN 100	DIN 2637	1071.45		27.20				19.88
12"	Cl. 150	ANSI B16.5	981.06	35.43	28.66	19.09	19.69	10.63	
	Cl. 300		1089.08		28.66				20.47
	Cl. 600		1234.59		28.66				22.05
	Cl. 900		1424.98		26.97				24.02
DN 300	PN 16	DIN 2633	972.24	35.43	28.66	18.11	19.69	10.63	
	PN 63	DIN 2636	1122.15		28.66				20.87
	PN 100	DIN 2637	1289.70		25.12				23.03

Nominal pipe size	Connection flange	Standard	Weight ¹⁾	Length (A)	Height ²⁾ (B)	Flange diameter (C)	Width of measuring section (D)	Internal diameter (E)
			[lbs]	[inch]	[inch]	[inch]	[inch]	[inch]
14"	Cl. 150	ANSI B16.5	1047.19	41.34	25.28	21.06	21.26	12.40
	Cl. 300		1322.77		26.26	23.03		
	Cl. 600		1488.12		26.65	23.82		
	Cl. 900		1873.93		27.56	25.20		
DN 350	PN 16	DIN 2633	1047.19		25.00	20.47		
	PN 63	DIN 2636	1377.89		26.57	23.62		
	PN 100	DIN 2637	1653.47		27.76	25.79		
For all meters ≥ 16" an installation length of 3D is optionally available								
16"	Cl. 150	ANSI B16.5	1418.50	30.00	33.23	23.43	24.02	14.17
	Cl. 300		1675.51		33.23	25.59		
	Cl. 600		1889.36		33.23	26.97		
	Cl. 900		2041.48	31.50	27.76	27.76		
DN 400	PN 16	DIN 2633	1450.64	30.00	33.23	22.83		
	PN 63	DIN 2636	1750.47		33.23	26.38		
18"	Cl. 150	ANSI B16.5	1455.05	32.28	29.69	25.00	24.41	16.34
	Cl. 300		1675.51		31.18	27.95		
	Cl. 600		2116.44		32.28	29.33		
	Cl. 900		2866.01	35.43	32.68	30.91		
DN 450	Data on request							
20"	Cl. 150	ANSI B16.5	1653.47	35.51	32.09	27.56	26.38	17.72
	Cl. 300		2050.30		33.58	30.51		
	Cl. 600		2380.99		34.33	32.09		
	Cl. 900		3306.93	39.37	35.12	33.66		
DN 500	PN 16	DIN 2633	1543.23	35.51	32.40	28.15		
22"	Data on request							
DN 550	Data on request							
24"	Cl. 150	ANSI B16.5	2403.04	39.02	36.50	32.09	29.92	21.26
	Cl. 300		3064.42		38.50	36.02		
	Cl. 600		3560.46		38.98	37.01		
	Cl. 900		4629.70	47.24	40.94	40.94		
DN 600	PN 16	DIN 2633	2237.69	39.02	37.01	33.07		
26"	Cl. 150	ASME B16.47	3251.81	41.34	37.99	34.25	32.60	23.03
	Cl. 300		4023.43		40.00	38.27		
	Cl. 600		4629.70		40.87	40.00		
	Cl. 900		5511.55	49.21	42.24	42.76		
DN 650	Data on request							
28"	Cl. 150	ASME B16.47	4299.01	43.31	40.43	36.50	33.94	24.80
	Cl. 300		4905.28		42.52	40.75		
	Cl. 600		5401.32		43.31	42.24		
	Cl. 900		6613.86	51.18	45.28	46.02		
DN 700	Data on request							


Nominal pipe size	Connection flange	Standard	Weight ¹⁾	Length (A)	Hight ²⁾ (B)	Flange diameter (C)	Width of measuring section (D)	Internal diameter (E)
			[lbs]	[inch]	[inch]	[inch]	[inch]	[inch]
30"	Cl. 150	ASME B16.47	4839.14	45.28	42.52	38.78	35.51	26.57
	Cl. 300		5610.76		44.69	42.99		
	Cl. 600		6217.03		45.43	44.49		
	Cl. 900		7385.48	53.15	47.44	48.50		
DN 750	Data on request							
32"	Cl. 150	ASME B16.47	5478.48	47.24	45.08	41.77	38.54	28.35
	Cl. 300		6250.10		46.85	45.28		
	Cl. 600		6856.37		47.72	47.01		
	Cl. 900		8377.56	55.15	50.08	51.77		
DN 800	Data on request							
34"	Data on request							
DN 850	Data on request							
36"	Cl. 150	ASME B16.47	6889.44	49.21	49.21	46.02	42.60	31.889
	Cl. 300		7771.29		51.18	50.00		
	Cl. 600		8487.79		52.09	51.77		
	Cl. 900		11519.14	57.09	54.96	57.54		
DN 900	Data on request							
38"	Cl. 150	ASME B16.47	8377.56	51.10	51.57	48.74	45.67	33.66
	Cl. 300		8212.21		50.20	46.02		
	Cl. 600		9479.87		52.17	50.00		
	Cl. 900		Data on request		55.94	57.52		
DN 950	Data on request							
40"	Cl. 150	ASME B16.47	8432.67	53.15	53.50	50.75	47.76	35.43
	Cl. 300		9094.06		52.52	48.78		
	Cl. 600		10306.60		54.13	52.01		
	Cl. 900		Data on request		57.87	59.53		
DN 1000	Data on request							
42"	Cl. 150	ASME B16.47	10306.60	57.09	55.71	52.99	49.65	37.20
	Cl. 300		10251.48		54.57	50.75		
	Cl. 600		12015.18		56.85	55.28		
	Cl. 900		Data on request		59.96	61.50		
DN 1050	Data on request							
44"	Data on request							
DN 1100	Data on request							
46"	Data on request							
DN 1150	Data on request							
48"	Cl. 150	ASME B16.47	14109.57	62.99	61.97	59.49	55.75	42.52
	Cl. 300		14274.19		61.10	57.76		
	Cl. 600		17306.27		63.85	62.76		
	Cl. 900		26675.90	74.80	67.36	70.28		
DN 1200	Data on request							

¹⁾ Devices with single SPU; devices with double SPU: weight + 7 kg

²⁾ Optional neck extension: B + 200 mm

Mounting instructions


Installation of the FLOWSIC600-XT in the pipeline for unidirectional use (minimum requirements)



- ① FLOWSIC600-XT
- ② Temperature measuring point
- ③ Flow conditioner

Configuration A			Configuration B						
Number of measuring paths	OIML R 137	A	Number of measuring paths	OIML R 137 A ¹⁾	A	B	C	D	E
4	Class 1.0	10 DN	4	Class 1.0	5 DN	2 DN	3 DN	3 DN	1 ... 5 DN
8	Class 1.0	2 DN	4	Class 0.5	10 DN	2 DN	8 DN	3 DN	1 ... 5 DN
8	Class 0.5	5 DN	8	Class 1.0	5 DN	2 DN	3 DN	3 DN	1 ... 5 DN
2	Class 1.5	50 DN	2	Class 1.5	20 DN	10 DN	10 DN	3 DN	1 ... 5 DN
Number of measuring paths	AGA Report 9, 4 th Edition, 2022	A	Number of measuring paths	AGA Report 9 ²⁾	A	B	C	D	E
4	"Metering package performance" according to § 6.3	10 DN	4	"Metering package performance" according to § 6.3	10 DN	5 DN	5 DN	3 DN	2 ... 5 DN
8	"Metering package performance" according to § 6.3	5 DN	8	"Metering package performance" according to § 6.3	5 DN	2 DN	3 DN	3 DN	2 ... 5 DN
			¹⁾ Minimum requirements with SICK flow conditioner (PTB type); Installation recommendations for other flow conditioners on request ²⁾ Minimum requirements with CPA50E, CPA55E or SICK flow conditioner (PTB type); installation recommendations for other flow conditioners on request						

Installation of the FLOWSIC600-XT in the pipeline for bidirectional use (minimum requirements)



- ① FLOWSIC600-XT
- ② Alternative temperature measuring points
- ③ Flow conditioner

Configuration A			Configuration B					
Number of measuring paths	OIML R 137	A	Number of measuring paths	OIML R 137 A ¹⁾	A	B	C ³⁾	D
4	Class 1.0	10 DN	4	Class 1.0	5 DN	2 DN	3 DN	3 ... 5 DN
8	Class 1.0	5 DN	4	Class 0.5	10 DN	2 DN	8 DN	3 ... 5 DN
8	Class 0.5	5 DN	8	Class 1.0	5 DN	2 DN	3 DN	3 ... 5 DN
2	Class 1.5	50 DN	t	Class 1.5	20 DN	10 DN	10 DN	3 ... 5 DN
Number of measuring paths	AGA report 9, 4 th Edition, 2022	A	Number of measuring paths	AGA report 9, 4 th Edition, 2022 ²⁾	A	B	C ³⁾	D ⁴⁾
4	“Metering package performance” according to § 6.3	10 DN	4	“Metering package performance” according to § 6.3	10 DN	5 DN	5 DN	3 ... 5 DN
8	“Metering package performance” according to § 6.3	5 DN	8	“Metering package performance” according to § 6.3	6 DN	3 DN	3 DN	3 ... 5 DN
			¹⁾ Minimum requirements with SICK flow conditioner (PTB type); installation recommendations for other flow conditioners on request ²⁾ Minimum requirements with CPA50E, CPA55E or SICK flow conditioner (PTB type); installation recommendations for other flow conditioners on request ³⁾ If C ≥ 5 DN, the temperature measuring point must be located in the pipe section C at a distance of 3 ... 5 DN ⁴⁾ Measuring distances must be calibrated for the temperature measuring point with a thermowell installed					

WORKING WITH SICK IN A DIGITAL WORLD

Making your digital business environment comfortable

Find a suitable solution in next to no time

- Online product catalog
- Application Solver
- Online configurators and selectors

My SICK is your personal self-service portal

- Open around the clock
- Clear product information
- Company-specific price conditions
- Convenience during the ordering process
- Document overview
- Availability and delivery times

Register now:

→ www.sick.com/myBenefits

Even more value

- Digital Customer Trainings → www.sick.com/c/g300887
- Digital Service Catalog → cloud.sick.com
- SICK AppPool → apppool.cloud.sick.com



SERVICES FOR MACHINES AND PLANTS: SICK LifeTime Services

Our comprehensive and versatile LifeTime Services are the perfect addition to the comprehensive range of products from SICK. The services range from product-independent consulting to traditional product services.



Consulting and design
Safe and professional



Product and system support
Reliable, fast, and on-site



Verification and optimization
Safe and regularly inspected



Upgrade and retrofits
Easy, safe, and economical



Training and education
Practical, focused, and professional

SICK AT A GLANCE

SICK is a leading manufacturer of intelligent sensors and sensor solutions for industrial applications. With more than 11,000 employees and over 50 subsidiaries and equity investments as well as numerous agencies worldwide, SICK is always close to its customers. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents, and preventing damage to the environment.

SICK has extensive experience in various industries and understands their processes and requirements. With intelligent sensors, SICK delivers exactly what the customers need. In application centers in Europe, Asia, and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes SICK a reliable supplier and development partner.

Comprehensive services round out the offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

That is “Sensor Intelligence.”

Worldwide presence:

Australia, Austria, Belgium, Brazil, Canada, Chile, China, Czech Republic, Denmark, Finland, France, Germany, Great Britain, Hungary, Hong Kong, India, Israel, Italy, Japan, Malaysia, Mexico, Netherlands, New Zealand, Norway, Poland, Romania, Russia, Singapore, Slovakia, Slovenia, South Africa, South Korea, Spain, Sweden, Switzerland, Taiwan, Thailand, Turkey, United Arab Emirates, USA, Vietnam.

Detailed addresses and further locations → www.sick.com